

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333550-840

Luminaire Tested: **S125RDIP-S850D365U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333550-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S850D365U840-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4789.2 lumens  
Efficiency: N/A  
Efficacy: 136.8 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69
1	103	98	95	91	97	93	90	87	83	81	79	74	73	71	66	65	63	59
2	94	87	81	76	89	82	77	72	74	70	66	66	63	60	59	56	54	51
3	86	77	69	64	81	73	66	61	66	60	56	59	55	51	53	49	47	43
4	79	68	60	54	74	65	58	52	59	53	48	53	48	44	47	44	41	38
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	33
6	67	55	47	41	63	52	45	40	48	41	37	43	38	34	39	35	32	29
7	62	50	42	36	59	48	40	35	43	37	33	39	34	30	36	31	28	26
8	58	45	38	32	55	43	36	31	40	34	29	36	31	27	33	29	25	23
9	54	42	34	29	51	40	33	28	36	30	26	33	28	25	30	26	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8250	8250	8250	8250
5°	9491	8261	7295	8261
10°	10887	8218	6437	8218
15°	11760	8134	5722	8134
20°	12967	8036	5283	8036
25°	15007	7906	4903	7906
30°	16330	7770	4653	7770
35°	13775	7611	4424	7611
40°	9620	7325	4226	7325
45°	7136	6940	4032	6940
50°	5690	6539	3867	6539
55°	4829	6040	3719	6040
60°	4173	5594	3481	5594
65°	3718	5113	2997	5113
70°	3269	4683	2732	4683
75°	2827	4057	2565	4057
80°	2146	3414	2146	3414
85°	1786	2682	2023	2682



TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.5	2.6
10°-20°	359.0	7.5
20°-30°	569.2	11.9
30°-40°	686.4	14.3
40°-50°	613.0	12.8
50°-60°	470.0	9.8
60°-70°	305.5	6.4
70°-80°	148.5	3.1
80°-90°	36.5	0.8
90°-100°	17.5	0.4
100°-110°	107.8	2.3
110°-120°	195.6	4.1
120°-130°	251.0	5.2
130°-140°	270.0	5.6
140°-150°	253.4	5.3
150°-160°	205.0	4.3
160°-170°	132.6	2.8
170°-180°	45.7	1.0
0°-30°	1050.6	21.9
0°-40°	1737.0	36.3
0°-60°	2820.0	58.9
0°-90°	3310.5	69.1
90°-120°	321.0	6.7
90°-150°	1095.4	22.9
90°-180°	1479.0	30.9
0°-180°	4789.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1277	1277	1277	1277	1277	
5°	1464	1274	1125	1274	1464	146
15°	1759	1217	856	1217	1759	504
25°	2106	1110	688	1110	2106	967
35°	1747	965	561	965	1747	1055
45°	781	760	442	760	781	623
55°	429	536	330	536	429	389
65°	243	335	196	335	243	242
75°	113	163	103	163	113	121
85°	24	36	27	36	24	28
90°	9	0	9	0	9	5
95°	8	20	8	20	8	6
105°	106	105	106	105	106	96
115°	196	197	196	197	196	194
125°	280	280	280	280	280	249
135°	348	350	348	350	348	269
145°	404	405	404	405	404	252
155°	443	446	443	446	443	204
165°	468	471	468	471	468	132
175°	479	482	479	482	479	46
180°	482	482	482	482	482	



TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1343.6	1342.8	1344.5	1339.9	1340.3	1333.1	1333.1	1327.7	1320.6	1315.1	1312.6
5°	1464.0	1465.1	1463.0	1455.1	1449.9	1442.0	1433.1	1417.3	1404.2	1391.7	1381.7
7.5°	1588.0	1588.7	1581.9	1579.4	1566.2	1556.5	1536.7	1515.3	1496.3	1472.2	1453.8
10°	1660.1	1659.6	1652.3	1646.5	1635.0	1620.3	1600.9	1575.7	1552.2	1525.9	1500.8
12.5°	1702.1	1700.7	1698.4	1691.4	1680.7	1667.7	1651.2	1626.5	1597.4	1568.7	1539.3
15°	1758.8	1755.0	1748.3	1739.3	1724.1	1708.9	1690.6	1668.6	1640.7	1608.2	1580.9
17.5°	1828.8	1828.9	1818.5	1806.0	1785.3	1758.6	1730.2	1694.7	1656.9	1621.1	1592.1
20°	1886.7	1885.1	1874.6	1850.5	1826.9	1793.3	1760.8	1717.3	1671.1	1624.5	1588.3
22.5°	1969.7	1965.7	1954.8	1923.1	1886.5	1843.3	1793.5	1740.4	1684.6	1631.6	1584.2
25°	2105.9	2102.7	2081.2	2044.6	1993.2	1926.5	1861.5	1788.7	1708.4	1638.7	1580.9
27.5°	2199.0	2195.5	2179.6	2149.1	2101.7	2031.6	1943.6	1846.2	1746.1	1650.1	1566.9
30°	2189.8	2197.7	2195.5	2181.4	2145.8	2082.8	2001.6	1892.0	1772.9	1660.1	1561.0
32.5°	2058.0	2065.1	2083.6	2111.3	2113.4	2088.3	2027.5	1926.3	1803.1	1674.9	1556.4
35°	1747.2	1756.7	1792.3	1848.5	1921.8	1983.2	1995.8	1941.3	1830.6	1692.6	1549.5
37.5°	1343.2	1394.8	1424.8	1483.9	1594.8	1707.7	1816.2	1856.1	1809.1	1685.4	1538.3
40°	1141.0	1153.6	1207.1	1273.7	1367.1	1484.5	1639.2	1750.9	1754.5	1668.6	1520.7
42.5°	976.5	992.5	1029.3	1082.4	1162.4	1279.8	1439.5	1586.9	1655.2	1622.4	1497.6
45°	781.3	793.3	820.1	861.0	922.4	1019.4	1156.8	1327.2	1462.5	1515.4	1435.7
47.5°	641.9	648.3	671.7	702.8	748.2	818.9	925.2	1073.2	1235.5	1349.2	1338.0
50°	566.3	573.7	591.5	615.1	653.4	713.2	798.1	921.3	1088.6	1227.6	1255.4
52.5°	507.6	513.7	524.8	547.1	578.7	624.6	693.2	804.7	955.2	1103.0	1167.2
55°	428.9	433.1	442.0	454.6	479.8	512.8	572.1	649.1	770.8	919.8	1014.1
57.5°	364.2	366.2	371.9	383.5	400.9	425.1	467.9	533.2	620.5	754.6	858.7
60°	323.1	325.1	332.4	340.3	354.0	376.0	409.5	455.1	539.1	649.6	755.1
62.5°	290.3	291.5	294.7	302.6	314.5	331.5	357.9	395.2	461.9	559.1	658.6
65°	243.3	243.9	244.9	251.2	258.5	271.1	288.4	314.6	365.0	438.4	526.4
67.5°	198.2	198.9	202.6	204.8	212.5	219.0	229.2	249.3	284.8	334.3	402.7
70°	173.1	172.5	176.2	178.8	181.5	189.2	196.1	212.4	234.4	272.2	329.3
72.5°	149.6	148.1	149.8	150.7	154.2	159.6	166.3	176.3	193.3	219.2	263.1
75°	113.3	113.8	113.8	114.8	117.4	119.6	121.7	126.9	136.3	153.6	177.2
77.5°	79.5	78.7	80.9	81.2	82.7	85.0	86.8	89.0	92.8	100.0	112.1
80°	57.7	57.7	58.2	59.8	59.3	60.3	62.9	65.0	69.8	73.9	78.2
82.5°	44.2	43.8	44.3	44.6	44.5	45.6	46.6	47.0	48.8	50.9	53.8
85°	24.1	24.1	24.6	24.6	25.1	25.1	25.7	25.7	25.7	26.3	26.8
87.5°	10.9	10.5	10.0	10.0	10.3	11.1	10.6	10.1	10.0	10.0	10.3
90°	8.6	8.3	8.1	7.9	7.6	7.3	6.9	6.5	6.1	5.8	5.2
92.5°	8.0	7.9	7.8	7.7	7.6	7.3	6.9	6.5	6.1	5.8	5.3
95°	7.5	7.5	7.5	7.5	7.5	7.3	6.9	6.5	6.1	5.8	8.7
97.5°	7.5	7.5	7.5	7.5	7.5	8.6	10.8	13.1	15.3	17.6	23.5
100°	7.5	7.8	8.2	8.5	8.8	14.8	26.7	38.5	50.3	62.1	61.8
102.5°	44.9	50.3	55.7	61.1	66.4	70.3	72.5	74.7	77.1	79.3	79.1
105°	106.0	106.1	106.1	106.2	106.3	106.3	106.3	106.3	106.3	106.3	106.3
107.5°	133.6	133.9	134.1	134.4	134.6	134.7	134.7	134.7	134.6	134.6	134.5
110°	152.8	152.7	152.6	152.6	152.5	152.6	152.8	153.0	153.3	153.5	153.3



TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.0	170.1	170.2	170.3	170.4	170.6	170.9	171.2	171.5	171.8	171.7
115°	195.6	196.1	196.6	197.0	197.5	197.9	198.2	198.5	198.8	199.1	199.1
117.5°	223.1	223.3	223.5	223.7	223.9	224.2	224.6	225.0	225.4	225.8	225.5
120°	239.8	240.2	240.7	241.1	241.5	241.8	241.9	242.1	242.3	242.4	242.2
122.5°	255.9	256.3	256.8	257.2	257.7	258.0	258.2	258.3	258.5	258.6	258.5
125°	280.2	280.4	280.7	280.9	281.1	281.4	281.8	282.1	282.4	282.8	282.8
127.5°	300.7	301.3	301.8	302.5	303.1	303.5	303.6	303.8	304.0	304.2	304.2
130°	315.6	316.0	316.4	316.8	317.1	317.5	317.7	317.9	318.2	318.4	318.3
132.5°	329.3	329.6	330.0	330.4	330.8	331.0	331.1	331.1	331.2	331.2	331.4
135°	348.0	348.5	349.0	349.5	349.9	350.2	350.4	350.6	350.7	350.9	351.0
137.5°	366.9	367.3	367.7	368.1	368.5	368.7	368.7	368.7	368.6	368.6	368.7
140°	378.0	378.5	379.0	379.5	379.9	380.1	379.9	379.8	379.6	379.5	379.5
142.5°	388.6	389.1	389.5	390.0	390.5	390.7	390.7	390.6	390.6	390.6	390.5
145°	404.0	404.6	405.1	405.6	406.0	406.2	406.1	406.1	406.0	405.9	405.9
147.5°	416.9	417.5	418.0	418.6	419.2	419.4	419.3	419.2	419.1	419.0	418.9
150°	425.2	425.8	426.5	427.1	427.7	427.9	427.8	427.6	427.5	427.3	427.2
152.5°	432.8	433.4	434.0	434.5	435.2	435.4	435.2	435.0	434.8	434.7	434.5
155°	443.0	443.6	444.2	444.9	445.6	445.8	445.5	445.2	445.0	444.7	444.6
157.5°	451.5	452.1	452.7	453.4	454.0	454.2	453.9	453.7	453.4	453.2	453.2
160°	457.0	457.6	458.2	458.8	459.5	459.6	459.3	459.0	458.7	458.4	458.3
162.5°	461.8	462.5	463.1	463.8	464.5	464.7	464.2	463.8	463.3	462.9	462.8
165°	468.4	469.0	469.6	470.3	470.9	471.0	470.5	470.0	469.5	469.1	469.0
167.5°	472.9	473.6	474.3	475.0	475.7	475.8	475.2	474.7	474.1	473.5	473.5
170°	475.4	476.2	477.0	477.7	478.4	478.4	477.8	477.1	476.5	475.8	475.7
172.5°	477.2	477.9	478.6	479.4	480.1	480.1	479.6	479.0	478.4	477.9	477.7
175°	479.4	480.1	480.8	481.5	482.3	482.3	481.7	481.0	480.4	479.8	479.7
177.5°	480.7	481.2	481.7	482.2	482.7	482.7	482.3	481.9	481.4	481.0	480.9
180°	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5



TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1312.6	1309.7	1304.2	1299.2	1292.9	1287.5	1283.6	1279.1	1273.1	1266.1	1260.2
5°	1370.7	1359.2	1343.9	1330.9	1314.0	1301.0	1287.4	1274.2	1261.1	1244.4	1229.6
7.5°	1435.1	1411.3	1388.2	1359.0	1332.5	1308.9	1286.3	1263.3	1240.9	1217.1	1194.1
10°	1474.5	1445.7	1413.7	1377.0	1343.4	1311.4	1282.1	1253.2	1222.8	1196.1	1167.2
12.5°	1511.5	1474.2	1437.6	1391.3	1351.0	1311.9	1274.6	1238.6	1206.1	1171.3	1140.4
15°	1544.8	1508.1	1467.2	1410.6	1354.4	1307.3	1263.2	1216.6	1176.2	1137.4	1102.8
17.5°	1557.7	1519.2	1471.7	1417.2	1355.9	1296.6	1239.8	1188.6	1141.1	1095.9	1057.0
20°	1552.7	1515.4	1466.6	1414.7	1349.2	1287.4	1226.0	1169.3	1116.4	1068.6	1027.2
22.5°	1540.4	1502.0	1454.9	1400.1	1337.9	1272.2	1206.7	1146.3	1090.8	1041.4	996.2
25°	1522.3	1469.9	1421.6	1368.1	1308.8	1243.9	1176.2	1109.5	1050.4	1000.0	950.7
27.5°	1503.3	1437.8	1376.4	1323.3	1260.7	1202.6	1137.5	1069.1	1006.9	955.6	905.0
30°	1486.1	1412.7	1345.0	1284.8	1225.5	1170.4	1108.5	1041.9	978.0	925.0	873.6
32.5°	1464.7	1386.6	1312.3	1242.7	1185.6	1130.9	1075.0	1011.3	949.0	894.3	842.1
35°	1437.8	1338.2	1257.5	1183.5	1120.0	1067.1	1016.7	965.3	902.9	846.4	795.5
37.5°	1402.6	1289.5	1196.1	1115.6	1048.6	995.4	955.7	908.8	851.8	797.6	750.3
40°	1381.2	1254.3	1152.1	1072.4	1002.1	945.9	908.8	868.9	817.0	766.1	718.9
42.5°	1352.7	1222.0	1107.6	1024.5	953.8	899.8	862.1	827.4	783.9	735.9	685.4
45°	1296.8	1159.4	1039.4	950.2	878.9	825.9	790.7	759.8	726.8	682.8	638.6
47.5°	1224.0	1094.1	968.4	871.1	801.2	752.0	718.0	693.6	669.9	632.5	589.7
50°	1165.7	1040.4	917.7	823.2	748.8	702.2	670.1	650.8	629.2	595.1	559.5
52.5°	1096.9	985.0	864.7	768.3	698.0	654.3	623.6	604.2	586.4	558.7	524.7
55°	988.5	890.4	780.2	692.7	628.2	584.1	554.8	536.4	525.9	502.3	475.6
57.5°	863.3	793.0	695.9	611.5	554.5	511.0	489.5	473.8	462.0	445.2	426.5
60°	776.1	726.8	639.7	559.5	507.1	465.6	446.3	433.1	422.1	408.0	393.2
62.5°	687.5	651.7	575.9	507.1	458.8	424.1	406.0	394.2	381.4	371.9	357.6
65°	569.0	536.9	484.5	430.5	386.0	358.1	345.1	334.6	326.7	316.2	306.2
67.5°	442.5	429.6	393.3	356.2	324.2	299.4	288.1	280.7	271.4	265.0	258.2
70°	365.0	358.7	333.0	308.3	278.4	261.7	251.2	248.0	236.5	230.2	225.5
72.5°	296.2	293.3	278.4	261.4	240.2	225.6	215.9	212.4	205.0	200.0	196.9
75°	202.9	204.0	201.4	190.4	182.5	173.1	164.6	162.6	157.3	153.1	150.5
77.5°	128.4	133.7	133.9	133.4	130.3	124.5	121.0	119.5	114.3	112.7	112.1
80°	88.1	93.8	99.1	98.6	97.6	95.9	93.3	91.8	89.2	87.6	86.5
82.5°	58.8	64.1	68.5	71.3	71.1	69.6	67.8	67.1	66.4	65.3	65.1
85°	27.8	28.9	30.4	34.1	36.7	37.3	36.7	36.2	34.6	35.1	35.6
87.5°	10.6	10.5	10.8	10.6	10.1	12.1	13.2	13.5	12.8	12.1	11.3
90°	4.6	4.0	3.5	2.9	2.2	1.6	1.0	0.4	1.0	1.6	2.2
92.5°	4.7	4.2	3.7	3.7	4.1	4.6	5.0	5.5	5.0	4.6	4.1
95°	11.7	14.7	17.8	19.4	19.6	19.9	20.1	20.3	20.1	19.9	19.6
97.5°	29.5	35.4	41.4	44.2	43.7	43.3	42.9	42.5	42.9	43.3	43.7
100°	61.5	61.2	60.8	60.6	60.3	60.1	59.9	59.6	59.9	60.1	60.3
102.5°	78.9	78.7	78.5	78.3	78.0	77.7	77.4	77.1	77.4	77.7	78.0
105°	106.3	106.3	106.3	106.2	105.9	105.6	105.2	104.9	105.2	105.6	105.9
107.5°	134.3	134.2	134.0	133.9	133.9	133.9	133.9	133.9	133.9	133.9	133.9
110°	153.2	153.0	152.9	152.8	152.8	152.8	152.8	152.8	152.8	152.8	152.8





TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	171.6	171.5	171.4	171.3	171.1	170.9	170.7	170.5	170.7	170.9	171.1
115°	199.0	198.9	198.8	198.6	198.2	197.8	197.4	197.0	197.4	197.8	198.2
117.5°	225.2	224.9	224.6	224.5	224.5	224.5	224.5	224.5	224.5	224.5	224.5
120°	241.9	241.7	241.5	241.4	241.5	241.6	241.6	241.7	241.6	241.6	241.5
122.5°	258.4	258.3	258.2	258.0	257.7	257.4	257.1	256.8	257.1	257.4	257.7
125°	282.8	282.8	282.8	282.5	281.9	281.3	280.7	280.2	280.7	281.3	281.9
127.5°	304.3	304.3	304.4	304.2	303.8	303.4	303.0	302.6	303.0	303.4	303.8
130°	318.2	318.2	318.1	317.9	317.5	317.1	316.7	316.3	316.7	317.1	317.5
132.5°	331.6	331.8	331.9	331.8	331.3	330.9	330.4	330.0	330.4	330.9	331.3
135°	351.2	351.3	351.5	351.3	350.9	350.4	349.9	349.5	349.9	350.4	350.9
137.5°	368.9	369.0	369.2	369.0	368.6	368.2	367.8	367.4	367.8	368.2	368.6
140°	379.6	379.7	379.8	379.7	379.6	379.4	379.3	379.1	379.3	379.4	379.6
142.5°	390.4	390.3	390.1	390.0	389.9	389.9	389.8	389.7	389.8	389.9	389.9
145°	405.9	405.9	405.9	405.8	405.7	405.5	405.4	405.2	405.4	405.5	405.7
147.5°	418.8	418.7	418.6	418.6	418.6	418.7	418.7	418.7	418.7	418.7	418.6
150°	427.0	426.8	426.7	426.7	426.8	427.0	427.2	427.3	427.2	427.0	426.8
152.5°	434.4	434.2	434.0	434.1	434.5	434.8	435.3	435.6	435.3	434.8	434.5
155°	444.4	444.3	444.1	444.3	444.7	445.2	445.8	446.3	445.8	445.2	444.7
157.5°	453.2	453.1	453.1	453.3	453.5	453.8	454.1	454.4	454.1	453.8	453.5
160°	458.2	458.1	458.1	458.3	458.7	459.2	459.7	460.1	459.7	459.2	458.7
162.5°	462.7	462.7	462.6	462.8	463.2	463.7	464.2	464.7	464.2	463.7	463.2
165°	468.9	468.8	468.8	469.0	469.4	469.9	470.4	470.8	470.4	469.9	469.4
167.5°	473.4	473.3	473.2	473.4	473.9	474.4	474.9	475.4	474.9	474.4	473.9
170°	475.6	475.6	475.5	475.7	476.4	476.9	477.5	478.0	477.5	476.9	476.4
172.5°	477.6	477.4	477.3	477.5	478.1	478.6	479.2	479.7	479.2	478.6	478.1
175°	479.6	479.5	479.5	479.7	480.1	480.6	481.1	481.5	481.1	480.6	480.1
177.5°	480.9	480.8	480.7	480.9	481.3	481.6	482.0	482.4	482.0	481.6	481.3
180°	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5



TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1256.0	1250.1	1245.9	1237.5	1231.6	1229.1	1224.6	1223.2	1227.9	1224.6	1224.1
5°	1218.6	1203.5	1191.3	1179.3	1166.2	1157.8	1145.2	1143.2	1139.9	1135.3	1134.2
7.5°	1173.9	1154.1	1138.5	1118.6	1101.3	1087.3	1071.6	1064.2	1060.1	1054.0	1045.8
10°	1143.7	1120.0	1099.0	1079.1	1057.6	1040.4	1024.6	1012.6	1004.7	997.3	994.2
12.5°	1113.9	1089.8	1063.0	1038.8	1014.9	995.4	978.1	970.2	961.5	952.9	945.5
15°	1067.6	1035.6	1006.2	978.5	958.1	937.1	920.3	908.8	895.6	891.9	877.8
17.5°	1018.5	987.1	952.8	923.5	899.8	876.8	858.3	845.2	835.4	821.8	815.3
20°	988.0	950.7	917.2	890.4	864.1	836.9	818.0	807.0	797.6	786.6	781.3
22.5°	955.2	918.8	884.4	853.0	826.4	799.6	786.2	774.7	764.0	753.9	746.9
25°	907.2	870.5	834.2	801.7	774.0	754.6	738.8	725.7	719.9	710.0	702.7
27.5°	859.7	820.6	783.0	750.7	728.9	709.7	696.8	686.4	676.0	667.3	661.0
30°	829.0	789.2	748.3	722.6	699.5	681.2	667.0	657.0	649.1	641.3	636.6
32.5°	798.4	757.3	721.0	693.2	671.4	655.6	641.0	631.5	623.2	614.5	608.9
35°	749.3	707.4	678.0	650.8	629.2	614.6	604.6	591.0	584.1	577.8	572.1
37.5°	703.7	664.7	632.9	609.0	590.4	575.7	562.9	555.5	547.1	541.5	536.6
40°	670.1	634.5	605.6	580.5	566.8	550.6	538.6	529.1	522.8	515.4	510.2
42.5°	640.0	606.8	578.8	556.1	539.2	525.4	513.8	504.3	496.3	491.1	486.8
45°	597.2	564.2	536.9	515.9	500.3	487.2	475.0	470.4	459.9	453.6	451.5
47.5°	553.1	523.5	497.3	477.9	461.8	449.4	438.1	428.4	422.6	416.5	413.1
50°	523.3	495.0	470.4	451.5	435.8	422.1	411.6	405.4	397.5	391.7	387.5
52.5°	493.5	467.4	442.7	424.6	411.0	397.4	385.7	379.3	371.9	368.2	365.3
55°	451.0	423.1	402.2	384.4	370.2	357.6	346.6	340.3	335.6	331.9	330.8
57.5°	402.7	380.7	361.2	345.2	330.4	318.6	308.9	303.0	298.8	298.2	295.1
60°	371.2	351.3	333.5	316.2	303.6	292.6	284.2	277.4	273.2	272.7	271.7
62.5°	339.8	320.7	304.2	288.9	277.6	267.0	259.0	251.4	248.8	246.2	244.0
65°	293.2	275.8	262.2	250.1	238.0	229.1	221.3	216.5	210.8	207.6	201.9
67.5°	247.3	233.9	220.8	210.6	201.2	192.7	186.1	179.2	175.2	172.7	168.5
70°	217.1	206.6	193.5	182.5	175.1	168.3	163.1	155.2	152.6	150.5	148.3
72.5°	188.5	179.4	168.3	159.5	152.1	145.6	139.6	135.9	133.3	131.2	130.0
75°	148.3	139.5	130.1	123.7	118.6	113.3	110.1	107.4	106.4	105.9	103.8
77.5°	109.0	104.2	96.6	91.7	88.2	86.1	83.3	81.9	81.8	79.5	78.8
80°	83.4	80.8	74.4	72.4	69.8	67.7	66.0	63.4	60.8	59.8	58.2
82.5°	62.0	59.4	56.9	53.5	51.3	50.0	48.5	47.5	47.9	46.4	45.6
85°	33.0	30.4	29.4	28.9	27.8	28.9	28.3	27.8	27.3	26.8	27.3
87.5°	11.1	11.2	10.9	11.8	10.7	11.2	11.3	10.9	11.0	11.1	10.7
90°	2.9	3.5	4.0	4.6	5.2	5.8	6.1	6.5	6.9	7.3	7.6
92.5°	3.7	3.7	4.2	4.7	5.3	5.8	6.1	6.5	6.9	7.3	7.6
95°	19.4	17.8	14.7	11.7	8.7	5.8	6.1	6.5	6.9	7.3	7.5
97.5°	44.2	41.4	35.4	29.5	23.5	17.6	15.3	13.1	10.8	8.6	7.5
100°	60.6	60.8	61.2	61.5	61.8	62.1	50.3	38.5	26.7	14.8	8.8
102.5°	78.3	78.5	78.7	78.9	79.1	79.3	77.1	74.7	72.5	70.3	66.4
105°	106.2	106.3	106.3	106.3	106.3	106.3	106.3	106.3	106.3	106.3	106.3
107.5°	133.9	134.0	134.2	134.3	134.5	134.6	134.6	134.7	134.7	134.7	134.6
110°	152.8	152.9	153.0	153.2	153.3	153.5	153.3	153.0	152.8	152.6	152.5



TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	171.3	171.4	171.5	171.6	171.7	171.8	171.5	171.2	170.9	170.6	170.4
115°	198.6	198.8	198.9	199.0	199.1	199.1	198.8	198.5	198.2	197.9	197.5
117.5°	224.5	224.6	224.9	225.2	225.5	225.8	225.4	225.0	224.6	224.2	223.9
120°	241.4	241.5	241.7	241.9	242.2	242.4	242.3	242.1	241.9	241.8	241.5
122.5°	258.0	258.2	258.3	258.4	258.5	258.6	258.5	258.3	258.2	258.0	257.7
125°	282.5	282.8	282.8	282.8	282.8	282.8	282.4	282.1	281.8	281.4	281.1
127.5°	304.2	304.4	304.3	304.3	304.2	304.2	304.0	303.8	303.6	303.5	303.1
130°	317.9	318.1	318.2	318.2	318.3	318.4	318.2	317.9	317.7	317.5	317.1
132.5°	331.8	331.9	331.8	331.6	331.4	331.2	331.2	331.1	331.1	331.0	330.8
135°	351.3	351.5	351.3	351.2	351.0	350.9	350.7	350.6	350.4	350.2	349.9
137.5°	369.0	369.2	369.0	368.9	368.7	368.6	368.6	368.7	368.7	368.7	368.5
140°	379.7	379.8	379.7	379.6	379.5	379.5	379.6	379.8	379.9	380.1	379.9
142.5°	390.0	390.1	390.3	390.4	390.5	390.6	390.6	390.6	390.7	390.7	390.5
145°	405.8	405.9	405.9	405.9	405.9	405.9	406.0	406.1	406.1	406.2	406.0
147.5°	418.6	418.6	418.7	418.8	418.9	419.0	419.1	419.2	419.3	419.4	419.2
150°	426.7	426.7	426.8	427.0	427.2	427.3	427.5	427.6	427.8	427.9	427.7
152.5°	434.1	434.0	434.2	434.4	434.5	434.7	434.8	435.0	435.2	435.4	435.2
155°	444.3	444.1	444.3	444.4	444.6	444.7	445.0	445.2	445.5	445.8	445.6
157.5°	453.3	453.1	453.1	453.2	453.2	453.2	453.4	453.7	453.9	454.2	454.0
160°	458.3	458.1	458.1	458.2	458.3	458.4	458.7	459.0	459.3	459.6	459.5
162.5°	462.8	462.6	462.7	462.7	462.8	462.9	463.3	463.8	464.2	464.7	464.5
165°	469.0	468.8	468.8	468.9	469.0	469.1	469.5	470.0	470.5	471.0	470.9
167.5°	473.4	473.2	473.3	473.4	473.5	473.5	474.1	474.7	475.2	475.8	475.7
170°	475.7	475.5	475.6	475.6	475.7	475.8	476.5	477.1	477.8	478.4	478.4
172.5°	477.5	477.3	477.4	477.6	477.7	477.9	478.4	479.0	479.6	480.1	480.1
175°	479.7	479.5	479.5	479.6	479.7	479.8	480.4	481.0	481.7	482.3	482.3
177.5°	480.9	480.7	480.8	480.9	480.9	481.0	481.4	481.9	482.3	482.7	482.7
180°	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5



TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1223.7	1219.1	1217.8	1219.5	1217.8	1219.1	1223.7	1224.1	1224.6	1227.9	1223.2
5°	1128.9	1123.8	1126.3	1125.3	1126.3	1123.8	1128.9	1134.2	1135.3	1139.9	1143.2
7.5°	1045.7	1039.2	1032.3	1034.5	1032.3	1039.2	1045.7	1045.8	1054.0	1060.1	1064.2
10°	987.3	982.2	979.0	981.6	979.0	982.2	987.3	994.2	997.3	1004.7	1012.6
12.5°	938.3	935.1	932.4	931.3	932.4	935.1	938.3	945.5	952.9	961.5	970.2
15°	871.5	865.3	862.6	855.8	862.6	865.3	871.5	877.8	891.9	895.6	908.8
17.5°	809.9	807.9	801.0	798.1	801.0	807.9	809.9	815.3	821.8	835.4	845.2
20°	773.5	771.3	764.6	768.7	764.6	771.3	773.5	781.3	786.6	797.6	807.0
22.5°	743.3	738.6	736.4	735.2	736.4	738.6	743.3	746.9	753.9	764.0	774.7
25°	700.5	693.8	691.2	688.0	691.2	693.8	700.5	702.7	710.0	719.9	725.7
27.5°	658.0	654.3	650.9	650.1	650.9	654.3	658.0	661.0	667.3	676.0	686.4
30°	630.3	626.6	624.0	624.0	624.0	626.6	630.3	636.6	641.3	649.1	657.0
32.5°	605.5	602.7	600.1	599.7	600.1	602.7	605.5	608.9	614.5	623.2	631.5
35°	569.5	565.3	564.2	561.1	564.2	565.3	569.5	572.1	577.8	584.1	591.0
37.5°	532.0	528.6	528.5	528.2	528.5	528.6	532.0	536.6	541.5	547.1	555.5
40°	508.2	505.5	504.9	501.3	504.9	505.5	508.2	510.2	515.4	522.8	529.1
42.5°	482.5	481.2	479.4	477.8	479.4	481.2	482.5	486.8	491.1	496.3	504.3
45°	447.8	444.1	444.1	441.5	444.1	444.1	447.8	451.5	453.6	459.9	470.4
47.5°	411.9	409.1	409.4	406.7	409.4	409.1	411.9	413.1	416.5	422.6	428.4
50°	388.0	386.5	386.0	384.9	386.0	386.5	388.0	387.5	391.7	397.5	405.4
52.5°	364.2	363.3	365.4	363.0	365.4	363.3	364.2	365.3	368.2	371.9	379.3
55°	331.9	330.3	333.5	330.3	333.5	330.3	331.9	330.8	331.9	335.6	340.3
57.5°	294.9	293.5	296.3	294.7	296.3	293.5	294.9	295.1	298.2	298.8	303.0
60°	270.5	267.4	269.0	269.5	269.0	267.4	270.5	271.7	272.7	273.2	277.4
62.5°	241.7	239.7	240.9	238.5	240.9	239.7	241.7	244.0	246.2	248.8	251.4
65°	200.9	199.2	197.1	196.1	197.1	199.2	200.9	201.9	207.6	210.8	216.5
67.5°	168.7	165.0	164.9	165.7	164.9	165.0	168.7	168.5	172.7	175.2	179.2
70°	145.2	145.2	144.7	144.7	144.7	145.2	145.2	148.3	150.5	152.6	155.2
72.5°	128.9	128.5	127.5	127.1	127.5	128.5	128.9	130.0	131.2	133.3	135.9
75°	103.8	104.3	103.3	102.8	103.3	104.3	103.8	103.8	105.9	106.4	107.4
77.5°	76.6	74.4	75.6	74.4	75.6	74.4	76.6	78.8	79.5	81.8	81.9
80°	58.2	57.7	59.3	57.7	59.3	57.7	58.2	58.2	59.8	60.8	63.4
82.5°	46.0	45.5	46.3	45.1	46.3	45.5	46.0	45.6	46.4	47.9	47.5
85°	27.8	27.3	26.8	27.3	26.8	27.3	27.8	27.3	26.8	27.3	27.8
87.5°	11.2	10.8	10.9	10.9	10.9	10.8	11.2	10.7	11.1	11.0	10.9
90°	7.9	8.1	8.3	8.6	8.3	8.1	7.9	7.6	7.3	6.9	6.5
92.5°	7.7	7.8	7.9	8.0	7.9	7.8	7.7	7.6	7.3	6.9	6.5
95°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.3	6.9	6.5
97.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	8.6	10.8	13.1
100°	8.5	8.2	7.8	7.5	7.8	8.2	8.5	8.8	14.8	26.7	38.5
102.5°	61.1	55.7	50.3	44.9	50.3	55.7	61.1	66.4	70.3	72.5	74.7
105°	106.2	106.1	106.1	106.0	106.1	106.1	106.2	106.3	106.3	106.3	106.3
107.5°	134.4	134.1	133.9	133.6	133.9	134.1	134.4	134.6	134.7	134.7	134.7
110°	152.6	152.6	152.7	152.8	152.7	152.6	152.6	152.5	152.6	152.8	153.0



TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	170.3	170.2	170.1	170.0	170.1	170.2	170.3	170.4	170.6	170.9	171.2
115°	197.0	196.6	196.1	195.6	196.1	196.6	197.0	197.5	197.9	198.2	198.5
117.5°	223.7	223.5	223.3	223.1	223.3	223.5	223.7	223.9	224.2	224.6	225.0
120°	241.1	240.7	240.2	239.8	240.2	240.7	241.1	241.5	241.8	241.9	242.1
122.5°	257.2	256.8	256.3	255.9	256.3	256.8	257.2	257.7	258.0	258.2	258.3
125°	280.9	280.7	280.4	280.2	280.4	280.7	280.9	281.1	281.4	281.8	282.1
127.5°	302.5	301.8	301.3	300.7	301.3	301.8	302.5	303.1	303.5	303.6	303.8
130°	316.8	316.4	316.0	315.6	316.0	316.4	316.8	317.1	317.5	317.7	317.9
132.5°	330.4	330.0	329.6	329.3	329.6	330.0	330.4	330.8	331.0	331.1	331.1
135°	349.5	349.0	348.5	348.0	348.5	349.0	349.5	349.9	350.2	350.4	350.6
137.5°	368.1	367.7	367.3	366.9	367.3	367.7	368.1	368.5	368.7	368.7	368.7
140°	379.5	379.0	378.5	378.0	378.5	379.0	379.5	379.9	380.1	379.9	379.8
142.5°	390.0	389.5	389.1	388.6	389.1	389.5	390.0	390.5	390.7	390.7	390.6
145°	405.6	405.1	404.6	404.0	404.6	405.1	405.6	406.0	406.2	406.1	406.1
147.5°	418.6	418.0	417.5	416.9	417.5	418.0	418.6	419.2	419.4	419.3	419.2
150°	427.1	426.5	425.8	425.2	425.8	426.5	427.1	427.7	427.9	427.8	427.6
152.5°	434.5	434.0	433.4	432.8	433.4	434.0	434.5	435.2	435.4	435.2	435.0
155°	444.9	444.2	443.6	443.0	443.6	444.2	444.9	445.6	445.8	445.5	445.2
157.5°	453.4	452.7	452.1	451.5	452.1	452.7	453.4	454.0	454.2	453.9	453.7
160°	458.8	458.2	457.6	457.0	457.6	458.2	458.8	459.5	459.6	459.3	459.0
162.5°	463.8	463.1	462.5	461.8	462.5	463.1	463.8	464.5	464.7	464.2	463.8
165°	470.3	469.6	469.0	468.4	469.0	469.6	470.3	470.9	471.0	470.5	470.0
167.5°	475.0	474.3	473.6	472.9	473.6	474.3	475.0	475.7	475.8	475.2	474.7
170°	477.7	477.0	476.2	475.4	476.2	477.0	477.7	478.4	478.4	477.8	477.1
172.5°	479.4	478.6	477.9	477.2	477.9	478.6	479.4	480.1	480.1	479.6	479.0
175°	481.5	480.8	480.1	479.4	480.1	480.8	481.5	482.3	482.3	481.7	481.0
177.5°	482.2	481.7	481.2	480.7	481.2	481.7	482.2	482.7	482.7	482.3	481.9
180°	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5



TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1224.6	1229.1	1231.6	1237.5	1245.9	1250.1	1256.0	1260.2	1266.1	1273.1	1279.1
5°	1145.2	1157.8	1166.2	1179.3	1191.3	1203.5	1218.6	1229.6	1244.4	1261.1	1274.2
7.5°	1071.6	1087.3	1101.3	1118.6	1138.5	1154.1	1173.9	1194.1	1217.1	1240.9	1263.3
10°	1024.6	1040.4	1057.6	1079.1	1099.0	1120.0	1143.7	1167.2	1196.1	1222.8	1253.2
12.5°	978.1	995.4	1014.9	1038.8	1063.0	1089.8	1113.9	1140.4	1171.3	1206.1	1238.6
15°	920.3	937.1	958.1	978.5	1006.2	1035.6	1067.6	1102.8	1137.4	1176.2	1216.6
17.5°	858.3	876.8	899.8	923.5	952.8	987.1	1018.5	1057.0	1095.9	1141.1	1188.6
20°	818.0	836.9	864.1	890.4	917.2	950.7	988.0	1027.2	1068.6	1116.4	1169.3
22.5°	786.2	799.6	826.4	853.0	884.4	918.8	955.2	996.2	1041.4	1090.8	1146.3
25°	738.8	754.6	774.0	801.7	834.2	870.5	907.2	950.7	1000.0	1050.4	1109.5
27.5°	696.8	709.7	728.9	750.7	783.0	820.6	859.7	905.0	955.6	1006.9	1069.1
30°	667.0	681.2	699.5	722.6	748.3	789.2	829.0	873.6	925.0	978.0	1041.9
32.5°	641.0	655.6	671.4	693.2	721.0	757.3	798.4	842.1	894.3	949.0	1011.3
35°	604.6	614.6	629.2	650.8	678.0	707.4	749.3	795.5	846.4	902.9	965.3
37.5°	562.9	575.7	590.4	609.0	632.9	664.7	703.7	750.3	797.6	851.8	908.8
40°	538.6	550.6	566.8	580.5	605.6	634.5	670.1	718.9	766.1	817.0	868.9
42.5°	513.8	525.4	539.2	556.1	578.8	606.8	640.0	685.4	735.9	783.9	827.4
45°	475.0	487.2	500.3	515.9	536.9	564.2	597.2	638.6	682.8	726.8	759.8
47.5°	438.1	449.4	461.8	477.9	497.3	523.5	553.1	589.7	632.5	669.9	693.6
50°	411.6	422.1	435.8	451.5	470.4	495.0	523.3	559.5	595.1	629.2	650.8
52.5°	385.7	397.4	411.0	424.6	442.7	467.4	493.5	524.7	558.7	586.4	604.2
55°	346.6	357.6	370.2	384.4	402.2	423.1	451.0	475.6	502.3	525.9	536.4
57.5°	308.9	318.6	330.4	345.2	361.2	380.7	402.7	426.5	445.2	462.0	473.8
60°	284.2	292.6	303.6	316.2	333.5	351.3	371.2	393.2	408.0	422.1	433.1
62.5°	259.0	267.0	277.6	288.9	304.2	320.7	339.8	357.6	371.9	381.4	394.2
65°	221.3	229.1	238.0	250.1	262.2	275.8	293.2	306.2	316.2	326.7	334.6
67.5°	186.1	192.7	201.2	210.6	220.8	233.9	247.3	258.2	265.0	271.4	280.7
70°	163.1	168.3	175.1	182.5	193.5	206.6	217.1	225.5	230.2	236.5	248.0
72.5°	139.6	145.6	152.1	159.5	168.3	179.4	188.5	196.9	200.0	205.0	212.4
75°	110.1	113.3	118.6	123.7	130.1	139.5	148.3	150.5	153.1	157.3	162.6
77.5°	83.3	86.1	88.2	91.7	96.6	104.2	109.0	112.1	112.7	114.3	119.5
80°	66.0	67.7	69.8	72.4	74.4	80.8	83.4	86.5	87.6	89.2	91.8
82.5°	48.5	50.0	51.3	53.5	56.9	59.4	62.0	65.1	65.3	66.4	67.1
85°	28.3	28.9	27.8	28.9	29.4	30.4	33.0	35.6	35.1	34.6	36.2
87.5°	11.3	11.2	10.7	11.8	10.9	11.2	11.1	11.3	12.1	12.8	13.5
90°	6.1	5.8	5.2	4.6	4.0	3.5	2.9	2.2	1.6	1.0	0.4
92.5°	6.1	5.8	5.3	4.7	4.2	3.7	3.7	4.1	4.6	5.0	5.5
95°	6.1	5.8	8.7	11.7	14.7	17.8	19.4	19.6	19.9	20.1	20.3
97.5°	15.3	17.6	23.5	29.5	35.4	41.4	44.2	43.7	43.3	42.9	42.5
100°	50.3	62.1	61.8	61.5	61.2	60.8	60.6	60.3	60.1	59.9	59.6
102.5°	77.1	79.3	79.1	78.9	78.7	78.5	78.3	78.0	77.7	77.4	77.1
105°	106.3	106.3	106.3	106.3	106.3	106.3	106.2	105.9	105.6	105.2	104.9
107.5°	134.6	134.6	134.5	134.3	134.2	134.0	133.9	133.9	133.9	133.9	133.9
110°	153.3	153.5	153.3	153.2	153.0	152.9	152.8	152.8	152.8	152.8	152.8



TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	171.5	171.8	171.7	171.6	171.5	171.4	171.3	171.1	170.9	170.7	170.5
115°	198.8	199.1	199.1	199.0	198.9	198.8	198.6	198.2	197.8	197.4	197.0
117.5°	225.4	225.8	225.5	225.2	224.9	224.6	224.5	224.5	224.5	224.5	224.5
120°	242.3	242.4	242.2	241.9	241.7	241.5	241.4	241.5	241.6	241.6	241.7
122.5°	258.5	258.6	258.5	258.4	258.3	258.2	258.0	257.7	257.4	257.1	256.8
125°	282.4	282.8	282.8	282.8	282.8	282.8	282.5	281.9	281.3	280.7	280.2
127.5°	304.0	304.2	304.2	304.3	304.3	304.4	304.2	303.8	303.4	303.0	302.6
130°	318.2	318.4	318.3	318.2	318.2	318.1	317.9	317.5	317.1	316.7	316.3
132.5°	331.2	331.2	331.4	331.6	331.8	331.9	331.8	331.3	330.9	330.4	330.0
135°	350.7	350.9	351.0	351.2	351.3	351.5	351.3	350.9	350.4	349.9	349.5
137.5°	368.6	368.6	368.7	368.9	369.0	369.2	369.0	368.6	368.2	367.8	367.4
140°	379.6	379.5	379.5	379.6	379.7	379.8	379.7	379.6	379.4	379.3	379.1
142.5°	390.6	390.6	390.5	390.4	390.3	390.1	390.0	389.9	389.9	389.8	389.7
145°	406.0	405.9	405.9	405.9	405.9	405.9	405.8	405.7	405.5	405.4	405.2
147.5°	419.1	419.0	418.9	418.8	418.7	418.6	418.6	418.6	418.7	418.7	418.7
150°	427.5	427.3	427.2	427.0	426.8	426.7	426.7	426.8	427.0	427.2	427.3
152.5°	434.8	434.7	434.5	434.4	434.2	434.0	434.1	434.5	434.8	435.3	435.6
155°	445.0	444.7	444.6	444.4	444.3	444.1	444.3	444.7	445.2	445.8	446.3
157.5°	453.4	453.2	453.2	453.2	453.1	453.1	453.3	453.5	453.8	454.1	454.4
160°	458.7	458.4	458.3	458.2	458.1	458.1	458.3	458.7	459.2	459.7	460.1
162.5°	463.3	462.9	462.8	462.7	462.7	462.6	462.8	463.2	463.7	464.2	464.7
165°	469.5	469.1	469.0	468.9	468.8	468.8	469.0	469.4	469.9	470.4	470.8
167.5°	474.1	473.5	473.5	473.4	473.3	473.2	473.4	473.9	474.4	474.9	475.4
170°	476.5	475.8	475.7	475.6	475.6	475.5	475.7	476.4	476.9	477.5	478.0
172.5°	478.4	477.9	477.7	477.6	477.4	477.3	477.5	478.1	478.6	479.2	479.7
175°	480.4	479.8	479.7	479.6	479.5	479.5	479.7	480.1	480.6	481.1	481.5
177.5°	481.4	481.0	480.9	480.9	480.8	480.7	480.9	481.3	481.6	482.0	482.4
180°	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5



TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1283.6	1287.5	1292.9	1299.2	1304.2	1309.7	1312.6	1312.6	1315.1	1320.6	1327.7
5°	1287.4	1301.0	1314.0	1330.9	1343.9	1359.2	1370.7	1381.7	1391.7	1404.2	1417.3
7.5°	1286.3	1308.9	1332.5	1359.0	1388.2	1411.3	1435.1	1453.8	1472.2	1496.3	1515.3
10°	1282.1	1311.4	1343.4	1377.0	1413.7	1445.7	1474.5	1500.8	1525.9	1552.2	1575.7
12.5°	1274.6	1311.9	1351.0	1391.3	1437.6	1474.2	1511.5	1539.3	1568.7	1597.4	1626.5
15°	1263.2	1307.3	1354.4	1410.6	1467.2	1508.1	1544.8	1580.9	1608.2	1640.7	1668.6
17.5°	1239.8	1296.6	1355.9	1417.2	1471.7	1519.2	1557.7	1592.1	1621.1	1656.9	1694.7
20°	1226.0	1287.4	1349.2	1414.7	1466.6	1515.4	1552.7	1588.3	1624.5	1671.1	1717.3
22.5°	1206.7	1272.2	1337.9	1400.1	1454.9	1502.0	1540.4	1584.2	1631.6	1684.6	1740.4
25°	1176.2	1243.9	1308.8	1368.1	1421.6	1469.9	1522.3	1580.9	1638.7	1708.4	1788.7
27.5°	1137.5	1202.6	1260.7	1323.3	1376.4	1437.8	1503.3	1566.9	1650.1	1746.1	1846.2
30°	1108.5	1170.4	1225.5	1284.8	1345.0	1412.7	1486.1	1561.0	1660.1	1772.9	1892.0
32.5°	1075.0	1130.9	1185.6	1242.7	1312.3	1386.6	1464.7	1556.4	1674.9	1803.1	1926.3
35°	1016.7	1067.1	1120.0	1183.5	1257.5	1338.2	1437.8	1549.5	1692.6	1830.6	1941.3
37.5°	955.7	995.4	1048.6	1115.6	1196.1	1289.5	1402.6	1538.3	1685.4	1809.1	1856.1
40°	908.8	945.9	1002.1	1072.4	1152.1	1254.3	1381.2	1520.7	1668.6	1754.5	1750.9
42.5°	862.1	899.8	953.8	1024.5	1107.6	1222.0	1352.7	1497.6	1622.4	1655.2	1586.9
45°	790.7	825.9	878.9	950.2	1039.4	1159.4	1296.8	1435.7	1515.4	1462.5	1327.2
47.5°	718.0	752.0	801.2	871.1	968.4	1094.1	1224.0	1338.0	1349.2	1235.5	1073.2
50°	670.1	702.2	748.8	823.2	917.7	1040.4	1165.7	1255.4	1227.6	1088.6	921.3
52.5°	623.6	654.3	698.0	768.3	864.7	985.0	1096.9	1167.2	1103.0	955.2	804.7
55°	554.8	584.1	628.2	692.7	780.2	890.4	988.5	1014.1	919.8	770.8	649.1
57.5°	489.5	511.0	554.5	611.5	695.9	793.0	863.3	858.7	754.6	620.5	533.2
60°	446.3	465.6	507.1	559.5	639.7	726.8	776.1	755.1	649.6	539.1	455.1
62.5°	406.0	424.1	458.8	507.1	575.9	651.7	687.5	658.6	559.1	461.9	395.2
65°	345.1	358.1	386.0	430.5	484.5	536.9	569.0	526.4	438.4	365.0	314.6
67.5°	288.1	299.4	324.2	356.2	393.3	429.6	442.5	402.7	334.3	284.8	249.3
70°	251.2	261.7	278.4	308.3	333.0	358.7	365.0	329.3	272.2	234.4	212.4
72.5°	215.9	225.6	240.2	261.4	278.4	293.3	296.2	263.1	219.2	193.3	176.3
75°	164.6	173.1	182.5	190.4	201.4	204.0	202.9	177.2	153.6	136.3	126.9
77.5°	121.0	124.5	130.3	133.4	133.9	133.7	128.4	112.1	100.0	92.8	89.0
80°	93.3	95.9	97.6	98.6	99.1	93.8	88.1	78.2	73.9	69.8	65.0
82.5°	67.8	69.6	71.1	71.3	68.5	64.1	58.8	53.8	50.9	48.8	47.0
85°	36.7	37.3	36.7	34.1	30.4	28.9	27.8	26.8	26.3	25.7	25.7
87.5°	13.2	12.1	10.1	10.6	10.8	10.5	10.6	10.3	10.0	10.0	10.1
90°	1.0	1.6	2.2	2.9	3.5	4.0	4.6	5.2	5.8	6.1	6.5
92.5°	5.0	4.6	4.1	3.7	3.7	4.2	4.7	5.3	5.8	6.1	6.5
95°	20.1	19.9	19.6	19.4	17.8	14.7	11.7	8.7	5.8	6.1	6.5
97.5°	42.9	43.3	43.7	44.2	41.4	35.4	29.5	23.5	17.6	15.3	13.1
100°	59.9	60.1	60.3	60.6	60.8	61.2	61.5	61.8	62.1	50.3	38.5
102.5°	77.4	77.7	78.0	78.3	78.5	78.7	78.9	79.1	79.3	77.1	74.7
105°	105.2	105.6	105.9	106.2	106.3	106.3	106.3	106.3	106.3	106.3	106.3
107.5°	133.9	133.9	133.9	133.9	134.0	134.2	134.3	134.5	134.6	134.6	134.7
110°	152.8	152.8	152.8	152.8	152.9	153.0	153.2	153.3	153.5	153.3	153.0





TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	170.7	170.9	171.1	171.3	171.4	171.5	171.6	171.7	171.8	171.5	171.2
115°	197.4	197.8	198.2	198.6	198.8	198.9	199.0	199.1	199.1	198.8	198.5
117.5°	224.5	224.5	224.5	224.5	224.6	224.9	225.2	225.5	225.8	225.4	225.0
120°	241.6	241.6	241.5	241.4	241.5	241.7	241.9	242.2	242.4	242.3	242.1
122.5°	257.1	257.4	257.7	258.0	258.2	258.3	258.4	258.5	258.6	258.5	258.3
125°	280.7	281.3	281.9	282.5	282.8	282.8	282.8	282.8	282.8	282.4	282.1
127.5°	303.0	303.4	303.8	304.2	304.4	304.3	304.3	304.2	304.2	304.0	303.8
130°	316.7	317.1	317.5	317.9	318.1	318.2	318.2	318.3	318.4	318.2	317.9
132.5°	330.4	330.9	331.3	331.8	331.9	331.8	331.6	331.4	331.2	331.2	331.1
135°	349.9	350.4	350.9	351.3	351.5	351.3	351.2	351.0	350.9	350.7	350.6
137.5°	367.8	368.2	368.6	369.0	369.2	369.0	368.9	368.7	368.6	368.6	368.7
140°	379.3	379.4	379.6	379.7	379.8	379.7	379.6	379.5	379.5	379.6	379.8
142.5°	389.8	389.9	389.9	390.0	390.1	390.3	390.4	390.5	390.6	390.6	390.6
145°	405.4	405.5	405.7	405.8	405.9	405.9	405.9	405.9	405.9	406.0	406.1
147.5°	418.7	418.7	418.6	418.6	418.6	418.7	418.8	418.9	419.0	419.1	419.2
150°	427.2	427.0	426.8	426.7	426.7	426.8	427.0	427.2	427.3	427.5	427.6
152.5°	435.3	434.8	434.5	434.1	434.0	434.2	434.4	434.5	434.7	434.8	435.0
155°	445.8	445.2	444.7	444.3	444.1	444.3	444.4	444.6	444.7	445.0	445.2
157.5°	454.1	453.8	453.5	453.3	453.1	453.1	453.2	453.2	453.2	453.4	453.7
160°	459.7	459.2	458.7	458.3	458.1	458.1	458.2	458.3	458.4	458.7	459.0
162.5°	464.2	463.7	463.2	462.8	462.6	462.7	462.7	462.8	462.9	463.3	463.8
165°	470.4	469.9	469.4	469.0	468.8	468.8	468.9	469.0	469.1	469.5	470.0
167.5°	474.9	474.4	473.9	473.4	473.2	473.3	473.4	473.5	473.5	474.1	474.7
170°	477.5	476.9	476.4	475.7	475.5	475.6	475.6	475.7	475.8	476.5	477.1
172.5°	479.2	478.6	478.1	477.5	477.3	477.4	477.6	477.7	477.9	478.4	479.0
175°	481.1	480.6	480.1	479.7	479.5	479.5	479.6	479.7	479.8	480.4	481.0
177.5°	482.0	481.6	481.3	480.9	480.7	480.8	480.9	480.9	481.0	481.4	481.9
180°	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5



TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1333.1	1333.1	1340.3	1339.9	1344.5	1342.8	1343.6
5°	1433.1	1442.0	1449.9	1455.1	1463.0	1465.1	1464.0
7.5°	1536.7	1556.5	1566.2	1579.4	1581.9	1588.7	1588.0
10°	1600.9	1620.3	1635.0	1646.5	1652.3	1659.6	1660.1
12.5°	1651.2	1667.7	1680.7	1691.4	1698.4	1700.7	1702.1
15°	1690.6	1708.9	1724.1	1739.3	1748.3	1755.0	1758.8
17.5°	1730.2	1758.6	1785.3	1806.0	1818.5	1828.9	1828.8
20°	1760.8	1793.3	1826.9	1850.5	1874.6	1885.1	1886.7
22.5°	1793.5	1843.3	1886.5	1923.1	1954.8	1965.7	1969.7
25°	1861.5	1926.5	1993.2	2044.6	2081.2	2102.7	2105.9
27.5°	1943.6	2031.6	2101.7	2149.1	2179.6	2195.5	2199.0
30°	2001.6	2082.8	2145.8	2181.4	2195.5	2197.7	2189.8
32.5°	2027.5	2088.3	2113.4	2111.3	2083.6	2065.1	2058.0
35°	1995.8	1983.2	1921.8	1848.5	1792.3	1756.7	1747.2
37.5°	1816.2	1707.7	1594.8	1483.9	1424.8	1394.8	1343.2
40°	1639.2	1484.5	1367.1	1273.7	1207.1	1153.6	1141.0
42.5°	1439.5	1279.8	1162.4	1082.4	1029.3	992.5	976.5
45°	1156.8	1019.4	922.4	861.0	820.1	793.3	781.3
47.5°	925.2	818.9	748.2	702.8	671.7	648.3	641.9
50°	798.1	713.2	653.4	615.1	591.5	573.7	566.3
52.5°	693.2	624.6	578.7	547.1	524.8	513.7	507.6
55°	572.1	512.8	479.8	454.6	442.0	433.1	428.9
57.5°	467.9	425.1	400.9	383.5	371.9	366.2	364.2
60°	409.5	376.0	354.0	340.3	332.4	325.1	323.1
62.5°	357.9	331.5	314.5	302.6	294.7	291.5	290.3
65°	288.4	271.1	258.5	251.2	244.9	243.9	243.3
67.5°	229.2	219.0	212.5	204.8	202.6	198.9	198.2
70°	196.1	189.2	181.5	178.8	176.2	172.5	173.1
72.5°	166.3	159.6	154.2	150.7	149.8	148.1	149.6
75°	121.7	119.6	117.4	114.8	113.8	113.8	113.3
77.5°	86.8	85.0	82.7	81.2	80.9	78.7	79.5
80°	62.9	60.3	59.3	59.8	58.2	57.7	57.7
82.5°	46.6	45.6	44.5	44.6	44.3	43.8	44.2
85°	25.7	25.1	25.1	24.6	24.6	24.1	24.1
87.5°	10.6	11.1	10.3	10.0	10.0	10.5	10.9
90°	6.9	7.3	7.6	7.9	8.1	8.3	8.6
92.5°	6.9	7.3	7.6	7.7	7.8	7.9	8.0
95°	6.9	7.3	7.5	7.5	7.5	7.5	7.5
97.5°	10.8	8.6	7.5	7.5	7.5	7.5	7.5
100°	26.7	14.8	8.8	8.5	8.2	7.8	7.5
102.5°	72.5	70.3	66.4	61.1	55.7	50.3	44.9
105°	106.3	106.3	106.3	106.2	106.1	106.1	106.0
107.5°	134.7	134.7	134.6	134.4	134.1	133.9	133.6
110°	152.8	152.6	152.5	152.6	152.6	152.7	152.8



TEST NUMBER: P333550-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	170.9	170.6	170.4	170.3	170.2	170.1	170.0
115°	198.2	197.9	197.5	197.0	196.6	196.1	195.6
117.5°	224.6	224.2	223.9	223.7	223.5	223.3	223.1
120°	241.9	241.8	241.5	241.1	240.7	240.2	239.8
122.5°	258.2	258.0	257.7	257.2	256.8	256.3	255.9
125°	281.8	281.4	281.1	280.9	280.7	280.4	280.2
127.5°	303.6	303.5	303.1	302.5	301.8	301.3	300.7
130°	317.7	317.5	317.1	316.8	316.4	316.0	315.6
132.5°	331.1	331.0	330.8	330.4	330.0	329.6	329.3
135°	350.4	350.2	349.9	349.5	349.0	348.5	348.0
137.5°	368.7	368.7	368.5	368.1	367.7	367.3	366.9
140°	379.9	380.1	379.9	379.5	379.0	378.5	378.0
142.5°	390.7	390.7	390.5	390.0	389.5	389.1	388.6
145°	406.1	406.2	406.0	405.6	405.1	404.6	404.0
147.5°	419.3	419.4	419.2	418.6	418.0	417.5	416.9
150°	427.8	427.9	427.7	427.1	426.5	425.8	425.2
152.5°	435.2	435.4	435.2	434.5	434.0	433.4	432.8
155°	445.5	445.8	445.6	444.9	444.2	443.6	443.0
157.5°	453.9	454.2	454.0	453.4	452.7	452.1	451.5
160°	459.3	459.6	459.5	458.8	458.2	457.6	457.0
162.5°	464.2	464.7	464.5	463.8	463.1	462.5	461.8
165°	470.5	471.0	470.9	470.3	469.6	469.0	468.4
167.5°	475.2	475.8	475.7	475.0	474.3	473.6	472.9
170°	477.8	478.4	478.4	477.7	477.0	476.2	475.4
172.5°	479.6	480.1	480.1	479.4	478.6	477.9	477.2
175°	481.7	482.3	482.3	481.5	480.8	480.1	479.4
177.5°	482.3	482.7	482.7	482.2	481.7	481.2	480.7
180°	481.5	481.5	481.5	481.5	481.5	481.5	481.5

(END OF REPORT)