

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333559-840

Luminaire Tested: **S125RDIP-S850D590U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333559-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D590U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5668.9 lumens
Efficiency: N/A
Efficacy: 140.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333559-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333559-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	88	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	72	85	78	73	68	68	64	61	59	56	53	50	48	46	42
3	83	74	66	61	77	69	63	57	60	55	51	52	48	45	44	42	39	36
4	76	65	58	52	71	61	54	49	54	48	44	47	42	39	40	37	34	31
5	70	59	50	44	65	55	48	42	48	42	38	42	37	34	36	33	30	27
6	65	53	44	39	60	49	42	37	44	38	33	38	33	30	33	29	26	24
7	60	48	40	34	56	45	38	32	40	34	29	35	30	26	30	26	24	21
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8969	8969	8969
5°	8989	8887	8941
10°	8921	8804	8804
15°	8815	8625	8555
20°	8678	8376	8276
25°	8521	8131	7952
30°	8322	7845	7594
35°	8121	7550	7194
40°	7932	7242	6800
45°	7701	6898	6370
50°	7471	6523	5923
55°	7203	6164	5444
60°	6935	5730	4930
65°	6619	5225	4343
70°	6258	4594	3743
75°	5759	3873	3114
80°	5069	3042	2615
85°	4276	2482	2334



TEST NUMBER: P333559-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	2.3
10°-20°	364.9	6.4
20°-30°	529.2	9.3
30°-40°	603.1	10.6
40°-50°	587.8	10.4
50°-60°	494.8	8.7
60°-70°	346.9	6.1
70°-80°	178.3	3.1
80°-90°	46.6	0.8
90°-100°	28.3	0.5
100°-110°	174.1	3.1
110°-120°	315.7	5.6
120°-130°	405.2	7.1
130°-140°	435.8	7.7
140°-150°	409.1	7.2
150°-160°	330.9	5.8
160°-170°	214.0	3.8
170°-180°	73.8	1.3
0°-30°	1024.6	18.1
0°-40°	1627.7	28.7
0°-60°	2710.4	47.8
0°-90°	3282.2	57.9
90°-120°	518.0	9.1
90°-150°	1768.1	31.2
90°-180°	2387.0	42.1
0°-180°	5668.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1386	1382	1371	1381	1379	131
15°	1318	1311	1290	1289	1280	371
25°	1196	1179	1141	1128	1116	550
35°	1030	1004	958	928	912	645
45°	843	811	755	715	697	650
55°	640	605	547	502	484	572
65°	433	396	342	301	284	429
75°	231	199	155	133	125	244
85°	58	40	34	32	32	65
90°	1	5	9	12	14	4
95°	33	30	9	12	12	42
105°	169	172	172	172	171	180
115°	318	321	322	319	316	315
125°	452	456	456	454	452	404
135°	564	567	566	565	562	435
145°	654	655	655	655	652	409
155°	720	717	718	719	715	332
165°	760	757	757	760	756	215
175°	777	774	774	778	774	74
180°	777	777	777	777	777	



TEST NUMBER: P333559-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1391.1	1390.6	1390.0	1389.5	1388.9	1387.7	1385.8	1383.9	1382.1	1380.2	1382.1
5°	1386.5	1385.6	1384.6	1383.7	1382.8	1381.1	1378.5	1375.9	1373.3	1370.8	1373.1
7.5°	1372.9	1372.0	1371.1	1370.2	1369.4	1367.4	1364.3	1361.2	1358.2	1355.0	1356.7
10°	1360.3	1359.6	1358.9	1358.2	1357.5	1355.5	1352.3	1349.0	1345.7	1342.5	1343.1
12.5°	1346.0	1345.1	1344.2	1343.4	1342.5	1339.9	1335.4	1331.1	1326.8	1322.3	1322.8
15°	1318.4	1317.0	1315.6	1314.1	1312.7	1309.6	1304.7	1299.8	1294.9	1290.0	1289.8
17.5°	1287.1	1285.0	1282.8	1280.7	1278.5	1274.3	1268.2	1262.0	1255.9	1249.7	1248.6
20°	1262.7	1260.4	1258.1	1255.8	1253.4	1248.5	1241.1	1233.7	1226.2	1218.7	1217.6
22.5°	1235.9	1233.6	1231.2	1228.9	1226.6	1221.5	1213.7	1205.9	1198.0	1190.2	1187.9
25°	1195.7	1192.1	1188.6	1185.2	1181.6	1175.6	1167.0	1158.3	1149.7	1141.1	1138.1
27.5°	1149.5	1145.3	1141.0	1136.8	1132.6	1125.8	1116.6	1107.3	1098.1	1088.8	1084.6
30°	1115.9	1111.5	1107.1	1102.7	1098.2	1091.1	1081.4	1071.6	1061.8	1052.0	1046.6
32.5°	1083.2	1078.0	1072.9	1067.7	1062.5	1054.9	1045.0	1035.0	1025.0	1015.0	1009.2
35°	1030.0	1024.3	1018.8	1013.1	1007.5	999.5	989.1	978.6	968.1	957.6	950.8
37.5°	977.7	970.9	964.1	957.3	950.5	941.7	930.9	920.0	909.2	898.4	890.3
40°	940.8	933.8	926.8	919.8	912.8	903.7	892.5	881.3	870.2	859.0	850.1
42.5°	902.2	895.0	887.9	880.6	873.4	864.1	852.5	841.0	829.4	817.9	809.4
45°	843.2	836.5	829.7	822.9	816.2	806.4	793.6	780.8	768.0	755.2	745.8
47.5°	782.2	775.1	767.9	760.8	753.7	743.7	730.7	717.8	704.9	692.0	682.4
50°	743.6	735.9	728.2	720.5	712.9	702.4	689.0	675.8	662.5	649.2	639.4
52.5°	701.7	693.8	685.9	678.0	670.1	659.9	647.4	634.9	622.3	609.8	599.3
55°	639.7	632.3	624.9	617.4	610.0	599.7	586.6	573.6	560.6	547.4	536.9
57.5°	577.2	569.3	561.3	553.3	545.4	535.1	522.5	509.9	497.4	484.7	474.5
60°	536.9	528.9	520.7	512.5	504.3	494.0	481.4	468.8	456.3	443.6	433.4
62.5°	494.2	486.5	478.7	470.8	463.0	452.8	440.0	427.3	414.4	401.7	392.2
65°	433.1	425.3	417.3	409.4	401.4	391.3	379.0	366.6	354.3	341.9	332.5
67.5°	372.5	364.6	356.7	348.8	340.8	330.9	319.1	307.3	295.5	283.6	275.1
70°	331.4	323.5	315.6	307.6	299.7	289.9	278.3	266.6	255.0	243.3	236.1
72.5°	291.1	283.4	275.7	267.9	260.2	250.9	239.9	229.0	218.1	207.2	200.6
75°	230.8	223.8	216.7	209.7	202.8	194.4	184.6	174.8	165.0	155.2	150.1
77.5°	170.8	165.1	159.6	154.0	148.3	141.7	133.8	126.0	118.2	110.4	106.7
80°	136.3	130.8	125.1	119.6	114.0	108.0	101.4	94.8	88.4	81.8	79.7
82.5°	102.8	97.8	92.7	87.7	82.6	77.9	73.4	69.0	64.4	60.0	59.0
85°	57.7	53.5	49.3	45.1	40.9	38.2	37.1	35.9	34.7	33.5	33.3
87.5°	19.4	18.3	17.2	16.2	15.0	14.4	14.4	14.4	14.4	14.4	14.5
90°	0.6	1.6	2.6	3.6	4.6	5.7	6.6	7.5	8.3	9.2	9.9
92.5°	8.9	8.2	7.5	6.8	6.0	6.1	6.9	7.7	8.4	9.2	9.9
95°	32.8	32.4	32.1	31.7	31.3	28.7	23.8	19.0	14.0	9.2	9.9
97.5°	68.6	69.3	70.0	70.6	71.3	66.9	57.3	47.6	38.0	28.4	24.7
100°	96.2	96.6	96.9	97.4	97.8	98.2	98.8	99.3	99.8	100.3	81.2
102.5°	124.3	124.8	125.3	125.8	126.2	126.6	126.9	127.3	127.6	127.9	124.3
105°	169.4	169.9	170.5	171.0	171.5	171.7	171.7	171.7	171.7	171.7	171.7
107.5°	216.2	216.2	216.2	216.2	216.2	216.3	216.5	216.8	217.1	217.3	217.3
110°	246.6	246.6	246.6	246.6	246.6	246.7	247.0	247.2	247.5	247.7	247.4



TEST NUMBER: P333559-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.2	275.5	275.8	276.1	276.4	276.6	276.8	276.9	277.1	277.2	276.8
115°	318.0	318.7	319.3	319.9	320.6	321.0	321.1	321.2	321.3	321.5	321.0
117.5°	362.4	362.3	362.3	362.3	362.3	362.5	363.0	363.6	364.0	364.5	363.9
120°	390.1	389.9	389.8	389.7	389.5	389.7	390.1	390.4	390.8	391.2	390.9
122.5°	414.4	415.0	415.5	416.0	416.5	416.8	417.0	417.2	417.3	417.5	417.3
125°	452.3	453.2	454.0	454.9	455.9	456.4	456.4	456.4	456.4	456.4	455.9
127.5°	488.4	489.0	489.7	490.3	490.9	491.2	491.1	491.1	491.0	490.9	490.6
130°	510.5	511.1	511.8	512.4	513.0	513.4	513.5	513.7	513.8	513.9	513.5
132.5°	532.6	533.3	534.1	534.8	535.5	535.8	535.5	535.2	534.9	534.7	534.6
135°	564.1	564.8	565.6	566.3	567.1	567.4	567.1	566.8	566.6	566.3	566.1
137.5°	593.0	593.7	594.3	595.0	595.6	595.9	595.6	595.4	595.2	594.9	595.0
140°	611.9	612.2	612.4	612.7	612.9	613.0	612.9	612.7	612.6	612.5	612.7
142.5°	628.9	629.1	629.2	629.4	629.5	629.8	630.0	630.1	630.3	630.5	630.5
145°	654.0	654.2	654.5	654.7	655.0	655.1	655.1	655.1	655.1	655.1	655.2
147.5°	675.8	675.8	675.7	675.7	675.6	675.7	675.8	676.0	676.1	676.3	676.5
150°	689.6	689.4	689.1	688.9	688.6	688.6	688.9	689.1	689.4	689.6	689.9
152.5°	703.1	702.5	702.0	701.4	700.7	700.6	700.8	701.1	701.4	701.7	702.0
155°	720.2	719.4	718.7	717.9	717.1	716.9	717.1	717.4	717.6	717.9	718.3
157.5°	733.5	733.0	732.6	732.1	731.6	731.4	731.4	731.4	731.4	731.5	732.0
160°	742.7	741.9	741.1	740.3	739.6	739.3	739.4	739.5	739.6	739.8	740.3
162.5°	750.0	749.3	748.5	747.7	747.0	746.7	746.8	746.9	747.0	747.2	747.9
165°	759.9	759.2	758.4	757.7	756.9	756.6	756.7	756.8	757.0	757.1	757.8
167.5°	767.3	766.6	765.8	765.0	764.2	763.9	764.0	764.1	764.2	764.4	765.3
170°	771.5	770.6	769.7	768.8	767.9	767.5	767.6	767.8	767.9	768.0	769.0
172.5°	774.3	773.4	772.4	771.5	770.6	770.3	770.5	770.8	771.0	771.2	772.1
175°	777.3	776.5	775.7	775.0	774.2	773.9	774.0	774.2	774.3	774.4	775.4
177.5°	778.6	778.0	777.4	776.8	776.2	775.9	776.0	776.1	776.2	776.3	777.1
180°	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3



TEST NUMBER: P333559-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1383.9	1385.8	1387.7	1388.6	1388.4	1388.2	1388.0	1387.8
5°	1375.4	1377.8	1380.1	1381.1	1380.6	1380.1	1379.7	1379.2
7.5°	1358.4	1360.0	1361.6	1362.1	1361.6	1361.1	1360.6	1360.1
10°	1343.8	1344.5	1345.2	1345.2	1344.5	1343.8	1343.1	1342.5
12.5°	1323.3	1323.8	1324.3	1324.1	1323.0	1321.9	1320.9	1319.8
15°	1289.6	1289.3	1289.1	1288.0	1285.9	1283.7	1281.6	1279.5
17.5°	1247.4	1246.3	1245.1	1243.6	1241.9	1240.2	1238.5	1236.8
20°	1216.4	1215.2	1214.1	1212.4	1210.3	1208.2	1206.1	1204.1
22.5°	1185.6	1183.4	1181.0	1179.0	1177.3	1175.6	1173.9	1172.2
25°	1135.1	1132.1	1129.0	1126.2	1123.6	1121.1	1118.5	1115.9
27.5°	1080.4	1076.1	1071.9	1068.5	1066.1	1063.6	1061.2	1058.6
30°	1041.3	1035.9	1030.5	1026.8	1024.7	1022.6	1020.5	1018.3
32.5°	1003.2	997.2	991.4	987.0	984.4	981.8	979.1	976.4
35°	944.0	937.3	930.5	925.5	922.2	919.0	915.7	912.4
37.5°	882.2	874.0	866.0	860.3	857.2	853.9	850.8	847.7
40°	841.2	832.4	823.5	817.7	815.0	812.1	809.3	806.6
42.5°	800.9	792.4	784.0	777.6	773.6	769.4	765.3	761.2
45°	736.5	727.2	717.8	711.4	707.9	704.5	700.9	697.4
47.5°	672.8	663.2	653.6	646.8	643.0	639.1	635.2	631.4
50°	629.7	619.9	610.1	603.4	600.0	596.4	592.9	589.5
52.5°	588.8	578.1	567.6	560.6	557.1	553.6	550.2	546.6
55°	526.5	516.0	505.5	498.4	494.7	491.0	487.3	483.5
57.5°	464.2	454.0	443.7	437.0	433.6	430.3	427.1	423.7
60°	423.1	412.8	402.6	395.8	392.2	388.8	385.3	381.7
62.5°	382.6	373.1	363.7	357.2	353.7	350.1	346.7	343.2
65°	323.3	314.0	304.6	298.2	294.7	291.2	287.7	284.2
67.5°	266.5	258.0	249.4	243.8	241.1	238.2	235.4	232.7
70°	228.8	221.7	214.4	209.4	206.6	203.8	201.1	198.2
72.5°	193.9	187.2	180.6	176.3	174.4	172.6	170.8	168.8
75°	145.0	139.9	134.7	131.4	129.7	128.1	126.4	124.8
77.5°	103.1	99.6	95.9	93.6	92.4	91.2	90.0	88.8
80°	77.7	75.5	73.4	72.1	71.7	71.2	70.7	70.3
82.5°	58.1	57.1	56.0	55.4	55.1	54.9	54.6	54.3
85°	33.1	32.8	32.6	32.4	32.1	31.9	31.7	31.5
87.5°	14.6	14.8	14.9	14.9	14.8	14.7	14.6	14.5
90°	10.5	11.1	11.8	12.3	12.7	13.0	13.4	13.8
92.5°	10.5	11.1	11.8	12.2	12.3	12.5	12.7	12.9
95°	10.5	11.1	11.8	12.1	12.1	12.1	12.1	12.1
97.5°	21.1	17.5	13.9	12.1	12.1	12.1	12.1	12.1
100°	62.1	43.0	23.9	14.1	13.6	13.1	12.6	12.1
102.5°	120.7	117.0	113.5	107.3	98.6	89.9	81.2	72.5
105°	171.7	171.7	171.7	171.7	171.5	171.4	171.3	171.1
107.5°	217.4	217.4	217.4	217.2	216.9	216.5	216.1	215.7
110°	247.0	246.6	246.2	246.1	246.2	246.3	246.5	246.6



TEST NUMBER: P333559-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	276.3	275.8	275.3	275.0	274.8	274.6	274.5	274.3
115°	320.4	319.9	319.4	318.8	318.0	317.3	316.5	315.8
117.5°	363.1	362.4	361.8	361.3	361.0	360.6	360.3	360.0
120°	390.7	390.4	390.2	389.7	389.1	388.5	387.8	387.2
122.5°	417.0	416.8	416.5	416.0	415.3	414.4	413.7	413.0
125°	455.3	454.7	454.2	453.8	453.4	453.0	452.7	452.3
127.5°	490.3	490.1	489.8	489.2	488.2	487.3	486.4	485.3
130°	513.2	512.8	512.4	511.9	511.3	510.6	510.0	509.4
132.5°	534.5	534.4	534.4	534.0	533.4	532.7	532.1	531.5
135°	565.8	565.6	565.3	564.8	564.1	563.3	562.5	561.8
137.5°	595.0	595.1	595.1	594.8	594.2	593.5	592.9	592.2
140°	613.0	613.2	613.5	613.2	612.5	611.7	611.0	610.2
142.5°	630.6	630.6	630.7	630.3	629.5	628.7	627.9	627.2
145°	655.4	655.5	655.6	655.3	654.5	653.8	653.0	652.2
147.5°	676.6	676.8	676.9	676.5	675.6	674.7	673.8	672.9
150°	690.1	690.4	690.6	690.3	689.3	688.2	687.2	686.2
152.5°	702.2	702.5	702.7	702.4	701.5	700.5	699.5	698.6
155°	718.7	719.0	719.4	719.1	718.1	717.1	716.1	715.0
157.5°	732.4	732.8	733.2	732.9	731.8	730.7	729.7	728.7
160°	740.8	741.3	741.8	741.5	740.5	739.5	738.5	737.5
162.5°	748.6	749.3	750.0	749.8	748.7	747.6	746.5	745.3
165°	758.6	759.4	760.1	760.0	759.0	758.0	757.0	755.9
167.5°	766.2	767.1	768.0	767.9	766.8	765.6	764.5	763.3
170°	770.1	771.1	772.1	772.0	770.9	769.7	768.6	767.5
172.5°	773.1	774.1	775.0	774.9	773.7	772.5	771.3	770.2
175°	776.4	777.4	778.5	778.4	777.3	776.1	775.0	773.8
177.5°	777.8	778.5	779.2	779.1	778.3	777.5	776.7	775.9
180°	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3

(END OF REPORT)