

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333544-930

Luminaire Tested: **S125RDIP-S610D1205U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333544-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D1205U930-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5882.5 lumens  
Efficiency: N/A  
Efficacy: 119.1 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	36	36	35	29
2	86	79	73	68	77	72	67	62	57	54	51	44	42	40	32	31	30	24
3	79	70	63	57	71	63	57	52	51	47	43	39	37	34	29	27	26	21
4	72	62	54	48	65	56	49	44	45	41	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	36	32	32	28	26	23	21	19	16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14
7	56	44	37	31	51	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4873	4873	4873	4873
5°	5606	4879	4309	4879
10°	6431	4854	3802	4854
15°	6946	4804	3380	4804
20°	7659	4746	3120	4746
25°	8863	4670	2895	4670
30°	9645	4589	2748	4589
35°	8136	4495	2613	4495
40°	5681	4326	2496	4326
45°	4215	4098	2382	4098
50°	3361	3861	2284	3861
55°	2852	3567	2197	3567
60°	2465	3304	2056	3304
65°	2196	3020	1771	3020
70°	1930	2766	1613	2766
75°	1669	2395	1515	2395
80°	1268	2016	1268	2016
85°	1060	1586	1193	1586



TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.3	1.2
10°-20°	212.0	3.6
20°-30°	336.2	5.7
30°-40°	405.4	6.9
40°-50°	362.0	6.2
50°-60°	277.6	4.7
60°-70°	180.4	3.1
70°-80°	87.7	1.5
80°-90°	23.6	0.4
90°-100°	46.5	0.8
100°-110°	286.3	4.9
110°-120°	519.2	8.8
120°-130°	666.3	11.3
130°-140°	716.7	12.2
140°-150°	672.7	11.4
150°-160°	544.2	9.3
160°-170°	351.9	6.0
170°-180°	121.4	2.1
0°-30°	620.5	10.5
0°-40°	1025.9	17.4
0°-60°	1665.6	28.3
0°-90°	1957.3	33.3
90°-120°	851.9	14.5
90°-150°	2907.7	49.4
90°-180°	3925.0	66.7
0°-180°	5882.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	754	754	754	754	754	
5°	865	753	665	753	865	86
15°	1039	718	506	718	1039	298
25°	1244	655	406	655	1244	571
35°	1032	570	331	570	1032	623
45°	462	449	261	449	462	368
55°	253	317	195	317	253	230
65°	144	198	116	198	144	143
75°	67	96	61	96	67	71
85°	14	21	16	21	14	17
90°	23	1	23	1	23	10
95°	20	54	20	54	20	16
105°	281	279	281	279	281	254
115°	519	523	519	523	519	515
125°	744	744	744	744	744	662
135°	924	928	924	928	924	713
145°	1073	1076	1073	1076	1073	670
155°	1176	1184	1176	1184	1176	542
165°	1243	1250	1243	1250	1243	351
175°	1272	1278	1272	1278	1272	121
180°	1278	1278	1278	1278	1278	



TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	793.6	793.1	794.1	791.3	791.7	787.4	787.4	784.2	780.0	776.7	775.3
5°	864.7	865.4	864.1	859.4	856.3	851.7	846.4	837.1	829.4	822.0	816.1
7.5°	937.9	938.3	934.3	932.9	925.0	919.3	907.7	895.0	883.8	869.5	858.7
10°	980.6	980.2	975.9	972.5	965.6	957.0	945.5	930.7	916.7	901.2	886.4
12.5°	1005.3	1004.5	1003.1	999.0	992.7	985.0	975.3	960.7	943.5	926.5	909.2
15°	1038.8	1036.6	1032.6	1027.3	1018.3	1009.3	998.5	985.5	969.1	949.9	933.8
17.5°	1080.1	1080.2	1074.0	1066.7	1054.5	1038.6	1021.9	1000.9	978.6	957.5	940.4
20°	1114.4	1113.4	1107.2	1093.0	1079.0	1059.2	1040.0	1014.3	987.1	959.4	938.1
22.5°	1163.4	1161.0	1154.5	1135.8	1114.2	1088.7	1059.3	1027.9	995.0	963.7	935.6
25°	1243.8	1241.9	1229.2	1207.5	1177.2	1137.8	1099.4	1056.4	1009.0	967.8	933.8
27.5°	1298.8	1296.7	1287.4	1269.3	1241.3	1200.0	1147.9	1090.5	1031.3	974.6	925.4
30°	1293.3	1298.0	1296.7	1288.4	1267.3	1230.1	1182.2	1117.4	1047.1	980.6	922.0
32.5°	1215.5	1219.7	1230.6	1247.0	1248.2	1233.4	1197.5	1137.8	1064.9	989.2	919.2
35°	1031.9	1037.5	1058.6	1091.7	1135.1	1171.3	1178.8	1146.6	1081.2	999.7	915.2
37.5°	793.4	823.9	841.6	876.4	941.9	1008.6	1072.7	1096.3	1068.5	995.4	908.6
40°	673.9	681.3	713.0	752.3	807.4	876.8	968.2	1034.1	1036.2	985.5	898.1
42.5°	576.8	586.2	607.9	639.3	686.5	755.9	850.2	937.3	977.5	958.2	884.5
45°	461.5	468.6	484.4	508.5	544.8	602.1	683.2	783.9	863.8	895.0	848.0
47.5°	379.1	382.9	396.6	415.1	441.9	483.6	546.4	633.8	729.7	796.9	790.3
50°	334.5	338.8	349.4	363.3	385.9	421.2	471.4	544.1	642.9	725.0	741.4
52.5°	299.8	303.4	310.0	323.2	341.8	368.9	409.4	475.3	564.2	651.4	689.4
55°	253.3	255.8	261.1	268.5	283.4	302.9	337.9	383.4	455.3	543.2	599.0
57.5°	215.1	216.3	219.6	226.5	236.8	251.0	276.3	315.0	366.5	445.6	507.2
60°	190.8	192.0	196.3	201.0	209.0	222.1	241.9	268.8	318.4	383.8	446.0
62.5°	171.5	172.2	174.1	178.7	185.7	195.8	211.4	233.4	272.8	330.2	389.0
65°	143.7	144.0	144.6	148.4	152.7	160.1	170.3	185.8	215.6	258.9	311.0
67.5°	117.1	117.5	119.7	121.0	125.5	129.4	135.4	147.2	168.2	197.4	237.8
70°	102.2	101.9	104.0	105.6	107.1	111.8	115.9	125.4	138.4	160.8	194.5
72.5°	88.3	87.6	88.5	89.0	91.1	94.2	98.2	104.1	114.1	129.6	155.3
75°	66.9	67.2	67.2	67.8	69.4	70.6	71.8	74.9	80.6	90.7	104.7
77.5°	47.0	46.5	47.8	47.9	48.8	50.2	51.3	52.5	54.8	59.0	66.2
80°	34.1	34.1	34.4	35.3	35.0	35.6	37.2	38.4	41.2	43.7	46.1
82.5°	26.2	25.9	26.2	26.4	26.3	26.9	27.5	27.7	28.8	30.0	31.8
85°	14.3	14.3	14.6	14.6	14.8	14.8	15.2	15.2	15.2	15.5	15.8
87.5°	10.0	9.6	9.2	9.1	9.2	9.5	9.1	8.6	8.5	8.2	8.2
90°	22.7	22.1	21.4	20.9	20.2	19.4	18.3	17.3	16.2	15.2	13.7
92.5°	21.2	21.0	20.6	20.3	20.1	19.4	18.3	17.3	16.2	15.2	13.9
95°	19.9	19.9	19.9	19.9	19.9	19.4	18.3	17.3	16.2	15.2	23.2
97.5°	19.9	19.9	19.9	19.9	19.9	22.8	28.8	34.7	40.7	46.6	62.5
100°	19.9	20.7	21.6	22.4	23.2	39.4	70.8	102.2	133.5	164.9	164.0
102.5°	119.2	133.5	147.8	162.2	176.5	186.6	192.6	198.4	204.4	210.3	209.9
105°	281.4	281.6	281.8	282.0	282.3	282.3	282.3	282.3	282.3	282.3	282.3
107.5°	354.7	355.4	356.0	356.6	357.3	357.6	357.5	357.5	357.4	357.4	357.0
110°	405.5	405.4	405.1	404.9	404.7	404.9	405.5	406.2	406.8	407.4	407.0



TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	451.0	451.3	451.6	451.9	452.2	452.7	453.6	454.4	455.2	455.9	455.7
115°	519.3	520.5	521.8	523.0	524.3	525.4	526.2	527.0	527.9	528.7	528.5
117.5°	592.0	592.6	593.1	593.6	594.2	595.0	596.1	597.2	598.3	599.4	598.6
120°	636.7	637.8	638.9	639.9	641.0	641.7	642.1	642.5	642.9	643.4	642.7
122.5°	679.2	680.4	681.6	682.8	684.0	684.9	685.3	685.7	686.2	686.6	686.3
125°	743.8	744.4	745.1	745.7	746.3	747.1	747.9	748.8	749.6	750.4	750.4
127.5°	798.2	799.7	801.3	802.9	804.5	805.4	805.9	806.3	806.8	807.3	807.4
130°	837.6	838.7	839.8	840.7	841.8	842.7	843.3	843.9	844.6	845.2	845.0
132.5°	874.0	875.1	876.1	877.2	878.2	878.8	878.9	879.1	879.2	879.3	879.8
135°	923.8	925.1	926.3	927.6	928.9	929.8	930.2	930.6	931.0	931.4	931.8
137.5°	973.9	974.9	976.1	977.1	978.3	978.8	978.7	978.6	978.5	978.4	978.8
140°	1003.5	1004.7	1006.0	1007.2	1008.4	1008.9	1008.4	1008.0	1007.6	1007.2	1007.5
142.5°	1031.5	1032.7	1034.0	1035.3	1036.6	1037.1	1037.1	1037.0	1036.9	1036.8	1036.5
145°	1072.6	1073.8	1075.1	1076.4	1077.7	1078.2	1078.0	1077.7	1077.6	1077.3	1077.3
147.5°	1106.5	1108.1	1109.5	1111.1	1112.6	1113.2	1113.0	1112.7	1112.5	1112.2	1112.0
150°	1128.5	1130.2	1131.9	1133.6	1135.2	1135.9	1135.5	1135.1	1134.6	1134.2	1133.8
152.5°	1149.0	1150.5	1152.0	1153.5	1155.0	1155.6	1155.2	1154.7	1154.3	1153.9	1153.5
155°	1175.9	1177.5	1179.2	1181.0	1182.6	1183.2	1182.5	1181.9	1181.3	1180.6	1180.2
157.5°	1198.4	1200.1	1201.8	1203.5	1205.2	1205.7	1205.0	1204.4	1203.6	1203.0	1203.0
160°	1212.8	1214.6	1216.2	1217.9	1219.6	1220.0	1219.1	1218.3	1217.5	1216.6	1216.4
162.5°	1225.7	1227.6	1229.4	1231.3	1233.1	1233.5	1232.3	1231.1	1230.0	1228.7	1228.6
165°	1243.2	1244.8	1246.5	1248.2	1249.9	1250.1	1248.9	1247.6	1246.3	1245.0	1244.8
167.5°	1255.3	1257.2	1259.1	1260.9	1262.9	1263.1	1261.5	1260.0	1258.5	1257.0	1256.8
170°	1262.1	1264.0	1265.9	1267.8	1269.7	1269.8	1268.1	1266.4	1264.8	1263.1	1262.8
172.5°	1266.6	1268.5	1270.5	1272.4	1274.2	1274.4	1272.9	1271.4	1269.9	1268.4	1268.0
175°	1272.5	1274.4	1276.4	1278.2	1280.1	1280.2	1278.6	1276.8	1275.1	1273.5	1273.3
177.5°	1275.9	1277.2	1278.6	1280.0	1281.3	1281.4	1280.3	1279.0	1277.9	1276.7	1276.5
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	775.3	773.6	770.3	767.4	763.6	760.4	758.1	755.5	752.0	747.8	744.3
5°	809.6	802.7	793.8	786.0	776.2	768.4	760.3	752.6	744.9	734.9	726.3
7.5°	847.6	833.6	819.9	802.7	787.0	773.1	759.7	746.2	732.9	718.8	705.2
10°	870.9	853.9	834.9	813.3	793.4	774.6	757.2	740.2	722.3	706.5	689.4
12.5°	892.7	870.7	849.1	821.7	797.9	774.9	752.8	731.6	712.3	691.9	673.5
15°	912.4	890.7	866.6	833.2	800.0	772.1	746.1	718.5	694.7	671.7	651.3
17.5°	920.0	897.3	869.2	837.1	800.9	765.8	732.3	702.1	674.0	647.3	624.3
20°	917.0	895.0	866.3	835.6	796.9	760.3	724.1	690.6	659.3	631.2	606.7
22.5°	909.9	887.1	859.3	827.0	790.2	751.4	712.7	677.0	644.2	615.1	588.4
25°	899.1	868.1	839.6	808.0	773.1	734.7	694.7	655.3	620.4	590.6	561.5
27.5°	887.9	849.2	813.0	781.5	744.6	710.4	671.8	631.5	594.7	564.4	534.6
30°	877.8	834.4	794.4	758.8	723.8	691.3	654.7	615.4	577.6	546.3	516.0
32.5°	865.1	819.0	775.1	734.0	700.3	668.0	634.9	597.3	560.5	528.2	497.4
35°	849.2	790.4	742.7	699.0	661.5	630.2	600.5	570.1	533.3	499.9	469.9
37.5°	828.4	761.7	706.5	658.8	619.4	587.9	564.5	536.7	503.1	471.1	443.2
40°	815.8	740.9	680.4	633.3	591.8	558.7	536.7	513.1	482.5	452.5	424.6
42.5°	798.9	721.8	654.2	605.1	563.4	531.5	509.2	488.7	462.9	434.6	404.8
45°	765.9	684.8	613.8	561.2	519.1	487.8	467.0	448.7	429.3	403.2	377.2
47.5°	722.9	646.2	571.9	514.5	473.2	444.2	424.0	409.6	395.7	373.6	348.3
50°	688.5	614.5	542.0	486.2	442.3	414.7	395.8	384.3	371.6	351.6	330.4
52.5°	647.8	581.8	510.8	453.8	412.3	386.5	368.3	356.9	346.3	330.0	309.9
55°	583.8	525.9	460.8	409.1	371.0	345.0	327.7	316.8	310.6	296.7	280.9
57.5°	509.9	468.4	411.1	361.2	327.5	301.7	289.1	279.9	272.9	263.0	251.8
60°	458.4	429.3	377.8	330.4	299.5	275.0	263.6	255.8	249.3	240.9	232.3
62.5°	406.1	384.9	340.2	299.5	271.0	250.5	239.8	232.8	225.3	219.6	211.2
65°	336.1	317.2	286.2	254.3	228.0	211.6	203.8	197.6	193.0	186.8	180.8
67.5°	261.4	253.7	232.4	210.3	191.4	176.8	170.2	165.8	160.2	156.5	152.5
70°	215.6	211.8	196.7	182.1	164.4	154.6	148.4	146.5	139.7	136.0	133.1
72.5°	175.0	173.2	164.4	154.3	141.9	133.2	127.5	125.4	121.1	118.1	116.3
75°	119.8	120.5	119.0	112.4	107.8	102.2	97.3	96.0	92.9	90.4	88.9
77.5°	75.8	79.0	79.1	78.8	77.0	73.5	71.5	70.5	67.5	66.6	66.2
80°	52.0	55.4	58.5	58.2	57.6	56.7	55.1	54.2	52.7	51.7	51.1
82.5°	34.7	37.8	40.4	42.2	42.0	41.1	40.0	39.5	39.3	38.6	38.5
85°	16.4	17.0	17.9	20.1	21.7	22.0	21.7	21.4	20.5	20.8	21.0
87.5°	8.2	7.8	7.8	7.5	6.9	7.8	8.2	8.2	8.0	7.8	7.7
90°	12.2	10.8	9.3	7.7	6.0	4.3	2.6	1.0	2.6	4.3	6.0
92.5°	12.6	11.3	9.9	9.9	11.1	12.2	13.5	14.6	13.5	12.2	11.1
95°	31.1	39.1	47.2	51.4	52.1	52.7	53.4	54.0	53.4	52.7	52.1
97.5°	78.3	94.1	110.0	117.3	116.2	115.0	113.9	112.8	113.9	115.0	116.2
100°	163.2	162.3	161.5	160.8	160.1	159.5	158.9	158.2	158.9	159.5	160.1
102.5°	209.4	208.8	208.3	207.7	206.8	206.1	205.3	204.5	205.3	206.1	206.8
105°	282.3	282.3	282.3	281.9	281.1	280.2	279.4	278.6	279.4	280.2	281.1
107.5°	356.5	356.1	355.7	355.6	355.6	355.6	355.6	355.6	355.6	355.6	355.6
110°	406.6	406.2	405.8	405.5	405.5	405.5	405.5	405.5	405.5	405.5	405.5





TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	455.4	455.2	454.9	454.5	454.0	453.6	453.1	452.6	453.1	453.6	454.0
115°	528.3	528.1	527.9	527.3	526.2	525.1	524.1	523.0	524.1	525.1	526.2
117.5°	597.8	597.0	596.2	595.8	595.9	595.9	596.0	596.0	596.0	595.9	595.9
120°	642.1	641.5	640.8	640.7	640.8	641.1	641.2	641.5	641.2	641.1	640.8
122.5°	686.0	685.7	685.4	684.9	684.0	683.2	682.5	681.7	682.5	683.2	684.0
125°	750.4	750.4	750.4	749.7	748.2	746.7	745.3	743.8	745.3	746.7	748.2
127.5°	807.6	807.6	807.8	807.3	806.2	805.2	804.2	803.2	804.2	805.2	806.2
130°	844.8	844.6	844.3	843.8	842.7	841.6	840.6	839.5	840.6	841.6	842.7
132.5°	880.2	880.7	881.2	880.8	879.5	878.3	877.1	875.9	877.1	878.3	879.5
135°	932.3	932.7	933.1	932.7	931.4	930.2	928.9	927.6	928.9	930.2	931.4
137.5°	979.2	979.6	979.9	979.6	978.4	977.4	976.3	975.2	976.3	977.4	978.4
140°	1007.6	1007.9	1008.0	1008.0	1007.5	1007.1	1006.7	1006.2	1006.7	1007.1	1007.5
142.5°	1036.2	1035.9	1035.6	1035.3	1035.1	1034.9	1034.5	1034.3	1034.5	1034.9	1035.1
145°	1077.3	1077.3	1077.3	1077.1	1076.7	1076.3	1075.9	1075.5	1075.9	1076.3	1076.7
147.5°	1111.7	1111.4	1111.2	1111.1	1111.2	1111.3	1111.3	1111.4	1111.3	1111.3	1111.2
150°	1133.3	1132.9	1132.5	1132.5	1132.9	1133.3	1133.8	1134.2	1133.8	1133.3	1132.9
152.5°	1153.1	1152.7	1152.2	1152.4	1153.4	1154.3	1155.3	1156.2	1155.3	1154.3	1153.4
155°	1179.7	1179.3	1178.9	1179.3	1180.6	1181.9	1183.2	1184.4	1183.2	1181.9	1180.6
157.5°	1202.9	1202.9	1202.8	1203.1	1204.0	1204.7	1205.4	1206.2	1205.4	1204.7	1204.0
160°	1216.2	1216.0	1215.8	1216.3	1217.6	1218.9	1220.1	1221.4	1220.1	1218.9	1217.6
162.5°	1228.3	1228.1	1227.9	1228.4	1229.7	1230.9	1232.2	1233.5	1232.2	1230.9	1229.7
165°	1244.6	1244.4	1244.2	1244.7	1246.0	1247.2	1248.5	1249.8	1248.5	1247.2	1246.0
167.5°	1256.5	1256.4	1256.1	1256.7	1258.0	1259.3	1260.6	1261.9	1260.6	1259.3	1258.0
170°	1262.7	1262.4	1262.2	1262.8	1264.3	1265.8	1267.3	1268.8	1267.3	1265.8	1264.3
172.5°	1267.6	1267.2	1266.8	1267.4	1268.9	1270.3	1271.8	1273.3	1271.8	1270.3	1268.9
175°	1273.1	1272.8	1272.6	1273.2	1274.4	1275.7	1276.9	1278.2	1276.9	1275.7	1274.4
177.5°	1276.4	1276.2	1276.0	1276.4	1277.5	1278.5	1279.4	1280.5	1279.4	1278.5	1277.5
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	741.8	738.3	735.9	730.9	727.4	725.9	723.3	722.5	725.2	723.3	723.0
5°	719.7	710.8	703.7	696.5	688.8	683.9	676.4	675.1	673.3	670.5	669.9
7.5°	693.3	681.6	672.5	660.6	650.4	642.2	632.9	628.5	626.1	622.5	617.7
10°	675.5	661.5	649.1	637.4	624.7	614.5	605.2	598.0	593.4	589.1	587.2
12.5°	657.9	643.7	627.9	613.6	599.4	587.9	577.6	573.0	567.9	562.8	558.5
15°	630.6	611.6	594.4	577.9	565.8	553.4	543.6	536.7	529.0	526.8	518.4
17.5°	601.6	583.0	562.7	545.4	531.5	517.8	507.0	499.2	493.3	485.3	481.5
20°	583.5	561.5	541.7	525.9	510.4	494.3	483.1	476.6	471.1	464.6	461.5
22.5°	564.2	542.7	522.4	503.9	488.1	472.2	464.3	457.5	451.3	445.2	441.2
25°	535.8	514.1	492.8	473.5	457.1	445.6	436.3	428.6	425.3	419.3	415.0
27.5°	507.8	484.7	462.5	443.4	430.5	419.1	411.6	405.4	399.3	394.1	390.4
30°	489.7	466.1	442.0	426.8	413.1	402.4	394.0	388.1	383.4	378.8	376.0
32.5°	471.6	447.3	425.8	409.4	396.6	387.2	378.6	372.9	368.0	362.9	359.6
35°	442.5	417.8	400.5	384.3	371.6	363.0	357.1	349.0	345.0	341.3	337.9
37.5°	415.6	392.6	373.8	359.7	348.7	340.1	332.5	328.1	323.2	319.8	317.0
40°	395.8	374.7	357.8	342.8	334.8	325.2	318.0	312.5	308.8	304.4	301.3
42.5°	378.0	358.4	341.9	328.5	318.5	310.3	303.5	297.9	293.2	290.1	287.5
45°	352.8	333.2	317.2	304.8	295.5	287.7	280.6	277.8	271.6	267.9	266.7
47.5°	326.7	309.2	293.7	282.3	272.7	265.4	258.7	253.1	249.6	246.0	244.0
50°	309.1	292.4	277.8	266.7	257.4	249.3	243.1	239.4	234.7	231.4	228.9
52.5°	291.5	276.0	261.5	250.8	242.7	234.7	227.8	224.0	219.6	217.4	215.7
55°	266.4	250.0	237.6	227.0	218.7	211.2	204.7	201.0	198.2	196.1	195.4
57.5°	237.8	224.9	213.4	203.8	195.2	188.2	182.5	179.0	176.5	176.2	174.3
60°	219.2	207.5	197.0	186.8	179.3	172.8	167.9	163.9	161.3	161.0	160.5
62.5°	200.7	189.4	179.6	170.6	164.0	157.7	153.0	148.5	147.0	145.4	144.1
65°	173.1	162.9	154.8	147.7	140.6	135.3	130.7	127.9	124.5	122.6	119.3
67.5°	146.0	138.1	130.4	124.4	118.8	113.8	110.0	105.8	103.5	102.0	99.5
70°	128.2	122.1	114.3	107.8	103.5	99.4	96.3	91.6	90.1	88.9	87.6
72.5°	111.4	105.9	99.4	94.2	89.8	86.0	82.4	80.3	78.8	77.5	76.7
75°	87.6	82.3	76.8	73.1	70.0	66.9	65.1	63.5	62.9	62.5	61.3
77.5°	64.3	61.6	57.1	54.1	52.1	50.9	49.2	48.3	48.3	47.0	46.6
80°	49.2	47.7	43.9	42.7	41.2	39.9	39.1	37.5	36.0	35.3	34.4
82.5°	36.6	35.1	33.6	31.6	30.3	29.5	28.6	28.0	28.2	27.4	26.9
85°	19.5	17.9	17.4	17.0	16.4	17.0	16.7	16.4	16.1	15.8	16.1
87.5°	7.7	8.1	8.1	8.9	8.4	9.0	9.2	9.1	9.4	9.5	9.5
90°	7.7	9.3	10.8	12.2	13.7	15.2	16.2	17.3	18.3	19.4	20.2
92.5°	9.9	9.9	11.3	12.6	13.9	15.2	16.2	17.3	18.3	19.4	20.1
95°	51.4	47.2	39.1	31.1	23.2	15.2	16.2	17.3	18.3	19.4	19.9
97.5°	117.3	110.0	94.1	78.3	62.5	46.6	40.7	34.7	28.8	22.8	19.9
100°	160.8	161.5	162.3	163.2	164.0	164.9	133.5	102.2	70.8	39.4	23.2
102.5°	207.7	208.3	208.8	209.4	209.9	210.3	204.4	198.4	192.6	186.6	176.5
105°	281.9	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3
107.5°	355.6	355.7	356.1	356.5	357.0	357.4	357.4	357.5	357.5	357.6	357.3
110°	405.5	405.8	406.2	406.6	407.0	407.4	406.8	406.2	405.5	404.9	404.7



TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	454.5	454.9	455.2	455.4	455.7	455.9	455.2	454.4	453.6	452.7	452.2
115°	527.3	527.9	528.1	528.3	528.5	528.7	527.9	527.0	526.2	525.4	524.3
117.5°	595.8	596.2	597.0	597.8	598.6	599.4	598.3	597.2	596.1	595.0	594.2
120°	640.7	640.8	641.5	642.1	642.7	643.4	642.9	642.5	642.1	641.7	641.0
122.5°	684.9	685.4	685.7	686.0	686.3	686.6	686.2	685.7	685.3	684.9	684.0
125°	749.7	750.4	750.4	750.4	750.4	750.4	749.6	748.8	747.9	747.1	746.3
127.5°	807.3	807.8	807.6	807.6	807.4	807.3	806.8	806.3	805.9	805.4	804.5
130°	843.8	844.3	844.6	844.8	845.0	845.2	844.6	843.9	843.3	842.7	841.8
132.5°	880.8	881.2	880.7	880.2	879.8	879.3	879.2	879.1	878.9	878.8	878.2
135°	932.7	933.1	932.7	932.3	931.8	931.4	931.0	930.6	930.2	929.8	928.9
137.5°	979.6	979.9	979.6	979.2	978.8	978.4	978.5	978.6	978.7	978.8	978.3
140°	1008.0	1008.0	1007.9	1007.6	1007.5	1007.2	1007.6	1008.0	1008.4	1008.9	1008.4
142.5°	1035.3	1035.6	1035.9	1036.2	1036.5	1036.8	1036.9	1037.0	1037.1	1037.1	1036.6
145°	1077.1	1077.3	1077.3	1077.3	1077.3	1077.3	1077.6	1077.7	1078.0	1078.2	1077.7
147.5°	1111.1	1111.2	1111.4	1111.7	1112.0	1112.2	1112.5	1112.7	1113.0	1113.2	1112.6
150°	1132.5	1132.5	1132.9	1133.3	1133.8	1134.2	1134.6	1135.1	1135.5	1135.9	1135.2
152.5°	1152.4	1152.2	1152.7	1153.1	1153.5	1153.9	1154.3	1154.7	1155.2	1155.6	1155.0
155°	1179.3	1178.9	1179.3	1179.7	1180.2	1180.6	1181.3	1181.9	1182.5	1183.2	1182.6
157.5°	1203.1	1202.8	1202.9	1202.9	1203.0	1203.0	1203.6	1204.4	1205.0	1205.7	1205.2
160°	1216.3	1215.8	1216.0	1216.2	1216.4	1216.6	1217.5	1218.3	1219.1	1220.0	1219.6
162.5°	1228.4	1227.9	1228.1	1228.3	1228.6	1228.7	1230.0	1231.1	1232.3	1233.5	1233.1
165°	1244.7	1244.2	1244.4	1244.6	1244.8	1245.0	1246.3	1247.6	1248.9	1250.1	1249.9
167.5°	1256.7	1256.1	1256.4	1256.5	1256.8	1257.0	1258.5	1260.0	1261.5	1263.1	1262.9
170°	1262.8	1262.2	1262.4	1262.7	1262.8	1263.1	1264.8	1266.4	1268.1	1269.8	1269.7
172.5°	1267.4	1266.8	1267.2	1267.6	1268.0	1268.4	1269.9	1271.4	1272.9	1274.4	1274.2
175°	1273.2	1272.6	1272.8	1273.1	1273.3	1273.5	1275.1	1276.8	1278.6	1280.2	1280.1
177.5°	1276.4	1276.0	1276.2	1276.4	1276.5	1276.7	1277.9	1279.0	1280.3	1281.4	1281.3
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	722.8	720.0	719.3	720.2	719.3	720.0	722.8	723.0	723.3	725.2	722.5
5°	666.8	663.7	665.3	664.6	665.3	663.7	666.8	669.9	670.5	673.3	675.1
7.5°	617.6	613.8	609.7	611.0	609.7	613.8	617.6	617.7	622.5	626.1	628.5
10°	583.2	580.1	578.2	579.8	578.2	580.1	583.2	587.2	589.1	593.4	598.0
12.5°	554.2	552.4	550.7	550.1	550.7	552.4	554.2	558.5	562.8	567.9	573.0
15°	514.7	511.0	509.5	505.5	509.5	511.0	514.7	518.4	526.8	529.0	536.7
17.5°	478.3	477.1	473.1	471.4	473.1	477.1	478.3	481.5	485.3	493.3	499.2
20°	456.8	455.6	451.6	454.0	451.6	455.6	456.8	461.5	464.6	471.1	476.6
22.5°	439.0	436.3	435.0	434.2	435.0	436.3	439.0	441.2	445.2	451.3	457.5
25°	413.8	409.8	408.2	406.3	408.2	409.8	413.8	415.0	419.3	425.3	428.6
27.5°	388.7	386.5	384.4	383.9	384.4	386.5	388.7	390.4	394.1	399.3	405.4
30°	372.3	370.1	368.5	368.5	368.5	370.1	372.3	376.0	378.8	383.4	388.1
32.5°	357.7	356.0	354.4	354.2	354.4	356.0	357.7	359.6	362.9	368.0	372.9
35°	336.3	333.9	333.2	331.4	333.2	333.9	336.3	337.9	341.3	345.0	349.0
37.5°	314.2	312.2	312.1	311.9	312.1	312.2	314.2	317.0	319.8	323.2	328.1
40°	300.1	298.6	298.2	296.1	298.2	298.6	300.1	301.3	304.4	308.8	312.5
42.5°	285.0	284.2	283.2	282.2	283.2	284.2	285.0	287.5	290.1	293.2	297.9
45°	264.5	262.4	262.4	260.8	262.4	262.4	264.5	266.7	267.9	271.6	277.8
47.5°	243.3	241.7	241.8	240.2	241.8	241.7	243.3	244.0	246.0	249.6	253.1
50°	229.2	228.3	228.0	227.3	228.0	228.3	229.2	228.9	231.4	234.7	239.4
52.5°	215.1	214.7	215.8	214.4	215.8	214.7	215.1	215.7	217.4	219.6	224.0
55°	196.1	195.1	197.0	195.1	197.0	195.1	196.1	195.4	196.1	198.2	201.0
57.5°	174.1	173.3	175.0	174.1	175.0	173.3	174.1	174.3	176.2	176.5	179.0
60°	159.8	157.9	158.9	159.2	158.9	157.9	159.8	160.5	161.0	161.3	163.9
62.5°	142.7	141.6	142.3	140.9	142.3	141.6	142.7	144.1	145.4	147.0	148.5
65°	118.6	117.7	116.4	115.9	116.4	117.7	118.6	119.3	122.6	124.5	127.9
67.5°	99.6	97.4	97.3	97.8	97.3	97.4	99.6	99.5	102.0	103.5	105.8
70°	85.8	85.8	85.4	85.4	85.4	85.8	85.8	87.6	88.9	90.1	91.6
72.5°	76.1	75.9	75.3	75.1	75.3	75.9	76.1	76.7	77.5	78.8	80.3
75°	61.3	61.6	61.0	60.7	61.0	61.6	61.3	61.3	62.5	62.9	63.5
77.5°	45.2	43.9	44.7	43.9	44.7	43.9	45.2	46.6	47.0	48.3	48.3
80°	34.4	34.1	35.0	34.1	35.0	34.1	34.4	34.4	35.3	36.0	37.5
82.5°	27.2	26.9	27.3	26.7	27.3	26.9	27.2	26.9	27.4	28.2	28.0
85°	16.4	16.1	15.8	16.1	15.8	16.1	16.4	16.1	15.8	16.1	16.4
87.5°	9.9	9.8	9.9	10.0	9.9	9.8	9.9	9.5	9.5	9.4	9.1
90°	20.9	21.4	22.1	22.7	22.1	21.4	20.9	20.2	19.4	18.3	17.3
92.5°	20.3	20.6	21.0	21.2	21.0	20.6	20.3	20.1	19.4	18.3	17.3
95°	19.9	19.9	19.9	19.9	19.9	19.9	19.9	19.9	19.4	18.3	17.3
97.5°	19.9	19.9	19.9	19.9	19.9	19.9	19.9	19.9	22.8	28.8	34.7
100°	22.4	21.6	20.7	19.9	20.7	21.6	22.4	23.2	39.4	70.8	102.2
102.5°	162.2	147.8	133.5	119.2	133.5	147.8	162.2	176.5	186.6	192.6	198.4
105°	282.0	281.8	281.6	281.4	281.6	281.8	282.0	282.3	282.3	282.3	282.3
107.5°	356.6	356.0	355.4	354.7	355.4	356.0	356.6	357.3	357.6	357.5	357.5
110°	404.9	405.1	405.4	405.5	405.4	405.1	404.9	404.7	404.9	405.5	406.2



TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	451.9	451.6	451.3	451.0	451.3	451.6	451.9	452.2	452.7	453.6	454.4
115°	523.0	521.8	520.5	519.3	520.5	521.8	523.0	524.3	525.4	526.2	527.0
117.5°	593.6	593.1	592.6	592.0	592.6	593.1	593.6	594.2	595.0	596.1	597.2
120°	639.9	638.9	637.8	636.7	637.8	638.9	639.9	641.0	641.7	642.1	642.5
122.5°	682.8	681.6	680.4	679.2	680.4	681.6	682.8	684.0	684.9	685.3	685.7
125°	745.7	745.1	744.4	743.8	744.4	745.1	745.7	746.3	747.1	747.9	748.8
127.5°	802.9	801.3	799.7	798.2	799.7	801.3	802.9	804.5	805.4	805.9	806.3
130°	840.7	839.8	838.7	837.6	838.7	839.8	840.7	841.8	842.7	843.3	843.9
132.5°	877.2	876.1	875.1	874.0	875.1	876.1	877.2	878.2	878.8	878.9	879.1
135°	927.6	926.3	925.1	923.8	925.1	926.3	927.6	928.9	929.8	930.2	930.6
137.5°	977.1	976.1	974.9	973.9	974.9	976.1	977.1	978.3	978.8	978.7	978.6
140°	1007.2	1006.0	1004.7	1003.5	1004.7	1006.0	1007.2	1008.4	1008.9	1008.4	1008.0
142.5°	1035.3	1034.0	1032.7	1031.5	1032.7	1034.0	1035.3	1036.6	1037.1	1037.1	1037.0
145°	1076.4	1075.1	1073.8	1072.6	1073.8	1075.1	1076.4	1077.7	1078.2	1078.0	1077.7
147.5°	1111.1	1109.5	1108.1	1106.5	1108.1	1109.5	1111.1	1112.6	1113.2	1113.0	1112.7
150°	1133.6	1131.9	1130.2	1128.5	1130.2	1131.9	1133.6	1135.2	1135.9	1135.5	1135.1
152.5°	1153.5	1152.0	1150.5	1149.0	1150.5	1152.0	1153.5	1155.0	1155.6	1155.2	1154.7
155°	1181.0	1179.2	1177.5	1175.9	1177.5	1179.2	1181.0	1182.6	1183.2	1182.5	1181.9
157.5°	1203.5	1201.8	1200.1	1198.4	1200.1	1201.8	1203.5	1205.2	1205.7	1205.0	1204.4
160°	1217.9	1216.2	1214.6	1212.8	1214.6	1216.2	1217.9	1219.6	1220.0	1219.1	1218.3
162.5°	1231.3	1229.4	1227.6	1225.7	1227.6	1229.4	1231.3	1233.1	1233.5	1232.3	1231.1
165°	1248.2	1246.5	1244.8	1243.2	1244.8	1246.5	1248.2	1249.9	1250.1	1248.9	1247.6
167.5°	1260.9	1259.1	1257.2	1255.3	1257.2	1259.1	1260.9	1262.9	1263.1	1261.5	1260.0
170°	1267.8	1265.9	1264.0	1262.1	1264.0	1265.9	1267.8	1269.7	1269.8	1268.1	1266.4
172.5°	1272.4	1270.5	1268.5	1266.6	1268.5	1270.5	1272.4	1274.2	1274.4	1272.9	1271.4
175°	1278.2	1276.4	1274.4	1272.5	1274.4	1276.4	1278.2	1280.1	1280.2	1278.6	1276.8
177.5°	1280.0	1278.6	1277.2	1275.9	1277.2	1278.6	1280.0	1281.3	1281.4	1280.3	1279.0
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	723.3	725.9	727.4	730.9	735.9	738.3	741.8	744.3	747.8	752.0	755.5
5°	676.4	683.9	688.8	696.5	703.7	710.8	719.7	726.3	734.9	744.9	752.6
7.5°	632.9	642.2	650.4	660.6	672.5	681.6	693.3	705.2	718.8	732.9	746.2
10°	605.2	614.5	624.7	637.4	649.1	661.5	675.5	689.4	706.5	722.3	740.2
12.5°	577.6	587.9	599.4	613.6	627.9	643.7	657.9	673.5	691.9	712.3	731.6
15°	543.6	553.4	565.8	577.9	594.4	611.6	630.6	651.3	671.7	694.7	718.5
17.5°	507.0	517.8	531.5	545.4	562.7	583.0	601.6	624.3	647.3	674.0	702.1
20°	483.1	494.3	510.4	525.9	541.7	561.5	583.5	606.7	631.2	659.3	690.6
22.5°	464.3	472.2	488.1	503.9	522.4	542.7	564.2	588.4	615.1	644.2	677.0
25°	436.3	445.6	457.1	473.5	492.8	514.1	535.8	561.5	590.6	620.4	655.3
27.5°	411.6	419.1	430.5	443.4	462.5	484.7	507.8	534.6	564.4	594.7	631.5
30°	394.0	402.4	413.1	426.8	442.0	466.1	489.7	516.0	546.3	577.6	615.4
32.5°	378.6	387.2	396.6	409.4	425.8	447.3	471.6	497.4	528.2	560.5	597.3
35°	357.1	363.0	371.6	384.3	400.5	417.8	442.5	469.9	499.9	533.3	570.1
37.5°	332.5	340.1	348.7	359.7	373.8	392.6	415.6	443.2	471.1	503.1	536.7
40°	318.0	325.2	334.8	342.8	357.8	374.7	395.8	424.6	452.5	482.5	513.1
42.5°	303.5	310.3	318.5	328.5	341.9	358.4	378.0	404.8	434.6	462.9	488.7
45°	280.6	287.7	295.5	304.8	317.2	333.2	352.8	377.2	403.2	429.3	448.7
47.5°	258.7	265.4	272.7	282.3	293.7	309.2	326.7	348.3	373.6	395.7	409.6
50°	243.1	249.3	257.4	266.7	277.8	292.4	309.1	330.4	351.6	371.6	384.3
52.5°	227.8	234.7	242.7	250.8	261.5	276.0	291.5	309.9	330.0	346.3	356.9
55°	204.7	211.2	218.7	227.0	237.6	250.0	266.4	280.9	296.7	310.6	316.8
57.5°	182.5	188.2	195.2	203.8	213.4	224.9	237.8	251.8	263.0	272.9	279.9
60°	167.9	172.8	179.3	186.8	197.0	207.5	219.2	232.3	240.9	249.3	255.8
62.5°	153.0	157.7	164.0	170.6	179.6	189.4	200.7	211.2	219.6	225.3	232.8
65°	130.7	135.3	140.6	147.7	154.8	162.9	173.1	180.8	186.8	193.0	197.6
67.5°	110.0	113.8	118.8	124.4	130.4	138.1	146.0	152.5	156.5	160.2	165.8
70°	96.3	99.4	103.5	107.8	114.3	122.1	128.2	133.1	136.0	139.7	146.5
72.5°	82.4	86.0	89.8	94.2	99.4	105.9	111.4	116.3	118.1	121.1	125.4
75°	65.1	66.9	70.0	73.1	76.8	82.3	87.6	88.9	90.4	92.9	96.0
77.5°	49.2	50.9	52.1	54.1	57.1	61.6	64.3	66.2	66.6	67.5	70.5
80°	39.1	39.9	41.2	42.7	43.9	47.7	49.2	51.1	51.7	52.7	54.2
82.5°	28.6	29.5	30.3	31.6	33.6	35.1	36.6	38.5	38.6	39.3	39.5
85°	16.7	17.0	16.4	17.0	17.4	17.9	19.5	21.0	20.8	20.5	21.4
87.5°	9.2	9.0	8.4	8.9	8.1	8.1	7.7	7.7	7.8	8.0	8.2
90°	16.2	15.2	13.7	12.2	10.8	9.3	7.7	6.0	4.3	2.6	1.0
92.5°	16.2	15.2	13.9	12.6	11.3	9.9	9.9	11.1	12.2	13.5	14.6
95°	16.2	15.2	23.2	31.1	39.1	47.2	51.4	52.1	52.7	53.4	54.0
97.5°	40.7	46.6	62.5	78.3	94.1	110.0	117.3	116.2	115.0	113.9	112.8
100°	133.5	164.9	164.0	163.2	162.3	161.5	160.8	160.1	159.5	158.9	158.2
102.5°	204.4	210.3	209.9	209.4	208.8	208.3	207.7	206.8	206.1	205.3	204.5
105°	282.3	282.3	282.3	282.3	282.3	282.3	281.9	281.1	280.2	279.4	278.6
107.5°	357.4	357.4	357.0	356.5	356.1	355.7	355.6	355.6	355.6	355.6	355.6
110°	406.8	407.4	407.0	406.6	406.2	405.8	405.5	405.5	405.5	405.5	405.5



TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	455.2	455.9	455.7	455.4	455.2	454.9	454.5	454.0	453.6	453.1	452.6
115°	527.9	528.7	528.5	528.3	528.1	527.9	527.3	526.2	525.1	524.1	523.0
117.5°	598.3	599.4	598.6	597.8	597.0	596.2	595.8	595.9	595.9	596.0	596.0
120°	642.9	643.4	642.7	642.1	641.5	640.8	640.7	640.8	641.1	641.2	641.5
122.5°	686.2	686.6	686.3	686.0	685.7	685.4	684.9	684.0	683.2	682.5	681.7
125°	749.6	750.4	750.4	750.4	750.4	750.4	749.7	748.2	746.7	745.3	743.8
127.5°	806.8	807.3	807.4	807.6	807.6	807.8	807.3	806.2	805.2	804.2	803.2
130°	844.6	845.2	845.0	844.8	844.6	844.3	843.8	842.7	841.6	840.6	839.5
132.5°	879.2	879.3	879.8	880.2	880.7	881.2	880.8	879.5	878.3	877.1	875.9
135°	931.0	931.4	931.8	932.3	932.7	933.1	932.7	931.4	930.2	928.9	927.6
137.5°	978.5	978.4	978.8	979.2	979.6	979.9	979.6	978.4	977.4	976.3	975.2
140°	1007.6	1007.2	1007.5	1007.6	1007.9	1008.0	1008.0	1007.5	1007.1	1006.7	1006.2
142.5°	1036.9	1036.8	1036.5	1036.2	1035.9	1035.6	1035.3	1035.1	1034.9	1034.5	1034.3
145°	1077.6	1077.3	1077.3	1077.3	1077.3	1077.3	1077.1	1076.7	1076.3	1075.9	1075.5
147.5°	1112.5	1112.2	1112.0	1111.7	1111.4	1111.2	1111.1	1111.2	1111.3	1111.3	1111.4
150°	1134.6	1134.2	1133.8	1133.3	1132.9	1132.5	1132.5	1132.9	1133.3	1133.8	1134.2
152.5°	1154.3	1153.9	1153.5	1153.1	1152.7	1152.2	1152.4	1153.4	1154.3	1155.3	1156.2
155°	1181.3	1180.6	1180.2	1179.7	1179.3	1178.9	1179.3	1180.6	1181.9	1183.2	1184.4
157.5°	1203.6	1203.0	1203.0	1202.9	1202.9	1202.8	1203.1	1204.0	1204.7	1205.4	1206.2
160°	1217.5	1216.6	1216.4	1216.2	1216.0	1215.8	1216.3	1217.6	1218.9	1220.1	1221.4
162.5°	1230.0	1228.7	1228.6	1228.3	1228.1	1227.9	1228.4	1229.7	1230.9	1232.2	1233.5
165°	1246.3	1245.0	1244.8	1244.6	1244.4	1244.2	1244.7	1246.0	1247.2	1248.5	1249.8
167.5°	1258.5	1257.0	1256.8	1256.5	1256.4	1256.1	1256.7	1258.0	1259.3	1260.6	1261.9
170°	1264.8	1263.1	1262.8	1262.7	1262.4	1262.2	1262.8	1264.3	1265.8	1267.3	1268.8
172.5°	1269.9	1268.4	1268.0	1267.6	1267.2	1266.8	1267.4	1268.9	1270.3	1271.8	1273.3
175°	1275.1	1273.5	1273.3	1273.1	1272.8	1272.6	1273.2	1274.4	1275.7	1276.9	1278.2
177.5°	1277.9	1276.7	1276.5	1276.4	1276.2	1276.0	1276.4	1277.5	1278.5	1279.4	1280.5
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	758.1	760.4	763.6	767.4	770.3	773.6	775.3	775.3	776.7	780.0	784.2
5°	760.3	768.4	776.2	786.0	793.8	802.7	809.6	816.1	822.0	829.4	837.1
7.5°	759.7	773.1	787.0	802.7	819.9	833.6	847.6	858.7	869.5	883.8	895.0
10°	757.2	774.6	793.4	813.3	834.9	853.9	870.9	886.4	901.2	916.7	930.7
12.5°	752.8	774.9	797.9	821.7	849.1	870.7	892.7	909.2	926.5	943.5	960.7
15°	746.1	772.1	800.0	833.2	866.6	890.7	912.4	933.8	949.9	969.1	985.5
17.5°	732.3	765.8	800.9	837.1	869.2	897.3	920.0	940.4	957.5	978.6	1000.9
20°	724.1	760.3	796.9	835.6	866.3	895.0	917.0	938.1	959.4	987.1	1014.3
22.5°	712.7	751.4	790.2	827.0	859.3	887.1	909.9	935.6	963.7	995.0	1027.9
25°	694.7	734.7	773.1	808.0	839.6	868.1	899.1	933.8	967.8	1009.0	1056.4
27.5°	671.8	710.4	744.6	781.5	813.0	849.2	887.9	925.4	974.6	1031.3	1090.5
30°	654.7	691.3	723.8	758.8	794.4	834.4	877.8	922.0	980.6	1047.1	1117.4
32.5°	634.9	668.0	700.3	734.0	775.1	819.0	865.1	919.2	989.2	1064.9	1137.8
35°	600.5	630.2	661.5	699.0	742.7	790.4	849.2	915.2	999.7	1081.2	1146.6
37.5°	564.5	587.9	619.4	658.8	706.5	761.7	828.4	908.6	995.4	1068.5	1096.3
40°	536.7	558.7	591.8	633.3	680.4	740.9	815.8	898.1	985.5	1036.2	1034.1
42.5°	509.2	531.5	563.4	605.1	654.2	721.8	798.9	884.5	958.2	977.5	937.3
45°	467.0	487.8	519.1	561.2	613.8	684.8	765.9	848.0	895.0	863.8	783.9
47.5°	424.0	444.2	473.2	514.5	571.9	646.2	722.9	790.3	796.9	729.7	633.8
50°	395.8	414.7	442.3	486.2	542.0	614.5	688.5	741.4	725.0	642.9	544.1
52.5°	368.3	386.5	412.3	453.8	510.8	581.8	647.8	689.4	651.4	564.2	475.3
55°	327.7	345.0	371.0	409.1	460.8	525.9	583.8	599.0	543.2	455.3	383.4
57.5°	289.1	301.7	327.5	361.2	411.1	468.4	509.9	507.2	445.6	366.5	315.0
60°	263.6	275.0	299.5	330.4	377.8	429.3	458.4	446.0	383.8	318.4	268.8
62.5°	239.8	250.5	271.0	299.5	340.2	384.9	406.1	389.0	330.2	272.8	233.4
65°	203.8	211.6	228.0	254.3	286.2	317.2	336.1	311.0	258.9	215.6	185.8
67.5°	170.2	176.8	191.4	210.3	232.4	253.7	261.4	237.8	197.4	168.2	147.2
70°	148.4	154.6	164.4	182.1	196.7	211.8	215.6	194.5	160.8	138.4	125.4
72.5°	127.5	133.2	141.9	154.3	164.4	173.2	175.0	155.3	129.6	114.1	104.1
75°	97.3	102.2	107.8	112.4	119.0	120.5	119.8	104.7	90.7	80.6	74.9
77.5°	71.5	73.5	77.0	78.8	79.1	79.0	75.8	66.2	59.0	54.8	52.5
80°	55.1	56.7	57.6	58.2	58.5	55.4	52.0	46.1	43.7	41.2	38.4
82.5°	40.0	41.1	42.0	42.2	40.4	37.8	34.7	31.8	30.0	28.8	27.7
85°	21.7	22.0	21.7	20.1	17.9	17.0	16.4	15.8	15.5	15.2	15.2
87.5°	8.2	7.8	6.9	7.5	7.8	7.8	8.2	8.2	8.2	8.5	8.6
90°	2.6	4.3	6.0	7.7	9.3	10.8	12.2	13.7	15.2	16.2	17.3
92.5°	13.5	12.2	11.1	9.9	9.9	11.3	12.6	13.9	15.2	16.2	17.3
95°	53.4	52.7	52.1	51.4	47.2	39.1	31.1	23.2	15.2	16.2	17.3
97.5°	113.9	115.0	116.2	117.3	110.0	94.1	78.3	62.5	46.6	40.7	34.7
100°	158.9	159.5	160.1	160.8	161.5	162.3	163.2	164.0	164.9	133.5	102.2
102.5°	205.3	206.1	206.8	207.7	208.3	208.8	209.4	209.9	210.3	204.4	198.4
105°	279.4	280.2	281.1	281.9	282.3	282.3	282.3	282.3	282.3	282.3	282.3
107.5°	355.6	355.6	355.6	355.6	355.7	356.1	356.5	357.0	357.4	357.4	357.5
110°	405.5	405.5	405.5	405.5	405.8	406.2	406.6	407.0	407.4	406.8	406.2





TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	453.1	453.6	454.0	454.5	454.9	455.2	455.4	455.7	455.9	455.2	454.4
115°	524.1	525.1	526.2	527.3	527.9	528.1	528.3	528.5	528.7	527.9	527.0
117.5°	596.0	595.9	595.9	595.8	596.2	597.0	597.8	598.6	599.4	598.3	597.2
120°	641.2	641.1	640.8	640.7	640.8	641.5	642.1	642.7	643.4	642.9	642.5
122.5°	682.5	683.2	684.0	684.9	685.4	685.7	686.0	686.3	686.6	686.2	685.7
125°	745.3	746.7	748.2	749.7	750.4	750.4	750.4	750.4	750.4	749.6	748.8
127.5°	804.2	805.2	806.2	807.3	807.8	807.6	807.6	807.4	807.3	806.8	806.3
130°	840.6	841.6	842.7	843.8	844.3	844.6	844.8	845.0	845.2	844.6	843.9
132.5°	877.1	878.3	879.5	880.8	881.2	880.7	880.2	879.8	879.3	879.2	879.1
135°	928.9	930.2	931.4	932.7	933.1	932.7	932.3	931.8	931.4	931.0	930.6
137.5°	976.3	977.4	978.4	979.6	979.9	979.6	979.2	978.8	978.4	978.5	978.6
140°	1006.7	1007.1	1007.5	1008.0	1008.0	1007.9	1007.6	1007.5	1007.2	1007.6	1008.0
142.5°	1034.5	1034.9	1035.1	1035.3	1035.6	1035.9	1036.2	1036.5	1036.8	1036.9	1037.0
145°	1075.9	1076.3	1076.7	1077.1	1077.3	1077.3	1077.3	1077.3	1077.3	1077.6	1077.7
147.5°	1111.3	1111.3	1111.2	1111.1	1111.2	1111.4	1111.7	1112.0	1112.2	1112.5	1112.7
150°	1133.8	1133.3	1132.9	1132.5	1132.5	1132.9	1133.3	1133.8	1134.2	1134.6	1135.1
152.5°	1155.3	1154.3	1153.4	1152.4	1152.2	1152.7	1153.1	1153.5	1153.9	1154.3	1154.7
155°	1183.2	1181.9	1180.6	1179.3	1178.9	1179.3	1179.7	1180.2	1180.6	1181.3	1181.9
157.5°	1205.4	1204.7	1204.0	1203.1	1202.8	1202.9	1202.9	1203.0	1203.0	1203.6	1204.4
160°	1220.1	1218.9	1217.6	1216.3	1215.8	1216.0	1216.2	1216.4	1216.6	1217.5	1218.3
162.5°	1232.2	1230.9	1229.7	1228.4	1227.9	1228.1	1228.3	1228.6	1228.7	1230.0	1231.1
165°	1248.5	1247.2	1246.0	1244.7	1244.2	1244.4	1244.6	1244.8	1245.0	1246.3	1247.6
167.5°	1260.6	1259.3	1258.0	1256.7	1256.1	1256.4	1256.5	1256.8	1257.0	1258.5	1260.0
170°	1267.3	1265.8	1264.3	1262.8	1262.2	1262.4	1262.7	1262.8	1263.1	1264.8	1266.4
172.5°	1271.8	1270.3	1268.9	1267.4	1266.8	1267.2	1267.6	1268.0	1268.4	1269.9	1271.4
175°	1276.9	1275.7	1274.4	1273.2	1272.6	1272.8	1273.1	1273.3	1273.5	1275.1	1276.8
177.5°	1279.4	1278.5	1277.5	1276.4	1276.0	1276.2	1276.4	1276.5	1276.7	1277.9	1279.0
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	787.4	787.4	791.7	791.3	794.1	793.1	793.6
5°	846.4	851.7	856.3	859.4	864.1	865.4	864.7
7.5°	907.7	919.3	925.0	932.9	934.3	938.3	937.9
10°	945.5	957.0	965.6	972.5	975.9	980.2	980.6
12.5°	975.3	985.0	992.7	999.0	1003.1	1004.5	1005.3
15°	998.5	1009.3	1018.3	1027.3	1032.6	1036.6	1038.8
17.5°	1021.9	1038.6	1054.5	1066.7	1074.0	1080.2	1080.1
20°	1040.0	1059.2	1079.0	1093.0	1107.2	1113.4	1114.4
22.5°	1059.3	1088.7	1114.2	1135.8	1154.5	1161.0	1163.4
25°	1099.4	1137.8	1177.2	1207.5	1229.2	1241.9	1243.8
27.5°	1147.9	1200.0	1241.3	1269.3	1287.4	1296.7	1298.8
30°	1182.2	1230.1	1267.3	1288.4	1296.7	1298.0	1293.3
32.5°	1197.5	1233.4	1248.2	1247.0	1230.6	1219.7	1215.5
35°	1178.8	1171.3	1135.1	1091.7	1058.6	1037.5	1031.9
37.5°	1072.7	1008.6	941.9	876.4	841.6	823.9	793.4
40°	968.2	876.8	807.4	752.3	713.0	681.3	673.9
42.5°	850.2	755.9	686.5	639.3	607.9	586.2	576.8
45°	683.2	602.1	544.8	508.5	484.4	468.6	461.5
47.5°	546.4	483.6	441.9	415.1	396.6	382.9	379.1
50°	471.4	421.2	385.9	363.3	349.4	338.8	334.5
52.5°	409.4	368.9	341.8	323.2	310.0	303.4	299.8
55°	337.9	302.9	283.4	268.5	261.1	255.8	253.3
57.5°	276.3	251.0	236.8	226.5	219.6	216.3	215.1
60°	241.9	222.1	209.0	201.0	196.3	192.0	190.8
62.5°	211.4	195.8	185.7	178.7	174.1	172.2	171.5
65°	170.3	160.1	152.7	148.4	144.6	144.0	143.7
67.5°	135.4	129.4	125.5	121.0	119.7	117.5	117.1
70°	115.9	111.8	107.1	105.6	104.0	101.9	102.2
72.5°	98.2	94.2	91.1	89.0	88.5	87.6	88.3
75°	71.8	70.6	69.4	67.8	67.2	67.2	66.9
77.5°	51.3	50.2	48.8	47.9	47.8	46.5	47.0
80°	37.2	35.6	35.0	35.3	34.4	34.1	34.1
82.5°	27.5	26.9	26.3	26.4	26.2	25.9	26.2
85°	15.2	14.8	14.8	14.6	14.6	14.3	14.3
87.5°	9.1	9.5	9.2	9.1	9.2	9.6	10.0
90°	18.3	19.4	20.2	20.9	21.4	22.1	22.7
92.5°	18.3	19.4	20.1	20.3	20.6	21.0	21.2
95°	18.3	19.4	19.9	19.9	19.9	19.9	19.9
97.5°	28.8	22.8	19.9	19.9	19.9	19.9	19.9
100°	70.8	39.4	23.2	22.4	21.6	20.7	19.9
102.5°	192.6	186.6	176.5	162.2	147.8	133.5	119.2
105°	282.3	282.3	282.3	282.0	281.8	281.6	281.4
107.5°	357.5	357.6	357.3	356.6	356.0	355.4	354.7
110°	405.5	404.9	404.7	404.9	405.1	405.4	405.5



TEST NUMBER: P333544-930

CATALOG NUMBER: S125RDIP-S610D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	453.6	452.7	452.2	451.9	451.6	451.3	451.0
115°	526.2	525.4	524.3	523.0	521.8	520.5	519.3
117.5°	596.1	595.0	594.2	593.6	593.1	592.6	592.0
120°	642.1	641.7	641.0	639.9	638.9	637.8	636.7
122.5°	685.3	684.9	684.0	682.8	681.6	680.4	679.2
125°	747.9	747.1	746.3	745.7	745.1	744.4	743.8
127.5°	805.9	805.4	804.5	802.9	801.3	799.7	798.2
130°	843.3	842.7	841.8	840.7	839.8	838.7	837.6
132.5°	878.9	878.8	878.2	877.2	876.1	875.1	874.0
135°	930.2	929.8	928.9	927.6	926.3	925.1	923.8
137.5°	978.7	978.8	978.3	977.1	976.1	974.9	973.9
140°	1008.4	1008.9	1008.4	1007.2	1006.0	1004.7	1003.5
142.5°	1037.1	1037.1	1036.6	1035.3	1034.0	1032.7	1031.5
145°	1078.0	1078.2	1077.7	1076.4	1075.1	1073.8	1072.6
147.5°	1113.0	1113.2	1112.6	1111.1	1109.5	1108.1	1106.5
150°	1135.5	1135.9	1135.2	1133.6	1131.9	1130.2	1128.5
152.5°	1155.2	1155.6	1155.0	1153.5	1152.0	1150.5	1149.0
155°	1182.5	1183.2	1182.6	1181.0	1179.2	1177.5	1175.9
157.5°	1205.0	1205.7	1205.2	1203.5	1201.8	1200.1	1198.4
160°	1219.1	1220.0	1219.6	1217.9	1216.2	1214.6	1212.8
162.5°	1232.3	1233.5	1233.1	1231.3	1229.4	1227.6	1225.7
165°	1248.9	1250.1	1249.9	1248.2	1246.5	1244.8	1243.2
167.5°	1261.5	1263.1	1262.9	1260.9	1259.1	1257.2	1255.3
170°	1268.1	1269.8	1269.7	1267.8	1265.9	1264.0	1262.1
172.5°	1272.9	1274.4	1274.2	1272.4	1270.5	1268.5	1266.6
175°	1278.6	1280.2	1280.1	1278.2	1276.4	1274.4	1272.5
177.5°	1280.3	1281.4	1281.3	1280.0	1278.6	1277.2	1275.9
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2

(END OF REPORT)