

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333561-840

Luminaire Tested: **S125RDIP-S850D590U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333561-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D590U840-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5424.8 lumens
Efficiency: N/A
Efficacy: 134.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333561-840
CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333561-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	59	57	56	52
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	52	50	48	44
3	84	74	67	61	78	70	63	58	61	56	52	53	50	46	46	43	41	37
4	77	66	58	52	72	62	55	49	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27	25
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8969	8969	8969
5°	8989	8887	8941
10°	8921	8804	8804
15°	8815	8625	8555
20°	8678	8376	8276
25°	8521	8131	7952
30°	8322	7845	7594
35°	8121	7550	7194
40°	7932	7242	6800
45°	7701	6898	6370
50°	7471	6523	5923
55°	7203	6164	5444
60°	6935	5730	4930
65°	6619	5225	4343
70°	6258	4594	3743
75°	5759	3873	3114
80°	5069	3042	2615
85°	4276	2482	2334



TEST NUMBER: P333561-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	2.4
10°-20°	364.9	6.7
20°-30°	529.2	9.8
30°-40°	603.1	11.1
40°-50°	587.8	10.8
50°-60°	494.8	9.1
60°-70°	346.9	6.4
70°-80°	178.3	3.3
80°-90°	46.6	0.9
90°-100°	207.1	3.8
100°-110°	445.2	8.2
110°-120°	417.8	7.7
120°-130°	338.6	6.2
130°-140°	271.7	5.0
140°-150°	205.1	3.8
150°-160°	144.3	2.7
160°-170°	85.1	1.6
170°-180°	27.7	0.5
0°-30°	1024.6	18.9
0°-40°	1627.7	30.0
0°-60°	2710.4	50.0
0°-90°	3282.1	60.5
90°-120°	1070.2	19.7
90°-150°	1885.6	34.8
90°-180°	2143.0	39.5
0°-180°	5424.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1386	1382	1371	1381	1379	131
15°	1318	1311	1290	1289	1280	371
25°	1196	1179	1141	1128	1116	550
35°	1030	1004	958	928	912	645
45°	843	811	755	715	697	650
55°	640	605	547	502	484	572
65°	433	396	342	301	284	429
75°	231	199	155	133	125	244
85°	58	40	34	32	32	65
90°	1	5	9	12	13	4
95°	19	56	510	232	135	20
105°	65	91	418	822	763	69
115°	116	140	335	723	850	114
125°	161	189	321	575	670	143
135°	189	227	319	482	556	147
145°	220	252	320	399	439	138
155°	251	270	312	353	368	116
165°	274	282	300	318	323	77
175°	285	285	287	291	290	27
180°	286	286	286	286	286	



TEST NUMBER: P333561-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1391.1	1390.6	1390.0	1389.5	1388.9	1387.7	1385.8	1383.9	1382.1	1380.2	1382.1
5°	1386.5	1385.6	1384.6	1383.7	1382.8	1381.1	1378.5	1375.9	1373.3	1370.8	1373.1
7.5°	1372.9	1372.0	1371.1	1370.2	1369.4	1367.4	1364.3	1361.2	1358.2	1355.0	1356.7
10°	1360.3	1359.6	1358.9	1358.2	1357.5	1355.5	1352.3	1349.0	1345.7	1342.5	1343.1
12.5°	1346.0	1345.1	1344.2	1343.4	1342.5	1339.9	1335.4	1331.1	1326.8	1322.3	1322.8
15°	1318.4	1317.0	1315.6	1314.1	1312.7	1309.6	1304.7	1299.8	1294.9	1290.0	1289.8
17.5°	1287.1	1285.0	1282.8	1280.7	1278.5	1274.3	1268.2	1262.0	1255.9	1249.7	1248.6
20°	1262.7	1260.4	1258.1	1255.8	1253.4	1248.5	1241.1	1233.7	1226.2	1218.7	1217.6
22.5°	1235.9	1233.6	1231.2	1228.9	1226.6	1221.5	1213.7	1205.9	1198.0	1190.2	1187.9
25°	1195.7	1192.1	1188.6	1185.2	1181.6	1175.6	1167.0	1158.3	1149.7	1141.1	1138.1
27.5°	1149.5	1145.3	1141.0	1136.8	1132.6	1125.8	1116.6	1107.3	1098.1	1088.8	1084.6
30°	1115.9	1111.5	1107.1	1102.7	1098.2	1091.1	1081.4	1071.6	1061.8	1052.0	1046.6
32.5°	1083.2	1078.0	1072.9	1067.7	1062.5	1054.9	1045.0	1035.0	1025.0	1015.0	1009.2
35°	1030.0	1024.3	1018.8	1013.1	1007.5	999.5	989.1	978.6	968.1	957.6	950.8
37.5°	977.7	970.9	964.1	957.3	950.5	941.7	930.9	920.0	909.2	898.4	890.3
40°	940.8	933.8	926.8	919.8	912.8	903.7	892.5	881.3	870.2	859.0	850.1
42.5°	902.2	895.0	887.9	880.6	873.4	864.1	852.5	841.0	829.4	817.9	809.4
45°	843.2	836.5	829.7	822.9	816.2	806.4	793.6	780.8	768.0	755.2	745.8
47.5°	782.2	775.1	767.9	760.8	753.7	743.7	730.7	717.8	704.9	692.0	682.4
50°	743.6	735.9	728.2	720.5	712.9	702.4	689.0	675.8	662.5	649.2	639.4
52.5°	701.7	693.8	685.9	678.0	670.1	659.9	647.4	634.9	622.3	609.8	599.3
55°	639.7	632.3	624.9	617.4	610.0	599.7	586.6	573.6	560.6	547.4	536.9
57.5°	577.2	569.3	561.3	553.3	545.4	535.1	522.5	509.9	497.4	484.7	474.5
60°	536.9	528.9	520.7	512.5	504.3	494.0	481.4	468.8	456.3	443.6	433.4
62.5°	494.2	486.5	478.7	470.8	463.0	452.8	440.0	427.3	414.4	401.7	392.2
65°	433.1	425.3	417.3	409.4	401.4	391.3	379.0	366.6	354.3	341.9	332.5
67.5°	372.5	364.6	356.7	348.8	340.8	330.9	319.1	307.3	295.5	283.6	275.1
70°	331.4	323.5	315.6	307.6	299.7	289.9	278.3	266.6	255.0	243.3	236.1
72.5°	291.1	283.4	275.7	267.9	260.2	250.9	239.9	229.0	218.1	207.2	200.6
75°	230.8	223.8	216.7	209.7	202.8	194.4	184.6	174.8	165.0	155.2	150.1
77.5°	170.8	165.1	159.6	154.0	148.3	141.7	133.8	126.0	118.2	110.4	106.7
80°	136.3	130.8	125.1	119.6	114.0	108.0	101.4	94.8	88.4	81.8	79.7
82.5°	102.8	97.8	92.7	87.7	82.6	77.9	73.4	69.0	64.4	60.0	59.0
85°	57.7	53.5	49.3	45.1	40.9	38.2	37.1	35.9	34.7	33.5	33.3
87.5°	19.4	18.2	17.2	16.1	15.0	14.4	14.4	14.4	14.3	14.4	14.5
90°	0.6	1.1	2.3	3.4	4.6	5.8	6.4	7.5	8.1	9.2	9.8
92.5°	7.1	8.5	13.3	20.5	30.4	47.3	78.7	131.5	188.7	185.7	150.4
95°	19.0	19.6	24.2	30.5	43.2	69.2	130.8	257.5	416.5	510.4	499.5
97.5°	31.6	32.2	35.4	41.8	53.2	71.9	112.7	205.5	371.9	545.0	632.0
100°	40.3	41.5	43.8	50.1	61.1	78.4	111.8	186.6	331.8	520.2	664.2
102.5°	50.0	50.7	52.5	59.4	69.4	86.1	115.9	178.8	301.3	476.4	644.8
105°	65.1	65.1	68.0	73.7	82.9	99.1	124.4	175.7	271.9	417.7	583.0
107.5°	79.9	81.0	83.7	88.5	98.1	112.6	137.1	181.0	259.4	377.2	519.9
110°	90.5	91.6	93.9	99.1	107.8	122.7	146.3	186.0	255.8	358.3	483.9



TEST NUMBER: P333561-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	101.1	102.2	104.0	109.3	117.9	132.4	155.1	192.5	255.8	347.3	457.2
115°	116.3	117.5	119.3	124.4	133.1	147.4	168.7	202.2	257.5	335.3	428.0
117.5°	130.2	131.9	133.8	139.0	148.8	162.7	182.9	213.3	261.3	329.4	410.6
120°	139.4	141.2	143.4	148.7	158.4	172.8	193.0	220.7	265.0	326.6	400.9
122.5°	149.1	150.4	152.2	157.3	168.1	182.5	202.7	228.9	268.2	324.4	392.6
125°	161.3	162.5	165.3	170.5	181.5	196.4	215.4	240.2	273.7	321.4	381.3
127.5°	170.9	172.6	176.3	182.9	194.5	209.4	227.7	250.5	279.7	320.0	371.0
130°	176.8	178.5	183.2	190.7	202.8	217.7	235.6	257.5	283.5	319.1	364.1
132.5°	181.5	183.7	189.1	197.6	210.2	225.1	243.0	263.5	287.6	319.1	358.5
135°	188.9	191.3	198.1	207.4	219.4	235.0	252.9	271.9	293.2	319.1	351.9
137.5°	198.4	200.2	206.6	215.8	227.6	243.7	259.9	278.1	298.4	319.8	346.1
140°	203.9	205.6	212.6	221.8	232.8	248.3	265.0	282.3	300.7	320.3	343.4
142.5°	210.4	211.7	218.1	227.3	237.8	252.5	268.2	284.6	302.1	320.7	341.0
145°	220.0	221.2	226.9	235.0	245.4	258.6	273.7	288.0	303.6	320.3	337.6
147.5°	230.1	230.9	235.8	243.3	252.3	264.0	277.1	290.1	304.2	318.8	334.0
150°	236.2	237.3	241.4	248.8	256.9	266.7	279.4	291.4	304.2	317.4	331.2
152.5°	242.7	243.3	246.9	253.5	261.1	269.9	281.7	292.4	303.7	315.6	328.0
155°	251.2	251.2	254.6	260.3	266.1	274.2	284.0	293.2	302.5	312.3	322.6
157.5°	258.7	258.6	261.5	266.4	271.5	277.5	286.0	293.8	300.9	308.7	317.5
160°	263.9	263.3	265.6	269.6	274.2	279.4	286.9	293.8	299.5	306.5	313.4
162.5°	268.0	267.4	269.7	273.3	277.0	281.2	287.8	293.4	298.2	303.7	309.7
165°	274.2	273.1	274.8	277.6	279.9	283.5	288.0	292.7	296.1	299.5	304.2
167.5°	278.3	277.8	278.8	280.4	282.1	284.2	288.0	291.2	292.9	295.5	298.7
170°	281.1	280.5	281.1	282.3	283.5	285.2	288.0	290.3	291.4	293.2	295.5
172.5°	283.0	282.0	282.5	283.7	284.4	285.2	287.6	289.4	289.6	290.4	292.3
175°	285.2	284.0	284.6	285.2	285.2	285.2	286.9	288.0	287.4	287.4	288.0
177.5°	286.2	285.3	285.3	285.7	285.3	285.3	286.2	286.6	285.7	285.7	286.2
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333561-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1383.9	1385.8	1387.7	1388.6	1388.4	1388.2	1388.0	1387.8
5°	1375.4	1377.8	1380.1	1381.1	1380.6	1380.1	1379.7	1379.2
7.5°	1358.4	1360.0	1361.6	1362.1	1361.6	1361.1	1360.6	1360.1
10°	1343.8	1344.5	1345.2	1345.2	1344.5	1343.8	1343.1	1342.5
12.5°	1323.3	1323.8	1324.3	1324.1	1323.0	1321.9	1320.9	1319.8
15°	1289.6	1289.3	1289.1	1288.0	1285.9	1283.7	1281.6	1279.5
17.5°	1247.4	1246.3	1245.1	1243.6	1241.9	1240.2	1238.5	1236.8
20°	1216.4	1215.2	1214.1	1212.4	1210.3	1208.2	1206.1	1204.1
22.5°	1185.6	1183.4	1181.0	1179.0	1177.3	1175.6	1173.9	1172.2
25°	1135.1	1132.1	1129.0	1126.2	1123.6	1121.1	1118.5	1115.9
27.5°	1080.4	1076.1	1071.9	1068.5	1066.1	1063.6	1061.2	1058.6
30°	1041.3	1035.9	1030.5	1026.8	1024.7	1022.6	1020.5	1018.3
32.5°	1003.2	997.2	991.4	987.0	984.4	981.8	979.1	976.4
35°	944.0	937.3	930.5	925.5	922.2	919.0	915.7	912.4
37.5°	882.2	874.0	866.0	860.3	857.2	853.9	850.8	847.7
40°	841.2	832.4	823.5	817.7	815.0	812.1	809.3	806.6
42.5°	800.9	792.4	784.0	777.6	773.6	769.4	765.3	761.2
45°	736.5	727.2	717.8	711.4	707.9	704.5	700.9	697.4
47.5°	672.8	663.2	653.6	646.8	643.0	639.1	635.2	631.4
50°	629.7	619.9	610.1	603.4	600.0	596.4	592.9	589.5
52.5°	588.8	578.1	567.6	560.6	557.1	553.6	550.2	546.6
55°	526.5	516.0	505.5	498.4	494.7	491.0	487.3	483.5
57.5°	464.2	454.0	443.7	437.0	433.6	430.3	427.1	423.7
60°	423.1	412.8	402.6	395.8	392.2	388.8	385.3	381.7
62.5°	382.6	373.1	363.7	357.2	353.7	350.1	346.7	343.2
65°	323.3	314.0	304.6	298.2	294.7	291.2	287.7	284.2
67.5°	266.5	258.0	249.4	243.8	241.1	238.2	235.4	232.7
70°	228.8	221.7	214.4	209.4	206.6	203.8	201.1	198.2
72.5°	193.9	187.2	180.6	176.3	174.4	172.6	170.8	168.8
75°	145.0	139.9	134.7	131.4	129.7	128.1	126.4	124.8
77.5°	103.1	99.6	95.9	93.6	92.4	91.2	90.0	88.8
80°	77.7	75.5	73.4	72.1	71.7	71.2	70.7	70.3
82.5°	58.1	57.1	56.0	55.4	55.1	54.9	54.6	54.3
85°	33.1	32.8	32.6	32.4	32.1	31.9	31.7	31.5
87.5°	14.6	14.7	14.8	15.0	14.8	14.6	14.5	14.4
90°	10.4	10.9	11.5	12.6	12.6	12.6	13.2	13.2
92.5°	102.1	74.1	55.7	47.3	39.9	38.5	37.7	36.8
95°	414.1	326.6	255.8	207.4	166.5	149.2	144.6	135.4
97.5°	616.8	555.4	486.5	419.1	383.5	351.2	334.6	327.2
100°	708.5	680.3	621.0	561.1	521.3	479.9	458.6	449.3
102.5°	739.4	756.8	728.3	687.8	645.3	615.8	592.7	585.7
105°	721.2	800.1	825.5	819.1	800.7	781.7	770.2	763.3
107.5°	656.2	761.5	826.7	856.7	866.1	866.0	862.1	857.5
110°	608.3	717.8	799.0	848.0	873.8	884.8	888.9	888.9



TEST NUMBER: P333561-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	570.6	674.5	756.6	814.4	852.2	871.0	881.0	885.1
115°	523.0	612.4	691.3	754.1	799.0	826.7	842.7	850.3
117.5°	492.4	569.4	637.3	695.0	739.9	768.5	784.5	789.1
120°	475.8	544.9	608.3	659.0	701.7	729.3	744.9	749.4
122.5°	463.4	527.5	583.9	631.4	669.3	694.7	710.2	714.4
125°	445.2	504.0	554.2	595.6	627.9	651.6	664.2	669.9
127.5°	426.9	481.7	528.5	567.3	596.5	617.4	629.3	632.0
130°	415.4	466.1	511.0	548.4	577.2	596.2	607.7	611.2
132.5°	403.8	451.3	492.1	528.2	556.9	575.9	586.5	590.5
135°	388.8	428.6	465.4	498.3	523.6	542.6	553.0	556.4
137.5°	376.2	408.3	439.0	466.9	489.5	506.9	516.3	520.2
140°	369.2	396.4	422.8	447.1	468.4	483.3	491.9	494.8
142.5°	363.2	386.2	409.0	430.0	448.1	460.7	468.9	471.3
145°	355.5	373.2	391.1	406.7	420.5	430.3	436.7	439.0
147.5°	348.1	362.5	376.3	388.0	399.0	406.8	410.5	411.5
150°	343.9	356.6	367.5	377.9	386.6	393.4	395.8	396.4
152.5°	339.3	350.6	360.6	368.7	376.0	381.4	383.7	384.4
155°	332.3	341.6	349.6	356.0	361.7	365.8	367.5	368.1
157.5°	325.5	333.1	339.3	344.3	348.7	352.0	353.7	353.6
160°	320.8	326.6	332.3	336.4	340.4	343.4	344.5	343.9
162.5°	315.8	321.1	325.9	329.5	332.6	335.1	335.3	335.2
165°	308.7	312.8	316.3	319.1	321.4	322.6	322.6	322.6
167.5°	302.1	304.8	307.4	309.4	310.6	311.6	311.1	311.0
170°	298.4	300.1	301.8	303.0	304.2	304.8	304.8	304.2
172.5°	294.3	296.0	297.2	297.9	298.2	299.2	298.3	297.7
175°	289.7	289.7	290.9	290.9	290.9	291.4	290.3	289.7
177.5°	286.6	287.1	287.1	287.1	286.6	287.1	285.7	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7

(END OF REPORT)