

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333566-840

Luminaire Tested: **S125RDIP-S850D810U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333566-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D810U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6114.3 lumens
Efficiency: N/A
Efficacy: 133.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333566-840

CATALOG NUMBER: S125RDIP-S850D810U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333566-840

CATALOG NUMBER: S125RDIP-S850D810U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	60	53	48	52	47	43	45	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	29	33	29	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	22	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8969	8969	8969
5°	8989	8887	8941
10°	8921	8804	8804
15°	8815	8625	8555
20°	8678	8376	8276
25°	8521	8131	7952
30°	8322	7845	7594
35°	8121	7550	7194
40°	7932	7242	6800
45°	7701	6898	6370
50°	7471	6523	5923
55°	7203	6164	5444
60°	6935	5730	4930
65°	6619	5225	4343
70°	6258	4594	3743
75°	5759	3873	3114
80°	5069	3042	2615
85°	4276	2482	2334



TEST NUMBER: P333566-840

CATALOG NUMBER: S125RDIP-S850D810U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	2.1
10°-20°	364.9	6.0
20°-30°	529.2	8.7
30°-40°	603.1	9.9
40°-50°	587.8	9.6
50°-60°	494.8	8.1
60°-70°	346.9	5.7
70°-80°	178.3	2.9
80°-90°	47.2	0.8
90°-100°	68.0	1.1
100°-110°	200.7	3.3
110°-120°	339.9	5.6
120°-130°	447.4	7.3
130°-140°	501.3	8.2
140°-150°	491.3	8.0
150°-160°	412.7	6.7
160°-170°	274.3	4.5
170°-180°	96.0	1.6
0°-30°	1024.6	16.8
0°-40°	1627.7	26.6
0°-60°	2710.4	44.3
0°-90°	3282.8	53.7
90°-120°	608.6	10.0
90°-150°	2048.6	33.5
90°-180°	2832.0	46.3
0°-180°	6114.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1386	1382	1371	1381	1379	131
15°	1318	1311	1290	1289	1280	371
25°	1196	1179	1141	1128	1116	550
35°	1030	1004	958	928	912	645
45°	843	811	755	715	697	650
55°	640	605	547	502	484	572
65°	433	396	342	301	284	429
75°	231	199	155	133	125	244
85°	58	40	34	32	32	65
90°	1	7	13	17	19	6
95°	51	53	61	66	68	55
105°	180	184	189	193	196	192
115°	340	343	345	344	344	336
125°	497	501	502	501	500	445
135°	646	650	652	651	648	498
145°	782	786	788	788	786	489
155°	895	895	896	899	895	412
165°	974	972	973	976	971	275
175°	1012	1009	1009	1013	1008	96
180°	1015	1015	1015	1015	1015	



TEST NUMBER: P333566-840

CATALOG NUMBER: S125RDIP-S850D810U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1391.1	1390.6	1390.0	1389.5	1388.9	1387.7	1385.8	1383.9	1382.1	1380.2	1382.1
5°	1386.5	1385.6	1384.6	1383.7	1382.8	1381.1	1378.5	1375.9	1373.3	1370.8	1373.1
7.5°	1372.9	1372.0	1371.1	1370.2	1369.4	1367.4	1364.3	1361.2	1358.2	1355.0	1356.7
10°	1360.3	1359.6	1358.9	1358.2	1357.5	1355.5	1352.3	1349.0	1345.7	1342.5	1343.1
12.5°	1346.0	1345.1	1344.2	1343.4	1342.5	1339.9	1335.4	1331.1	1326.8	1322.3	1322.8
15°	1318.4	1317.0	1315.6	1314.1	1312.7	1309.6	1304.7	1299.8	1294.9	1290.0	1289.8
17.5°	1287.1	1285.0	1282.8	1280.7	1278.5	1274.3	1268.2	1262.0	1255.9	1249.7	1248.6
20°	1262.7	1260.4	1258.1	1255.8	1253.4	1248.5	1241.1	1233.7	1226.2	1218.7	1217.6
22.5°	1235.9	1233.6	1231.2	1228.9	1226.6	1221.5	1213.7	1205.9	1198.0	1190.2	1187.9
25°	1195.7	1192.1	1188.6	1185.2	1181.6	1175.6	1167.0	1158.3	1149.7	1141.1	1138.1
27.5°	1149.5	1145.3	1141.0	1136.8	1132.6	1125.8	1116.6	1107.3	1098.1	1088.8	1084.6
30°	1115.9	1111.5	1107.1	1102.7	1098.2	1091.1	1081.4	1071.6	1061.8	1052.0	1046.6
32.5°	1083.2	1078.0	1072.9	1067.7	1062.5	1054.9	1045.0	1035.0	1025.0	1015.0	1009.2
35°	1030.0	1024.3	1018.8	1013.1	1007.5	999.5	989.1	978.6	968.1	957.6	950.8
37.5°	977.7	970.9	964.1	957.3	950.5	941.7	930.9	920.0	909.2	898.4	890.3
40°	940.8	933.8	926.8	919.8	912.8	903.7	892.5	881.3	870.2	859.0	850.1
42.5°	902.2	895.0	887.9	880.6	873.4	864.1	852.5	841.0	829.4	817.9	809.4
45°	843.2	836.5	829.7	822.9	816.2	806.4	793.6	780.8	768.0	755.2	745.8
47.5°	782.2	775.1	767.9	760.8	753.7	743.7	730.7	717.8	704.9	692.0	682.4
50°	743.6	735.9	728.2	720.5	712.9	702.4	689.0	675.8	662.5	649.2	639.4
52.5°	701.7	693.8	685.9	678.0	670.1	659.9	647.4	634.9	622.3	609.8	599.3
55°	639.7	632.3	624.9	617.4	610.0	599.7	586.6	573.6	560.6	547.4	536.9
57.5°	577.2	569.3	561.3	553.3	545.4	535.1	522.5	509.9	497.4	484.7	474.5
60°	536.9	528.9	520.7	512.5	504.3	494.0	481.4	468.8	456.3	443.6	433.4
62.5°	494.2	486.5	478.7	470.8	463.0	452.8	440.0	427.3	414.4	401.7	392.2
65°	433.1	425.3	417.3	409.4	401.4	391.3	379.0	366.6	354.3	341.9	332.5
67.5°	372.5	364.6	356.7	348.8	340.8	330.9	319.1	307.3	295.5	283.6	275.1
70°	331.4	323.5	315.6	307.6	299.7	289.9	278.3	266.6	255.0	243.3	236.1
72.5°	291.1	283.4	275.7	267.9	260.2	250.9	239.9	229.0	218.1	207.2	200.6
75°	230.8	223.8	216.7	209.7	202.8	194.4	184.6	174.8	165.0	155.2	150.1
77.5°	170.8	165.1	159.6	154.0	148.3	141.7	133.8	126.0	118.2	110.4	106.7
80°	136.3	130.8	125.1	119.6	114.0	108.0	101.4	94.8	88.4	81.8	79.7
82.5°	102.8	97.8	92.7	87.7	82.6	77.9	73.4	69.0	64.4	60.0	59.0
85°	57.7	53.5	49.3	45.1	40.9	38.2	37.1	35.9	34.7	33.5	33.3
87.5°	19.5	18.5	17.4	16.4	15.3	14.8	14.9	14.9	15.0	15.1	15.2
90°	0.8	2.2	3.6	5.0	6.4	7.7	9.0	10.2	11.4	12.6	13.5
92.5°	19.1	20.1	21.1	22.0	23.0	24.2	25.8	27.3	28.8	30.3	31.5
95°	51.3	51.7	52.0	52.4	52.7	53.8	55.5	57.3	59.1	60.8	62.0
97.5°	85.3	85.4	85.5	85.7	85.8	87.2	89.6	92.0	94.4	96.8	98.0
100°	110.6	110.6	110.6	110.6	110.6	111.7	114.0	116.2	118.6	120.8	122.4
102.5°	137.7	138.5	139.2	139.9	140.6	141.5	142.6	143.8	144.9	146.1	147.8
105°	180.1	181.0	181.8	182.7	183.6	184.5	185.6	186.6	187.6	188.7	189.8
107.5°	226.8	227.6	228.5	229.4	230.4	231.2	232.0	232.8	233.6	234.4	234.9
110°	259.0	259.9	260.7	261.7	262.6	263.3	263.8	264.3	264.8	265.3	265.9



TEST NUMBER: P333566-840

CATALOG NUMBER: S125RDIP-S850D810U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	291.9	292.4	292.8	293.3	293.7	294.3	294.9	295.6	296.3	296.9	297.2
115°	340.3	341.0	341.7	342.4	343.2	343.7	344.1	344.4	344.8	345.1	344.9
117.5°	389.0	389.3	389.6	389.9	390.2	390.6	390.9	391.2	391.5	391.8	391.9
120°	419.3	420.2	421.1	421.9	422.8	423.3	423.5	423.7	423.8	424.0	424.0
122.5°	452.1	452.5	452.8	453.1	453.4	453.8	454.2	454.7	455.1	455.7	455.4
125°	496.7	497.8	498.8	499.9	500.9	501.5	501.7	501.9	502.0	502.2	501.9
127.5°	544.1	544.7	545.2	545.8	546.4	546.8	547.0	547.2	547.5	547.8	547.5
130°	572.5	573.4	574.3	575.1	576.0	576.6	576.9	577.3	577.6	578.0	577.8
132.5°	601.0	602.4	603.8	605.2	606.7	607.3	607.3	607.2	607.1	607.1	606.9
135°	645.9	647.0	648.0	649.1	650.2	650.8	651.0	651.2	651.3	651.5	651.5
137.5°	688.3	689.3	690.3	691.4	692.4	693.1	693.5	693.8	694.2	694.6	694.8
140°	715.5	716.3	717.2	718.1	718.9	719.6	720.1	720.7	721.2	721.8	722.2
142.5°	742.7	743.4	744.1	744.8	745.6	746.3	746.9	747.6	748.2	748.9	749.1
145°	782.5	783.3	784.0	784.7	785.4	786.0	786.5	787.0	787.6	788.1	788.1
147.5°	819.5	819.9	820.3	820.7	821.0	821.4	821.9	822.3	822.7	823.1	823.5
150°	844.1	843.9	843.8	843.6	843.4	843.7	844.4	845.2	845.9	846.6	846.6
152.5°	864.3	864.6	864.8	865.2	865.4	865.7	865.9	866.2	866.5	866.8	867.2
155°	895.4	895.4	895.4	895.4	895.4	895.5	895.8	896.0	896.1	896.3	897.0
157.5°	923.3	922.9	922.5	922.1	921.7	921.6	921.8	922.0	922.1	922.3	923.0
160°	939.7	939.2	938.7	938.2	937.6	937.5	937.6	937.8	938.0	938.2	938.9
162.5°	954.2	953.8	953.4	953.1	952.7	952.5	952.5	952.6	952.6	952.7	953.5
165°	973.7	973.3	973.0	972.6	972.3	972.2	972.3	972.5	972.7	972.9	973.6
167.5°	990.1	989.4	988.7	988.0	987.2	986.9	986.9	986.9	986.9	986.9	988.0
170°	999.0	998.3	997.5	996.8	996.1	995.7	995.7	995.7	995.7	995.7	996.8
172.5°	1005.2	1004.5	1003.8	1003.1	1002.4	1002.1	1002.1	1002.1	1002.1	1002.1	1003.1
175°	1012.4	1011.7	1011.0	1010.3	1009.6	1009.2	1009.2	1009.2	1009.2	1009.2	1010.3
177.5°	1016.0	1015.4	1014.9	1014.3	1013.7	1013.4	1013.3	1013.1	1013.0	1012.8	1013.7
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333566-840

CATALOG NUMBER: S125RDIP-S850D810U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1383.9	1385.8	1387.7	1388.6	1388.4	1388.2	1388.0	1387.8
5°	1375.4	1377.8	1380.1	1381.1	1380.6	1380.1	1379.7	1379.2
7.5°	1358.4	1360.0	1361.6	1362.1	1361.6	1361.1	1360.6	1360.1
10°	1343.8	1344.5	1345.2	1345.2	1344.5	1343.8	1343.1	1342.5
12.5°	1323.3	1323.8	1324.3	1324.1	1323.0	1321.9	1320.9	1319.8
15°	1289.6	1289.3	1289.1	1288.0	1285.9	1283.7	1281.6	1279.5
17.5°	1247.4	1246.3	1245.1	1243.6	1241.9	1240.2	1238.5	1236.8
20°	1216.4	1215.2	1214.1	1212.4	1210.3	1208.2	1206.1	1204.1
22.5°	1185.6	1183.4	1181.0	1179.0	1177.3	1175.6	1173.9	1172.2
25°	1135.1	1132.1	1129.0	1126.2	1123.6	1121.1	1118.5	1115.9
27.5°	1080.4	1076.1	1071.9	1068.5	1066.1	1063.6	1061.2	1058.6
30°	1041.3	1035.9	1030.5	1026.8	1024.7	1022.6	1020.5	1018.3
32.5°	1003.2	997.2	991.4	987.0	984.4	981.8	979.1	976.4
35°	944.0	937.3	930.5	925.5	922.2	919.0	915.7	912.4
37.5°	882.2	874.0	866.0	860.3	857.2	853.9	850.8	847.7
40°	841.2	832.4	823.5	817.7	815.0	812.1	809.3	806.6
42.5°	800.9	792.4	784.0	777.6	773.6	769.4	765.3	761.2
45°	736.5	727.2	717.8	711.4	707.9	704.5	700.9	697.4
47.5°	672.8	663.2	653.6	646.8	643.0	639.1	635.2	631.4
50°	629.7	619.9	610.1	603.4	600.0	596.4	592.9	589.5
52.5°	588.8	578.1	567.6	560.6	557.1	553.6	550.2	546.6
55°	526.5	516.0	505.5	498.4	494.7	491.0	487.3	483.5
57.5°	464.2	454.0	443.7	437.0	433.6	430.3	427.1	423.7
60°	423.1	412.8	402.6	395.8	392.2	388.8	385.3	381.7
62.5°	382.6	373.1	363.7	357.2	353.7	350.1	346.7	343.2
65°	323.3	314.0	304.6	298.2	294.7	291.2	287.7	284.2
67.5°	266.5	258.0	249.4	243.8	241.1	238.2	235.4	232.7
70°	228.8	221.7	214.4	209.4	206.6	203.8	201.1	198.2
72.5°	193.9	187.2	180.6	176.3	174.4	172.6	170.8	168.8
75°	145.0	139.9	134.7	131.4	129.7	128.1	126.4	124.8
77.5°	103.1	99.6	95.9	93.6	92.4	91.2	90.0	88.8
80°	77.7	75.5	73.4	72.1	71.7	71.2	70.7	70.3
82.5°	58.1	57.1	56.0	55.4	55.1	54.9	54.6	54.3
85°	33.1	32.8	32.6	32.4	32.1	31.9	31.7	31.5
87.5°	15.5	15.7	15.9	15.9	15.8	15.7	15.7	15.6
90°	14.3	15.2	16.2	16.9	17.4	17.9	18.4	19.0
92.5°	32.6	33.8	34.9	35.7	36.2	36.5	36.9	37.3
95°	63.2	64.5	65.7	66.6	66.9	67.3	67.6	67.9
97.5°	99.2	100.3	101.5	102.1	102.3	102.5	102.8	103.0
100°	124.0	125.5	127.1	128.2	128.5	128.8	129.2	129.5
102.5°	149.6	151.3	153.0	154.1	154.6	155.0	155.5	156.0
105°	190.9	191.9	193.0	193.7	194.3	194.8	195.3	195.8
107.5°	235.4	235.9	236.5	236.7	236.7	236.6	236.6	236.6
110°	266.4	266.9	267.4	267.6	267.4	267.2	267.1	266.9



TEST NUMBER: P333566-840

CATALOG NUMBER: S125RDIP-S850D810U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	297.4	297.6	297.9	297.9	297.5	297.2	296.9	296.6
115°	344.8	344.6	344.4	344.2	344.1	343.9	343.7	343.6
117.5°	392.1	392.2	392.4	392.1	391.4	390.7	390.0	389.3
120°	424.0	424.0	424.0	423.7	423.0	422.3	421.6	420.9
122.5°	455.3	455.2	455.0	454.7	454.1	453.6	453.0	452.5
125°	501.5	501.2	500.8	500.6	500.4	500.2	500.1	499.9
127.5°	547.3	547.1	547.0	546.7	546.4	546.0	545.7	545.3
130°	577.6	577.5	577.3	577.0	576.7	576.3	576.0	575.6
132.5°	606.7	606.5	606.4	606.0	605.6	605.1	604.6	604.1
135°	651.5	651.5	651.5	651.2	650.5	649.7	649.0	648.3
137.5°	695.0	695.2	695.4	695.1	694.2	693.4	692.5	691.6
140°	722.5	722.8	723.2	722.9	722.1	721.1	720.2	719.4
142.5°	749.3	749.5	749.7	749.4	748.5	747.7	746.8	745.9
145°	788.1	788.1	788.1	787.8	787.3	786.8	786.3	785.7
147.5°	823.9	824.5	824.9	824.5	823.2	822.0	820.9	819.7
150°	846.6	846.6	846.6	846.4	846.0	845.7	845.3	845.0
152.5°	867.6	868.0	868.4	868.3	867.7	867.1	866.5	865.8
155°	897.7	898.4	899.1	899.0	898.1	897.3	896.4	895.4
157.5°	923.7	924.4	925.1	924.9	923.7	922.6	921.4	920.3
160°	939.6	940.2	940.9	940.9	940.0	939.1	938.2	937.4
162.5°	954.3	955.2	956.0	955.9	954.9	953.9	952.9	951.9
165°	974.3	975.0	975.6	975.5	974.4	973.4	972.3	971.3
167.5°	989.1	990.1	991.2	991.1	990.1	989.0	987.8	986.7
170°	997.8	999.0	1000.0	999.9	998.7	997.4	996.2	995.0
172.5°	1004.2	1005.2	1006.3	1006.3	1005.2	1004.1	1003.0	1001.9
175°	1011.3	1012.4	1013.4	1013.3	1012.1	1010.9	1009.7	1008.5
177.5°	1014.5	1015.3	1016.2	1016.1	1015.1	1014.2	1013.2	1012.2
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7

(END OF REPORT)