

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333567-930

Luminaire Tested: **S125RDIP-S850D810U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333567-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D810U930-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5021.4 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333567-930

CATALOG NUMBER: S125RDIP-S850D810U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333567-930

CATALOG NUMBER: S125RDIP-S850D810U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	58	56	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	32
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7240	7240	7240
5°	7257	7175	7219
10°	7202	7108	7108
15°	7117	6964	6907
20°	7007	6762	6681
25°	6879	6565	6420
30°	6718	6334	6131
35°	6556	6095	5807
40°	6403	5847	5490
45°	6218	5569	5142
50°	6031	5267	4782
55°	5816	4977	4396
60°	5599	4627	3981
65°	5344	4219	3506
70°	5053	3709	3021
75°	4649	3127	2515
80°	4095	2455	2109
85°	3453	2008	1882



TEST NUMBER: P333567-930

CATALOG NUMBER: S125RDIP-S850D810U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	2.1
10°-20°	294.6	5.9
20°-30°	427.2	8.5
30°-40°	486.9	9.7
40°-50°	474.6	9.5
50°-60°	399.5	8.0
60°-70°	280.0	5.6
70°-80°	143.9	2.9
80°-90°	38.1	0.8
90°-100°	229.2	4.6
100°-110°	492.7	9.8
110°-120°	462.4	9.2
120°-130°	374.7	7.5
130°-140°	300.7	6.0
140°-150°	226.9	4.5
150°-160°	159.7	3.2
160°-170°	94.2	1.9
170°-180°	30.6	0.6
0°-30°	827.2	16.5
0°-40°	1314.1	26.2
0°-60°	2188.2	43.6
0°-90°	2650.3	52.8
90°-120°	1184.3	23.6
90°-150°	2086.6	41.6
90°-180°	2371.0	47.2
0°-180°	5021.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1121	1121	1121	1121	1121	
5°	1119	1116	1107	1115	1114	106
15°	1064	1059	1042	1040	1033	300
25°	965	952	921	910	901	444
35°	832	810	773	749	737	520
45°	681	655	610	577	563	525
55°	516	488	442	405	390	462
65°	350	320	276	243	229	346
75°	186	160	125	107	101	197
85°	47	32	27	26	25	52
90°	1	6	10	13	15	3
95°	21	62	565	256	150	22
105°	72	101	462	910	845	76
115°	129	155	371	800	941	127
125°	178	209	356	636	741	158
135°	209	252	353	533	616	162
145°	244	279	354	441	486	153
155°	278	299	346	390	407	128
165°	304	312	332	352	357	85
175°	316	316	318	322	321	30
180°	316	316	316	316	316	



TEST NUMBER: P333567-930

CATALOG NUMBER: S125RDIP-S850D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1
2.5°	1123.1	1122.7	1122.2	1121.8	1121.3	1120.3	1118.8	1117.3	1115.8	1114.3	1115.8
5°	1119.4	1118.7	1117.9	1117.1	1116.4	1115.0	1112.9	1110.8	1108.7	1106.7	1108.6
7.5°	1108.4	1107.7	1106.9	1106.2	1105.5	1103.9	1101.5	1098.9	1096.5	1094.0	1095.3
10°	1098.2	1097.6	1097.1	1096.5	1095.9	1094.4	1091.8	1089.1	1086.5	1083.9	1084.3
12.5°	1086.7	1086.0	1085.2	1084.6	1083.9	1081.7	1078.2	1074.6	1071.1	1067.6	1068.0
15°	1064.4	1063.2	1062.1	1060.9	1059.8	1057.3	1053.4	1049.4	1045.5	1041.5	1041.3
17.5°	1039.1	1037.4	1035.7	1034.0	1032.2	1028.8	1023.9	1018.9	1013.9	1008.9	1008.0
20°	1019.5	1017.6	1015.7	1013.8	1011.9	1008.0	1002.0	996.0	989.9	983.9	983.0
22.5°	997.8	995.9	994.0	992.1	990.3	986.2	979.8	973.5	967.2	960.9	959.0
25°	965.3	962.5	959.6	956.8	954.0	949.1	942.2	935.1	928.2	921.3	918.8
27.5°	928.1	924.6	921.2	917.8	914.4	908.9	901.5	894.0	886.6	879.1	875.6
30°	900.9	897.3	893.8	890.2	886.6	880.8	873.0	865.1	857.2	849.3	845.0
32.5°	874.5	870.3	866.2	862.0	857.8	851.7	843.7	835.6	827.5	819.5	814.7
35°	831.5	827.0	822.5	817.9	813.4	806.9	798.5	790.0	781.5	773.1	767.6
37.5°	789.3	783.8	778.4	772.8	767.4	760.3	751.5	742.7	734.0	725.3	718.8
40°	759.5	753.9	748.2	742.6	736.9	729.6	720.6	711.5	702.5	693.5	686.3
42.5°	728.4	722.6	716.8	710.9	705.2	697.7	688.3	679.0	669.6	660.3	653.5
45°	680.8	675.3	669.8	664.4	658.9	651.0	640.7	630.4	620.0	609.7	602.1
47.5°	631.5	625.7	620.0	614.2	608.5	600.4	590.0	579.5	569.1	558.6	550.9
50°	600.3	594.1	587.9	581.7	575.5	567.0	556.3	545.6	534.8	524.2	516.2
52.5°	566.5	560.1	553.8	547.4	541.0	532.8	522.7	512.6	502.4	492.3	483.8
55°	516.5	510.5	504.5	498.5	492.4	484.1	473.6	463.1	452.6	442.0	433.5
57.5°	466.0	459.6	453.1	446.7	440.3	432.0	421.8	411.6	401.5	391.3	383.1
60°	433.5	427.0	420.4	413.8	407.2	398.8	388.7	378.5	368.4	358.2	349.9
62.5°	399.0	392.7	386.5	380.1	373.8	365.6	355.2	345.0	334.6	324.3	316.7
65°	349.7	343.3	336.9	330.5	324.1	315.9	306.0	296.0	286.0	276.1	268.5
67.5°	300.8	294.3	288.0	281.6	275.2	267.2	257.6	248.1	238.6	228.9	222.1
70°	267.6	261.1	254.8	248.3	242.0	234.1	224.7	215.2	205.9	196.4	190.6
72.5°	235.1	228.8	222.6	216.3	210.1	202.5	193.7	184.9	176.1	167.3	161.9
75°	186.3	180.7	175.0	169.3	163.7	156.9	149.0	141.1	133.2	125.3	121.2
77.5°	137.9	133.3	128.8	124.3	119.8	114.4	108.0	101.7	95.4	89.1	86.2
80°	110.1	105.6	101.0	96.5	92.0	87.2	81.9	76.6	71.3	66.0	64.3
82.5°	83.0	78.9	74.8	70.8	66.7	62.9	59.3	55.7	52.0	48.4	47.6
85°	46.6	43.2	39.8	36.4	33.0	30.8	29.9	28.9	28.0	27.1	26.9
87.5°	15.7	14.8	14.0	13.2	12.4	12.1	12.0	12.1	12.1	12.2	12.3
90°	0.7	1.3	2.5	3.8	5.1	6.4	7.0	8.3	8.9	10.2	10.8
92.5°	7.7	9.5	14.8	22.7	33.7	52.3	87.1	145.4	208.8	205.5	166.4
95°	21.0	21.7	26.7	33.8	47.8	76.5	144.7	284.9	460.9	564.8	552.7
97.5°	34.9	35.7	39.3	46.3	58.9	79.6	124.7	227.5	411.6	603.2	699.3
100°	44.6	45.9	48.4	55.4	67.6	86.7	123.7	206.5	367.2	575.7	735.0
102.5°	55.4	56.1	58.1	65.6	76.7	95.4	128.2	197.9	333.5	527.2	713.6
105°	72.1	72.1	75.3	81.6	91.8	109.7	137.7	194.4	300.9	462.2	645.1
107.5°	88.4	89.6	92.7	97.9	108.5	124.6	151.7	200.3	287.1	417.4	575.3
110°	100.1	101.3	103.9	109.7	119.2	135.7	161.9	205.9	283.1	396.5	535.5



TEST NUMBER: P333567-930

CATALOG NUMBER: S125RDIP-S850D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	111.8	113.1	115.1	120.8	130.4	146.5	171.6	213.0	283.1	384.3	505.9
115°	128.7	130.0	132.0	137.7	147.2	163.2	186.8	223.7	284.9	371.0	473.6
117.5°	144.1	146.0	148.1	153.8	164.6	180.0	202.4	236.0	289.2	364.5	454.4
120°	154.3	156.2	158.7	164.4	175.3	191.3	213.5	244.2	293.3	361.4	443.7
122.5°	165.0	166.4	168.4	174.1	186.1	201.9	224.3	253.3	296.8	358.9	434.5
125°	178.5	179.8	183.0	188.7	200.8	217.4	238.4	265.8	302.8	355.7	422.0
127.5°	189.1	191.0	195.1	202.4	215.2	231.8	252.1	277.3	309.6	354.2	410.5
130°	195.7	197.6	202.7	211.0	224.4	241.0	260.7	284.9	313.6	353.2	402.9
132.5°	200.8	203.3	209.4	218.7	232.5	249.2	268.9	291.6	318.2	353.2	396.8
135°	209.1	211.7	219.3	229.5	242.9	260.1	279.9	300.9	324.5	353.2	389.5
137.5°	219.6	221.4	228.6	238.8	251.9	269.6	287.6	307.8	330.2	353.9	383.0
140°	225.7	227.6	235.2	245.4	257.6	274.8	293.3	312.3	332.7	354.4	379.9
142.5°	232.8	234.2	241.3	251.5	263.2	279.3	296.8	315.0	334.3	355.0	377.4
145°	243.5	244.8	251.2	260.1	271.6	286.3	302.8	318.7	336.0	354.4	373.6
147.5°	254.7	255.5	261.0	269.3	279.2	292.1	306.6	321.1	336.6	352.8	369.6
150°	261.4	262.6	267.1	275.4	284.3	295.1	309.2	322.5	336.6	351.2	366.6
152.5°	268.5	269.3	273.2	280.5	288.9	298.7	311.7	323.6	336.1	349.2	363.0
155°	277.9	277.9	281.8	288.1	294.5	303.5	314.3	324.5	334.7	345.5	357.0
157.5°	286.3	286.3	289.3	294.7	300.4	307.1	316.4	325.1	333.0	341.7	351.4
160°	292.0	291.3	293.9	298.3	303.5	309.2	317.5	325.1	331.5	339.2	346.8
162.5°	296.5	296.0	298.5	302.4	306.5	311.2	318.5	324.6	330.0	336.1	342.7
165°	303.5	302.1	304.1	307.3	309.8	313.6	318.7	323.8	327.7	331.5	336.6
167.5°	308.0	307.4	308.5	310.3	312.1	314.5	318.7	322.3	324.1	327.0	330.6
170°	311.1	310.5	311.1	312.3	313.6	315.5	318.7	321.3	322.5	324.5	327.0
172.5°	313.2	312.0	312.6	313.9	314.6	315.5	318.2	320.2	320.5	321.4	323.4
175°	315.5	314.3	315.0	315.5	315.5	315.5	317.5	318.7	318.1	318.1	318.7
177.5°	316.7	315.7	315.7	316.2	315.7	315.7	316.7	317.2	316.2	316.2	316.7
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2



TEST NUMBER: P333567-930

CATALOG NUMBER: S125RDIP-S850D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1
2.5°	1117.3	1118.8	1120.3	1121.0	1120.9	1120.7	1120.5	1120.4
5°	1110.4	1112.3	1114.2	1115.0	1114.6	1114.2	1113.9	1113.5
7.5°	1096.7	1098.0	1099.3	1099.7	1099.3	1098.9	1098.5	1098.0
10°	1084.9	1085.5	1086.1	1086.1	1085.5	1084.9	1084.3	1083.9
12.5°	1068.4	1068.8	1069.2	1069.0	1068.1	1067.2	1066.4	1065.5
15°	1041.1	1040.9	1040.7	1039.8	1038.1	1036.4	1034.7	1033.0
17.5°	1007.1	1006.2	1005.2	1004.0	1002.7	1001.3	999.9	998.5
20°	982.0	981.0	980.2	978.8	977.1	975.4	973.7	972.1
22.5°	957.2	955.4	953.5	951.9	950.5	949.1	947.7	946.3
25°	916.4	914.0	911.5	909.2	907.1	905.1	903.0	900.9
27.5°	872.2	868.8	865.4	862.7	860.7	858.7	856.7	854.7
30°	840.7	836.3	831.9	829.0	827.3	825.6	823.9	822.1
32.5°	809.9	805.1	800.4	796.9	794.8	792.6	790.4	788.3
35°	762.1	756.7	751.2	747.2	744.5	741.9	739.3	736.6
37.5°	712.2	705.6	699.1	694.6	692.0	689.4	686.9	684.4
40°	679.1	672.1	664.9	660.1	657.9	655.7	653.4	651.2
42.5°	646.6	639.8	632.9	627.8	624.5	621.2	617.8	614.6
45°	594.6	587.1	579.5	574.4	571.5	568.8	565.9	563.0
47.5°	543.2	535.4	527.7	522.2	519.1	516.0	512.8	509.7
50°	508.3	500.4	492.5	487.1	484.4	481.5	478.7	475.9
52.5°	475.3	466.8	458.3	452.6	449.8	446.9	444.2	441.3
55°	425.1	416.6	408.1	402.4	399.4	396.4	393.4	390.4
57.5°	374.8	366.6	358.2	352.8	350.1	347.4	344.8	342.1
60°	341.6	333.3	325.1	319.5	316.7	313.9	311.0	308.2
62.5°	308.9	301.3	293.6	288.4	285.5	282.7	279.9	277.0
65°	261.0	253.5	245.9	240.8	237.9	235.1	232.3	229.4
67.5°	215.2	208.3	201.4	196.8	194.6	192.3	190.0	187.8
70°	184.7	179.0	173.1	169.1	166.8	164.5	162.3	160.0
72.5°	156.5	151.2	145.8	142.4	140.8	139.3	137.9	136.3
75°	117.1	112.9	108.8	106.1	104.7	103.4	102.1	100.8
77.5°	83.2	80.4	77.5	75.6	74.6	73.6	72.6	71.7
80°	62.7	61.0	59.3	58.2	57.9	57.5	57.1	56.7
82.5°	46.9	46.1	45.2	44.8	44.5	44.4	44.1	43.9
85°	26.7	26.5	26.3	26.2	25.9	25.8	25.6	25.4
87.5°	12.5	12.6	12.7	12.9	12.7	12.6	12.6	12.4
90°	11.5	12.1	12.7	14.0	14.0	14.0	14.7	14.7
92.5°	113.0	82.0	61.7	52.3	44.1	42.6	41.7	40.7
95°	458.4	361.4	283.1	229.5	184.3	165.1	160.0	149.8
97.5°	682.7	614.7	538.3	463.8	424.4	388.7	370.2	362.1
100°	784.1	752.8	687.2	620.9	576.9	531.0	507.4	497.3
102.5°	818.2	837.6	806.0	761.2	714.1	681.4	655.8	648.2
105°	798.1	885.5	913.5	906.5	886.1	865.0	852.3	844.7
107.5°	726.2	842.8	914.8	948.0	958.4	958.2	954.1	948.9
110°	673.2	794.3	884.2	938.3	967.0	979.2	983.7	983.7



TEST NUMBER: P333567-930

CATALOG NUMBER: S125RDIP-S850D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	631.4	746.3	837.2	901.2	943.1	963.8	974.9	979.6
115°	578.9	677.7	765.0	834.5	884.2	914.8	932.6	940.9
117.5°	544.9	630.1	705.3	769.1	818.8	850.4	868.1	873.2
120°	526.5	603.1	673.2	729.3	776.4	807.1	824.3	829.3
122.5°	512.8	583.7	646.1	698.7	740.8	768.8	786.0	790.6
125°	492.8	557.8	613.3	659.2	694.9	721.0	735.0	741.4
127.5°	472.4	533.0	584.8	627.8	660.1	683.2	696.5	699.3
130°	459.6	515.8	565.4	606.9	638.8	659.8	672.5	676.4
132.5°	446.9	499.4	544.5	584.4	616.3	637.3	649.1	653.4
135°	430.3	474.3	515.1	551.4	579.4	600.5	612.0	615.8
137.5°	416.3	451.8	485.8	516.6	541.8	560.8	571.4	575.7
140°	408.6	438.5	467.9	494.6	518.3	534.8	544.4	547.6
142.5°	402.0	427.4	452.6	475.8	495.9	509.9	518.9	521.5
145°	393.3	413.1	432.8	450.0	465.4	476.2	483.2	485.8
147.5°	385.1	401.2	416.4	429.4	441.5	450.2	454.3	455.4
150°	380.6	394.6	406.7	418.2	427.8	435.4	438.0	438.5
152.5°	375.4	388.0	399.1	408.0	416.0	422.2	424.7	425.3
155°	367.9	378.1	386.9	394.0	400.3	404.8	406.7	407.3
157.5°	360.2	368.6	375.4	381.0	386.0	389.6	391.4	391.3
160°	355.1	361.4	367.9	372.3	376.7	379.9	381.2	380.6
162.5°	349.4	355.3	360.7	364.6	368.1	370.7	371.0	370.9
165°	341.7	346.2	350.0	353.2	355.7	357.0	357.0	357.0
167.5°	334.3	337.2	340.1	342.4	343.7	344.9	344.4	344.2
170°	330.2	332.2	334.0	335.3	336.6	337.2	337.2	336.6
172.5°	325.6	327.5	329.0	329.7	330.0	331.1	330.1	329.5
175°	320.7	320.7	322.0	322.0	322.0	322.5	321.3	320.7
177.5°	317.2	317.7	317.7	317.7	317.2	317.7	316.2	316.2
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2

(END OF REPORT)