

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333293-940

Luminaire Tested: **S125DIP-S1090D1205U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333293-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1205U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7677.8 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333293-940

CATALOG NUMBER: S125DIP-S1090D1205U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333293-940

CATALOG NUMBER: S125DIP-S1090D1205U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	86	91	87	83	80	74	71	69	62	60	58	51	50	49	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	25	46	36	29	24	31	25	22	27	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	25	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9827	9827	9827
5°	9849	9756	9818
10°	9789	9686	9742
15°	9682	9570	9610
20°	9531	9407	9423
25°	9368	9213	9204
30°	9165	9004	8959
35°	8949	8779	8656
40°	8728	8535	8413
45°	8488	8312	8147
50°	8225	8043	7801
55°	7970	7739	7523
60°	7665	7432	7167
65°	7303	7065	6825
70°	6956	6637	6411
75°	6338	6128	5916
80°	5642	5553	5415
85°	4905	4994	4728



TEST NUMBER: P333293-940

CATALOG NUMBER: S125DIP-S1090D1205U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.5	1.9
10°-20°	405.3	5.3
20°-30°	598.4	7.8
30°-40°	698.2	9.1
40°-50°	701.3	9.1
50°-60°	615.6	8.0
60°-70°	458.7	6.0
70°-80°	262.3	3.4
80°-90°	79.2	1.0
90°-100°	89.2	1.2
100°-110°	263.4	3.4
110°-120°	446.1	5.8
120°-130°	587.0	7.6
130°-140°	657.8	8.6
140°-150°	644.7	8.4
150°-160°	541.5	7.1
160°-170°	359.9	4.7
170°-180°	126.0	1.6
0°-30°	1147.1	14.9
0°-40°	1845.3	24.0
0°-60°	3162.2	41.2
0°-90°	3962.3	51.6
90°-120°	798.6	10.4
90°-150°	2688.1	35.0
90°-180°	3716.0	48.4
0°-180°	7677.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1522	1522	1522	1522	1522	
5°	1519	1516	1505	1515	1514	144
15°	1448	1444	1431	1437	1437	408
25°	1315	1308	1293	1295	1292	605
35°	1135	1130	1114	1107	1098	710
45°	929	924	910	896	892	716
55°	708	703	687	677	668	632
65°	478	475	462	452	447	474
75°	254	251	246	242	237	271
85°	66	67	67	66	64	74
90°	1	9	17	22	25	7
95°	67	70	80	87	89	72
105°	236	242	248	254	257	252
115°	447	451	453	452	451	442
125°	652	658	659	657	656	584
135°	848	854	855	855	851	653
145°	1027	1031	1034	1034	1031	642
155°	1175	1175	1176	1180	1175	541
165°	1278	1276	1277	1280	1274	360
175°	1328	1324	1324	1330	1323	126
180°	1332	1332	1332	1332	1332	



TEST NUMBER: P333293-940

CATALOG NUMBER: S125DIP-S1090D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
2.5°	1525.4	1524.8	1524.1	1523.5	1522.9	1521.4	1519.3	1517.2	1515.0	1512.9	1515.0
5°	1519.2	1518.7	1518.1	1517.6	1517.1	1515.5	1512.8	1510.1	1507.4	1504.8	1507.2
7.5°	1505.2	1504.7	1504.1	1503.6	1503.1	1501.3	1498.3	1495.4	1492.5	1489.5	1491.9
10°	1492.7	1492.2	1491.7	1491.1	1490.6	1488.8	1485.9	1482.9	1480.0	1477.0	1479.2
12.5°	1477.3	1476.3	1475.3	1474.4	1473.5	1471.6	1468.8	1466.2	1463.4	1460.6	1462.4
15°	1448.1	1447.3	1446.5	1445.7	1444.9	1443.1	1440.1	1437.2	1434.2	1431.3	1432.6
17.5°	1414.7	1413.5	1412.3	1411.1	1410.0	1407.8	1404.8	1401.8	1398.7	1395.6	1397.3
20°	1386.8	1386.3	1385.7	1385.2	1384.6	1382.6	1379.1	1375.6	1372.2	1368.7	1370.6
22.5°	1358.8	1357.9	1356.9	1355.9	1355.0	1352.8	1349.6	1346.3	1343.1	1339.8	1341.0
25°	1314.6	1313.2	1311.9	1310.5	1309.2	1306.8	1303.3	1299.8	1296.4	1292.9	1293.4
27.5°	1262.8	1261.9	1261.1	1260.3	1259.5	1257.4	1253.7	1250.2	1246.6	1243.0	1243.1
30°	1229.0	1228.2	1227.4	1226.6	1225.8	1223.4	1219.4	1215.4	1211.4	1207.4	1206.8
32.5°	1192.5	1191.2	1190.0	1188.7	1187.6	1185.2	1181.5	1177.9	1174.4	1170.8	1169.8
35°	1135.1	1134.1	1133.0	1131.9	1130.9	1128.5	1124.7	1121.0	1117.2	1113.5	1112.1
37.5°	1075.7	1074.3	1073.0	1071.7	1070.3	1067.9	1064.3	1060.9	1057.3	1053.8	1051.8
40°	1035.3	1033.9	1032.6	1031.3	1029.9	1027.3	1023.6	1019.8	1016.1	1012.4	1010.0
42.5°	991.9	990.8	989.7	988.6	987.4	985.0	981.2	977.5	973.7	970.0	967.8
45°	929.3	928.3	927.2	926.1	925.1	922.9	919.7	916.5	913.3	910.1	906.9
47.5°	861.9	861.9	862.0	862.1	862.1	860.2	856.4	852.5	848.6	844.8	841.5
50°	818.6	817.8	817.0	816.2	815.4	813.3	810.1	806.9	803.7	800.5	797.0
52.5°	774.3	773.6	773.1	772.5	772.0	769.9	766.5	763.0	759.6	756.2	753.1
55°	707.8	707.0	706.2	705.4	704.6	702.3	698.6	694.8	691.1	687.3	684.9
57.5°	637.8	637.3	636.9	636.5	636.1	634.3	631.1	627.9	624.8	621.6	618.5
60°	593.4	592.4	591.3	590.2	589.2	587.2	584.2	581.3	578.4	575.4	572.7
62.5°	547.2	546.4	545.5	544.7	543.9	542.2	539.6	537.1	534.6	532.1	529.1
65°	477.9	477.3	476.8	476.3	475.7	474.0	471.1	468.1	465.2	462.3	459.9
67.5°	410.7	409.6	408.5	407.3	406.3	404.6	402.3	400.2	398.0	395.8	393.8
70°	368.4	367.0	365.7	364.4	363.0	361.1	358.7	356.3	353.9	351.5	349.9
72.5°	322.2	321.2	320.3	319.4	318.5	317.3	315.8	314.1	312.6	311.0	309.2
75°	254.0	253.4	252.9	252.4	251.8	250.9	249.6	248.3	246.9	245.6	244.8
77.5°	191.2	190.9	190.7	190.6	190.3	189.8	189.0	188.3	187.6	186.8	186.4
80°	151.7	151.7	151.7	151.7	151.7	151.4	150.9	150.3	149.8	149.3	149.0
82.5°	117.0	116.5	116.2	115.7	115.3	115.0	114.9	114.9	114.7	114.6	114.1
85°	66.2	66.4	66.7	67.0	67.2	67.4	67.4	67.4	67.4	67.4	67.1
87.5°	26.2	26.6	26.9	27.3	27.6	27.9	28.0	28.2	28.3	28.4	28.6
90°	1.1	2.9	4.7	6.6	8.4	10.2	11.8	13.4	15.0	16.6	17.7
92.5°	25.1	26.4	27.6	29.0	30.2	31.8	33.9	35.8	37.8	39.8	41.3
95°	67.3	67.8	68.3	68.8	69.2	70.5	72.9	75.2	77.5	79.8	81.4
97.5°	111.9	112.1	112.3	112.4	112.6	114.3	117.5	120.6	123.9	127.1	128.6
100°	145.1	145.1	145.1	145.1	145.1	146.6	149.5	152.6	155.5	158.5	160.6
102.5°	180.7	181.6	182.5	183.5	184.4	185.7	187.2	188.7	190.2	191.7	193.9
105°	236.2	237.4	238.5	239.7	240.9	242.1	243.5	244.9	246.3	247.6	249.1
107.5°	297.6	298.7	299.9	301.0	302.2	303.3	304.3	305.4	306.5	307.6	308.3
110°	339.9	341.0	342.1	343.3	344.5	345.4	346.1	346.8	347.5	348.1	348.8



TEST NUMBER: P333293-940

CATALOG NUMBER: S125DIP-S1090D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	383.0	383.6	384.1	384.8	385.4	386.1	387.0	387.9	388.7	389.6	389.9
115°	446.6	447.5	448.4	449.3	450.3	450.9	451.5	451.9	452.4	452.8	452.6
117.5°	510.4	510.9	511.3	511.7	512.1	512.5	512.9	513.4	513.7	514.2	514.3
120°	550.2	551.3	552.5	553.7	554.8	555.5	555.7	556.0	556.2	556.4	556.4
122.5°	593.3	593.8	594.1	594.6	594.9	595.5	596.1	596.7	597.3	597.9	597.7
125°	651.8	653.2	654.5	655.9	657.3	658.1	658.4	658.5	658.8	659.1	658.5
127.5°	714.0	714.7	715.5	716.3	717.1	717.6	717.9	718.2	718.5	718.7	718.5
130°	751.3	752.4	753.6	754.7	755.8	756.7	757.2	757.6	758.0	758.5	758.3
132.5°	788.5	790.4	792.4	794.2	796.1	797.0	796.9	796.8	796.7	796.7	796.4
135°	847.7	849.0	850.4	851.8	853.2	854.0	854.2	854.4	854.6	854.9	854.9
137.5°	903.1	904.5	905.8	907.1	908.5	909.5	909.9	910.4	911.0	911.4	911.7
140°	938.8	940.0	941.1	942.3	943.4	944.3	945.0	945.7	946.4	947.1	947.5
142.5°	974.5	975.4	976.4	977.3	978.3	979.3	980.1	981.0	981.9	982.8	983.0
145°	1026.9	1027.8	1028.8	1029.7	1030.6	1031.4	1032.1	1032.8	1033.4	1034.1	1034.1
147.5°	1075.4	1075.8	1076.4	1076.9	1077.4	1077.9	1078.5	1079.1	1079.6	1080.1	1080.7
150°	1107.7	1107.5	1107.2	1107.1	1106.8	1107.1	1108.0	1108.9	1109.9	1110.8	1110.8
152.5°	1134.3	1134.5	1134.9	1135.2	1135.5	1135.9	1136.2	1136.6	1137.0	1137.4	1137.9
155°	1175.1	1175.1	1175.1	1175.1	1175.1	1175.2	1175.5	1175.6	1175.9	1176.1	1177.1
157.5°	1211.6	1211.0	1210.5	1210.1	1209.5	1209.3	1209.6	1209.9	1210.1	1210.3	1211.2
160°	1233.1	1232.4	1231.7	1231.0	1230.3	1230.1	1230.3	1230.6	1230.8	1231.0	1231.9
162.5°	1252.1	1251.7	1251.2	1250.6	1250.1	1249.9	1249.9	1250.0	1250.0	1250.1	1251.2
165°	1277.6	1277.2	1276.8	1276.3	1275.8	1275.7	1275.9	1276.1	1276.4	1276.6	1277.6
167.5°	1299.2	1298.2	1297.4	1296.5	1295.5	1295.0	1295.0	1295.0	1295.0	1295.0	1296.5
170°	1310.8	1309.9	1308.9	1308.1	1307.2	1306.6	1306.6	1306.6	1306.6	1306.6	1308.1
172.5°	1319.1	1318.2	1317.2	1316.3	1315.5	1314.9	1314.9	1314.9	1314.9	1314.9	1316.3
175°	1328.4	1327.5	1326.6	1325.6	1324.7	1324.3	1324.3	1324.3	1324.3	1324.3	1325.6
177.5°	1333.2	1332.5	1331.7	1331.0	1330.3	1329.8	1329.6	1329.5	1329.2	1329.0	1330.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333293-940

CATALOG NUMBER: S125DIP-S1090D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
2.5°	1517.2	1519.3	1521.4	1522.4	1522.2	1522.0	1521.8	1521.6
5°	1509.6	1512.0	1514.4	1515.5	1515.2	1514.9	1514.7	1514.4
7.5°	1494.2	1496.6	1499.0	1500.0	1499.8	1499.5	1499.2	1499.0
10°	1481.3	1483.5	1485.6	1486.6	1486.3	1486.0	1485.8	1485.5
12.5°	1464.1	1465.8	1467.5	1468.4	1468.3	1468.2	1468.2	1468.1
15°	1434.0	1435.3	1436.6	1437.3	1437.3	1437.3	1437.3	1437.3
17.5°	1399.0	1400.6	1402.3	1402.5	1401.1	1399.8	1398.5	1397.1
20°	1372.4	1374.3	1376.2	1376.4	1375.1	1373.8	1372.4	1371.1
22.5°	1342.3	1343.5	1344.7	1344.9	1344.0	1343.1	1342.2	1341.2
25°	1294.0	1294.5	1295.0	1294.9	1294.1	1293.2	1292.4	1291.6
27.5°	1243.2	1243.3	1243.5	1243.1	1242.3	1241.5	1240.7	1239.9
30°	1206.3	1205.8	1205.2	1204.6	1203.8	1203.0	1202.2	1201.4
32.5°	1168.9	1167.9	1167.0	1165.7	1164.3	1162.9	1161.4	1159.9
35°	1110.8	1109.5	1108.1	1106.4	1104.3	1102.2	1100.0	1097.9
37.5°	1049.8	1047.8	1045.9	1044.3	1043.0	1041.8	1040.5	1039.4
40°	1007.5	1005.1	1002.7	1001.1	1000.3	999.5	998.7	997.9
42.5°	965.6	963.4	961.3	959.5	958.3	957.1	955.8	954.6
45°	903.7	900.4	897.2	895.2	894.4	893.6	892.8	892.0
47.5°	838.3	835.0	831.8	829.2	827.3	825.5	823.6	821.7
50°	793.5	790.1	786.6	783.9	782.0	780.2	778.3	776.4
52.5°	750.1	747.1	744.0	741.5	739.3	737.3	735.2	733.1
55°	682.5	680.1	677.7	675.6	673.7	671.8	669.9	668.1
57.5°	615.5	612.3	609.2	607.2	606.2	605.1	604.1	603.1
60°	570.1	567.4	564.7	562.4	560.5	558.7	556.8	554.9
62.5°	526.3	523.4	520.5	518.4	516.9	515.5	514.0	512.6
65°	457.4	455.0	452.6	450.8	449.8	448.7	447.6	446.6
67.5°	391.7	389.7	387.6	386.3	385.7	385.0	384.4	383.8
70°	348.3	346.7	345.1	343.8	342.7	341.6	340.5	339.5
72.5°	307.5	305.6	303.8	302.4	301.3	300.2	299.2	298.1
75°	244.0	243.2	242.4	241.4	240.3	239.2	238.2	237.1
77.5°	185.8	185.4	184.9	184.3	183.5	182.8	182.0	181.3
80°	148.7	148.5	148.2	147.8	147.2	146.7	146.2	145.6
82.5°	113.6	113.2	112.7	112.4	112.3	112.2	112.1	111.9
85°	66.9	66.6	66.3	65.9	65.4	64.8	64.3	63.8
87.5°	28.8	29.1	29.2	29.2	29.0	28.6	28.4	28.1
90°	18.9	20.1	21.2	22.1	22.8	23.5	24.2	24.9
92.5°	42.8	44.3	45.8	46.9	47.3	47.9	48.4	48.9
95°	83.0	84.6	86.2	87.3	87.7	88.2	88.6	89.1
97.5°	130.1	131.6	133.1	134.0	134.3	134.6	134.8	135.1
100°	162.6	164.8	166.8	168.1	168.5	169.0	169.5	170.0
102.5°	196.2	198.5	200.7	202.2	202.9	203.5	204.1	204.7
105°	250.4	251.8	253.2	254.2	254.9	255.6	256.3	257.0
107.5°	308.9	309.6	310.3	310.7	310.6	310.6	310.5	310.4
110°	349.6	350.3	350.9	351.2	350.9	350.7	350.4	350.3



TEST NUMBER: P333293-940

CATALOG NUMBER: S125DIP-S1090D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	390.3	390.6	390.9	390.8	390.5	390.0	389.6	389.2
115°	452.4	452.1	451.9	451.7	451.5	451.2	450.9	450.8
117.5°	514.5	514.7	514.9	514.5	513.6	512.7	511.8	510.9
120°	556.4	556.4	556.4	556.0	555.1	554.1	553.2	552.3
122.5°	597.5	597.4	597.2	596.7	595.9	595.2	594.5	593.8
125°	658.1	657.6	657.2	656.8	656.7	656.4	656.1	655.9
127.5°	718.3	718.0	717.8	717.5	717.0	716.5	716.0	715.6
130°	758.0	757.8	757.6	757.2	756.8	756.3	755.8	755.4
132.5°	796.2	795.9	795.7	795.3	794.6	794.0	793.4	792.7
135°	854.9	854.9	854.9	854.4	853.5	852.6	851.7	850.7
137.5°	912.0	912.3	912.6	912.1	911.0	909.8	908.7	907.5
140°	948.0	948.5	949.0	948.6	947.4	946.3	945.1	944.0
142.5°	983.3	983.6	983.8	983.4	982.2	981.1	980.0	978.8
145°	1034.1	1034.1	1034.1	1033.8	1033.1	1032.4	1031.7	1031.0
147.5°	1081.3	1081.8	1082.4	1081.8	1080.3	1078.7	1077.2	1075.6
150°	1110.8	1110.8	1110.8	1110.6	1110.1	1109.6	1109.2	1108.8
152.5°	1138.4	1139.0	1139.5	1139.4	1138.6	1137.7	1136.9	1136.1
155°	1177.9	1178.8	1179.8	1179.6	1178.5	1177.3	1176.3	1175.1
157.5°	1212.1	1213.1	1214.0	1213.7	1212.2	1210.7	1209.2	1207.6
160°	1232.9	1233.8	1234.7	1234.6	1233.4	1232.3	1231.1	1230.0
162.5°	1252.3	1253.4	1254.5	1254.4	1253.0	1251.7	1250.4	1249.0
165°	1278.4	1279.3	1280.3	1280.1	1278.7	1277.3	1275.9	1274.5
167.5°	1297.8	1299.2	1300.6	1300.6	1299.1	1297.7	1296.3	1294.9
170°	1309.4	1310.8	1312.2	1312.1	1310.5	1308.9	1307.2	1305.6
172.5°	1317.7	1319.1	1320.4	1320.4	1319.0	1317.6	1316.2	1314.7
175°	1327.0	1328.4	1329.8	1329.7	1328.1	1326.5	1324.8	1323.2
177.5°	1331.2	1332.4	1333.5	1333.4	1332.1	1330.8	1329.5	1328.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5

(END OF REPORT)