

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333257

Luminaire Tested: **S125DIP-S1090D365U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333257
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D365U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5708.6 lumens
Efficiency: N/A
Efficacy: 131.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333257

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333257

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	65
2	95	87	80	75	90	83	77	72	76	71	67	69	66	62	63	60	58	55
3	86	76	69	62	82	73	66	60	67	61	57	61	57	53	56	52	49	46
4	79	68	59	53	75	65	57	51	60	53	48	55	50	45	50	46	42	40
5	73	60	52	46	69	58	50	44	53	47	42	49	44	39	45	41	37	34
6	67	54	46	40	64	52	44	39	48	42	37	45	39	35	41	36	33	30
7	62	49	41	35	59	47	40	34	44	37	32	41	35	31	38	33	29	27
8	58	45	37	31	55	43	36	30	40	34	29	37	32	27	35	30	26	24
9	54	41	33	28	51	40	32	27	37	31	26	34	29	25	32	27	24	22
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	21	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11021	11021	11021
5°	11045	10940	11010
10°	10978	10863	10925
15°	10858	10732	10777
20°	10689	10549	10568
25°	10505	10332	10322
30°	10279	10097	10047
35°	10037	9845	9707
40°	9788	9571	9435
45°	9519	9322	9136
50°	9224	9020	8748
55°	8938	8679	8436
60°	8596	8335	8038
65°	8189	7922	7653
70°	7801	7444	7189
75°	7107	6872	6635
80°	6326	6226	6073
85°	5498	5602	5298



TEST NUMBER: P333257

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.9	2.8
10°-20°	454.5	8.0
20°-30°	671.0	11.8
30°-40°	783.0	13.7
40°-50°	786.4	13.8
50°-60°	690.3	12.1
60°-70°	514.4	9.0
70°-80°	294.1	5.2
80°-90°	86.6	1.5
90°-100°	30.4	0.5
100°-110°	89.8	1.6
110°-120°	152.1	2.7
120°-130°	200.2	3.5
130°-140°	224.4	3.9
140°-150°	219.9	3.9
150°-160°	184.7	3.2
160°-170°	122.8	2.2
170°-180°	43.0	0.8
0°-30°	1286.4	22.5
0°-40°	2069.4	36.3
0°-60°	3546.2	62.1
0°-90°	4441.2	77.8
90°-120°	272.4	4.8
90°-150°	916.9	16.1
90°-180°	1267.0	22.2
0°-180°	5708.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1706	1706	1706	1706	1706	
5°	1704	1700	1688	1699	1698	162
15°	1624	1619	1605	1612	1612	458
25°	1474	1467	1450	1452	1448	678
35°	1273	1267	1249	1242	1231	796
45°	1042	1036	1021	1005	1000	803
55°	794	789	771	759	749	708
65°	536	533	518	507	501	532
75°	285	282	275	271	266	304
85°	74	76	76	74	72	83
90°	0	3	6	7	8	5
95°	23	24	27	30	30	25
105°	81	82	84	87	88	86
115°	152	154	154	154	154	151
125°	222	224	225	224	224	199
135°	289	291	292	292	290	223
145°	350	352	353	353	352	219
155°	401	401	401	402	401	185
165°	436	435	435	437	435	123
175°	453	452	452	454	451	43
180°	454	454	454	454	454	



TEST NUMBER: P333257

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1710.7	1710.0	1709.2	1708.5	1707.8	1706.2	1703.8	1701.4	1699.0	1696.6	1699.0
5°	1703.7	1703.1	1702.5	1701.9	1701.3	1699.5	1696.5	1693.5	1690.5	1687.5	1690.2
7.5°	1688.0	1687.4	1686.8	1686.2	1685.6	1683.6	1680.3	1677.0	1673.7	1670.4	1673.1
10°	1674.0	1673.4	1672.8	1672.2	1671.6	1669.6	1666.3	1663.0	1659.7	1656.4	1658.8
12.5°	1656.7	1655.6	1654.5	1653.4	1652.4	1650.3	1647.2	1644.2	1641.1	1638.0	1640.0
15°	1624.0	1623.1	1622.2	1621.3	1620.4	1618.3	1615.0	1611.7	1608.4	1605.1	1606.6
17.5°	1586.5	1585.2	1583.8	1582.5	1581.2	1578.8	1575.4	1572.0	1568.6	1565.1	1567.0
20°	1555.2	1554.6	1554.0	1553.4	1552.8	1550.5	1546.6	1542.7	1538.8	1534.9	1537.0
22.5°	1523.8	1522.8	1521.7	1520.6	1519.5	1517.1	1513.5	1509.8	1506.2	1502.5	1503.9
25°	1474.2	1472.7	1471.2	1469.7	1468.2	1465.5	1461.6	1457.7	1453.8	1449.9	1450.5
27.5°	1416.1	1415.2	1414.3	1413.4	1412.5	1410.1	1406.0	1402.0	1398.0	1394.0	1394.1
30°	1378.3	1377.4	1376.5	1375.6	1374.7	1372.0	1367.5	1363.0	1358.5	1354.0	1353.4
32.5°	1337.3	1335.9	1334.5	1333.1	1331.8	1329.1	1325.0	1321.0	1317.0	1313.0	1311.9
35°	1273.0	1271.8	1270.6	1269.4	1268.2	1265.5	1261.3	1257.1	1252.9	1248.7	1247.2
37.5°	1206.3	1204.8	1203.3	1201.8	1200.3	1197.6	1193.6	1189.7	1185.7	1181.8	1179.5
40°	1161.0	1159.5	1158.0	1156.5	1155.0	1152.1	1147.9	1143.7	1139.5	1135.3	1132.6
42.5°	1112.4	1111.1	1109.9	1108.6	1107.3	1104.6	1100.4	1096.2	1092.0	1087.8	1085.3
45°	1042.2	1041.0	1039.8	1038.6	1037.4	1035.0	1031.4	1027.8	1024.2	1020.6	1017.0
47.5°	966.6	966.6	966.7	966.8	966.8	964.7	960.4	956.0	951.7	947.4	943.7
50°	918.0	917.1	916.2	915.3	914.4	912.1	908.5	904.9	901.3	897.7	893.8
52.5°	868.3	867.6	867.0	866.3	865.7	863.4	859.6	855.7	851.9	848.0	844.6
55°	793.8	792.9	792.0	791.1	790.2	787.6	783.4	779.2	775.0	770.8	768.1
57.5°	715.2	714.7	714.3	713.8	713.3	711.3	707.7	704.2	700.7	697.1	693.6
60°	665.5	664.3	663.1	661.9	660.7	658.5	655.2	651.9	648.6	645.3	642.3
62.5°	613.7	612.7	611.8	610.8	609.9	608.0	605.1	602.3	599.5	596.7	593.4
65°	535.9	535.3	534.7	534.1	533.5	531.6	528.3	525.0	521.7	518.4	515.7
67.5°	460.6	459.3	458.1	456.8	455.6	453.7	451.2	448.8	446.3	443.9	441.6
70°	413.1	411.6	410.1	408.6	407.1	405.0	402.3	399.6	396.9	394.2	392.4
72.5°	361.3	360.2	359.2	358.2	357.2	355.8	354.1	352.3	350.6	348.8	346.8
75°	284.8	284.2	283.6	283.0	282.4	281.4	279.9	278.4	276.9	275.4	274.5
77.5°	214.4	214.1	213.9	213.7	213.4	212.9	212.0	211.2	210.4	209.5	209.0
80°	170.1	170.1	170.1	170.1	170.1	169.8	169.2	168.6	168.0	167.4	167.1
82.5°	131.2	130.7	130.3	129.8	129.3	129.0	128.9	128.8	128.6	128.5	128.0
85°	74.2	74.5	74.8	75.1	75.4	75.6	75.6	75.6	75.6	75.6	75.3
87.5°	29.2	29.4	29.5	29.6	29.7	29.7	29.6	29.5	29.3	29.2	29.3
90°	0.4	1.0	1.6	2.2	2.9	3.5	4.0	4.6	5.1	5.7	6.0
92.5°	8.6	9.0	9.4	9.9	10.3	10.9	11.5	12.2	12.9	13.6	14.1
95°	23.0	23.1	23.3	23.4	23.6	24.1	24.9	25.6	26.4	27.2	27.8
97.5°	38.2	38.2	38.3	38.4	38.4	39.0	40.1	41.2	42.2	43.3	43.9
100°	49.5	49.5	49.5	49.5	49.5	50.0	51.0	52.0	53.1	54.1	54.8
102.5°	61.6	62.0	62.3	62.6	62.9	63.3	63.8	64.3	64.9	65.4	66.2
105°	80.6	81.0	81.4	81.8	82.2	82.6	83.1	83.5	84.0	84.5	84.9
107.5°	101.5	101.9	102.3	102.7	103.1	103.5	103.8	104.2	104.5	104.9	105.1
110°	115.9	116.3	116.7	117.1	117.5	117.8	118.0	118.3	118.5	118.8	119.0



TEST NUMBER: P333257

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	130.6	130.8	131.0	131.2	131.4	131.7	132.0	132.3	132.6	132.9	133.0
115°	152.3	152.6	153.0	153.3	153.6	153.8	154.0	154.1	154.3	154.5	154.4
117.5°	174.1	174.2	174.4	174.5	174.7	174.8	175.0	175.1	175.2	175.4	175.4
120°	187.7	188.1	188.5	188.9	189.2	189.5	189.6	189.6	189.7	189.8	189.8
122.5°	202.4	202.5	202.7	202.8	202.9	203.1	203.3	203.5	203.7	203.9	203.9
125°	222.3	222.8	223.3	223.7	224.2	224.5	224.6	224.6	224.7	224.8	224.6
127.5°	243.5	243.8	244.1	244.3	244.6	244.8	244.9	245.0	245.1	245.1	245.1
130°	256.2	256.6	257.0	257.4	257.8	258.1	258.2	258.4	258.6	258.7	258.6
132.5°	269.0	269.6	270.3	270.9	271.5	271.9	271.8	271.8	271.8	271.7	271.6
135°	289.1	289.6	290.1	290.5	291.0	291.3	291.4	291.4	291.5	291.6	291.6
137.5°	308.1	308.5	309.0	309.4	309.9	310.2	310.4	310.5	310.7	310.9	311.0
140°	320.2	320.6	321.0	321.4	321.8	322.1	322.3	322.6	322.8	323.0	323.2
142.5°	332.4	332.7	333.0	333.4	333.7	334.0	334.3	334.6	334.9	335.2	335.3
145°	350.3	350.6	350.9	351.2	351.5	351.8	352.0	352.3	352.5	352.7	352.7
147.5°	366.8	367.0	367.1	367.3	367.5	367.7	367.9	368.1	368.2	368.4	368.6
150°	377.8	377.8	377.7	377.6	377.5	377.6	377.9	378.3	378.6	378.9	378.9
152.5°	386.9	387.0	387.1	387.2	387.3	387.4	387.6	387.7	387.8	387.9	388.1
155°	400.8	400.8	400.8	400.8	400.8	400.8	400.9	401.0	401.1	401.2	401.5
157.5°	413.2	413.1	412.9	412.7	412.6	412.5	412.6	412.7	412.7	412.8	413.1
160°	420.6	420.4	420.1	419.9	419.7	419.6	419.7	419.7	419.8	419.9	420.2
162.5°	427.1	426.9	426.8	426.6	426.4	426.3	426.3	426.4	426.4	426.4	426.8
165°	435.8	435.6	435.5	435.3	435.2	435.1	435.2	435.3	435.4	435.4	435.8
167.5°	443.1	442.8	442.5	442.2	441.9	441.7	441.7	441.7	441.7	441.7	442.2
170°	447.1	446.8	446.5	446.2	445.8	445.7	445.7	445.7	445.7	445.7	446.2
172.5°	449.9	449.6	449.3	449.0	448.7	448.5	448.5	448.5	448.5	448.5	449.0
175°	453.1	452.8	452.5	452.2	451.9	451.7	451.7	451.7	451.7	451.7	452.2
177.5°	454.7	454.5	454.2	454.0	453.7	453.6	453.5	453.5	453.4	453.3	453.7
180°	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2



TEST NUMBER: P333257

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1701.4	1703.8	1706.2	1707.3	1707.1	1706.8	1706.6	1706.4
5°	1692.9	1695.6	1698.3	1699.5	1699.2	1698.9	1698.6	1698.3
7.5°	1675.7	1678.4	1681.0	1682.2	1681.9	1681.6	1681.3	1681.0
10°	1661.2	1663.6	1666.0	1667.1	1666.8	1666.5	1666.2	1665.9
12.5°	1641.9	1643.8	1645.7	1646.7	1646.6	1646.5	1646.5	1646.4
15°	1608.1	1609.6	1611.1	1611.9	1611.9	1611.9	1611.9	1611.9
17.5°	1568.9	1570.7	1572.6	1572.8	1571.3	1569.8	1568.3	1566.8
20°	1539.1	1541.2	1543.3	1543.6	1542.1	1540.6	1539.1	1537.6
22.5°	1505.3	1506.7	1508.0	1508.2	1507.2	1506.2	1505.2	1504.1
25°	1451.1	1451.7	1452.3	1452.1	1451.2	1450.3	1449.4	1448.5
27.5°	1394.2	1394.3	1394.5	1394.1	1393.2	1392.3	1391.4	1390.5
30°	1352.8	1352.2	1351.6	1350.9	1350.0	1349.1	1348.2	1347.3
32.5°	1310.8	1309.7	1308.7	1307.3	1305.7	1304.1	1302.4	1300.8
35°	1245.7	1244.2	1242.7	1240.8	1238.4	1236.0	1233.6	1231.2
37.5°	1177.3	1175.1	1172.9	1171.1	1169.7	1168.3	1166.9	1165.6
40°	1129.9	1127.2	1124.5	1122.7	1121.8	1120.9	1120.0	1119.1
42.5°	1082.9	1080.4	1078.0	1076.0	1074.7	1073.3	1071.9	1070.5
45°	1013.4	1009.8	1006.2	1003.9	1003.0	1002.1	1001.2	1000.3
47.5°	940.1	936.4	932.8	929.9	927.8	925.7	923.6	921.5
50°	889.9	886.0	882.1	879.1	877.0	874.9	872.8	870.7
52.5°	841.2	837.8	834.4	831.5	829.1	826.8	824.5	822.1
55°	765.4	762.7	760.0	757.6	755.5	753.4	751.3	749.2
57.5°	690.2	686.7	683.2	680.9	679.8	678.6	677.5	676.3
60°	639.3	636.3	633.3	630.7	628.6	626.5	624.4	622.3
62.5°	590.2	587.0	583.7	581.3	579.7	578.1	576.4	574.8
65°	513.0	510.3	507.6	505.6	504.4	503.2	502.0	500.8
67.5°	439.3	437.0	434.7	433.2	432.5	431.8	431.1	430.4
70°	390.6	388.8	387.0	385.5	384.3	383.1	381.9	380.7
72.5°	344.8	342.7	340.7	339.1	337.9	336.7	335.5	334.3
75°	273.6	272.7	271.8	270.7	269.5	268.3	267.1	265.9
77.5°	208.4	207.9	207.4	206.7	205.8	205.0	204.1	203.3
80°	166.8	166.5	166.2	165.7	165.1	164.5	163.9	163.3
82.5°	127.4	126.9	126.4	126.0	125.9	125.8	125.7	125.5
85°	75.0	74.7	74.4	73.9	73.3	72.7	72.1	71.5
87.5°	29.4	29.4	29.5	29.3	28.9	28.5	28.0	27.6
90°	6.4	6.8	7.2	7.5	7.8	8.0	8.2	8.5
92.5°	14.6	15.1	15.6	16.0	16.2	16.3	16.5	16.7
95°	28.3	28.9	29.4	29.8	29.9	30.1	30.2	30.4
97.5°	44.4	44.9	45.4	45.7	45.8	45.9	46.0	46.1
100°	55.5	56.2	56.9	57.3	57.5	57.7	57.8	58.0
102.5°	66.9	67.7	68.5	69.0	69.2	69.4	69.6	69.8
105°	85.4	85.9	86.4	86.7	86.9	87.2	87.4	87.7
107.5°	105.4	105.6	105.8	106.0	105.9	105.9	105.9	105.9
110°	119.2	119.5	119.7	119.8	119.7	119.6	119.5	119.5



TEST NUMBER: P333257

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	133.1	133.2	133.3	133.3	133.2	133.0	132.9	132.8
115°	154.3	154.2	154.1	154.1	154.0	153.9	153.8	153.7
117.5°	175.5	175.6	175.6	175.5	175.2	174.9	174.6	174.2
120°	189.8	189.8	189.8	189.6	189.3	189.0	188.7	188.4
122.5°	203.8	203.7	203.7	203.5	203.3	203.0	202.8	202.5
125°	224.5	224.3	224.2	224.0	224.0	223.9	223.8	223.7
127.5°	245.0	244.9	244.8	244.7	244.6	244.4	244.2	244.1
130°	258.6	258.5	258.4	258.3	258.1	258.0	257.8	257.7
132.5°	271.6	271.5	271.4	271.3	271.0	270.8	270.6	270.4
135°	291.6	291.6	291.6	291.4	291.1	290.8	290.5	290.2
137.5°	311.1	311.2	311.3	311.1	310.7	310.3	309.9	309.5
140°	323.4	323.5	323.7	323.6	323.2	322.8	322.4	322.0
142.5°	335.4	335.5	335.6	335.4	335.0	334.6	334.3	333.9
145°	352.7	352.7	352.7	352.6	352.4	352.1	351.9	351.7
147.5°	368.8	369.0	369.2	369.0	368.5	367.9	367.4	366.9
150°	378.9	378.9	378.9	378.8	378.7	378.5	378.3	378.2
152.5°	388.3	388.5	388.7	388.6	388.4	388.1	387.8	387.5
155°	401.8	402.1	402.4	402.4	402.0	401.6	401.2	400.8
157.5°	413.4	413.8	414.1	414.0	413.5	412.9	412.4	411.9
160°	420.5	420.8	421.1	421.1	420.7	420.3	419.9	419.5
162.5°	427.1	427.5	427.9	427.9	427.4	426.9	426.5	426.0
165°	436.1	436.4	436.7	436.6	436.1	435.7	435.2	434.7
167.5°	442.7	443.1	443.6	443.6	443.1	442.6	442.1	441.7
170°	446.6	447.1	447.6	447.5	447.0	446.4	445.9	445.3
172.5°	449.5	449.9	450.4	450.4	449.9	449.4	448.9	448.4
175°	452.6	453.1	453.6	453.5	453.0	452.4	451.9	451.3
177.5°	454.1	454.5	454.8	454.8	454.4	453.9	453.5	453.0
180°	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2

(END OF REPORT)