

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333261

Luminaire Tested: **S125DIP-S1090D590U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333261  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D590U835-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6610.5 lumens  
Efficiency: N/A  
Efficacy: 135.5 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    ··· 90°-270°    - · 135°-315°



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	73	73	73	68
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	65	63	62	58
2	93	86	80	74	88	81	76	71	73	68	65	65	61	58	57	55	53	49
3	85	76	68	62	80	72	65	60	64	59	55	57	53	50	51	48	45	42
4	78	67	59	53	73	64	56	51	57	51	47	51	47	43	46	42	39	36
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	28
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	27	24
8	57	44	37	31	54	42	35	30	39	32	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10270	10270	10270	10270
5°	11893	10305	9022	10305
10°	13837	10251	7906	10251
15°	15317	10176	7293	10176
20°	17145	10057	6801	10057
25°	20085	9922	6560	9922
30°	21694	9790	6352	9790
35°	17837	9541	6215	9541
40°	12678	9195	6066	9195
45°	9740	8729	5980	8729
50°	8314	8151	5968	8151
55°	7402	7585	6019	7585
60°	6678	6966	6173	6966
65°	6168	6343	6333	6343
70°	5608	5697	6424	5697
75°	4951	5018	6366	5018
80°	4166	4091	5824	4091
85°	3298	2949	4698	2949



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.1	2.3
10°-20°	455.8	6.9
20°-30°	740.1	11.2
30°-40°	902.8	13.7
40°-50°	821.3	12.4
50°-60°	654.2	9.9
60°-70°	455.6	6.9
70°-80°	243.0	3.7
80°-90°	62.9	1.0
90°-100°	205.1	3.1
100°-110°	440.9	6.7
110°-120°	413.8	6.3
120°-130°	335.3	5.1
130°-140°	269.1	4.1
140°-150°	203.1	3.1
150°-160°	142.9	2.2
160°-170°	84.3	1.3
170°-180°	27.4	0.4
0°-30°	1349.0	20.4
0°-40°	2251.8	34.1
0°-60°	3727.3	56.4
0°-90°	4488.8	67.9
90°-120°	1059.7	16.0
90°-150°	1867.2	28.2
90°-180°	2122.0	32.1
0°-180°	6610.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1590	1590	1590	1590	1590	
5°	1834	1590	1392	1590	1834	185
15°	2291	1522	1091	1522	2291	656
25°	2819	1392	921	1392	2819	1287
35°	2262	1210	788	1210	2262	1385
45°	1066	956	655	956	1066	854
55°	657	674	535	674	657	592
65°	404	415	414	415	404	401
75°	198	201	255	201	198	214
85°	44	40	63	40	44	52
90°	13	1	13	1	13	11
95°	134	19	134	19	134	190
105°	756	64	756	64	756	751
115°	842	115	842	115	842	823
125°	663	160	663	160	663	600
135°	551	187	551	187	551	427
145°	435	218	435	218	435	276
155°	364	249	364	249	364	170
165°	319	272	319	272	319	91
175°	287	282	287	282	287	28
180°	283	283	283	283	283	



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1682.0	1679.8	1677.7	1673.3	1676.6	1667.4	1663.1	1655.5	1646.3	1643.1	1639.3
5°	1834.5	1837.9	1841.3	1827.1	1828.4	1819.0	1797.4	1779.8	1765.7	1747.4	1734.6
7.5°	2018.1	2010.1	2009.5	2000.3	1984.5	1971.8	1949.1	1920.2	1892.3	1860.4	1834.1
10°	2109.9	2110.6	2104.5	2093.7	2076.8	2064.7	2035.0	2006.6	1972.2	1931.7	1902.7
12.5°	2179.0	2181.8	2174.2	2159.6	2151.3	2124.1	2100.9	2067.1	2026.2	1993.8	1949.7
15°	2290.8	2283.4	2278.0	2259.7	2245.6	2217.2	2180.1	2145.0	2100.4	2059.3	2018.1
17.5°	2398.5	2404.4	2394.3	2377.7	2333.7	2300.6	2250.8	2202.8	2147.3	2092.1	2042.9
20°	2494.6	2500.0	2484.5	2455.5	2402.8	2369.8	2304.3	2242.2	2178.1	2107.2	2053.2
22.5°	2614.5	2610.2	2589.2	2545.1	2499.5	2438.3	2367.5	2291.9	2211.5	2131.5	2059.7
25°	2818.6	2790.2	2777.4	2722.8	2662.7	2572.9	2475.7	2365.0	2265.1	2159.2	2067.4
27.5°	2931.7	2922.8	2908.5	2870.4	2807.3	2711.3	2596.7	2461.8	2320.9	2187.1	2067.0
30°	2909.0	2910.4	2911.7	2899.6	2859.1	2786.9	2672.8	2527.7	2360.3	2209.8	2070.7
32.5°	2708.2	2732.7	2756.2	2784.0	2795.4	2781.5	2710.1	2579.0	2406.7	2235.7	2068.6
35°	2262.4	2269.9	2346.1	2421.7	2524.3	2604.0	2657.3	2599.2	2454.1	2257.7	2066.0
37.5°	1764.1	1800.5	1853.3	1938.7	2086.8	2219.4	2389.9	2468.3	2421.5	2264.9	2061.3
40°	1503.8	1537.5	1572.0	1659.0	1783.9	1944.5	2138.2	2303.6	2342.1	2242.2	2045.1
42.5°	1302.9	1329.7	1367.9	1433.3	1537.7	1680.0	1865.0	2081.1	2214.1	2176.3	2011.1
45°	1066.4	1083.3	1113.0	1165.0	1240.6	1351.9	1515.3	1751.5	1957.4	2025.5	1930.4
47.5°	912.8	912.7	935.8	971.7	1026.2	1120.8	1241.6	1426.7	1646.6	1809.3	1801.7
50°	827.5	824.1	842.3	873.4	916.6	979.4	1094.8	1242.6	1453.8	1638.1	1689.4
52.5°	754.1	754.5	765.7	788.6	824.8	878.4	964.6	1097.9	1278.4	1467.5	1564.1
55°	657.4	654.7	667.5	683.1	709.4	744.5	806.6	908.5	1054.9	1241.2	1366.8
57.5°	568.8	576.3	581.4	592.2	614.1	637.6	689.9	764.7	880.9	1040.8	1173.5
60°	517.0	524.4	528.5	539.3	556.8	577.1	617.6	678.3	776.2	913.9	1045.5
62.5°	470.6	476.4	477.7	487.4	501.8	521.5	553.3	604.4	681.7	802.1	931.0
65°	403.6	403.6	406.3	416.4	423.2	440.7	465.0	502.2	564.3	658.1	768.1
67.5°	339.1	342.3	341.7	346.1	352.3	366.0	383.4	414.0	460.0	528.5	616.5
70°	297.0	299.7	299.0	302.4	309.1	317.9	332.1	361.1	394.2	452.9	528.5
72.5°	259.2	260.3	258.5	263.0	267.0	274.7	290.5	306.0	336.9	386.5	448.6
75°	198.4	199.8	201.1	203.8	207.9	211.9	220.0	235.6	255.8	292.9	332.8
77.5°	148.8	146.2	149.4	149.0	151.3	154.4	161.6	169.8	186.4	209.9	240.7
80°	112.0	112.7	112.7	113.4	116.8	118.8	124.9	130.9	143.8	161.3	182.9
82.5°	81.8	83.6	82.5	83.7	86.5	88.0	91.4	96.4	103.8	117.6	133.2
85°	44.5	41.2	42.5	43.9	43.9	44.5	47.2	49.3	53.3	58.7	64.8
87.5°	15.6	16.7	17.1	17.1	17.6	17.4	19.4	19.3	20.8	22.3	24.3
90°	13.1	13.1	12.5	12.5	12.5	11.4	10.8	10.3	9.7	9.1	8.0
92.5°	36.4	37.3	38.1	39.5	46.8	55.2	73.4	101.1	148.9	183.9	186.9
95°	134.1	143.2	147.7	164.9	205.4	253.3	323.4	410.1	494.6	505.4	412.4
97.5°	324.0	331.3	347.8	379.8	415.0	481.7	550.0	610.8	625.8	539.7	368.3
100°	444.9	454.1	475.2	516.2	555.6	614.9	673.7	701.6	657.7	515.1	328.6
102.5°	580.0	586.9	609.8	639.0	681.1	721.2	749.4	732.2	638.5	471.7	298.4
105°	755.8	762.7	774.1	792.9	811.1	817.4	792.3	714.2	577.3	413.6	269.2
107.5°	849.1	853.7	857.5	857.6	848.3	818.6	754.1	649.8	514.8	373.5	256.9
110°	880.2	880.2	876.2	865.3	839.7	791.2	710.8	602.4	479.2	354.8	253.3



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	876.5	872.4	862.5	843.9	806.4	749.2	667.9	565.0	452.7	343.9	253.3
115°	842.0	834.5	818.6	791.2	746.7	684.5	606.4	517.9	423.8	332.0	255.0
117.5°	781.4	776.8	761.0	732.7	688.2	631.1	563.8	487.6	406.6	326.2	258.7
120°	742.1	737.6	722.2	694.8	652.6	602.4	539.6	471.2	397.0	323.4	262.4
122.5°	707.4	703.3	687.9	662.8	625.2	578.2	522.3	458.9	388.8	321.2	265.6
125°	663.4	657.7	645.2	621.8	589.8	548.8	499.1	440.9	377.6	318.3	271.0
127.5°	625.8	623.2	611.4	590.7	561.8	523.3	477.0	422.7	367.4	316.9	277.0
130°	605.2	601.8	590.4	571.6	543.0	506.0	461.5	411.3	360.5	316.0	280.7
132.5°	584.7	580.8	570.3	551.5	523.0	487.3	446.9	399.9	355.0	316.0	284.8
135°	551.0	547.6	537.3	518.5	493.4	460.9	424.4	385.0	348.5	316.0	290.3
137.5°	515.1	511.3	501.9	484.7	462.3	434.7	404.3	372.5	342.7	316.7	295.5
140°	490.0	487.1	478.6	463.8	442.7	418.7	392.5	365.6	340.0	317.2	297.8
142.5°	466.7	464.3	456.2	443.7	425.8	405.0	382.4	359.7	337.7	317.6	299.1
145°	434.7	432.4	426.1	416.4	402.7	387.3	369.6	352.0	334.3	317.2	300.6
147.5°	407.5	406.5	402.8	395.1	384.2	372.6	359.0	344.7	330.7	315.7	301.2
150°	392.5	391.9	389.6	382.8	374.2	363.9	353.1	340.5	328.0	314.3	301.2
152.5°	380.6	380.0	377.7	372.3	365.1	357.1	347.2	336.0	324.8	312.5	300.7
155°	364.5	363.9	362.2	358.2	352.5	346.2	338.3	329.1	319.4	309.2	299.5
157.5°	350.1	350.2	348.6	345.3	340.9	336.0	329.8	322.3	314.4	305.7	298.0
160°	340.5	341.1	340.0	337.1	333.1	329.1	323.4	317.7	310.3	303.5	296.6
162.5°	331.9	332.0	331.8	329.4	326.3	322.7	318.0	312.7	306.7	300.7	295.3
165°	319.4	319.4	319.4	318.3	316.0	313.2	309.7	305.7	301.2	296.6	293.2
167.5°	308.0	308.1	308.6	307.6	306.4	304.4	301.8	299.1	295.8	292.6	290.0
170°	301.2	301.8	301.8	301.2	300.0	298.9	297.2	295.5	292.6	290.3	288.6
172.5°	294.8	295.4	296.3	295.3	295.0	294.3	293.1	291.4	289.4	287.6	286.8
175°	286.9	287.5	288.6	288.1	288.1	288.1	286.9	286.9	285.2	284.6	284.6
177.5°	282.9	282.9	284.3	283.8	284.3	284.3	284.3	283.8	283.4	282.9	282.9
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1636.1	1632.3	1628.0	1620.4	1611.2	1606.4	1598.8	1594.0	1584.2	1576.1	1567.5
5°	1719.1	1701.6	1685.4	1664.4	1641.5	1626.6	1609.1	1589.5	1569.3	1548.3	1525.4
7.5°	1805.1	1774.0	1740.3	1704.0	1668.5	1635.8	1604.6	1574.0	1545.4	1510.8	1481.5
10°	1862.9	1823.7	1781.9	1732.6	1684.7	1642.8	1600.3	1563.2	1525.4	1484.9	1449.1
12.5°	1920.6	1868.5	1809.4	1755.3	1697.6	1647.1	1597.1	1549.7	1502.2	1457.4	1415.6
15°	1961.4	1915.5	1860.8	1783.9	1719.1	1649.6	1583.4	1522.0	1464.6	1414.7	1362.1
17.5°	1988.3	1929.1	1870.4	1796.6	1711.7	1633.9	1559.0	1488.7	1424.0	1360.7	1309.9
20°	1993.1	1932.4	1871.0	1798.7	1711.7	1622.6	1547.7	1463.3	1393.8	1328.3	1266.2
22.5°	1991.5	1922.7	1855.8	1781.5	1696.6	1614.5	1523.9	1437.9	1362.5	1298.1	1233.3
25°	1976.3	1902.7	1819.0	1744.1	1660.4	1573.3	1481.5	1392.4	1315.5	1241.9	1177.8
27.5°	1963.6	1868.1	1773.4	1686.0	1605.2	1525.4	1437.5	1346.3	1260.9	1186.4	1126.0
30°	1947.9	1843.3	1736.6	1645.5	1562.5	1484.9	1401.9	1312.8	1223.7	1150.8	1086.0
32.5°	1933.9	1812.0	1699.4	1600.2	1512.3	1436.8	1360.3	1275.5	1188.0	1114.1	1049.3
35°	1906.7	1765.7	1636.8	1524.7	1430.9	1353.3	1289.2	1210.2	1129.9	1058.3	996.2
37.5°	1872.3	1704.9	1566.6	1449.1	1346.3	1264.5	1204.8	1144.2	1067.1	998.1	942.0
40°	1845.3	1661.7	1515.3	1395.1	1288.5	1203.4	1148.1	1090.7	1026.6	962.5	903.1
42.5°	1811.3	1622.9	1463.4	1334.1	1228.5	1145.7	1087.6	1038.9	982.3	922.5	867.4
45°	1748.8	1552.4	1379.6	1240.6	1133.9	1052.2	992.2	955.7	913.2	856.5	809.9
47.5°	1656.9	1467.7	1289.0	1145.5	1035.5	959.8	903.5	868.5	838.6	796.4	754.2
50°	1575.3	1404.6	1223.7	1081.3	971.3	895.0	843.0	811.3	785.6	753.2	717.5
52.5°	1484.1	1325.2	1159.4	1018.6	909.7	834.5	783.6	755.7	734.3	711.1	675.9
55°	1339.1	1204.1	1050.2	916.6	816.0	742.4	697.9	673.6	656.1	638.5	616.9
57.5°	1179.4	1073.8	937.5	815.3	722.7	655.8	614.2	590.6	576.9	567.9	555.2
60°	1067.1	976.7	859.2	747.8	657.4	598.0	557.5	539.3	527.8	520.4	510.9
62.5°	962.9	888.6	779.8	678.2	599.1	542.9	506.8	489.1	478.1	474.5	466.7
65°	809.3	751.9	662.1	577.8	510.3	462.3	432.0	415.1	408.3	404.3	405.0
67.5°	657.9	623.0	550.9	478.9	425.1	384.9	360.6	347.6	344.2	338.8	338.7
70°	565.6	539.3	478.5	415.8	367.8	336.8	315.2	301.7	298.3	295.6	295.0
72.5°	484.1	461.0	408.3	358.0	314.9	287.7	269.8	261.7	256.2	254.6	254.5
75°	363.8	351.0	309.1	269.3	239.6	220.7	208.6	201.1	197.1	196.4	197.1
77.5°	258.6	247.4	220.8	192.6	173.9	159.6	149.3	146.7	142.1	142.3	141.6
80°	194.4	187.0	170.1	147.8	132.3	120.1	114.7	110.0	108.7	106.6	108.7
82.5°	140.9	133.0	121.5	107.3	94.5	87.2	81.8	80.3	79.5	78.6	79.0
85°	69.5	70.2	63.4	52.6	47.2	43.2	39.8	39.8	39.1	38.5	39.1
87.5°	25.2	23.9	21.7	19.8	16.9	15.0	14.3	14.7	13.2	12.9	13.6
90°	7.4	6.3	5.7	4.6	3.4	2.3	1.1	0.6	1.1	2.3	3.4
92.5°	130.2	77.9	46.8	30.1	20.3	13.2	8.4	7.0	8.4	13.2	20.3
95°	255.0	129.5	68.5	42.8	30.2	24.0	19.4	18.8	19.4	24.0	30.2
97.5°	203.5	111.6	71.2	52.7	41.4	35.1	31.9	31.3	31.9	35.1	41.4
100°	184.8	110.7	77.6	60.5	49.6	43.4	41.1	39.9	41.1	43.4	49.6
102.5°	177.1	114.8	85.3	68.7	58.8	52.0	50.2	49.5	50.2	52.0	58.8
105°	174.0	123.2	98.1	82.1	73.0	67.3	64.5	64.5	64.5	67.3	73.0
107.5°	179.2	135.8	111.5	97.1	87.6	82.9	80.2	79.1	80.2	82.9	87.6
110°	184.2	144.9	121.5	106.7	98.1	93.0	90.7	89.6	90.7	93.0	98.1





TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	190.6	153.6	131.1	116.7	108.2	103.0	101.2	100.1	101.2	103.0	108.2
115°	200.2	167.1	146.0	131.8	123.2	118.1	116.4	115.2	116.4	118.1	123.2
117.5°	211.2	181.1	161.1	147.3	137.6	132.5	130.6	128.9	130.6	132.5	137.6
120°	218.5	191.1	171.1	156.9	147.2	142.0	139.8	138.0	139.8	142.0	147.2
122.5°	226.7	200.7	180.7	166.5	155.8	150.7	148.9	147.6	148.9	150.7	155.8
125°	237.9	213.3	194.5	179.7	168.8	163.7	160.9	159.7	160.9	163.7	168.8
127.5°	248.1	225.5	207.4	192.6	181.1	174.6	170.9	169.2	170.9	174.6	181.1
130°	255.0	233.3	215.6	200.8	188.8	181.4	176.8	175.1	176.8	181.4	188.8
132.5°	260.9	240.6	222.9	208.1	195.7	187.3	181.9	179.7	181.9	187.3	195.7
135°	269.2	250.4	232.7	217.3	205.4	196.2	189.4	187.1	189.4	196.2	205.4
137.5°	275.4	257.4	241.3	225.4	213.7	204.6	198.2	196.5	198.2	204.6	213.7
140°	279.5	262.4	245.9	230.5	219.6	210.5	203.6	201.9	203.6	210.5	219.6
142.5°	281.8	265.6	250.0	235.5	225.1	216.0	209.6	208.3	209.6	216.0	225.1
145°	285.2	271.0	256.1	243.0	232.7	224.7	219.0	217.9	219.0	224.7	232.7
147.5°	287.3	274.4	261.4	249.8	240.9	233.5	228.6	227.9	228.6	233.5	240.9
150°	288.6	276.7	264.1	254.4	246.4	239.0	235.0	233.9	235.0	239.0	246.4
152.5°	289.5	278.9	267.3	258.5	251.0	244.5	240.9	240.3	240.9	244.5	251.0
155°	290.3	281.2	271.5	263.5	257.8	252.1	248.7	248.7	248.7	252.1	257.8
157.5°	290.9	283.2	274.8	268.8	263.8	258.9	256.1	256.2	256.1	258.9	263.8
160°	290.9	284.1	276.7	271.5	267.0	263.0	260.7	261.3	260.7	263.0	267.0
162.5°	290.5	285.0	278.5	274.3	270.6	267.1	264.8	265.4	264.8	267.1	270.6
165°	289.8	285.2	280.7	277.2	274.9	272.1	270.4	271.5	270.4	272.1	274.9
167.5°	288.4	285.2	281.4	279.3	277.7	276.1	275.1	275.6	275.1	276.1	277.7
170°	287.5	285.2	282.4	280.7	279.5	278.4	277.8	278.4	277.8	278.4	279.5
172.5°	286.6	284.8	282.4	281.6	280.9	279.7	279.2	280.2	279.2	279.7	280.9
175°	285.2	284.1	282.4	282.4	282.4	281.8	281.2	282.4	281.2	281.8	282.4
177.5°	283.8	283.4	282.5	282.5	282.9	282.5	282.5	283.4	282.5	282.5	282.9
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1562.6	1556.7	1551.8	1541.0	1535.1	1527.0	1520.5	1527.5	1520.0	1523.2	1518.4
5°	1513.9	1495.0	1481.5	1461.9	1445.1	1429.5	1418.1	1416.0	1410.6	1407.9	1399.8
7.5°	1455.3	1431.7	1408.5	1382.8	1361.2	1339.2	1325.2	1313.6	1305.9	1295.8	1288.9
10°	1420.8	1389.0	1362.1	1331.0	1304.0	1280.4	1261.5	1252.0	1243.3	1230.4	1225.7
12.5°	1378.1	1345.3	1312.4	1279.2	1253.2	1226.9	1210.7	1196.4	1190.3	1175.9	1174.4
15°	1327.0	1277.7	1245.3	1211.5	1175.8	1154.2	1140.7	1125.1	1118.4	1108.3	1100.8
17.5°	1265.9	1221.9	1181.4	1146.5	1115.8	1097.6	1080.9	1070.2	1058.6	1052.0	1039.8
20°	1221.7	1179.8	1139.3	1102.2	1078.6	1057.6	1044.1	1034.0	1021.9	1018.5	1006.4
22.5°	1184.4	1138.2	1099.4	1068.2	1042.4	1018.8	1004.2	997.3	988.9	978.5	976.1
25°	1123.8	1075.9	1042.8	1011.8	988.8	967.2	957.1	948.3	940.2	932.8	930.1
27.5°	1071.4	1028.6	989.3	961.3	941.3	921.6	912.7	902.0	896.1	890.1	882.8
30°	1034.7	990.8	956.4	929.4	907.8	890.3	880.8	873.4	868.0	862.6	858.5
32.5°	996.9	956.3	922.9	896.5	874.9	861.6	853.3	848.0	842.1	835.6	830.5
35°	947.0	902.4	870.0	847.1	830.2	820.1	810.6	805.9	799.1	799.1	793.7
37.5°	890.7	852.2	823.6	802.7	787.5	778.5	768.2	765.0	760.7	757.8	755.9
40°	857.2	821.4	794.4	773.5	757.3	749.9	741.8	736.4	733.7	730.3	728.9
42.5°	822.6	788.5	762.6	743.3	729.2	722.9	715.3	711.5	706.1	701.7	700.9
45°	770.1	737.0	713.4	697.9	685.7	678.3	673.6	665.5	662.8	657.4	656.7
47.5°	720.3	688.6	665.4	652.7	642.0	635.9	628.5	620.4	617.3	614.6	614.3
50°	683.1	654.0	632.4	620.3	610.2	601.4	594.0	588.6	586.5	586.5	587.9
52.5°	645.3	620.5	602.2	587.3	577.8	568.4	561.6	558.3	555.2	558.5	560.9
55°	589.9	564.9	551.4	537.3	527.8	517.0	513.6	512.3	510.3	515.7	518.4
57.5°	531.3	513.8	498.0	483.9	475.4	469.2	464.6	463.8	467.6	470.2	478.9
60°	494.1	473.8	459.6	448.8	438.7	434.7	433.3	432.0	434.7	442.1	453.6
62.5°	453.0	436.6	421.3	413.2	405.8	399.0	398.8	399.6	405.0	413.5	424.9
65°	392.8	378.6	368.5	359.1	353.0	348.9	350.3	353.0	359.1	370.5	383.4
67.5°	331.7	322.0	312.9	305.2	299.4	299.4	300.8	304.8	312.0	325.2	336.9
70°	292.3	281.5	274.0	270.7	265.9	263.2	267.3	274.0	280.1	292.3	302.4
72.5°	252.8	243.7	237.9	235.6	233.5	231.4	232.7	240.0	248.2	260.4	272.1
75°	194.4	191.0	187.0	184.3	182.2	183.6	184.9	191.7	198.4	211.3	224.8
77.5°	141.9	138.4	135.9	135.3	134.2	134.9	138.6	143.6	150.2	159.6	169.8
80°	107.3	106.0	104.6	103.9	103.9	104.6	110.0	113.4	119.5	128.2	136.3
82.5°	78.2	77.3	77.1	76.9	77.5	77.6	80.9	85.3	90.3	96.9	103.9
85°	41.2	39.8	41.8	42.5	41.2	43.2	44.5	47.2	49.3	52.6	56.0
87.5°	14.4	15.7	15.3	16.1	16.2	17.5	17.1	19.3	20.5	21.7	21.4
90°	4.6	5.7	6.3	7.4	8.0	9.1	9.7	10.3	10.8	11.4	12.5
92.5°	30.1	46.8	77.9	130.2	186.9	183.9	148.9	101.1	73.4	55.2	46.8
95°	42.8	68.5	129.5	255.0	412.4	505.4	494.6	410.1	323.4	253.3	205.4
97.5°	52.7	71.2	111.6	203.5	368.3	539.7	625.8	610.8	550.0	481.7	415.0
100°	60.5	77.6	110.7	184.8	328.6	515.1	657.7	701.6	673.7	614.9	555.6
102.5°	68.7	85.3	114.8	177.1	298.4	471.7	638.5	732.2	749.4	721.2	681.1
105°	82.1	98.1	123.2	174.0	269.2	413.6	577.3	714.2	792.3	817.4	811.1
107.5°	97.1	111.5	135.8	179.2	256.9	373.5	514.8	649.8	754.1	818.6	848.3
110°	106.7	121.5	144.9	184.2	253.3	354.8	479.2	602.4	710.8	791.2	839.7



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	116.7	131.1	153.6	190.6	253.3	343.9	452.7	565.0	667.9	749.2	806.4
115°	131.8	146.0	167.1	200.2	255.0	332.0	423.8	517.9	606.4	684.5	746.7
117.5°	147.3	161.1	181.1	211.2	258.7	326.2	406.6	487.6	563.8	631.1	688.2
120°	156.9	171.1	191.1	218.5	262.4	323.4	397.0	471.2	539.6	602.4	652.6
122.5°	166.5	180.7	200.7	226.7	265.6	321.2	388.8	458.9	522.3	578.2	625.2
125°	179.7	194.5	213.3	237.9	271.0	318.3	377.6	440.9	499.1	548.8	589.8
127.5°	192.6	207.4	225.5	248.1	277.0	316.9	367.4	422.7	477.0	523.3	561.8
130°	200.8	215.6	233.3	255.0	280.7	316.0	360.5	411.3	461.5	506.0	543.0
132.5°	208.1	222.9	240.6	260.9	284.8	316.0	355.0	399.9	446.9	487.3	523.0
135°	217.3	232.7	250.4	269.2	290.3	316.0	348.5	385.0	424.4	460.9	493.4
137.5°	225.4	241.3	257.4	275.4	295.5	316.7	342.7	372.5	404.3	434.7	462.3
140°	230.5	245.9	262.4	279.5	297.8	317.2	340.0	365.6	392.5	418.7	442.7
142.5°	235.5	250.0	265.6	281.8	299.1	317.6	337.7	359.7	382.4	405.0	425.8
145°	243.0	256.1	271.0	285.2	300.6	317.2	334.3	352.0	369.6	387.3	402.7
147.5°	249.8	261.4	274.4	287.3	301.2	315.7	330.7	344.7	359.0	372.6	384.2
150°	254.4	264.1	276.7	288.6	301.2	314.3	328.0	340.5	353.1	363.9	374.2
152.5°	258.5	267.3	278.9	289.5	300.7	312.5	324.8	336.0	347.2	357.1	365.1
155°	263.5	271.5	281.2	290.3	299.5	309.2	319.4	329.1	338.3	346.2	352.5
157.5°	268.8	274.8	283.2	290.9	298.0	305.7	314.4	322.3	329.8	336.0	340.9
160°	271.5	276.7	284.1	290.9	296.6	303.5	310.3	317.7	323.4	329.1	333.1
162.5°	274.3	278.5	285.0	290.5	295.3	300.7	306.7	312.7	318.0	322.7	326.3
165°	277.2	280.7	285.2	289.8	293.2	296.6	301.2	305.7	309.7	313.2	316.0
167.5°	279.3	281.4	285.2	288.4	290.0	292.6	295.8	299.1	301.8	304.4	306.4
170°	280.7	282.4	285.2	287.5	288.6	290.3	292.6	295.5	297.2	298.9	300.0
172.5°	281.6	282.4	284.8	286.6	286.8	287.6	289.4	291.4	293.1	294.3	295.0
175°	282.4	282.4	284.1	285.2	284.6	284.6	285.2	286.9	286.9	288.1	288.1
177.5°	282.5	282.5	283.4	283.8	282.9	282.9	283.4	283.8	284.3	284.3	284.3
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1515.1	1518.9	1515.7	1520.0	1515.7	1518.9	1515.1	1518.4	1523.2	1520.0	1527.5
5°	1396.5	1390.4	1394.4	1391.7	1394.4	1390.4	1396.5	1399.8	1407.9	1410.6	1416.0
7.5°	1286.9	1281.1	1274.4	1271.3	1274.4	1281.1	1286.9	1288.9	1295.8	1305.9	1313.6
10°	1218.3	1210.9	1210.2	1205.5	1210.2	1210.9	1218.3	1225.7	1230.4	1243.3	1252.0
12.5°	1168.1	1161.2	1153.5	1151.5	1153.5	1161.2	1168.1	1174.4	1175.9	1190.3	1196.4
15°	1096.8	1091.4	1086.7	1090.7	1086.7	1091.4	1096.8	1100.8	1108.3	1118.4	1125.1
17.5°	1037.5	1033.1	1032.3	1027.3	1032.3	1033.1	1037.5	1039.8	1052.0	1058.6	1070.2
20°	1000.3	996.9	998.3	989.5	998.3	996.9	1000.3	1006.4	1018.5	1021.9	1034.0
22.5°	970.6	964.0	963.2	961.4	963.2	964.0	970.6	976.1	978.5	988.9	997.3
25°	924.0	920.6	917.3	920.6	917.3	920.6	924.0	930.1	932.8	940.2	948.3
27.5°	883.4	879.3	878.4	878.8	878.4	879.3	883.4	882.8	890.1	896.1	902.0
30°	858.5	851.8	852.5	851.8	852.5	851.8	858.5	858.5	862.6	868.0	873.4
32.5°	831.5	826.9	826.0	824.8	826.0	826.9	831.5	830.5	835.6	842.1	848.0
35°	791.7	791.7	788.3	788.3	788.3	791.7	791.7	793.7	799.1	799.1	805.9
37.5°	754.3	753.6	751.6	751.9	751.6	753.6	754.3	755.9	757.8	760.7	765.0
40°	726.2	725.6	723.5	719.5	723.5	725.6	726.2	728.9	730.3	733.7	736.4
42.5°	699.2	697.0	696.0	694.7	696.0	697.0	699.2	700.9	701.7	706.1	711.5
45°	656.7	656.7	655.4	654.7	655.4	656.7	656.7	656.7	657.4	662.8	665.5
47.5°	615.4	616.6	619.2	618.8	619.2	616.6	615.4	614.3	614.6	617.3	620.4
50°	590.6	591.3	593.3	594.0	593.3	591.3	590.6	587.9	586.5	586.5	588.6
52.5°	563.0	567.0	569.5	569.1	569.5	567.0	563.0	560.9	558.5	555.2	558.3
55°	524.4	529.2	533.9	534.6	533.9	529.2	524.4	518.4	515.7	510.3	512.3
57.5°	486.2	492.8	497.8	499.5	497.8	492.8	486.2	478.9	470.2	467.6	463.8
60°	460.3	469.1	475.2	477.9	475.2	469.1	460.3	453.6	442.1	434.7	432.0
62.5°	435.5	445.3	451.4	451.9	451.4	445.3	435.5	424.9	413.5	405.0	399.6
65°	394.8	405.0	410.4	414.4	410.4	405.0	394.8	383.4	370.5	359.1	353.0
67.5°	351.1	361.2	367.2	370.4	367.2	361.2	351.1	336.9	325.2	312.0	304.8
70°	319.3	329.4	337.5	340.2	337.5	329.4	319.3	302.4	292.3	280.1	274.0
72.5°	287.9	297.0	303.5	306.7	303.5	297.0	287.9	272.1	260.4	248.2	240.0
75°	233.5	245.7	251.8	255.1	251.8	245.7	233.5	224.8	211.3	198.4	191.7
77.5°	180.1	191.1	194.8	196.5	194.8	191.1	180.1	169.8	159.6	150.2	143.6
80°	144.4	151.2	155.9	156.6	155.9	151.2	144.4	136.3	128.2	119.5	113.4
82.5°	111.0	116.6	118.1	119.9	118.1	116.6	111.0	103.9	96.9	90.3	85.3
85°	60.7	63.4	64.1	63.4	64.1	63.4	60.7	56.0	52.6	49.3	47.2
87.5°	22.5	21.9	22.1	23.1	22.1	21.9	22.5	21.4	21.7	20.5	19.3
90°	12.5	12.5	13.1	13.1	13.1	12.5	12.5	12.5	11.4	10.8	10.3
92.5°	39.5	38.1	37.3	36.4	37.3	38.1	39.5	46.8	55.2	73.4	101.1
95°	164.9	147.7	143.2	134.1	143.2	147.7	164.9	205.4	253.3	323.4	410.1
97.5°	379.8	347.8	331.3	324.0	331.3	347.8	379.8	415.0	481.7	550.0	610.8
100°	516.2	475.2	454.1	444.9	454.1	475.2	516.2	555.6	614.9	673.7	701.6
102.5°	639.0	609.8	586.9	580.0	586.9	609.8	639.0	681.1	721.2	749.4	732.2
105°	792.9	774.1	762.7	755.8	762.7	774.1	792.9	811.1	817.4	792.3	714.2
107.5°	857.6	857.5	853.7	849.1	853.7	857.5	857.6	848.3	818.6	754.1	649.8
110°	865.3	876.2	880.2	880.2	880.2	876.2	865.3	839.7	791.2	710.8	602.4



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	843.9	862.5	872.4	876.5	872.4	862.5	843.9	806.4	749.2	667.9	565.0
115°	791.2	818.6	834.5	842.0	834.5	818.6	791.2	746.7	684.5	606.4	517.9
117.5°	732.7	761.0	776.8	781.4	776.8	761.0	732.7	688.2	631.1	563.8	487.6
120°	694.8	722.2	737.6	742.1	737.6	722.2	694.8	652.6	602.4	539.6	471.2
122.5°	662.8	687.9	703.3	707.4	703.3	687.9	662.8	625.2	578.2	522.3	458.9
125°	621.8	645.2	657.7	663.4	657.7	645.2	621.8	589.8	548.8	499.1	440.9
127.5°	590.7	611.4	623.2	625.8	623.2	611.4	590.7	561.8	523.3	477.0	422.7
130°	571.6	590.4	601.8	605.2	601.8	590.4	571.6	543.0	506.0	461.5	411.3
132.5°	551.5	570.3	580.8	584.7	580.8	570.3	551.5	523.0	487.3	446.9	399.9
135°	518.5	537.3	547.6	551.0	547.6	537.3	518.5	493.4	460.9	424.4	385.0
137.5°	484.7	501.9	511.3	515.1	511.3	501.9	484.7	462.3	434.7	404.3	372.5
140°	463.8	478.6	487.1	490.0	487.1	478.6	463.8	442.7	418.7	392.5	365.6
142.5°	443.7	456.2	464.3	466.7	464.3	456.2	443.7	425.8	405.0	382.4	359.7
145°	416.4	426.1	432.4	434.7	432.4	426.1	416.4	402.7	387.3	369.6	352.0
147.5°	395.1	402.8	406.5	407.5	406.5	402.8	395.1	384.2	372.6	359.0	344.7
150°	382.8	389.6	391.9	392.5	391.9	389.6	382.8	374.2	363.9	353.1	340.5
152.5°	372.3	377.7	380.0	380.6	380.0	377.7	372.3	365.1	357.1	347.2	336.0
155°	358.2	362.2	363.9	364.5	363.9	362.2	358.2	352.5	346.2	338.3	329.1
157.5°	345.3	348.6	350.2	350.1	350.2	348.6	345.3	340.9	336.0	329.8	322.3
160°	337.1	340.0	341.1	340.5	341.1	340.0	337.1	333.1	329.1	323.4	317.7
162.5°	329.4	331.8	332.0	331.9	332.0	331.8	329.4	326.3	322.7	318.0	312.7
165°	318.3	319.4	319.4	319.4	319.4	319.4	318.3	316.0	313.2	309.7	305.7
167.5°	307.6	308.6	308.1	308.0	308.1	308.6	307.6	306.4	304.4	301.8	299.1
170°	301.2	301.8	301.8	301.2	301.8	301.8	301.2	300.0	298.9	297.2	295.5
172.5°	295.3	296.3	295.4	294.8	295.4	296.3	295.3	295.0	294.3	293.1	291.4
175°	288.1	288.6	287.5	286.9	287.5	288.6	288.1	288.1	288.1	286.9	286.9
177.5°	283.8	284.3	282.9	282.9	282.9	284.3	283.8	284.3	284.3	284.3	283.8
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1520.5	1527.0	1535.1	1541.0	1551.8	1556.7	1562.6	1567.5	1576.1	1584.2	1594.0
5°	1418.1	1429.5	1445.1	1461.9	1481.5	1495.0	1513.9	1525.4	1548.3	1569.3	1589.5
7.5°	1325.2	1339.2	1361.2	1382.8	1408.5	1431.7	1455.3	1481.5	1510.8	1545.4	1574.0
10°	1261.5	1280.4	1304.0	1331.0	1362.1	1389.0	1420.8	1449.1	1484.9	1525.4	1563.2
12.5°	1210.7	1226.9	1253.2	1279.2	1312.4	1345.3	1378.1	1415.6	1457.4	1502.2	1549.7
15°	1140.7	1154.2	1175.8	1211.5	1245.3	1277.7	1327.0	1362.1	1414.7	1464.6	1522.0
17.5°	1080.9	1097.6	1115.8	1146.5	1181.4	1221.9	1265.9	1309.9	1360.7	1424.0	1488.7
20°	1044.1	1057.6	1078.6	1102.2	1139.3	1179.8	1221.7	1266.2	1328.3	1393.8	1463.3
22.5°	1004.2	1018.8	1042.4	1068.2	1099.4	1138.2	1184.4	1233.3	1298.1	1362.5	1437.9
25°	957.1	967.2	988.8	1011.8	1042.8	1075.9	1123.8	1177.8	1241.9	1315.5	1392.4
27.5°	912.7	921.6	941.3	961.3	989.3	1028.6	1071.4	1126.0	1186.4	1260.9	1346.3
30°	880.8	890.3	907.8	929.4	956.4	990.8	1034.7	1086.0	1150.8	1223.7	1312.8
32.5°	853.3	861.6	874.9	896.5	922.9	956.3	996.9	1049.3	1114.1	1188.0	1275.5
35°	810.6	820.1	830.2	847.1	870.0	902.4	947.0	996.2	1058.3	1129.9	1210.2
37.5°	768.2	778.5	787.5	802.7	823.6	852.2	890.7	942.0	998.1	1067.1	1144.2
40°	741.8	749.9	757.3	773.5	794.4	821.4	857.2	903.1	962.5	1026.6	1090.7
42.5°	715.3	722.9	729.2	743.3	762.6	788.5	822.6	867.4	922.5	982.3	1038.9
45°	673.6	678.3	685.7	697.9	713.4	737.0	770.1	809.9	856.5	913.2	955.7
47.5°	628.5	635.9	642.0	652.7	665.4	688.6	720.3	754.2	796.4	838.6	868.5
50°	594.0	601.4	610.2	620.3	632.4	654.0	683.1	717.5	753.2	785.6	811.3
52.5°	561.6	568.4	577.8	587.3	602.2	620.5	645.3	675.9	711.1	734.3	755.7
55°	513.6	517.0	527.8	537.3	551.4	564.9	589.9	616.9	638.5	656.1	673.6
57.5°	464.6	469.2	475.4	483.9	498.0	513.8	531.3	555.2	567.9	576.9	590.6
60°	433.3	434.7	438.7	448.8	459.6	473.8	494.1	510.9	520.4	527.8	539.3
62.5°	398.8	399.0	405.8	413.2	421.3	436.6	453.0	466.7	474.5	478.1	489.1
65°	350.3	348.9	353.0	359.1	368.5	378.6	392.8	405.0	404.3	408.3	415.1
67.5°	300.8	299.4	299.4	305.2	312.9	322.0	331.7	338.7	338.8	344.2	347.6
70°	267.3	263.2	265.9	270.7	274.0	281.5	292.3	295.0	295.6	298.3	301.7
72.5°	232.7	231.4	233.5	235.6	237.9	243.7	252.8	254.5	254.6	256.2	261.7
75°	184.9	183.6	182.2	184.3	187.0	191.0	194.4	197.1	196.4	197.1	201.1
77.5°	138.6	134.9	134.2	135.3	135.9	138.4	141.9	141.6	142.3	142.1	146.7
80°	110.0	104.6	103.9	103.9	104.6	106.0	107.3	108.7	106.6	108.7	110.0
82.5°	80.9	77.6	77.5	76.9	77.1	77.3	78.2	79.0	78.6	79.5	80.3
85°	44.5	43.2	41.2	42.5	41.8	39.8	41.2	39.1	38.5	39.1	39.8
87.5°	17.1	17.5	16.2	16.1	15.3	15.7	14.4	13.6	12.9	13.2	14.7
90°	9.7	9.1	8.0	7.4	6.3	5.7	4.6	3.4	2.3	1.1	0.6
92.5°	148.9	183.9	186.9	130.2	77.9	46.8	30.1	20.3	13.2	8.4	7.0
95°	494.6	505.4	412.4	255.0	129.5	68.5	42.8	30.2	24.0	19.4	18.8
97.5°	625.8	539.7	368.3	203.5	111.6	71.2	52.7	41.4	35.1	31.9	31.3
100°	657.7	515.1	328.6	184.8	110.7	77.6	60.5	49.6	43.4	41.1	39.9
102.5°	638.5	471.7	298.4	177.1	114.8	85.3	68.7	58.8	52.0	50.2	49.5
105°	577.3	413.6	269.2	174.0	123.2	98.1	82.1	73.0	67.3	64.5	64.5
107.5°	514.8	373.5	256.9	179.2	135.8	111.5	97.1	87.6	82.9	80.2	79.1
110°	479.2	354.8	253.3	184.2	144.9	121.5	106.7	98.1	93.0	90.7	89.6



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	452.7	343.9	253.3	190.6	153.6	131.1	116.7	108.2	103.0	101.2	100.1
115°	423.8	332.0	255.0	200.2	167.1	146.0	131.8	123.2	118.1	116.4	115.2
117.5°	406.6	326.2	258.7	211.2	181.1	161.1	147.3	137.6	132.5	130.6	128.9
120°	397.0	323.4	262.4	218.5	191.1	171.1	156.9	147.2	142.0	139.8	138.0
122.5°	388.8	321.2	265.6	226.7	200.7	180.7	166.5	155.8	150.7	148.9	147.6
125°	377.6	318.3	271.0	237.9	213.3	194.5	179.7	168.8	163.7	160.9	159.7
127.5°	367.4	316.9	277.0	248.1	225.5	207.4	192.6	181.1	174.6	170.9	169.2
130°	360.5	316.0	280.7	255.0	233.3	215.6	200.8	188.8	181.4	176.8	175.1
132.5°	355.0	316.0	284.8	260.9	240.6	222.9	208.1	195.7	187.3	181.9	179.7
135°	348.5	316.0	290.3	269.2	250.4	232.7	217.3	205.4	196.2	189.4	187.1
137.5°	342.7	316.7	295.5	275.4	257.4	241.3	225.4	213.7	204.6	198.2	196.5
140°	340.0	317.2	297.8	279.5	262.4	245.9	230.5	219.6	210.5	203.6	201.9
142.5°	337.7	317.6	299.1	281.8	265.6	250.0	235.5	225.1	216.0	209.6	208.3
145°	334.3	317.2	300.6	285.2	271.0	256.1	243.0	232.7	224.7	219.0	217.9
147.5°	330.7	315.7	301.2	287.3	274.4	261.4	249.8	240.9	233.5	228.6	227.9
150°	328.0	314.3	301.2	288.6	276.7	264.1	254.4	246.4	239.0	235.0	233.9
152.5°	324.8	312.5	300.7	289.5	278.9	267.3	258.5	251.0	244.5	240.9	240.3
155°	319.4	309.2	299.5	290.3	281.2	271.5	263.5	257.8	252.1	248.7	248.7
157.5°	314.4	305.7	298.0	290.9	283.2	274.8	268.8	263.8	258.9	256.1	256.2
160°	310.3	303.5	296.6	290.9	284.1	276.7	271.5	267.0	263.0	260.7	261.3
162.5°	306.7	300.7	295.3	290.5	285.0	278.5	274.3	270.6	267.1	264.8	265.4
165°	301.2	296.6	293.2	289.8	285.2	280.7	277.2	274.9	272.1	270.4	271.5
167.5°	295.8	292.6	290.0	288.4	285.2	281.4	279.3	277.7	276.1	275.1	275.6
170°	292.6	290.3	288.6	287.5	285.2	282.4	280.7	279.5	278.4	277.8	278.4
172.5°	289.4	287.6	286.8	286.6	284.8	282.4	281.6	280.9	279.7	279.2	280.2
175°	285.2	284.6	284.6	285.2	284.1	282.4	282.4	282.4	281.8	281.2	282.4
177.5°	283.4	282.9	282.9	283.8	283.4	282.5	282.5	282.9	282.5	282.5	283.4
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1598.8	1606.4	1611.2	1620.4	1628.0	1632.3	1636.1	1639.3	1643.1	1646.3	1655.5
5°	1609.1	1626.6	1641.5	1664.4	1685.4	1701.6	1719.1	1734.6	1747.4	1765.7	1779.8
7.5°	1604.6	1635.8	1668.5	1704.0	1740.3	1774.0	1805.1	1834.1	1860.4	1892.3	1920.2
10°	1600.3	1642.8	1684.7	1732.6	1781.9	1823.7	1862.9	1902.7	1931.7	1972.2	2006.6
12.5°	1597.1	1647.1	1697.6	1755.3	1809.4	1868.5	1920.6	1949.7	1993.8	2026.2	2067.1
15°	1583.4	1649.6	1719.1	1783.9	1860.8	1915.5	1961.4	2018.1	2059.3	2100.4	2145.0
17.5°	1559.0	1633.9	1711.7	1796.6	1870.4	1929.1	1988.3	2042.9	2092.1	2147.3	2202.8
20°	1547.7	1622.6	1711.7	1798.7	1871.0	1932.4	1993.1	2053.2	2107.2	2178.1	2242.2
22.5°	1523.9	1614.5	1696.6	1781.5	1855.8	1922.7	1991.5	2059.7	2131.5	2211.5	2291.9
25°	1481.5	1573.3	1660.4	1744.1	1819.0	1902.7	1976.3	2067.4	2159.2	2265.1	2365.0
27.5°	1437.5	1525.4	1605.2	1686.0	1773.4	1868.1	1963.6	2067.0	2187.1	2320.9	2461.8
30°	1401.9	1484.9	1562.5	1645.5	1736.6	1843.3	1947.9	2070.7	2209.8	2360.3	2527.7
32.5°	1360.3	1436.8	1512.3	1600.2	1699.4	1812.0	1933.9	2068.6	2235.7	2406.7	2579.0
35°	1289.2	1353.3	1430.9	1524.7	1636.8	1765.7	1906.7	2066.0	2257.7	2454.1	2599.2
37.5°	1204.8	1264.5	1346.3	1449.1	1566.6	1704.9	1872.3	2061.3	2264.9	2421.5	2468.3
40°	1148.1	1203.4	1288.5	1395.1	1515.3	1661.7	1845.3	2045.1	2242.2	2342.1	2303.6
42.5°	1087.6	1145.7	1228.5	1334.1	1463.4	1622.9	1811.3	2011.1	2176.3	2214.1	2081.1
45°	992.2	1052.2	1133.9	1240.6	1379.6	1552.4	1748.8	1930.4	2025.5	1957.4	1751.5
47.5°	903.5	959.8	1035.5	1145.5	1289.0	1467.7	1656.9	1801.7	1809.3	1646.6	1426.7
50°	843.0	895.0	971.3	1081.3	1223.7	1404.6	1575.3	1689.4	1638.1	1453.8	1242.6
52.5°	783.6	834.5	909.7	1018.6	1159.4	1325.2	1484.1	1564.1	1467.5	1278.4	1097.9
55°	697.9	742.4	816.0	916.6	1050.2	1204.1	1339.1	1366.8	1241.2	1054.9	908.5
57.5°	614.2	655.8	722.7	815.3	937.5	1073.8	1179.4	1173.5	1040.8	880.9	764.7
60°	557.5	598.0	657.4	747.8	859.2	976.7	1067.1	1045.5	913.9	776.2	678.3
62.5°	506.8	542.9	599.1	678.2	779.8	888.6	962.9	931.0	802.1	681.7	604.4
65°	432.0	462.3	510.3	577.8	662.1	751.9	809.3	768.1	658.1	564.3	502.2
67.5°	360.6	384.9	425.1	478.9	550.9	623.0	657.9	616.5	528.5	460.0	414.0
70°	315.2	336.8	367.8	415.8	478.5	539.3	565.6	528.5	452.9	394.2	361.1
72.5°	269.8	287.7	314.9	358.0	408.3	461.0	484.1	448.6	386.5	336.9	306.0
75°	208.6	220.7	239.6	269.3	309.1	351.0	363.8	332.8	292.9	255.8	235.6
77.5°	149.3	159.6	173.9	192.6	220.8	247.4	258.6	240.7	209.9	186.4	169.8
80°	114.7	120.1	132.3	147.8	170.1	187.0	194.4	182.9	161.3	143.8	130.9
82.5°	81.8	87.2	94.5	107.3	121.5	133.0	140.9	133.2	117.6	103.8	96.4
85°	39.8	43.2	47.2	52.6	63.4	70.2	69.5	64.8	58.7	53.3	49.3
87.5°	14.3	15.0	16.9	19.8	21.7	23.9	25.2	24.3	22.3	20.8	19.3
90°	1.1	2.3	3.4	4.6	5.7	6.3	7.4	8.0	9.1	9.7	10.3
92.5°	8.4	13.2	20.3	30.1	46.8	77.9	130.2	186.9	183.9	148.9	101.1
95°	19.4	24.0	30.2	42.8	68.5	129.5	255.0	412.4	505.4	494.6	410.1
97.5°	31.9	35.1	41.4	52.7	71.2	111.6	203.5	368.3	539.7	625.8	610.8
100°	41.1	43.4	49.6	60.5	77.6	110.7	184.8	328.6	515.1	657.7	701.6
102.5°	50.2	52.0	58.8	68.7	85.3	114.8	177.1	298.4	471.7	638.5	732.2
105°	64.5	67.3	73.0	82.1	98.1	123.2	174.0	269.2	413.6	577.3	714.2
107.5°	80.2	82.9	87.6	97.1	111.5	135.8	179.2	256.9	373.5	514.8	649.8
110°	90.7	93.0	98.1	106.7	121.5	144.9	184.2	253.3	354.8	479.2	602.4





TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	101.2	103.0	108.2	116.7	131.1	153.6	190.6	253.3	343.9	452.7	565.0
115°	116.4	118.1	123.2	131.8	146.0	167.1	200.2	255.0	332.0	423.8	517.9
117.5°	130.6	132.5	137.6	147.3	161.1	181.1	211.2	258.7	326.2	406.6	487.6
120°	139.8	142.0	147.2	156.9	171.1	191.1	218.5	262.4	323.4	397.0	471.2
122.5°	148.9	150.7	155.8	166.5	180.7	200.7	226.7	265.6	321.2	388.8	458.9
125°	160.9	163.7	168.8	179.7	194.5	213.3	237.9	271.0	318.3	377.6	440.9
127.5°	170.9	174.6	181.1	192.6	207.4	225.5	248.1	277.0	316.9	367.4	422.7
130°	176.8	181.4	188.8	200.8	215.6	233.3	255.0	280.7	316.0	360.5	411.3
132.5°	181.9	187.3	195.7	208.1	222.9	240.6	260.9	284.8	316.0	355.0	399.9
135°	189.4	196.2	205.4	217.3	232.7	250.4	269.2	290.3	316.0	348.5	385.0
137.5°	198.2	204.6	213.7	225.4	241.3	257.4	275.4	295.5	316.7	342.7	372.5
140°	203.6	210.5	219.6	230.5	245.9	262.4	279.5	297.8	317.2	340.0	365.6
142.5°	209.6	216.0	225.1	235.5	250.0	265.6	281.8	299.1	317.6	337.7	359.7
145°	219.0	224.7	232.7	243.0	256.1	271.0	285.2	300.6	317.2	334.3	352.0
147.5°	228.6	233.5	240.9	249.8	261.4	274.4	287.3	301.2	315.7	330.7	344.7
150°	235.0	239.0	246.4	254.4	264.1	276.7	288.6	301.2	314.3	328.0	340.5
152.5°	240.9	244.5	251.0	258.5	267.3	278.9	289.5	300.7	312.5	324.8	336.0
155°	248.7	252.1	257.8	263.5	271.5	281.2	290.3	299.5	309.2	319.4	329.1
157.5°	256.1	258.9	263.8	268.8	274.8	283.2	290.9	298.0	305.7	314.4	322.3
160°	260.7	263.0	267.0	271.5	276.7	284.1	290.9	296.6	303.5	310.3	317.7
162.5°	264.8	267.1	270.6	274.3	278.5	285.0	290.5	295.3	300.7	306.7	312.7
165°	270.4	272.1	274.9	277.2	280.7	285.2	289.8	293.2	296.6	301.2	305.7
167.5°	275.1	276.1	277.7	279.3	281.4	285.2	288.4	290.0	292.6	295.8	299.1
170°	277.8	278.4	279.5	280.7	282.4	285.2	287.5	288.6	290.3	292.6	295.5
172.5°	279.2	279.7	280.9	281.6	282.4	284.8	286.6	286.8	287.6	289.4	291.4
175°	281.2	281.8	282.4	282.4	282.4	284.1	285.2	284.6	284.6	285.2	286.9
177.5°	282.5	282.5	282.9	282.5	282.5	283.4	283.8	282.9	282.9	283.4	283.8
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1663.1	1667.4	1676.6	1673.3	1677.7	1679.8	1682.0
5°	1797.4	1819.0	1828.4	1827.1	1841.3	1837.9	1834.5
7.5°	1949.1	1971.8	1984.5	2000.3	2009.5	2010.1	2018.1
10°	2035.0	2064.7	2076.8	2093.7	2104.5	2110.6	2109.9
12.5°	2100.9	2124.1	2151.3	2159.6	2174.2	2181.8	2179.0
15°	2180.1	2217.2	2245.6	2259.7	2278.0	2283.4	2290.8
17.5°	2250.8	2300.6	2333.7	2377.7	2394.3	2404.4	2398.5
20°	2304.3	2369.8	2402.8	2455.5	2484.5	2500.0	2494.6
22.5°	2367.5	2438.3	2499.5	2545.1	2589.2	2610.2	2614.5
25°	2475.7	2572.9	2662.7	2722.8	2777.4	2790.2	2818.6
27.5°	2596.7	2711.3	2807.3	2870.4	2908.5	2922.8	2931.7
30°	2672.8	2786.9	2859.1	2899.6	2911.7	2910.4	2909.0
32.5°	2710.1	2781.5	2795.4	2784.0	2756.2	2732.7	2708.2
35°	2657.3	2604.0	2524.3	2421.7	2346.1	2269.9	2262.4
37.5°	2389.9	2219.4	2086.8	1938.7	1853.3	1800.5	1764.1
40°	2138.2	1944.5	1783.9	1659.0	1572.0	1537.5	1503.8
42.5°	1865.0	1680.0	1537.7	1433.3	1367.9	1329.7	1302.9
45°	1515.3	1351.9	1240.6	1165.0	1113.0	1083.3	1066.4
47.5°	1241.6	1120.8	1026.2	971.7	935.8	912.7	912.8
50°	1094.8	979.4	916.6	873.4	842.3	824.1	827.5
52.5°	964.6	878.4	824.8	788.6	765.7	754.5	754.1
55°	806.6	744.5	709.4	683.1	667.5	654.7	657.4
57.5°	689.9	637.6	614.1	592.2	581.4	576.3	568.8
60°	617.6	577.1	556.8	539.3	528.5	524.4	517.0
62.5°	553.3	521.5	501.8	487.4	477.7	476.4	470.6
65°	465.0	440.7	423.2	416.4	406.3	403.6	403.6
67.5°	383.4	366.0	352.3	346.1	341.7	342.3	339.1
70°	332.1	317.9	309.1	302.4	299.0	299.7	297.0
72.5°	290.5	274.7	267.0	263.0	258.5	260.3	259.2
75°	220.0	211.9	207.9	203.8	201.1	199.8	198.4
77.5°	161.6	154.4	151.3	149.0	149.4	146.2	148.8
80°	124.9	118.8	116.8	113.4	112.7	112.7	112.0
82.5°	91.4	88.0	86.5	83.7	82.5	83.6	81.8
85°	47.2	44.5	43.9	43.9	42.5	41.2	44.5
87.5°	19.4	17.4	17.6	17.1	17.1	16.7	15.6
90°	10.8	11.4	12.5	12.5	12.5	13.1	13.1
92.5°	73.4	55.2	46.8	39.5	38.1	37.3	36.4
95°	323.4	253.3	205.4	164.9	147.7	143.2	134.1
97.5°	550.0	481.7	415.0	379.8	347.8	331.3	324.0
100°	673.7	614.9	555.6	516.2	475.2	454.1	444.9
102.5°	749.4	721.2	681.1	639.0	609.8	586.9	580.0
105°	792.3	817.4	811.1	792.9	774.1	762.7	755.8
107.5°	754.1	818.6	848.3	857.6	857.5	853.7	849.1
110°	710.8	791.2	839.7	865.3	876.2	880.2	880.2



TEST NUMBER: P333261

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	667.9	749.2	806.4	843.9	862.5	872.4	876.5
115°	606.4	684.5	746.7	791.2	818.6	834.5	842.0
117.5°	563.8	631.1	688.2	732.7	761.0	776.8	781.4
120°	539.6	602.4	652.6	694.8	722.2	737.6	742.1
122.5°	522.3	578.2	625.2	662.8	687.9	703.3	707.4
125°	499.1	548.8	589.8	621.8	645.2	657.7	663.4
127.5°	477.0	523.3	561.8	590.7	611.4	623.2	625.8
130°	461.5	506.0	543.0	571.6	590.4	601.8	605.2
132.5°	446.9	487.3	523.0	551.5	570.3	580.8	584.7
135°	424.4	460.9	493.4	518.5	537.3	547.6	551.0
137.5°	404.3	434.7	462.3	484.7	501.9	511.3	515.1
140°	392.5	418.7	442.7	463.8	478.6	487.1	490.0
142.5°	382.4	405.0	425.8	443.7	456.2	464.3	466.7
145°	369.6	387.3	402.7	416.4	426.1	432.4	434.7
147.5°	359.0	372.6	384.2	395.1	402.8	406.5	407.5
150°	353.1	363.9	374.2	382.8	389.6	391.9	392.5
152.5°	347.2	357.1	365.1	372.3	377.7	380.0	380.6
155°	338.3	346.2	352.5	358.2	362.2	363.9	364.5
157.5°	329.8	336.0	340.9	345.3	348.6	350.2	350.1
160°	323.4	329.1	333.1	337.1	340.0	341.1	340.5
162.5°	318.0	322.7	326.3	329.4	331.8	332.0	331.9
165°	309.7	313.2	316.0	318.3	319.4	319.4	319.4
167.5°	301.8	304.4	306.4	307.6	308.6	308.1	308.0
170°	297.2	298.9	300.0	301.2	301.8	301.8	301.2
172.5°	293.1	294.3	295.0	295.3	296.3	295.4	294.8
175°	286.9	288.1	288.1	288.1	288.6	287.5	286.9
177.5°	284.3	284.3	284.3	283.8	284.3	282.9	282.9
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9

(END OF REPORT)