

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333274-940

Luminaire Tested: **S125DIP-S1090D810U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333274-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D810U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6850.2 lumens
Efficiency: N/A
Efficacy: 125.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333274-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333274-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	99	95	91	88	93	89	85	82	77	74	72	66	64	62	56	55	53	49
2	91	83	77	71	84	78	72	67	67	63	60	58	55	52	49	47	45	41
3	83	73	65	59	77	68	62	56	59	54	50	51	47	44	43	41	38	34
4	76	65	57	50	70	60	53	48	53	47	43	46	41	38	39	36	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29	26
6	64	52	43	38	59	49	41	36	43	37	32	37	32	29	32	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9827	9827	9827
5°	9849	9756	9818
10°	9789	9686	9742
15°	9682	9570	9610
20°	9531	9407	9423
25°	9368	9213	9204
30°	9165	9004	8959
35°	8949	8779	8656
40°	8728	8535	8413
45°	8488	8312	8147
50°	8225	8043	7801
55°	7970	7739	7523
60°	7665	7432	7167
65°	7303	7065	6825
70°	6956	6637	6411
75°	6338	6128	5916
80°	5642	5553	5415
85°	4905	4994	4728



TEST NUMBER: P333274-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.5	2.1
10°-20°	405.3	5.9
20°-30°	598.4	8.7
30°-40°	698.2	10.2
40°-50°	701.3	10.2
50°-60°	615.6	9.0
60°-70°	458.7	6.7
70°-80°	262.3	3.8
80°-90°	78.3	1.1
90°-100°	34.2	0.5
100°-110°	210.7	3.1
110°-120°	382.1	5.6
120°-130°	490.4	7.2
130°-140°	527.5	7.7
140°-150°	495.1	7.2
150°-160°	400.5	5.8
160°-170°	259.0	3.8
170°-180°	89.3	1.3
0°-30°	1147.1	16.7
0°-40°	1845.3	26.9
0°-60°	3162.2	46.2
0°-90°	3961.3	57.8
90°-120°	627.0	9.2
90°-150°	2140.0	31.2
90°-180°	2889.0	42.2
0°-180°	6850.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1522	1522	1522	1522	1522	
5°	1519	1516	1505	1515	1514	144
15°	1448	1444	1431	1437	1437	408
25°	1315	1308	1293	1295	1292	605
35°	1135	1130	1114	1107	1098	710
45°	929	924	910	896	892	716
55°	708	703	687	677	668	632
65°	478	475	462	452	447	474
75°	254	251	246	242	237	271
85°	66	67	67	66	64	74
90°	1	6	11	15	17	5
95°	40	36	11	14	15	51
105°	205	208	208	208	207	217
115°	385	388	389	386	382	381
125°	547	552	552	550	547	489
135°	683	687	686	684	680	526
145°	792	793	793	793	789	495
155°	872	868	869	871	865	401
165°	920	916	916	920	915	260
175°	941	937	937	942	937	90
180°	941	941	941	941	941	



TEST NUMBER: P333274-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
2.5°	1525.4	1524.8	1524.1	1523.5	1522.9	1521.4	1519.3	1517.2	1515.0	1512.9	1515.0
5°	1519.2	1518.7	1518.1	1517.6	1517.1	1515.5	1512.8	1510.1	1507.4	1504.8	1507.2
7.5°	1505.2	1504.7	1504.1	1503.6	1503.1	1501.3	1498.3	1495.4	1492.5	1489.5	1491.9
10°	1492.7	1492.2	1491.7	1491.1	1490.6	1488.8	1485.9	1482.9	1480.0	1477.0	1479.2
12.5°	1477.3	1476.3	1475.3	1474.4	1473.5	1471.6	1468.8	1466.2	1463.4	1460.6	1462.4
15°	1448.1	1447.3	1446.5	1445.7	1444.9	1443.1	1440.1	1437.2	1434.2	1431.3	1432.6
17.5°	1414.7	1413.5	1412.3	1411.1	1410.0	1407.8	1404.8	1401.8	1398.7	1395.6	1397.3
20°	1386.8	1386.3	1385.7	1385.2	1384.6	1382.6	1379.1	1375.6	1372.2	1368.7	1370.6
22.5°	1358.8	1357.9	1356.9	1355.9	1355.0	1352.8	1349.6	1346.3	1343.1	1339.8	1341.0
25°	1314.6	1313.2	1311.9	1310.5	1309.2	1306.8	1303.3	1299.8	1296.4	1292.9	1293.4
27.5°	1262.8	1261.9	1261.1	1260.3	1259.5	1257.4	1253.7	1250.2	1246.6	1243.0	1243.1
30°	1229.0	1228.2	1227.4	1226.6	1225.8	1223.4	1219.4	1215.4	1211.4	1207.4	1206.8
32.5°	1192.5	1191.2	1190.0	1188.7	1187.6	1185.2	1181.5	1177.9	1174.4	1170.8	1169.8
35°	1135.1	1134.1	1133.0	1131.9	1130.9	1128.5	1124.7	1121.0	1117.2	1113.5	1112.1
37.5°	1075.7	1074.3	1073.0	1071.7	1070.3	1067.9	1064.3	1060.9	1057.3	1053.8	1051.8
40°	1035.3	1033.9	1032.6	1031.3	1029.9	1027.3	1023.6	1019.8	1016.1	1012.4	1010.0
42.5°	991.9	990.8	989.7	988.6	987.4	985.0	981.2	977.5	973.7	970.0	967.8
45°	929.3	928.3	927.2	926.1	925.1	922.9	919.7	916.5	913.3	910.1	906.9
47.5°	861.9	861.9	862.0	862.1	862.1	860.2	856.4	852.5	848.6	844.8	841.5
50°	818.6	817.8	817.0	816.2	815.4	813.3	810.1	806.9	803.7	800.5	797.0
52.5°	774.3	773.6	773.1	772.5	772.0	769.9	766.5	763.0	759.6	756.2	753.1
55°	707.8	707.0	706.2	705.4	704.6	702.3	698.6	694.8	691.1	687.3	684.9
57.5°	637.8	637.3	636.9	636.5	636.1	634.3	631.1	627.9	624.8	621.6	618.5
60°	593.4	592.4	591.3	590.2	589.2	587.2	584.2	581.3	578.4	575.4	572.7
62.5°	547.2	546.4	545.5	544.7	543.9	542.2	539.6	537.1	534.6	532.1	529.1
65°	477.9	477.3	476.8	476.3	475.7	474.0	471.1	468.1	465.2	462.3	459.9
67.5°	410.7	409.6	408.5	407.3	406.3	404.6	402.3	400.2	398.0	395.8	393.8
70°	368.4	367.0	365.7	364.4	363.0	361.1	358.7	356.3	353.9	351.5	349.9
72.5°	322.2	321.2	320.3	319.4	318.5	317.3	315.8	314.1	312.6	311.0	309.2
75°	254.0	253.4	252.9	252.4	251.8	250.9	249.6	248.3	246.9	245.6	244.8
77.5°	191.2	190.9	190.7	190.6	190.3	189.8	189.0	188.3	187.6	186.8	186.4
80°	151.7	151.7	151.7	151.7	151.7	151.4	150.9	150.3	149.8	149.3	149.0
82.5°	117.0	116.5	116.2	115.7	115.3	115.0	114.9	114.9	114.7	114.6	114.1
85°	66.2	66.4	66.7	67.0	67.2	67.4	67.4	67.4	67.4	67.4	67.1
87.5°	26.1	26.4	26.7	26.8	27.1	27.3	27.3	27.3	27.3	27.3	27.5
90°	0.7	2.0	3.2	4.5	5.6	6.8	7.9	9.0	10.1	11.1	11.9
92.5°	10.7	9.9	9.0	8.1	7.3	7.3	8.3	9.3	10.2	11.1	11.9
95°	39.8	39.3	38.8	38.3	37.9	34.7	28.8	22.9	17.0	11.1	11.9
97.5°	83.0	83.8	84.6	85.5	86.3	81.0	69.3	57.6	45.9	34.3	30.0
100°	116.5	116.9	117.3	117.9	118.3	118.9	119.5	120.1	120.7	121.4	98.3
102.5°	150.5	151.1	151.7	152.2	152.8	153.3	153.7	154.1	154.4	154.8	150.4
105°	205.0	205.6	206.3	206.9	207.5	207.8	207.8	207.8	207.8	207.8	207.8
107.5°	261.6	261.6	261.6	261.6	261.6	261.8	262.1	262.4	262.7	263.1	263.1
110°	298.5	298.5	298.5	298.5	298.5	298.6	298.9	299.3	299.5	299.9	299.4



TEST NUMBER: P333274-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	333.1	333.4	333.8	334.2	334.6	334.8	335.0	335.2	335.4	335.6	335.0
115°	385.0	385.8	386.5	387.3	388.1	388.5	388.7	388.8	389.0	389.1	388.5
117.5°	438.6	438.6	438.5	438.5	438.5	438.8	439.3	440.0	440.6	441.1	440.3
120°	472.1	472.0	471.8	471.6	471.4	471.6	472.1	472.6	473.1	473.5	473.2
122.5°	501.7	502.3	502.8	503.5	504.0	504.4	504.6	504.9	505.1	505.3	505.0
125°	547.4	548.5	549.6	550.7	551.8	552.3	552.3	552.3	552.3	552.3	551.7
127.5°	591.1	591.8	592.6	593.4	594.1	594.5	594.4	594.3	594.2	594.1	593.8
130°	617.9	618.7	619.4	620.2	621.0	621.4	621.6	621.7	621.9	622.1	621.6
132.5°	644.6	645.5	646.4	647.3	648.3	648.5	648.2	647.8	647.5	647.1	647.0
135°	682.7	683.7	684.6	685.5	686.4	686.7	686.4	686.1	685.8	685.5	685.2
137.5°	717.7	718.5	719.3	720.1	720.9	721.2	720.9	720.7	720.4	720.1	720.1
140°	740.6	740.9	741.2	741.5	741.8	741.9	741.7	741.6	741.5	741.3	741.6
142.5°	761.3	761.4	761.6	761.8	762.0	762.1	762.4	762.6	762.9	763.0	763.1
145°	791.5	791.8	792.1	792.5	792.7	792.9	792.9	792.9	792.9	792.9	793.1
147.5°	818.0	818.0	817.9	817.8	817.8	817.8	818.0	818.1	818.4	818.6	818.8
150°	834.7	834.5	834.1	833.8	833.5	833.5	833.8	834.1	834.5	834.7	835.1
152.5°	851.0	850.2	849.5	848.9	848.2	848.0	848.3	848.6	848.9	849.3	849.5
155°	871.7	870.8	869.9	868.9	868.0	867.6	868.0	868.3	868.6	868.9	869.3
157.5°	887.7	887.2	886.6	886.1	885.5	885.2	885.3	885.3	885.3	885.4	885.8
160°	898.9	898.0	897.1	896.1	895.2	894.8	894.9	895.1	895.3	895.4	896.0
162.5°	907.9	906.9	906.0	905.0	904.1	903.7	903.8	904.0	904.2	904.4	905.2
165°	919.8	918.9	917.9	917.0	916.1	915.7	915.9	916.1	916.1	916.3	917.3
167.5°	928.7	927.8	926.8	925.9	924.9	924.5	924.6	924.8	925.0	925.1	926.2
170°	933.8	932.6	931.6	930.5	929.4	929.0	929.1	929.3	929.4	929.6	930.9
172.5°	937.1	936.0	935.0	933.9	932.7	932.4	932.6	932.9	933.2	933.4	934.6
175°	940.8	939.8	938.9	938.0	937.0	936.7	936.7	936.9	937.1	937.3	938.5
177.5°	942.4	941.6	940.9	940.2	939.4	939.1	939.2	939.3	939.5	939.6	940.5
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8



TEST NUMBER: P333274-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
2.5°	1517.2	1519.3	1521.4	1522.4	1522.2	1522.0	1521.8	1521.6
5°	1509.6	1512.0	1514.4	1515.5	1515.2	1514.9	1514.7	1514.4
7.5°	1494.2	1496.6	1499.0	1500.0	1499.8	1499.5	1499.2	1499.0
10°	1481.3	1483.5	1485.6	1486.6	1486.3	1486.0	1485.8	1485.5
12.5°	1464.1	1465.8	1467.5	1468.4	1468.3	1468.2	1468.2	1468.1
15°	1434.0	1435.3	1436.6	1437.3	1437.3	1437.3	1437.3	1437.3
17.5°	1399.0	1400.6	1402.3	1402.5	1401.1	1399.8	1398.5	1397.1
20°	1372.4	1374.3	1376.2	1376.4	1375.1	1373.8	1372.4	1371.1
22.5°	1342.3	1343.5	1344.7	1344.9	1344.0	1343.1	1342.2	1341.2
25°	1294.0	1294.5	1295.0	1294.9	1294.1	1293.2	1292.4	1291.6
27.5°	1243.2	1243.3	1243.5	1243.1	1242.3	1241.5	1240.7	1239.9
30°	1206.3	1205.8	1205.2	1204.6	1203.8	1203.0	1202.2	1201.4
32.5°	1168.9	1167.9	1167.0	1165.7	1164.3	1162.9	1161.4	1159.9
35°	1110.8	1109.5	1108.1	1106.4	1104.3	1102.2	1100.0	1097.9
37.5°	1049.8	1047.8	1045.9	1044.3	1043.0	1041.8	1040.5	1039.4
40°	1007.5	1005.1	1002.7	1001.1	1000.3	999.5	998.7	997.9
42.5°	965.6	963.4	961.3	959.5	958.3	957.1	955.8	954.6
45°	903.7	900.4	897.2	895.2	894.4	893.6	892.8	892.0
47.5°	838.3	835.0	831.8	829.2	827.3	825.5	823.6	821.7
50°	793.5	790.1	786.6	783.9	782.0	780.2	778.3	776.4
52.5°	750.1	747.1	744.0	741.5	739.3	737.3	735.2	733.1
55°	682.5	680.1	677.7	675.6	673.7	671.8	669.9	668.1
57.5°	615.5	612.3	609.2	607.2	606.2	605.1	604.1	603.1
60°	570.1	567.4	564.7	562.4	560.5	558.7	556.8	554.9
62.5°	526.3	523.4	520.5	518.4	516.9	515.5	514.0	512.6
65°	457.4	455.0	452.6	450.8	449.8	448.7	447.6	446.6
67.5°	391.7	389.7	387.6	386.3	385.7	385.0	384.4	383.8
70°	348.3	346.7	345.1	343.8	342.7	341.6	340.5	339.5
72.5°	307.5	305.6	303.8	302.4	301.3	300.2	299.2	298.1
75°	244.0	243.2	242.4	241.4	240.3	239.2	238.2	237.1
77.5°	185.8	185.4	184.9	184.3	183.5	182.8	182.0	181.3
80°	148.7	148.5	148.2	147.8	147.2	146.7	146.2	145.6
82.5°	113.6	113.2	112.7	112.4	112.3	112.2	112.1	111.9
85°	66.9	66.6	66.3	65.9	65.4	64.8	64.3	63.8
87.5°	27.6	27.7	27.9	27.8	27.5	27.1	26.8	26.5
90°	12.8	13.5	14.3	14.9	15.3	15.8	16.2	16.8
92.5°	12.8	13.5	14.3	14.7	15.0	15.2	15.4	15.6
95°	12.8	13.5	14.3	14.6	14.6	14.6	14.6	14.6
97.5°	25.6	21.2	16.9	14.6	14.6	14.6	14.6	14.6
100°	75.2	52.1	29.0	17.1	16.5	15.9	15.2	14.6
102.5°	146.1	141.7	137.3	129.9	119.3	108.8	98.3	87.7
105°	207.8	207.8	207.8	207.8	207.6	207.4	207.2	207.1
107.5°	263.1	263.1	263.1	263.0	262.5	262.0	261.5	261.1
110°	298.9	298.5	298.0	297.8	298.0	298.2	298.3	298.5



TEST NUMBER: P333274-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	334.4	333.8	333.2	332.8	332.6	332.3	332.2	332.0
115°	387.9	387.3	386.6	385.8	385.0	384.0	383.1	382.2
117.5°	439.5	438.7	437.9	437.3	436.9	436.5	436.1	435.7
120°	472.9	472.6	472.3	471.7	470.9	470.2	469.4	468.6
122.5°	504.7	504.4	504.1	503.5	502.6	501.7	500.8	499.9
125°	551.1	550.5	549.8	549.3	548.8	548.3	547.9	547.4
127.5°	593.4	593.2	592.8	592.0	590.9	589.8	588.6	587.5
130°	621.1	620.6	620.2	619.6	618.8	618.0	617.2	616.4
132.5°	646.9	646.8	646.8	646.3	645.6	644.8	644.0	643.3
135°	684.9	684.6	684.3	683.7	682.7	681.8	680.8	679.9
137.5°	720.2	720.2	720.3	720.0	719.2	718.4	717.6	716.8
140°	741.9	742.3	742.5	742.3	741.3	740.4	739.4	738.5
142.5°	763.2	763.2	763.3	762.9	762.0	761.0	760.1	759.1
145°	793.2	793.4	793.5	793.1	792.2	791.3	790.3	789.4
147.5°	818.9	819.1	819.3	818.9	817.7	816.6	815.5	814.4
150°	835.4	835.7	836.0	835.5	834.3	833.0	831.8	830.5
152.5°	849.9	850.2	850.5	850.1	849.0	847.8	846.8	845.6
155°	869.9	870.3	870.8	870.4	869.2	867.9	866.7	865.4
157.5°	886.4	886.9	887.3	887.0	885.7	884.5	883.2	882.0
160°	896.6	897.2	897.9	897.6	896.3	895.1	893.9	892.6
162.5°	906.1	907.0	907.8	907.6	906.2	904.8	903.5	902.1
165°	918.2	919.1	920.1	919.9	918.6	917.4	916.1	914.9
167.5°	927.4	928.4	929.6	929.4	928.0	926.7	925.2	923.9
170°	932.0	933.3	934.5	934.4	933.1	931.7	930.2	928.9
172.5°	935.7	936.8	938.0	937.8	936.4	935.0	933.6	932.2
175°	939.7	940.9	942.2	942.1	940.8	939.3	938.0	936.6
177.5°	941.4	942.2	943.1	943.1	942.0	941.0	940.0	939.1
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8

(END OF REPORT)