

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333323

Luminaire Tested: **S125DIP-S1270D1035U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333323
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D1035U835-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8765.0 lumens
Efficiency: N/A
Efficacy: 131.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59																												
1	100	96	92	89	93	90	86	83	78	76	73	67	66	64	57	56	55	50																												
2	91	84	78	73	85	79	73	69	69	65	61	59	56	54	51	49	47	43																												
3	83	74	67	61	78	69	63	58	61	56	52	53	49	46	45	42	40	36																												
4	76	66	58	52	71	62	55	49	54	49	44	47	43	39	41	37	35	31																												
5	70	59	50	44	65	55	48	42	49	43	38	42	38	34	37	33	30	27																												
6	65	53	45	39	60	50	42	37	44	38	33	38	34	30	33	30	27	24																												
7	60	48	40	34	56	45	38	32	40	34	30	35	30	27	30	27	24	21																												
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19																												
9	52	40	32	27	48	37	30	26	33	28	24	29	25	21	26	22	19	17																												
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	16																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11861	11861	11861	11861
5°	13736	11902	10421	11902
10°	15980	11840	9130	11840
15°	17690	11753	8423	11753
20°	19801	11615	7854	11615
25°	23197	11460	7577	11460
30°	25055	11307	7337	11307
35°	20601	11020	7179	11020
40°	14643	10620	7006	10620
45°	11249	10082	6906	10082
50°	9602	9414	6893	9414
55°	8550	8760	6952	8760
60°	7713	8045	7129	8045
65°	7124	7326	7314	7326
70°	6477	6579	7419	6579
75°	5719	5797	7354	5797
80°	4813	4727	6724	4727
85°	3809	3409	5432	3409



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.8	2.0
10°-20°	526.4	6.0
20°-30°	854.8	9.8
30°-40°	1042.7	11.9
40°-50°	948.5	10.8
50°-60°	755.5	8.6
60°-70°	526.2	6.0
70°-80°	280.6	3.2
80°-90°	73.6	0.8
90°-100°	85.9	1.0
100°-110°	253.7	2.9
110°-120°	429.8	4.9
120°-130°	565.6	6.5
130°-140°	633.8	7.2
140°-150°	621.1	7.1
150°-160°	521.7	6.0
160°-170°	346.8	4.0
170°-180°	121.4	1.4
0°-30°	1558.0	17.8
0°-40°	2600.7	29.7
0°-60°	4304.7	49.1
0°-90°	5185.2	59.2
90°-120°	769.4	8.8
90°-150°	2589.9	29.5
90°-180°	3580.0	40.8
0°-180°	8765.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1837	1837	1837	1837	1837	
5°	2119	1836	1607	1836	2119	214
15°	2646	1758	1260	1758	2646	757
25°	3255	1608	1063	1608	3255	1487
35°	2613	1398	910	1398	2613	1599
45°	1232	1104	756	1104	1232	986
55°	759	778	617	778	759	684
65°	466	479	479	479	466	463
75°	229	232	295	232	229	247
85°	51	46	73	46	51	60
90°	24	1	24	1	24	16
95°	86	65	86	65	86	87
105°	248	228	248	228	248	262
115°	434	430	434	430	434	430
125°	632	628	632	628	632	564
135°	820	817	820	817	820	632
145°	993	989	993	989	993	620
155°	1132	1132	1132	1132	1132	521
165°	1228	1231	1228	1231	1228	346
175°	1275	1280	1275	1280	1275	121
180°	1283	1283	1283	1283	1283	



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1942.6	1940.1	1937.6	1932.6	1936.3	1925.7	1920.7	1912.0	1901.4	1897.7	1893.3
5°	2118.7	2122.6	2126.5	2110.2	2111.7	2100.8	2075.9	2055.6	2039.2	2018.2	2003.4
7.5°	2330.8	2321.6	2320.8	2310.2	2292.0	2277.3	2251.1	2217.7	2185.5	2148.7	2118.3
10°	2436.8	2437.6	2430.6	2418.1	2398.6	2384.6	2350.3	2317.5	2277.8	2231.0	2197.5
12.5°	2516.6	2519.9	2511.0	2494.2	2484.6	2453.2	2426.3	2387.4	2340.1	2302.7	2251.7
15°	2645.7	2637.1	2630.9	2609.8	2593.5	2560.7	2517.9	2477.3	2425.9	2378.3	2330.8
17.5°	2770.1	2777.0	2765.3	2746.1	2695.3	2657.1	2599.6	2544.0	2480.0	2416.2	2359.5
20°	2881.1	2887.4	2869.4	2835.9	2775.1	2736.9	2661.3	2589.6	2515.5	2433.7	2371.3
22.5°	3019.6	3014.6	2990.4	2939.4	2886.7	2816.1	2734.3	2646.9	2554.2	2461.7	2378.8
25°	3255.3	3222.5	3207.7	3144.6	3075.2	2971.5	2859.3	2731.4	2616.1	2493.7	2387.7
27.5°	3385.9	3375.6	3359.1	3315.2	3242.2	3131.3	2999.0	2843.2	2680.5	2526.0	2387.2
30°	3359.7	3361.3	3362.9	3348.8	3302.1	3218.6	3086.9	2919.3	2726.0	2552.2	2391.6
32.5°	3127.8	3156.1	3183.3	3215.4	3228.5	3212.4	3129.9	2978.6	2779.6	2582.1	2389.1
35°	2613.0	2621.5	2709.6	2796.9	2915.4	3007.4	3069.0	3001.9	2834.3	2607.5	2386.1
37.5°	2037.4	2079.5	2140.4	2239.1	2410.1	2563.2	2760.1	2850.7	2796.6	2615.8	2380.7
40°	1736.8	1775.8	1815.5	1916.1	2060.3	2245.8	2469.5	2660.5	2704.9	2589.6	2362.0
42.5°	1504.8	1535.7	1579.8	1655.4	1775.9	1940.2	2154.0	2403.6	2557.1	2513.5	2322.7
45°	1231.6	1251.1	1285.4	1345.5	1432.8	1561.4	1750.0	2022.9	2260.6	2339.3	2229.4
47.5°	1054.2	1054.1	1080.7	1122.2	1185.2	1294.5	1434.0	1647.8	1901.7	2089.6	2080.9
50°	955.7	951.8	972.8	1008.7	1058.6	1131.1	1264.4	1435.1	1679.1	1891.9	1951.1
52.5°	870.9	871.3	884.3	910.8	952.6	1014.5	1114.1	1268.0	1476.4	1694.8	1806.5
55°	759.3	756.1	770.9	788.9	819.3	859.8	931.5	1049.2	1218.4	1433.5	1578.5
57.5°	657.0	665.6	671.5	684.0	709.2	736.3	796.8	883.2	1017.4	1202.0	1355.3
60°	597.1	605.7	610.4	622.8	643.1	666.5	713.3	783.4	896.5	1055.5	1207.5
62.5°	543.5	550.2	551.7	563.0	579.5	602.3	639.1	698.0	787.3	926.4	1075.3
65°	466.2	466.2	469.3	481.0	488.8	509.0	537.1	580.0	651.7	760.0	887.1
67.5°	391.6	395.4	394.6	399.7	406.9	422.7	442.8	478.2	531.3	610.4	712.0
70°	343.0	346.1	345.3	349.2	357.0	367.2	383.5	417.0	455.2	523.1	610.4
72.5°	299.3	300.6	298.6	303.7	308.4	317.3	335.5	353.4	389.1	446.4	518.1
75°	229.2	230.7	232.3	235.4	240.1	244.8	254.1	272.1	295.4	338.3	384.3
77.5°	171.8	168.8	172.6	172.1	174.8	178.4	186.6	196.1	215.3	242.4	278.0
80°	129.4	130.2	130.2	131.0	134.9	137.2	144.2	151.2	166.0	186.3	211.3
82.5°	94.5	96.5	95.3	96.7	99.9	101.6	105.5	111.3	119.9	135.8	153.9
85°	51.4	47.6	49.1	50.7	50.7	51.4	54.6	56.9	61.6	67.8	74.8
87.5°	19.8	20.9	21.4	21.2	21.7	21.5	23.8	23.6	25.2	26.9	29.1
90°	24.0	23.3	22.6	22.0	21.3	20.4	19.3	18.2	17.1	16.0	14.4
92.5°	47.1	46.6	46.1	45.7	45.2	44.2	42.7	41.3	39.8	38.3	36.4
95°	85.9	85.4	85.0	84.5	84.1	83.1	81.5	80.0	78.4	76.9	74.7
97.5°	130.2	129.9	129.7	129.4	129.1	128.3	126.8	125.3	123.9	122.4	119.3
100°	163.7	163.3	162.8	162.4	162.0	160.7	158.7	156.7	154.7	152.7	149.9
102.5°	197.3	196.7	196.0	195.4	194.8	193.4	191.2	189.0	186.9	184.7	183.2
105°	247.6	246.9	246.3	245.6	244.9	243.9	242.6	241.3	239.9	238.6	237.3
107.5°	299.1	299.2	299.2	299.2	299.3	299.0	298.3	297.6	297.0	296.3	295.3
110°	337.4	337.7	337.9	338.1	338.3	338.1	337.4	336.8	336.1	335.4	334.8



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	375.0	375.4	375.8	376.2	376.6	376.6	376.3	376.0	375.7	375.4	374.5
115°	434.3	434.5	434.7	434.9	435.2	435.4	435.6	435.8	436.1	436.3	435.8
117.5°	492.2	493.1	494.0	494.8	495.7	496.1	495.9	495.7	495.6	495.4	495.0
120°	532.1	533.0	533.9	534.8	535.7	536.1	536.1	536.1	536.1	536.1	535.9
122.5°	572.1	572.8	573.5	574.2	574.9	575.3	575.5	575.7	575.9	576.0	575.5
125°	632.0	632.2	632.4	632.6	632.8	633.2	633.6	634.1	634.5	635.0	634.7
127.5°	689.5	689.9	690.3	690.8	691.2	691.6	691.8	692.0	692.2	692.5	692.2
130°	727.8	728.2	728.7	729.1	729.6	729.9	730.1	730.3	730.6	730.8	730.3
132.5°	763.7	764.4	765.0	765.6	766.2	766.6	766.9	767.1	767.3	767.5	767.6
135°	819.6	820.5	821.4	822.3	823.2	823.6	823.6	823.6	823.6	823.6	823.4
137.5°	874.4	875.5	876.6	877.7	878.8	879.2	878.9	878.7	878.4	878.1	877.7
140°	909.5	910.6	911.7	912.8	913.9	914.3	913.8	913.4	912.9	912.5	911.8
142.5°	943.0	944.2	945.3	946.4	947.5	947.9	947.6	947.4	947.1	946.8	946.0
145°	993.4	994.0	994.7	995.4	996.0	996.4	996.4	996.4	996.4	996.4	995.7
147.5°	1036.3	1037.8	1039.3	1040.8	1042.3	1042.8	1042.3	1041.7	1041.2	1040.7	1040.1
150°	1068.2	1068.7	1069.1	1069.6	1070.0	1070.2	1070.2	1070.2	1070.2	1070.2	1069.3
152.5°	1094.6	1095.4	1096.2	1097.0	1097.8	1097.9	1097.4	1096.9	1096.3	1095.8	1095.4
155°	1132.1	1133.2	1134.3	1135.5	1136.6	1136.7	1135.8	1134.9	1134.0	1133.1	1132.9
157.5°	1163.5	1164.9	1166.4	1167.9	1169.3	1169.6	1168.7	1167.8	1167.0	1166.1	1165.9
160°	1185.0	1186.2	1187.3	1188.4	1189.5	1189.6	1188.7	1187.8	1186.9	1186.0	1185.8
162.5°	1203.4	1204.7	1206.0	1207.3	1208.6	1208.7	1207.6	1206.5	1205.5	1204.4	1204.4
165°	1228.0	1229.3	1230.6	1232.0	1233.3	1233.5	1232.6	1231.7	1230.9	1230.0	1229.7
167.5°	1247.5	1248.9	1250.3	1251.7	1253.0	1253.1	1251.7	1250.4	1249.1	1247.7	1247.7
170°	1257.9	1259.5	1261.0	1262.6	1264.1	1264.2	1262.9	1261.6	1260.3	1258.9	1258.9
172.5°	1266.7	1268.1	1269.5	1270.8	1272.2	1272.2	1270.9	1269.6	1268.2	1266.9	1266.9
175°	1274.9	1276.4	1278.0	1279.6	1281.1	1281.2	1279.9	1278.6	1277.2	1275.9	1275.9
177.5°	1279.7	1280.9	1282.2	1283.4	1284.7	1284.7	1283.7	1282.6	1281.6	1280.5	1280.7
180°	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9



TEST NUMBER: P33323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1889.6	1885.2	1880.2	1871.5	1860.9	1855.3	1846.5	1840.9	1829.7	1820.3	1810.4
5°	1985.4	1965.2	1946.5	1922.3	1895.8	1878.6	1858.4	1835.8	1812.4	1788.2	1761.7
7.5°	2084.8	2048.9	2009.9	1968.0	1927.0	1889.2	1853.2	1817.8	1784.8	1744.9	1711.1
10°	2151.5	2106.3	2057.9	2001.0	1945.7	1897.4	1848.2	1805.4	1761.7	1714.9	1673.6
12.5°	2218.2	2158.0	2089.7	2027.2	1960.7	1902.3	1844.5	1789.8	1734.9	1683.1	1635.0
15°	2265.3	2212.3	2149.1	2060.3	1985.4	1905.2	1828.8	1757.8	1691.6	1633.9	1573.1
17.5°	2296.3	2228.0	2160.2	2074.9	1976.9	1887.1	1800.5	1719.3	1644.6	1571.5	1512.9
20°	2301.9	2231.8	2160.8	2077.4	1976.9	1874.0	1787.4	1690.0	1609.7	1534.1	1462.4
22.5°	2300.1	2220.5	2143.4	2057.5	1959.4	1864.6	1760.0	1660.7	1573.5	1499.2	1424.3
25°	2282.4	2197.5	2100.8	2014.3	1917.6	1817.1	1711.1	1608.2	1519.3	1434.3	1360.3
27.5°	2267.8	2157.6	2048.1	1947.2	1853.9	1761.7	1660.2	1554.8	1456.3	1370.2	1300.4
30°	2249.7	2128.9	2005.7	1900.5	1804.6	1714.9	1619.1	1516.2	1413.3	1329.1	1254.3
32.5°	2233.5	2092.7	1962.7	1848.1	1746.6	1659.4	1571.0	1473.1	1372.1	1286.7	1211.8
35°	2202.2	2039.2	1890.3	1760.9	1652.6	1562.9	1488.9	1397.7	1304.9	1222.3	1150.6
37.5°	2162.4	1969.1	1809.3	1673.6	1554.8	1460.4	1391.4	1321.4	1232.4	1152.8	1087.9
40°	2131.2	1919.2	1750.0	1611.3	1488.1	1389.9	1326.0	1259.7	1185.7	1111.6	1043.0
42.5°	2091.9	1874.3	1690.2	1540.8	1418.9	1323.2	1256.1	1199.8	1134.5	1065.5	1001.8
45°	2019.7	1792.9	1593.3	1432.8	1309.6	1215.3	1145.9	1103.8	1054.7	989.2	935.4
47.5°	1913.6	1695.1	1488.7	1323.0	1195.9	1108.5	1043.5	1003.1	968.5	919.8	871.0
50°	1819.4	1622.2	1413.3	1248.8	1121.7	1033.6	973.6	937.0	907.4	869.9	828.6
52.5°	1714.0	1530.5	1339.1	1176.5	1050.6	963.8	905.0	872.8	848.1	821.3	780.6
55°	1546.6	1390.7	1212.9	1058.6	942.4	857.5	806.0	778.0	757.7	737.4	712.5
57.5°	1362.1	1240.2	1082.8	941.7	834.7	757.4	709.4	682.1	666.3	655.9	641.2
60°	1232.4	1128.0	992.3	863.7	759.3	690.7	643.9	622.8	609.6	601.0	590.1
62.5°	1112.1	1026.3	900.7	783.3	691.9	627.0	585.3	564.8	552.2	548.0	539.0
65°	934.6	868.4	764.7	667.3	589.3	534.0	498.9	479.4	471.6	466.9	467.7
67.5°	759.9	719.5	636.2	553.1	490.9	444.5	416.4	401.5	397.6	391.3	391.2
70°	653.2	622.8	552.7	480.2	424.8	389.0	364.0	348.4	344.5	341.4	340.7
72.5°	559.1	532.4	471.6	413.5	363.7	332.2	311.7	302.3	295.9	294.0	293.9
75°	420.2	405.4	357.0	311.0	276.7	254.9	240.9	232.3	227.6	226.8	227.6
77.5°	298.7	285.8	255.1	222.5	200.8	184.3	172.4	169.5	164.2	164.3	163.5
80°	224.5	215.9	196.4	170.7	152.8	138.8	132.5	127.1	125.5	123.2	125.5
82.5°	162.8	153.6	140.3	123.9	109.1	100.7	94.5	92.8	91.8	90.7	91.2
85°	80.3	81.1	73.3	60.8	54.6	49.9	46.0	46.0	45.2	44.4	45.2
87.5°	30.0	28.5	25.6	23.4	20.0	17.7	16.8	17.0	15.5	15.3	16.2
90°	12.9	11.3	9.8	8.1	6.3	4.5	2.8	1.0	2.8	4.5	6.3
92.5°	34.5	32.6	30.7	29.1	27.9	26.6	25.4	24.2	25.4	26.6	27.9
95°	72.4	70.2	68.0	66.7	66.2	65.8	65.3	64.9	65.3	65.8	66.2
97.5°	116.3	113.2	110.2	108.5	108.4	108.2	108.0	107.8	108.0	108.2	108.4
100°	147.0	144.1	141.2	139.8	139.8	139.8	139.8	139.8	139.8	139.8	139.8
102.5°	181.8	180.3	178.8	177.7	176.8	175.9	175.0	174.1	175.0	175.9	176.8
105°	235.9	234.6	233.3	232.1	231.0	229.8	228.7	227.6	228.7	229.8	231.0
107.5°	294.3	293.2	292.2	291.2	290.1	288.9	287.8	286.7	287.8	288.9	290.1
110°	334.1	333.4	332.8	331.9	330.8	329.7	328.6	327.5	328.6	329.7	330.8



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	373.7	372.9	372.0	371.3	370.7	370.1	369.6	369.0	369.6	370.1	370.7
115°	435.4	434.9	434.5	433.8	433.0	432.1	431.2	430.3	431.2	432.1	433.0
117.5°	494.6	494.2	493.8	493.4	493.0	492.6	492.2	491.8	492.2	492.6	493.0
120°	535.7	535.4	535.2	534.6	533.5	532.3	531.2	530.1	531.2	532.3	533.5
122.5°	574.9	574.3	573.7	573.3	572.9	572.5	572.1	571.7	572.1	572.5	572.9
125°	634.5	634.3	634.1	633.3	632.0	630.6	629.3	628.0	629.3	630.6	632.0
127.5°	691.9	691.7	691.4	690.9	690.1	689.4	688.6	687.9	688.6	689.4	690.1
130°	729.9	729.5	729.0	728.2	727.1	726.0	724.9	723.8	724.9	726.0	727.1
132.5°	767.7	767.8	767.9	767.0	765.2	763.4	761.6	759.7	761.6	763.4	765.2
135°	823.2	823.0	822.8	822.0	820.6	819.3	818.0	816.7	818.0	819.3	820.6
137.5°	877.2	876.7	876.2	875.3	874.0	872.7	871.4	870.2	871.4	872.7	874.0
140°	911.2	910.5	909.8	908.9	907.8	906.7	905.6	904.5	905.6	906.7	907.8
142.5°	945.2	944.3	943.5	942.6	941.6	940.7	939.8	938.8	939.8	940.7	941.6
145°	995.0	994.4	993.7	992.9	992.0	991.1	990.3	989.4	990.3	991.1	992.0
147.5°	1039.6	1039.1	1038.6	1038.0	1037.6	1037.1	1036.6	1036.1	1036.6	1037.1	1037.6
150°	1068.5	1067.6	1066.7	1066.4	1066.6	1066.8	1067.0	1067.2	1067.0	1066.8	1066.6
152.5°	1095.1	1094.7	1094.4	1094.0	1093.7	1093.4	1093.1	1092.8	1093.1	1093.4	1093.7
155°	1132.7	1132.5	1132.2	1132.1	1132.1	1132.1	1132.1	1132.1	1132.1	1132.1	1132.1
157.5°	1165.6	1165.4	1165.2	1165.3	1165.8	1166.3	1166.8	1167.3	1166.8	1166.3	1165.8
160°	1185.6	1185.4	1185.2	1185.4	1186.0	1186.7	1187.4	1188.0	1187.4	1186.7	1186.0
162.5°	1204.3	1204.3	1204.2	1204.5	1204.9	1205.4	1205.9	1206.4	1205.9	1205.4	1204.9
165°	1229.5	1229.3	1229.1	1229.2	1229.6	1230.1	1230.5	1231.0	1230.5	1230.1	1229.6
167.5°	1247.7	1247.7	1247.7	1248.2	1249.1	1250.0	1250.8	1251.7	1250.8	1250.0	1249.1
170°	1258.9	1258.9	1258.9	1259.4	1260.3	1261.1	1262.0	1262.9	1262.0	1261.1	1260.3
172.5°	1266.9	1266.9	1266.9	1267.4	1268.2	1269.1	1270.0	1270.9	1270.0	1269.1	1268.2
175°	1275.9	1275.9	1275.9	1276.3	1277.2	1278.1	1279.0	1279.9	1279.0	1278.1	1277.2
177.5°	1280.8	1281.0	1281.2	1281.6	1282.3	1283.1	1283.8	1284.5	1283.8	1283.1	1282.3
180°	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1804.7	1797.9	1792.3	1779.8	1772.9	1763.6	1756.1	1764.2	1755.5	1759.2	1753.6
5°	1748.5	1726.6	1711.1	1688.4	1669.0	1651.0	1637.8	1635.4	1629.2	1626.1	1616.7
7.5°	1680.8	1653.5	1626.7	1597.1	1572.1	1546.7	1530.5	1517.1	1508.2	1496.5	1488.6
10°	1640.9	1604.3	1573.1	1537.2	1506.0	1478.8	1456.9	1446.0	1435.9	1421.1	1415.6
12.5°	1591.6	1553.7	1515.7	1477.4	1447.4	1417.0	1398.3	1381.8	1374.8	1358.1	1356.4
15°	1532.5	1475.6	1438.2	1399.2	1357.9	1333.0	1317.4	1299.5	1291.7	1280.0	1271.4
17.5°	1462.1	1411.2	1364.5	1324.1	1288.7	1267.7	1248.3	1236.0	1222.6	1215.0	1200.9
20°	1410.9	1362.6	1315.8	1273.0	1245.7	1221.5	1205.9	1194.2	1180.2	1176.3	1162.3
22.5°	1367.9	1314.6	1269.7	1233.7	1203.9	1176.6	1159.8	1151.8	1142.2	1130.2	1127.3
25°	1297.9	1242.6	1204.4	1168.5	1142.0	1117.1	1105.4	1095.2	1085.9	1077.3	1074.2
27.5°	1237.4	1188.0	1142.6	1110.2	1087.1	1064.4	1054.1	1041.8	1034.9	1028.0	1019.6
30°	1195.0	1144.3	1104.6	1073.4	1048.5	1028.2	1017.3	1008.7	1002.5	996.2	991.6
32.5°	1151.4	1104.4	1065.9	1035.4	1010.4	995.1	985.5	979.4	972.5	965.0	959.1
35°	1093.7	1042.2	1004.8	978.3	958.8	947.1	936.2	930.7	923.0	923.0	916.7
37.5°	1028.7	984.2	951.2	927.0	909.5	899.1	887.3	883.5	878.5	875.2	873.1
40°	990.0	948.7	917.5	893.3	874.6	866.0	856.7	850.5	847.3	843.4	841.9
42.5°	950.1	910.6	880.7	858.4	842.2	834.9	826.1	821.8	815.5	810.4	809.5
45°	889.4	851.2	824.0	806.0	792.0	783.4	778.0	768.6	765.5	759.3	758.5
47.5°	831.9	795.3	768.5	753.8	741.5	734.5	725.9	716.5	713.0	709.8	709.5
50°	788.9	755.4	730.4	716.4	704.7	694.6	686.0	679.7	677.4	677.4	679.0
52.5°	745.2	716.7	695.5	678.3	667.3	656.5	648.6	644.8	641.2	645.0	647.8
55°	681.3	652.5	636.9	620.5	609.6	597.1	593.2	591.7	589.3	595.6	598.7
57.5°	613.6	593.4	575.1	558.9	549.1	541.9	536.6	535.7	540.1	543.0	553.1
60°	570.6	547.2	530.9	518.4	506.7	502.0	500.5	498.9	502.0	510.6	523.8
62.5°	523.2	504.2	486.6	477.2	468.6	460.9	460.5	461.5	467.7	477.5	490.8
65°	453.7	437.3	425.6	414.7	407.7	403.0	404.6	407.7	414.7	428.0	442.8
67.5°	383.1	371.8	361.4	352.5	345.8	345.8	347.4	352.0	360.3	375.6	389.1
70°	337.5	325.1	316.5	312.6	307.1	304.0	308.7	316.5	323.5	337.5	349.2
72.5°	292.0	281.4	274.7	272.1	269.7	267.2	268.8	277.2	286.7	300.7	314.3
75°	224.5	220.6	215.9	212.8	210.5	212.0	213.6	221.4	229.2	244.0	259.6
77.5°	163.9	159.8	157.0	156.2	155.0	155.7	160.1	165.9	173.5	184.3	196.1
80°	123.9	122.4	120.8	120.0	120.0	120.8	127.1	131.0	138.0	148.1	157.5
82.5°	90.3	89.3	89.0	88.9	89.5	89.6	93.4	98.5	104.3	111.9	120.0
85°	47.6	46.0	48.3	49.1	47.6	49.9	51.4	54.6	56.9	60.8	64.7
87.5°	17.2	18.8	18.5	19.4	19.7	21.3	20.9	23.6	25.1	26.5	26.1
90°	8.1	9.8	11.3	12.9	14.4	16.0	17.1	18.2	19.3	20.4	21.3
92.5°	29.1	30.7	32.6	34.5	36.4	38.3	39.8	41.3	42.7	44.2	45.2
95°	66.7	68.0	70.2	72.4	74.7	76.9	78.4	80.0	81.5	83.1	84.1
97.5°	108.5	110.2	113.2	116.3	119.3	122.4	123.9	125.3	126.8	128.3	129.1
100°	139.8	141.2	144.1	147.0	149.9	152.7	154.7	156.7	158.7	160.7	162.0
102.5°	177.7	178.8	180.3	181.8	183.2	184.7	186.9	189.0	191.2	193.4	194.8
105°	232.1	233.3	234.6	235.9	237.3	238.6	239.9	241.3	242.6	243.9	244.9
107.5°	291.2	292.2	293.2	294.3	295.3	296.3	297.0	297.6	298.3	299.0	299.3
110°	331.9	332.8	333.4	334.1	334.8	335.4	336.1	336.8	337.4	338.1	338.3



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	371.3	372.0	372.9	373.7	374.5	375.4	375.7	376.0	376.3	376.6	376.6
115°	433.8	434.5	434.9	435.4	435.8	436.3	436.1	435.8	435.6	435.4	435.2
117.5°	493.4	493.8	494.2	494.6	495.0	495.4	495.6	495.7	495.9	496.1	495.7
120°	534.6	535.2	535.4	535.7	535.9	536.1	536.1	536.1	536.1	536.1	535.7
122.5°	573.3	573.7	574.3	574.9	575.5	576.0	575.9	575.7	575.5	575.3	574.9
125°	633.3	634.1	634.3	634.5	634.7	635.0	634.5	634.1	633.6	633.2	632.8
127.5°	690.9	691.4	691.7	691.9	692.2	692.5	692.2	692.0	691.8	691.6	691.2
130°	728.2	729.0	729.5	729.9	730.3	730.8	730.6	730.3	730.1	729.9	729.6
132.5°	767.0	767.9	767.8	767.7	767.6	767.5	767.3	767.1	766.9	766.6	766.2
135°	822.0	822.8	823.0	823.2	823.4	823.6	823.6	823.6	823.6	823.6	823.2
137.5°	875.3	876.2	876.7	877.2	877.7	878.1	878.4	878.7	878.9	879.2	878.8
140°	908.9	909.8	910.5	911.2	911.8	912.5	912.9	913.4	913.8	914.3	913.9
142.5°	942.6	943.5	944.3	945.2	946.0	946.8	947.1	947.4	947.6	947.9	947.5
145°	992.9	993.7	994.4	995.0	995.7	996.4	996.4	996.4	996.4	996.4	996.0
147.5°	1038.0	1038.6	1039.1	1039.6	1040.1	1040.7	1041.2	1041.7	1042.3	1042.8	1042.3
150°	1066.4	1066.7	1067.6	1068.5	1069.3	1070.2	1070.2	1070.2	1070.2	1070.2	1070.0
152.5°	1094.0	1094.4	1094.7	1095.1	1095.4	1095.8	1096.3	1096.9	1097.4	1097.9	1097.8
155°	1132.1	1132.2	1132.5	1132.7	1132.9	1133.1	1134.0	1134.9	1135.8	1136.7	1136.6
157.5°	1165.3	1165.2	1165.4	1165.6	1165.9	1166.1	1167.0	1167.8	1168.7	1169.6	1169.3
160°	1185.4	1185.2	1185.4	1185.6	1185.8	1186.0	1186.9	1187.8	1188.7	1189.6	1189.5
162.5°	1204.5	1204.2	1204.3	1204.3	1204.4	1204.4	1205.5	1206.5	1207.6	1208.7	1208.6
165°	1229.2	1229.1	1229.3	1229.5	1229.7	1230.0	1230.9	1231.7	1232.6	1233.5	1233.3
167.5°	1248.2	1247.7	1247.7	1247.7	1247.7	1247.7	1249.1	1250.4	1251.7	1253.1	1253.0
170°	1259.4	1258.9	1258.9	1258.9	1258.9	1258.9	1260.3	1261.6	1262.9	1264.2	1264.1
172.5°	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.2	1269.6	1270.9	1272.2	1272.2
175°	1276.3	1275.9	1275.9	1275.9	1275.9	1275.9	1277.2	1278.6	1279.9	1281.2	1281.1
177.5°	1281.6	1281.2	1281.0	1280.8	1280.7	1280.5	1281.6	1282.6	1283.7	1284.7	1284.7
180°	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1749.9	1754.2	1750.5	1755.5	1750.5	1754.2	1749.9	1753.6	1759.2	1755.5	1764.2
5°	1612.8	1605.8	1610.5	1607.4	1610.5	1605.8	1612.8	1616.7	1626.1	1629.2	1635.4
7.5°	1486.2	1479.5	1471.9	1468.3	1471.9	1479.5	1486.2	1488.6	1496.5	1508.2	1517.1
10°	1407.0	1398.5	1397.7	1392.2	1397.7	1398.5	1407.0	1415.6	1421.1	1435.9	1446.0
12.5°	1349.0	1341.1	1332.2	1329.9	1332.2	1341.1	1349.0	1356.4	1358.1	1374.8	1381.8
15°	1266.7	1260.5	1255.0	1259.7	1255.0	1260.5	1266.7	1271.4	1280.0	1291.7	1299.5
17.5°	1198.3	1193.1	1192.2	1186.4	1192.2	1193.1	1198.3	1200.9	1215.0	1222.6	1236.0
20°	1155.3	1151.4	1152.9	1142.8	1152.9	1151.4	1155.3	1162.3	1176.3	1180.2	1194.2
22.5°	1121.0	1113.3	1112.4	1110.4	1112.4	1113.3	1121.0	1127.3	1130.2	1142.2	1151.8
25°	1067.2	1063.3	1059.4	1063.3	1059.4	1063.3	1067.2	1074.2	1077.3	1085.9	1095.2
27.5°	1020.2	1015.6	1014.5	1014.9	1014.5	1015.6	1020.2	1019.6	1028.0	1034.9	1041.8
30°	991.6	983.8	984.5	983.8	984.5	983.8	991.6	991.6	996.2	1002.5	1008.7
32.5°	960.4	955.1	954.0	952.6	954.0	955.1	960.4	959.1	965.0	972.5	979.4
35°	914.4	914.4	910.5	910.5	910.5	914.4	914.4	916.7	923.0	923.0	930.7
37.5°	871.2	870.4	868.1	868.4	868.1	870.4	871.2	873.1	875.2	878.5	883.5
40°	838.8	838.0	835.6	831.0	835.6	838.0	838.8	841.9	843.4	847.3	850.5
42.5°	807.6	804.9	803.8	802.3	803.8	804.9	807.6	809.5	810.4	815.5	821.8
45°	758.5	758.5	756.9	756.1	756.9	758.5	758.5	758.5	759.3	765.5	768.6
47.5°	710.8	712.2	715.1	714.7	715.1	712.2	710.8	709.5	709.8	713.0	716.5
50°	682.1	682.9	685.2	686.0	685.2	682.9	682.1	679.0	677.4	677.4	679.7
52.5°	650.3	654.8	657.8	657.3	657.8	654.8	650.3	647.8	645.0	641.2	644.8
55°	605.7	611.1	616.6	617.4	616.6	611.1	605.7	598.7	595.6	589.3	591.7
57.5°	561.6	569.2	575.0	576.8	575.0	569.2	561.6	553.1	543.0	540.1	535.7
60°	531.6	541.8	548.8	551.9	548.8	541.8	531.6	523.8	510.6	502.0	498.9
62.5°	502.9	514.3	521.3	522.0	521.3	514.3	502.9	490.8	477.5	467.7	461.5
65°	456.0	467.7	473.9	478.6	473.9	467.7	456.0	442.8	428.0	414.7	407.7
67.5°	405.5	417.2	424.1	427.8	424.1	417.2	405.5	389.1	375.6	360.3	352.0
70°	368.7	380.4	389.8	392.9	389.8	380.4	368.7	349.2	337.5	323.5	316.5
72.5°	332.5	343.0	350.5	354.2	350.5	343.0	332.5	314.3	300.7	286.7	277.2
75°	269.7	283.7	290.8	294.7	290.8	283.7	269.7	259.6	244.0	229.2	221.4
77.5°	208.0	220.8	225.0	227.0	225.0	220.8	208.0	196.1	184.3	173.5	165.9
80°	166.8	174.6	180.1	180.8	180.1	174.6	166.8	157.5	148.1	138.0	131.0
82.5°	128.2	134.7	136.4	138.4	136.4	134.7	128.2	120.0	111.9	104.3	98.5
85°	70.2	73.3	74.1	73.3	74.1	73.3	70.2	64.7	60.8	56.9	54.6
87.5°	27.5	27.0	27.1	28.5	27.1	27.0	27.5	26.1	26.5	25.1	23.6
90°	22.0	22.6	23.3	24.0	23.3	22.6	22.0	21.3	20.4	19.3	18.2
92.5°	45.7	46.1	46.6	47.1	46.6	46.1	45.7	45.2	44.2	42.7	41.3
95°	84.5	85.0	85.4	85.9	85.4	85.0	84.5	84.1	83.1	81.5	80.0
97.5°	129.4	129.7	129.9	130.2	129.9	129.7	129.4	129.1	128.3	126.8	125.3
100°	162.4	162.8	163.3	163.7	163.3	162.8	162.4	162.0	160.7	158.7	156.7
102.5°	195.4	196.0	196.7	197.3	196.7	196.0	195.4	194.8	193.4	191.2	189.0
105°	245.6	246.3	246.9	247.6	246.9	246.3	245.6	244.9	243.9	242.6	241.3
107.5°	299.2	299.2	299.2	299.1	299.2	299.2	299.2	299.3	299.0	298.3	297.6
110°	338.1	337.9	337.7	337.4	337.7	337.9	338.1	338.3	338.1	337.4	336.8



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	376.2	375.8	375.4	375.0	375.4	375.8	376.2	376.6	376.6	376.3	376.0
115°	434.9	434.7	434.5	434.3	434.5	434.7	434.9	435.2	435.4	435.6	435.8
117.5°	494.8	494.0	493.1	492.2	493.1	494.0	494.8	495.7	496.1	495.9	495.7
120°	534.8	533.9	533.0	532.1	533.0	533.9	534.8	535.7	536.1	536.1	536.1
122.5°	574.2	573.5	572.8	572.1	572.8	573.5	574.2	574.9	575.3	575.5	575.7
125°	632.6	632.4	632.2	632.0	632.2	632.4	632.6	632.8	633.2	633.6	634.1
127.5°	690.8	690.3	689.9	689.5	689.9	690.3	690.8	691.2	691.6	691.8	692.0
130°	729.1	728.7	728.2	727.8	728.2	728.7	729.1	729.6	729.9	730.1	730.3
132.5°	765.6	765.0	764.4	763.7	764.4	765.0	765.6	766.2	766.6	766.9	767.1
135°	822.3	821.4	820.5	819.6	820.5	821.4	822.3	823.2	823.6	823.6	823.6
137.5°	877.7	876.6	875.5	874.4	875.5	876.6	877.7	878.8	879.2	878.9	878.7
140°	912.8	911.7	910.6	909.5	910.6	911.7	912.8	913.9	914.3	913.8	913.4
142.5°	946.4	945.3	944.2	943.0	944.2	945.3	946.4	947.5	947.9	947.6	947.4
145°	995.4	994.7	994.0	993.4	994.0	994.7	995.4	996.0	996.4	996.4	996.4
147.5°	1040.8	1039.3	1037.8	1036.3	1037.8	1039.3	1040.8	1042.3	1042.8	1042.3	1041.7
150°	1069.6	1069.1	1068.7	1068.2	1068.7	1069.1	1069.6	1070.0	1070.2	1070.2	1070.2
152.5°	1097.0	1096.2	1095.4	1094.6	1095.4	1096.2	1097.0	1097.8	1097.9	1097.4	1096.9
155°	1135.5	1134.3	1133.2	1132.1	1133.2	1134.3	1135.5	1136.6	1136.7	1135.8	1134.9
157.5°	1167.9	1166.4	1164.9	1163.5	1164.9	1166.4	1167.9	1169.3	1169.6	1168.7	1167.8
160°	1188.4	1187.3	1186.2	1185.0	1186.2	1187.3	1188.4	1189.5	1189.6	1188.7	1187.8
162.5°	1207.3	1206.0	1204.7	1203.4	1204.7	1206.0	1207.3	1208.6	1208.7	1207.6	1206.5
165°	1232.0	1230.6	1229.3	1228.0	1229.3	1230.6	1232.0	1233.3	1233.5	1232.6	1231.7
167.5°	1251.7	1250.3	1248.9	1247.5	1248.9	1250.3	1251.7	1253.0	1253.1	1251.7	1250.4
170°	1262.6	1261.0	1259.5	1257.9	1259.5	1261.0	1262.6	1264.1	1264.2	1262.9	1261.6
172.5°	1270.8	1269.5	1268.1	1266.7	1268.1	1269.5	1270.8	1272.2	1272.2	1270.9	1269.6
175°	1279.6	1278.0	1276.4	1274.9	1276.4	1278.0	1279.6	1281.1	1281.2	1279.9	1278.6
177.5°	1283.4	1282.2	1280.9	1279.7	1280.9	1282.2	1283.4	1284.7	1284.7	1283.7	1282.6
180°	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1756.1	1763.6	1772.9	1779.8	1792.3	1797.9	1804.7	1810.4	1820.3	1829.7	1840.9
5°	1637.8	1651.0	1669.0	1688.4	1711.1	1726.6	1748.5	1761.7	1788.2	1812.4	1835.8
7.5°	1530.5	1546.7	1572.1	1597.1	1626.7	1653.5	1680.8	1711.1	1744.9	1784.8	1817.8
10°	1456.9	1478.8	1506.0	1537.2	1573.1	1604.3	1640.9	1673.6	1714.9	1761.7	1805.4
12.5°	1398.3	1417.0	1447.4	1477.4	1515.7	1553.7	1591.6	1635.0	1683.1	1734.9	1789.8
15°	1317.4	1333.0	1357.9	1399.2	1438.2	1475.6	1532.5	1573.1	1633.9	1691.6	1757.8
17.5°	1248.3	1267.7	1288.7	1324.1	1364.5	1411.2	1462.1	1512.9	1571.5	1644.6	1719.3
20°	1205.9	1221.5	1245.7	1273.0	1315.8	1362.6	1410.9	1462.4	1534.1	1609.7	1690.0
22.5°	1159.8	1176.6	1203.9	1233.7	1269.7	1314.6	1367.9	1424.3	1499.2	1573.5	1660.7
25°	1105.4	1117.1	1142.0	1168.5	1204.4	1242.6	1297.9	1360.3	1434.3	1519.3	1608.2
27.5°	1054.1	1064.4	1087.1	1110.2	1142.6	1188.0	1237.4	1300.4	1370.2	1456.3	1554.8
30°	1017.3	1028.2	1048.5	1073.4	1104.6	1144.3	1195.0	1254.3	1329.1	1413.3	1516.2
32.5°	985.5	995.1	1010.4	1035.4	1065.9	1104.4	1151.4	1211.8	1286.7	1372.1	1473.1
35°	936.2	947.1	958.8	978.3	1004.8	1042.2	1093.7	1150.6	1222.3	1304.9	1397.7
37.5°	887.3	899.1	909.5	927.0	951.2	984.2	1028.7	1087.9	1152.8	1232.4	1321.4
40°	856.7	866.0	874.6	893.3	917.5	948.7	990.0	1043.0	1111.6	1185.7	1259.7
42.5°	826.1	834.9	842.2	858.4	880.7	910.6	950.1	1001.8	1065.5	1134.5	1199.8
45°	778.0	783.4	792.0	806.0	824.0	851.2	889.4	935.4	989.2	1054.7	1103.8
47.5°	725.9	734.5	741.5	753.8	768.5	795.3	831.9	871.0	919.8	968.5	1003.1
50°	686.0	694.6	704.7	716.4	730.4	755.4	788.9	828.6	869.9	907.4	937.0
52.5°	648.6	656.5	667.3	678.3	695.5	716.7	745.2	780.6	821.3	848.1	872.8
55°	593.2	597.1	609.6	620.5	636.9	652.5	681.3	712.5	737.4	757.7	778.0
57.5°	536.6	541.9	549.1	558.9	575.1	593.4	613.6	641.2	655.9	666.3	682.1
60°	500.5	502.0	506.7	518.4	530.9	547.2	570.6	590.1	601.0	609.6	622.8
62.5°	460.5	460.9	468.6	477.2	486.6	504.2	523.2	539.0	548.0	552.2	564.8
65°	404.6	403.0	407.7	414.7	425.6	437.3	453.7	467.7	466.9	471.6	479.4
67.5°	347.4	345.8	345.8	352.5	361.4	371.8	383.1	391.2	391.3	397.6	401.5
70°	308.7	304.0	307.1	312.6	316.5	325.1	337.5	340.7	341.4	344.5	348.4
72.5°	268.8	267.2	269.7	272.1	274.7	281.4	292.0	293.9	294.0	295.9	302.3
75°	213.6	212.0	210.5	212.8	215.9	220.6	224.5	227.6	226.8	227.6	232.3
77.5°	160.1	155.7	155.0	156.2	157.0	159.8	163.9	163.5	164.3	164.2	169.5
80°	127.1	120.8	120.0	120.0	120.8	122.4	123.9	125.5	123.2	125.5	127.1
82.5°	93.4	89.6	89.5	88.9	89.0	89.3	90.3	91.2	90.7	91.8	92.8
85°	51.4	49.9	47.6	49.1	48.3	46.0	47.6	45.2	44.4	45.2	46.0
87.5°	20.9	21.3	19.7	19.4	18.5	18.8	17.2	16.2	15.3	15.5	17.0
90°	17.1	16.0	14.4	12.9	11.3	9.8	8.1	6.3	4.5	2.8	1.0
92.5°	39.8	38.3	36.4	34.5	32.6	30.7	29.1	27.9	26.6	25.4	24.2
95°	78.4	76.9	74.7	72.4	70.2	68.0	66.7	66.2	65.8	65.3	64.9
97.5°	123.9	122.4	119.3	116.3	113.2	110.2	108.5	108.4	108.2	108.0	107.8
100°	154.7	152.7	149.9	147.0	144.1	141.2	139.8	139.8	139.8	139.8	139.8
102.5°	186.9	184.7	183.2	181.8	180.3	178.8	177.7	176.8	175.9	175.0	174.1
105°	239.9	238.6	237.3	235.9	234.6	233.3	232.1	231.0	229.8	228.7	227.6
107.5°	297.0	296.3	295.3	294.3	293.2	292.2	291.2	290.1	288.9	287.8	286.7
110°	336.1	335.4	334.8	334.1	333.4	332.8	331.9	330.8	329.7	328.6	327.5



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	375.7	375.4	374.5	373.7	372.9	372.0	371.3	370.7	370.1	369.6	369.0
115°	436.1	436.3	435.8	435.4	434.9	434.5	433.8	433.0	432.1	431.2	430.3
117.5°	495.6	495.4	495.0	494.6	494.2	493.8	493.4	493.0	492.6	492.2	491.8
120°	536.1	536.1	535.9	535.7	535.4	535.2	534.6	533.5	532.3	531.2	530.1
122.5°	575.9	576.0	575.5	574.9	574.3	573.7	573.3	572.9	572.5	572.1	571.7
125°	634.5	635.0	634.7	634.5	634.3	634.1	633.3	632.0	630.6	629.3	628.0
127.5°	692.2	692.5	692.2	691.9	691.7	691.4	690.9	690.1	689.4	688.6	687.9
130°	730.6	730.8	730.3	729.9	729.5	729.0	728.2	727.1	726.0	724.9	723.8
132.5°	767.3	767.5	767.6	767.7	767.8	767.9	767.0	765.2	763.4	761.6	759.7
135°	823.6	823.6	823.4	823.2	823.0	822.8	822.0	820.6	819.3	818.0	816.7
137.5°	878.4	878.1	877.7	877.2	876.7	876.2	875.3	874.0	872.7	871.4	870.2
140°	912.9	912.5	911.8	911.2	910.5	909.8	908.9	907.8	906.7	905.6	904.5
142.5°	947.1	946.8	946.0	945.2	944.3	943.5	942.6	941.6	940.7	939.8	938.8
145°	996.4	996.4	995.7	995.0	994.4	993.7	992.9	992.0	991.1	990.3	989.4
147.5°	1041.2	1040.7	1040.1	1039.6	1039.1	1038.6	1038.0	1037.6	1037.1	1036.6	1036.1
150°	1070.2	1070.2	1069.3	1068.5	1067.6	1066.7	1066.4	1066.6	1066.8	1067.0	1067.2
152.5°	1096.3	1095.8	1095.4	1095.1	1094.7	1094.4	1094.0	1093.7	1093.4	1093.1	1092.8
155°	1134.0	1133.1	1132.9	1132.7	1132.5	1132.2	1132.1	1132.1	1132.1	1132.1	1132.1
157.5°	1167.0	1166.1	1165.9	1165.6	1165.4	1165.2	1165.3	1165.8	1166.3	1166.8	1167.3
160°	1186.9	1186.0	1185.8	1185.6	1185.4	1185.2	1185.4	1186.0	1186.7	1187.4	1188.0
162.5°	1205.5	1204.4	1204.4	1204.3	1204.3	1204.2	1204.5	1204.9	1205.4	1205.9	1206.4
165°	1230.9	1230.0	1229.7	1229.5	1229.3	1229.1	1229.2	1229.6	1230.1	1230.5	1231.0
167.5°	1249.1	1247.7	1247.7	1247.7	1247.7	1247.7	1248.2	1249.1	1250.0	1250.8	1251.7
170°	1260.3	1258.9	1258.9	1258.9	1258.9	1258.9	1259.4	1260.3	1261.1	1262.0	1262.9
172.5°	1268.2	1266.9	1266.9	1266.9	1266.9	1266.9	1267.4	1268.2	1269.1	1270.0	1270.9
175°	1277.2	1275.9	1275.9	1275.9	1275.9	1275.9	1276.3	1277.2	1278.1	1279.0	1279.9
177.5°	1281.6	1280.5	1280.7	1280.8	1281.0	1281.2	1281.6	1282.3	1283.1	1283.8	1284.5
180°	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1846.5	1855.3	1860.9	1871.5	1880.2	1885.2	1889.6	1893.3	1897.7	1901.4	1912.0
5°	1858.4	1878.6	1895.8	1922.3	1946.5	1965.2	1985.4	2003.4	2018.2	2039.2	2055.6
7.5°	1853.2	1889.2	1927.0	1968.0	2009.9	2048.9	2084.8	2118.3	2148.7	2185.5	2217.7
10°	1848.2	1897.4	1945.7	2001.0	2057.9	2106.3	2151.5	2197.5	2231.0	2277.8	2317.5
12.5°	1844.5	1902.3	1960.7	2027.2	2089.7	2158.0	2218.2	2251.7	2302.7	2340.1	2387.4
15°	1828.8	1905.2	1985.4	2060.3	2149.1	2212.3	2265.3	2330.8	2378.3	2425.9	2477.3
17.5°	1800.5	1887.1	1976.9	2074.9	2160.2	2228.0	2296.3	2359.5	2416.2	2480.0	2544.0
20°	1787.4	1874.0	1976.9	2077.4	2160.8	2231.8	2301.9	2371.3	2433.7	2515.5	2589.6
22.5°	1760.0	1864.6	1959.4	2057.5	2143.4	2220.5	2300.1	2378.8	2461.7	2554.2	2646.9
25°	1711.1	1817.1	1917.6	2014.3	2100.8	2197.5	2282.4	2387.7	2493.7	2616.1	2731.4
27.5°	1660.2	1761.7	1853.9	1947.2	2048.1	2157.6	2267.8	2387.2	2526.0	2680.5	2843.2
30°	1619.1	1714.9	1804.6	1900.5	2005.7	2128.9	2249.7	2391.6	2552.2	2726.0	2919.3
32.5°	1571.0	1659.4	1746.6	1848.1	1962.7	2092.7	2233.5	2389.1	2582.1	2779.6	2978.6
35°	1488.9	1562.9	1652.6	1760.9	1890.3	2039.2	2202.2	2386.1	2607.5	2834.3	3001.9
37.5°	1391.4	1460.4	1554.8	1673.6	1809.3	1969.1	2162.4	2380.7	2615.8	2796.6	2850.7
40°	1326.0	1389.9	1488.1	1611.3	1750.0	1919.2	2131.2	2362.0	2589.6	2704.9	2660.5
42.5°	1256.1	1323.2	1418.9	1540.8	1690.2	1874.3	2091.9	2322.7	2513.5	2557.1	2403.6
45°	1145.9	1215.3	1309.6	1432.8	1593.3	1792.9	2019.7	2229.4	2339.3	2260.6	2022.9
47.5°	1043.5	1108.5	1195.9	1323.0	1488.7	1695.1	1913.6	2080.9	2089.6	1901.7	1647.8
50°	973.6	1033.6	1121.7	1248.8	1413.3	1622.2	1819.4	1951.1	1891.9	1679.1	1435.1
52.5°	905.0	963.8	1050.6	1176.5	1339.1	1530.5	1714.0	1806.5	1694.8	1476.4	1268.0
55°	806.0	857.5	942.4	1058.6	1212.9	1390.7	1546.6	1578.5	1433.5	1218.4	1049.2
57.5°	709.4	757.4	834.7	941.7	1082.8	1240.2	1362.1	1355.3	1202.0	1017.4	883.2
60°	643.9	690.7	759.3	863.7	992.3	1128.0	1232.4	1207.5	1055.5	896.5	783.4
62.5°	585.3	627.0	691.9	783.3	900.7	1026.3	1112.1	1075.3	926.4	787.3	698.0
65°	498.9	534.0	589.3	667.3	764.7	868.4	934.6	887.1	760.0	651.7	580.0
67.5°	416.4	444.5	490.9	553.1	636.2	719.5	759.9	712.0	610.4	531.3	478.2
70°	364.0	389.0	424.8	480.2	552.7	622.8	653.2	610.4	523.1	455.2	417.0
72.5°	311.7	332.2	363.7	413.5	471.6	532.4	559.1	518.1	446.4	389.1	353.4
75°	240.9	254.9	276.7	311.0	357.0	405.4	420.2	384.3	338.3	295.4	272.1
77.5°	172.4	184.3	200.8	222.5	255.1	285.8	298.7	278.0	242.4	215.3	196.1
80°	132.5	138.8	152.8	170.7	196.4	215.9	224.5	211.3	186.3	166.0	151.2
82.5°	94.5	100.7	109.1	123.9	140.3	153.6	162.8	153.9	135.8	119.9	111.3
85°	46.0	49.9	54.6	60.8	73.3	81.1	80.3	74.8	67.8	61.6	56.9
87.5°	16.8	17.7	20.0	23.4	25.6	28.5	30.0	29.1	26.9	25.2	23.6
90°	2.8	4.5	6.3	8.1	9.8	11.3	12.9	14.4	16.0	17.1	18.2
92.5°	25.4	26.6	27.9	29.1	30.7	32.6	34.5	36.4	38.3	39.8	41.3
95°	65.3	65.8	66.2	66.7	68.0	70.2	72.4	74.7	76.9	78.4	80.0
97.5°	108.0	108.2	108.4	108.5	110.2	113.2	116.3	119.3	122.4	123.9	125.3
100°	139.8	139.8	139.8	139.8	141.2	144.1	147.0	149.9	152.7	154.7	156.7
102.5°	175.0	175.9	176.8	177.7	178.8	180.3	181.8	183.2	184.7	186.9	189.0
105°	228.7	229.8	231.0	232.1	233.3	234.6	235.9	237.3	238.6	239.9	241.3
107.5°	287.8	288.9	290.1	291.2	292.2	293.2	294.3	295.3	296.3	297.0	297.6
110°	328.6	329.7	330.8	331.9	332.8	333.4	334.1	334.8	335.4	336.1	336.8



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	369.6	370.1	370.7	371.3	372.0	372.9	373.7	374.5	375.4	375.7	376.0
115°	431.2	432.1	433.0	433.8	434.5	434.9	435.4	435.8	436.3	436.1	435.8
117.5°	492.2	492.6	493.0	493.4	493.8	494.2	494.6	495.0	495.4	495.6	495.7
120°	531.2	532.3	533.5	534.6	535.2	535.4	535.7	535.9	536.1	536.1	536.1
122.5°	572.1	572.5	572.9	573.3	573.7	574.3	574.9	575.5	576.0	575.9	575.7
125°	629.3	630.6	632.0	633.3	634.1	634.3	634.5	634.7	635.0	634.5	634.1
127.5°	688.6	689.4	690.1	690.9	691.4	691.7	691.9	692.2	692.5	692.2	692.0
130°	724.9	726.0	727.1	728.2	729.0	729.5	729.9	730.3	730.8	730.6	730.3
132.5°	761.6	763.4	765.2	767.0	767.9	767.8	767.7	767.6	767.5	767.3	767.1
135°	818.0	819.3	820.6	822.0	822.8	823.0	823.2	823.4	823.6	823.6	823.6
137.5°	871.4	872.7	874.0	875.3	876.2	876.7	877.2	877.7	878.1	878.4	878.7
140°	905.6	906.7	907.8	908.9	909.8	910.5	911.2	911.8	912.5	912.9	913.4
142.5°	939.8	940.7	941.6	942.6	943.5	944.3	945.2	946.0	946.8	947.1	947.4
145°	990.3	991.1	992.0	992.9	993.7	994.4	995.0	995.7	996.4	996.4	996.4
147.5°	1036.6	1037.1	1037.6	1038.0	1038.6	1039.1	1039.6	1040.1	1040.7	1041.2	1041.7
150°	1067.0	1066.8	1066.6	1066.4	1066.7	1067.6	1068.5	1069.3	1070.2	1070.2	1070.2
152.5°	1093.1	1093.4	1093.7	1094.0	1094.4	1094.7	1095.1	1095.4	1095.8	1096.3	1096.9
155°	1132.1	1132.1	1132.1	1132.1	1132.2	1132.5	1132.7	1132.9	1133.1	1134.0	1134.9
157.5°	1166.8	1166.3	1165.8	1165.3	1165.2	1165.4	1165.6	1165.9	1166.1	1167.0	1167.8
160°	1187.4	1186.7	1186.0	1185.4	1185.2	1185.4	1185.6	1185.8	1186.0	1186.9	1187.8
162.5°	1205.9	1205.4	1204.9	1204.5	1204.2	1204.3	1204.3	1204.4	1204.4	1205.5	1206.5
165°	1230.5	1230.1	1229.6	1229.2	1229.1	1229.3	1229.5	1229.7	1230.0	1230.9	1231.7
167.5°	1250.8	1250.0	1249.1	1248.2	1247.7	1247.7	1247.7	1247.7	1247.7	1249.1	1250.4
170°	1262.0	1261.1	1260.3	1259.4	1258.9	1258.9	1258.9	1258.9	1258.9	1260.3	1261.6
172.5°	1270.0	1269.1	1268.2	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.2	1269.6
175°	1279.0	1278.1	1277.2	1276.3	1275.9	1275.9	1275.9	1275.9	1275.9	1277.2	1278.6
177.5°	1283.8	1283.1	1282.3	1281.6	1281.2	1281.0	1280.8	1280.7	1280.5	1281.6	1282.6
180°	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1920.7	1925.7	1936.3	1932.6	1937.6	1940.1	1942.6
5°	2075.9	2100.8	2111.7	2110.2	2126.5	2122.6	2118.7
7.5°	2251.1	2277.3	2292.0	2310.2	2320.8	2321.6	2330.8
10°	2350.3	2384.6	2398.6	2418.1	2430.6	2437.6	2436.8
12.5°	2426.3	2453.2	2484.6	2494.2	2511.0	2519.9	2516.6
15°	2517.9	2560.7	2593.5	2609.8	2630.9	2637.1	2645.7
17.5°	2599.6	2657.1	2695.3	2746.1	2765.3	2777.0	2770.1
20°	2661.3	2736.9	2775.1	2835.9	2869.4	2887.4	2881.1
22.5°	2734.3	2816.1	2886.7	2939.4	2990.4	3014.6	3019.6
25°	2859.3	2971.5	3075.2	3144.6	3207.7	3222.5	3255.3
27.5°	2999.0	3131.3	3242.2	3315.2	3359.1	3375.6	3385.9
30°	3086.9	3218.6	3302.1	3348.8	3362.9	3361.3	3359.7
32.5°	3129.9	3212.4	3228.5	3215.4	3183.3	3156.1	3127.8
35°	3069.0	3007.4	2915.4	2796.9	2709.6	2621.5	2613.0
37.5°	2760.1	2563.2	2410.1	2239.1	2140.4	2079.5	2037.4
40°	2469.5	2245.8	2060.3	1916.1	1815.5	1775.8	1736.8
42.5°	2154.0	1940.2	1775.9	1655.4	1579.8	1535.7	1504.8
45°	1750.0	1561.4	1432.8	1345.5	1285.4	1251.1	1231.6
47.5°	1434.0	1294.5	1185.2	1122.2	1080.7	1054.1	1054.2
50°	1264.4	1131.1	1058.6	1008.7	972.8	951.8	955.7
52.5°	1114.1	1014.5	952.6	910.8	884.3	871.3	870.9
55°	931.5	859.8	819.3	788.9	770.9	756.1	759.3
57.5°	796.8	736.3	709.2	684.0	671.5	665.6	657.0
60°	713.3	666.5	643.1	622.8	610.4	605.7	597.1
62.5°	639.1	602.3	579.5	563.0	551.7	550.2	543.5
65°	537.1	509.0	488.8	481.0	469.3	466.2	466.2
67.5°	442.8	422.7	406.9	399.7	394.6	395.4	391.6
70°	383.5	367.2	357.0	349.2	345.3	346.1	343.0
72.5°	335.5	317.3	308.4	303.7	298.6	300.6	299.3
75°	254.1	244.8	240.1	235.4	232.3	230.7	229.2
77.5°	186.6	178.4	174.8	172.1	172.6	168.8	171.8
80°	144.2	137.2	134.9	131.0	130.2	130.2	129.4
82.5°	105.5	101.6	99.9	96.7	95.3	96.5	94.5
85°	54.6	51.4	50.7	50.7	49.1	47.6	51.4
87.5°	23.8	21.5	21.7	21.2	21.4	20.9	19.8
90°	19.3	20.4	21.3	22.0	22.6	23.3	24.0
92.5°	42.7	44.2	45.2	45.7	46.1	46.6	47.1
95°	81.5	83.1	84.1	84.5	85.0	85.4	85.9
97.5°	126.8	128.3	129.1	129.4	129.7	129.9	130.2
100°	158.7	160.7	162.0	162.4	162.8	163.3	163.7
102.5°	191.2	193.4	194.8	195.4	196.0	196.7	197.3
105°	242.6	243.9	244.9	245.6	246.3	246.9	247.6
107.5°	298.3	299.0	299.3	299.2	299.2	299.2	299.1
110°	337.4	338.1	338.3	338.1	337.9	337.7	337.4



TEST NUMBER: P333323

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	376.3	376.6	376.6	376.2	375.8	375.4	375.0
115°	435.6	435.4	435.2	434.9	434.7	434.5	434.3
117.5°	495.9	496.1	495.7	494.8	494.0	493.1	492.2
120°	536.1	536.1	535.7	534.8	533.9	533.0	532.1
122.5°	575.5	575.3	574.9	574.2	573.5	572.8	572.1
125°	633.6	633.2	632.8	632.6	632.4	632.2	632.0
127.5°	691.8	691.6	691.2	690.8	690.3	689.9	689.5
130°	730.1	729.9	729.6	729.1	728.7	728.2	727.8
132.5°	766.9	766.6	766.2	765.6	765.0	764.4	763.7
135°	823.6	823.6	823.2	822.3	821.4	820.5	819.6
137.5°	878.9	879.2	878.8	877.7	876.6	875.5	874.4
140°	913.8	914.3	913.9	912.8	911.7	910.6	909.5
142.5°	947.6	947.9	947.5	946.4	945.3	944.2	943.0
145°	996.4	996.4	996.0	995.4	994.7	994.0	993.4
147.5°	1042.3	1042.8	1042.3	1040.8	1039.3	1037.8	1036.3
150°	1070.2	1070.2	1070.0	1069.6	1069.1	1068.7	1068.2
152.5°	1097.4	1097.9	1097.8	1097.0	1096.2	1095.4	1094.6
155°	1135.8	1136.7	1136.6	1135.5	1134.3	1133.2	1132.1
157.5°	1168.7	1169.6	1169.3	1167.9	1166.4	1164.9	1163.5
160°	1188.7	1189.6	1189.5	1188.4	1187.3	1186.2	1185.0
162.5°	1207.6	1208.7	1208.6	1207.3	1206.0	1204.7	1203.4
165°	1232.6	1233.5	1233.3	1232.0	1230.6	1229.3	1228.0
167.5°	1251.7	1253.1	1253.0	1251.7	1250.3	1248.9	1247.5
170°	1262.9	1264.2	1264.1	1262.6	1261.0	1259.5	1257.9
172.5°	1270.9	1272.2	1272.2	1270.8	1269.5	1268.1	1266.7
175°	1279.9	1281.2	1281.1	1279.6	1278.0	1276.4	1274.9
177.5°	1283.7	1284.7	1284.7	1283.4	1282.2	1280.9	1279.7
180°	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9

(END OF REPORT)