

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333312-940

Luminaire Tested: **S125DIP-S1270D590U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333312-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D590U940-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6466.3 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333312-940

CATALOG NUMBER: S125DIP-S1270D590U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333312-940

CATALOG NUMBER: S125DIP-S1270D590U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	65	63	59
2	93	85	79	74	88	81	75	71	73	68	64	65	62	59	58	56	53	50
3	85	75	67	61	80	71	64	59	64	59	54	58	53	50	52	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39	36
5	72	59	51	45	67	57	49	43	51	45	40	46	41	37	42	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	37	32	38	33	30	27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	35	30	27	24
8	57	44	36	30	54	42	35	30	38	32	28	35	30	26	32	27	24	22
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	22	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11349	11349	11349
5°	11374	11267	11339
10°	11305	11187	11252
15°	11183	11053	11099
20°	11008	10864	10883
25°	10819	10641	10630
30°	10586	10399	10347
35°	10336	10139	9996
40°	10080	9857	9716
45°	9803	9600	9409
50°	9499	9289	9010
55°	9205	8939	8688
60°	8853	8584	8280
65°	8436	8159	7882
70°	8033	7666	7404
75°	7321	7079	6832
80°	6512	6412	6259
85°	5669	5765	5461



TEST NUMBER: P333312-940

CATALOG NUMBER: S125DIP-S1270D590U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.7	2.6
10°-20°	468.1	7.2
20°-30°	691.1	10.7
30°-40°	806.4	12.5
40°-50°	809.9	12.5
50°-60°	710.9	11.0
60°-70°	529.7	8.2
70°-80°	302.9	4.7
80°-90°	89.5	1.4
90°-100°	182.9	2.8
100°-110°	393.1	6.1
110°-120°	369.0	5.7
120°-130°	299.0	4.6
130°-140°	240.0	3.7
140°-150°	181.1	2.8
150°-160°	127.5	2.0
160°-170°	75.1	1.2
170°-180°	24.4	0.4
0°-30°	1324.8	20.5
0°-40°	2131.2	33.0
0°-60°	3652.1	56.5
0°-90°	4574.3	70.7
90°-120°	945.0	14.6
90°-150°	1665.0	25.7
90°-180°	1892.0	29.3
0°-180°	6466.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1757	1757	1757	1757	1757	
5°	1754	1751	1738	1750	1749	166
15°	1672	1668	1653	1660	1660	471
25°	1518	1511	1493	1496	1492	698
35°	1311	1305	1286	1279	1268	820
45°	1073	1067	1051	1035	1030	827
55°	818	812	794	781	772	730
65°	552	548	534	522	516	548
75°	293	290	284	279	274	313
85°	76	78	78	76	74	85
90°	0	5	8	11	12	5
95°	17	50	451	205	120	18
105°	58	80	369	726	674	61
115°	103	124	296	638	751	101
125°	142	167	284	508	592	126
135°	167	201	282	426	491	129
145°	194	223	283	352	388	122
155°	222	239	276	312	325	102
165°	242	249	264	281	285	68
175°	252	252	254	257	256	24
180°	252	252	252	252	252	



TEST NUMBER: P333312-940

CATALOG NUMBER: S125DIP-S1270D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3
2.5°	1761.8	1761.0	1760.3	1759.5	1758.8	1757.2	1754.7	1752.2	1749.8	1747.3	1749.8
5°	1754.5	1753.9	1753.3	1752.7	1752.0	1750.2	1747.1	1744.0	1741.0	1737.9	1740.6
7.5°	1738.4	1737.8	1737.1	1736.5	1735.9	1733.9	1730.5	1727.2	1723.8	1720.4	1723.1
10°	1723.9	1723.3	1722.7	1722.1	1721.4	1719.5	1716.1	1712.7	1709.2	1705.8	1708.3
12.5°	1706.1	1705.0	1704.0	1702.8	1701.7	1699.6	1696.4	1693.3	1690.1	1686.9	1689.0
15°	1672.5	1671.6	1670.6	1669.7	1668.8	1666.6	1663.2	1659.8	1656.4	1653.1	1654.6
17.5°	1633.9	1632.5	1631.1	1629.8	1628.4	1625.9	1622.5	1618.9	1615.4	1611.9	1613.8
20°	1601.6	1601.0	1600.4	1599.7	1599.1	1596.8	1592.8	1588.8	1584.7	1580.7	1582.9
22.5°	1569.3	1568.3	1567.1	1566.0	1564.9	1562.5	1558.7	1555.0	1551.1	1547.4	1548.8
25°	1518.2	1516.6	1515.1	1513.6	1512.0	1509.2	1505.2	1501.2	1497.2	1493.2	1493.8
27.5°	1458.4	1457.5	1456.5	1455.6	1454.7	1452.2	1448.0	1443.9	1439.8	1435.6	1435.7
30°	1419.5	1418.5	1417.6	1416.7	1415.8	1413.0	1408.4	1403.7	1399.1	1394.5	1393.8
32.5°	1377.2	1375.8	1374.4	1373.0	1371.5	1368.8	1364.6	1360.5	1356.3	1352.2	1351.1
35°	1311.0	1309.8	1308.6	1307.3	1306.1	1303.3	1299.0	1294.7	1290.3	1286.0	1284.5
37.5°	1242.3	1240.8	1239.3	1237.7	1236.2	1233.3	1229.3	1225.2	1221.1	1217.1	1214.8
40°	1195.6	1194.1	1192.6	1191.0	1189.5	1186.5	1182.2	1177.9	1173.6	1169.2	1166.4
42.5°	1145.6	1144.3	1143.0	1141.7	1140.4	1137.6	1133.3	1128.9	1124.6	1120.3	1117.8
45°	1073.3	1072.1	1070.9	1069.6	1068.4	1065.9	1062.2	1058.5	1054.8	1051.1	1047.3
47.5°	995.4	995.5	995.6	995.6	995.7	993.5	989.1	984.6	980.2	975.7	972.0
50°	945.4	944.5	943.5	942.6	941.6	939.3	935.7	931.9	928.3	924.5	920.5
52.5°	894.2	893.6	892.9	892.2	891.5	889.2	885.2	881.3	877.4	873.3	869.9
55°	817.5	816.5	815.6	814.7	813.8	811.2	806.8	802.5	798.2	793.9	791.0
57.5°	736.6	736.1	735.6	735.1	734.6	732.5	728.9	725.2	721.6	717.9	714.3
60°	685.4	684.2	683.0	681.7	680.5	678.1	674.8	671.4	668.0	664.6	661.5
62.5°	632.0	631.1	630.1	629.0	628.0	626.2	623.2	620.3	617.4	614.5	611.2
65°	552.0	551.3	550.7	550.1	549.5	547.4	544.0	540.6	537.3	533.9	531.1
67.5°	474.4	473.1	471.8	470.5	469.2	467.3	464.8	462.2	459.7	457.1	454.8
70°	425.4	423.9	422.3	420.8	419.3	417.1	414.3	411.5	408.8	406.0	404.1
72.5°	372.0	371.0	370.0	368.9	367.8	366.4	364.6	362.8	361.1	359.3	357.1
75°	293.4	292.7	292.1	291.5	290.9	289.8	288.3	286.7	285.2	283.7	282.7
77.5°	220.8	220.5	220.3	220.1	219.8	219.3	218.4	217.5	216.6	215.8	215.3
80°	175.1	175.1	175.1	175.1	175.1	174.9	174.2	173.6	173.0	172.4	172.1
82.5°	135.1	134.6	134.1	133.7	133.1	132.9	132.7	132.6	132.5	132.3	131.8
85°	76.5	76.8	77.0	77.4	77.7	77.8	77.8	77.8	77.8	77.8	77.6
87.5°	30.1	30.2	30.4	30.7	30.9	30.9	30.8	30.8	30.6	30.6	30.7
90°	0.5	1.0	2.1	3.0	4.1	5.1	5.6	6.6	7.1	8.1	8.6
92.5°	6.2	7.5	11.8	18.1	26.8	41.7	69.5	116.1	166.7	164.0	132.8
95°	16.8	17.3	21.4	26.9	38.2	61.1	115.5	227.4	367.7	450.7	441.0
97.5°	27.9	28.4	31.3	36.9	47.0	63.5	99.5	181.5	328.4	481.3	558.0
100°	35.6	36.6	38.7	44.2	53.9	69.2	98.7	164.8	293.0	459.3	586.5
102.5°	44.1	44.8	46.4	52.4	61.3	76.1	102.4	157.9	266.1	420.6	569.4
105°	57.5	57.5	60.0	65.1	73.2	87.5	109.9	155.2	240.0	368.8	514.8
107.5°	70.5	71.5	73.9	78.1	86.6	99.4	121.1	159.8	229.1	333.1	459.1
110°	79.9	80.9	82.9	87.5	95.1	108.3	129.2	164.3	225.9	316.4	427.3



TEST NUMBER: P333312-940

CATALOG NUMBER: S125DIP-S1270D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	89.3	90.2	91.8	96.5	104.1	116.9	137.0	170.0	225.9	306.7	403.7
115°	102.7	103.8	105.3	109.9	117.5	130.2	149.0	178.5	227.4	296.0	377.9
117.5°	114.9	116.5	118.2	122.7	131.3	143.7	161.5	188.3	230.7	290.9	362.6
120°	123.1	124.7	126.6	131.3	139.9	152.6	170.4	194.8	234.0	288.4	354.0
122.5°	131.6	132.8	134.4	138.9	148.5	161.1	179.0	202.2	236.8	286.4	346.7
125°	142.4	143.5	146.0	150.5	160.2	173.4	190.2	212.1	241.7	283.8	336.7
127.5°	150.9	152.4	155.7	161.5	171.7	184.9	201.1	221.2	247.0	282.6	327.6
130°	156.1	157.7	161.8	168.4	179.1	192.3	208.0	227.4	250.3	281.8	321.5
132.5°	160.2	162.2	167.0	174.5	185.6	198.8	214.5	232.6	254.0	281.8	316.6
135°	166.8	168.9	175.0	183.2	193.8	207.5	223.3	240.0	258.9	281.8	310.8
137.5°	175.2	176.7	182.4	190.6	201.0	215.2	229.5	245.6	263.5	282.4	305.6
140°	180.0	181.6	187.7	195.8	205.5	219.3	234.0	249.2	265.6	282.9	303.2
142.5°	185.7	186.9	192.6	200.7	210.0	222.9	236.8	251.3	266.7	283.2	301.1
145°	194.3	195.3	200.4	207.5	216.7	228.4	241.7	254.3	268.0	282.9	298.1
147.5°	203.2	203.8	208.2	214.8	222.7	233.1	244.7	256.2	268.6	281.5	294.9
150°	208.6	209.6	213.1	219.7	226.9	235.5	246.7	257.3	268.6	280.3	292.5
152.5°	214.3	214.8	218.0	223.8	230.5	238.4	248.7	258.2	268.1	278.7	289.6
155°	221.8	221.8	224.8	229.9	235.0	242.1	250.7	258.9	267.1	275.7	284.8
157.5°	228.5	228.4	230.9	235.2	239.7	245.0	252.5	259.4	265.7	272.6	280.4
160°	233.0	232.5	234.5	238.1	242.1	246.7	253.3	259.4	264.5	270.6	276.7
162.5°	236.7	236.1	238.2	241.3	244.6	248.3	254.1	259.0	263.3	268.1	273.5
165°	242.1	241.1	242.6	245.1	247.2	250.3	254.3	258.4	261.4	264.5	268.6
167.5°	245.8	245.3	246.2	247.6	249.1	250.9	254.3	257.2	258.6	260.9	263.8
170°	248.3	247.7	248.3	249.2	250.3	251.8	254.3	256.4	257.3	258.9	260.9
172.5°	249.9	249.0	249.4	250.5	251.1	251.8	254.0	255.6	255.7	256.5	258.1
175°	251.8	250.7	251.3	251.8	251.8	251.8	253.3	254.3	253.8	253.8	254.3
177.5°	252.7	251.9	251.9	252.3	251.9	251.9	252.7	253.1	252.3	252.3	252.7
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333312-940

CATALOG NUMBER: S125DIP-S1270D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3
2.5°	1752.2	1754.7	1757.2	1758.3	1758.1	1757.8	1757.6	1757.3
5°	1743.4	1746.2	1749.0	1750.2	1749.9	1749.6	1749.3	1749.0
7.5°	1725.7	1728.5	1731.2	1732.4	1732.1	1731.8	1731.5	1731.2
10°	1710.8	1713.3	1715.7	1716.8	1716.5	1716.2	1715.9	1715.7
12.5°	1691.0	1692.9	1694.9	1695.9	1695.8	1695.7	1695.7	1695.6
15°	1656.2	1657.7	1659.2	1660.0	1660.0	1660.0	1660.0	1660.0
17.5°	1615.7	1617.7	1619.5	1619.7	1618.2	1616.7	1615.1	1613.6
20°	1585.1	1587.2	1589.4	1589.7	1588.1	1586.6	1585.1	1583.5
22.5°	1550.2	1551.7	1553.1	1553.3	1552.2	1551.1	1550.1	1549.1
25°	1494.4	1495.0	1495.7	1495.5	1494.6	1493.6	1492.7	1491.7
27.5°	1435.8	1436.0	1436.1	1435.7	1434.8	1433.9	1432.9	1432.0
30°	1393.2	1392.6	1392.0	1391.2	1390.3	1389.4	1388.4	1387.5
32.5°	1350.0	1348.9	1347.7	1346.3	1344.7	1343.0	1341.3	1339.7
35°	1282.9	1281.4	1279.9	1277.8	1275.3	1272.9	1270.4	1267.9
37.5°	1212.5	1210.2	1207.9	1206.0	1204.6	1203.2	1201.8	1200.3
40°	1163.7	1160.9	1158.1	1156.3	1155.3	1154.4	1153.4	1152.5
42.5°	1115.3	1112.7	1110.2	1108.2	1106.8	1105.4	1103.9	1102.5
45°	1043.7	1039.9	1036.3	1033.9	1033.0	1032.1	1031.1	1030.2
47.5°	968.1	964.4	960.6	957.7	955.5	953.3	951.2	949.0
50°	916.5	912.5	908.5	905.4	903.2	901.1	898.9	896.7
52.5°	866.3	862.8	859.3	856.3	853.9	851.5	849.1	846.7
55°	788.3	785.5	782.7	780.2	778.1	776.0	773.7	771.6
57.5°	710.8	707.2	703.6	701.2	700.1	698.9	697.7	696.5
60°	658.4	655.3	652.2	649.6	647.4	645.2	643.1	641.0
62.5°	607.8	604.5	601.2	598.7	597.0	595.3	593.6	592.0
65°	528.3	525.5	522.7	520.8	519.5	518.3	517.0	515.8
67.5°	452.5	450.0	447.7	446.2	445.4	444.7	444.0	443.2
70°	402.3	400.4	398.5	397.0	395.7	394.5	393.3	392.1
72.5°	355.1	352.9	350.9	349.2	347.9	346.7	345.4	344.2
75°	281.8	280.8	279.9	278.8	277.6	276.3	275.1	273.8
77.5°	214.6	214.1	213.6	212.9	212.0	211.1	210.3	209.4
80°	171.7	171.5	171.1	170.7	170.0	169.4	168.8	168.3
82.5°	131.3	130.7	130.1	129.8	129.7	129.6	129.4	129.3
85°	77.2	77.0	76.6	76.2	75.5	74.9	74.3	73.7
87.5°	30.8	30.9	30.9	30.9	30.4	30.0	29.5	29.1
90°	9.2	9.6	10.2	11.1	11.1	11.1	11.7	11.7
92.5°	90.2	65.5	49.2	41.7	35.2	34.0	33.3	32.5
95°	365.7	288.4	225.9	183.2	147.0	131.7	127.7	119.6
97.5°	544.7	490.4	429.5	370.1	338.7	310.1	295.4	288.9
100°	625.6	600.7	548.3	495.4	460.3	423.7	404.9	396.7
102.5°	652.9	668.2	643.1	607.3	569.8	543.8	523.3	517.2
105°	636.9	706.5	728.9	723.3	707.0	690.3	680.1	674.0
107.5°	579.4	672.4	730.0	756.4	764.7	764.6	761.3	757.2
110°	537.2	633.8	705.5	748.8	771.6	781.3	784.9	784.9



TEST NUMBER: P333312-940

CATALOG NUMBER: S125DIP-S1270D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	503.8	595.6	668.1	719.1	752.5	769.1	777.9	781.6
115°	461.8	540.7	610.4	665.8	705.5	730.0	744.1	750.8
117.5°	434.8	502.7	562.8	613.7	653.4	678.6	692.7	696.8
120°	420.2	481.2	537.2	581.9	619.6	644.0	657.7	661.7
122.5°	409.2	465.7	515.6	557.5	591.0	613.4	627.1	630.8
125°	393.2	445.1	489.4	525.9	554.5	575.3	586.5	591.6
127.5°	376.9	425.3	466.6	501.0	526.7	545.2	555.7	558.0
130°	366.8	411.5	451.2	484.2	509.7	526.5	536.6	539.7
132.5°	356.6	398.5	434.5	466.4	491.8	508.5	517.9	521.4
135°	343.3	378.4	411.0	440.0	462.4	479.1	488.3	491.3
137.5°	332.2	360.5	387.6	412.2	432.2	447.5	455.9	459.3
140°	326.0	350.0	373.4	394.8	413.6	426.8	434.4	436.9
142.5°	320.7	341.0	361.1	379.7	395.7	406.8	414.0	416.2
145°	313.9	329.6	345.4	359.1	371.3	380.0	385.6	387.6
147.5°	307.4	320.1	332.3	342.6	352.3	359.2	362.5	363.4
150°	303.6	314.9	324.5	333.7	341.3	347.4	349.5	350.0
152.5°	299.6	309.6	318.4	325.6	332.0	336.8	338.9	339.4
155°	293.5	301.7	308.7	314.3	319.4	323.0	324.5	325.0
157.5°	287.4	294.1	299.6	304.0	307.9	310.9	312.3	312.2
160°	283.3	288.4	293.5	297.0	300.6	303.2	304.2	303.6
162.5°	278.8	283.6	287.8	291.0	293.7	295.9	296.0	296.0
165°	272.6	276.2	279.3	281.8	283.8	284.8	284.8	284.8
167.5°	266.7	269.1	271.4	273.2	274.3	275.2	274.7	274.6
170°	263.5	265.0	266.5	267.5	268.6	269.1	269.1	268.6
172.5°	259.8	261.4	262.4	263.1	263.3	264.2	263.4	262.9
175°	255.8	255.8	256.9	256.9	256.9	257.3	256.4	255.8
177.5°	253.1	253.5	253.5	253.5	253.1	253.5	252.3	252.3
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3

(END OF REPORT)