

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333333

Luminaire Tested: **S125DIP-S1270D1205U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333333
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D1205U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9507.6 lumens
Efficiency: N/A
Efficacy: 132.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	45	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11861	11861	11861	11861
5°	13736	11902	10421	11902
10°	15980	11840	9130	11840
15°	17690	11753	8423	11753
20°	19801	11615	7854	11615
25°	23197	11460	7577	11460
30°	25055	11307	7337	11307
35°	20601	11020	7179	11020
40°	14643	10620	7006	10620
45°	11249	10082	6906	10082
50°	9602	9414	6893	9414
55°	8550	8760	6952	8760
60°	7713	8045	7129	8045
65°	7124	7326	7314	7326
70°	6477	6579	7419	6579
75°	5719	5797	7354	5797
80°	4813	4727	6724	4727
85°	3809	3409	5432	3409



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.8	1.9
10°-20°	526.4	5.5
20°-30°	854.8	9.0
30°-40°	1042.7	11.0
40°-50°	948.5	10.0
50°-60°	755.5	7.9
60°-70°	526.2	5.5
70°-80°	280.6	3.0
80°-90°	74.0	0.8
90°-100°	417.8	4.4
100°-110°	898.0	9.4
110°-120°	842.8	8.9
120°-130°	683.0	7.2
130°-140°	548.1	5.8
140°-150°	413.6	4.4
150°-160°	291.2	3.1
160°-170°	171.6	1.8
170°-180°	55.8	0.6
0°-30°	1558.0	16.4
0°-40°	2600.7	27.4
0°-60°	4304.7	45.3
0°-90°	5185.6	54.5
90°-120°	2158.6	22.7
90°-150°	3803.4	40.0
90°-180°	4322.0	45.5
0°-180°	9507.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1837	1837	1837	1837	1837	
5°	2119	1836	1607	1836	2119	214
15°	2646	1758	1260	1758	2646	757
25°	3255	1608	1063	1608	3255	1487
35°	2613	1398	910	1398	2613	1599
45°	1232	1104	756	1104	1232	986
55°	759	778	617	778	759	684
65°	466	479	479	479	466	463
75°	229	232	295	232	229	247
85°	51	46	73	46	51	60
90°	27	1	27	1	27	20
95°	273	38	273	38	273	387
105°	1540	131	1540	131	1540	1530
115°	1715	235	1715	235	1715	1676
125°	1351	325	1351	325	1351	1223
135°	1122	381	1122	381	1122	870
145°	885	444	885	444	885	563
155°	742	507	742	507	742	346
165°	651	553	651	553	651	186
175°	584	575	584	575	584	57
180°	576	576	576	576	576	



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1942.6	1940.1	1937.6	1932.6	1936.3	1925.7	1920.7	1912.0	1901.4	1897.7	1893.3
5°	2118.7	2122.6	2126.5	2110.2	2111.7	2100.8	2075.9	2055.6	2039.2	2018.2	2003.4
7.5°	2330.8	2321.6	2320.8	2310.2	2292.0	2277.3	2251.1	2217.7	2185.5	2148.7	2118.3
10°	2436.8	2437.6	2430.6	2418.1	2398.6	2384.6	2350.3	2317.5	2277.8	2231.0	2197.5
12.5°	2516.6	2519.9	2511.0	2494.2	2484.6	2453.2	2426.3	2387.4	2340.1	2302.7	2251.7
15°	2645.7	2637.1	2630.9	2609.8	2593.5	2560.7	2517.9	2477.3	2425.9	2378.3	2330.8
17.5°	2770.1	2777.0	2765.3	2746.1	2695.3	2657.1	2599.6	2544.0	2480.0	2416.2	2359.5
20°	2881.1	2887.4	2869.4	2835.9	2775.1	2736.9	2661.3	2589.6	2515.5	2433.7	2371.3
22.5°	3019.6	3014.6	2990.4	2939.4	2886.7	2816.1	2734.3	2646.9	2554.2	2461.7	2378.8
25°	3255.3	3222.5	3207.7	3144.6	3075.2	2971.5	2859.3	2731.4	2616.1	2493.7	2387.7
27.5°	3385.9	3375.6	3359.1	3315.2	3242.2	3131.3	2999.0	2843.2	2680.5	2526.0	2387.2
30°	3359.7	3361.3	3362.9	3348.8	3302.1	3218.6	3086.9	2919.3	2726.0	2552.2	2391.6
32.5°	3127.8	3156.1	3183.3	3215.4	3228.5	3212.4	3129.9	2978.6	2779.6	2582.1	2389.1
35°	2613.0	2621.5	2709.6	2796.9	2915.4	3007.4	3069.0	3001.9	2834.3	2607.5	2386.1
37.5°	2037.4	2079.5	2140.4	2239.1	2410.1	2563.2	2760.1	2850.7	2796.6	2615.8	2380.7
40°	1736.8	1775.8	1815.5	1916.1	2060.3	2245.8	2469.5	2660.5	2704.9	2589.6	2362.0
42.5°	1504.8	1535.7	1579.8	1655.4	1775.9	1940.2	2154.0	2403.6	2557.1	2513.5	2322.7
45°	1231.6	1251.1	1285.4	1345.5	1432.8	1561.4	1750.0	2022.9	2260.6	2339.3	2229.4
47.5°	1054.2	1054.1	1080.7	1122.2	1185.2	1294.5	1434.0	1647.8	1901.7	2089.6	2080.9
50°	955.7	951.8	972.8	1008.7	1058.6	1131.1	1264.4	1435.1	1679.1	1891.9	1951.1
52.5°	870.9	871.3	884.3	910.8	952.6	1014.5	1114.1	1268.0	1476.4	1694.8	1806.5
55°	759.3	756.1	770.9	788.9	819.3	859.8	931.5	1049.2	1218.4	1433.5	1578.5
57.5°	657.0	665.6	671.5	684.0	709.2	736.3	796.8	883.2	1017.4	1202.0	1355.3
60°	597.1	605.7	610.4	622.8	643.1	666.5	713.3	783.4	896.5	1055.5	1207.5
62.5°	543.5	550.2	551.7	563.0	579.5	602.3	639.1	698.0	787.3	926.4	1075.3
65°	466.2	466.2	469.3	481.0	488.8	509.0	537.1	580.0	651.7	760.0	887.1
67.5°	391.6	395.4	394.6	399.7	406.9	422.7	442.8	478.2	531.3	610.4	712.0
70°	343.0	346.1	345.3	349.2	357.0	367.2	383.5	417.0	455.2	523.1	610.4
72.5°	299.3	300.6	298.6	303.7	308.4	317.3	335.5	353.4	389.1	446.4	518.1
75°	229.2	230.7	232.3	235.4	240.1	244.8	254.1	272.1	295.4	338.3	384.3
77.5°	171.8	168.8	172.6	172.1	174.8	178.4	186.6	196.1	215.3	242.4	278.0
80°	129.4	130.2	130.2	131.0	134.9	137.2	144.2	151.2	166.0	186.3	211.3
82.5°	94.5	96.5	95.3	96.7	99.9	101.6	105.5	111.3	119.9	135.8	153.9
85°	51.4	47.6	49.1	50.7	50.7	51.4	54.6	56.9	61.6	67.8	74.8
87.5°	20.3	21.6	22.0	22.0	22.6	22.1	24.4	24.1	25.8	27.4	29.4
90°	26.7	26.7	25.6	25.6	25.6	23.2	22.1	20.9	19.8	18.6	16.3
92.5°	74.1	76.0	77.6	80.4	95.3	112.5	149.4	205.9	303.3	374.6	380.7
95°	273.1	291.7	300.9	335.8	418.3	515.9	658.8	835.4	1007.4	1029.5	840.1
97.5°	660.0	674.9	708.6	773.6	845.4	981.2	1120.4	1244.2	1274.7	1099.4	750.2
100°	906.3	924.9	967.9	1051.6	1131.7	1252.6	1372.3	1429.2	1339.7	1049.2	669.3
102.5°	1181.5	1195.4	1242.1	1301.6	1387.4	1469.2	1526.6	1491.5	1300.7	960.9	607.9
105°	1539.6	1553.5	1576.8	1615.1	1652.3	1665.1	1614.0	1454.8	1175.9	842.4	548.4
107.5°	1729.7	1739.0	1746.7	1746.9	1728.1	1667.4	1536.1	1323.7	1048.6	760.8	523.3
110°	1792.9	1792.9	1784.8	1762.7	1710.4	1611.6	1447.8	1227.0	976.0	722.7	515.9



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1785.5	1777.1	1756.9	1719.0	1642.5	1526.1	1360.4	1150.8	922.1	700.4	515.9
115°	1715.0	1699.9	1667.4	1611.6	1521.0	1394.3	1235.2	1055.1	863.3	676.3	519.4
117.5°	1591.6	1582.4	1550.1	1492.4	1401.8	1285.6	1148.5	993.2	828.2	664.4	527.1
120°	1511.7	1502.4	1471.0	1415.3	1329.3	1227.0	1099.2	959.8	808.7	658.8	534.5
122.5°	1441.1	1432.7	1401.3	1350.2	1273.5	1177.8	1063.9	934.7	792.0	654.2	541.0
125°	1351.4	1339.7	1314.2	1266.5	1201.5	1117.8	1016.7	898.2	769.2	648.4	551.9
127.5°	1274.7	1269.6	1245.4	1203.3	1144.3	1066.0	971.6	861.0	748.3	645.6	564.2
130°	1232.8	1225.9	1202.6	1164.3	1106.2	1030.7	940.0	837.8	734.4	643.7	571.7
132.5°	1191.0	1183.1	1161.7	1123.4	1065.3	992.5	910.3	814.5	723.2	643.7	580.0
135°	1122.5	1115.5	1094.6	1056.2	1005.1	938.9	864.5	784.3	710.0	643.7	591.4
137.5°	1049.2	1041.6	1022.3	987.4	941.7	885.4	823.6	758.8	698.1	645.1	601.9
140°	998.1	992.3	974.9	944.7	901.7	852.9	799.4	744.8	692.5	646.0	606.5
142.5°	950.7	945.8	929.3	903.8	867.3	825.0	779.0	732.7	687.9	647.0	609.3
145°	885.4	880.8	868.0	848.2	820.3	789.0	752.9	716.9	680.9	646.0	612.4
147.5°	830.1	828.0	820.6	804.8	782.7	759.0	731.3	702.1	673.7	643.0	613.5
150°	799.4	798.3	793.6	779.7	762.2	741.3	719.3	693.7	668.1	640.2	613.5
152.5°	775.3	774.1	769.4	758.3	743.7	727.4	707.2	684.4	661.6	636.5	612.6
155°	742.5	741.3	737.8	729.7	718.1	705.3	689.0	670.4	650.7	629.8	610.0
157.5°	713.2	713.4	710.2	703.4	694.4	684.4	671.8	656.5	640.5	622.8	607.0
160°	693.7	694.9	692.5	686.7	678.6	670.4	658.8	647.2	632.1	618.2	604.2
162.5°	676.0	676.3	675.8	670.9	664.6	657.4	647.7	637.0	624.7	612.6	601.4
165°	650.7	650.7	650.7	648.4	643.7	637.9	630.9	622.8	613.5	604.2	597.2
167.5°	627.5	627.7	628.6	626.5	624.2	620.0	614.7	609.3	602.6	596.1	590.7
170°	613.5	614.7	614.7	613.5	611.2	608.9	605.4	601.9	596.1	591.4	588.0
172.5°	600.5	601.7	603.5	601.4	601.0	599.6	597.0	593.5	589.6	585.9	584.2
175°	584.5	585.6	588.0	586.8	586.8	586.8	584.5	584.5	581.0	579.8	579.8
177.5°	576.3	576.3	579.1	578.2	579.1	579.1	579.1	578.2	577.3	576.3	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1889.6	1885.2	1880.2	1871.5	1860.9	1855.3	1846.5	1840.9	1829.7	1820.3	1810.4
5°	1985.4	1965.2	1946.5	1922.3	1895.8	1878.6	1858.4	1835.8	1812.4	1788.2	1761.7
7.5°	2084.8	2048.9	2009.9	1968.0	1927.0	1889.2	1853.2	1817.8	1784.8	1744.9	1711.1
10°	2151.5	2106.3	2057.9	2001.0	1945.7	1897.4	1848.2	1805.4	1761.7	1714.9	1673.6
12.5°	2218.2	2158.0	2089.7	2027.2	1960.7	1902.3	1844.5	1789.8	1734.9	1683.1	1635.0
15°	2265.3	2212.3	2149.1	2060.3	1985.4	1905.2	1828.8	1757.8	1691.6	1633.9	1573.1
17.5°	2296.3	2228.0	2160.2	2074.9	1976.9	1887.1	1800.5	1719.3	1644.6	1571.5	1512.9
20°	2301.9	2231.8	2160.8	2077.4	1976.9	1874.0	1787.4	1690.0	1609.7	1534.1	1462.4
22.5°	2300.1	2220.5	2143.4	2057.5	1959.4	1864.6	1760.0	1660.7	1573.5	1499.2	1424.3
25°	2282.4	2197.5	2100.8	2014.3	1917.6	1817.1	1711.1	1608.2	1519.3	1434.3	1360.3
27.5°	2267.8	2157.6	2048.1	1947.2	1853.9	1761.7	1660.2	1554.8	1456.3	1370.2	1300.4
30°	2249.7	2128.9	2005.7	1900.5	1804.6	1714.9	1619.1	1516.2	1413.3	1329.1	1254.3
32.5°	2233.5	2092.7	1962.7	1848.1	1746.6	1659.4	1571.0	1473.1	1372.1	1286.7	1211.8
35°	2202.2	2039.2	1890.3	1760.9	1652.6	1562.9	1488.9	1397.7	1304.9	1222.3	1150.6
37.5°	2162.4	1969.1	1809.3	1673.6	1554.8	1460.4	1391.4	1321.4	1232.4	1152.8	1087.9
40°	2131.2	1919.2	1750.0	1611.3	1488.1	1389.9	1326.0	1259.7	1185.7	1111.6	1043.0
42.5°	2091.9	1874.3	1690.2	1540.8	1418.9	1323.2	1256.1	1199.8	1134.5	1065.5	1001.8
45°	2019.7	1792.9	1593.3	1432.8	1309.6	1215.3	1145.9	1103.8	1054.7	989.2	935.4
47.5°	1913.6	1695.1	1488.7	1323.0	1195.9	1108.5	1043.5	1003.1	968.5	919.8	871.0
50°	1819.4	1622.2	1413.3	1248.8	1121.7	1033.6	973.6	937.0	907.4	869.9	828.6
52.5°	1714.0	1530.5	1339.1	1176.5	1050.6	963.8	905.0	872.8	848.1	821.3	780.6
55°	1546.6	1390.7	1212.9	1058.6	942.4	857.5	806.0	778.0	757.7	737.4	712.5
57.5°	1362.1	1240.2	1082.8	941.7	834.7	757.4	709.4	682.1	666.3	655.9	641.2
60°	1232.4	1128.0	992.3	863.7	759.3	690.7	643.9	622.8	609.6	601.0	590.1
62.5°	1112.1	1026.3	900.7	783.3	691.9	627.0	585.3	564.8	552.2	548.0	539.0
65°	934.6	868.4	764.7	667.3	589.3	534.0	498.9	479.4	471.6	466.9	467.7
67.5°	759.9	719.5	636.2	553.1	490.9	444.5	416.4	401.5	397.6	391.3	391.2
70°	653.2	622.8	552.7	480.2	424.8	389.0	364.0	348.4	344.5	341.4	340.7
72.5°	559.1	532.4	471.6	413.5	363.7	332.2	311.7	302.3	295.9	294.0	293.9
75°	420.2	405.4	357.0	311.0	276.7	254.9	240.9	232.3	227.6	226.8	227.6
77.5°	298.7	285.8	255.1	222.5	200.8	184.3	172.4	169.5	164.2	164.3	163.5
80°	224.5	215.9	196.4	170.7	152.8	138.8	132.5	127.1	125.5	123.2	125.5
82.5°	162.8	153.6	140.3	123.9	109.1	100.7	94.5	92.8	91.8	90.7	91.2
85°	80.3	81.1	73.3	60.8	54.6	49.9	46.0	46.0	45.2	44.4	45.2
87.5°	30.5	28.7	26.0	23.7	20.1	17.8	16.7	17.1	15.4	15.3	16.4
90°	15.1	12.8	11.6	9.3	7.0	4.6	2.3	1.2	2.3	4.6	7.0
92.5°	265.2	158.7	95.3	61.4	41.4	27.0	17.2	14.2	17.2	27.0	41.4
95°	519.4	263.8	139.4	87.1	61.6	48.8	39.5	38.3	39.5	48.8	61.6
97.5°	414.6	227.3	145.0	107.4	84.4	71.6	65.1	63.7	65.1	71.6	84.4
100°	376.5	225.4	158.0	123.2	101.1	88.3	83.7	81.3	83.7	88.3	101.1
102.5°	360.7	233.8	173.8	139.9	119.7	106.0	102.3	100.9	102.3	106.0	119.7
105°	354.4	251.0	199.9	167.3	148.7	137.1	131.3	131.3	131.3	137.1	148.7
107.5°	365.1	276.5	227.0	197.8	178.5	168.9	163.4	161.0	163.4	168.9	178.5
110°	375.3	295.1	247.5	217.3	199.9	189.4	184.8	182.4	184.8	189.4	199.9



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	388.3	312.8	267.0	237.7	220.3	209.8	206.1	203.8	206.1	209.8	220.3
115°	407.8	340.5	297.5	268.4	251.0	240.5	237.0	234.7	237.0	240.5	251.0
117.5°	430.2	368.8	328.1	300.0	280.3	269.8	266.1	262.6	266.1	269.8	280.3
120°	445.0	389.3	348.6	319.5	299.8	289.3	284.7	281.2	284.7	289.3	299.8
122.5°	461.8	408.8	368.1	339.1	317.4	307.0	303.3	300.7	303.3	307.0	317.4
125°	484.5	434.6	396.2	366.0	343.9	333.5	327.7	325.3	327.7	333.5	343.9
127.5°	505.5	459.4	422.5	392.3	368.8	355.6	348.1	344.6	348.1	355.6	368.8
130°	519.4	475.2	439.2	409.0	384.6	369.5	360.2	356.7	360.2	369.5	384.6
132.5°	531.5	490.1	454.1	423.9	398.6	381.6	370.4	366.0	370.4	381.6	398.6
135°	548.4	510.1	474.1	442.7	418.3	399.7	385.8	381.1	385.8	399.7	418.3
137.5°	561.0	524.3	491.5	459.2	435.3	416.7	403.7	400.2	403.7	416.7	435.3
140°	569.4	534.5	500.8	469.4	447.4	428.8	414.8	411.3	414.8	428.8	447.4
142.5°	574.0	541.0	509.2	479.7	458.5	439.9	426.9	424.3	426.9	439.9	458.5
145°	581.0	551.9	521.7	495.0	474.1	457.8	446.2	443.9	446.2	457.8	474.1
147.5°	585.2	558.9	532.4	508.9	490.8	475.7	465.7	464.3	465.7	475.7	490.8
150°	588.0	563.5	538.0	518.2	502.0	486.9	478.7	476.4	478.7	486.9	502.0
152.5°	589.8	568.2	544.5	526.6	511.3	498.0	490.8	489.4	490.8	498.0	511.3
155°	591.4	572.8	553.1	536.8	525.2	513.6	506.6	506.6	506.6	513.6	525.2
157.5°	592.6	576.8	559.8	547.5	537.3	527.3	521.7	522.0	521.7	527.3	537.3
160°	592.6	578.7	563.5	553.1	543.8	535.7	531.0	532.2	531.0	535.7	543.8
162.5°	591.7	580.5	567.3	558.7	551.2	544.0	539.4	540.5	539.4	544.0	551.2
165°	590.3	581.0	571.7	564.7	560.1	554.3	550.8	553.1	550.8	554.3	560.1
167.5°	587.5	581.0	573.3	568.9	565.6	562.4	560.3	561.5	560.3	562.4	565.6
170°	585.6	581.0	575.2	571.7	569.4	567.0	565.9	567.0	565.9	567.0	569.4
172.5°	583.8	580.0	575.2	573.5	572.1	569.8	568.7	570.8	568.7	569.8	572.1
175°	581.0	578.7	575.2	575.2	575.2	574.0	572.8	575.2	572.8	574.0	575.2
177.5°	578.2	577.3	575.4	575.4	576.3	575.4	575.4	577.3	575.4	575.4	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1804.7	1797.9	1792.3	1779.8	1772.9	1763.6	1756.1	1764.2	1755.5	1759.2	1753.6
5°	1748.5	1726.6	1711.1	1688.4	1669.0	1651.0	1637.8	1635.4	1629.2	1626.1	1616.7
7.5°	1680.8	1653.5	1626.7	1597.1	1572.1	1546.7	1530.5	1517.1	1508.2	1496.5	1488.6
10°	1640.9	1604.3	1573.1	1537.2	1506.0	1478.8	1456.9	1446.0	1435.9	1421.1	1415.6
12.5°	1591.6	1553.7	1515.7	1477.4	1447.4	1417.0	1398.3	1381.8	1374.8	1358.1	1356.4
15°	1532.5	1475.6	1438.2	1399.2	1357.9	1333.0	1317.4	1299.5	1291.7	1280.0	1271.4
17.5°	1462.1	1411.2	1364.5	1324.1	1288.7	1267.7	1248.3	1236.0	1222.6	1215.0	1200.9
20°	1410.9	1362.6	1315.8	1273.0	1245.7	1221.5	1205.9	1194.2	1180.2	1176.3	1162.3
22.5°	1367.9	1314.6	1269.7	1233.7	1203.9	1176.6	1159.8	1151.8	1142.2	1130.2	1127.3
25°	1297.9	1242.6	1204.4	1168.5	1142.0	1117.1	1105.4	1095.2	1085.9	1077.3	1074.2
27.5°	1237.4	1188.0	1142.6	1110.2	1087.1	1064.4	1054.1	1041.8	1034.9	1028.0	1019.6
30°	1195.0	1144.3	1104.6	1073.4	1048.5	1028.2	1017.3	1008.7	1002.5	996.2	991.6
32.5°	1151.4	1104.4	1065.9	1035.4	1010.4	995.1	985.5	979.4	972.5	965.0	959.1
35°	1093.7	1042.2	1004.8	978.3	958.8	947.1	936.2	930.7	923.0	923.0	916.7
37.5°	1028.7	984.2	951.2	927.0	909.5	899.1	887.3	883.5	878.5	875.2	873.1
40°	990.0	948.7	917.5	893.3	874.6	866.0	856.7	850.5	847.3	843.4	841.9
42.5°	950.1	910.6	880.7	858.4	842.2	834.9	826.1	821.8	815.5	810.4	809.5
45°	889.4	851.2	824.0	806.0	792.0	783.4	778.0	768.6	765.5	759.3	758.5
47.5°	831.9	795.3	768.5	753.8	741.5	734.5	725.9	716.5	713.0	709.8	709.5
50°	788.9	755.4	730.4	716.4	704.7	694.6	686.0	679.7	677.4	677.4	679.0
52.5°	745.2	716.7	695.5	678.3	667.3	656.5	648.6	644.8	641.2	645.0	647.8
55°	681.3	652.5	636.9	620.5	609.6	597.1	593.2	591.7	589.3	595.6	598.7
57.5°	613.6	593.4	575.1	558.9	549.1	541.9	536.6	535.7	540.1	543.0	553.1
60°	570.6	547.2	530.9	518.4	506.7	502.0	500.5	498.9	502.0	510.6	523.8
62.5°	523.2	504.2	486.6	477.2	468.6	460.9	460.5	461.5	467.7	477.5	490.8
65°	453.7	437.3	425.6	414.7	407.7	403.0	404.6	407.7	414.7	428.0	442.8
67.5°	383.1	371.8	361.4	352.5	345.8	345.8	347.4	352.0	360.3	375.6	389.1
70°	337.5	325.1	316.5	312.6	307.1	304.0	308.7	316.5	323.5	337.5	349.2
72.5°	292.0	281.4	274.7	272.1	269.7	267.2	268.8	277.2	286.7	300.7	314.3
75°	224.5	220.6	215.9	212.8	210.5	212.0	213.6	221.4	229.2	244.0	259.6
77.5°	163.9	159.8	157.0	156.2	155.0	155.7	160.1	165.9	173.5	184.3	196.1
80°	123.9	122.4	120.8	120.0	120.0	120.8	127.1	131.0	138.0	148.1	157.5
82.5°	90.3	89.3	89.0	88.9	89.5	89.6	93.4	98.5	104.3	111.9	120.0
85°	47.6	46.0	48.3	49.1	47.6	49.9	51.4	54.6	56.9	60.8	64.7
87.5°	17.4	19.2	18.8	19.9	20.1	21.8	21.4	24.1	25.6	27.1	26.9
90°	9.3	11.6	12.8	15.1	16.3	18.6	19.8	20.9	22.1	23.2	25.6
92.5°	61.4	95.3	158.7	265.2	380.7	374.6	303.3	205.9	149.4	112.5	95.3
95°	87.1	139.4	263.8	519.4	840.1	1029.5	1007.4	835.4	658.8	515.9	418.3
97.5°	107.4	145.0	227.3	414.6	750.2	1099.4	1274.7	1244.2	1120.4	981.2	845.4
100°	123.2	158.0	225.4	376.5	669.3	1049.2	1339.7	1429.2	1372.3	1252.6	1131.7
102.5°	139.9	173.8	233.8	360.7	607.9	960.9	1300.7	1491.5	1526.6	1469.2	1387.4
105°	167.3	199.9	251.0	354.4	548.4	842.4	1175.9	1454.8	1614.0	1665.1	1652.3
107.5°	197.8	227.0	276.5	365.1	523.3	760.8	1048.6	1323.7	1536.1	1667.4	1728.1
110°	217.3	247.5	295.1	375.3	515.9	722.7	976.0	1227.0	1447.8	1611.6	1710.4



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	237.7	267.0	312.8	388.3	515.9	700.4	922.1	1150.8	1360.4	1526.1	1642.5
115°	268.4	297.5	340.5	407.8	519.4	676.3	863.3	1055.1	1235.2	1394.3	1521.0
117.5°	300.0	328.1	368.8	430.2	527.1	664.4	828.2	993.2	1148.5	1285.6	1401.8
120°	319.5	348.6	389.3	445.0	534.5	658.8	808.7	959.8	1099.2	1227.0	1329.3
122.5°	339.1	368.1	408.8	461.8	541.0	654.2	792.0	934.7	1063.9	1177.8	1273.5
125°	366.0	396.2	434.6	484.5	551.9	648.4	769.2	898.2	1016.7	1117.8	1201.5
127.5°	392.3	422.5	459.4	505.5	564.2	645.6	748.3	861.0	971.6	1066.0	1144.3
130°	409.0	439.2	475.2	519.4	571.7	643.7	734.4	837.8	940.0	1030.7	1106.2
132.5°	423.9	454.1	490.1	531.5	580.0	643.7	723.2	814.5	910.3	992.5	1065.3
135°	442.7	474.1	510.1	548.4	591.4	643.7	710.0	784.3	864.5	938.9	1005.1
137.5°	459.2	491.5	524.3	561.0	601.9	645.1	698.1	758.8	823.6	885.4	941.7
140°	469.4	500.8	534.5	569.4	606.5	646.0	692.5	744.8	799.4	852.9	901.7
142.5°	479.7	509.2	541.0	574.0	609.3	647.0	687.9	732.7	779.0	825.0	867.3
145°	495.0	521.7	551.9	581.0	612.4	646.0	680.9	716.9	752.9	789.0	820.3
147.5°	508.9	532.4	558.9	585.2	613.5	643.0	673.7	702.1	731.3	759.0	782.7
150°	518.2	538.0	563.5	588.0	613.5	640.2	668.1	693.7	719.3	741.3	762.2
152.5°	526.6	544.5	568.2	589.8	612.6	636.5	661.6	684.4	707.2	727.4	743.7
155°	536.8	553.1	572.8	591.4	610.0	629.8	650.7	670.4	689.0	705.3	718.1
157.5°	547.5	559.8	576.8	592.6	607.0	622.8	640.5	656.5	671.8	684.4	694.4
160°	553.1	563.5	578.7	592.6	604.2	618.2	632.1	647.2	658.8	670.4	678.6
162.5°	558.7	567.3	580.5	591.7	601.4	612.6	624.7	637.0	647.7	657.4	664.6
165°	564.7	571.7	581.0	590.3	597.2	604.2	613.5	622.8	630.9	637.9	643.7
167.5°	568.9	573.3	581.0	587.5	590.7	596.1	602.6	609.3	614.7	620.0	624.2
170°	571.7	575.2	581.0	585.6	588.0	591.4	596.1	601.9	605.4	608.9	611.2
172.5°	573.5	575.2	580.0	583.8	584.2	585.9	589.6	593.5	597.0	599.6	601.0
175°	575.2	575.2	578.7	581.0	579.8	579.8	581.0	584.5	584.5	586.8	586.8
177.5°	575.4	575.4	577.3	578.2	576.3	576.3	577.3	578.2	579.1	579.1	579.1
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1749.9	1754.2	1750.5	1755.5	1750.5	1754.2	1749.9	1753.6	1759.2	1755.5	1764.2
5°	1612.8	1605.8	1610.5	1607.4	1610.5	1605.8	1612.8	1616.7	1626.1	1629.2	1635.4
7.5°	1486.2	1479.5	1471.9	1468.3	1471.9	1479.5	1486.2	1488.6	1496.5	1508.2	1517.1
10°	1407.0	1398.5	1397.7	1392.2	1397.7	1398.5	1407.0	1415.6	1421.1	1435.9	1446.0
12.5°	1349.0	1341.1	1332.2	1329.9	1332.2	1341.1	1349.0	1356.4	1358.1	1374.8	1381.8
15°	1266.7	1260.5	1255.0	1259.7	1255.0	1260.5	1266.7	1271.4	1280.0	1291.7	1299.5
17.5°	1198.3	1193.1	1192.2	1186.4	1192.2	1193.1	1198.3	1200.9	1215.0	1222.6	1236.0
20°	1155.3	1151.4	1152.9	1142.8	1152.9	1151.4	1155.3	1162.3	1176.3	1180.2	1194.2
22.5°	1121.0	1113.3	1112.4	1110.4	1112.4	1113.3	1121.0	1127.3	1130.2	1142.2	1151.8
25°	1067.2	1063.3	1059.4	1063.3	1059.4	1063.3	1067.2	1074.2	1077.3	1085.9	1095.2
27.5°	1020.2	1015.6	1014.5	1014.9	1014.5	1015.6	1020.2	1019.6	1028.0	1034.9	1041.8
30°	991.6	983.8	984.5	983.8	984.5	983.8	991.6	991.6	996.2	1002.5	1008.7
32.5°	960.4	955.1	954.0	952.6	954.0	955.1	960.4	959.1	965.0	972.5	979.4
35°	914.4	914.4	910.5	910.5	910.5	914.4	914.4	916.7	923.0	923.0	930.7
37.5°	871.2	870.4	868.1	868.4	868.1	870.4	871.2	873.1	875.2	878.5	883.5
40°	838.8	838.0	835.6	831.0	835.6	838.0	838.8	841.9	843.4	847.3	850.5
42.5°	807.6	804.9	803.8	802.3	803.8	804.9	807.6	809.5	810.4	815.5	821.8
45°	758.5	758.5	756.9	756.1	756.9	758.5	758.5	758.5	759.3	765.5	768.6
47.5°	710.8	712.2	715.1	714.7	715.1	712.2	710.8	709.5	709.8	713.0	716.5
50°	682.1	682.9	685.2	686.0	685.2	682.9	682.1	679.0	677.4	677.4	679.7
52.5°	650.3	654.8	657.8	657.3	657.8	654.8	650.3	647.8	645.0	641.2	644.8
55°	605.7	611.1	616.6	617.4	616.6	611.1	605.7	598.7	595.6	589.3	591.7
57.5°	561.6	569.2	575.0	576.8	575.0	569.2	561.6	553.1	543.0	540.1	535.7
60°	531.6	541.8	548.8	551.9	548.8	541.8	531.6	523.8	510.6	502.0	498.9
62.5°	502.9	514.3	521.3	522.0	521.3	514.3	502.9	490.8	477.5	467.7	461.5
65°	456.0	467.7	473.9	478.6	473.9	467.7	456.0	442.8	428.0	414.7	407.7
67.5°	405.5	417.2	424.1	427.8	424.1	417.2	405.5	389.1	375.6	360.3	352.0
70°	368.7	380.4	389.8	392.9	389.8	380.4	368.7	349.2	337.5	323.5	316.5
72.5°	332.5	343.0	350.5	354.2	350.5	343.0	332.5	314.3	300.7	286.7	277.2
75°	269.7	283.7	290.8	294.7	290.8	283.7	269.7	259.6	244.0	229.2	221.4
77.5°	208.0	220.8	225.0	227.0	225.0	220.8	208.0	196.1	184.3	173.5	165.9
80°	166.8	174.6	180.1	180.8	180.1	174.6	166.8	157.5	148.1	138.0	131.0
82.5°	128.2	134.7	136.4	138.4	136.4	134.7	128.2	120.0	111.9	104.3	98.5
85°	70.2	73.3	74.1	73.3	74.1	73.3	70.2	64.7	60.8	56.9	54.6
87.5°	28.2	27.6	27.8	29.0	27.8	27.6	28.2	26.9	27.1	25.6	24.1
90°	25.6	25.6	26.7	26.7	26.7	25.6	25.6	25.6	23.2	22.1	20.9
92.5°	80.4	77.6	76.0	74.1	76.0	77.6	80.4	95.3	112.5	149.4	205.9
95°	335.8	300.9	291.7	273.1	291.7	300.9	335.8	418.3	515.9	658.8	835.4
97.5°	773.6	708.6	674.9	660.0	674.9	708.6	773.6	845.4	981.2	1120.4	1244.2
100°	1051.6	967.9	924.9	906.3	924.9	967.9	1051.6	1131.7	1252.6	1372.3	1429.2
102.5°	1301.6	1242.1	1195.4	1181.5	1195.4	1242.1	1301.6	1387.4	1469.2	1526.6	1491.5
105°	1615.1	1576.8	1553.5	1539.6	1553.5	1576.8	1615.1	1652.3	1665.1	1614.0	1454.8
107.5°	1746.9	1746.7	1739.0	1729.7	1739.0	1746.7	1746.9	1728.1	1667.4	1536.1	1323.7
110°	1762.7	1784.8	1792.9	1792.9	1792.9	1784.8	1762.7	1710.4	1611.6	1447.8	1227.0



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1719.0	1756.9	1777.1	1785.5	1777.1	1756.9	1719.0	1642.5	1526.1	1360.4	1150.8
115°	1611.6	1667.4	1699.9	1715.0	1699.9	1667.4	1611.6	1521.0	1394.3	1235.2	1055.1
117.5°	1492.4	1550.1	1582.4	1591.6	1582.4	1550.1	1492.4	1401.8	1285.6	1148.5	993.2
120°	1415.3	1471.0	1502.4	1511.7	1502.4	1471.0	1415.3	1329.3	1227.0	1099.2	959.8
122.5°	1350.2	1401.3	1432.7	1441.1	1432.7	1401.3	1350.2	1273.5	1177.8	1063.9	934.7
125°	1266.5	1314.2	1339.7	1351.4	1339.7	1314.2	1266.5	1201.5	1117.8	1016.7	898.2
127.5°	1203.3	1245.4	1269.6	1274.7	1269.6	1245.4	1203.3	1144.3	1066.0	971.6	861.0
130°	1164.3	1202.6	1225.9	1232.8	1225.9	1202.6	1164.3	1106.2	1030.7	940.0	837.8
132.5°	1123.4	1161.7	1183.1	1191.0	1183.1	1161.7	1123.4	1065.3	992.5	910.3	814.5
135°	1056.2	1094.6	1115.5	1122.5	1115.5	1094.6	1056.2	1005.1	938.9	864.5	784.3
137.5°	987.4	1022.3	1041.6	1049.2	1041.6	1022.3	987.4	941.7	885.4	823.6	758.8
140°	944.7	974.9	992.3	998.1	992.3	974.9	944.7	901.7	852.9	799.4	744.8
142.5°	903.8	929.3	945.8	950.7	945.8	929.3	903.8	867.3	825.0	779.0	732.7
145°	848.2	868.0	880.8	885.4	880.8	868.0	848.2	820.3	789.0	752.9	716.9
147.5°	804.8	820.6	828.0	830.1	828.0	820.6	804.8	782.7	759.0	731.3	702.1
150°	779.7	793.6	798.3	799.4	798.3	793.6	779.7	762.2	741.3	719.3	693.7
152.5°	758.3	769.4	774.1	775.3	774.1	769.4	758.3	743.7	727.4	707.2	684.4
155°	729.7	737.8	741.3	742.5	741.3	737.8	729.7	718.1	705.3	689.0	670.4
157.5°	703.4	710.2	713.4	713.2	713.4	710.2	703.4	694.4	684.4	671.8	656.5
160°	686.7	692.5	694.9	693.7	694.9	692.5	686.7	678.6	670.4	658.8	647.2
162.5°	670.9	675.8	676.3	676.0	676.3	675.8	670.9	664.6	657.4	647.7	637.0
165°	648.4	650.7	650.7	650.7	650.7	650.7	648.4	643.7	637.9	630.9	622.8
167.5°	626.5	628.6	627.7	627.5	627.7	628.6	626.5	624.2	620.0	614.7	609.3
170°	613.5	614.7	614.7	613.5	614.7	614.7	613.5	611.2	608.9	605.4	601.9
172.5°	601.4	603.5	601.7	600.5	601.7	603.5	601.4	601.0	599.6	597.0	593.5
175°	586.8	588.0	585.6	584.5	585.6	588.0	586.8	586.8	586.8	584.5	584.5
177.5°	578.2	579.1	576.3	576.3	576.3	579.1	578.2	579.1	579.1	579.1	578.2
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1756.1	1763.6	1772.9	1779.8	1792.3	1797.9	1804.7	1810.4	1820.3	1829.7	1840.9
5°	1637.8	1651.0	1669.0	1688.4	1711.1	1726.6	1748.5	1761.7	1788.2	1812.4	1835.8
7.5°	1530.5	1546.7	1572.1	1597.1	1626.7	1653.5	1680.8	1711.1	1744.9	1784.8	1817.8
10°	1456.9	1478.8	1506.0	1537.2	1573.1	1604.3	1640.9	1673.6	1714.9	1761.7	1805.4
12.5°	1398.3	1417.0	1447.4	1477.4	1515.7	1553.7	1591.6	1635.0	1683.1	1734.9	1789.8
15°	1317.4	1333.0	1357.9	1399.2	1438.2	1475.6	1532.5	1573.1	1633.9	1691.6	1757.8
17.5°	1248.3	1267.7	1288.7	1324.1	1364.5	1411.2	1462.1	1512.9	1571.5	1644.6	1719.3
20°	1205.9	1221.5	1245.7	1273.0	1315.8	1362.6	1410.9	1462.4	1534.1	1609.7	1690.0
22.5°	1159.8	1176.6	1203.9	1233.7	1269.7	1314.6	1367.9	1424.3	1499.2	1573.5	1660.7
25°	1105.4	1117.1	1142.0	1168.5	1204.4	1242.6	1297.9	1360.3	1434.3	1519.3	1608.2
27.5°	1054.1	1064.4	1087.1	1110.2	1142.6	1188.0	1237.4	1300.4	1370.2	1456.3	1554.8
30°	1017.3	1028.2	1048.5	1073.4	1104.6	1144.3	1195.0	1254.3	1329.1	1413.3	1516.2
32.5°	985.5	995.1	1010.4	1035.4	1065.9	1104.4	1151.4	1211.8	1286.7	1372.1	1473.1
35°	936.2	947.1	958.8	978.3	1004.8	1042.2	1093.7	1150.6	1222.3	1304.9	1397.7
37.5°	887.3	899.1	909.5	927.0	951.2	984.2	1028.7	1087.9	1152.8	1232.4	1321.4
40°	856.7	866.0	874.6	893.3	917.5	948.7	990.0	1043.0	1111.6	1185.7	1259.7
42.5°	826.1	834.9	842.2	858.4	880.7	910.6	950.1	1001.8	1065.5	1134.5	1199.8
45°	778.0	783.4	792.0	806.0	824.0	851.2	889.4	935.4	989.2	1054.7	1103.8
47.5°	725.9	734.5	741.5	753.8	768.5	795.3	831.9	871.0	919.8	968.5	1003.1
50°	686.0	694.6	704.7	716.4	730.4	755.4	788.9	828.6	869.9	907.4	937.0
52.5°	648.6	656.5	667.3	678.3	695.5	716.7	745.2	780.6	821.3	848.1	872.8
55°	593.2	597.1	609.6	620.5	636.9	652.5	681.3	712.5	737.4	757.7	778.0
57.5°	536.6	541.9	549.1	558.9	575.1	593.4	613.6	641.2	655.9	666.3	682.1
60°	500.5	502.0	506.7	518.4	530.9	547.2	570.6	590.1	601.0	609.6	622.8
62.5°	460.5	460.9	468.6	477.2	486.6	504.2	523.2	539.0	548.0	552.2	564.8
65°	404.6	403.0	407.7	414.7	425.6	437.3	453.7	467.7	466.9	471.6	479.4
67.5°	347.4	345.8	345.8	352.5	361.4	371.8	383.1	391.2	391.3	397.6	401.5
70°	308.7	304.0	307.1	312.6	316.5	325.1	337.5	340.7	341.4	344.5	348.4
72.5°	268.8	267.2	269.7	272.1	274.7	281.4	292.0	293.9	294.0	295.9	302.3
75°	213.6	212.0	210.5	212.8	215.9	220.6	224.5	227.6	226.8	227.6	232.3
77.5°	160.1	155.7	155.0	156.2	157.0	159.8	163.9	163.5	164.3	164.2	169.5
80°	127.1	120.8	120.0	120.0	120.8	122.4	123.9	125.5	123.2	125.5	127.1
82.5°	93.4	89.6	89.5	88.9	89.0	89.3	90.3	91.2	90.7	91.8	92.8
85°	51.4	49.9	47.6	49.1	48.3	46.0	47.6	45.2	44.4	45.2	46.0
87.5°	21.4	21.8	20.1	19.9	18.8	19.2	17.4	16.4	15.3	15.4	17.1
90°	19.8	18.6	16.3	15.1	12.8	11.6	9.3	7.0	4.6	2.3	1.2
92.5°	303.3	374.6	380.7	265.2	158.7	95.3	61.4	41.4	27.0	17.2	14.2
95°	1007.4	1029.5	840.1	519.4	263.8	139.4	87.1	61.6	48.8	39.5	38.3
97.5°	1274.7	1099.4	750.2	414.6	227.3	145.0	107.4	84.4	71.6	65.1	63.7
100°	1339.7	1049.2	669.3	376.5	225.4	158.0	123.2	101.1	88.3	83.7	81.3
102.5°	1300.7	960.9	607.9	360.7	233.8	173.8	139.9	119.7	106.0	102.3	100.9
105°	1175.9	842.4	548.4	354.4	251.0	199.9	167.3	148.7	137.1	131.3	131.3
107.5°	1048.6	760.8	523.3	365.1	276.5	227.0	197.8	178.5	168.9	163.4	161.0
110°	976.0	722.7	515.9	375.3	295.1	247.5	217.3	199.9	189.4	184.8	182.4



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	922.1	700.4	515.9	388.3	312.8	267.0	237.7	220.3	209.8	206.1	203.8
115°	863.3	676.3	519.4	407.8	340.5	297.5	268.4	251.0	240.5	237.0	234.7
117.5°	828.2	664.4	527.1	430.2	368.8	328.1	300.0	280.3	269.8	266.1	262.6
120°	808.7	658.8	534.5	445.0	389.3	348.6	319.5	299.8	289.3	284.7	281.2
122.5°	792.0	654.2	541.0	461.8	408.8	368.1	339.1	317.4	307.0	303.3	300.7
125°	769.2	648.4	551.9	484.5	434.6	396.2	366.0	343.9	333.5	327.7	325.3
127.5°	748.3	645.6	564.2	505.5	459.4	422.5	392.3	368.8	355.6	348.1	344.6
130°	734.4	643.7	571.7	519.4	475.2	439.2	409.0	384.6	369.5	360.2	356.7
132.5°	723.2	643.7	580.0	531.5	490.1	454.1	423.9	398.6	381.6	370.4	366.0
135°	710.0	643.7	591.4	548.4	510.1	474.1	442.7	418.3	399.7	385.8	381.1
137.5°	698.1	645.1	601.9	561.0	524.3	491.5	459.2	435.3	416.7	403.7	400.2
140°	692.5	646.0	606.5	569.4	534.5	500.8	469.4	447.4	428.8	414.8	411.3
142.5°	687.9	647.0	609.3	574.0	541.0	509.2	479.7	458.5	439.9	426.9	424.3
145°	680.9	646.0	612.4	581.0	551.9	521.7	495.0	474.1	457.8	446.2	443.9
147.5°	673.7	643.0	613.5	585.2	558.9	532.4	508.9	490.8	475.7	465.7	464.3
150°	668.1	640.2	613.5	588.0	563.5	538.0	518.2	502.0	486.9	478.7	476.4
152.5°	661.6	636.5	612.6	589.8	568.2	544.5	526.6	511.3	498.0	490.8	489.4
155°	650.7	629.8	610.0	591.4	572.8	553.1	536.8	525.2	513.6	506.6	506.6
157.5°	640.5	622.8	607.0	592.6	576.8	559.8	547.5	537.3	527.3	521.7	522.0
160°	632.1	618.2	604.2	592.6	578.7	563.5	553.1	543.8	535.7	531.0	532.2
162.5°	624.7	612.6	601.4	591.7	580.5	567.3	558.7	551.2	544.0	539.4	540.5
165°	613.5	604.2	597.2	590.3	581.0	571.7	564.7	560.1	554.3	550.8	553.1
167.5°	602.6	596.1	590.7	587.5	581.0	573.3	568.9	565.6	562.4	560.3	561.5
170°	596.1	591.4	588.0	585.6	581.0	575.2	571.7	569.4	567.0	565.9	567.0
172.5°	589.6	585.9	584.2	583.8	580.0	575.2	573.5	572.1	569.8	568.7	570.8
175°	581.0	579.8	579.8	581.0	578.7	575.2	575.2	575.2	574.0	572.8	575.2
177.5°	577.3	576.3	576.3	578.2	577.3	575.4	575.4	576.3	575.4	575.4	577.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1846.5	1855.3	1860.9	1871.5	1880.2	1885.2	1889.6	1893.3	1897.7	1901.4	1912.0
5°	1858.4	1878.6	1895.8	1922.3	1946.5	1965.2	1985.4	2003.4	2018.2	2039.2	2055.6
7.5°	1853.2	1889.2	1927.0	1968.0	2009.9	2048.9	2084.8	2118.3	2148.7	2185.5	2217.7
10°	1848.2	1897.4	1945.7	2001.0	2057.9	2106.3	2151.5	2197.5	2231.0	2277.8	2317.5
12.5°	1844.5	1902.3	1960.7	2027.2	2089.7	2158.0	2218.2	2251.7	2302.7	2340.1	2387.4
15°	1828.8	1905.2	1985.4	2060.3	2149.1	2212.3	2265.3	2330.8	2378.3	2425.9	2477.3
17.5°	1800.5	1887.1	1976.9	2074.9	2160.2	2228.0	2296.3	2359.5	2416.2	2480.0	2544.0
20°	1787.4	1874.0	1976.9	2077.4	2160.8	2231.8	2301.9	2371.3	2433.7	2515.5	2589.6
22.5°	1760.0	1864.6	1959.4	2057.5	2143.4	2220.5	2300.1	2378.8	2461.7	2554.2	2646.9
25°	1711.1	1817.1	1917.6	2014.3	2100.8	2197.5	2282.4	2387.7	2493.7	2616.1	2731.4
27.5°	1660.2	1761.7	1853.9	1947.2	2048.1	2157.6	2267.8	2387.2	2526.0	2680.5	2843.2
30°	1619.1	1714.9	1804.6	1900.5	2005.7	2128.9	2249.7	2391.6	2552.2	2726.0	2919.3
32.5°	1571.0	1659.4	1746.6	1848.1	1962.7	2092.7	2233.5	2389.1	2582.1	2779.6	2978.6
35°	1488.9	1562.9	1652.6	1760.9	1890.3	2039.2	2202.2	2386.1	2607.5	2834.3	3001.9
37.5°	1391.4	1460.4	1554.8	1673.6	1809.3	1969.1	2162.4	2380.7	2615.8	2796.6	2850.7
40°	1326.0	1389.9	1488.1	1611.3	1750.0	1919.2	2131.2	2362.0	2589.6	2704.9	2660.5
42.5°	1256.1	1323.2	1418.9	1540.8	1690.2	1874.3	2091.9	2322.7	2513.5	2557.1	2403.6
45°	1145.9	1215.3	1309.6	1432.8	1593.3	1792.9	2019.7	2229.4	2339.3	2260.6	2022.9
47.5°	1043.5	1108.5	1195.9	1323.0	1488.7	1695.1	1913.6	2080.9	2089.6	1901.7	1647.8
50°	973.6	1033.6	1121.7	1248.8	1413.3	1622.2	1819.4	1951.1	1891.9	1679.1	1435.1
52.5°	905.0	963.8	1050.6	1176.5	1339.1	1530.5	1714.0	1806.5	1694.8	1476.4	1268.0
55°	806.0	857.5	942.4	1058.6	1212.9	1390.7	1546.6	1578.5	1433.5	1218.4	1049.2
57.5°	709.4	757.4	834.7	941.7	1082.8	1240.2	1362.1	1355.3	1202.0	1017.4	883.2
60°	643.9	690.7	759.3	863.7	992.3	1128.0	1232.4	1207.5	1055.5	896.5	783.4
62.5°	585.3	627.0	691.9	783.3	900.7	1026.3	1112.1	1075.3	926.4	787.3	698.0
65°	498.9	534.0	589.3	667.3	764.7	868.4	934.6	887.1	760.0	651.7	580.0
67.5°	416.4	444.5	490.9	553.1	636.2	719.5	759.9	712.0	610.4	531.3	478.2
70°	364.0	389.0	424.8	480.2	552.7	622.8	653.2	610.4	523.1	455.2	417.0
72.5°	311.7	332.2	363.7	413.5	471.6	532.4	559.1	518.1	446.4	389.1	353.4
75°	240.9	254.9	276.7	311.0	357.0	405.4	420.2	384.3	338.3	295.4	272.1
77.5°	172.4	184.3	200.8	222.5	255.1	285.8	298.7	278.0	242.4	215.3	196.1
80°	132.5	138.8	152.8	170.7	196.4	215.9	224.5	211.3	186.3	166.0	151.2
82.5°	94.5	100.7	109.1	123.9	140.3	153.6	162.8	153.9	135.8	119.9	111.3
85°	46.0	49.9	54.6	60.8	73.3	81.1	80.3	74.8	67.8	61.6	56.9
87.5°	16.7	17.8	20.1	23.7	26.0	28.7	30.5	29.4	27.4	25.8	24.1
90°	2.3	4.6	7.0	9.3	11.6	12.8	15.1	16.3	18.6	19.8	20.9
92.5°	17.2	27.0	41.4	61.4	95.3	158.7	265.2	380.7	374.6	303.3	205.9
95°	39.5	48.8	61.6	87.1	139.4	263.8	519.4	840.1	1029.5	1007.4	835.4
97.5°	65.1	71.6	84.4	107.4	145.0	227.3	414.6	750.2	1099.4	1274.7	1244.2
100°	83.7	88.3	101.1	123.2	158.0	225.4	376.5	669.3	1049.2	1339.7	1429.2
102.5°	102.3	106.0	119.7	139.9	173.8	233.8	360.7	607.9	960.9	1300.7	1491.5
105°	131.3	137.1	148.7	167.3	199.9	251.0	354.4	548.4	842.4	1175.9	1454.8
107.5°	163.4	168.9	178.5	197.8	227.0	276.5	365.1	523.3	760.8	1048.6	1323.7
110°	184.8	189.4	199.9	217.3	247.5	295.1	375.3	515.9	722.7	976.0	1227.0



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	206.1	209.8	220.3	237.7	267.0	312.8	388.3	515.9	700.4	922.1	1150.8
115°	237.0	240.5	251.0	268.4	297.5	340.5	407.8	519.4	676.3	863.3	1055.1
117.5°	266.1	269.8	280.3	300.0	328.1	368.8	430.2	527.1	664.4	828.2	993.2
120°	284.7	289.3	299.8	319.5	348.6	389.3	445.0	534.5	658.8	808.7	959.8
122.5°	303.3	307.0	317.4	339.1	368.1	408.8	461.8	541.0	654.2	792.0	934.7
125°	327.7	333.5	343.9	366.0	396.2	434.6	484.5	551.9	648.4	769.2	898.2
127.5°	348.1	355.6	368.8	392.3	422.5	459.4	505.5	564.2	645.6	748.3	861.0
130°	360.2	369.5	384.6	409.0	439.2	475.2	519.4	571.7	643.7	734.4	837.8
132.5°	370.4	381.6	398.6	423.9	454.1	490.1	531.5	580.0	643.7	723.2	814.5
135°	385.8	399.7	418.3	442.7	474.1	510.1	548.4	591.4	643.7	710.0	784.3
137.5°	403.7	416.7	435.3	459.2	491.5	524.3	561.0	601.9	645.1	698.1	758.8
140°	414.8	428.8	447.4	469.4	500.8	534.5	569.4	606.5	646.0	692.5	744.8
142.5°	426.9	439.9	458.5	479.7	509.2	541.0	574.0	609.3	647.0	687.9	732.7
145°	446.2	457.8	474.1	495.0	521.7	551.9	581.0	612.4	646.0	680.9	716.9
147.5°	465.7	475.7	490.8	508.9	532.4	558.9	585.2	613.5	643.0	673.7	702.1
150°	478.7	486.9	502.0	518.2	538.0	563.5	588.0	613.5	640.2	668.1	693.7
152.5°	490.8	498.0	511.3	526.6	544.5	568.2	589.8	612.6	636.5	661.6	684.4
155°	506.6	513.6	525.2	536.8	553.1	572.8	591.4	610.0	629.8	650.7	670.4
157.5°	521.7	527.3	537.3	547.5	559.8	576.8	592.6	607.0	622.8	640.5	656.5
160°	531.0	535.7	543.8	553.1	563.5	578.7	592.6	604.2	618.2	632.1	647.2
162.5°	539.4	544.0	551.2	558.7	567.3	580.5	591.7	601.4	612.6	624.7	637.0
165°	550.8	554.3	560.1	564.7	571.7	581.0	590.3	597.2	604.2	613.5	622.8
167.5°	560.3	562.4	565.6	568.9	573.3	581.0	587.5	590.7	596.1	602.6	609.3
170°	565.9	567.0	569.4	571.7	575.2	581.0	585.6	588.0	591.4	596.1	601.9
172.5°	568.7	569.8	572.1	573.5	575.2	580.0	583.8	584.2	585.9	589.6	593.5
175°	572.8	574.0	575.2	575.2	575.2	578.7	581.0	579.8	579.8	581.0	584.5
177.5°	575.4	575.4	576.3	575.4	575.4	577.3	578.2	576.3	576.3	577.3	578.2
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1920.7	1925.7	1936.3	1932.6	1937.6	1940.1	1942.6
5°	2075.9	2100.8	2111.7	2110.2	2126.5	2122.6	2118.7
7.5°	2251.1	2277.3	2292.0	2310.2	2320.8	2321.6	2330.8
10°	2350.3	2384.6	2398.6	2418.1	2430.6	2437.6	2436.8
12.5°	2426.3	2453.2	2484.6	2494.2	2511.0	2519.9	2516.6
15°	2517.9	2560.7	2593.5	2609.8	2630.9	2637.1	2645.7
17.5°	2599.6	2657.1	2695.3	2746.1	2765.3	2777.0	2770.1
20°	2661.3	2736.9	2775.1	2835.9	2869.4	2887.4	2881.1
22.5°	2734.3	2816.1	2886.7	2939.4	2990.4	3014.6	3019.6
25°	2859.3	2971.5	3075.2	3144.6	3207.7	3222.5	3255.3
27.5°	2999.0	3131.3	3242.2	3315.2	3359.1	3375.6	3385.9
30°	3086.9	3218.6	3302.1	3348.8	3362.9	3361.3	3359.7
32.5°	3129.9	3212.4	3228.5	3215.4	3183.3	3156.1	3127.8
35°	3069.0	3007.4	2915.4	2796.9	2709.6	2621.5	2613.0
37.5°	2760.1	2563.2	2410.1	2239.1	2140.4	2079.5	2037.4
40°	2469.5	2245.8	2060.3	1916.1	1815.5	1775.8	1736.8
42.5°	2154.0	1940.2	1775.9	1655.4	1579.8	1535.7	1504.8
45°	1750.0	1561.4	1432.8	1345.5	1285.4	1251.1	1231.6
47.5°	1434.0	1294.5	1185.2	1122.2	1080.7	1054.1	1054.2
50°	1264.4	1131.1	1058.6	1008.7	972.8	951.8	955.7
52.5°	1114.1	1014.5	952.6	910.8	884.3	871.3	870.9
55°	931.5	859.8	819.3	788.9	770.9	756.1	759.3
57.5°	796.8	736.3	709.2	684.0	671.5	665.6	657.0
60°	713.3	666.5	643.1	622.8	610.4	605.7	597.1
62.5°	639.1	602.3	579.5	563.0	551.7	550.2	543.5
65°	537.1	509.0	488.8	481.0	469.3	466.2	466.2
67.5°	442.8	422.7	406.9	399.7	394.6	395.4	391.6
70°	383.5	367.2	357.0	349.2	345.3	346.1	343.0
72.5°	335.5	317.3	308.4	303.7	298.6	300.6	299.3
75°	254.1	244.8	240.1	235.4	232.3	230.7	229.2
77.5°	186.6	178.4	174.8	172.1	172.6	168.8	171.8
80°	144.2	137.2	134.9	131.0	130.2	130.2	129.4
82.5°	105.5	101.6	99.9	96.7	95.3	96.5	94.5
85°	54.6	51.4	50.7	50.7	49.1	47.6	51.4
87.5°	24.4	22.1	22.6	22.0	22.0	21.6	20.3
90°	22.1	23.2	25.6	25.6	25.6	26.7	26.7
92.5°	149.4	112.5	95.3	80.4	77.6	76.0	74.1
95°	658.8	515.9	418.3	335.8	300.9	291.7	273.1
97.5°	1120.4	981.2	845.4	773.6	708.6	674.9	660.0
100°	1372.3	1252.6	1131.7	1051.6	967.9	924.9	906.3
102.5°	1526.6	1469.2	1387.4	1301.6	1242.1	1195.4	1181.5
105°	1614.0	1665.1	1652.3	1615.1	1576.8	1553.5	1539.6
107.5°	1536.1	1667.4	1728.1	1746.9	1746.7	1739.0	1729.7
110°	1447.8	1611.6	1710.4	1762.7	1784.8	1792.9	1792.9



TEST NUMBER: P333333

CATALOG NUMBER: S125DIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1360.4	1526.1	1642.5	1719.0	1756.9	1777.1	1785.5
115°	1235.2	1394.3	1521.0	1611.6	1667.4	1699.9	1715.0
117.5°	1148.5	1285.6	1401.8	1492.4	1550.1	1582.4	1591.6
120°	1099.2	1227.0	1329.3	1415.3	1471.0	1502.4	1511.7
122.5°	1063.9	1177.8	1273.5	1350.2	1401.3	1432.7	1441.1
125°	1016.7	1117.8	1201.5	1266.5	1314.2	1339.7	1351.4
127.5°	971.6	1066.0	1144.3	1203.3	1245.4	1269.6	1274.7
130°	940.0	1030.7	1106.2	1164.3	1202.6	1225.9	1232.8
132.5°	910.3	992.5	1065.3	1123.4	1161.7	1183.1	1191.0
135°	864.5	938.9	1005.1	1056.2	1094.6	1115.5	1122.5
137.5°	823.6	885.4	941.7	987.4	1022.3	1041.6	1049.2
140°	799.4	852.9	901.7	944.7	974.9	992.3	998.1
142.5°	779.0	825.0	867.3	903.8	929.3	945.8	950.7
145°	752.9	789.0	820.3	848.2	868.0	880.8	885.4
147.5°	731.3	759.0	782.7	804.8	820.6	828.0	830.1
150°	719.3	741.3	762.2	779.7	793.6	798.3	799.4
152.5°	707.2	727.4	743.7	758.3	769.4	774.1	775.3
155°	689.0	705.3	718.1	729.7	737.8	741.3	742.5
157.5°	671.8	684.4	694.4	703.4	710.2	713.4	713.2
160°	658.8	670.4	678.6	686.7	692.5	694.9	693.7
162.5°	647.7	657.4	664.6	670.9	675.8	676.3	676.0
165°	630.9	637.9	643.7	648.4	650.7	650.7	650.7
167.5°	614.7	620.0	624.2	626.5	628.6	627.7	627.5
170°	605.4	608.9	611.2	613.5	614.7	614.7	613.5
172.5°	597.0	599.6	601.0	601.4	603.5	601.7	600.5
175°	584.5	586.8	586.8	586.8	588.0	585.6	584.5
177.5°	579.1	579.1	579.1	578.2	579.1	576.3	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3

(END OF REPORT)