

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333143-940

Luminaire Tested: **S125DIP-S375D1035U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333143-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D1035U940-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4564.5 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30				
1	93	89	86	82	84	80	77	74	63	61	59	48	47	45	34	33	32	26				
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	28	27	22				
3	78	69	62	56	69	62	56	51	49	45	42	37	35	32	26	25	23	18				
4	71	61	53	47	64	55	48	43	44	39	35	33	30	28	24	22	20	16				
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	18	14				
6	60	48	41	35	54	44	37	32	35	30	26	27	23	21	19	17	15	12				
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	18	15	14	11				
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10				
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3135	3135	3135	3135
5°	3630	3146	2755	3146
10°	4224	3129	2413	3129
15°	4676	3107	2226	3107
20°	5234	3070	2076	3070
25°	6131	3029	2003	3029
30°	6623	2988	1939	2988
35°	5445	2912	1898	2912
40°	3871	2807	1851	2807
45°	2974	2665	1825	2665
50°	2538	2488	1822	2488
55°	2260	2315	1838	2315
60°	2038	2126	1885	2126
65°	1883	1936	1933	1936
70°	1713	1739	1962	1739
75°	1510	1532	1941	1532
80°	1272	1250	1778	1250
85°	1008	897	1438	897



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	1.0
10°-20°	139.1	3.0
20°-30°	225.9	4.9
30°-40°	275.6	6.0
40°-50°	250.7	5.5
50°-60°	199.7	4.4
60°-70°	139.1	3.0
70°-80°	74.2	1.6
80°-90°	21.2	0.5
90°-100°	76.6	1.7
100°-110°	226.3	5.0
110°-120°	383.2	8.4
120°-130°	504.3	11.0
130°-140°	565.1	12.4
140°-150°	553.9	12.1
150°-160°	465.2	10.2
160°-170°	309.2	6.8
170°-180°	108.2	2.4
0°-30°	411.8	9.0
0°-40°	687.4	15.1
0°-60°	1137.8	24.9
0°-90°	1372.3	30.1
90°-120°	686.1	15.0
90°-150°	2309.5	50.6
90°-180°	3192.0	69.9
0°-180°	4564.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	560	485	425	485	560	56
15°	699	465	333	465	699	200
25°	860	425	281	425	860	393
35°	691	369	241	369	691	423
45°	326	292	200	292	326	261
55°	201	206	163	206	201	181
65°	123	127	126	127	123	122
75°	60	61	78	61	60	65
85°	14	12	19	12	14	16
90°	21	1	21	1	21	13
95°	77	58	77	58	77	78
105°	221	203	221	203	221	234
115°	387	384	387	384	387	383
125°	564	560	564	560	564	503
135°	731	728	731	728	731	564
145°	886	882	886	882	886	553
155°	1010	1010	1010	1010	1010	465
165°	1095	1098	1095	1098	1095	309
175°	1137	1141	1137	1141	1137	108
180°	1144	1144	1144	1144	1144	



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	513.4	512.8	512.1	510.9	511.8	509.0	507.7	505.4	502.6	501.6	500.4
5°	560.0	561.1	562.1	557.8	558.2	555.3	548.7	543.3	539.0	533.4	529.5
7.5°	616.1	613.7	613.4	610.6	605.8	601.9	595.0	586.2	577.7	567.9	559.9
10°	644.1	644.4	642.5	639.2	634.0	630.3	621.3	612.6	602.1	589.7	580.9
12.5°	665.2	666.1	663.7	659.2	656.7	648.5	641.3	631.1	618.6	608.7	595.2
15°	699.3	697.1	695.4	689.8	685.5	676.9	665.6	654.8	641.2	628.7	616.1
17.5°	732.2	734.1	730.9	725.9	712.4	702.3	687.2	672.4	655.5	638.6	623.7
20°	761.5	763.2	758.5	749.6	733.5	723.4	703.5	684.5	664.9	643.3	626.8
22.5°	798.2	796.8	790.4	776.9	763.0	744.4	722.7	699.6	675.1	650.7	628.7
25°	860.4	851.8	847.8	831.2	812.9	785.4	755.8	722.0	691.5	659.2	631.2
27.5°	895.0	892.2	887.9	876.3	857.0	827.7	792.7	751.5	708.6	667.7	631.0
30°	888.1	888.5	888.9	885.2	872.8	850.8	815.9	771.7	720.5	674.6	632.1
32.5°	826.7	834.2	841.4	849.9	853.4	849.1	827.3	787.3	734.7	682.5	631.5
35°	690.6	692.9	716.2	739.3	770.6	795.0	811.2	793.4	749.2	689.2	630.7
37.5°	538.5	549.7	565.8	591.8	637.0	677.5	729.6	753.5	739.2	691.4	629.3
40°	459.1	469.4	479.9	506.5	544.6	593.6	652.7	703.2	715.0	684.5	624.3
42.5°	397.8	405.9	417.6	437.6	469.4	512.8	569.4	635.3	675.9	664.4	613.9
45°	325.6	330.7	339.7	355.6	378.7	412.7	462.5	534.7	597.5	618.3	589.3
47.5°	278.7	278.7	285.7	296.6	313.3	342.1	379.1	435.5	502.7	552.3	550.0
50°	252.6	251.6	257.2	266.6	279.8	299.0	334.2	379.3	443.8	500.1	515.8
52.5°	230.2	230.3	233.7	240.8	251.8	268.1	294.4	335.2	390.2	448.0	477.5
55°	200.7	199.8	203.8	208.5	216.6	227.3	246.2	277.3	322.1	378.9	417.2
57.5°	173.6	175.9	177.5	180.7	187.4	194.7	210.6	233.4	268.9	317.7	358.2
60°	157.8	160.1	161.3	164.6	170.0	176.2	188.5	207.1	236.9	279.0	319.1
62.5°	143.7	145.4	145.9	148.8	153.2	159.2	168.9	184.5	208.1	244.9	284.2
65°	123.2	123.2	124.0	127.2	129.2	134.6	142.0	153.3	172.3	200.9	234.5
67.5°	103.5	104.5	104.3	105.7	107.5	111.7	117.0	126.4	140.4	161.3	188.2
70°	90.7	91.5	91.3	92.3	94.3	97.0	101.4	110.2	120.3	138.2	161.3
72.5°	79.1	79.5	78.9	80.3	81.5	83.8	88.7	93.5	102.8	118.0	137.0
75°	60.5	61.0	61.4	62.2	63.5	64.7	67.1	71.9	78.1	89.4	101.6
77.5°	45.4	44.6	45.7	45.5	46.2	47.2	49.3	51.8	56.9	64.1	73.5
80°	34.2	34.4	34.4	34.6	35.7	36.3	38.1	39.9	43.9	49.2	55.8
82.5°	25.0	25.5	25.1	25.6	26.4	26.8	27.9	29.4	31.7	35.9	40.7
85°	13.6	12.6	13.0	13.4	13.4	13.6	14.4	15.1	16.3	17.9	19.8
87.5°	8.2	8.5	8.5	8.4	8.4	8.3	8.7	8.6	8.8	9.1	9.5
90°	21.4	20.8	20.2	19.6	19.0	18.2	17.2	16.2	15.2	14.3	12.8
92.5°	42.0	41.6	41.1	40.8	40.3	39.4	38.1	36.8	35.5	34.2	32.5
95°	76.6	76.2	75.8	75.3	75.0	74.1	72.7	71.3	69.9	68.6	66.6
97.5°	116.1	115.8	115.7	115.4	115.1	114.4	113.1	111.7	110.5	109.1	106.4
100°	146.0	145.6	145.2	144.8	144.5	143.3	141.5	139.7	137.9	136.2	133.7
102.5°	175.9	175.4	174.8	174.2	173.7	172.5	170.5	168.5	166.7	164.7	163.4
105°	220.8	220.2	219.6	219.0	218.4	217.5	216.3	215.2	213.9	212.8	211.6
107.5°	266.7	266.8	266.8	266.8	266.9	266.6	266.0	265.4	264.8	264.2	263.3
110°	300.9	301.1	301.3	301.5	301.7	301.5	300.9	300.3	299.7	299.1	298.5



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	334.4	334.7	335.1	335.5	335.8	335.8	335.6	335.3	335.0	334.7	333.9
115°	387.3	387.4	387.6	387.8	388.1	388.3	388.4	388.6	388.9	389.1	388.6
117.5°	438.9	439.7	440.5	441.2	442.0	442.4	442.2	442.0	441.9	441.8	441.4
120°	474.5	475.3	476.1	476.9	477.7	478.0	478.0	478.0	478.0	478.0	477.9
122.5°	510.1	510.8	511.4	512.0	512.6	513.0	513.2	513.4	513.5	513.6	513.2
125°	563.6	563.7	563.9	564.1	564.3	564.6	565.0	565.4	565.8	566.2	566.0
127.5°	614.8	615.2	615.5	616.0	616.4	616.7	616.9	617.1	617.2	617.5	617.2
130°	649.0	649.3	649.8	650.1	650.6	650.9	651.0	651.2	651.5	651.7	651.2
132.5°	681.0	681.6	682.2	682.7	683.2	683.6	683.9	684.0	684.2	684.4	684.5
135°	730.8	731.6	732.5	733.3	734.1	734.4	734.4	734.4	734.4	734.4	734.2
137.5°	779.7	780.7	781.7	782.7	783.6	784.0	783.7	783.5	783.3	783.0	782.7
140°	811.0	812.0	813.0	814.0	814.9	815.3	814.8	814.5	814.0	813.7	813.1
142.5°	840.9	842.0	842.9	843.9	844.9	845.3	845.0	844.8	844.5	844.3	843.6
145°	885.8	886.4	887.0	887.6	888.1	888.5	888.5	888.5	888.5	888.5	887.9
147.5°	924.1	925.4	926.8	928.1	929.4	929.9	929.4	928.9	928.4	928.0	927.5
150°	952.5	953.0	953.3	953.8	954.1	954.3	954.3	954.3	954.3	954.3	953.5
152.5°	976.1	976.8	977.5	978.2	978.9	979.0	978.6	978.1	977.6	977.1	976.8
155°	1009.5	1010.5	1011.5	1012.5	1013.5	1013.6	1012.8	1012.0	1011.2	1010.4	1010.2
157.5°	1037.5	1038.8	1040.1	1041.4	1042.7	1042.9	1042.1	1041.3	1040.6	1039.8	1039.6
160°	1056.7	1057.7	1058.7	1059.7	1060.7	1060.8	1060.0	1059.2	1058.4	1057.6	1057.4
162.5°	1073.1	1074.2	1075.4	1076.6	1077.7	1077.8	1076.8	1075.8	1075.0	1074.0	1074.0
165°	1095.0	1096.2	1097.3	1098.6	1099.7	1099.9	1099.1	1098.3	1097.6	1096.8	1096.5
167.5°	1112.4	1113.7	1114.9	1116.2	1117.3	1117.4	1116.2	1115.0	1113.8	1112.6	1112.6
170°	1121.7	1123.1	1124.4	1125.9	1127.2	1127.3	1126.1	1125.0	1123.8	1122.6	1122.6
172.5°	1129.5	1130.8	1132.0	1133.2	1134.4	1134.4	1133.3	1132.1	1130.9	1129.7	1129.7
175°	1136.8	1138.2	1139.6	1141.0	1142.4	1142.5	1141.3	1140.1	1138.9	1137.7	1137.7
177.5°	1141.1	1142.2	1143.4	1144.4	1145.6	1145.6	1144.7	1143.7	1142.8	1141.8	1142.0
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	499.4	498.3	497.0	494.6	491.9	490.4	488.1	486.6	483.7	481.2	478.5
5°	524.8	519.4	514.5	508.1	501.1	496.6	491.2	485.3	479.0	472.7	465.7
7.5°	551.1	541.5	531.3	520.2	509.3	499.4	489.8	480.5	471.8	461.2	452.3
10°	568.6	556.7	543.9	529.0	514.2	501.5	488.6	477.2	465.7	453.3	442.4
12.5°	586.3	570.4	552.3	535.8	518.3	502.8	487.6	473.1	458.6	444.9	432.1
15°	598.8	584.8	568.1	544.6	524.8	503.5	483.4	464.7	447.1	431.9	415.8
17.5°	607.0	588.9	571.0	548.5	522.5	498.8	475.9	454.4	434.7	415.4	399.9
20°	608.4	589.9	571.1	549.1	522.5	495.3	472.4	446.7	425.5	405.5	386.6
22.5°	608.0	586.9	566.5	543.9	517.9	492.8	465.2	439.0	415.9	396.3	376.5
25°	603.3	580.9	555.3	532.4	506.8	480.3	452.3	425.1	401.6	379.2	359.5
27.5°	599.4	570.3	541.4	514.7	490.0	465.7	438.8	411.0	385.0	362.2	343.8
30°	594.7	562.7	530.1	502.3	477.0	453.3	427.9	400.7	373.5	351.3	331.5
32.5°	590.4	553.1	518.8	488.5	461.6	438.6	415.3	389.4	362.7	340.1	320.3
35°	582.1	539.0	499.6	465.5	436.8	413.1	393.5	369.4	344.9	323.1	304.2
37.5°	571.6	520.5	478.2	442.4	411.0	386.0	367.8	349.3	325.7	304.7	287.6
40°	563.3	507.3	462.5	425.9	393.3	367.4	350.4	333.0	313.4	293.8	275.7
42.5°	552.9	495.4	446.7	407.2	375.1	349.7	332.0	317.2	299.9	281.6	264.8
45°	533.9	473.9	421.2	378.7	346.2	321.2	302.9	291.8	278.7	261.4	247.3
47.5°	505.8	448.1	393.5	349.7	316.1	293.0	275.8	265.1	256.0	243.2	230.2
50°	480.9	428.8	373.5	330.1	296.5	273.2	257.3	247.6	239.9	230.0	219.0
52.5°	453.1	404.6	353.9	310.9	277.7	254.8	239.2	230.7	224.2	217.1	206.3
55°	408.8	367.6	320.6	279.8	249.1	226.7	213.0	205.6	200.3	194.9	188.3
57.5°	360.1	327.8	286.2	248.9	220.6	200.2	187.5	180.3	176.1	173.3	169.5
60°	325.7	298.2	262.3	228.3	200.7	182.5	170.2	164.6	161.1	158.9	156.0
62.5°	293.9	271.3	238.1	207.1	182.9	165.8	154.7	149.3	146.0	144.8	142.5
65°	247.1	229.5	202.2	176.4	155.8	141.2	131.9	126.7	124.7	123.4	123.6
67.5°	200.8	190.2	168.2	146.2	129.7	117.5	110.0	106.1	105.0	103.4	103.4
70°	172.6	164.6	146.1	126.9	112.3	102.8	96.2	92.1	91.0	90.2	90.1
72.5°	147.8	140.7	124.7	109.3	96.1	87.8	82.4	79.9	78.2	77.8	77.7
75°	111.0	107.2	94.3	82.2	73.1	67.4	63.7	61.4	60.2	59.9	60.2
77.5°	78.9	75.5	67.4	58.8	53.1	48.7	45.6	44.8	43.4	43.4	43.2
80°	59.3	57.1	51.9	45.1	40.4	36.6	35.0	33.6	33.2	32.5	33.2
82.5°	43.0	40.6	37.1	32.7	28.8	26.7	25.0	24.5	24.3	24.0	24.1
85°	21.2	21.4	19.4	16.1	14.4	13.2	12.1	12.1	11.9	11.8	11.9
87.5°	9.5	8.9	8.0	7.2	6.1	5.3	4.8	4.6	4.5	4.6	5.1
90°	11.5	10.1	8.7	7.2	5.6	4.0	2.5	0.9	2.5	4.0	5.6
92.5°	30.8	29.1	27.4	25.9	24.9	23.7	22.6	21.6	22.6	23.7	24.9
95°	64.6	62.6	60.6	59.5	59.0	58.7	58.2	57.9	58.2	58.7	59.0
97.5°	103.7	100.9	98.3	96.8	96.7	96.5	96.3	96.1	96.3	96.5	96.7
100°	131.1	128.5	125.9	124.7	124.7	124.7	124.7	124.7	124.7	124.7	124.7
102.5°	162.1	160.8	159.4	158.5	157.7	156.9	156.0	155.2	156.0	156.9	157.7
105°	210.4	209.2	208.0	207.0	206.0	204.9	203.9	203.0	203.9	204.9	206.0
107.5°	262.4	261.4	260.6	259.7	258.7	257.6	256.6	255.7	256.6	257.6	258.7
110°	297.9	297.3	296.8	296.0	295.0	294.0	293.0	292.0	293.0	294.0	295.0



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	333.2	332.5	331.7	331.1	330.6	330.0	329.6	329.0	329.6	330.0	330.6
115°	388.3	387.8	387.4	386.8	386.1	385.3	384.5	383.7	384.5	385.3	386.1
117.5°	441.0	440.7	440.3	440.0	439.6	439.3	438.9	438.5	438.9	439.3	439.6
120°	477.7	477.4	477.2	476.7	475.7	474.7	473.7	472.7	473.7	474.7	475.7
122.5°	512.6	512.1	511.6	511.2	510.9	510.5	510.1	509.8	510.1	510.5	510.9
125°	565.8	565.6	565.4	564.7	563.6	562.3	561.2	560.0	561.2	562.3	563.6
127.5°	617.0	616.8	616.5	616.1	615.4	614.7	614.0	613.4	614.0	614.7	615.4
130°	650.9	650.5	650.1	649.3	648.4	647.4	646.4	645.4	646.4	647.4	648.4
132.5°	684.6	684.7	684.7	683.9	682.3	680.7	679.1	677.4	679.1	680.7	682.3
135°	734.1	733.9	733.7	733.0	731.7	730.6	729.4	728.3	729.4	730.6	731.7
137.5°	782.2	781.8	781.3	780.5	779.4	778.2	777.0	776.0	777.0	778.2	779.4
140°	812.5	811.9	811.3	810.5	809.5	808.5	807.5	806.6	807.5	808.5	809.5
142.5°	842.8	842.0	841.3	840.5	839.6	838.8	838.0	837.1	838.0	838.8	839.6
145°	887.3	886.7	886.1	885.4	884.6	883.8	883.1	882.3	883.1	883.8	884.6
147.5°	927.0	926.6	926.1	925.6	925.2	924.8	924.3	923.9	924.3	924.8	925.2
150°	952.8	952.0	951.2	950.9	951.1	951.3	951.5	951.6	951.5	951.3	951.1
152.5°	976.5	976.2	975.9	975.5	975.3	975.0	974.7	974.5	974.7	975.0	975.3
155°	1010.0	1009.9	1009.6	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5
157.5°	1039.4	1039.2	1039.0	1039.1	1039.6	1040.0	1040.4	1040.9	1040.4	1040.0	1039.6
160°	1057.2	1057.0	1056.9	1057.0	1057.6	1058.2	1058.8	1059.4	1058.8	1058.2	1057.6
162.5°	1073.9	1073.9	1073.8	1074.1	1074.4	1074.9	1075.3	1075.8	1075.3	1074.9	1074.4
165°	1096.4	1096.2	1096.0	1096.1	1096.4	1096.9	1097.3	1097.7	1097.3	1096.9	1096.4
167.5°	1112.6	1112.6	1112.6	1113.0	1113.8	1114.6	1115.4	1116.2	1115.4	1114.6	1113.8
170°	1122.6	1122.6	1122.6	1123.0	1123.8	1124.5	1125.3	1126.1	1125.3	1124.5	1123.8
172.5°	1129.7	1129.7	1129.7	1130.2	1130.9	1131.7	1132.5	1133.3	1132.5	1131.7	1130.9
175°	1137.7	1137.7	1137.7	1138.1	1138.9	1139.7	1140.5	1141.3	1140.5	1139.7	1138.9
177.5°	1142.1	1142.3	1142.5	1142.8	1143.4	1144.2	1144.8	1145.4	1144.8	1144.2	1143.4
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	477.1	475.2	473.8	470.5	468.6	466.2	464.2	466.4	464.0	465.0	463.5
5°	462.2	456.4	452.3	446.3	441.1	436.4	432.9	432.3	430.6	429.8	427.3
7.5°	444.3	437.0	430.0	422.1	415.5	408.8	404.6	401.0	398.7	395.6	393.4
10°	433.7	424.0	415.8	406.4	398.1	390.8	385.1	382.2	379.5	375.6	374.2
12.5°	420.7	410.7	400.6	390.5	382.5	374.5	369.6	365.2	363.4	359.0	358.6
15°	405.1	390.0	380.1	369.9	358.9	352.3	348.2	343.5	341.4	338.3	336.1
17.5°	386.5	373.0	360.7	350.0	340.6	335.1	329.9	326.7	323.2	321.1	317.4
20°	372.9	360.2	347.8	336.4	329.2	322.9	318.8	315.7	311.9	310.9	307.2
22.5°	361.6	347.5	335.6	326.1	318.3	311.0	306.6	304.4	301.9	298.7	298.0
25°	343.0	328.4	318.3	308.9	301.8	295.2	292.2	289.5	287.0	284.7	283.9
27.5°	327.1	314.0	302.0	293.5	287.3	281.3	278.7	275.4	273.6	271.7	269.5
30°	315.8	302.5	291.9	283.7	277.1	271.8	268.9	266.6	265.0	263.3	262.1
32.5°	304.3	291.9	281.8	273.7	267.1	263.1	260.5	258.9	257.1	255.1	253.5
35°	289.1	275.4	265.6	258.6	253.4	250.3	247.4	246.0	244.0	244.0	242.3
37.5°	271.9	260.1	251.4	245.0	240.4	237.6	234.5	233.5	232.2	231.3	230.8
40°	261.7	250.7	242.5	236.1	231.2	228.9	226.4	224.8	224.0	222.9	222.6
42.5°	251.1	240.7	232.8	226.9	222.6	220.7	218.4	217.2	215.5	214.2	213.9
45°	235.1	225.0	217.8	213.0	209.4	207.1	205.6	203.1	202.3	200.7	200.5
47.5°	219.9	210.2	203.1	199.2	196.0	194.1	191.9	189.4	188.4	187.6	187.5
50°	208.5	199.7	193.1	189.4	186.3	183.6	181.3	179.7	179.1	179.1	179.5
52.5°	197.0	189.4	183.9	179.3	176.4	173.5	171.4	170.4	169.5	170.5	171.2
55°	180.1	172.5	168.4	164.0	161.1	157.8	156.8	156.4	155.8	157.4	158.3
57.5°	162.2	156.9	152.0	147.8	145.2	143.2	141.9	141.6	142.8	143.6	146.2
60°	150.8	144.6	140.4	137.1	133.9	132.7	132.2	131.9	132.7	134.9	138.5
62.5°	138.3	133.3	128.6	126.2	123.9	121.8	121.7	122.0	123.6	126.3	129.7
65°	119.9	115.6	112.5	109.6	107.7	106.6	106.9	107.7	109.6	113.2	117.0
67.5°	101.2	98.3	95.5	93.2	91.4	91.4	91.8	93.1	95.2	99.2	102.8
70°	89.3	86.0	83.6	82.7	81.1	80.3	81.6	83.6	85.5	89.3	92.3
72.5°	77.2	74.4	72.6	71.9	71.2	70.6	71.1	73.3	75.8	79.5	83.1
75°	59.3	58.3	57.1	56.3	55.6	56.1	56.4	58.5	60.5	64.5	68.6
77.5°	43.3	42.3	41.5	41.3	40.9	41.2	42.4	43.9	45.8	48.7	51.8
80°	32.7	32.4	31.9	31.7	31.7	31.9	33.6	34.6	36.5	39.1	41.6
82.5°	23.9	23.6	23.5	23.5	23.6	23.7	24.7	26.0	27.6	29.6	31.7
85°	12.6	12.1	12.8	13.0	12.6	13.2	13.6	14.4	15.1	16.1	17.1
87.5°	5.5	6.2	6.3	6.8	7.0	7.7	7.7	8.6	9.0	9.5	9.5
90°	7.2	8.7	10.1	11.5	12.8	14.3	15.2	16.2	17.2	18.2	19.0
92.5°	25.9	27.4	29.1	30.8	32.5	34.2	35.5	36.8	38.1	39.4	40.3
95°	59.5	60.6	62.6	64.6	66.6	68.6	69.9	71.3	72.7	74.1	75.0
97.5°	96.8	98.3	100.9	103.7	106.4	109.1	110.5	111.7	113.1	114.4	115.1
100°	124.7	125.9	128.5	131.1	133.7	136.2	137.9	139.7	141.5	143.3	144.5
102.5°	158.5	159.4	160.8	162.1	163.4	164.7	166.7	168.5	170.5	172.5	173.7
105°	207.0	208.0	209.2	210.4	211.6	212.8	213.9	215.2	216.3	217.5	218.4
107.5°	259.7	260.6	261.4	262.4	263.3	264.2	264.8	265.4	266.0	266.6	266.9
110°	296.0	296.8	297.3	297.9	298.5	299.1	299.7	300.3	300.9	301.5	301.7



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	331.1	331.7	332.5	333.2	333.9	334.7	335.0	335.3	335.6	335.8	335.8
115°	386.8	387.4	387.8	388.3	388.6	389.1	388.9	388.6	388.4	388.3	388.1
117.5°	440.0	440.3	440.7	441.0	441.4	441.8	441.9	442.0	442.2	442.4	442.0
120°	476.7	477.2	477.4	477.7	477.9	478.0	478.0	478.0	478.0	478.0	477.7
122.5°	511.2	511.6	512.1	512.6	513.2	513.6	513.5	513.4	513.2	513.0	512.6
125°	564.7	565.4	565.6	565.8	566.0	566.2	565.8	565.4	565.0	564.6	564.3
127.5°	616.1	616.5	616.8	617.0	617.2	617.5	617.2	617.1	616.9	616.7	616.4
130°	649.3	650.1	650.5	650.9	651.2	651.7	651.5	651.2	651.0	650.9	650.6
132.5°	683.9	684.7	684.7	684.6	684.5	684.4	684.2	684.0	683.9	683.6	683.2
135°	733.0	733.7	733.9	734.1	734.2	734.4	734.4	734.4	734.4	734.4	734.1
137.5°	780.5	781.3	781.8	782.2	782.7	783.0	783.3	783.5	783.7	784.0	783.6
140°	810.5	811.3	811.9	812.5	813.1	813.7	814.0	814.5	814.8	815.3	814.9
142.5°	840.5	841.3	842.0	842.8	843.6	844.3	844.5	844.8	845.0	845.3	844.9
145°	885.4	886.1	886.7	887.3	887.9	888.5	888.5	888.5	888.5	888.5	888.1
147.5°	925.6	926.1	926.6	927.0	927.5	928.0	928.4	928.9	929.4	929.9	929.4
150°	950.9	951.2	952.0	952.8	953.5	954.3	954.3	954.3	954.3	954.3	954.1
152.5°	975.5	975.9	976.2	976.5	976.8	977.1	977.6	978.1	978.6	979.0	978.9
155°	1009.5	1009.6	1009.9	1010.0	1010.2	1010.4	1011.2	1012.0	1012.8	1013.6	1013.5
157.5°	1039.1	1039.0	1039.2	1039.4	1039.6	1039.8	1040.6	1041.3	1042.1	1042.9	1042.7
160°	1057.0	1056.9	1057.0	1057.2	1057.4	1057.6	1058.4	1059.2	1060.0	1060.8	1060.7
162.5°	1074.1	1073.8	1073.9	1073.9	1074.0	1074.0	1075.0	1075.8	1076.8	1077.8	1077.7
165°	1096.1	1096.0	1096.2	1096.4	1096.5	1096.8	1097.6	1098.3	1099.1	1099.9	1099.7
167.5°	1113.0	1112.6	1112.6	1112.6	1112.6	1112.6	1113.8	1115.0	1116.2	1117.4	1117.3
170°	1123.0	1122.6	1122.6	1122.6	1122.6	1122.6	1123.8	1125.0	1126.1	1127.3	1127.2
172.5°	1130.2	1129.7	1129.7	1129.7	1129.7	1129.7	1130.9	1132.1	1133.3	1134.4	1134.4
175°	1138.1	1137.7	1137.7	1137.7	1137.7	1137.7	1138.9	1140.1	1141.3	1142.5	1142.4
177.5°	1142.8	1142.5	1142.3	1142.1	1142.0	1141.8	1142.8	1143.7	1144.7	1145.6	1145.6
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	462.5	463.7	462.7	464.0	462.7	463.7	462.5	463.5	465.0	464.0	466.4
5°	426.3	424.5	425.7	424.9	425.7	424.5	426.3	427.3	429.8	430.6	432.3
7.5°	392.9	391.1	389.1	388.1	389.1	391.1	392.9	393.4	395.6	398.7	401.0
10°	371.9	369.6	369.4	368.0	369.4	369.6	371.9	374.2	375.6	379.5	382.2
12.5°	356.6	354.5	352.1	351.5	352.1	354.5	356.6	358.6	359.0	363.4	365.2
15°	334.8	333.1	331.7	333.0	331.7	333.1	334.8	336.1	338.3	341.4	343.5
17.5°	316.7	315.4	315.1	313.6	315.1	315.4	316.7	317.4	321.1	323.2	326.7
20°	305.3	304.3	304.8	302.0	304.8	304.3	305.3	307.2	310.9	311.9	315.7
22.5°	296.3	294.3	294.0	293.5	294.0	294.3	296.3	298.0	298.7	301.9	304.4
25°	282.0	281.1	280.0	281.1	280.0	281.1	282.0	283.9	284.7	287.0	289.5
27.5°	269.7	268.4	268.1	268.3	268.1	268.4	269.7	269.5	271.7	273.6	275.4
30°	262.1	260.0	260.2	260.0	260.2	260.0	262.1	262.1	263.3	265.0	266.6
32.5°	253.9	252.4	252.2	251.8	252.2	252.4	253.9	253.5	255.1	257.1	258.9
35°	241.7	241.7	240.7	240.7	240.7	241.7	241.7	242.3	244.0	244.0	246.0
37.5°	230.2	230.1	229.4	229.5	229.4	230.1	230.2	230.8	231.3	232.2	233.5
40°	221.7	221.5	220.9	219.6	220.9	221.5	221.7	222.6	222.9	224.0	224.8
42.5°	213.5	212.8	212.5	212.0	212.5	212.8	213.5	213.9	214.2	215.5	217.2
45°	200.5	200.5	200.1	199.8	200.1	200.5	200.5	200.5	200.7	202.3	203.1
47.5°	187.9	188.2	189.0	188.9	189.0	188.2	187.9	187.5	187.6	188.4	189.4
50°	180.3	180.5	181.1	181.3	181.1	180.5	180.3	179.5	179.1	179.1	179.7
52.5°	171.9	173.1	173.9	173.7	173.9	173.1	171.9	171.2	170.5	169.5	170.4
55°	160.1	161.6	163.0	163.2	163.0	161.6	160.1	158.3	157.4	155.8	156.4
57.5°	148.5	150.4	151.9	152.5	151.9	150.4	148.5	146.2	143.6	142.8	141.6
60°	140.5	143.2	145.1	145.9	145.1	143.2	140.5	138.5	134.9	132.7	131.9
62.5°	133.0	136.0	137.8	137.9	137.8	136.0	133.0	129.7	126.3	123.6	122.0
65°	120.6	123.6	125.3	126.5	125.3	123.6	120.6	117.0	113.2	109.6	107.7
67.5°	107.2	110.3	112.1	113.1	112.1	110.3	107.2	102.8	99.2	95.2	93.1
70°	97.5	100.6	103.0	103.9	103.0	100.6	97.5	92.3	89.3	85.5	83.6
72.5°	87.9	90.7	92.6	93.6	92.6	90.7	87.9	83.1	79.5	75.8	73.3
75°	71.2	75.0	76.9	77.8	76.9	75.0	71.2	68.6	64.5	60.5	58.5
77.5°	54.9	58.3	59.5	60.0	59.5	58.3	54.9	51.8	48.7	45.8	43.9
80°	44.1	46.2	47.6	47.8	47.6	46.2	44.1	41.6	39.1	36.5	34.6
82.5°	33.9	35.6	36.0	36.6	36.0	35.6	33.9	31.7	29.6	27.6	26.0
85°	18.5	19.4	19.6	19.4	19.6	19.4	18.5	17.1	16.1	15.1	14.4
87.5°	10.0	10.0	10.1	10.5	10.1	10.0	10.0	9.5	9.5	9.0	8.6
90°	19.6	20.2	20.8	21.4	20.8	20.2	19.6	19.0	18.2	17.2	16.2
92.5°	40.8	41.1	41.6	42.0	41.6	41.1	40.8	40.3	39.4	38.1	36.8
95°	75.3	75.8	76.2	76.6	76.2	75.8	75.3	75.0	74.1	72.7	71.3
97.5°	115.4	115.7	115.8	116.1	115.8	115.7	115.4	115.1	114.4	113.1	111.7
100°	144.8	145.2	145.6	146.0	145.6	145.2	144.8	144.5	143.3	141.5	139.7
102.5°	174.2	174.8	175.4	175.9	175.4	174.8	174.2	173.7	172.5	170.5	168.5
105°	219.0	219.6	220.2	220.8	220.2	219.6	219.0	218.4	217.5	216.3	215.2
107.5°	266.8	266.8	266.8	266.7	266.8	266.8	266.8	266.9	266.6	266.0	265.4
110°	301.5	301.3	301.1	300.9	301.1	301.3	301.5	301.7	301.5	300.9	300.3



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	335.5	335.1	334.7	334.4	334.7	335.1	335.5	335.8	335.8	335.6	335.3
115°	387.8	387.6	387.4	387.3	387.4	387.6	387.8	388.1	388.3	388.4	388.6
117.5°	441.2	440.5	439.7	438.9	439.7	440.5	441.2	442.0	442.4	442.2	442.0
120°	476.9	476.1	475.3	474.5	475.3	476.1	476.9	477.7	478.0	478.0	478.0
122.5°	512.0	511.4	510.8	510.1	510.8	511.4	512.0	512.6	513.0	513.2	513.4
125°	564.1	563.9	563.7	563.6	563.7	563.9	564.1	564.3	564.6	565.0	565.4
127.5°	616.0	615.5	615.2	614.8	615.2	615.5	616.0	616.4	616.7	616.9	617.1
130°	650.1	649.8	649.3	649.0	649.3	649.8	650.1	650.6	650.9	651.0	651.2
132.5°	682.7	682.2	681.6	681.0	681.6	682.2	682.7	683.2	683.6	683.9	684.0
135°	733.3	732.5	731.6	730.8	731.6	732.5	733.3	734.1	734.4	734.4	734.4
137.5°	782.7	781.7	780.7	779.7	780.7	781.7	782.7	783.6	784.0	783.7	783.5
140°	814.0	813.0	812.0	811.0	812.0	813.0	814.0	814.9	815.3	814.8	814.5
142.5°	843.9	842.9	842.0	840.9	842.0	842.9	843.9	844.9	845.3	845.0	844.8
145°	887.6	887.0	886.4	885.8	886.4	887.0	887.6	888.1	888.5	888.5	888.5
147.5°	928.1	926.8	925.4	924.1	925.4	926.8	928.1	929.4	929.9	929.4	928.9
150°	953.8	953.3	953.0	952.5	953.0	953.3	953.8	954.1	954.3	954.3	954.3
152.5°	978.2	977.5	976.8	976.1	976.8	977.5	978.2	978.9	979.0	978.6	978.1
155°	1012.5	1011.5	1010.5	1009.5	1010.5	1011.5	1012.5	1013.5	1013.6	1012.8	1012.0
157.5°	1041.4	1040.1	1038.8	1037.5	1038.8	1040.1	1041.4	1042.7	1042.9	1042.1	1041.3
160°	1059.7	1058.7	1057.7	1056.7	1057.7	1058.7	1059.7	1060.7	1060.8	1060.0	1059.2
162.5°	1076.6	1075.4	1074.2	1073.1	1074.2	1075.4	1076.6	1077.7	1077.8	1076.8	1075.8
165°	1098.6	1097.3	1096.2	1095.0	1096.2	1097.3	1098.6	1099.7	1099.9	1099.1	1098.3
167.5°	1116.2	1114.9	1113.7	1112.4	1113.7	1114.9	1116.2	1117.3	1117.4	1116.2	1115.0
170°	1125.9	1124.4	1123.1	1121.7	1123.1	1124.4	1125.9	1127.2	1127.3	1126.1	1125.0
172.5°	1133.2	1132.0	1130.8	1129.5	1130.8	1132.0	1133.2	1134.4	1134.4	1133.3	1132.1
175°	1141.0	1139.6	1138.2	1136.8	1138.2	1139.6	1141.0	1142.4	1142.5	1141.3	1140.1
177.5°	1144.4	1143.4	1142.2	1141.1	1142.2	1143.4	1144.4	1145.6	1145.6	1144.7	1143.7
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	464.2	466.2	468.6	470.5	473.8	475.2	477.1	478.5	481.2	483.7	486.6
5°	432.9	436.4	441.1	446.3	452.3	456.4	462.2	465.7	472.7	479.0	485.3
7.5°	404.6	408.8	415.5	422.1	430.0	437.0	444.3	452.3	461.2	471.8	480.5
10°	385.1	390.8	398.1	406.4	415.8	424.0	433.7	442.4	453.3	465.7	477.2
12.5°	369.6	374.5	382.5	390.5	400.6	410.7	420.7	432.1	444.9	458.6	473.1
15°	348.2	352.3	358.9	369.9	380.1	390.0	405.1	415.8	431.9	447.1	464.7
17.5°	329.9	335.1	340.6	350.0	360.7	373.0	386.5	399.9	415.4	434.7	454.4
20°	318.8	322.9	329.2	336.4	347.8	360.2	372.9	386.6	405.5	425.5	446.7
22.5°	306.6	311.0	318.3	326.1	335.6	347.5	361.6	376.5	396.3	415.9	439.0
25°	292.2	295.2	301.8	308.9	318.3	328.4	343.0	359.5	379.2	401.6	425.1
27.5°	278.7	281.3	287.3	293.5	302.0	314.0	327.1	343.8	362.2	385.0	411.0
30°	268.9	271.8	277.1	283.7	291.9	302.5	315.8	331.5	351.3	373.5	400.7
32.5°	260.5	263.1	267.1	273.7	281.8	291.9	304.3	320.3	340.1	362.7	389.4
35°	247.4	250.3	253.4	258.6	265.6	275.4	289.1	304.2	323.1	344.9	369.4
37.5°	234.5	237.6	240.4	245.0	251.4	260.1	271.9	287.6	304.7	325.7	349.3
40°	226.4	228.9	231.2	236.1	242.5	250.7	261.7	275.7	293.8	313.4	333.0
42.5°	218.4	220.7	222.6	226.9	232.8	240.7	251.1	264.8	281.6	299.9	317.2
45°	205.6	207.1	209.4	213.0	217.8	225.0	235.1	247.3	261.4	278.7	291.8
47.5°	191.9	194.1	196.0	199.2	203.1	210.2	219.9	230.2	243.2	256.0	265.1
50°	181.3	183.6	186.3	189.4	193.1	199.7	208.5	219.0	230.0	239.9	247.6
52.5°	171.4	173.5	176.4	179.3	183.9	189.4	197.0	206.3	217.1	224.2	230.7
55°	156.8	157.8	161.1	164.0	168.4	172.5	180.1	188.3	194.9	200.3	205.6
57.5°	141.9	143.2	145.2	147.8	152.0	156.9	162.2	169.5	173.3	176.1	180.3
60°	132.2	132.7	133.9	137.1	140.4	144.6	150.8	156.0	158.9	161.1	164.6
62.5°	121.7	121.8	123.9	126.2	128.6	133.3	138.3	142.5	144.8	146.0	149.3
65°	106.9	106.6	107.7	109.6	112.5	115.6	119.9	123.6	123.4	124.7	126.7
67.5°	91.8	91.4	91.4	93.2	95.5	98.3	101.2	103.4	103.4	105.0	106.1
70°	81.6	80.3	81.1	82.7	83.6	86.0	89.3	90.1	90.2	91.0	92.1
72.5°	71.1	70.6	71.2	71.9	72.6	74.4	77.2	77.7	77.8	78.2	79.9
75°	56.4	56.1	55.6	56.3	57.1	58.3	59.3	60.2	59.9	60.2	61.4
77.5°	42.4	41.2	40.9	41.3	41.5	42.3	43.3	43.2	43.4	43.4	44.8
80°	33.6	31.9	31.7	31.7	31.9	32.4	32.7	33.2	32.5	33.2	33.6
82.5°	24.7	23.7	23.6	23.5	23.5	23.6	23.9	24.1	24.0	24.3	24.5
85°	13.6	13.2	12.6	13.0	12.8	12.1	12.6	11.9	11.8	11.9	12.1
87.5°	7.7	7.7	7.0	6.8	6.3	6.2	5.5	5.1	4.6	4.5	4.6
90°	15.2	14.3	12.8	11.5	10.1	8.7	7.2	5.6	4.0	2.5	0.9
92.5°	35.5	34.2	32.5	30.8	29.1	27.4	25.9	24.9	23.7	22.6	21.6
95°	69.9	68.6	66.6	64.6	62.6	60.6	59.5	59.0	58.7	58.2	57.9
97.5°	110.5	109.1	106.4	103.7	100.9	98.3	96.8	96.7	96.5	96.3	96.1
100°	137.9	136.2	133.7	131.1	128.5	125.9	124.7	124.7	124.7	124.7	124.7
102.5°	166.7	164.7	163.4	162.1	160.8	159.4	158.5	157.7	156.9	156.0	155.2
105°	213.9	212.8	211.6	210.4	209.2	208.0	207.0	206.0	204.9	203.9	203.0
107.5°	264.8	264.2	263.3	262.4	261.4	260.6	259.7	258.7	257.6	256.6	255.7
110°	299.7	299.1	298.5	297.9	297.3	296.8	296.0	295.0	294.0	293.0	292.0



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	335.0	334.7	333.9	333.2	332.5	331.7	331.1	330.6	330.0	329.6	329.0
115°	388.9	389.1	388.6	388.3	387.8	387.4	386.8	386.1	385.3	384.5	383.7
117.5°	441.9	441.8	441.4	441.0	440.7	440.3	440.0	439.6	439.3	438.9	438.5
120°	478.0	478.0	477.9	477.7	477.4	477.2	476.7	475.7	474.7	473.7	472.7
122.5°	513.5	513.6	513.2	512.6	512.1	511.6	511.2	510.9	510.5	510.1	509.8
125°	565.8	566.2	566.0	565.8	565.6	565.4	564.7	563.6	562.3	561.2	560.0
127.5°	617.2	617.5	617.2	617.0	616.8	616.5	616.1	615.4	614.7	614.0	613.4
130°	651.5	651.7	651.2	650.9	650.5	650.1	649.3	648.4	647.4	646.4	645.4
132.5°	684.2	684.4	684.5	684.6	684.7	684.7	683.9	682.3	680.7	679.1	677.4
135°	734.4	734.4	734.2	734.1	733.9	733.7	733.0	731.7	730.6	729.4	728.3
137.5°	783.3	783.0	782.7	782.2	781.8	781.3	780.5	779.4	778.2	777.0	776.0
140°	814.0	813.7	813.1	812.5	811.9	811.3	810.5	809.5	808.5	807.5	806.6
142.5°	844.5	844.3	843.6	842.8	842.0	841.3	840.5	839.6	838.8	838.0	837.1
145°	888.5	888.5	887.9	887.3	886.7	886.1	885.4	884.6	883.8	883.1	882.3
147.5°	928.4	928.0	927.5	927.0	926.6	926.1	925.6	925.2	924.8	924.3	923.9
150°	954.3	954.3	953.5	952.8	952.0	951.2	950.9	951.1	951.3	951.5	951.6
152.5°	977.6	977.1	976.8	976.5	976.2	975.9	975.5	975.3	975.0	974.7	974.5
155°	1011.2	1010.4	1010.2	1010.0	1009.9	1009.6	1009.5	1009.5	1009.5	1009.5	1009.5
157.5°	1040.6	1039.8	1039.6	1039.4	1039.2	1039.0	1039.1	1039.6	1040.0	1040.4	1040.9
160°	1058.4	1057.6	1057.4	1057.2	1057.0	1056.9	1057.0	1057.6	1058.2	1058.8	1059.4
162.5°	1075.0	1074.0	1074.0	1073.9	1073.9	1073.8	1074.1	1074.4	1074.9	1075.3	1075.8
165°	1097.6	1096.8	1096.5	1096.4	1096.2	1096.0	1096.1	1096.4	1096.9	1097.3	1097.7
167.5°	1113.8	1112.6	1112.6	1112.6	1112.6	1112.6	1113.0	1113.8	1114.6	1115.4	1116.2
170°	1123.8	1122.6	1122.6	1122.6	1122.6	1122.6	1123.0	1123.8	1124.5	1125.3	1126.1
172.5°	1130.9	1129.7	1129.7	1129.7	1129.7	1129.7	1130.2	1130.9	1131.7	1132.5	1133.3
175°	1138.9	1137.7	1137.7	1137.7	1137.7	1137.7	1138.1	1138.9	1139.7	1140.5	1141.3
177.5°	1142.8	1141.8	1142.0	1142.1	1142.3	1142.5	1142.8	1143.4	1144.2	1144.8	1145.4
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	488.1	490.4	491.9	494.6	497.0	498.3	499.4	500.4	501.6	502.6	505.4
5°	491.2	496.6	501.1	508.1	514.5	519.4	524.8	529.5	533.4	539.0	543.3
7.5°	489.8	499.4	509.3	520.2	531.3	541.5	551.1	559.9	567.9	577.7	586.2
10°	488.6	501.5	514.2	529.0	543.9	556.7	568.6	580.9	589.7	602.1	612.6
12.5°	487.6	502.8	518.3	535.8	552.3	570.4	586.3	595.2	608.7	618.6	631.1
15°	483.4	503.5	524.8	544.6	568.1	584.8	598.8	616.1	628.7	641.2	654.8
17.5°	475.9	498.8	522.5	548.5	571.0	588.9	607.0	623.7	638.6	655.5	672.4
20°	472.4	495.3	522.5	549.1	571.1	589.9	608.4	626.8	643.3	664.9	684.5
22.5°	465.2	492.8	517.9	543.9	566.5	586.9	608.0	628.7	650.7	675.1	699.6
25°	452.3	480.3	506.8	532.4	555.3	580.9	603.3	631.2	659.2	691.5	722.0
27.5°	438.8	465.7	490.0	514.7	541.4	570.3	599.4	631.0	667.7	708.6	751.5
30°	427.9	453.3	477.0	502.3	530.1	562.7	594.7	632.1	674.6	720.5	771.7
32.5°	415.3	438.6	461.6	488.5	518.8	553.1	590.4	631.5	682.5	734.7	787.3
35°	393.5	413.1	436.8	465.5	499.6	539.0	582.1	630.7	689.2	749.2	793.4
37.5°	367.8	386.0	411.0	442.4	478.2	520.5	571.6	629.3	691.4	739.2	753.5
40°	350.4	367.4	393.3	425.9	462.5	507.3	563.3	624.3	684.5	715.0	703.2
42.5°	332.0	349.7	375.1	407.2	446.7	495.4	552.9	613.9	664.4	675.9	635.3
45°	302.9	321.2	346.2	378.7	421.2	473.9	533.9	589.3	618.3	597.5	534.7
47.5°	275.8	293.0	316.1	349.7	393.5	448.1	505.8	550.0	552.3	502.7	435.5
50°	257.3	273.2	296.5	330.1	373.5	428.8	480.9	515.8	500.1	443.8	379.3
52.5°	239.2	254.8	277.7	310.9	353.9	404.6	453.1	477.5	448.0	390.2	335.2
55°	213.0	226.7	249.1	279.8	320.6	367.6	408.8	417.2	378.9	322.1	277.3
57.5°	187.5	200.2	220.6	248.9	286.2	327.8	360.1	358.2	317.7	268.9	233.4
60°	170.2	182.5	200.7	228.3	262.3	298.2	325.7	319.1	279.0	236.9	207.1
62.5°	154.7	165.8	182.9	207.1	238.1	271.3	293.9	284.2	244.9	208.1	184.5
65°	131.9	141.2	155.8	176.4	202.2	229.5	247.1	234.5	200.9	172.3	153.3
67.5°	110.0	117.5	129.7	146.2	168.2	190.2	200.8	188.2	161.3	140.4	126.4
70°	96.2	102.8	112.3	126.9	146.1	164.6	172.6	161.3	138.2	120.3	110.2
72.5°	82.4	87.8	96.1	109.3	124.7	140.7	147.8	137.0	118.0	102.8	93.5
75°	63.7	67.4	73.1	82.2	94.3	107.2	111.0	101.6	89.4	78.1	71.9
77.5°	45.6	48.7	53.1	58.8	67.4	75.5	78.9	73.5	64.1	56.9	51.8
80°	35.0	36.6	40.4	45.1	51.9	57.1	59.3	55.8	49.2	43.9	39.9
82.5°	25.0	26.7	28.8	32.7	37.1	40.6	43.0	40.7	35.9	31.7	29.4
85°	12.1	13.2	14.4	16.1	19.4	21.4	21.2	19.8	17.9	16.3	15.1
87.5°	4.8	5.3	6.1	7.2	8.0	8.9	9.5	9.5	9.1	8.8	8.6
90°	2.5	4.0	5.6	7.2	8.7	10.1	11.5	12.8	14.3	15.2	16.2
92.5°	22.6	23.7	24.9	25.9	27.4	29.1	30.8	32.5	34.2	35.5	36.8
95°	58.2	58.7	59.0	59.5	60.6	62.6	64.6	66.6	68.6	69.9	71.3
97.5°	96.3	96.5	96.7	96.8	98.3	100.9	103.7	106.4	109.1	110.5	111.7
100°	124.7	124.7	124.7	124.7	125.9	128.5	131.1	133.7	136.2	137.9	139.7
102.5°	156.0	156.9	157.7	158.5	159.4	160.8	162.1	163.4	164.7	166.7	168.5
105°	203.9	204.9	206.0	207.0	208.0	209.2	210.4	211.6	212.8	213.9	215.2
107.5°	256.6	257.6	258.7	259.7	260.6	261.4	262.4	263.3	264.2	264.8	265.4
110°	293.0	294.0	295.0	296.0	296.8	297.3	297.9	298.5	299.1	299.7	300.3



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	329.6	330.0	330.6	331.1	331.7	332.5	333.2	333.9	334.7	335.0	335.3
115°	384.5	385.3	386.1	386.8	387.4	387.8	388.3	388.6	389.1	388.9	388.6
117.5°	438.9	439.3	439.6	440.0	440.3	440.7	441.0	441.4	441.8	441.9	442.0
120°	473.7	474.7	475.7	476.7	477.2	477.4	477.7	477.9	478.0	478.0	478.0
122.5°	510.1	510.5	510.9	511.2	511.6	512.1	512.6	513.2	513.6	513.5	513.4
125°	561.2	562.3	563.6	564.7	565.4	565.6	565.8	566.0	566.2	565.8	565.4
127.5°	614.0	614.7	615.4	616.1	616.5	616.8	617.0	617.2	617.5	617.2	617.1
130°	646.4	647.4	648.4	649.3	650.1	650.5	650.9	651.2	651.7	651.5	651.2
132.5°	679.1	680.7	682.3	683.9	684.7	684.7	684.6	684.5	684.4	684.2	684.0
135°	729.4	730.6	731.7	733.0	733.7	733.9	734.1	734.2	734.4	734.4	734.4
137.5°	777.0	778.2	779.4	780.5	781.3	781.8	782.2	782.7	783.0	783.3	783.5
140°	807.5	808.5	809.5	810.5	811.3	811.9	812.5	813.1	813.7	814.0	814.5
142.5°	838.0	838.8	839.6	840.5	841.3	842.0	842.8	843.6	844.3	844.5	844.8
145°	883.1	883.8	884.6	885.4	886.1	886.7	887.3	887.9	888.5	888.5	888.5
147.5°	924.3	924.8	925.2	925.6	926.1	926.6	927.0	927.5	928.0	928.4	928.9
150°	951.5	951.3	951.1	950.9	951.2	952.0	952.8	953.5	954.3	954.3	954.3
152.5°	974.7	975.0	975.3	975.5	975.9	976.2	976.5	976.8	977.1	977.6	978.1
155°	1009.5	1009.5	1009.5	1009.5	1009.6	1009.9	1010.0	1010.2	1010.4	1011.2	1012.0
157.5°	1040.4	1040.0	1039.6	1039.1	1039.0	1039.2	1039.4	1039.6	1039.8	1040.6	1041.3
160°	1058.8	1058.2	1057.6	1057.0	1056.9	1057.0	1057.2	1057.4	1057.6	1058.4	1059.2
162.5°	1075.3	1074.9	1074.4	1074.1	1073.8	1073.9	1073.9	1074.0	1074.0	1075.0	1075.8
165°	1097.3	1096.9	1096.4	1096.1	1096.0	1096.2	1096.4	1096.5	1096.8	1097.6	1098.3
167.5°	1115.4	1114.6	1113.8	1113.0	1112.6	1112.6	1112.6	1112.6	1112.6	1113.8	1115.0
170°	1125.3	1124.5	1123.8	1123.0	1122.6	1122.6	1122.6	1122.6	1122.6	1123.8	1125.0
172.5°	1132.5	1131.7	1130.9	1130.2	1129.7	1129.7	1129.7	1129.7	1129.7	1130.9	1132.1
175°	1140.5	1139.7	1138.9	1138.1	1137.7	1137.7	1137.7	1137.7	1137.7	1138.9	1140.1
177.5°	1144.8	1144.2	1143.4	1142.8	1142.5	1142.3	1142.1	1142.0	1141.8	1142.8	1143.7
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	507.7	509.0	511.8	510.9	512.1	512.8	513.4
5°	548.7	555.3	558.2	557.8	562.1	561.1	560.0
7.5°	595.0	601.9	605.8	610.6	613.4	613.7	616.1
10°	621.3	630.3	634.0	639.2	642.5	644.4	644.1
12.5°	641.3	648.5	656.7	659.2	663.7	666.1	665.2
15°	665.6	676.9	685.5	689.8	695.4	697.1	699.3
17.5°	687.2	702.3	712.4	725.9	730.9	734.1	732.2
20°	703.5	723.4	733.5	749.6	758.5	763.2	761.5
22.5°	722.7	744.4	763.0	776.9	790.4	796.8	798.2
25°	755.8	785.4	812.9	831.2	847.8	851.8	860.4
27.5°	792.7	827.7	857.0	876.3	887.9	892.2	895.0
30°	815.9	850.8	872.8	885.2	888.9	888.5	888.1
32.5°	827.3	849.1	853.4	849.9	841.4	834.2	826.7
35°	811.2	795.0	770.6	739.3	716.2	692.9	690.6
37.5°	729.6	677.5	637.0	591.8	565.8	549.7	538.5
40°	652.7	593.6	544.6	506.5	479.9	469.4	459.1
42.5°	569.4	512.8	469.4	437.6	417.6	405.9	397.8
45°	462.5	412.7	378.7	355.6	339.7	330.7	325.6
47.5°	379.1	342.1	313.3	296.6	285.7	278.7	278.7
50°	334.2	299.0	279.8	266.6	257.2	251.6	252.6
52.5°	294.4	268.1	251.8	240.8	233.7	230.3	230.2
55°	246.2	227.3	216.6	208.5	203.8	199.8	200.7
57.5°	210.6	194.7	187.4	180.7	177.5	175.9	173.6
60°	188.5	176.2	170.0	164.6	161.3	160.1	157.8
62.5°	168.9	159.2	153.2	148.8	145.9	145.4	143.7
65°	142.0	134.6	129.2	127.2	124.0	123.2	123.2
67.5°	117.0	111.7	107.5	105.7	104.3	104.5	103.5
70°	101.4	97.0	94.3	92.3	91.3	91.5	90.7
72.5°	88.7	83.8	81.5	80.3	78.9	79.5	79.1
75°	67.1	64.7	63.5	62.2	61.4	61.0	60.5
77.5°	49.3	47.2	46.2	45.5	45.7	44.6	45.4
80°	38.1	36.3	35.7	34.6	34.4	34.4	34.2
82.5°	27.9	26.8	26.4	25.6	25.1	25.5	25.0
85°	14.4	13.6	13.4	13.4	13.0	12.6	13.6
87.5°	8.7	8.3	8.4	8.4	8.5	8.5	8.2
90°	17.2	18.2	19.0	19.6	20.2	20.8	21.4
92.5°	38.1	39.4	40.3	40.8	41.1	41.6	42.0
95°	72.7	74.1	75.0	75.3	75.8	76.2	76.6
97.5°	113.1	114.4	115.1	115.4	115.7	115.8	116.1
100°	141.5	143.3	144.5	144.8	145.2	145.6	146.0
102.5°	170.5	172.5	173.7	174.2	174.8	175.4	175.9
105°	216.3	217.5	218.4	219.0	219.6	220.2	220.8
107.5°	266.0	266.6	266.9	266.8	266.8	266.8	266.7
110°	300.9	301.5	301.7	301.5	301.3	301.1	300.9



TEST NUMBER: P333143-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	335.6	335.8	335.8	335.5	335.1	334.7	334.4
115°	388.4	388.3	388.1	387.8	387.6	387.4	387.3
117.5°	442.2	442.4	442.0	441.2	440.5	439.7	438.9
120°	478.0	478.0	477.7	476.9	476.1	475.3	474.5
122.5°	513.2	513.0	512.6	512.0	511.4	510.8	510.1
125°	565.0	564.6	564.3	564.1	563.9	563.7	563.6
127.5°	616.9	616.7	616.4	616.0	615.5	615.2	614.8
130°	651.0	650.9	650.6	650.1	649.8	649.3	649.0
132.5°	683.9	683.6	683.2	682.7	682.2	681.6	681.0
135°	734.4	734.4	734.1	733.3	732.5	731.6	730.8
137.5°	783.7	784.0	783.6	782.7	781.7	780.7	779.7
140°	814.8	815.3	814.9	814.0	813.0	812.0	811.0
142.5°	845.0	845.3	844.9	843.9	842.9	842.0	840.9
145°	888.5	888.5	888.1	887.6	887.0	886.4	885.8
147.5°	929.4	929.9	929.4	928.1	926.8	925.4	924.1
150°	954.3	954.3	954.1	953.8	953.3	953.0	952.5
152.5°	978.6	979.0	978.9	978.2	977.5	976.8	976.1
155°	1012.8	1013.6	1013.5	1012.5	1011.5	1010.5	1009.5
157.5°	1042.1	1042.9	1042.7	1041.4	1040.1	1038.8	1037.5
160°	1060.0	1060.8	1060.7	1059.7	1058.7	1057.7	1056.7
162.5°	1076.8	1077.8	1077.7	1076.6	1075.4	1074.2	1073.1
165°	1099.1	1099.9	1099.7	1098.6	1097.3	1096.2	1095.0
167.5°	1116.2	1117.4	1117.3	1116.2	1114.9	1113.7	1112.4
170°	1126.1	1127.3	1127.2	1125.9	1124.4	1123.1	1121.7
172.5°	1133.3	1134.4	1134.4	1133.2	1132.0	1130.8	1129.5
175°	1141.3	1142.5	1142.4	1141.0	1139.6	1138.2	1136.8
177.5°	1144.7	1145.6	1145.6	1144.4	1143.4	1142.2	1141.1
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0

(END OF REPORT)