

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333157-940

Luminaire Tested: **S125DIP-S375D1205U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333157-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D1205U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5651.5 lumens
Efficiency: N/A
Efficacy: 133.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333157-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333157-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27	20
2	84	77	71	66	74	68	63	59	53	49	46	38	36	34	25	24	23	17
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	21	19	14
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	39	56	47	40	36	37	32	28	27	24	21	18	16	14	11
6	59	47	39	34	52	42	35	31	33	28	25	24	21	19	16	14	13	9
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	20	38	29	23	18	23	18	15	17	14	12	11	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3364	3364	3364
5°	3371	3339	3361
10°	3351	3316	3335
15°	3315	3276	3290
20°	3263	3221	3226
25°	3207	3154	3151
30°	3138	3082	3067
35°	3064	3005	2964
40°	2989	2922	2880
45°	2906	2846	2789
50°	2816	2753	2671
55°	2728	2649	2575
60°	2623	2545	2454
65°	2500	2419	2337
70°	2381	2274	2194
75°	2168	2099	2024
80°	1930	1901	1852
85°	1675	1712	1615



TEST NUMBER: P333157-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.1	0.9
10°-20°	138.7	2.5
20°-30°	204.9	3.6
30°-40°	239.0	4.2
40°-50°	240.1	4.2
50°-60°	210.7	3.7
60°-70°	157.0	2.8
70°-80°	89.8	1.6
80°-90°	29.0	0.5
90°-100°	50.8	0.9
100°-110°	313.1	5.5
110°-120°	567.9	10.0
120°-130°	728.8	12.9
130°-140°	783.9	13.9
140°-150°	735.8	13.0
150°-160°	595.2	10.5
160°-170°	384.9	6.8
170°-180°	132.8	2.3
0°-30°	392.7	6.9
0°-40°	631.7	11.2
0°-60°	1082.6	19.2
0°-90°	1358.4	24.0
90°-120°	931.8	16.5
90°-150°	3180.2	56.3
90°-180°	4293.0	76.0
0°-180°	5651.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	521	521	521	521	521	
5°	520	519	515	519	518	49
15°	496	494	490	492	492	140
25°	450	448	443	443	442	207
35°	389	387	381	379	376	243
45°	318	316	312	307	305	245
55°	242	241	235	232	229	216
65°	164	163	158	155	153	162
75°	87	86	84	83	81	93
85°	23	23	23	23	22	25
90°	1	9	17	22	25	4
95°	59	54	17	22	22	75
105°	305	309	309	309	308	323
115°	572	577	578	574	568	567
125°	814	820	821	817	814	726
135°	1015	1020	1019	1016	1010	782
145°	1176	1178	1178	1179	1173	735
155°	1295	1290	1291	1294	1286	597
165°	1367	1361	1362	1367	1360	386
175°	1398	1392	1393	1400	1392	133
180°	1398	1398	1398	1398	1398	



TEST NUMBER: P333157-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	522.2	522.0	521.8	521.6	521.4	520.8	520.1	519.4	518.7	517.9	518.7
5°	520.0	519.9	519.7	519.5	519.3	518.8	517.9	517.0	516.0	515.1	515.9
7.5°	515.3	515.1	515.0	514.8	514.6	514.0	513.0	511.9	511.0	510.0	510.8
10°	511.0	510.9	510.7	510.5	510.3	509.7	508.7	507.7	506.7	505.7	506.4
12.5°	505.8	505.4	505.1	504.8	504.4	503.8	502.8	501.9	501.0	500.1	500.6
15°	495.8	495.5	495.3	495.0	494.6	494.0	493.0	492.0	491.0	490.0	490.4
17.5°	484.3	483.9	483.5	483.1	482.7	482.0	480.9	479.9	478.8	477.8	478.4
20°	474.7	474.6	474.4	474.2	474.0	473.3	472.2	470.9	469.8	468.6	469.2
22.5°	465.2	464.8	464.5	464.2	463.9	463.2	462.0	460.9	459.8	458.7	459.1
25°	450.0	449.6	449.1	448.6	448.2	447.4	446.2	445.0	443.8	442.6	442.8
27.5°	432.3	432.0	431.8	431.5	431.2	430.4	429.3	428.0	426.8	425.5	425.6
30°	420.8	420.5	420.2	419.9	419.6	418.8	417.5	416.1	414.7	413.3	413.1
32.5°	408.2	407.8	407.4	407.0	406.5	405.7	404.5	403.2	402.1	400.8	400.5
35°	388.6	388.3	387.9	387.5	387.2	386.3	385.0	383.8	382.5	381.2	380.8
37.5°	368.3	367.8	367.4	366.8	366.4	365.6	364.4	363.2	361.9	360.8	360.1
40°	354.5	353.9	353.5	353.0	352.6	351.7	350.4	349.2	347.9	346.6	345.8
42.5°	339.6	339.2	338.9	338.4	338.0	337.2	335.9	334.7	333.3	332.1	331.4
45°	318.2	317.8	317.4	317.1	316.6	315.9	314.9	313.8	312.6	311.6	310.5
47.5°	295.1	295.1	295.1	295.2	295.2	294.5	293.2	291.9	290.5	289.2	288.1
50°	280.3	280.0	279.7	279.4	279.1	278.5	277.3	276.3	275.2	274.0	272.9
52.5°	265.1	264.8	264.7	264.5	264.3	263.6	262.4	261.3	260.0	258.9	257.9
55°	242.3	242.0	241.7	241.5	241.2	240.4	239.2	237.9	236.6	235.3	234.5
57.5°	218.4	218.2	218.0	217.9	217.8	217.1	216.1	215.0	213.9	212.9	211.8
60°	203.1	202.8	202.4	202.1	201.7	201.0	200.0	199.0	198.0	197.0	196.1
62.5°	187.3	187.1	186.7	186.5	186.2	185.6	184.8	183.9	183.0	182.2	181.2
65°	163.6	163.5	163.3	163.1	162.9	162.3	161.3	160.2	159.3	158.3	157.4
67.5°	140.6	140.3	139.8	139.5	139.1	138.5	137.8	137.0	136.3	135.5	134.8
70°	126.1	125.6	125.2	124.8	124.3	123.6	122.8	122.0	121.2	120.4	119.8
72.5°	110.3	109.9	109.7	109.3	109.1	108.6	108.1	107.5	107.0	106.5	105.8
75°	86.9	86.8	86.6	86.4	86.2	85.9	85.4	85.0	84.5	84.1	83.8
77.5°	65.5	65.4	65.3	65.2	65.2	65.0	64.7	64.5	64.2	63.9	63.8
80°	51.9	51.9	51.9	51.9	51.9	51.8	51.6	51.5	51.3	51.1	51.0
82.5°	40.0	39.9	39.8	39.6	39.5	39.4	39.3	39.3	39.2	39.2	39.1
85°	22.6	22.7	22.8	22.9	23.0	23.1	23.1	23.1	23.1	23.1	23.0
87.5°	9.1	9.5	9.8	10.3	10.6	10.9	11.1	11.4	11.7	11.9	12.1
90°	1.1	2.9	4.7	6.6	8.4	10.2	11.8	13.4	15.0	16.6	17.7
92.5°	16.0	14.7	13.4	12.1	10.8	10.9	12.3	13.7	15.2	16.6	17.7
95°	59.0	58.4	57.7	57.0	56.3	51.6	42.8	34.1	25.3	16.6	17.7
97.5°	123.3	124.6	125.8	127.1	128.3	120.3	102.9	85.6	68.3	51.0	44.5
100°	173.1	173.8	174.4	175.1	175.8	176.6	177.5	178.5	179.4	180.3	146.0
102.5°	223.6	224.5	225.4	226.2	227.1	227.8	228.4	229.0	229.5	230.1	223.6
105°	304.7	305.6	306.5	307.5	308.4	308.8	308.8	308.8	308.8	308.8	308.8
107.5°	388.9	388.9	388.9	388.9	388.9	389.1	389.5	389.9	390.5	390.9	390.9
110°	443.5	443.5	443.5	443.5	443.5	443.8	444.3	444.7	445.1	445.6	445.0



TEST NUMBER: P333157-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	495.0	495.5	496.1	496.6	497.1	497.6	497.8	498.1	498.4	498.6	497.8
115°	572.0	573.2	574.4	575.5	576.7	577.4	577.6	577.8	578.0	578.3	577.4
117.5°	651.8	651.8	651.8	651.8	651.7	652.1	653.0	653.8	654.7	655.6	654.4
120°	701.6	701.3	701.2	700.9	700.7	700.9	701.6	702.3	702.9	703.6	703.2
122.5°	745.6	746.5	747.3	748.1	749.0	749.7	749.9	750.3	750.6	750.9	750.5
125°	813.5	815.1	816.7	818.3	819.9	820.7	820.7	820.7	820.7	820.7	819.8
127.5°	878.4	879.6	880.7	881.8	883.0	883.5	883.3	883.2	883.1	883.0	882.4
130°	918.2	919.4	920.5	921.7	922.8	923.5	923.7	924.0	924.2	924.4	923.7
132.5°	958.0	959.3	960.6	962.0	963.3	963.8	963.2	962.7	962.2	961.7	961.6
135°	1014.6	1015.9	1017.4	1018.7	1020.1	1020.6	1020.1	1019.7	1019.1	1018.7	1018.2
137.5°	1066.6	1067.8	1069.0	1070.1	1071.4	1071.7	1071.4	1070.9	1070.5	1070.1	1070.2
140°	1100.5	1101.1	1101.5	1102.0	1102.4	1102.5	1102.3	1102.1	1101.9	1101.6	1102.1
142.5°	1131.2	1131.5	1131.8	1132.1	1132.4	1132.7	1133.0	1133.3	1133.6	1134.0	1134.1
145°	1176.3	1176.7	1177.1	1177.6	1178.0	1178.3	1178.3	1178.3	1178.3	1178.3	1178.6
147.5°	1215.6	1215.5	1215.4	1215.3	1215.2	1215.3	1215.6	1215.8	1216.2	1216.5	1216.7
150°	1240.5	1240.0	1239.6	1239.1	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5	1240.9
152.5°	1264.5	1263.6	1262.5	1261.5	1260.4	1260.2	1260.7	1261.1	1261.6	1262.0	1262.5
155°	1295.4	1294.1	1292.6	1291.3	1289.9	1289.4	1289.9	1290.3	1290.8	1291.3	1292.0
157.5°	1319.3	1318.4	1317.6	1316.8	1315.9	1315.5	1315.6	1315.6	1315.7	1315.7	1316.4
160°	1335.9	1334.4	1333.1	1331.7	1330.3	1329.7	1330.0	1330.2	1330.4	1330.6	1331.6
162.5°	1349.1	1347.7	1346.3	1345.0	1343.5	1343.0	1343.2	1343.5	1343.7	1343.9	1345.2
165°	1366.9	1365.6	1364.1	1362.8	1361.4	1360.8	1361.0	1361.3	1361.5	1361.7	1363.2
167.5°	1380.2	1378.8	1377.3	1375.9	1374.5	1373.9	1374.1	1374.3	1374.6	1374.8	1376.4
170°	1387.7	1386.1	1384.4	1382.8	1381.2	1380.5	1380.7	1381.0	1381.2	1381.4	1383.3
172.5°	1392.6	1391.0	1389.4	1387.8	1386.2	1385.5	1386.0	1386.4	1386.8	1387.2	1388.9
175°	1398.0	1396.6	1395.3	1393.8	1392.5	1391.9	1392.1	1392.4	1392.6	1392.9	1394.6
177.5°	1400.5	1399.4	1398.3	1397.2	1396.1	1395.6	1395.8	1396.0	1396.2	1396.3	1397.7
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333157-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	519.4	520.1	520.8	521.2	521.1	521.0	521.0	520.9
5°	516.7	517.6	518.4	518.8	518.7	518.6	518.5	518.4
7.5°	511.6	512.4	513.2	513.5	513.4	513.4	513.3	513.2
10°	507.1	507.8	508.6	508.9	508.8	508.7	508.6	508.5
12.5°	501.2	501.9	502.4	502.7	502.7	502.7	502.7	502.6
15°	490.9	491.3	491.9	492.0	492.0	492.0	492.0	492.0
17.5°	478.9	479.5	480.1	480.1	479.7	479.2	478.8	478.3
20°	469.8	470.5	471.1	471.3	470.7	470.3	469.8	469.4
22.5°	459.5	459.9	460.4	460.4	460.1	459.8	459.5	459.1
25°	443.0	443.2	443.4	443.3	443.0	442.7	442.5	442.2
27.5°	425.6	425.6	425.7	425.6	425.3	425.0	424.7	424.5
30°	413.0	412.8	412.6	412.4	412.1	411.9	411.5	411.3
32.5°	400.2	399.8	399.5	399.1	398.6	398.1	397.6	397.1
35°	380.3	379.9	379.3	378.8	378.1	377.3	376.6	375.9
37.5°	359.4	358.7	358.0	357.5	357.0	356.7	356.2	355.8
40°	344.9	344.1	343.3	342.8	342.5	342.1	341.9	341.6
42.5°	330.6	329.8	329.0	328.5	328.1	327.6	327.3	326.8
45°	309.3	308.3	307.2	306.5	306.2	305.9	305.7	305.4
47.5°	287.0	285.9	284.7	283.8	283.2	282.6	282.0	281.3
50°	271.7	270.5	269.3	268.4	267.7	267.1	266.4	265.8
52.5°	256.8	255.7	254.7	253.9	253.2	252.4	251.7	251.0
55°	233.6	232.8	232.0	231.3	230.7	230.0	229.3	228.7
57.5°	210.7	209.6	208.6	207.9	207.5	207.1	206.8	206.4
60°	195.2	194.2	193.3	192.5	191.9	191.3	190.6	190.0
62.5°	180.2	179.1	178.2	177.5	177.0	176.5	175.9	175.5
65°	156.6	155.8	155.0	154.4	154.0	153.6	153.3	152.9
67.5°	134.1	133.4	132.7	132.2	132.1	131.8	131.6	131.3
70°	119.2	118.7	118.2	117.7	117.3	117.0	116.5	116.2
72.5°	105.2	104.6	104.0	103.5	103.2	102.8	102.4	102.0
75°	83.6	83.3	82.9	82.7	82.3	81.9	81.6	81.1
77.5°	63.7	63.5	63.3	63.1	62.9	62.6	62.3	62.1
80°	50.9	50.8	50.7	50.6	50.4	50.2	50.0	49.8
82.5°	38.9	38.7	38.6	38.4	38.4	38.4	38.3	38.3
85°	22.9	22.8	22.7	22.6	22.4	22.2	22.0	21.8
87.5°	12.3	12.6	12.8	12.9	12.9	12.9	12.9	12.9
90°	18.9	20.1	21.2	22.1	22.8	23.5	24.2	24.9
92.5°	18.9	20.1	21.2	21.9	22.2	22.6	22.9	23.2
95°	18.9	20.1	21.2	21.8	21.8	21.8	21.8	21.8
97.5°	38.0	31.5	25.0	21.8	21.8	21.8	21.8	21.8
100°	111.7	77.4	43.1	25.4	24.5	23.6	22.6	21.8
102.5°	217.0	210.6	204.1	193.1	177.4	161.7	146.1	130.4
105°	308.8	308.8	308.8	308.7	308.4	308.3	308.0	307.8
107.5°	391.0	391.0	391.1	390.7	390.0	389.4	388.7	388.0
110°	444.3	443.5	442.8	442.6	442.8	443.1	443.4	443.5



TEST NUMBER: P333157-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	497.0	496.1	495.2	494.5	494.3	493.9	493.7	493.3
115°	576.4	575.5	574.6	573.5	572.0	570.7	569.3	567.9
117.5°	653.2	652.0	650.8	649.9	649.3	648.7	648.1	647.5
120°	702.8	702.3	701.9	701.1	699.9	698.7	697.6	696.4
122.5°	750.0	749.6	749.1	748.1	746.8	745.5	744.2	742.9
125°	818.9	818.0	817.1	816.3	815.6	814.9	814.2	813.5
127.5°	881.9	881.5	880.9	879.9	878.2	876.4	874.7	873.0
130°	923.0	922.3	921.7	920.7	919.5	918.5	917.3	916.1
132.5°	961.4	961.3	961.2	960.6	959.4	958.2	957.1	955.9
135°	1017.8	1017.4	1016.9	1015.9	1014.6	1013.2	1011.8	1010.4
137.5°	1070.3	1070.4	1070.5	1070.0	1068.7	1067.6	1066.3	1065.1
140°	1102.5	1103.0	1103.5	1103.0	1101.6	1100.3	1098.9	1097.5
142.5°	1134.2	1134.3	1134.3	1133.7	1132.3	1131.0	1129.5	1128.2
145°	1178.8	1179.0	1179.2	1178.7	1177.2	1175.9	1174.5	1173.1
147.5°	1217.0	1217.3	1217.5	1216.8	1215.2	1213.5	1211.9	1210.2
150°	1241.4	1241.9	1242.3	1241.6	1239.8	1238.0	1236.1	1234.3
152.5°	1262.9	1263.5	1263.9	1263.3	1261.6	1260.0	1258.3	1256.7
155°	1292.6	1293.3	1294.1	1293.4	1291.6	1289.8	1287.9	1286.1
157.5°	1317.2	1317.9	1318.7	1318.1	1316.3	1314.5	1312.6	1310.7
160°	1332.5	1333.4	1334.4	1333.9	1332.0	1330.2	1328.4	1326.5
162.5°	1346.5	1347.8	1349.1	1348.7	1346.7	1344.6	1342.6	1340.6
165°	1364.5	1365.9	1367.3	1367.0	1365.2	1363.3	1361.5	1359.7
167.5°	1378.1	1379.7	1381.4	1381.3	1379.1	1377.1	1375.0	1373.0
170°	1385.1	1387.0	1388.8	1388.7	1386.6	1384.6	1382.5	1380.4
172.5°	1390.5	1392.2	1393.8	1393.7	1391.6	1389.6	1387.4	1385.4
175°	1396.5	1398.4	1400.2	1400.1	1398.0	1396.0	1393.8	1391.8
177.5°	1398.9	1400.3	1401.5	1401.4	1400.0	1398.5	1397.0	1395.5
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0

(END OF REPORT)