

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333303

Luminaire Tested: **S125DIP-S1270D365U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333303
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D365U835-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6443.7 lumens
Efficiency: N/A
Efficacy: 129.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333303

CATALOG NUMBER: S125DIP-S1270D365U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333303

CATALOG NUMBER: S125DIP-S1270D365U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	74	72	70	67
2	95	87	81	75	91	84	78	73	77	72	68	70	67	63	65	62	59	56
3	87	77	69	63	83	74	66	61	68	62	57	62	58	54	57	54	50	47
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43	41
5	73	61	52	46	70	58	50	45	54	47	42	50	44	40	46	42	38	35
6	67	55	46	40	64	53	45	39	49	42	37	45	40	35	42	37	33	31
7	62	50	41	35	60	48	40	34	44	38	33	41	35	31	38	33	30	27
8	58	45	37	31	55	44	36	31	41	34	29	38	32	28	35	30	27	25
9	54	41	33	28	52	40	33	28	37	31	26	35	29	25	33	28	24	22
10	51	38	31	25	49	37	30	25	35	28	24	32	27	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12727	12727	12727
5°	12756	12635	12716
10°	12679	12545	12618
15°	12541	12395	12447
20°	12344	12183	12205
25°	12133	11932	11921
30°	11872	11662	11604
35°	11591	11371	11211
40°	11304	11054	10897
45°	10993	10766	10552
50°	10652	10417	10104
55°	10323	10025	9743
60°	9928	9627	9285
65°	9459	9149	8839
70°	9009	8597	8303
75°	8210	7938	7663
80°	7305	7189	7018
85°	6358	6469	6121



TEST NUMBER: P333303

CATALOG NUMBER: S125DIP-S1270D365U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.8	2.9
10°-20°	524.9	8.1
20°-30°	775.0	12.0
30°-40°	904.3	14.0
40°-50°	908.3	14.1
50°-60°	797.3	12.4
60°-70°	594.1	9.2
70°-80°	339.7	5.3
80°-90°	99.8	1.5
90°-100°	127.1	2.0
100°-110°	273.1	4.2
110°-120°	256.3	4.0
120°-130°	207.7	3.2
130°-140°	166.7	2.6
140°-150°	125.8	2.0
150°-160°	88.6	1.4
160°-170°	52.2	0.8
170°-180°	17.0	0.3
0°-30°	1485.7	23.1
0°-40°	2390.0	37.1
0°-60°	4095.6	63.6
0°-90°	5129.1	79.6
90°-120°	656.5	10.2
90°-150°	1156.8	18.0
90°-180°	1315.0	20.4
0°-180°	6443.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1968	1964	1949	1962	1961	187
15°	1876	1870	1854	1861	1862	528
25°	1703	1694	1674	1677	1673	783
35°	1470	1463	1442	1434	1422	919
45°	1204	1197	1179	1161	1155	927
55°	917	911	890	876	865	818
65°	619	615	599	585	578	614
75°	329	326	318	313	307	351
85°	86	87	87	86	83	96
90°	0	3	6	7	8	5
95°	12	34	313	142	83	12
105°	40	56	256	504	468	42
115°	71	86	206	443	522	70
125°	99	116	197	353	411	88
135°	116	139	196	296	341	90
145°	135	155	196	245	269	85
155°	154	166	192	216	226	71
165°	168	173	184	195	198	47
175°	175	175	176	178	178	17
180°	175	175	175	175	175	



TEST NUMBER: P333303

CATALOG NUMBER: S125DIP-S1270D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1975.7	1974.9	1974.1	1973.2	1972.4	1970.6	1967.8	1965.0	1962.3	1959.5	1962.3
5°	1967.6	1966.9	1966.2	1965.5	1964.8	1962.8	1959.3	1955.8	1952.4	1948.9	1952.0
7.5°	1949.5	1948.8	1948.1	1947.4	1946.7	1944.5	1940.7	1936.9	1933.1	1929.3	1932.3
10°	1933.3	1932.6	1931.9	1931.2	1930.5	1928.3	1924.5	1920.7	1916.8	1913.0	1915.8
12.5°	1913.3	1912.1	1910.9	1909.6	1908.4	1906.0	1902.4	1898.9	1895.4	1891.8	1894.1
15°	1875.6	1874.6	1873.5	1872.5	1871.5	1869.0	1865.2	1861.4	1857.6	1853.8	1855.5
17.5°	1832.3	1830.8	1829.2	1827.7	1826.2	1823.4	1819.5	1815.5	1811.6	1807.6	1809.8
20°	1796.1	1795.4	1794.7	1794.0	1793.3	1790.7	1786.2	1781.7	1777.2	1772.7	1775.1
22.5°	1759.9	1758.7	1757.4	1756.2	1754.9	1752.2	1748.0	1743.8	1739.5	1735.3	1736.9
25°	1702.6	1700.8	1699.1	1697.4	1695.6	1692.5	1688.0	1683.5	1679.0	1674.5	1675.2
27.5°	1635.5	1634.5	1633.4	1632.4	1631.4	1628.5	1623.9	1619.2	1614.6	1609.9	1610.1
30°	1591.9	1590.8	1589.8	1588.7	1587.7	1584.6	1579.4	1574.2	1569.0	1563.8	1563.1
32.5°	1544.5	1542.9	1541.3	1539.7	1538.1	1535.0	1530.3	1525.7	1521.0	1516.4	1515.2
35°	1470.2	1468.9	1467.5	1466.1	1464.7	1461.6	1456.7	1451.9	1447.0	1442.2	1440.5
37.5°	1393.2	1391.5	1389.8	1388.0	1386.3	1383.1	1378.6	1374.0	1369.4	1364.9	1362.3
40°	1340.8	1339.1	1337.4	1335.6	1333.9	1330.6	1325.8	1320.9	1316.1	1311.2	1308.1
42.5°	1284.7	1283.3	1281.8	1280.3	1278.9	1275.7	1270.9	1266.0	1261.2	1256.3	1253.5
45°	1203.6	1202.3	1200.9	1199.5	1198.1	1195.3	1191.2	1187.0	1182.9	1178.7	1174.5
47.5°	1116.3	1116.4	1116.5	1116.5	1116.6	1114.1	1109.2	1104.2	1099.2	1094.2	1090.0
50°	1060.2	1059.2	1058.1	1057.1	1056.0	1053.4	1049.3	1045.1	1041.0	1036.8	1032.3
52.5°	1002.8	1002.1	1001.3	1000.5	999.8	997.2	992.7	988.3	983.9	979.4	975.5
55°	916.8	915.7	914.7	913.6	912.6	909.7	904.8	900.0	895.1	890.3	887.1
57.5°	826.0	825.5	824.9	824.4	823.8	821.5	817.4	813.3	809.2	805.1	801.1
60°	768.6	767.3	765.9	764.5	763.1	760.5	756.7	752.9	749.1	745.3	741.8
62.5°	708.8	707.7	706.6	705.4	704.3	702.2	698.9	695.6	692.4	689.1	685.4
65°	619.0	618.3	617.6	616.9	616.2	613.9	610.1	606.3	602.5	598.7	595.6
67.5°	532.0	530.5	529.1	527.6	526.2	524.0	521.2	518.3	515.5	512.6	510.0
70°	477.1	475.4	473.6	471.9	470.2	467.7	464.6	461.5	458.4	455.3	453.2
72.5°	417.2	416.0	414.9	413.7	412.5	410.9	408.9	406.9	404.9	402.9	400.5
75°	329.0	328.3	327.6	326.9	326.2	325.0	323.3	321.5	319.8	318.1	317.0
77.5°	247.6	247.3	247.0	246.8	246.5	245.9	244.9	243.9	242.9	242.0	241.4
80°	196.4	196.4	196.4	196.4	196.4	196.1	195.4	194.7	194.0	193.3	193.0
82.5°	151.5	151.0	150.4	149.9	149.3	149.0	148.8	148.7	148.6	148.4	147.8
85°	85.8	86.1	86.4	86.8	87.1	87.3	87.3	87.3	87.3	87.3	87.0
87.5°	33.7	33.8	34.0	34.1	34.2	34.2	34.0	33.9	33.7	33.6	33.6
90°	0.4	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.7	6.0
92.5°	4.3	5.2	8.2	12.6	18.7	29.0	48.3	80.6	115.8	113.9	92.2
95°	11.7	12.0	14.8	18.7	26.5	42.4	80.2	158.0	255.5	313.1	306.4
97.5°	19.4	19.8	21.8	25.7	32.7	44.1	69.1	126.1	228.2	334.4	387.7
100°	24.7	25.4	26.9	30.7	37.5	48.1	68.6	114.5	203.6	319.1	407.5
102.5°	30.7	31.1	32.2	36.4	42.6	52.9	71.1	109.7	184.9	292.3	395.6
105°	39.9	39.9	41.7	45.2	50.9	60.8	76.3	107.8	166.8	256.2	357.7
107.5°	49.0	49.7	51.4	54.3	60.2	69.1	84.1	111.0	159.2	231.4	318.9
110°	55.5	56.2	57.6	60.8	66.1	75.3	89.8	114.2	156.9	219.8	296.9



TEST NUMBER: P333303

CATALOG NUMBER: S125DIP-S1270D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.0	62.7	63.8	67.0	72.3	81.2	95.1	118.1	156.9	213.0	280.5
115°	71.4	72.1	73.2	76.3	81.6	90.5	103.6	124.0	158.0	205.7	262.6
117.5°	79.9	80.9	82.1	85.2	91.3	99.8	112.2	130.8	160.3	202.1	251.9
120°	85.5	86.6	88.0	91.2	97.2	106.0	118.4	135.4	162.6	200.4	246.0
122.5°	91.5	92.2	93.4	96.6	103.1	112.0	124.3	140.4	164.5	199.0	240.9
125°	99.0	99.7	101.4	104.6	111.3	120.5	132.2	147.4	167.9	197.2	234.0
127.5°	104.8	105.9	108.1	112.2	119.3	128.5	139.7	153.7	171.6	196.4	227.6
130°	108.5	109.6	112.4	117.0	124.4	133.6	144.5	158.0	173.9	195.8	223.4
132.5°	111.3	112.7	116.1	121.2	128.9	138.1	149.1	161.7	176.4	195.8	220.0
135°	115.9	117.3	121.6	127.2	134.7	144.2	155.1	166.8	179.9	195.8	215.9
137.5°	121.7	122.8	126.7	132.4	139.7	149.5	159.5	170.6	183.1	196.2	212.3
140°	125.1	126.2	130.4	136.1	142.8	152.3	162.6	173.2	184.5	196.5	210.6
142.5°	129.1	129.8	133.8	139.5	145.9	154.9	164.5	174.6	185.3	196.8	209.2
145°	135.0	135.7	139.2	144.2	150.6	158.7	167.9	176.7	186.2	196.5	207.1
147.5°	141.2	141.6	144.7	149.3	154.8	161.9	170.0	178.0	186.6	195.6	204.9
150°	144.9	145.6	148.1	152.7	157.6	163.6	171.4	178.8	186.6	194.7	203.2
152.5°	148.9	149.3	151.5	155.5	160.2	165.6	172.8	179.4	186.3	193.6	201.2
155°	154.1	154.1	156.2	159.7	163.3	168.2	174.2	179.9	185.5	191.6	197.9
157.5°	158.8	158.7	160.4	163.4	166.5	170.3	175.4	180.2	184.6	189.4	194.8
160°	161.9	161.5	162.9	165.4	168.2	171.4	176.0	180.2	183.8	188.0	192.3
162.5°	164.4	164.1	165.5	167.7	169.9	172.5	176.6	180.0	182.9	186.3	190.0
165°	168.2	167.5	168.6	170.3	171.8	173.9	176.7	179.5	181.7	183.8	186.6
167.5°	170.8	170.4	171.1	172.0	173.0	174.4	176.7	178.7	179.7	181.3	183.3
170°	172.5	172.1	172.5	173.2	173.9	174.9	176.7	178.1	178.8	179.9	181.3
172.5°	173.6	173.0	173.3	174.0	174.4	174.9	176.4	177.6	177.7	178.2	179.3
175°	174.9	174.2	174.6	174.9	174.9	174.9	176.0	176.7	176.4	176.4	176.7
177.5°	175.6	175.0	175.0	175.3	175.0	175.0	175.6	175.9	175.3	175.3	175.6
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333303

CATALOG NUMBER: S125DIP-S1270D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1965.0	1967.8	1970.6	1971.8	1971.6	1971.3	1971.0	1970.7
5°	1955.1	1958.3	1961.4	1962.8	1962.4	1962.1	1961.7	1961.4
7.5°	1935.3	1938.4	1941.4	1942.8	1942.5	1942.1	1941.8	1941.4
10°	1918.6	1921.4	1924.1	1925.3	1925.0	1924.6	1924.3	1924.0
12.5°	1896.3	1898.5	1900.7	1901.8	1901.7	1901.6	1901.6	1901.5
15°	1857.3	1859.0	1860.7	1861.6	1861.6	1861.6	1861.6	1861.6
17.5°	1811.9	1814.1	1816.2	1816.4	1814.7	1813.0	1811.2	1809.5
20°	1777.6	1780.0	1782.4	1782.8	1781.0	1779.3	1777.6	1775.8
22.5°	1738.5	1740.1	1741.7	1741.9	1740.7	1739.5	1738.3	1737.2
25°	1675.9	1676.6	1677.3	1677.1	1676.1	1675.0	1674.0	1672.9
27.5°	1610.2	1610.4	1610.5	1610.0	1609.0	1608.0	1606.9	1605.9
30°	1562.4	1561.7	1561.0	1560.2	1559.1	1558.1	1557.0	1556.0
32.5°	1513.9	1512.7	1511.4	1509.8	1508.0	1506.1	1504.2	1502.4
35°	1438.7	1437.0	1435.3	1433.0	1430.2	1427.5	1424.7	1421.9
37.5°	1359.7	1357.2	1354.6	1352.5	1350.9	1349.3	1347.7	1346.1
40°	1305.0	1301.9	1298.7	1296.7	1295.6	1294.6	1293.5	1292.5
42.5°	1250.7	1247.8	1245.0	1242.8	1241.2	1239.6	1238.0	1236.4
45°	1170.4	1166.2	1162.1	1159.5	1158.4	1157.4	1156.3	1155.3
47.5°	1085.7	1081.5	1077.3	1074.0	1071.5	1069.1	1066.7	1064.3
50°	1027.8	1023.3	1018.8	1015.3	1012.9	1010.5	1008.1	1005.6
52.5°	971.5	967.6	963.6	960.3	957.6	954.9	952.2	949.5
55°	884.0	880.9	877.8	875.0	872.6	870.2	867.7	865.3
57.5°	797.1	793.1	789.1	786.4	785.1	783.8	782.4	781.1
60°	738.3	734.9	731.4	728.5	726.0	723.6	721.2	718.8
62.5°	681.6	677.9	674.2	671.4	669.5	667.6	665.7	663.9
65°	592.5	589.3	586.2	584.0	582.6	581.2	579.8	578.4
67.5°	507.4	504.7	502.1	500.4	499.5	498.7	497.9	497.0
70°	451.1	449.0	446.9	445.2	443.8	442.4	441.1	439.7
72.5°	398.2	395.8	393.5	391.6	390.2	388.8	387.4	386.0
75°	316.0	314.9	313.9	312.7	311.3	309.9	308.5	307.1
77.5°	240.7	240.1	239.5	238.7	237.7	236.7	235.8	234.8
80°	192.6	192.3	191.9	191.4	190.7	190.0	189.3	188.7
82.5°	147.2	146.6	145.9	145.6	145.4	145.3	145.1	145.0
85°	86.6	86.3	85.9	85.4	84.7	84.0	83.3	82.6
87.5°	33.7	33.8	33.8	33.7	33.2	32.6	32.1	31.6
90°	6.4	6.7	7.1	7.8	7.8	7.8	8.1	8.1
92.5°	62.6	45.4	34.2	29.0	24.5	23.6	23.1	22.5
95°	254.1	200.4	156.9	127.2	102.1	91.5	88.7	83.1
97.5°	378.4	340.8	298.4	257.1	235.3	215.5	205.3	200.7
100°	434.7	417.4	381.0	344.2	319.8	294.4	281.3	275.7
102.5°	453.6	464.3	446.9	422.0	395.9	377.8	363.6	359.4
105°	442.5	490.9	506.4	502.6	491.2	479.6	472.5	468.3
107.5°	402.6	467.2	507.1	525.6	531.3	531.3	528.9	526.1
110°	373.2	440.4	490.2	520.2	536.1	542.8	545.3	545.3



TEST NUMBER: P333303

CATALOG NUMBER: S125DIP-S1270D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	350.0	413.8	464.2	499.6	522.8	534.4	540.5	543.1
115°	320.9	375.7	424.1	462.6	490.2	507.1	517.0	521.6
117.5°	302.1	349.3	391.0	426.4	453.9	471.5	481.3	484.1
120°	291.9	334.3	373.2	404.3	430.5	447.4	457.0	459.8
122.5°	284.3	323.6	358.2	387.3	410.7	426.2	435.8	438.3
125°	273.2	309.2	340.0	365.4	385.2	399.7	407.5	411.0
127.5°	261.9	295.5	324.2	348.0	366.0	378.8	386.1	387.7
130°	254.8	285.9	313.5	336.5	354.1	365.8	372.9	375.0
132.5°	247.7	276.9	301.9	324.0	341.7	353.3	359.8	362.2
135°	238.6	262.9	285.6	305.7	321.3	332.9	339.3	341.4
137.5°	230.8	250.5	269.3	286.4	300.3	310.9	316.8	319.1
140°	226.5	243.1	259.4	274.2	287.3	296.5	301.8	303.6
142.5°	222.9	236.9	250.9	263.8	274.9	282.7	287.7	289.2
145°	218.1	229.0	240.0	249.5	258.0	264.0	267.9	269.3
147.5°	213.5	222.4	230.9	238.1	244.8	249.6	251.8	252.5
150°	211.0	218.8	225.5	231.8	237.1	241.4	242.8	243.1
152.5°	208.2	215.1	221.2	226.2	230.6	234.0	235.4	235.8
155°	203.9	209.6	214.5	218.4	221.9	224.4	225.5	225.8
157.5°	199.7	204.3	208.2	211.2	214.0	216.0	217.0	216.9
160°	196.9	200.4	203.9	206.4	208.9	210.6	211.3	211.0
162.5°	193.7	197.0	200.0	202.2	204.1	205.5	205.7	205.6
165°	189.4	191.9	194.0	195.8	197.2	197.9	197.9	197.9
167.5°	185.3	187.0	188.6	189.9	190.6	191.2	190.9	190.8
170°	183.1	184.1	185.2	185.9	186.6	187.0	187.0	186.6
172.5°	180.5	181.6	182.4	182.8	182.9	183.6	183.0	182.6
175°	177.8	177.8	178.5	178.5	178.5	178.8	178.1	177.8
177.5°	175.9	176.1	176.1	176.1	175.9	176.1	175.3	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3

(END OF REPORT)