

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333310

Luminaire Tested: **S125DIP-S1270D590U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333310  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1270D590U835-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7493.3 lumens  
Efficiency: N/A  
Efficacy: 136.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333310

CATALOG NUMBER: S125DIP-S1270D590U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333310

CATALOG NUMBER: S125DIP-S1270D590U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68
1	102	97	93	90	96	92	88	85	82	79	77	73	71	69	64	63	62	57
2	93	85	79	73	87	80	75	70	72	67	64	64	61	58	57	54	52	48
3	85	75	67	61	80	71	64	58	63	58	53	57	52	49	50	47	44	41
4	77	66	58	52	73	63	55	50	56	50	46	50	46	42	45	41	38	35
5	71	59	51	44	67	56	48	43	51	44	39	45	40	36	40	36	33	30
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	32	29	27
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	34	29	26	24
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	24	32	26	23	28	24	21	19
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12727	12727	12727
5°	12756	12635	12716
10°	12679	12545	12618
15°	12541	12395	12447
20°	12344	12183	12205
25°	12133	11932	11921
30°	11872	11662	11604
35°	11591	11371	11211
40°	11304	11054	10897
45°	10993	10766	10552
50°	10652	10417	10104
55°	10323	10025	9743
60°	9928	9627	9285
65°	9459	9149	8839
70°	9009	8597	8303
75°	8210	7938	7663
80°	7305	7189	7018
85°	6358	6469	6121



TEST NUMBER: P333310

CATALOG NUMBER: S125DIP-S1270D590U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	185.8	2.5
10°-20°	524.9	7.0
20°-30°	775.0	10.3
30°-40°	904.3	12.1
40°-50°	908.3	12.1
50°-60°	797.3	10.6
60°-70°	594.1	7.9
70°-80°	339.7	4.5
80°-90°	100.4	1.3
90°-100°	28.0	0.4
100°-110°	172.4	2.3
110°-120°	312.6	4.2
120°-130°	401.2	5.4
130°-140°	431.5	5.8
140°-150°	405.1	5.4
150°-160°	327.7	4.4
160°-170°	211.9	2.8
170°-180°	73.1	1.0
0°-30°	1485.7	19.8
0°-40°	2390.0	31.9
0°-60°	4095.6	54.7
0°-90°	5129.8	68.5
90°-120°	513.0	6.8
90°-150°	1750.8	23.4
90°-180°	2364.0	31.5
0°-180°	7493.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1968	1964	1949	1962	1961	187
15°	1876	1870	1854	1861	1862	528
25°	1703	1694	1674	1677	1673	783
35°	1470	1463	1442	1434	1422	919
45°	1204	1197	1179	1161	1155	927
55°	917	911	890	876	865	818
65°	619	615	599	585	578	614
75°	329	326	318	313	307	351
85°	86	87	87	86	83	96
90°	1	5	9	12	14	6
95°	32	30	9	12	12	41
105°	168	170	170	170	169	178
115°	315	318	318	316	313	312
125°	448	452	452	450	448	400
135°	559	562	561	560	556	430
145°	648	649	649	649	646	405
155°	713	710	711	712	708	328
165°	752	749	750	753	748	212
175°	770	766	767	771	766	73
180°	770	770	770	770	770	



TEST NUMBER: P333310

CATALOG NUMBER: S125DIP-S1270D590U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1975.7	1974.9	1974.1	1973.2	1972.4	1970.6	1967.8	1965.0	1962.3	1959.5	1962.3
5°	1967.6	1966.9	1966.2	1965.5	1964.8	1962.8	1959.3	1955.8	1952.4	1948.9	1952.0
7.5°	1949.5	1948.8	1948.1	1947.4	1946.7	1944.5	1940.7	1936.9	1933.1	1929.3	1932.3
10°	1933.3	1932.6	1931.9	1931.2	1930.5	1928.3	1924.5	1920.7	1916.8	1913.0	1915.8
12.5°	1913.3	1912.1	1910.9	1909.6	1908.4	1906.0	1902.4	1898.9	1895.4	1891.8	1894.1
15°	1875.6	1874.6	1873.5	1872.5	1871.5	1869.0	1865.2	1861.4	1857.6	1853.8	1855.5
17.5°	1832.3	1830.8	1829.2	1827.7	1826.2	1823.4	1819.5	1815.5	1811.6	1807.6	1809.8
20°	1796.1	1795.4	1794.7	1794.0	1793.3	1790.7	1786.2	1781.7	1777.2	1772.7	1775.1
22.5°	1759.9	1758.7	1757.4	1756.2	1754.9	1752.2	1748.0	1743.8	1739.5	1735.3	1736.9
25°	1702.6	1700.8	1699.1	1697.4	1695.6	1692.5	1688.0	1683.5	1679.0	1674.5	1675.2
27.5°	1635.5	1634.5	1633.4	1632.4	1631.4	1628.5	1623.9	1619.2	1614.6	1609.9	1610.1
30°	1591.9	1590.8	1589.8	1588.7	1587.7	1584.6	1579.4	1574.2	1569.0	1563.8	1563.1
32.5°	1544.5	1542.9	1541.3	1539.7	1538.1	1535.0	1530.3	1525.7	1521.0	1516.4	1515.2
35°	1470.2	1468.9	1467.5	1466.1	1464.7	1461.6	1456.7	1451.9	1447.0	1442.2	1440.5
37.5°	1393.2	1391.5	1389.8	1388.0	1386.3	1383.1	1378.6	1374.0	1369.4	1364.9	1362.3
40°	1340.8	1339.1	1337.4	1335.6	1333.9	1330.6	1325.8	1320.9	1316.1	1311.2	1308.1
42.5°	1284.7	1283.3	1281.8	1280.3	1278.9	1275.7	1270.9	1266.0	1261.2	1256.3	1253.5
45°	1203.6	1202.3	1200.9	1199.5	1198.1	1195.3	1191.2	1187.0	1182.9	1178.7	1174.5
47.5°	1116.3	1116.4	1116.5	1116.5	1116.6	1114.1	1109.2	1104.2	1099.2	1094.2	1090.0
50°	1060.2	1059.2	1058.1	1057.1	1056.0	1053.4	1049.3	1045.1	1041.0	1036.8	1032.3
52.5°	1002.8	1002.1	1001.3	1000.5	999.8	997.2	992.7	988.3	983.9	979.4	975.5
55°	916.8	915.7	914.7	913.6	912.6	909.7	904.8	900.0	895.1	890.3	887.1
57.5°	826.0	825.5	824.9	824.4	823.8	821.5	817.4	813.3	809.2	805.1	801.1
60°	768.6	767.3	765.9	764.5	763.1	760.5	756.7	752.9	749.1	745.3	741.8
62.5°	708.8	707.7	706.6	705.4	704.3	702.2	698.9	695.6	692.4	689.1	685.4
65°	619.0	618.3	617.6	616.9	616.2	613.9	610.1	606.3	602.5	598.7	595.6
67.5°	532.0	530.5	529.1	527.6	526.2	524.0	521.2	518.3	515.5	512.6	510.0
70°	477.1	475.4	473.6	471.9	470.2	467.7	464.6	461.5	458.4	455.3	453.2
72.5°	417.2	416.0	414.9	413.7	412.5	410.9	408.9	406.9	404.9	402.9	400.5
75°	329.0	328.3	327.6	326.9	326.2	325.0	323.3	321.5	319.8	318.1	317.0
77.5°	247.6	247.3	247.0	246.8	246.5	245.9	244.9	243.9	242.9	242.0	241.4
80°	196.4	196.4	196.4	196.4	196.4	196.1	195.4	194.7	194.0	193.3	193.0
82.5°	151.5	151.0	150.4	149.9	149.3	149.0	148.8	148.7	148.6	148.4	147.8
85°	85.8	86.1	86.4	86.8	87.1	87.3	87.3	87.3	87.3	87.3	87.0
87.5°	33.8	34.0	34.2	34.4	34.6	34.7	34.6	34.5	34.4	34.3	34.4
90°	0.6	1.6	2.6	3.6	4.6	5.6	6.5	7.4	8.2	9.1	9.8
92.5°	8.8	8.1	7.4	6.7	5.9	6.0	6.8	7.6	8.3	9.1	9.8
95°	32.5	32.1	31.8	31.4	31.0	28.4	23.6	18.8	13.9	9.1	9.8
97.5°	67.9	68.6	69.3	69.9	70.6	66.2	56.7	47.1	37.6	28.1	24.5
100°	95.3	95.7	96.0	96.4	96.8	97.2	97.8	98.3	98.8	99.3	80.4
102.5°	123.1	123.6	124.1	124.6	125.0	125.4	125.7	126.1	126.4	126.7	123.1
105°	167.7	168.2	168.8	169.3	169.8	170.0	170.0	170.0	170.0	170.0	170.0
107.5°	214.1	214.1	214.1	214.1	214.1	214.2	214.4	214.7	215.0	215.2	215.2
110°	244.2	244.2	244.2	244.2	244.2	244.3	244.6	244.8	245.1	245.3	245.0



TEST NUMBER: P333310

CATALOG NUMBER: S125DIP-S1270D590U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	272.5	272.8	273.1	273.4	273.7	273.9	274.1	274.2	274.4	274.5	274.1
115°	314.9	315.6	316.2	316.8	317.5	317.9	318.0	318.1	318.2	318.4	317.9
117.5°	358.9	358.8	358.8	358.8	358.8	359.0	359.5	360.0	360.4	360.9	360.3
120°	386.3	386.1	386.0	385.9	385.7	385.9	386.3	386.6	387.0	387.4	387.1
122.5°	410.4	410.9	411.4	411.9	412.4	412.7	412.9	413.1	413.2	413.4	413.2
125°	447.9	448.8	449.6	450.5	451.4	451.9	451.9	451.9	451.9	451.9	451.4
127.5°	483.6	484.2	484.9	485.5	486.1	486.4	486.3	486.3	486.2	486.1	485.8
130°	505.5	506.1	506.8	507.4	508.0	508.4	508.5	508.7	508.8	508.9	508.5
132.5°	527.4	528.1	528.9	529.6	530.3	530.6	530.3	530.0	529.7	529.5	529.4
135°	558.6	559.3	560.1	560.8	561.6	561.9	561.6	561.3	561.1	560.8	560.6
137.5°	587.2	587.9	588.5	589.2	589.8	590.1	589.8	589.6	589.4	589.1	589.2
140°	605.9	606.2	606.4	606.7	606.9	607.0	606.9	606.7	606.6	606.5	606.7
142.5°	622.8	623.0	623.1	623.3	623.4	623.6	623.8	623.9	624.1	624.3	624.3
145°	647.6	647.8	648.1	648.3	648.6	648.7	648.7	648.7	648.7	648.7	648.8
147.5°	669.2	669.2	669.1	669.1	669.0	669.1	669.2	669.4	669.5	669.7	669.9
150°	682.9	682.7	682.4	682.2	681.9	681.9	682.2	682.4	682.7	682.9	683.2
152.5°	696.2	695.6	695.1	694.5	693.9	693.8	694.0	694.3	694.5	694.8	695.1
155°	713.2	712.4	711.7	710.9	710.1	709.9	710.1	710.4	710.6	710.9	711.3
157.5°	726.3	725.8	725.4	724.9	724.5	724.3	724.3	724.3	724.3	724.4	724.8
160°	735.4	734.7	733.9	733.1	732.4	732.1	732.2	732.3	732.4	732.6	733.1
162.5°	742.7	742.0	741.2	740.4	739.7	739.4	739.5	739.6	739.7	739.9	740.6
165°	752.5	751.8	751.0	750.3	749.5	749.2	749.3	749.4	749.6	749.7	750.4
167.5°	759.8	759.1	758.3	757.5	756.7	756.4	756.5	756.6	756.7	756.9	757.8
170°	764.0	763.1	762.2	761.3	760.4	760.0	760.1	760.3	760.4	760.5	761.5
172.5°	766.7	765.8	764.9	764.0	763.1	762.8	763.0	763.3	763.5	763.7	764.6
175°	769.7	768.9	768.1	767.4	766.6	766.3	766.4	766.6	766.7	766.8	767.8
177.5°	771.0	770.4	769.8	769.2	768.6	768.3	768.4	768.5	768.6	768.7	769.5
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333310

CATALOG NUMBER: S125DIP-S1270D590U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1965.0	1967.8	1970.6	1971.8	1971.6	1971.3	1971.0	1970.7
5°	1955.1	1958.3	1961.4	1962.8	1962.4	1962.1	1961.7	1961.4
7.5°	1935.3	1938.4	1941.4	1942.8	1942.5	1942.1	1941.8	1941.4
10°	1918.6	1921.4	1924.1	1925.3	1925.0	1924.6	1924.3	1924.0
12.5°	1896.3	1898.5	1900.7	1901.8	1901.7	1901.6	1901.6	1901.5
15°	1857.3	1859.0	1860.7	1861.6	1861.6	1861.6	1861.6	1861.6
17.5°	1811.9	1814.1	1816.2	1816.4	1814.7	1813.0	1811.2	1809.5
20°	1777.6	1780.0	1782.4	1782.8	1781.0	1779.3	1777.6	1775.8
22.5°	1738.5	1740.1	1741.7	1741.9	1740.7	1739.5	1738.3	1737.2
25°	1675.9	1676.6	1677.3	1677.1	1676.1	1675.0	1674.0	1672.9
27.5°	1610.2	1610.4	1610.5	1610.0	1609.0	1608.0	1606.9	1605.9
30°	1562.4	1561.7	1561.0	1560.2	1559.1	1558.1	1557.0	1556.0
32.5°	1513.9	1512.7	1511.4	1509.8	1508.0	1506.1	1504.2	1502.4
35°	1438.7	1437.0	1435.3	1433.0	1430.2	1427.5	1424.7	1421.9
37.5°	1359.7	1357.2	1354.6	1352.5	1350.9	1349.3	1347.7	1346.1
40°	1305.0	1301.9	1298.7	1296.7	1295.6	1294.6	1293.5	1292.5
42.5°	1250.7	1247.8	1245.0	1242.8	1241.2	1239.6	1238.0	1236.4
45°	1170.4	1166.2	1162.1	1159.5	1158.4	1157.4	1156.3	1155.3
47.5°	1085.7	1081.5	1077.3	1074.0	1071.5	1069.1	1066.7	1064.3
50°	1027.8	1023.3	1018.8	1015.3	1012.9	1010.5	1008.1	1005.6
52.5°	971.5	967.6	963.6	960.3	957.6	954.9	952.2	949.5
55°	884.0	880.9	877.8	875.0	872.6	870.2	867.7	865.3
57.5°	797.1	793.1	789.1	786.4	785.1	783.8	782.4	781.1
60°	738.3	734.9	731.4	728.5	726.0	723.6	721.2	718.8
62.5°	681.6	677.9	674.2	671.4	669.5	667.6	665.7	663.9
65°	592.5	589.3	586.2	584.0	582.6	581.2	579.8	578.4
67.5°	507.4	504.7	502.1	500.4	499.5	498.7	497.9	497.0
70°	451.1	449.0	446.9	445.2	443.8	442.4	441.1	439.7
72.5°	398.2	395.8	393.5	391.6	390.2	388.8	387.4	386.0
75°	316.0	314.9	313.9	312.7	311.3	309.9	308.5	307.1
77.5°	240.7	240.1	239.5	238.7	237.7	236.7	235.8	234.8
80°	192.6	192.3	191.9	191.4	190.7	190.0	189.3	188.7
82.5°	147.2	146.6	145.9	145.6	145.4	145.3	145.1	145.0
85°	86.6	86.3	85.9	85.4	84.7	84.0	83.3	82.6
87.5°	34.5	34.6	34.8	34.6	34.1	33.6	33.2	32.7
90°	10.4	11.0	11.7	12.2	12.6	12.9	13.3	13.7
92.5°	10.4	11.0	11.7	12.1	12.2	12.4	12.6	12.8
95°	10.4	11.0	11.7	12.0	12.0	12.0	12.0	12.0
97.5°	20.9	17.3	13.8	12.0	12.0	12.0	12.0	12.0
100°	61.5	42.6	23.7	14.0	13.5	13.0	12.5	12.0
102.5°	119.5	115.9	112.4	106.3	97.6	89.0	80.4	71.8
105°	170.0	170.0	170.0	170.0	169.8	169.7	169.6	169.4
107.5°	215.3	215.3	215.3	215.1	214.8	214.4	214.0	213.6
110°	244.6	244.2	243.8	243.7	243.8	243.9	244.1	244.2





TEST NUMBER: P333310

CATALOG NUMBER: S125DIP-S1270D590U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	273.6	273.1	272.6	272.3	272.1	271.9	271.8	271.6
115°	317.3	316.8	316.3	315.7	314.9	314.2	313.4	312.7
117.5°	359.6	358.9	358.3	357.8	357.5	357.1	356.8	356.5
120°	386.9	386.6	386.4	385.9	385.3	384.7	384.0	383.4
122.5°	412.9	412.7	412.4	411.9	411.2	410.4	409.7	409.0
125°	450.9	450.3	449.8	449.4	449.0	448.6	448.3	447.9
127.5°	485.5	485.3	485.0	484.4	483.4	482.5	481.6	480.6
130°	508.2	507.8	507.4	506.9	506.3	505.6	505.0	504.4
132.5°	529.3	529.2	529.2	528.8	528.2	527.5	526.9	526.3
135°	560.3	560.1	559.8	559.3	558.6	557.8	557.0	556.3
137.5°	589.2	589.3	589.3	589.0	588.4	587.7	587.1	586.4
140°	607.0	607.2	607.5	607.2	606.5	605.7	605.0	604.2
142.5°	624.4	624.4	624.5	624.1	623.4	622.6	621.8	621.1
145°	649.0	649.1	649.2	648.9	648.1	647.4	646.6	645.8
147.5°	670.0	670.2	670.3	669.9	669.0	668.1	667.2	666.3
150°	683.4	683.7	683.9	683.6	682.6	681.5	680.5	679.5
152.5°	695.3	695.6	695.8	695.5	694.6	693.7	692.7	691.8
155°	711.7	712.0	712.4	712.1	711.1	710.1	709.1	708.0
157.5°	725.2	725.6	726.0	725.7	724.7	723.6	722.6	721.6
160°	733.6	734.1	734.6	734.3	733.3	732.3	731.3	730.3
162.5°	741.3	742.0	742.7	742.5	741.4	740.3	739.2	738.0
165°	751.2	752.0	752.7	752.6	751.6	750.6	749.6	748.5
167.5°	758.7	759.6	760.5	760.4	759.3	758.1	757.0	755.8
170°	762.6	763.6	764.6	764.5	763.4	762.2	761.1	760.0
172.5°	765.5	766.5	767.4	767.3	766.1	765.0	763.8	762.7
175°	768.8	769.8	770.9	770.8	769.7	768.5	767.4	766.2
177.5°	770.2	770.9	771.6	771.5	770.7	769.9	769.1	768.3
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7

(END OF REPORT)