

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333116-940

Luminaire Tested: **S125DIP-S375D365U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333116-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D365U940-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2500.8 lumens  
Efficiency: N/A  
Efficacy: 123.2 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	39	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	31	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	22	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3135	3135	3135	3135
5°	3630	3146	2755	3146
10°	4224	3129	2413	3129
15°	4676	3107	2226	3107
20°	5234	3070	2076	3070
25°	6131	3029	2003	3029
30°	6623	2988	1939	2988
35°	5445	2912	1898	2912
40°	3871	2807	1851	2807
45°	2974	2665	1825	2665
50°	2538	2488	1822	2488
55°	2260	2315	1838	2315
60°	2038	2126	1885	2126
65°	1883	1936	1933	1936
70°	1713	1739	1962	1739
75°	1510	1532	1941	1532
80°	1272	1250	1778	1250
85°	1008	897	1438	897



TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.7	1.9
10°-20°	139.1	5.6
20°-30°	225.9	9.0
30°-40°	275.6	11.0
40°-50°	250.7	10.0
50°-60°	199.7	8.0
60°-70°	139.1	5.6
70°-80°	74.2	3.0
80°-90°	19.6	0.8
90°-100°	27.1	1.1
100°-110°	80.1	3.2
110°-120°	135.7	5.4
120°-130°	178.6	7.1
130°-140°	200.1	8.0
140°-150°	196.1	7.8
150°-160°	164.7	6.6
160°-170°	109.5	4.4
170°-180°	38.3	1.5
0°-30°	411.8	16.5
0°-40°	687.4	27.5
0°-60°	1137.8	45.5
0°-90°	1370.7	54.8
90°-120°	242.9	9.7
90°-150°	817.6	32.7
90°-180°	1130.0	45.2
0°-180°	2500.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	560	485	425	485	560	56
15°	699	465	333	465	699	200
25°	860	425	281	425	860	393
35°	691	369	241	369	691	423
45°	326	292	200	292	326	261
55°	201	206	163	206	201	181
65°	123	127	126	127	123	122
75°	60	61	78	61	60	65
85°	14	12	19	12	14	16
90°	8	0	8	0	8	5
95°	27	20	27	20	27	28
105°	78	72	78	72	78	83
115°	137	136	137	136	137	136
125°	200	198	200	198	200	178
135°	259	258	259	258	259	200
145°	314	312	314	312	314	196
155°	357	357	357	357	357	164
165°	388	389	388	389	388	109
175°	402	404	402	404	402	38
180°	405	405	405	405	405	



TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	513.4	512.8	512.1	510.9	511.8	509.0	507.7	505.4	502.6	501.6	500.4
5°	560.0	561.1	562.1	557.8	558.2	555.3	548.7	543.3	539.0	533.4	529.5
7.5°	616.1	613.7	613.4	610.6	605.8	601.9	595.0	586.2	577.7	567.9	559.9
10°	644.1	644.4	642.5	639.2	634.0	630.3	621.3	612.6	602.1	589.7	580.9
12.5°	665.2	666.1	663.7	659.2	656.7	648.5	641.3	631.1	618.6	608.7	595.2
15°	699.3	697.1	695.4	689.8	685.5	676.9	665.6	654.8	641.2	628.7	616.1
17.5°	732.2	734.1	730.9	725.9	712.4	702.3	687.2	672.4	655.5	638.6	623.7
20°	761.5	763.2	758.5	749.6	733.5	723.4	703.5	684.5	664.9	643.3	626.8
22.5°	798.2	796.8	790.4	776.9	763.0	744.4	722.7	699.6	675.1	650.7	628.7
25°	860.4	851.8	847.8	831.2	812.9	785.4	755.8	722.0	691.5	659.2	631.2
27.5°	895.0	892.2	887.9	876.3	857.0	827.7	792.7	751.5	708.6	667.7	631.0
30°	888.1	888.5	888.9	885.2	872.8	850.8	815.9	771.7	720.5	674.6	632.1
32.5°	826.7	834.2	841.4	849.9	853.4	849.1	827.3	787.3	734.7	682.5	631.5
35°	690.6	692.9	716.2	739.3	770.6	795.0	811.2	793.4	749.2	689.2	630.7
37.5°	538.5	549.7	565.8	591.8	637.0	677.5	729.6	753.5	739.2	691.4	629.3
40°	459.1	469.4	479.9	506.5	544.6	593.6	652.7	703.2	715.0	684.5	624.3
42.5°	397.8	405.9	417.6	437.6	469.4	512.8	569.4	635.3	675.9	664.4	613.9
45°	325.6	330.7	339.7	355.6	378.7	412.7	462.5	534.7	597.5	618.3	589.3
47.5°	278.7	278.7	285.7	296.6	313.3	342.1	379.1	435.5	502.7	552.3	550.0
50°	252.6	251.6	257.2	266.6	279.8	299.0	334.2	379.3	443.8	500.1	515.8
52.5°	230.2	230.3	233.7	240.8	251.8	268.1	294.4	335.2	390.2	448.0	477.5
55°	200.7	199.8	203.8	208.5	216.6	227.3	246.2	277.3	322.1	378.9	417.2
57.5°	173.6	175.9	177.5	180.7	187.4	194.7	210.6	233.4	268.9	317.7	358.2
60°	157.8	160.1	161.3	164.6	170.0	176.2	188.5	207.1	236.9	279.0	319.1
62.5°	143.7	145.4	145.9	148.8	153.2	159.2	168.9	184.5	208.1	244.9	284.2
65°	123.2	123.2	124.0	127.2	129.2	134.6	142.0	153.3	172.3	200.9	234.5
67.5°	103.5	104.5	104.3	105.7	107.5	111.7	117.0	126.4	140.4	161.3	188.2
70°	90.7	91.5	91.3	92.3	94.3	97.0	101.4	110.2	120.3	138.2	161.3
72.5°	79.1	79.5	78.9	80.3	81.5	83.8	88.7	93.5	102.8	118.0	137.0
75°	60.5	61.0	61.4	62.2	63.5	64.7	67.1	71.9	78.1	89.4	101.6
77.5°	45.4	44.6	45.7	45.5	46.2	47.2	49.3	51.8	56.9	64.1	73.5
80°	34.2	34.4	34.4	34.6	35.7	36.3	38.1	39.9	43.9	49.2	55.8
82.5°	25.0	25.5	25.1	25.6	26.4	26.8	27.9	29.4	31.7	35.9	40.7
85°	13.6	12.6	13.0	13.4	13.4	13.6	14.4	15.1	16.3	17.9	19.8
87.5°	5.4	5.8	5.9	5.8	6.0	5.9	6.5	6.4	6.9	7.3	7.8
90°	7.6	7.3	7.1	7.0	6.7	6.4	6.1	5.7	5.4	5.1	4.5
92.5°	14.9	14.7	14.5	14.4	14.3	13.9	13.5	13.0	12.6	12.1	11.5
95°	27.1	26.9	26.8	26.7	26.6	26.2	25.8	25.2	24.8	24.3	23.5
97.5°	41.1	41.0	40.9	40.8	40.8	40.5	40.0	39.6	39.1	38.6	37.6
100°	51.7	51.5	51.5	51.3	51.1	50.7	50.1	49.5	48.9	48.2	47.3
102.5°	62.2	62.1	61.9	61.7	61.5	61.1	60.4	59.7	59.0	58.3	57.9
105°	78.2	77.9	77.8	77.5	77.3	77.0	76.6	76.2	75.7	75.3	74.9
107.5°	94.4	94.4	94.4	94.4	94.5	94.3	94.2	94.0	93.7	93.5	93.2
110°	106.6	106.6	106.6	106.7	106.8	106.7	106.6	106.3	106.1	105.9	105.7



TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	118.4	118.5	118.6	118.8	118.9	118.9	118.8	118.7	118.6	118.5	118.2
115°	137.1	137.1	137.2	137.3	137.4	137.4	137.5	137.6	137.7	137.8	137.6
117.5°	155.3	155.7	156.0	156.2	156.5	156.6	156.6	156.5	156.4	156.4	156.2
120°	168.0	168.3	168.5	168.8	169.1	169.2	169.2	169.2	169.2	169.2	169.2
122.5°	180.6	180.8	181.0	181.3	181.5	181.6	181.6	181.7	181.8	181.8	181.6
125°	199.5	199.6	199.7	199.7	199.7	199.9	200.0	200.2	200.3	200.5	200.4
127.5°	217.7	217.8	217.9	218.1	218.2	218.3	218.4	218.5	218.6	218.6	218.6
130°	229.8	229.9	230.1	230.2	230.3	230.4	230.5	230.6	230.6	230.7	230.6
132.5°	241.1	241.3	241.5	241.7	241.9	242.0	242.1	242.2	242.2	242.3	242.4
135°	258.8	259.0	259.3	259.6	259.8	260.0	260.0	260.0	260.0	260.0	259.9
137.5°	276.0	276.3	276.7	277.1	277.4	277.6	277.5	277.4	277.3	277.2	277.1
140°	287.1	287.5	287.8	288.2	288.6	288.6	288.5	288.4	288.2	288.0	287.8
142.5°	297.7	298.1	298.4	298.7	299.1	299.3	299.2	299.1	299.0	298.9	298.6
145°	313.6	313.8	314.0	314.2	314.4	314.5	314.5	314.5	314.5	314.5	314.3
147.5°	327.2	327.6	328.1	328.6	329.0	329.2	329.0	328.9	328.7	328.5	328.3
150°	337.2	337.3	337.5	337.7	337.8	337.9	337.9	337.9	337.9	337.9	337.6
152.5°	345.5	345.8	346.1	346.3	346.5	346.6	346.4	346.3	346.1	345.9	345.8
155°	357.4	357.8	358.1	358.5	358.8	358.8	358.6	358.3	358.0	357.8	357.7
157.5°	367.3	367.7	368.2	368.7	369.2	369.3	369.0	368.6	368.4	368.1	368.0
160°	374.1	374.4	374.8	375.1	375.5	375.5	375.2	375.0	374.7	374.4	374.3
162.5°	379.9	380.3	380.7	381.1	381.6	381.6	381.2	380.8	380.6	380.2	380.2
165°	387.6	388.1	388.5	388.9	389.3	389.4	389.1	388.9	388.6	388.3	388.3
167.5°	393.9	394.2	394.7	395.1	395.6	395.6	395.1	394.8	394.3	393.9	393.9
170°	397.1	397.6	398.1	398.6	399.0	399.1	398.7	398.2	397.9	397.4	397.4
172.5°	399.8	400.3	400.7	401.2	401.6	401.6	401.2	400.8	400.4	399.9	399.9
175°	402.4	403.0	403.4	403.9	404.4	404.5	404.0	403.6	403.2	402.8	402.8
177.5°	403.9	404.4	404.7	405.2	405.6	405.6	405.3	404.9	404.6	404.2	404.3
180°	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0



TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	499.4	498.3	497.0	494.6	491.9	490.4	488.1	486.6	483.7	481.2	478.5
5°	524.8	519.4	514.5	508.1	501.1	496.6	491.2	485.3	479.0	472.7	465.7
7.5°	551.1	541.5	531.3	520.2	509.3	499.4	489.8	480.5	471.8	461.2	452.3
10°	568.6	556.7	543.9	529.0	514.2	501.5	488.6	477.2	465.7	453.3	442.4
12.5°	586.3	570.4	552.3	535.8	518.3	502.8	487.6	473.1	458.6	444.9	432.1
15°	598.8	584.8	568.1	544.6	524.8	503.5	483.4	464.7	447.1	431.9	415.8
17.5°	607.0	588.9	571.0	548.5	522.5	498.8	475.9	454.4	434.7	415.4	399.9
20°	608.4	589.9	571.1	549.1	522.5	495.3	472.4	446.7	425.5	405.5	386.6
22.5°	608.0	586.9	566.5	543.9	517.9	492.8	465.2	439.0	415.9	396.3	376.5
25°	603.3	580.9	555.3	532.4	506.8	480.3	452.3	425.1	401.6	379.2	359.5
27.5°	599.4	570.3	541.4	514.7	490.0	465.7	438.8	411.0	385.0	362.2	343.8
30°	594.7	562.7	530.1	502.3	477.0	453.3	427.9	400.7	373.5	351.3	331.5
32.5°	590.4	553.1	518.8	488.5	461.6	438.6	415.3	389.4	362.7	340.1	320.3
35°	582.1	539.0	499.6	465.5	436.8	413.1	393.5	369.4	344.9	323.1	304.2
37.5°	571.6	520.5	478.2	442.4	411.0	386.0	367.8	349.3	325.7	304.7	287.6
40°	563.3	507.3	462.5	425.9	393.3	367.4	350.4	333.0	313.4	293.8	275.7
42.5°	552.9	495.4	446.7	407.2	375.1	349.7	332.0	317.2	299.9	281.6	264.8
45°	533.9	473.9	421.2	378.7	346.2	321.2	302.9	291.8	278.7	261.4	247.3
47.5°	505.8	448.1	393.5	349.7	316.1	293.0	275.8	265.1	256.0	243.2	230.2
50°	480.9	428.8	373.5	330.1	296.5	273.2	257.3	247.6	239.9	230.0	219.0
52.5°	453.1	404.6	353.9	310.9	277.7	254.8	239.2	230.7	224.2	217.1	206.3
55°	408.8	367.6	320.6	279.8	249.1	226.7	213.0	205.6	200.3	194.9	188.3
57.5°	360.1	327.8	286.2	248.9	220.6	200.2	187.5	180.3	176.1	173.3	169.5
60°	325.7	298.2	262.3	228.3	200.7	182.5	170.2	164.6	161.1	158.9	156.0
62.5°	293.9	271.3	238.1	207.1	182.9	165.8	154.7	149.3	146.0	144.8	142.5
65°	247.1	229.5	202.2	176.4	155.8	141.2	131.9	126.7	124.7	123.4	123.6
67.5°	200.8	190.2	168.2	146.2	129.7	117.5	110.0	106.1	105.0	103.4	103.4
70°	172.6	164.6	146.1	126.9	112.3	102.8	96.2	92.1	91.0	90.2	90.1
72.5°	147.8	140.7	124.7	109.3	96.1	87.8	82.4	79.9	78.2	77.8	77.7
75°	111.0	107.2	94.3	82.2	73.1	67.4	63.7	61.4	60.2	59.9	60.2
77.5°	78.9	75.5	67.4	58.8	53.1	48.7	45.6	44.8	43.4	43.4	43.2
80°	59.3	57.1	51.9	45.1	40.4	36.6	35.0	33.6	33.2	32.5	33.2
82.5°	43.0	40.6	37.1	32.7	28.8	26.7	25.0	24.5	24.3	24.0	24.1
85°	21.2	21.4	19.4	16.1	14.4	13.2	12.1	12.1	11.9	11.8	11.9
87.5°	8.0	7.7	6.9	6.2	5.4	4.7	4.5	4.5	4.1	4.1	4.4
90°	4.1	3.6	3.1	2.6	2.0	1.4	0.9	0.4	0.9	1.4	2.0
92.5°	10.9	10.3	9.7	9.2	8.8	8.4	8.0	7.7	8.0	8.4	8.8
95°	22.8	22.2	21.5	21.0	20.9	20.8	20.6	20.5	20.6	20.8	20.9
97.5°	36.7	35.8	34.8	34.2	34.2	34.2	34.1	34.1	34.1	34.2	34.2
100°	46.4	45.5	44.6	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1
102.5°	57.3	56.9	56.4	56.1	55.8	55.6	55.3	54.9	55.3	55.6	55.8
105°	74.5	74.1	73.7	73.3	72.9	72.6	72.2	71.9	72.2	72.6	72.9
107.5°	92.9	92.6	92.3	91.9	91.6	91.2	90.9	90.5	90.9	91.2	91.6
110°	105.5	105.2	105.0	104.8	104.4	104.1	103.7	103.3	103.7	104.1	104.4





TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	118.0	117.7	117.4	117.2	117.0	116.8	116.6	116.5	116.6	116.8	117.0
115°	137.4	137.3	137.1	137.0	136.7	136.4	136.1	135.8	136.1	136.4	136.7
117.5°	156.1	156.0	155.9	155.8	155.6	155.5	155.3	155.2	155.3	155.5	155.6
120°	169.1	169.1	169.0	168.7	168.4	168.1	167.7	167.4	167.7	168.1	168.4
122.5°	181.5	181.3	181.1	180.9	180.8	180.7	180.6	180.5	180.6	180.7	180.8
125°	200.3	200.3	200.2	199.9	199.5	199.1	198.7	198.2	198.7	199.1	199.5
127.5°	218.5	218.4	218.3	218.1	217.8	217.7	217.4	217.1	217.4	217.7	217.8
130°	230.4	230.2	230.2	229.9	229.5	229.2	228.8	228.5	228.8	229.2	229.5
132.5°	242.4	242.4	242.5	242.1	241.6	241.0	240.4	239.9	240.4	241.0	241.6
135°	259.8	259.8	259.8	259.5	259.0	258.7	258.2	257.8	258.2	258.7	259.0
137.5°	276.9	276.8	276.6	276.3	275.9	275.5	275.1	274.7	275.1	275.5	275.9
140°	287.7	287.4	287.2	287.0	286.6	286.2	285.9	285.5	285.9	286.2	286.6
142.5°	298.4	298.1	297.8	297.6	297.3	296.9	296.7	296.4	296.7	296.9	297.3
145°	314.1	313.9	313.7	313.4	313.2	312.9	312.6	312.4	312.6	312.9	313.2
147.5°	328.2	328.1	327.9	327.7	327.5	327.3	327.3	327.1	327.3	327.3	327.5
150°	337.3	337.0	336.7	336.6	336.7	336.8	336.9	336.9	336.9	336.8	336.7
152.5°	345.7	345.6	345.4	345.4	345.3	345.2	345.1	345.0	345.1	345.2	345.3
155°	357.6	357.5	357.4	357.4	357.4	357.4	357.4	357.4	357.4	357.4	357.4
157.5°	368.0	367.9	367.8	367.9	368.0	368.2	368.4	368.5	368.4	368.2	368.0
160°	374.3	374.3	374.2	374.3	374.4	374.6	374.9	375.1	374.9	374.6	374.4
162.5°	380.2	380.1	380.1	380.2	380.4	380.6	380.7	380.8	380.7	380.6	380.4
165°	388.2	388.1	388.0	388.1	388.2	388.3	388.4	388.6	388.4	388.3	388.2
167.5°	393.9	393.9	393.9	394.0	394.3	394.6	394.8	395.1	394.8	394.6	394.3
170°	397.4	397.4	397.4	397.5	397.9	398.1	398.4	398.7	398.4	398.1	397.9
172.5°	399.9	399.9	399.9	400.1	400.4	400.6	400.9	401.2	400.9	400.6	400.4
175°	402.8	402.8	402.8	403.0	403.2	403.5	403.8	404.0	403.8	403.5	403.2
177.5°	404.4	404.4	404.5	404.6	404.8	405.0	405.3	405.5	405.3	405.0	404.8
180°	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0



TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	477.1	475.2	473.8	470.5	468.6	466.2	464.2	466.4	464.0	465.0	463.5
5°	462.2	456.4	452.3	446.3	441.1	436.4	432.9	432.3	430.6	429.8	427.3
7.5°	444.3	437.0	430.0	422.1	415.5	408.8	404.6	401.0	398.7	395.6	393.4
10°	433.7	424.0	415.8	406.4	398.1	390.8	385.1	382.2	379.5	375.6	374.2
12.5°	420.7	410.7	400.6	390.5	382.5	374.5	369.6	365.2	363.4	359.0	358.6
15°	405.1	390.0	380.1	369.9	358.9	352.3	348.2	343.5	341.4	338.3	336.1
17.5°	386.5	373.0	360.7	350.0	340.6	335.1	329.9	326.7	323.2	321.1	317.4
20°	372.9	360.2	347.8	336.4	329.2	322.9	318.8	315.7	311.9	310.9	307.2
22.5°	361.6	347.5	335.6	326.1	318.3	311.0	306.6	304.4	301.9	298.7	298.0
25°	343.0	328.4	318.3	308.9	301.8	295.2	292.2	289.5	287.0	284.7	283.9
27.5°	327.1	314.0	302.0	293.5	287.3	281.3	278.7	275.4	273.6	271.7	269.5
30°	315.8	302.5	291.9	283.7	277.1	271.8	268.9	266.6	265.0	263.3	262.1
32.5°	304.3	291.9	281.8	273.7	267.1	263.1	260.5	258.9	257.1	255.1	253.5
35°	289.1	275.4	265.6	258.6	253.4	250.3	247.4	246.0	244.0	244.0	242.3
37.5°	271.9	260.1	251.4	245.0	240.4	237.6	234.5	233.5	232.2	231.3	230.8
40°	261.7	250.7	242.5	236.1	231.2	228.9	226.4	224.8	224.0	222.9	222.6
42.5°	251.1	240.7	232.8	226.9	222.6	220.7	218.4	217.2	215.5	214.2	213.9
45°	235.1	225.0	217.8	213.0	209.4	207.1	205.6	203.1	202.3	200.7	200.5
47.5°	219.9	210.2	203.1	199.2	196.0	194.1	191.9	189.4	188.4	187.6	187.5
50°	208.5	199.7	193.1	189.4	186.3	183.6	181.3	179.7	179.1	179.1	179.5
52.5°	197.0	189.4	183.9	179.3	176.4	173.5	171.4	170.4	169.5	170.5	171.2
55°	180.1	172.5	168.4	164.0	161.1	157.8	156.8	156.4	155.8	157.4	158.3
57.5°	162.2	156.9	152.0	147.8	145.2	143.2	141.9	141.6	142.8	143.6	146.2
60°	150.8	144.6	140.4	137.1	133.9	132.7	132.2	131.9	132.7	134.9	138.5
62.5°	138.3	133.3	128.6	126.2	123.9	121.8	121.7	122.0	123.6	126.3	129.7
65°	119.9	115.6	112.5	109.6	107.7	106.6	106.9	107.7	109.6	113.2	117.0
67.5°	101.2	98.3	95.5	93.2	91.4	91.4	91.8	93.1	95.2	99.2	102.8
70°	89.3	86.0	83.6	82.7	81.1	80.3	81.6	83.6	85.5	89.3	92.3
72.5°	77.2	74.4	72.6	71.9	71.2	70.6	71.1	73.3	75.8	79.5	83.1
75°	59.3	58.3	57.1	56.3	55.6	56.1	56.4	58.5	60.5	64.5	68.6
77.5°	43.3	42.3	41.5	41.3	40.9	41.2	42.4	43.9	45.8	48.7	51.8
80°	32.7	32.4	31.9	31.7	31.7	31.9	33.6	34.6	36.5	39.1	41.6
82.5°	23.9	23.6	23.5	23.5	23.6	23.7	24.7	26.0	27.6	29.6	31.7
85°	12.6	12.1	12.8	13.0	12.6	13.2	13.6	14.4	15.1	16.1	17.1
87.5°	4.6	5.1	5.0	5.3	5.4	5.8	5.7	6.4	6.9	7.2	7.1
90°	2.6	3.1	3.6	4.1	4.5	5.1	5.4	5.7	6.1	6.4	6.7
92.5°	9.2	9.7	10.3	10.9	11.5	12.1	12.6	13.0	13.5	13.9	14.3
95°	21.0	21.5	22.2	22.8	23.5	24.3	24.8	25.2	25.8	26.2	26.6
97.5°	34.2	34.8	35.8	36.7	37.6	38.6	39.1	39.6	40.0	40.5	40.8
100°	44.1	44.6	45.5	46.4	47.3	48.2	48.9	49.5	50.1	50.7	51.1
102.5°	56.1	56.4	56.9	57.3	57.9	58.3	59.0	59.7	60.4	61.1	61.5
105°	73.3	73.7	74.1	74.5	74.9	75.3	75.7	76.2	76.6	77.0	77.3
107.5°	91.9	92.3	92.6	92.9	93.2	93.5	93.7	94.0	94.2	94.3	94.5
110°	104.8	105.0	105.2	105.5	105.7	105.9	106.1	106.3	106.6	106.7	106.8



TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	117.2	117.4	117.7	118.0	118.2	118.5	118.6	118.7	118.8	118.9	118.9
115°	137.0	137.1	137.3	137.4	137.6	137.8	137.7	137.6	137.5	137.4	137.4
117.5°	155.8	155.9	156.0	156.1	156.2	156.4	156.4	156.5	156.6	156.6	156.5
120°	168.7	169.0	169.1	169.1	169.2	169.2	169.2	169.2	169.2	169.2	169.1
122.5°	180.9	181.1	181.3	181.5	181.6	181.8	181.8	181.7	181.6	181.6	181.5
125°	199.9	200.2	200.3	200.3	200.4	200.5	200.3	200.2	200.0	199.9	199.7
127.5°	218.1	218.3	218.4	218.5	218.6	218.6	218.6	218.5	218.4	218.3	218.2
130°	229.9	230.2	230.2	230.4	230.6	230.7	230.6	230.6	230.5	230.4	230.3
132.5°	242.1	242.5	242.4	242.4	242.4	242.3	242.2	242.2	242.1	242.0	241.9
135°	259.5	259.8	259.8	259.8	259.9	260.0	260.0	260.0	260.0	260.0	259.8
137.5°	276.3	276.6	276.8	276.9	277.1	277.2	277.3	277.4	277.5	277.6	277.4
140°	287.0	287.2	287.4	287.7	287.8	288.0	288.2	288.4	288.5	288.6	288.6
142.5°	297.6	297.8	298.1	298.4	298.6	298.9	299.0	299.1	299.2	299.3	299.1
145°	313.4	313.7	313.9	314.1	314.3	314.5	314.5	314.5	314.5	314.5	314.4
147.5°	327.7	327.9	328.1	328.2	328.3	328.5	328.7	328.9	329.0	329.2	329.0
150°	336.6	336.7	337.0	337.3	337.6	337.9	337.9	337.9	337.9	337.9	337.8
152.5°	345.4	345.4	345.6	345.7	345.8	345.9	346.1	346.3	346.4	346.6	346.5
155°	357.4	357.4	357.5	357.6	357.7	357.8	358.0	358.3	358.6	358.8	358.8
157.5°	367.9	367.8	367.9	368.0	368.0	368.1	368.4	368.6	369.0	369.3	369.2
160°	374.3	374.2	374.3	374.3	374.3	374.4	374.7	375.0	375.2	375.5	375.5
162.5°	380.2	380.1	380.1	380.2	380.2	380.2	380.6	380.8	381.2	381.6	381.6
165°	388.1	388.0	388.1	388.2	388.3	388.3	388.6	388.9	389.1	389.4	389.3
167.5°	394.0	393.9	393.9	393.9	393.9	393.9	394.3	394.8	395.1	395.6	395.6
170°	397.5	397.4	397.4	397.4	397.4	397.4	397.9	398.2	398.7	399.1	399.0
172.5°	400.1	399.9	399.9	399.9	399.9	399.9	400.4	400.8	401.2	401.6	401.6
175°	403.0	402.8	402.8	402.8	402.8	402.8	403.2	403.6	404.0	404.5	404.4
177.5°	404.6	404.5	404.4	404.4	404.3	404.2	404.6	404.9	405.3	405.6	405.6
180°	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0



TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	462.5	463.7	462.7	464.0	462.7	463.7	462.5	463.5	465.0	464.0	466.4
5°	426.3	424.5	425.7	424.9	425.7	424.5	426.3	427.3	429.8	430.6	432.3
7.5°	392.9	391.1	389.1	388.1	389.1	391.1	392.9	393.4	395.6	398.7	401.0
10°	371.9	369.6	369.4	368.0	369.4	369.6	371.9	374.2	375.6	379.5	382.2
12.5°	356.6	354.5	352.1	351.5	352.1	354.5	356.6	358.6	359.0	363.4	365.2
15°	334.8	333.1	331.7	333.0	331.7	333.1	334.8	336.1	338.3	341.4	343.5
17.5°	316.7	315.4	315.1	313.6	315.1	315.4	316.7	317.4	321.1	323.2	326.7
20°	305.3	304.3	304.8	302.0	304.8	304.3	305.3	307.2	310.9	311.9	315.7
22.5°	296.3	294.3	294.0	293.5	294.0	294.3	296.3	298.0	298.7	301.9	304.4
25°	282.0	281.1	280.0	281.1	280.0	281.1	282.0	283.9	284.7	287.0	289.5
27.5°	269.7	268.4	268.1	268.3	268.1	268.4	269.7	269.5	271.7	273.6	275.4
30°	262.1	260.0	260.2	260.0	260.2	260.0	262.1	262.1	263.3	265.0	266.6
32.5°	253.9	252.4	252.2	251.8	252.2	252.4	253.9	253.5	255.1	257.1	258.9
35°	241.7	241.7	240.7	240.7	240.7	241.7	241.7	242.3	244.0	244.0	246.0
37.5°	230.2	230.1	229.4	229.5	229.4	230.1	230.2	230.8	231.3	232.2	233.5
40°	221.7	221.5	220.9	219.6	220.9	221.5	221.7	222.6	222.9	224.0	224.8
42.5°	213.5	212.8	212.5	212.0	212.5	212.8	213.5	213.9	214.2	215.5	217.2
45°	200.5	200.5	200.1	199.8	200.1	200.5	200.5	200.5	200.7	202.3	203.1
47.5°	187.9	188.2	189.0	188.9	189.0	188.2	187.9	187.5	187.6	188.4	189.4
50°	180.3	180.5	181.1	181.3	181.1	180.5	180.3	179.5	179.1	179.1	179.7
52.5°	171.9	173.1	173.9	173.7	173.9	173.1	171.9	171.2	170.5	169.5	170.4
55°	160.1	161.6	163.0	163.2	163.0	161.6	160.1	158.3	157.4	155.8	156.4
57.5°	148.5	150.4	151.9	152.5	151.9	150.4	148.5	146.2	143.6	142.8	141.6
60°	140.5	143.2	145.1	145.9	145.1	143.2	140.5	138.5	134.9	132.7	131.9
62.5°	133.0	136.0	137.8	137.9	137.8	136.0	133.0	129.7	126.3	123.6	122.0
65°	120.6	123.6	125.3	126.5	125.3	123.6	120.6	117.0	113.2	109.6	107.7
67.5°	107.2	110.3	112.1	113.1	112.1	110.3	107.2	102.8	99.2	95.2	93.1
70°	97.5	100.6	103.0	103.9	103.0	100.6	97.5	92.3	89.3	85.5	83.6
72.5°	87.9	90.7	92.6	93.6	92.6	90.7	87.9	83.1	79.5	75.8	73.3
75°	71.2	75.0	76.9	77.8	76.9	75.0	71.2	68.6	64.5	60.5	58.5
77.5°	54.9	58.3	59.5	60.0	59.5	58.3	54.9	51.8	48.7	45.8	43.9
80°	44.1	46.2	47.6	47.8	47.6	46.2	44.1	41.6	39.1	36.5	34.6
82.5°	33.9	35.6	36.0	36.6	36.0	35.6	33.9	31.7	29.6	27.6	26.0
85°	18.5	19.4	19.6	19.4	19.6	19.4	18.5	17.1	16.1	15.1	14.4
87.5°	7.5	7.4	7.4	7.8	7.4	7.4	7.5	7.1	7.2	6.9	6.4
90°	7.0	7.1	7.3	7.6	7.3	7.1	7.0	6.7	6.4	6.1	5.7
92.5°	14.4	14.5	14.7	14.9	14.7	14.5	14.4	14.3	13.9	13.5	13.0
95°	26.7	26.8	26.9	27.1	26.9	26.8	26.7	26.6	26.2	25.8	25.2
97.5°	40.8	40.9	41.0	41.1	41.0	40.9	40.8	40.8	40.5	40.0	39.6
100°	51.3	51.5	51.5	51.7	51.5	51.5	51.3	51.1	50.7	50.1	49.5
102.5°	61.7	61.9	62.1	62.2	62.1	61.9	61.7	61.5	61.1	60.4	59.7
105°	77.5	77.8	77.9	78.2	77.9	77.8	77.5	77.3	77.0	76.6	76.2
107.5°	94.4	94.4	94.4	94.4	94.4	94.4	94.4	94.5	94.3	94.2	94.0
110°	106.7	106.6	106.6	106.6	106.6	106.6	106.7	106.8	106.7	106.6	106.3



TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	118.8	118.6	118.5	118.4	118.5	118.6	118.8	118.9	118.9	118.8	118.7
115°	137.3	137.2	137.1	137.1	137.1	137.2	137.3	137.4	137.4	137.5	137.6
117.5°	156.2	156.0	155.7	155.3	155.7	156.0	156.2	156.5	156.6	156.6	156.5
120°	168.8	168.5	168.3	168.0	168.3	168.5	168.8	169.1	169.2	169.2	169.2
122.5°	181.3	181.0	180.8	180.6	180.8	181.0	181.3	181.5	181.6	181.6	181.7
125°	199.7	199.7	199.6	199.5	199.6	199.7	199.7	199.7	199.9	200.0	200.2
127.5°	218.1	217.9	217.8	217.7	217.8	217.9	218.1	218.2	218.3	218.4	218.5
130°	230.2	230.1	229.9	229.8	229.9	230.1	230.2	230.3	230.4	230.5	230.6
132.5°	241.7	241.5	241.3	241.1	241.3	241.5	241.7	241.9	242.0	242.1	242.2
135°	259.6	259.3	259.0	258.8	259.0	259.3	259.6	259.8	260.0	260.0	260.0
137.5°	277.1	276.7	276.3	276.0	276.3	276.7	277.1	277.4	277.6	277.5	277.4
140°	288.2	287.8	287.5	287.1	287.5	287.8	288.2	288.6	288.6	288.5	288.4
142.5°	298.7	298.4	298.1	297.7	298.1	298.4	298.7	299.1	299.3	299.2	299.1
145°	314.2	314.0	313.8	313.6	313.8	314.0	314.2	314.4	314.5	314.5	314.5
147.5°	328.6	328.1	327.6	327.2	327.6	328.1	328.6	329.0	329.2	329.0	328.9
150°	337.7	337.5	337.3	337.2	337.3	337.5	337.7	337.8	337.9	337.9	337.9
152.5°	346.3	346.1	345.8	345.5	345.8	346.1	346.3	346.5	346.6	346.4	346.3
155°	358.5	358.1	357.8	357.4	357.8	358.1	358.5	358.8	358.8	358.6	358.3
157.5°	368.7	368.2	367.7	367.3	367.7	368.2	368.7	369.2	369.3	369.0	368.6
160°	375.1	374.8	374.4	374.1	374.4	374.8	375.1	375.5	375.5	375.2	375.0
162.5°	381.1	380.7	380.3	379.9	380.3	380.7	381.1	381.6	381.6	381.2	380.8
165°	388.9	388.5	388.1	387.6	388.1	388.5	388.9	389.3	389.4	389.1	388.9
167.5°	395.1	394.7	394.2	393.9	394.2	394.7	395.1	395.6	395.6	395.1	394.8
170°	398.6	398.1	397.6	397.1	397.6	398.1	398.6	399.0	399.1	398.7	398.2
172.5°	401.2	400.7	400.3	399.8	400.3	400.7	401.2	401.6	401.6	401.2	400.8
175°	403.9	403.4	403.0	402.4	403.0	403.4	403.9	404.4	404.5	404.0	403.6
177.5°	405.2	404.7	404.4	403.9	404.4	404.7	405.2	405.6	405.6	405.3	404.9
180°	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0



TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	464.2	466.2	468.6	470.5	473.8	475.2	477.1	478.5	481.2	483.7	486.6
5°	432.9	436.4	441.1	446.3	452.3	456.4	462.2	465.7	472.7	479.0	485.3
7.5°	404.6	408.8	415.5	422.1	430.0	437.0	444.3	452.3	461.2	471.8	480.5
10°	385.1	390.8	398.1	406.4	415.8	424.0	433.7	442.4	453.3	465.7	477.2
12.5°	369.6	374.5	382.5	390.5	400.6	410.7	420.7	432.1	444.9	458.6	473.1
15°	348.2	352.3	358.9	369.9	380.1	390.0	405.1	415.8	431.9	447.1	464.7
17.5°	329.9	335.1	340.6	350.0	360.7	373.0	386.5	399.9	415.4	434.7	454.4
20°	318.8	322.9	329.2	336.4	347.8	360.2	372.9	386.6	405.5	425.5	446.7
22.5°	306.6	311.0	318.3	326.1	335.6	347.5	361.6	376.5	396.3	415.9	439.0
25°	292.2	295.2	301.8	308.9	318.3	328.4	343.0	359.5	379.2	401.6	425.1
27.5°	278.7	281.3	287.3	293.5	302.0	314.0	327.1	343.8	362.2	385.0	411.0
30°	268.9	271.8	277.1	283.7	291.9	302.5	315.8	331.5	351.3	373.5	400.7
32.5°	260.5	263.1	267.1	273.7	281.8	291.9	304.3	320.3	340.1	362.7	389.4
35°	247.4	250.3	253.4	258.6	265.6	275.4	289.1	304.2	323.1	344.9	369.4
37.5°	234.5	237.6	240.4	245.0	251.4	260.1	271.9	287.6	304.7	325.7	349.3
40°	226.4	228.9	231.2	236.1	242.5	250.7	261.7	275.7	293.8	313.4	333.0
42.5°	218.4	220.7	222.6	226.9	232.8	240.7	251.1	264.8	281.6	299.9	317.2
45°	205.6	207.1	209.4	213.0	217.8	225.0	235.1	247.3	261.4	278.7	291.8
47.5°	191.9	194.1	196.0	199.2	203.1	210.2	219.9	230.2	243.2	256.0	265.1
50°	181.3	183.6	186.3	189.4	193.1	199.7	208.5	219.0	230.0	239.9	247.6
52.5°	171.4	173.5	176.4	179.3	183.9	189.4	197.0	206.3	217.1	224.2	230.7
55°	156.8	157.8	161.1	164.0	168.4	172.5	180.1	188.3	194.9	200.3	205.6
57.5°	141.9	143.2	145.2	147.8	152.0	156.9	162.2	169.5	173.3	176.1	180.3
60°	132.2	132.7	133.9	137.1	140.4	144.6	150.8	156.0	158.9	161.1	164.6
62.5°	121.7	121.8	123.9	126.2	128.6	133.3	138.3	142.5	144.8	146.0	149.3
65°	106.9	106.6	107.7	109.6	112.5	115.6	119.9	123.6	123.4	124.7	126.7
67.5°	91.8	91.4	91.4	93.2	95.5	98.3	101.2	103.4	103.4	105.0	106.1
70°	81.6	80.3	81.1	82.7	83.6	86.0	89.3	90.1	90.2	91.0	92.1
72.5°	71.1	70.6	71.2	71.9	72.6	74.4	77.2	77.7	77.8	78.2	79.9
75°	56.4	56.1	55.6	56.3	57.1	58.3	59.3	60.2	59.9	60.2	61.4
77.5°	42.4	41.2	40.9	41.3	41.5	42.3	43.3	43.2	43.4	43.4	44.8
80°	33.6	31.9	31.7	31.7	31.9	32.4	32.7	33.2	32.5	33.2	33.6
82.5°	24.7	23.7	23.6	23.5	23.5	23.6	23.9	24.1	24.0	24.3	24.5
85°	13.6	13.2	12.6	13.0	12.8	12.1	12.6	11.9	11.8	11.9	12.1
87.5°	5.7	5.8	5.4	5.3	5.0	5.1	4.6	4.4	4.1	4.1	4.5
90°	5.4	5.1	4.5	4.1	3.6	3.1	2.6	2.0	1.4	0.9	0.4
92.5°	12.6	12.1	11.5	10.9	10.3	9.7	9.2	8.8	8.4	8.0	7.7
95°	24.8	24.3	23.5	22.8	22.2	21.5	21.0	20.9	20.8	20.6	20.5
97.5°	39.1	38.6	37.6	36.7	35.8	34.8	34.2	34.2	34.2	34.1	34.1
100°	48.9	48.2	47.3	46.4	45.5	44.6	44.1	44.1	44.1	44.1	44.1
102.5°	59.0	58.3	57.9	57.3	56.9	56.4	56.1	55.8	55.6	55.3	54.9
105°	75.7	75.3	74.9	74.5	74.1	73.7	73.3	72.9	72.6	72.2	71.9
107.5°	93.7	93.5	93.2	92.9	92.6	92.3	91.9	91.6	91.2	90.9	90.5
110°	106.1	105.9	105.7	105.5	105.2	105.0	104.8	104.4	104.1	103.7	103.3



TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	118.6	118.5	118.2	118.0	117.7	117.4	117.2	117.0	116.8	116.6	116.5
115°	137.7	137.8	137.6	137.4	137.3	137.1	137.0	136.7	136.4	136.1	135.8
117.5°	156.4	156.4	156.2	156.1	156.0	155.9	155.8	155.6	155.5	155.3	155.2
120°	169.2	169.2	169.2	169.1	169.1	169.0	168.7	168.4	168.1	167.7	167.4
122.5°	181.8	181.8	181.6	181.5	181.3	181.1	180.9	180.8	180.7	180.6	180.5
125°	200.3	200.5	200.4	200.3	200.3	200.2	199.9	199.5	199.1	198.7	198.2
127.5°	218.6	218.6	218.6	218.5	218.4	218.3	218.1	217.8	217.7	217.4	217.1
130°	230.6	230.7	230.6	230.4	230.2	230.2	229.9	229.5	229.2	228.8	228.5
132.5°	242.2	242.3	242.4	242.4	242.4	242.5	242.1	241.6	241.0	240.4	239.9
135°	260.0	260.0	259.9	259.8	259.8	259.8	259.5	259.0	258.7	258.2	257.8
137.5°	277.3	277.2	277.1	276.9	276.8	276.6	276.3	275.9	275.5	275.1	274.7
140°	288.2	288.0	287.8	287.7	287.4	287.2	287.0	286.6	286.2	285.9	285.5
142.5°	299.0	298.9	298.6	298.4	298.1	297.8	297.6	297.3	296.9	296.7	296.4
145°	314.5	314.5	314.3	314.1	313.9	313.7	313.4	313.2	312.9	312.6	312.4
147.5°	328.7	328.5	328.3	328.2	328.1	327.9	327.7	327.5	327.3	327.3	327.1
150°	337.9	337.9	337.6	337.3	337.0	336.7	336.6	336.7	336.8	336.9	336.9
152.5°	346.1	345.9	345.8	345.7	345.6	345.4	345.4	345.3	345.2	345.1	345.0
155°	358.0	357.8	357.7	357.6	357.5	357.4	357.4	357.4	357.4	357.4	357.4
157.5°	368.4	368.1	368.0	368.0	367.9	367.8	367.9	368.0	368.2	368.4	368.5
160°	374.7	374.4	374.3	374.3	374.3	374.2	374.3	374.4	374.6	374.9	375.1
162.5°	380.6	380.2	380.2	380.2	380.1	380.1	380.2	380.4	380.6	380.7	380.8
165°	388.6	388.3	388.3	388.2	388.1	388.0	388.1	388.2	388.3	388.4	388.6
167.5°	394.3	393.9	393.9	393.9	393.9	393.9	394.0	394.3	394.6	394.8	395.1
170°	397.9	397.4	397.4	397.4	397.4	397.4	397.5	397.9	398.1	398.4	398.7
172.5°	400.4	399.9	399.9	399.9	399.9	399.9	400.1	400.4	400.6	400.9	401.2
175°	403.2	402.8	402.8	402.8	402.8	402.8	403.0	403.2	403.5	403.8	404.0
177.5°	404.6	404.2	404.3	404.4	404.4	404.5	404.6	404.8	405.0	405.3	405.5
180°	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0



TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	488.1	490.4	491.9	494.6	497.0	498.3	499.4	500.4	501.6	502.6	505.4
5°	491.2	496.6	501.1	508.1	514.5	519.4	524.8	529.5	533.4	539.0	543.3
7.5°	489.8	499.4	509.3	520.2	531.3	541.5	551.1	559.9	567.9	577.7	586.2
10°	488.6	501.5	514.2	529.0	543.9	556.7	568.6	580.9	589.7	602.1	612.6
12.5°	487.6	502.8	518.3	535.8	552.3	570.4	586.3	595.2	608.7	618.6	631.1
15°	483.4	503.5	524.8	544.6	568.1	584.8	598.8	616.1	628.7	641.2	654.8
17.5°	475.9	498.8	522.5	548.5	571.0	588.9	607.0	623.7	638.6	655.5	672.4
20°	472.4	495.3	522.5	549.1	571.1	589.9	608.4	626.8	643.3	664.9	684.5
22.5°	465.2	492.8	517.9	543.9	566.5	586.9	608.0	628.7	650.7	675.1	699.6
25°	452.3	480.3	506.8	532.4	555.3	580.9	603.3	631.2	659.2	691.5	722.0
27.5°	438.8	465.7	490.0	514.7	541.4	570.3	599.4	631.0	667.7	708.6	751.5
30°	427.9	453.3	477.0	502.3	530.1	562.7	594.7	632.1	674.6	720.5	771.7
32.5°	415.3	438.6	461.6	488.5	518.8	553.1	590.4	631.5	682.5	734.7	787.3
35°	393.5	413.1	436.8	465.5	499.6	539.0	582.1	630.7	689.2	749.2	793.4
37.5°	367.8	386.0	411.0	442.4	478.2	520.5	571.6	629.3	691.4	739.2	753.5
40°	350.4	367.4	393.3	425.9	462.5	507.3	563.3	624.3	684.5	715.0	703.2
42.5°	332.0	349.7	375.1	407.2	446.7	495.4	552.9	613.9	664.4	675.9	635.3
45°	302.9	321.2	346.2	378.7	421.2	473.9	533.9	589.3	618.3	597.5	534.7
47.5°	275.8	293.0	316.1	349.7	393.5	448.1	505.8	550.0	552.3	502.7	435.5
50°	257.3	273.2	296.5	330.1	373.5	428.8	480.9	515.8	500.1	443.8	379.3
52.5°	239.2	254.8	277.7	310.9	353.9	404.6	453.1	477.5	448.0	390.2	335.2
55°	213.0	226.7	249.1	279.8	320.6	367.6	408.8	417.2	378.9	322.1	277.3
57.5°	187.5	200.2	220.6	248.9	286.2	327.8	360.1	358.2	317.7	268.9	233.4
60°	170.2	182.5	200.7	228.3	262.3	298.2	325.7	319.1	279.0	236.9	207.1
62.5°	154.7	165.8	182.9	207.1	238.1	271.3	293.9	284.2	244.9	208.1	184.5
65°	131.9	141.2	155.8	176.4	202.2	229.5	247.1	234.5	200.9	172.3	153.3
67.5°	110.0	117.5	129.7	146.2	168.2	190.2	200.8	188.2	161.3	140.4	126.4
70°	96.2	102.8	112.3	126.9	146.1	164.6	172.6	161.3	138.2	120.3	110.2
72.5°	82.4	87.8	96.1	109.3	124.7	140.7	147.8	137.0	118.0	102.8	93.5
75°	63.7	67.4	73.1	82.2	94.3	107.2	111.0	101.6	89.4	78.1	71.9
77.5°	45.6	48.7	53.1	58.8	67.4	75.5	78.9	73.5	64.1	56.9	51.8
80°	35.0	36.6	40.4	45.1	51.9	57.1	59.3	55.8	49.2	43.9	39.9
82.5°	25.0	26.7	28.8	32.7	37.1	40.6	43.0	40.7	35.9	31.7	29.4
85°	12.1	13.2	14.4	16.1	19.4	21.4	21.2	19.8	17.9	16.3	15.1
87.5°	4.5	4.7	5.4	6.2	6.9	7.7	8.0	7.8	7.3	6.9	6.4
90°	0.9	1.4	2.0	2.6	3.1	3.6	4.1	4.5	5.1	5.4	5.7
92.5°	8.0	8.4	8.8	9.2	9.7	10.3	10.9	11.5	12.1	12.6	13.0
95°	20.6	20.8	20.9	21.0	21.5	22.2	22.8	23.5	24.3	24.8	25.2
97.5°	34.1	34.2	34.2	34.2	34.8	35.8	36.7	37.6	38.6	39.1	39.6
100°	44.1	44.1	44.1	44.1	44.6	45.5	46.4	47.3	48.2	48.9	49.5
102.5°	55.3	55.6	55.8	56.1	56.4	56.9	57.3	57.9	58.3	59.0	59.7
105°	72.2	72.6	72.9	73.3	73.7	74.1	74.5	74.9	75.3	75.7	76.2
107.5°	90.9	91.2	91.6	91.9	92.3	92.6	92.9	93.2	93.5	93.7	94.0
110°	103.7	104.1	104.4	104.8	105.0	105.2	105.5	105.7	105.9	106.1	106.3





TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	116.6	116.8	117.0	117.2	117.4	117.7	118.0	118.2	118.5	118.6	118.7
115°	136.1	136.4	136.7	137.0	137.1	137.3	137.4	137.6	137.8	137.7	137.6
117.5°	155.3	155.5	155.6	155.8	155.9	156.0	156.1	156.2	156.4	156.4	156.5
120°	167.7	168.1	168.4	168.7	169.0	169.1	169.1	169.2	169.2	169.2	169.2
122.5°	180.6	180.7	180.8	180.9	181.1	181.3	181.5	181.6	181.8	181.8	181.7
125°	198.7	199.1	199.5	199.9	200.2	200.3	200.3	200.4	200.5	200.3	200.2
127.5°	217.4	217.7	217.8	218.1	218.3	218.4	218.5	218.6	218.6	218.6	218.5
130°	228.8	229.2	229.5	229.9	230.2	230.2	230.4	230.6	230.7	230.6	230.6
132.5°	240.4	241.0	241.6	242.1	242.5	242.4	242.4	242.4	242.3	242.2	242.2
135°	258.2	258.7	259.0	259.5	259.8	259.8	259.8	259.9	260.0	260.0	260.0
137.5°	275.1	275.5	275.9	276.3	276.6	276.8	276.9	277.1	277.2	277.3	277.4
140°	285.9	286.2	286.6	287.0	287.2	287.4	287.7	287.8	288.0	288.2	288.4
142.5°	296.7	296.9	297.3	297.6	297.8	298.1	298.4	298.6	298.9	299.0	299.1
145°	312.6	312.9	313.2	313.4	313.7	313.9	314.1	314.3	314.5	314.5	314.5
147.5°	327.3	327.3	327.5	327.7	327.9	328.1	328.2	328.3	328.5	328.7	328.9
150°	336.9	336.8	336.7	336.6	336.7	337.0	337.3	337.6	337.9	337.9	337.9
152.5°	345.1	345.2	345.3	345.4	345.4	345.6	345.7	345.8	345.9	346.1	346.3
155°	357.4	357.4	357.4	357.4	357.4	357.5	357.6	357.7	357.8	358.0	358.3
157.5°	368.4	368.2	368.0	367.9	367.8	367.9	368.0	368.0	368.1	368.4	368.6
160°	374.9	374.6	374.4	374.3	374.2	374.3	374.3	374.3	374.4	374.7	375.0
162.5°	380.7	380.6	380.4	380.2	380.1	380.1	380.2	380.2	380.2	380.6	380.8
165°	388.4	388.3	388.2	388.1	388.0	388.1	388.2	388.3	388.3	388.6	388.9
167.5°	394.8	394.6	394.3	394.0	393.9	393.9	393.9	393.9	393.9	394.3	394.8
170°	398.4	398.1	397.9	397.5	397.4	397.4	397.4	397.4	397.4	397.9	398.2
172.5°	400.9	400.6	400.4	400.1	399.9	399.9	399.9	399.9	399.9	400.4	400.8
175°	403.8	403.5	403.2	403.0	402.8	402.8	402.8	402.8	402.8	403.2	403.6
177.5°	405.3	405.0	404.8	404.6	404.5	404.4	404.4	404.3	404.2	404.6	404.9
180°	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0



TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	507.7	509.0	511.8	510.9	512.1	512.8	513.4
5°	548.7	555.3	558.2	557.8	562.1	561.1	560.0
7.5°	595.0	601.9	605.8	610.6	613.4	613.7	616.1
10°	621.3	630.3	634.0	639.2	642.5	644.4	644.1
12.5°	641.3	648.5	656.7	659.2	663.7	666.1	665.2
15°	665.6	676.9	685.5	689.8	695.4	697.1	699.3
17.5°	687.2	702.3	712.4	725.9	730.9	734.1	732.2
20°	703.5	723.4	733.5	749.6	758.5	763.2	761.5
22.5°	722.7	744.4	763.0	776.9	790.4	796.8	798.2
25°	755.8	785.4	812.9	831.2	847.8	851.8	860.4
27.5°	792.7	827.7	857.0	876.3	887.9	892.2	895.0
30°	815.9	850.8	872.8	885.2	888.9	888.5	888.1
32.5°	827.3	849.1	853.4	849.9	841.4	834.2	826.7
35°	811.2	795.0	770.6	739.3	716.2	692.9	690.6
37.5°	729.6	677.5	637.0	591.8	565.8	549.7	538.5
40°	652.7	593.6	544.6	506.5	479.9	469.4	459.1
42.5°	569.4	512.8	469.4	437.6	417.6	405.9	397.8
45°	462.5	412.7	378.7	355.6	339.7	330.7	325.6
47.5°	379.1	342.1	313.3	296.6	285.7	278.7	278.7
50°	334.2	299.0	279.8	266.6	257.2	251.6	252.6
52.5°	294.4	268.1	251.8	240.8	233.7	230.3	230.2
55°	246.2	227.3	216.6	208.5	203.8	199.8	200.7
57.5°	210.6	194.7	187.4	180.7	177.5	175.9	173.6
60°	188.5	176.2	170.0	164.6	161.3	160.1	157.8
62.5°	168.9	159.2	153.2	148.8	145.9	145.4	143.7
65°	142.0	134.6	129.2	127.2	124.0	123.2	123.2
67.5°	117.0	111.7	107.5	105.7	104.3	104.5	103.5
70°	101.4	97.0	94.3	92.3	91.3	91.5	90.7
72.5°	88.7	83.8	81.5	80.3	78.9	79.5	79.1
75°	67.1	64.7	63.5	62.2	61.4	61.0	60.5
77.5°	49.3	47.2	46.2	45.5	45.7	44.6	45.4
80°	38.1	36.3	35.7	34.6	34.4	34.4	34.2
82.5°	27.9	26.8	26.4	25.6	25.1	25.5	25.0
85°	14.4	13.6	13.4	13.4	13.0	12.6	13.6
87.5°	6.5	5.9	6.0	5.8	5.9	5.8	5.4
90°	6.1	6.4	6.7	7.0	7.1	7.3	7.6
92.5°	13.5	13.9	14.3	14.4	14.5	14.7	14.9
95°	25.8	26.2	26.6	26.7	26.8	26.9	27.1
97.5°	40.0	40.5	40.8	40.8	40.9	41.0	41.1
100°	50.1	50.7	51.1	51.3	51.5	51.5	51.7
102.5°	60.4	61.1	61.5	61.7	61.9	62.1	62.2
105°	76.6	77.0	77.3	77.5	77.8	77.9	78.2
107.5°	94.2	94.3	94.5	94.4	94.4	94.4	94.4
110°	106.6	106.7	106.8	106.7	106.6	106.6	106.6



TEST NUMBER: P333116-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	118.8	118.9	118.9	118.8	118.6	118.5	118.4
115°	137.5	137.4	137.4	137.3	137.2	137.1	137.1
117.5°	156.6	156.6	156.5	156.2	156.0	155.7	155.3
120°	169.2	169.2	169.1	168.8	168.5	168.3	168.0
122.5°	181.6	181.6	181.5	181.3	181.0	180.8	180.6
125°	200.0	199.9	199.7	199.7	199.7	199.6	199.5
127.5°	218.4	218.3	218.2	218.1	217.9	217.8	217.7
130°	230.5	230.4	230.3	230.2	230.1	229.9	229.8
132.5°	242.1	242.0	241.9	241.7	241.5	241.3	241.1
135°	260.0	260.0	259.8	259.6	259.3	259.0	258.8
137.5°	277.5	277.6	277.4	277.1	276.7	276.3	276.0
140°	288.5	288.6	288.6	288.2	287.8	287.5	287.1
142.5°	299.2	299.3	299.1	298.7	298.4	298.1	297.7
145°	314.5	314.5	314.4	314.2	314.0	313.8	313.6
147.5°	329.0	329.2	329.0	328.6	328.1	327.6	327.2
150°	337.9	337.9	337.8	337.7	337.5	337.3	337.2
152.5°	346.4	346.6	346.5	346.3	346.1	345.8	345.5
155°	358.6	358.8	358.8	358.5	358.1	357.8	357.4
157.5°	369.0	369.3	369.2	368.7	368.2	367.7	367.3
160°	375.2	375.5	375.5	375.1	374.8	374.4	374.1
162.5°	381.2	381.6	381.6	381.1	380.7	380.3	379.9
165°	389.1	389.4	389.3	388.9	388.5	388.1	387.6
167.5°	395.1	395.6	395.6	395.1	394.7	394.2	393.9
170°	398.7	399.1	399.0	398.6	398.1	397.6	397.1
172.5°	401.2	401.6	401.6	401.2	400.7	400.3	399.8
175°	404.0	404.5	404.4	403.9	403.4	403.0	402.4
177.5°	405.3	405.6	405.6	405.2	404.7	404.4	403.9
180°	405.0	405.0	405.0	405.0	405.0	405.0	405.0

(END OF REPORT)