

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333157

Luminaire Tested: **S125DIP-S375D1205U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333157  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D1205U835-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6337.8 lumens  
Efficiency: N/A  
Efficacy: 150.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333157

CATALOG NUMBER: S125DIP-S375D1205U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333157

CATALOG NUMBER: S125DIP-S375D1205U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27	20
2	84	77	71	66	74	68	63	59	53	49	46	38	36	34	25	24	23	17
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	21	19	14
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	39	56	47	40	36	37	32	28	27	24	21	18	16	14	11
6	59	47	39	34	52	42	35	31	33	28	25	24	21	19	16	14	13	9
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	20	38	29	23	18	23	18	15	17	14	12	11	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3773	3773	3773
5°	3781	3745	3769
10°	3758	3719	3740
15°	3718	3674	3689
20°	3659	3612	3618
25°	3596	3537	3534
30°	3519	3457	3439
35°	3436	3370	3323
40°	3351	3277	3230
45°	3259	3191	3128
50°	3158	3088	2995
55°	3059	2971	2888
60°	2942	2853	2753
65°	2804	2713	2621
70°	2670	2549	2460
75°	2433	2353	2271
80°	2165	2131	2079
85°	1882	1919	1815



TEST NUMBER: P333157

CATALOG NUMBER: S125DIP-S375D1205U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.1	0.9
10°-20°	155.6	2.5
20°-30°	229.7	3.6
30°-40°	268.1	4.2
40°-50°	269.2	4.2
50°-60°	236.3	3.7
60°-70°	176.1	2.8
70°-80°	100.7	1.6
80°-90°	32.6	0.5
90°-100°	57.0	0.9
100°-110°	351.1	5.5
110°-120°	636.8	10.0
120°-130°	817.3	12.9
130°-140°	879.1	13.9
140°-150°	825.1	13.0
150°-160°	667.5	10.5
160°-170°	431.7	6.8
170°-180°	148.9	2.3
0°-30°	440.4	6.9
0°-40°	708.5	11.2
0°-60°	1214.0	19.2
0°-90°	1523.4	24.0
90°-120°	1044.9	16.5
90°-150°	3566.4	56.3
90°-180°	4814.0	76.0
0°-180°	6337.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	584	584	584	584	584	
5°	583	582	578	582	581	55
15°	556	554	550	552	552	157
25°	505	502	496	497	496	232
35°	436	434	428	425	422	272
45°	357	355	349	344	342	275
55°	272	270	264	260	256	243
65°	184	182	178	173	172	182
75°	98	96	94	93	91	104
85°	25	26	26	25	24	28
90°	1	10	19	24	28	4
95°	66	60	19	24	24	84
105°	342	346	346	346	345	362
115°	642	647	648	644	637	636
125°	912	920	920	916	912	815
135°	1138	1144	1142	1140	1133	877
145°	1319	1321	1321	1322	1316	825
155°	1453	1446	1448	1451	1442	669
165°	1533	1526	1527	1533	1525	433
175°	1568	1561	1562	1570	1561	149
180°	1568	1568	1568	1568	1568	



TEST NUMBER: P333157

CATALOG NUMBER: S125DIP-S375D1205U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2
2.5°	585.6	585.4	585.2	584.9	584.7	584.1	583.3	582.5	581.7	580.8	581.7
5°	583.2	583.0	582.8	582.6	582.4	581.8	580.8	579.8	578.7	577.7	578.6
7.5°	577.9	577.7	577.5	577.3	577.1	576.4	575.3	574.1	573.0	571.9	572.8
10°	573.1	572.9	572.7	572.5	572.3	571.6	570.5	569.3	568.2	567.1	567.9
12.5°	567.2	566.8	566.4	566.1	565.7	565.0	563.9	562.9	561.8	560.8	561.4
15°	556.0	555.7	555.4	555.1	554.7	554.0	552.9	551.8	550.6	549.5	550.0
17.5°	543.1	542.7	542.2	541.8	541.3	540.5	539.3	538.2	537.0	535.8	536.5
20°	532.4	532.2	532.0	531.8	531.6	530.8	529.5	528.1	526.8	525.5	526.2
22.5°	521.7	521.3	520.9	520.6	520.2	519.4	518.1	516.9	515.6	514.4	514.9
25°	504.7	504.2	503.6	503.1	502.6	501.7	500.4	499.0	497.7	496.4	496.6
27.5°	484.8	484.5	484.2	483.9	483.6	482.7	481.4	480.0	478.6	477.2	477.3
30°	471.9	471.6	471.2	470.9	470.6	469.7	468.2	466.6	465.1	463.5	463.3
32.5°	457.8	457.3	456.9	456.4	455.9	455.0	453.6	452.2	450.9	449.5	449.1
35°	435.8	435.4	435.0	434.6	434.2	433.2	431.8	430.4	428.9	427.5	427.0
37.5°	413.0	412.5	412.0	411.4	410.9	410.0	408.6	407.3	405.9	404.6	403.8
40°	397.5	396.9	396.4	395.9	395.4	394.4	393.0	391.6	390.1	388.7	387.8
42.5°	380.8	380.4	380.0	379.5	379.1	378.2	376.7	375.3	373.8	372.4	371.6
45°	356.8	356.4	356.0	355.6	355.1	354.3	353.1	351.9	350.6	349.4	348.2
47.5°	330.9	330.9	330.9	331.0	331.0	330.3	328.8	327.3	325.8	324.3	323.1
50°	314.3	314.0	313.7	313.3	313.0	312.3	311.0	309.8	308.6	307.3	306.0
52.5°	297.3	297.0	296.8	296.6	296.4	295.6	294.3	293.0	291.6	290.3	289.2
55°	271.7	271.4	271.1	270.8	270.5	269.6	268.2	266.8	265.3	263.9	263.0
57.5°	244.9	244.7	244.5	244.4	244.2	243.5	242.3	241.1	239.9	238.7	237.5
60°	227.8	227.4	227.0	226.6	226.2	225.4	224.3	223.2	222.0	220.9	219.9
62.5°	210.1	209.8	209.4	209.1	208.8	208.1	207.2	206.2	205.2	204.3	203.2
65°	183.5	183.3	183.1	182.9	182.7	182.0	180.9	179.7	178.6	177.5	176.5
67.5°	157.7	157.3	156.8	156.4	156.0	155.3	154.5	153.6	152.8	152.0	151.2
70°	141.4	140.9	140.4	139.9	139.4	138.6	137.7	136.8	135.9	135.0	134.3
72.5°	123.7	123.3	123.0	122.6	122.3	121.8	121.2	120.6	120.0	119.4	118.7
75°	97.5	97.3	97.1	96.9	96.7	96.3	95.8	95.3	94.8	94.3	94.0
77.5°	73.4	73.3	73.2	73.1	73.1	72.9	72.6	72.3	72.0	71.7	71.5
80°	58.2	58.2	58.2	58.2	58.2	58.1	57.9	57.7	57.5	57.3	57.2
82.5°	44.9	44.8	44.6	44.4	44.3	44.2	44.1	44.1	44.0	44.0	43.8
85°	25.4	25.5	25.6	25.7	25.8	25.9	25.9	25.9	25.9	25.9	25.8
87.5°	10.2	10.6	11.0	11.5	11.9	12.2	12.5	12.8	13.1	13.3	13.6
90°	1.2	3.2	5.3	7.4	9.4	11.4	13.2	15.0	16.8	18.6	19.9
92.5°	17.9	16.5	15.0	13.6	12.1	12.2	13.8	15.4	17.0	18.6	19.9
95°	66.2	65.5	64.7	63.9	63.1	57.9	48.0	38.2	28.4	18.6	19.9
97.5°	138.3	139.7	141.1	142.5	143.9	134.9	115.4	96.0	76.6	57.2	49.9
100°	194.1	194.9	195.6	196.4	197.2	198.1	199.1	200.2	201.2	202.2	163.7
102.5°	250.8	251.8	252.8	253.7	254.7	255.5	256.1	256.8	257.4	258.0	250.7
105°	341.7	342.7	343.7	344.8	345.8	346.3	346.3	346.3	346.3	346.3	346.3
107.5°	436.1	436.1	436.1	436.1	436.1	436.3	436.8	437.3	437.9	438.4	438.4
110°	497.4	497.4	497.4	497.4	497.4	497.7	498.2	498.7	499.2	499.7	499.0



TEST NUMBER: P333157

CATALOG NUMBER: S125DIP-S375D1205U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	555.1	555.7	556.3	556.9	557.5	558.0	558.3	558.6	558.9	559.2	558.3
115°	641.5	642.8	644.1	645.4	646.7	647.5	647.7	648.0	648.2	648.5	647.5
117.5°	731.0	731.0	730.9	730.9	730.8	731.3	732.3	733.2	734.2	735.2	733.9
120°	786.8	786.5	786.3	786.0	785.8	786.0	786.8	787.6	788.3	789.1	788.6
122.5°	836.1	837.1	838.0	839.0	840.0	840.7	841.0	841.4	841.8	842.1	841.6
125°	912.3	914.1	915.9	917.7	919.5	920.4	920.4	920.4	920.4	920.4	919.4
127.5°	985.1	986.4	987.6	988.9	990.2	990.8	990.6	990.5	990.3	990.2	989.6
130°	1029.7	1031.0	1032.3	1033.6	1034.9	1035.6	1035.9	1036.2	1036.4	1036.7	1035.9
132.5°	1074.3	1075.8	1077.3	1078.8	1080.3	1080.8	1080.2	1079.6	1079.1	1078.5	1078.4
135°	1137.8	1139.3	1140.9	1142.4	1144.0	1144.5	1144.0	1143.5	1142.9	1142.4	1141.9
137.5°	1196.1	1197.5	1198.8	1200.1	1201.5	1201.9	1201.5	1201.0	1200.5	1200.1	1200.2
140°	1234.2	1234.8	1235.3	1235.8	1236.3	1236.4	1236.2	1235.9	1235.7	1235.4	1235.9
142.5°	1268.6	1268.9	1269.3	1269.6	1269.9	1270.2	1270.6	1270.9	1271.3	1271.7	1271.8
145°	1319.1	1319.6	1320.1	1320.6	1321.1	1321.4	1321.4	1321.4	1321.4	1321.4	1321.7
147.5°	1363.2	1363.1	1363.0	1362.9	1362.8	1362.9	1363.2	1363.5	1363.9	1364.2	1364.5
150°	1391.1	1390.6	1390.1	1389.6	1389.1	1389.1	1389.6	1390.1	1390.6	1391.1	1391.6
152.5°	1418.1	1417.0	1415.8	1414.7	1413.5	1413.2	1413.8	1414.3	1414.8	1415.3	1415.8
155°	1452.7	1451.2	1449.6	1448.1	1446.5	1446.0	1446.5	1447.0	1447.6	1448.1	1448.9
157.5°	1479.5	1478.5	1477.6	1476.7	1475.7	1475.3	1475.4	1475.4	1475.5	1475.5	1476.3
160°	1498.1	1496.5	1495.0	1493.4	1491.9	1491.2	1491.5	1491.7	1492.0	1492.2	1493.3
162.5°	1512.9	1511.4	1509.8	1508.3	1506.7	1506.1	1506.3	1506.6	1506.9	1507.1	1508.6
165°	1532.9	1531.4	1529.8	1528.3	1526.7	1526.1	1526.3	1526.6	1526.8	1527.1	1528.7
167.5°	1547.8	1546.2	1544.6	1543.0	1541.4	1540.7	1541.0	1541.2	1541.5	1541.8	1543.6
170°	1556.2	1554.4	1552.5	1550.7	1548.9	1548.2	1548.4	1548.7	1548.9	1549.2	1551.3
172.5°	1561.7	1559.9	1558.1	1556.3	1554.5	1553.8	1554.3	1554.8	1555.2	1555.7	1557.6
175°	1567.8	1566.2	1564.7	1563.1	1561.6	1560.9	1561.2	1561.5	1561.7	1562.0	1564.0
177.5°	1570.6	1569.3	1568.1	1566.9	1565.6	1565.1	1565.3	1565.5	1565.7	1565.9	1567.4
180°	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8



TEST NUMBER: P333157

CATALOG NUMBER: S125DIP-S375D1205U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2
2.5°	582.5	583.3	584.1	584.5	584.4	584.3	584.3	584.2
5°	579.5	580.5	581.4	581.8	581.7	581.6	581.5	581.4
7.5°	573.7	574.6	575.5	575.9	575.8	575.7	575.6	575.5
10°	568.7	569.5	570.4	570.7	570.6	570.5	570.4	570.3
12.5°	562.1	562.8	563.4	563.7	563.7	563.7	563.7	563.6
15°	550.5	551.0	551.6	551.8	551.8	551.8	551.8	551.8
17.5°	537.1	537.7	538.4	538.4	537.9	537.4	536.9	536.4
20°	526.9	527.6	528.3	528.5	527.9	527.4	526.9	526.4
22.5°	515.3	515.8	516.3	516.3	516.0	515.6	515.3	514.9
25°	496.8	497.0	497.2	497.1	496.8	496.5	496.2	495.9
27.5°	477.3	477.3	477.4	477.3	476.9	476.6	476.3	476.0
30°	463.1	462.9	462.7	462.5	462.2	461.9	461.5	461.2
32.5°	448.8	448.4	448.0	447.6	447.0	446.4	445.9	445.3
35°	426.5	426.0	425.4	424.8	424.0	423.1	422.3	421.5
37.5°	403.1	402.3	401.5	400.9	400.4	400.0	399.5	399.0
40°	386.8	385.9	385.0	384.4	384.1	383.7	383.4	383.1
42.5°	370.7	369.9	369.0	368.4	367.9	367.4	367.0	366.5
45°	346.9	345.7	344.5	343.7	343.4	343.1	342.8	342.5
47.5°	321.8	320.6	319.3	318.3	317.6	316.9	316.2	315.5
50°	304.7	303.3	302.0	301.0	300.2	299.5	298.8	298.1
52.5°	288.0	286.8	285.6	284.7	283.9	283.1	282.3	281.5
55°	262.0	261.1	260.2	259.4	258.7	257.9	257.2	256.5
57.5°	236.3	235.1	233.9	233.1	232.7	232.3	231.9	231.5
60°	218.9	217.8	216.8	215.9	215.2	214.5	213.8	213.1
62.5°	202.1	200.9	199.8	199.0	198.5	197.9	197.3	196.8
65°	175.6	174.7	173.8	173.1	172.7	172.3	171.9	171.5
67.5°	150.4	149.6	148.8	148.3	148.1	147.8	147.6	147.3
70°	133.7	133.1	132.5	132.0	131.6	131.2	130.7	130.3
72.5°	118.0	117.3	116.6	116.1	115.7	115.3	114.8	114.4
75°	93.7	93.4	93.0	92.7	92.3	91.9	91.5	91.0
77.5°	71.4	71.2	71.0	70.8	70.5	70.2	69.9	69.6
80°	57.1	57.0	56.9	56.7	56.5	56.3	56.1	55.9
82.5°	43.6	43.4	43.3	43.1	43.1	43.1	43.0	43.0
85°	25.7	25.6	25.5	25.3	25.1	24.9	24.7	24.5
87.5°	13.8	14.1	14.4	14.5	14.5	14.5	14.5	14.5
90°	21.2	22.5	23.8	24.8	25.6	26.3	27.1	27.9
92.5°	21.2	22.5	23.8	24.6	24.9	25.3	25.7	26.0
95°	21.2	22.5	23.8	24.4	24.4	24.4	24.4	24.4
97.5°	42.6	35.3	28.0	24.4	24.4	24.4	24.4	24.4
100°	125.3	86.8	48.3	28.5	27.5	26.5	25.4	24.4
102.5°	243.4	236.2	228.9	216.5	198.9	181.3	163.8	146.2
105°	346.3	346.3	346.3	346.2	345.9	345.7	345.4	345.2
107.5°	438.5	438.5	438.6	438.2	437.4	436.7	435.9	435.1
110°	498.2	497.4	496.6	496.4	496.6	496.9	497.2	497.4





TEST NUMBER: P333157

CATALOG NUMBER: S125DIP-S375D1205U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	557.3	556.3	555.3	554.6	554.3	553.9	553.6	553.2
115°	646.4	645.4	644.4	643.1	641.5	640.0	638.4	636.9
117.5°	732.5	731.2	729.8	728.8	728.1	727.5	726.8	726.1
120°	788.1	787.6	787.1	786.2	784.9	783.6	782.3	781.0
122.5°	841.1	840.6	840.1	839.0	837.5	836.0	834.6	833.1
125°	918.4	917.3	916.3	915.4	914.6	913.9	913.1	912.3
127.5°	989.0	988.5	987.9	986.7	984.8	982.8	980.9	979.0
130°	1035.1	1034.3	1033.6	1032.5	1031.2	1030.0	1028.7	1027.4
132.5°	1078.2	1078.0	1077.9	1077.2	1075.9	1074.6	1073.3	1072.0
135°	1141.4	1140.9	1140.4	1139.3	1137.8	1136.2	1134.7	1133.1
137.5°	1200.3	1200.4	1200.5	1199.9	1198.5	1197.2	1195.8	1194.5
140°	1236.4	1236.9	1237.5	1236.9	1235.4	1233.9	1232.3	1230.8
142.5°	1271.9	1272.0	1272.1	1271.4	1269.8	1268.3	1266.7	1265.2
145°	1321.9	1322.2	1322.4	1321.8	1320.2	1318.7	1317.1	1315.6
147.5°	1364.8	1365.1	1365.4	1364.6	1362.8	1360.9	1359.1	1357.2
150°	1392.2	1392.7	1393.2	1392.4	1390.4	1388.3	1386.2	1384.2
152.5°	1416.3	1416.9	1417.4	1416.7	1414.8	1413.0	1411.1	1409.3
155°	1449.6	1450.4	1451.2	1450.5	1448.5	1446.4	1444.3	1442.3
157.5°	1477.2	1478.0	1478.8	1478.2	1476.1	1474.1	1472.0	1469.9
160°	1494.3	1495.3	1496.4	1495.9	1493.8	1491.7	1489.7	1487.6
162.5°	1510.0	1511.5	1512.9	1512.5	1510.2	1507.9	1505.7	1503.4
165°	1530.2	1531.8	1533.3	1533.0	1531.0	1528.9	1526.8	1524.8
167.5°	1545.5	1547.3	1549.2	1549.0	1546.6	1544.3	1542.0	1539.7
170°	1553.3	1555.4	1557.5	1557.3	1555.0	1552.7	1550.4	1548.0
172.5°	1559.4	1561.3	1563.1	1562.9	1560.6	1558.3	1555.9	1553.6
175°	1566.1	1568.2	1570.2	1570.1	1567.8	1565.5	1563.1	1560.8
177.5°	1568.8	1570.3	1571.7	1571.6	1570.0	1568.3	1566.6	1565.0
180°	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8

(END OF REPORT)