

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333123-940

Luminaire Tested: **S125DIP-S375D365U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333123-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D365U940-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2528.6 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333123-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333123-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38
3	82	72	65	59	76	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	44	39	36	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	32	54	43	36	31	38	32	27	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	17
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3364	3364	3364
5°	3371	3339	3361
10°	3351	3316	3335
15°	3315	3276	3290
20°	3263	3221	3226
25°	3207	3154	3151
30°	3138	3082	3067
35°	3064	3005	2964
40°	2989	2922	2880
45°	2906	2846	2789
50°	2816	2753	2671
55°	2728	2649	2575
60°	2623	2545	2454
65°	2500	2419	2337
70°	2381	2274	2194
75°	2168	2099	2024
80°	1930	1901	1852
85°	1675	1712	1615



TEST NUMBER: P333123-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.1	1.9
10°-20°	138.7	5.5
20°-30°	204.9	8.1
30°-40°	239.0	9.5
40°-50°	240.1	9.5
50°-60°	210.7	8.3
60°-70°	157.0	6.2
70°-80°	89.8	3.6
80°-90°	27.0	1.1
90°-100°	113.3	4.5
100°-110°	243.6	9.6
110°-120°	228.6	9.0
120°-130°	185.2	7.3
130°-140°	148.7	5.9
140°-150°	112.2	4.4
150°-160°	79.0	3.1
160°-170°	46.5	1.8
170°-180°	15.1	0.6
0°-30°	392.7	15.5
0°-40°	631.7	25.0
0°-60°	1082.6	42.8
0°-90°	1356.4	53.6
90°-120°	585.4	23.2
90°-150°	1031.5	40.8
90°-180°	1172.0	46.4
0°-180°	2528.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	521	521	521	521	521	
5°	520	519	515	519	518	49
15°	496	494	490	492	492	140
25°	450	448	443	443	442	207
35°	389	387	381	379	376	243
45°	318	316	312	307	305	245
55°	242	241	235	232	229	216
65°	164	163	158	155	153	162
75°	87	86	84	83	81	93
85°	23	23	23	23	22	25
90°	0	3	5	7	7	2
95°	10	31	279	127	74	11
105°	36	50	228	450	418	38
115°	64	77	183	395	465	63
125°	88	103	176	314	366	78
135°	103	124	175	264	304	80
145°	120	138	175	218	240	75
155°	137	148	171	193	201	63
165°	150	154	164	174	176	42
175°	156	156	157	159	158	15
180°	156	156	156	156	156	



TEST NUMBER: P333123-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	522.2	522.0	521.8	521.6	521.4	520.8	520.1	519.4	518.7	517.9	518.7
5°	520.0	519.9	519.7	519.5	519.3	518.8	517.9	517.0	516.0	515.1	515.9
7.5°	515.3	515.1	515.0	514.8	514.6	514.0	513.0	511.9	511.0	510.0	510.8
10°	511.0	510.9	510.7	510.5	510.3	509.7	508.7	507.7	506.7	505.7	506.4
12.5°	505.8	505.4	505.1	504.8	504.4	503.8	502.8	501.9	501.0	500.1	500.6
15°	495.8	495.5	495.3	495.0	494.6	494.0	493.0	492.0	491.0	490.0	490.4
17.5°	484.3	483.9	483.5	483.1	482.7	482.0	480.9	479.9	478.8	477.8	478.4
20°	474.7	474.6	474.4	474.2	474.0	473.3	472.2	470.9	469.8	468.6	469.2
22.5°	465.2	464.8	464.5	464.2	463.9	463.2	462.0	460.9	459.8	458.7	459.1
25°	450.0	449.6	449.1	448.6	448.2	447.4	446.2	445.0	443.8	442.6	442.8
27.5°	432.3	432.0	431.8	431.5	431.2	430.4	429.3	428.0	426.8	425.5	425.6
30°	420.8	420.5	420.2	419.9	419.6	418.8	417.5	416.1	414.7	413.3	413.1
32.5°	408.2	407.8	407.4	407.0	406.5	405.7	404.5	403.2	402.1	400.8	400.5
35°	388.6	388.3	387.9	387.5	387.2	386.3	385.0	383.8	382.5	381.2	380.8
37.5°	368.3	367.8	367.4	366.8	366.4	365.6	364.4	363.2	361.9	360.8	360.1
40°	354.5	353.9	353.5	353.0	352.6	351.7	350.4	349.2	347.9	346.6	345.8
42.5°	339.6	339.2	338.9	338.4	338.0	337.2	335.9	334.7	333.3	332.1	331.4
45°	318.2	317.8	317.4	317.1	316.6	315.9	314.9	313.8	312.6	311.6	310.5
47.5°	295.1	295.1	295.1	295.2	295.2	294.5	293.2	291.9	290.5	289.2	288.1
50°	280.3	280.0	279.7	279.4	279.1	278.5	277.3	276.3	275.2	274.0	272.9
52.5°	265.1	264.8	264.7	264.5	264.3	263.6	262.4	261.3	260.0	258.9	257.9
55°	242.3	242.0	241.7	241.5	241.2	240.4	239.2	237.9	236.6	235.3	234.5
57.5°	218.4	218.2	218.0	217.9	217.8	217.1	216.1	215.0	213.9	212.9	211.8
60°	203.1	202.8	202.4	202.1	201.7	201.0	200.0	199.0	198.0	197.0	196.1
62.5°	187.3	187.1	186.7	186.5	186.2	185.6	184.8	183.9	183.0	182.2	181.2
65°	163.6	163.5	163.3	163.1	162.9	162.3	161.3	160.2	159.3	158.3	157.4
67.5°	140.6	140.3	139.8	139.5	139.1	138.5	137.8	137.0	136.3	135.5	134.8
70°	126.1	125.6	125.2	124.8	124.3	123.6	122.8	122.0	121.2	120.4	119.8
72.5°	110.3	109.9	109.7	109.3	109.1	108.6	108.1	107.5	107.0	106.5	105.8
75°	86.9	86.8	86.6	86.4	86.2	85.9	85.4	85.0	84.5	84.1	83.8
77.5°	65.5	65.4	65.3	65.2	65.2	65.0	64.7	64.5	64.2	63.9	63.8
80°	51.9	51.9	51.9	51.9	51.9	51.8	51.6	51.5	51.3	51.1	51.0
82.5°	40.0	39.9	39.8	39.6	39.5	39.4	39.3	39.3	39.2	39.2	39.1
85°	22.6	22.7	22.8	22.9	23.0	23.1	23.1	23.1	23.1	23.1	23.0
87.5°	9.0	9.0	9.2	9.3	9.4	9.5	9.5	9.5	9.5	9.5	9.6
90°	0.4	0.6	1.2	1.9	2.5	3.1	3.5	4.1	4.4	5.1	5.4
92.5°	3.8	4.6	7.3	11.2	16.7	25.9	43.1	71.9	103.3	101.6	82.2
95°	10.4	10.7	13.2	16.7	23.6	37.8	71.5	140.9	227.8	279.2	273.2
97.5°	17.3	17.7	19.4	22.9	29.2	39.3	61.6	112.4	203.5	298.2	345.7
100°	22.0	22.6	24.0	27.4	33.4	42.9	61.2	102.1	181.6	284.5	363.4
102.5°	27.4	27.7	28.7	32.5	38.0	47.2	63.4	97.8	164.9	260.6	352.8
105°	35.6	35.6	37.2	40.3	45.4	54.2	68.0	96.1	148.7	228.5	319.0
107.5°	43.7	44.3	45.8	48.4	53.7	61.6	75.0	99.0	142.0	206.3	284.4
110°	49.5	50.1	51.4	54.2	58.9	67.1	80.1	101.8	139.9	196.0	264.7



TEST NUMBER: P333123-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	55.3	55.9	56.9	59.7	64.5	72.4	84.8	105.3	139.9	189.9	250.1
115°	63.7	64.3	65.3	68.0	72.8	80.7	92.4	110.6	140.9	183.4	234.2
117.5°	71.2	72.1	73.2	76.0	81.4	89.0	100.0	116.6	142.9	180.2	224.6
120°	76.2	77.2	78.5	81.3	86.7	94.5	105.6	120.7	145.0	178.7	219.4
122.5°	81.6	82.2	83.3	86.1	91.9	99.9	110.8	125.2	146.7	177.5	214.8
125°	88.3	88.9	90.4	93.3	99.2	107.5	117.9	131.4	149.7	175.8	208.7
127.5°	93.5	94.4	96.4	100.0	106.4	114.6	124.6	137.1	153.0	175.1	203.0
130°	96.8	97.7	100.2	104.3	110.9	119.1	128.9	140.9	155.1	174.6	199.2
132.5°	99.2	100.5	103.5	108.1	114.9	123.1	133.0	144.2	157.3	174.6	196.2
135°	103.3	104.6	108.4	113.4	120.1	128.6	138.3	148.7	160.4	174.6	192.5
137.5°	108.5	109.5	113.0	118.1	124.6	133.3	142.2	152.1	163.3	175.0	189.3
140°	111.6	112.5	116.3	121.4	127.3	135.8	145.0	154.4	164.5	175.2	187.8
142.5°	115.1	115.7	119.3	124.4	130.1	138.1	146.7	155.7	165.2	175.5	186.5
145°	120.4	121.0	124.1	128.6	134.3	141.5	149.7	157.6	166.0	175.2	184.7
147.5°	125.9	126.3	129.0	133.1	138.0	144.4	151.6	158.7	166.4	174.4	182.7
150°	129.2	129.8	132.1	136.2	140.5	145.9	152.8	159.4	166.4	173.6	181.2
152.5°	132.8	133.1	135.1	138.7	142.9	147.7	154.1	160.0	166.1	172.6	179.4
155°	137.4	137.4	139.3	142.4	145.6	150.0	155.3	160.4	165.4	170.9	176.5
157.5°	141.6	141.5	143.0	145.7	148.5	151.9	156.4	160.7	164.6	168.9	173.7
160°	144.4	144.0	145.3	147.5	150.0	152.8	156.9	160.7	163.9	167.6	171.5
162.5°	146.6	146.3	147.6	149.5	151.5	153.8	157.5	160.5	163.1	166.1	169.4
165°	150.0	149.4	150.3	151.9	153.2	155.1	157.6	160.1	162.0	163.9	166.4
167.5°	152.3	151.9	152.6	153.4	154.3	155.5	157.6	159.3	160.2	161.7	163.5
170°	153.8	153.5	153.8	154.4	155.1	156.0	157.6	158.8	159.4	160.4	161.7
172.5°	154.8	154.3	154.5	155.2	155.5	156.0	157.3	158.4	158.5	158.9	159.9
175°	156.0	155.3	155.7	156.0	156.0	156.0	156.9	157.6	157.3	157.3	157.6
177.5°	156.6	156.0	156.0	156.3	156.0	156.0	156.6	156.9	156.3	156.3	156.6
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333123-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	519.4	520.1	520.8	521.2	521.1	521.0	521.0	520.9
5°	516.7	517.6	518.4	518.8	518.7	518.6	518.5	518.4
7.5°	511.6	512.4	513.2	513.5	513.4	513.4	513.3	513.2
10°	507.1	507.8	508.6	508.9	508.8	508.7	508.6	508.5
12.5°	501.2	501.9	502.4	502.7	502.7	502.7	502.7	502.6
15°	490.9	491.3	491.9	492.0	492.0	492.0	492.0	492.0
17.5°	478.9	479.5	480.1	480.1	479.7	479.2	478.8	478.3
20°	469.8	470.5	471.1	471.3	470.7	470.3	469.8	469.4
22.5°	459.5	459.9	460.4	460.4	460.1	459.8	459.5	459.1
25°	443.0	443.2	443.4	443.3	443.0	442.7	442.5	442.2
27.5°	425.6	425.6	425.7	425.6	425.3	425.0	424.7	424.5
30°	413.0	412.8	412.6	412.4	412.1	411.9	411.5	411.3
32.5°	400.2	399.8	399.5	399.1	398.6	398.1	397.6	397.1
35°	380.3	379.9	379.3	378.8	378.1	377.3	376.6	375.9
37.5°	359.4	358.7	358.0	357.5	357.0	356.7	356.2	355.8
40°	344.9	344.1	343.3	342.8	342.5	342.1	341.9	341.6
42.5°	330.6	329.8	329.0	328.5	328.1	327.6	327.3	326.8
45°	309.3	308.3	307.2	306.5	306.2	305.9	305.7	305.4
47.5°	287.0	285.9	284.7	283.8	283.2	282.6	282.0	281.3
50°	271.7	270.5	269.3	268.4	267.7	267.1	266.4	265.8
52.5°	256.8	255.7	254.7	253.9	253.2	252.4	251.7	251.0
55°	233.6	232.8	232.0	231.3	230.7	230.0	229.3	228.7
57.5°	210.7	209.6	208.6	207.9	207.5	207.1	206.8	206.4
60°	195.2	194.2	193.3	192.5	191.9	191.3	190.6	190.0
62.5°	180.2	179.1	178.2	177.5	177.0	176.5	175.9	175.5
65°	156.6	155.8	155.0	154.4	154.0	153.6	153.3	152.9
67.5°	134.1	133.4	132.7	132.2	132.1	131.8	131.6	131.3
70°	119.2	118.7	118.2	117.7	117.3	117.0	116.5	116.2
72.5°	105.2	104.6	104.0	103.5	103.2	102.8	102.4	102.0
75°	83.6	83.3	82.9	82.7	82.3	81.9	81.6	81.1
77.5°	63.7	63.5	63.3	63.1	62.9	62.6	62.3	62.1
80°	50.9	50.8	50.7	50.6	50.4	50.2	50.0	49.8
82.5°	38.9	38.7	38.6	38.4	38.4	38.4	38.3	38.3
85°	22.9	22.8	22.7	22.6	22.4	22.2	22.0	21.8
87.5°	9.7	9.8	9.8	9.9	9.7	9.6	9.5	9.4
90°	5.7	6.0	6.3	7.0	7.0	7.0	7.2	7.2
92.5°	55.8	40.5	30.5	25.9	21.8	21.0	20.6	20.1
95°	226.6	178.7	139.9	113.4	91.0	81.6	79.1	74.1
97.5°	337.4	303.9	266.1	229.3	209.8	192.2	183.1	179.0
100°	387.6	372.2	339.7	306.9	285.2	262.5	250.8	245.8
102.5°	404.5	414.0	398.5	376.3	353.0	336.9	324.2	320.5
105°	394.6	437.7	451.6	448.2	438.0	427.7	421.3	417.6
107.5°	359.0	416.6	452.2	468.7	473.8	473.8	471.6	469.1
110°	332.8	392.7	437.1	463.9	478.0	484.0	486.2	486.2



TEST NUMBER: P333123-940

CATALOG NUMBER: S125DIP-S375D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	312.1	369.0	413.9	445.5	466.2	476.5	482.0	484.3
115°	286.1	335.0	378.2	412.5	437.1	452.2	461.0	465.1
117.5°	269.4	311.5	348.7	380.2	404.7	420.4	429.2	431.7
120°	260.3	298.1	332.8	360.5	383.9	399.0	407.5	410.0
122.5°	253.5	288.6	319.4	345.4	366.2	380.0	388.6	390.8
125°	243.6	275.7	303.2	325.8	343.5	356.4	363.4	366.5
127.5°	233.5	263.5	289.1	310.3	326.4	337.8	344.3	345.7
130°	227.2	254.9	279.6	300.1	315.8	326.2	332.5	334.4
132.5°	220.9	246.9	269.2	288.9	304.7	315.0	320.8	323.0
135°	212.8	234.4	254.7	272.6	286.5	296.9	302.6	304.4
137.5°	205.8	223.4	240.1	255.4	267.8	277.2	282.5	284.5
140°	202.0	216.8	231.3	244.5	256.2	264.4	269.1	270.7
142.5°	198.8	211.2	223.7	235.2	245.1	252.1	256.5	257.9
145°	194.5	204.2	214.0	222.5	230.1	235.4	238.9	240.1
147.5°	190.4	198.3	205.9	212.3	218.3	222.6	224.5	225.2
150°	188.2	195.1	201.1	206.7	211.4	215.3	216.5	216.8
152.5°	185.7	191.8	197.2	201.7	205.6	208.7	209.9	210.3
155°	181.8	186.9	191.3	194.7	197.9	200.1	201.1	201.3
157.5°	178.1	182.2	185.7	188.3	190.8	192.6	193.5	193.4
160°	175.6	178.7	181.8	184.0	186.3	187.8	188.4	188.2
162.5°	172.7	175.7	178.3	180.3	182.0	183.2	183.4	183.3
165°	168.9	171.1	173.0	174.6	175.8	176.5	176.5	176.5
167.5°	165.2	166.7	168.2	169.3	170.0	170.5	170.2	170.1
170°	163.3	164.2	165.1	165.8	166.4	166.7	166.7	166.4
172.5°	161.0	161.9	162.6	163.0	163.1	163.7	163.2	162.8
175°	158.5	158.5	159.2	159.2	159.2	159.4	158.8	158.5
177.5°	156.9	157.0	157.0	157.0	156.9	157.0	156.3	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3

(END OF REPORT)