

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333123

Luminaire Tested: **S125DIP-S375D365U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333123  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D365U835-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2835.6 lumens  
Efficiency: N/A  
Efficacy: 139.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333123

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333123

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54				
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45				
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38				
3	82	72	65	59	76	67	61	55	58	53	49	49	45	42	41	38	36	32				
4	75	64	56	50	69	60	52	47	51	46	41	44	39	36	36	33	31	27				
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24				
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21				
7	59	46	38	32	54	43	36	31	38	32	27	32	28	24	27	24	21	18				
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	17				
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15				
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	14				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3773	3773	3773
5°	3781	3745	3769
10°	3758	3719	3740
15°	3718	3674	3689
20°	3659	3612	3618
25°	3596	3537	3534
30°	3519	3457	3439
35°	3436	3370	3323
40°	3351	3277	3230
45°	3259	3191	3128
50°	3158	3088	2995
55°	3059	2971	2888
60°	2942	2853	2753
65°	2804	2713	2621
70°	2670	2549	2460
75°	2433	2353	2271
80°	2165	2131	2079
85°	1882	1919	1815



TEST NUMBER: P333123

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.1	1.9
10°-20°	155.6	5.5
20°-30°	229.7	8.1
30°-40°	268.1	9.5
40°-50°	269.2	9.5
50°-60°	236.3	8.3
60°-70°	176.1	6.2
70°-80°	100.7	3.6
80°-90°	30.3	1.1
90°-100°	127.1	4.5
100°-110°	273.1	9.6
110°-120°	256.3	9.0
120°-130°	207.7	7.3
130°-140°	166.7	5.9
140°-150°	125.8	4.4
150°-160°	88.6	3.1
160°-170°	52.2	1.8
170°-180°	17.0	0.6
0°-30°	440.4	15.5
0°-40°	708.5	25.0
0°-60°	1214.0	42.8
0°-90°	1521.1	53.6
90°-120°	656.5	23.2
90°-150°	1156.8	40.8
90°-180°	1315.0	46.4
0°-180°	2835.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	584	584	584	584	584	
5°	583	582	578	582	581	55
15°	556	554	550	552	552	157
25°	505	502	496	497	496	232
35°	436	434	428	425	422	272
45°	357	355	349	344	342	275
55°	272	270	264	260	256	243
65°	184	182	178	173	172	182
75°	98	96	94	93	91	104
85°	25	26	26	25	24	28
90°	0	3	6	7	8	2
95°	12	34	313	142	83	12
105°	40	56	256	504	468	42
115°	71	86	206	443	522	70
125°	99	116	197	353	411	88
135°	116	139	196	296	341	90
145°	135	155	196	245	269	85
155°	154	166	192	216	226	71
165°	168	173	184	195	198	47
175°	175	175	176	178	178	17
180°	175	175	175	175	175	



TEST NUMBER: P333123

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2
2.5°	585.6	585.4	585.2	584.9	584.7	584.1	583.3	582.5	581.7	580.8	581.7
5°	583.2	583.0	582.8	582.6	582.4	581.8	580.8	579.8	578.7	577.7	578.6
7.5°	577.9	577.7	577.5	577.3	577.1	576.4	575.3	574.1	573.0	571.9	572.8
10°	573.1	572.9	572.7	572.5	572.3	571.6	570.5	569.3	568.2	567.1	567.9
12.5°	567.2	566.8	566.4	566.1	565.7	565.0	563.9	562.9	561.8	560.8	561.4
15°	556.0	555.7	555.4	555.1	554.7	554.0	552.9	551.8	550.6	549.5	550.0
17.5°	543.1	542.7	542.2	541.8	541.3	540.5	539.3	538.2	537.0	535.8	536.5
20°	532.4	532.2	532.0	531.8	531.6	530.8	529.5	528.1	526.8	525.5	526.2
22.5°	521.7	521.3	520.9	520.6	520.2	519.4	518.1	516.9	515.6	514.4	514.9
25°	504.7	504.2	503.6	503.1	502.6	501.7	500.4	499.0	497.7	496.4	496.6
27.5°	484.8	484.5	484.2	483.9	483.6	482.7	481.4	480.0	478.6	477.2	477.3
30°	471.9	471.6	471.2	470.9	470.6	469.7	468.2	466.6	465.1	463.5	463.3
32.5°	457.8	457.3	456.9	456.4	455.9	455.0	453.6	452.2	450.9	449.5	449.1
35°	435.8	435.4	435.0	434.6	434.2	433.2	431.8	430.4	428.9	427.5	427.0
37.5°	413.0	412.5	412.0	411.4	410.9	410.0	408.6	407.3	405.9	404.6	403.8
40°	397.5	396.9	396.4	395.9	395.4	394.4	393.0	391.6	390.1	388.7	387.8
42.5°	380.8	380.4	380.0	379.5	379.1	378.2	376.7	375.3	373.8	372.4	371.6
45°	356.8	356.4	356.0	355.6	355.1	354.3	353.1	351.9	350.6	349.4	348.2
47.5°	330.9	330.9	330.9	331.0	331.0	330.3	328.8	327.3	325.8	324.3	323.1
50°	314.3	314.0	313.7	313.3	313.0	312.3	311.0	309.8	308.6	307.3	306.0
52.5°	297.3	297.0	296.8	296.6	296.4	295.6	294.3	293.0	291.6	290.3	289.2
55°	271.7	271.4	271.1	270.8	270.5	269.6	268.2	266.8	265.3	263.9	263.0
57.5°	244.9	244.7	244.5	244.4	244.2	243.5	242.3	241.1	239.9	238.7	237.5
60°	227.8	227.4	227.0	226.6	226.2	225.4	224.3	223.2	222.0	220.9	219.9
62.5°	210.1	209.8	209.4	209.1	208.8	208.1	207.2	206.2	205.2	204.3	203.2
65°	183.5	183.3	183.1	182.9	182.7	182.0	180.9	179.7	178.6	177.5	176.5
67.5°	157.7	157.3	156.8	156.4	156.0	155.3	154.5	153.6	152.8	152.0	151.2
70°	141.4	140.9	140.4	139.9	139.4	138.6	137.7	136.8	135.9	135.0	134.3
72.5°	123.7	123.3	123.0	122.6	122.3	121.8	121.2	120.6	120.0	119.4	118.7
75°	97.5	97.3	97.1	96.9	96.7	96.3	95.8	95.3	94.8	94.3	94.0
77.5°	73.4	73.3	73.2	73.1	73.1	72.9	72.6	72.3	72.0	71.7	71.5
80°	58.2	58.2	58.2	58.2	58.2	58.1	57.9	57.7	57.5	57.3	57.2
82.5°	44.9	44.8	44.6	44.4	44.3	44.2	44.1	44.1	44.0	44.0	43.8
85°	25.4	25.5	25.6	25.7	25.8	25.9	25.9	25.9	25.9	25.9	25.8
87.5°	10.1	10.1	10.3	10.4	10.5	10.6	10.6	10.7	10.7	10.7	10.8
90°	0.4	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.7	6.0
92.5°	4.3	5.2	8.2	12.6	18.7	29.0	48.3	80.6	115.8	113.9	92.2
95°	11.7	12.0	14.8	18.7	26.5	42.4	80.2	158.0	255.5	313.1	306.4
97.5°	19.4	19.8	21.8	25.7	32.7	44.1	69.1	126.1	228.2	334.4	387.7
100°	24.7	25.4	26.9	30.7	37.5	48.1	68.6	114.5	203.6	319.1	407.5
102.5°	30.7	31.1	32.2	36.4	42.6	52.9	71.1	109.7	184.9	292.3	395.6
105°	39.9	39.9	41.7	45.2	50.9	60.8	76.3	107.8	166.8	256.2	357.7
107.5°	49.0	49.7	51.4	54.3	60.2	69.1	84.1	111.0	159.2	231.4	318.9
110°	55.5	56.2	57.6	60.8	66.1	75.3	89.8	114.2	156.9	219.8	296.9



TEST NUMBER: P333123

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.0	62.7	63.8	67.0	72.3	81.2	95.1	118.1	156.9	213.0	280.5
115°	71.4	72.1	73.2	76.3	81.6	90.5	103.6	124.0	158.0	205.7	262.6
117.5°	79.9	80.9	82.1	85.2	91.3	99.8	112.2	130.8	160.3	202.1	251.9
120°	85.5	86.6	88.0	91.2	97.2	106.0	118.4	135.4	162.6	200.4	246.0
122.5°	91.5	92.2	93.4	96.6	103.1	112.0	124.3	140.4	164.5	199.0	240.9
125°	99.0	99.7	101.4	104.6	111.3	120.5	132.2	147.4	167.9	197.2	234.0
127.5°	104.8	105.9	108.1	112.2	119.3	128.5	139.7	153.7	171.6	196.4	227.6
130°	108.5	109.6	112.4	117.0	124.4	133.6	144.5	158.0	173.9	195.8	223.4
132.5°	111.3	112.7	116.1	121.2	128.9	138.1	149.1	161.7	176.4	195.8	220.0
135°	115.9	117.3	121.6	127.2	134.7	144.2	155.1	166.8	179.9	195.8	215.9
137.5°	121.7	122.8	126.7	132.4	139.7	149.5	159.5	170.6	183.1	196.2	212.3
140°	125.1	126.2	130.4	136.1	142.8	152.3	162.6	173.2	184.5	196.5	210.6
142.5°	129.1	129.8	133.8	139.5	145.9	154.9	164.5	174.6	185.3	196.8	209.2
145°	135.0	135.7	139.2	144.2	150.6	158.7	167.9	176.7	186.2	196.5	207.1
147.5°	141.2	141.6	144.7	149.3	154.8	161.9	170.0	178.0	186.6	195.6	204.9
150°	144.9	145.6	148.1	152.7	157.6	163.6	171.4	178.8	186.6	194.7	203.2
152.5°	148.9	149.3	151.5	155.5	160.2	165.6	172.8	179.4	186.3	193.6	201.2
155°	154.1	154.1	156.2	159.7	163.3	168.2	174.2	179.9	185.5	191.6	197.9
157.5°	158.8	158.7	160.4	163.4	166.5	170.3	175.4	180.2	184.6	189.4	194.8
160°	161.9	161.5	162.9	165.4	168.2	171.4	176.0	180.2	183.8	188.0	192.3
162.5°	164.4	164.1	165.5	167.7	169.9	172.5	176.6	180.0	182.9	186.3	190.0
165°	168.2	167.5	168.6	170.3	171.8	173.9	176.7	179.5	181.7	183.8	186.6
167.5°	170.8	170.4	171.1	172.0	173.0	174.4	176.7	178.7	179.7	181.3	183.3
170°	172.5	172.1	172.5	173.2	173.9	174.9	176.7	178.1	178.8	179.9	181.3
172.5°	173.6	173.0	173.3	174.0	174.4	174.9	176.4	177.6	177.7	178.2	179.3
175°	174.9	174.2	174.6	174.9	174.9	174.9	176.0	176.7	176.4	176.4	176.7
177.5°	175.6	175.0	175.0	175.3	175.0	175.0	175.6	175.9	175.3	175.3	175.6
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333123

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2
2.5°	582.5	583.3	584.1	584.5	584.4	584.3	584.3	584.2
5°	579.5	580.5	581.4	581.8	581.7	581.6	581.5	581.4
7.5°	573.7	574.6	575.5	575.9	575.8	575.7	575.6	575.5
10°	568.7	569.5	570.4	570.7	570.6	570.5	570.4	570.3
12.5°	562.1	562.8	563.4	563.7	563.7	563.7	563.7	563.6
15°	550.5	551.0	551.6	551.8	551.8	551.8	551.8	551.8
17.5°	537.1	537.7	538.4	538.4	537.9	537.4	536.9	536.4
20°	526.9	527.6	528.3	528.5	527.9	527.4	526.9	526.4
22.5°	515.3	515.8	516.3	516.3	516.0	515.6	515.3	514.9
25°	496.8	497.0	497.2	497.1	496.8	496.5	496.2	495.9
27.5°	477.3	477.3	477.4	477.3	476.9	476.6	476.3	476.0
30°	463.1	462.9	462.7	462.5	462.2	461.9	461.5	461.2
32.5°	448.8	448.4	448.0	447.6	447.0	446.4	445.9	445.3
35°	426.5	426.0	425.4	424.8	424.0	423.1	422.3	421.5
37.5°	403.1	402.3	401.5	400.9	400.4	400.0	399.5	399.0
40°	386.8	385.9	385.0	384.4	384.1	383.7	383.4	383.1
42.5°	370.7	369.9	369.0	368.4	367.9	367.4	367.0	366.5
45°	346.9	345.7	344.5	343.7	343.4	343.1	342.8	342.5
47.5°	321.8	320.6	319.3	318.3	317.6	316.9	316.2	315.5
50°	304.7	303.3	302.0	301.0	300.2	299.5	298.8	298.1
52.5°	288.0	286.8	285.6	284.7	283.9	283.1	282.3	281.5
55°	262.0	261.1	260.2	259.4	258.7	257.9	257.2	256.5
57.5°	236.3	235.1	233.9	233.1	232.7	232.3	231.9	231.5
60°	218.9	217.8	216.8	215.9	215.2	214.5	213.8	213.1
62.5°	202.1	200.9	199.8	199.0	198.5	197.9	197.3	196.8
65°	175.6	174.7	173.8	173.1	172.7	172.3	171.9	171.5
67.5°	150.4	149.6	148.8	148.3	148.1	147.8	147.6	147.3
70°	133.7	133.1	132.5	132.0	131.6	131.2	130.7	130.3
72.5°	118.0	117.3	116.6	116.1	115.7	115.3	114.8	114.4
75°	93.7	93.4	93.0	92.7	92.3	91.9	91.5	91.0
77.5°	71.4	71.2	71.0	70.8	70.5	70.2	69.9	69.6
80°	57.1	57.0	56.9	56.7	56.5	56.3	56.1	55.9
82.5°	43.6	43.4	43.3	43.1	43.1	43.1	43.0	43.0
85°	25.7	25.6	25.5	25.3	25.1	24.9	24.7	24.5
87.5°	10.9	11.0	11.0	11.1	10.9	10.8	10.7	10.5
90°	6.4	6.7	7.1	7.8	7.8	7.8	8.1	8.1
92.5°	62.6	45.4	34.2	29.0	24.5	23.6	23.1	22.5
95°	254.1	200.4	156.9	127.2	102.1	91.5	88.7	83.1
97.5°	378.4	340.8	298.4	257.1	235.3	215.5	205.3	200.7
100°	434.7	417.4	381.0	344.2	319.8	294.4	281.3	275.7
102.5°	453.6	464.3	446.9	422.0	395.9	377.8	363.6	359.4
105°	442.5	490.9	506.4	502.6	491.2	479.6	472.5	468.3
107.5°	402.6	467.2	507.1	525.6	531.3	531.3	528.9	526.1
110°	373.2	440.4	490.2	520.2	536.1	542.8	545.3	545.3





TEST NUMBER: P333123

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	350.0	413.8	464.2	499.6	522.8	534.4	540.5	543.1
115°	320.9	375.7	424.1	462.6	490.2	507.1	517.0	521.6
117.5°	302.1	349.3	391.0	426.4	453.9	471.5	481.3	484.1
120°	291.9	334.3	373.2	404.3	430.5	447.4	457.0	459.8
122.5°	284.3	323.6	358.2	387.3	410.7	426.2	435.8	438.3
125°	273.2	309.2	340.0	365.4	385.2	399.7	407.5	411.0
127.5°	261.9	295.5	324.2	348.0	366.0	378.8	386.1	387.7
130°	254.8	285.9	313.5	336.5	354.1	365.8	372.9	375.0
132.5°	247.7	276.9	301.9	324.0	341.7	353.3	359.8	362.2
135°	238.6	262.9	285.6	305.7	321.3	332.9	339.3	341.4
137.5°	230.8	250.5	269.3	286.4	300.3	310.9	316.8	319.1
140°	226.5	243.1	259.4	274.2	287.3	296.5	301.8	303.6
142.5°	222.9	236.9	250.9	263.8	274.9	282.7	287.7	289.2
145°	218.1	229.0	240.0	249.5	258.0	264.0	267.9	269.3
147.5°	213.5	222.4	230.9	238.1	244.8	249.6	251.8	252.5
150°	211.0	218.8	225.5	231.8	237.1	241.4	242.8	243.1
152.5°	208.2	215.1	221.2	226.2	230.6	234.0	235.4	235.8
155°	203.9	209.6	214.5	218.4	221.9	224.4	225.5	225.8
157.5°	199.7	204.3	208.2	211.2	214.0	216.0	217.0	216.9
160°	196.9	200.4	203.9	206.4	208.9	210.6	211.3	211.0
162.5°	193.7	197.0	200.0	202.2	204.1	205.5	205.7	205.6
165°	189.4	191.9	194.0	195.8	197.2	197.9	197.9	197.9
167.5°	185.3	187.0	188.6	189.9	190.6	191.2	190.9	190.8
170°	183.1	184.1	185.2	185.9	186.6	187.0	187.0	186.6
172.5°	180.5	181.6	182.4	182.8	182.9	183.6	183.0	182.6
175°	177.8	177.8	178.5	178.5	178.5	178.8	178.1	177.8
177.5°	175.9	176.1	176.1	176.1	175.9	176.1	175.3	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3

(END OF REPORT)