

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333133-940

Luminaire Tested: **S125DIP-S375D810U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333133-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D810U940-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4260.6 lumens
Efficiency: N/A
Efficacy: 136.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	35	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	25	20
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	66	54	47	41	59	49	43	37	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	22	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	14	12
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3135	3135	3135	3135
5°	3630	3146	2755	3146
10°	4224	3129	2413	3129
15°	4676	3107	2226	3107
20°	5234	3070	2076	3070
25°	6131	3029	2003	3029
30°	6623	2988	1939	2988
35°	5445	2912	1898	2912
40°	3871	2807	1851	2807
45°	2974	2665	1825	2665
50°	2538	2488	1822	2488
55°	2260	2315	1838	2315
60°	2038	2126	1885	2126
65°	1883	1936	1933	1936
70°	1713	1739	1962	1739
75°	1510	1532	1941	1532
80°	1272	1250	1778	1250
85°	1008	897	1438	897



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	1.1
10°-20°	139.1	3.3
20°-30°	225.9	5.3
30°-40°	275.6	6.5
40°-50°	250.7	5.9
50°-60°	199.7	4.7
60°-70°	139.1	3.3
70°-80°	74.2	1.7
80°-90°	20.7	0.5
90°-100°	34.2	0.8
100°-110°	210.7	4.9
110°-120°	382.1	9.0
120°-130°	490.4	11.5
130°-140°	527.5	12.4
140°-150°	495.1	11.6
150°-160°	400.5	9.4
160°-170°	259.0	6.1
170°-180°	89.3	2.1
0°-30°	411.8	9.7
0°-40°	687.4	16.1
0°-60°	1137.8	26.7
0°-90°	1371.8	32.2
90°-120°	627.0	14.7
90°-150°	2140.0	50.2
90°-180°	2889.0	67.8
0°-180°	4260.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	560	485	425	485	560	56
15°	699	465	333	465	699	200
25°	860	425	281	425	860	393
35°	691	369	241	369	691	423
45°	326	292	200	292	326	261
55°	201	206	163	206	201	181
65°	123	127	126	127	123	122
75°	60	61	78	61	60	65
85°	14	12	19	12	14	16
90°	17	1	17	1	17	8
95°	15	40	15	40	15	12
105°	207	205	207	205	207	187
115°	382	385	382	385	382	379
125°	547	547	547	547	547	487
135°	680	683	680	683	680	525
145°	789	792	789	792	789	493
155°	865	872	865	872	865	399
165°	915	920	915	920	915	258
175°	937	941	937	941	937	89
180°	941	941	941	941	941	



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	513.4	512.8	512.1	510.9	511.8	509.0	507.7	505.4	502.6	501.6	500.4
5°	560.0	561.1	562.1	557.8	558.2	555.3	548.7	543.3	539.0	533.4	529.5
7.5°	616.1	613.7	613.4	610.6	605.8	601.9	595.0	586.2	577.7	567.9	559.9
10°	644.1	644.4	642.5	639.2	634.0	630.3	621.3	612.6	602.1	589.7	580.9
12.5°	665.2	666.1	663.7	659.2	656.7	648.5	641.3	631.1	618.6	608.7	595.2
15°	699.3	697.1	695.4	689.8	685.5	676.9	665.6	654.8	641.2	628.7	616.1
17.5°	732.2	734.1	730.9	725.9	712.4	702.3	687.2	672.4	655.5	638.6	623.7
20°	761.5	763.2	758.5	749.6	733.5	723.4	703.5	684.5	664.9	643.3	626.8
22.5°	798.2	796.8	790.4	776.9	763.0	744.4	722.7	699.6	675.1	650.7	628.7
25°	860.4	851.8	847.8	831.2	812.9	785.4	755.8	722.0	691.5	659.2	631.2
27.5°	895.0	892.2	887.9	876.3	857.0	827.7	792.7	751.5	708.6	667.7	631.0
30°	888.1	888.5	888.9	885.2	872.8	850.8	815.9	771.7	720.5	674.6	632.1
32.5°	826.7	834.2	841.4	849.9	853.4	849.1	827.3	787.3	734.7	682.5	631.5
35°	690.6	692.9	716.2	739.3	770.6	795.0	811.2	793.4	749.2	689.2	630.7
37.5°	538.5	549.7	565.8	591.8	637.0	677.5	729.6	753.5	739.2	691.4	629.3
40°	459.1	469.4	479.9	506.5	544.6	593.6	652.7	703.2	715.0	684.5	624.3
42.5°	397.8	405.9	417.6	437.6	469.4	512.8	569.4	635.3	675.9	664.4	613.9
45°	325.6	330.7	339.7	355.6	378.7	412.7	462.5	534.7	597.5	618.3	589.3
47.5°	278.7	278.7	285.7	296.6	313.3	342.1	379.1	435.5	502.7	552.3	550.0
50°	252.6	251.6	257.2	266.6	279.8	299.0	334.2	379.3	443.8	500.1	515.8
52.5°	230.2	230.3	233.7	240.8	251.8	268.1	294.4	335.2	390.2	448.0	477.5
55°	200.7	199.8	203.8	208.5	216.6	227.3	246.2	277.3	322.1	378.9	417.2
57.5°	173.6	175.9	177.5	180.7	187.4	194.7	210.6	233.4	268.9	317.7	358.2
60°	157.8	160.1	161.3	164.6	170.0	176.2	188.5	207.1	236.9	279.0	319.1
62.5°	143.7	145.4	145.9	148.8	153.2	159.2	168.9	184.5	208.1	244.9	284.2
65°	123.2	123.2	124.0	127.2	129.2	134.6	142.0	153.3	172.3	200.9	234.5
67.5°	103.5	104.5	104.3	105.7	107.5	111.7	117.0	126.4	140.4	161.3	188.2
70°	90.7	91.5	91.3	92.3	94.3	97.0	101.4	110.2	120.3	138.2	161.3
72.5°	79.1	79.5	78.9	80.3	81.5	83.8	88.7	93.5	102.8	118.0	137.0
75°	60.5	61.0	61.4	62.2	63.5	64.7	67.1	71.9	78.1	89.4	101.6
77.5°	45.4	44.6	45.7	45.5	46.2	47.2	49.3	51.8	56.9	64.1	73.5
80°	34.2	34.4	34.4	34.6	35.7	36.3	38.1	39.9	43.9	49.2	55.8
82.5°	25.0	25.5	25.1	25.6	26.4	26.8	27.9	29.4	31.7	35.9	40.7
85°	13.6	12.6	13.0	13.4	13.4	13.6	14.4	15.1	16.3	17.9	19.8
87.5°	7.3	7.6	7.6	7.5	7.6	7.5	7.9	7.8	8.1	8.5	8.9
90°	16.8	16.2	15.8	15.3	14.9	14.3	13.5	12.8	11.9	11.1	10.1
92.5°	15.6	15.4	15.2	15.0	14.7	14.3	13.5	12.8	11.9	11.1	10.2
95°	14.6	14.6	14.6	14.6	14.6	14.3	13.5	12.8	11.9	11.1	17.0
97.5°	14.6	14.6	14.6	14.6	14.6	16.9	21.2	25.6	30.0	34.3	45.9
100°	14.6	15.2	15.9	16.5	17.1	29.0	52.1	75.2	98.3	121.4	120.7
102.5°	87.7	98.3	108.8	119.3	129.9	137.3	141.7	146.1	150.4	154.8	154.4
105°	207.1	207.2	207.4	207.6	207.8	207.8	207.8	207.8	207.8	207.8	207.8
107.5°	261.1	261.5	262.0	262.5	263.0	263.1	263.1	263.1	263.1	263.1	262.7
110°	298.5	298.3	298.2	298.0	297.8	298.0	298.5	298.9	299.4	299.9	299.5



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	332.0	332.2	332.3	332.6	332.8	333.2	333.8	334.4	335.0	335.6	335.4
115°	382.2	383.1	384.0	385.0	385.8	386.6	387.3	387.9	388.5	389.1	389.0
117.5°	435.7	436.1	436.5	436.9	437.3	437.9	438.7	439.5	440.3	441.1	440.6
120°	468.6	469.4	470.2	470.9	471.7	472.3	472.6	472.9	473.2	473.5	473.1
122.5°	499.9	500.8	501.7	502.6	503.5	504.1	504.4	504.7	505.0	505.3	505.1
125°	547.4	547.9	548.3	548.8	549.3	549.8	550.5	551.1	551.7	552.3	552.3
127.5°	587.5	588.6	589.8	590.9	592.0	592.8	593.2	593.4	593.8	594.1	594.2
130°	616.4	617.2	618.0	618.8	619.6	620.2	620.6	621.1	621.6	622.1	621.9
132.5°	643.3	644.0	644.8	645.6	646.3	646.8	646.8	646.9	647.0	647.1	647.5
135°	679.9	680.8	681.8	682.7	683.7	684.3	684.6	684.9	685.2	685.5	685.8
137.5°	716.8	717.6	718.4	719.2	720.0	720.3	720.2	720.2	720.1	720.1	720.4
140°	738.5	739.4	740.4	741.3	742.3	742.5	742.3	741.9	741.6	741.3	741.5
142.5°	759.1	760.1	761.0	762.0	762.9	763.3	763.2	763.2	763.1	763.0	762.9
145°	789.4	790.3	791.3	792.2	793.1	793.5	793.4	793.2	793.1	792.9	792.9
147.5°	814.4	815.5	816.6	817.7	818.9	819.3	819.1	818.9	818.8	818.6	818.4
150°	830.5	831.8	833.0	834.3	835.5	836.0	835.7	835.4	835.1	834.7	834.5
152.5°	845.6	846.8	847.8	849.0	850.1	850.5	850.2	849.9	849.5	849.3	848.9
155°	865.4	866.7	867.9	869.2	870.4	870.8	870.3	869.9	869.3	868.9	868.6
157.5°	882.0	883.2	884.5	885.7	887.0	887.3	886.9	886.4	885.8	885.4	885.3
160°	892.6	893.9	895.1	896.3	897.6	897.9	897.2	896.6	896.0	895.4	895.3
162.5°	902.1	903.5	904.8	906.2	907.6	907.8	907.0	906.1	905.2	904.4	904.2
165°	914.9	916.1	917.4	918.6	919.9	920.1	919.1	918.2	917.3	916.3	916.1
167.5°	923.9	925.2	926.7	928.0	929.4	929.6	928.4	927.4	926.2	925.1	925.0
170°	928.9	930.2	931.7	933.1	934.4	934.5	933.3	932.0	930.9	929.6	929.4
172.5°	932.2	933.6	935.0	936.4	937.8	938.0	936.8	935.7	934.6	933.4	933.2
175°	936.6	938.0	939.3	940.8	942.1	942.2	940.9	939.7	938.5	937.3	937.1
177.5°	939.1	940.0	941.0	942.0	943.1	943.1	942.2	941.4	940.5	939.6	939.5
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	499.4	498.3	497.0	494.6	491.9	490.4	488.1	486.6	483.7	481.2	478.5
5°	524.8	519.4	514.5	508.1	501.1	496.6	491.2	485.3	479.0	472.7	465.7
7.5°	551.1	541.5	531.3	520.2	509.3	499.4	489.8	480.5	471.8	461.2	452.3
10°	568.6	556.7	543.9	529.0	514.2	501.5	488.6	477.2	465.7	453.3	442.4
12.5°	586.3	570.4	552.3	535.8	518.3	502.8	487.6	473.1	458.6	444.9	432.1
15°	598.8	584.8	568.1	544.6	524.8	503.5	483.4	464.7	447.1	431.9	415.8
17.5°	607.0	588.9	571.0	548.5	522.5	498.8	475.9	454.4	434.7	415.4	399.9
20°	608.4	589.9	571.1	549.1	522.5	495.3	472.4	446.7	425.5	405.5	386.6
22.5°	608.0	586.9	566.5	543.9	517.9	492.8	465.2	439.0	415.9	396.3	376.5
25°	603.3	580.9	555.3	532.4	506.8	480.3	452.3	425.1	401.6	379.2	359.5
27.5°	599.4	570.3	541.4	514.7	490.0	465.7	438.8	411.0	385.0	362.2	343.8
30°	594.7	562.7	530.1	502.3	477.0	453.3	427.9	400.7	373.5	351.3	331.5
32.5°	590.4	553.1	518.8	488.5	461.6	438.6	415.3	389.4	362.7	340.1	320.3
35°	582.1	539.0	499.6	465.5	436.8	413.1	393.5	369.4	344.9	323.1	304.2
37.5°	571.6	520.5	478.2	442.4	411.0	386.0	367.8	349.3	325.7	304.7	287.6
40°	563.3	507.3	462.5	425.9	393.3	367.4	350.4	333.0	313.4	293.8	275.7
42.5°	552.9	495.4	446.7	407.2	375.1	349.7	332.0	317.2	299.9	281.6	264.8
45°	533.9	473.9	421.2	378.7	346.2	321.2	302.9	291.8	278.7	261.4	247.3
47.5°	505.8	448.1	393.5	349.7	316.1	293.0	275.8	265.1	256.0	243.2	230.2
50°	480.9	428.8	373.5	330.1	296.5	273.2	257.3	247.6	239.9	230.0	219.0
52.5°	453.1	404.6	353.9	310.9	277.7	254.8	239.2	230.7	224.2	217.1	206.3
55°	408.8	367.6	320.6	279.8	249.1	226.7	213.0	205.6	200.3	194.9	188.3
57.5°	360.1	327.8	286.2	248.9	220.6	200.2	187.5	180.3	176.1	173.3	169.5
60°	325.7	298.2	262.3	228.3	200.7	182.5	170.2	164.6	161.1	158.9	156.0
62.5°	293.9	271.3	238.1	207.1	182.9	165.8	154.7	149.3	146.0	144.8	142.5
65°	247.1	229.5	202.2	176.4	155.8	141.2	131.9	126.7	124.7	123.4	123.6
67.5°	200.8	190.2	168.2	146.2	129.7	117.5	110.0	106.1	105.0	103.4	103.4
70°	172.6	164.6	146.1	126.9	112.3	102.8	96.2	92.1	91.0	90.2	90.1
72.5°	147.8	140.7	124.7	109.3	96.1	87.8	82.4	79.9	78.2	77.8	77.7
75°	111.0	107.2	94.3	82.2	73.1	67.4	63.7	61.4	60.2	59.9	60.2
77.5°	78.9	75.5	67.4	58.8	53.1	48.7	45.6	44.8	43.4	43.4	43.2
80°	59.3	57.1	51.9	45.1	40.4	36.6	35.0	33.6	33.2	32.5	33.2
82.5°	43.0	40.6	37.1	32.7	28.8	26.7	25.0	24.5	24.3	24.0	24.1
85°	21.2	21.4	19.4	16.1	14.4	13.2	12.1	12.1	11.9	11.8	11.9
87.5°	9.0	8.5	7.7	6.9	5.8	5.1	4.6	4.5	4.4	4.5	4.8
90°	9.0	7.9	6.8	5.6	4.5	3.2	2.0	0.7	2.0	3.2	4.5
92.5°	9.3	8.3	7.3	7.3	8.1	9.0	9.9	10.7	9.9	9.0	8.1
95°	22.9	28.8	34.7	37.9	38.3	38.8	39.3	39.8	39.3	38.8	38.3
97.5°	57.6	69.3	81.0	86.3	85.5	84.6	83.8	83.0	83.8	84.6	85.5
100°	120.1	119.5	118.9	118.3	117.9	117.3	116.9	116.5	116.9	117.3	117.9
102.5°	154.1	153.7	153.3	152.8	152.2	151.7	151.1	150.5	151.1	151.7	152.2
105°	207.8	207.8	207.8	207.5	206.9	206.3	205.6	205.0	205.6	206.3	206.9
107.5°	262.4	262.1	261.8	261.6	261.6	261.6	261.6	261.6	261.6	261.6	261.6
110°	299.3	298.9	298.6	298.5	298.5	298.5	298.5	298.5	298.5	298.5	298.5



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	335.2	335.0	334.8	334.6	334.2	333.8	333.4	333.1	333.4	333.8	334.2
115°	388.8	388.7	388.5	388.1	387.3	386.5	385.8	385.0	385.8	386.5	387.3
117.5°	440.0	439.3	438.8	438.5	438.5	438.5	438.6	438.6	438.6	438.5	438.5
120°	472.6	472.1	471.6	471.4	471.6	471.8	472.0	472.1	472.0	471.8	471.6
122.5°	504.9	504.6	504.4	504.0	503.5	502.8	502.3	501.7	502.3	502.8	503.5
125°	552.3	552.3	552.3	551.8	550.7	549.6	548.5	547.4	548.5	549.6	550.7
127.5°	594.3	594.4	594.5	594.1	593.4	592.6	591.8	591.1	591.8	592.6	593.4
130°	621.7	621.6	621.4	621.0	620.2	619.4	618.7	617.9	618.7	619.4	620.2
132.5°	647.8	648.2	648.5	648.3	647.3	646.4	645.5	644.6	645.5	646.4	647.3
135°	686.1	686.4	686.7	686.4	685.5	684.6	683.7	682.7	683.7	684.6	685.5
137.5°	720.7	720.9	721.2	720.9	720.1	719.3	718.5	717.7	718.5	719.3	720.1
140°	741.6	741.7	741.9	741.8	741.5	741.2	740.9	740.6	740.9	741.2	741.5
142.5°	762.6	762.4	762.1	762.0	761.8	761.6	761.4	761.3	761.4	761.6	761.8
145°	792.9	792.9	792.9	792.7	792.5	792.1	791.8	791.5	791.8	792.1	792.5
147.5°	818.1	818.0	817.8	817.8	817.8	817.9	818.0	818.0	818.0	817.9	817.8
150°	834.1	833.8	833.5	833.5	833.8	834.1	834.5	834.7	834.5	834.1	833.8
152.5°	848.6	848.3	848.0	848.2	848.9	849.5	850.2	851.0	850.2	849.5	848.9
155°	868.3	868.0	867.6	868.0	868.9	869.9	870.8	871.7	870.8	869.9	868.9
157.5°	885.3	885.3	885.2	885.5	886.1	886.6	887.2	887.7	887.2	886.6	886.1
160°	895.1	894.9	894.8	895.2	896.1	897.1	898.0	898.9	898.0	897.1	896.1
162.5°	904.0	903.8	903.7	904.1	905.0	906.0	906.9	907.9	906.9	906.0	905.0
165°	916.1	915.9	915.7	916.1	917.0	917.9	918.9	919.8	918.9	917.9	917.0
167.5°	924.8	924.6	924.5	924.9	925.9	926.8	927.8	928.7	927.8	926.8	925.9
170°	929.3	929.1	929.0	929.4	930.5	931.6	932.6	933.8	932.6	931.6	930.5
172.5°	932.9	932.6	932.4	932.7	933.9	935.0	936.0	937.1	936.0	935.0	933.9
175°	936.9	936.7	936.7	937.0	938.0	938.9	939.8	940.8	939.8	938.9	938.0
177.5°	939.3	939.2	939.1	939.4	940.2	940.9	941.6	942.4	941.6	940.9	940.2
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	477.1	475.2	473.8	470.5	468.6	466.2	464.2	466.4	464.0	465.0	463.5
5°	462.2	456.4	452.3	446.3	441.1	436.4	432.9	432.3	430.6	429.8	427.3
7.5°	444.3	437.0	430.0	422.1	415.5	408.8	404.6	401.0	398.7	395.6	393.4
10°	433.7	424.0	415.8	406.4	398.1	390.8	385.1	382.2	379.5	375.6	374.2
12.5°	420.7	410.7	400.6	390.5	382.5	374.5	369.6	365.2	363.4	359.0	358.6
15°	405.1	390.0	380.1	369.9	358.9	352.3	348.2	343.5	341.4	338.3	336.1
17.5°	386.5	373.0	360.7	350.0	340.6	335.1	329.9	326.7	323.2	321.1	317.4
20°	372.9	360.2	347.8	336.4	329.2	322.9	318.8	315.7	311.9	310.9	307.2
22.5°	361.6	347.5	335.6	326.1	318.3	311.0	306.6	304.4	301.9	298.7	298.0
25°	343.0	328.4	318.3	308.9	301.8	295.2	292.2	289.5	287.0	284.7	283.9
27.5°	327.1	314.0	302.0	293.5	287.3	281.3	278.7	275.4	273.6	271.7	269.5
30°	315.8	302.5	291.9	283.7	277.1	271.8	268.9	266.6	265.0	263.3	262.1
32.5°	304.3	291.9	281.8	273.7	267.1	263.1	260.5	258.9	257.1	255.1	253.5
35°	289.1	275.4	265.6	258.6	253.4	250.3	247.4	246.0	244.0	244.0	242.3
37.5°	271.9	260.1	251.4	245.0	240.4	237.6	234.5	233.5	232.2	231.3	230.8
40°	261.7	250.7	242.5	236.1	231.2	228.9	226.4	224.8	224.0	222.9	222.6
42.5°	251.1	240.7	232.8	226.9	222.6	220.7	218.4	217.2	215.5	214.2	213.9
45°	235.1	225.0	217.8	213.0	209.4	207.1	205.6	203.1	202.3	200.7	200.5
47.5°	219.9	210.2	203.1	199.2	196.0	194.1	191.9	189.4	188.4	187.6	187.5
50°	208.5	199.7	193.1	189.4	186.3	183.6	181.3	179.7	179.1	179.1	179.5
52.5°	197.0	189.4	183.9	179.3	176.4	173.5	171.4	170.4	169.5	170.5	171.2
55°	180.1	172.5	168.4	164.0	161.1	157.8	156.8	156.4	155.8	157.4	158.3
57.5°	162.2	156.9	152.0	147.8	145.2	143.2	141.9	141.6	142.8	143.6	146.2
60°	150.8	144.6	140.4	137.1	133.9	132.7	132.2	131.9	132.7	134.9	138.5
62.5°	138.3	133.3	128.6	126.2	123.9	121.8	121.7	122.0	123.6	126.3	129.7
65°	119.9	115.6	112.5	109.6	107.7	106.6	106.9	107.7	109.6	113.2	117.0
67.5°	101.2	98.3	95.5	93.2	91.4	91.4	91.8	93.1	95.2	99.2	102.8
70°	89.3	86.0	83.6	82.7	81.1	80.3	81.6	83.6	85.5	89.3	92.3
72.5°	77.2	74.4	72.6	71.9	71.2	70.6	71.1	73.3	75.8	79.5	83.1
75°	59.3	58.3	57.1	56.3	55.6	56.1	56.4	58.5	60.5	64.5	68.6
77.5°	43.3	42.3	41.5	41.3	40.9	41.2	42.4	43.9	45.8	48.7	51.8
80°	32.7	32.4	31.9	31.7	31.7	31.9	33.6	34.6	36.5	39.1	41.6
82.5°	23.9	23.6	23.5	23.5	23.6	23.7	24.7	26.0	27.6	29.6	31.7
85°	12.6	12.1	12.8	13.0	12.6	13.2	13.6	14.4	15.1	16.1	17.1
87.5°	5.3	5.8	5.9	6.2	6.5	7.0	7.0	7.8	8.3	8.8	8.7
90°	5.6	6.8	7.9	9.0	10.1	11.1	11.9	12.8	13.5	14.3	14.9
92.5°	7.3	7.3	8.3	9.3	10.2	11.1	11.9	12.8	13.5	14.3	14.7
95°	37.9	34.7	28.8	22.9	17.0	11.1	11.9	12.8	13.5	14.3	14.6
97.5°	86.3	81.0	69.3	57.6	45.9	34.3	30.0	25.6	21.2	16.9	14.6
100°	118.3	118.9	119.5	120.1	120.7	121.4	98.3	75.2	52.1	29.0	17.1
102.5°	152.8	153.3	153.7	154.1	154.4	154.8	150.4	146.1	141.7	137.3	129.9
105°	207.5	207.8	207.8	207.8	207.8	207.8	207.8	207.8	207.8	207.8	207.8
107.5°	261.6	261.8	262.1	262.4	262.7	263.1	263.1	263.1	263.1	263.1	263.0
110°	298.5	298.6	298.9	299.3	299.5	299.9	299.4	298.9	298.5	298.0	297.8



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	334.6	334.8	335.0	335.2	335.4	335.6	335.0	334.4	333.8	333.2	332.8
115°	388.1	388.5	388.7	388.8	389.0	389.1	388.5	387.9	387.3	386.6	385.8
117.5°	438.5	438.8	439.3	440.0	440.6	441.1	440.3	439.5	438.7	437.9	437.3
120°	471.4	471.6	472.1	472.6	473.1	473.5	473.2	472.9	472.6	472.3	471.7
122.5°	504.0	504.4	504.6	504.9	505.1	505.3	505.0	504.7	504.4	504.1	503.5
125°	551.8	552.3	552.3	552.3	552.3	552.3	551.7	551.1	550.5	549.8	549.3
127.5°	594.1	594.5	594.4	594.3	594.2	594.1	593.8	593.4	593.2	592.8	592.0
130°	621.0	621.4	621.6	621.7	621.9	622.1	621.6	621.1	620.6	620.2	619.6
132.5°	648.3	648.5	648.2	647.8	647.5	647.1	647.0	646.9	646.8	646.8	646.3
135°	686.4	686.7	686.4	686.1	685.8	685.5	685.2	684.9	684.6	684.3	683.7
137.5°	720.9	721.2	720.9	720.7	720.4	720.1	720.1	720.2	720.2	720.3	720.0
140°	741.8	741.9	741.7	741.6	741.5	741.3	741.6	741.9	742.3	742.5	742.3
142.5°	762.0	762.1	762.4	762.6	762.9	763.0	763.1	763.2	763.2	763.3	762.9
145°	792.7	792.9	792.9	792.9	792.9	792.9	793.1	793.2	793.4	793.5	793.1
147.5°	817.8	817.8	818.0	818.1	818.4	818.6	818.8	818.9	819.1	819.3	818.9
150°	833.5	833.5	833.8	834.1	834.5	834.7	835.1	835.4	835.7	836.0	835.5
152.5°	848.2	848.0	848.3	848.6	848.9	849.3	849.5	849.9	850.2	850.5	850.1
155°	868.0	867.6	868.0	868.3	868.6	868.9	869.3	869.9	870.3	870.8	870.4
157.5°	885.5	885.2	885.3	885.3	885.3	885.4	885.8	886.4	886.9	887.3	887.0
160°	895.2	894.8	894.9	895.1	895.3	895.4	896.0	896.6	897.2	897.9	897.6
162.5°	904.1	903.7	903.8	904.0	904.2	904.4	905.2	906.1	907.0	907.8	907.6
165°	916.1	915.7	915.9	916.1	916.1	916.3	917.3	918.2	919.1	920.1	919.9
167.5°	924.9	924.5	924.6	924.8	925.0	925.1	926.2	927.4	928.4	929.6	929.4
170°	929.4	929.0	929.1	929.3	929.4	929.6	930.9	932.0	933.3	934.5	934.4
172.5°	932.7	932.4	932.6	932.9	933.2	933.4	934.6	935.7	936.8	938.0	937.8
175°	937.0	936.7	936.7	936.9	937.1	937.3	938.5	939.7	940.9	942.2	942.1
177.5°	939.4	939.1	939.2	939.3	939.5	939.6	940.5	941.4	942.2	943.1	943.1
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	462.5	463.7	462.7	464.0	462.7	463.7	462.5	463.5	465.0	464.0	466.4
5°	426.3	424.5	425.7	424.9	425.7	424.5	426.3	427.3	429.8	430.6	432.3
7.5°	392.9	391.1	389.1	388.1	389.1	391.1	392.9	393.4	395.6	398.7	401.0
10°	371.9	369.6	369.4	368.0	369.4	369.6	371.9	374.2	375.6	379.5	382.2
12.5°	356.6	354.5	352.1	351.5	352.1	354.5	356.6	358.6	359.0	363.4	365.2
15°	334.8	333.1	331.7	333.0	331.7	333.1	334.8	336.1	338.3	341.4	343.5
17.5°	316.7	315.4	315.1	313.6	315.1	315.4	316.7	317.4	321.1	323.2	326.7
20°	305.3	304.3	304.8	302.0	304.8	304.3	305.3	307.2	310.9	311.9	315.7
22.5°	296.3	294.3	294.0	293.5	294.0	294.3	296.3	298.0	298.7	301.9	304.4
25°	282.0	281.1	280.0	281.1	280.0	281.1	282.0	283.9	284.7	287.0	289.5
27.5°	269.7	268.4	268.1	268.3	268.1	268.4	269.7	269.5	271.7	273.6	275.4
30°	262.1	260.0	260.2	260.0	260.2	260.0	262.1	262.1	263.3	265.0	266.6
32.5°	253.9	252.4	252.2	251.8	252.2	252.4	253.9	253.5	255.1	257.1	258.9
35°	241.7	241.7	240.7	240.7	240.7	241.7	241.7	242.3	244.0	244.0	246.0
37.5°	230.2	230.1	229.4	229.5	229.4	230.1	230.2	230.8	231.3	232.2	233.5
40°	221.7	221.5	220.9	219.6	220.9	221.5	221.7	222.6	222.9	224.0	224.8
42.5°	213.5	212.8	212.5	212.0	212.5	212.8	213.5	213.9	214.2	215.5	217.2
45°	200.5	200.5	200.1	199.8	200.1	200.5	200.5	200.5	200.7	202.3	203.1
47.5°	187.9	188.2	189.0	188.9	189.0	188.2	187.9	187.5	187.6	188.4	189.4
50°	180.3	180.5	181.1	181.3	181.1	180.5	180.3	179.5	179.1	179.1	179.7
52.5°	171.9	173.1	173.9	173.7	173.9	173.1	171.9	171.2	170.5	169.5	170.4
55°	160.1	161.6	163.0	163.2	163.0	161.6	160.1	158.3	157.4	155.8	156.4
57.5°	148.5	150.4	151.9	152.5	151.9	150.4	148.5	146.2	143.6	142.8	141.6
60°	140.5	143.2	145.1	145.9	145.1	143.2	140.5	138.5	134.9	132.7	131.9
62.5°	133.0	136.0	137.8	137.9	137.8	136.0	133.0	129.7	126.3	123.6	122.0
65°	120.6	123.6	125.3	126.5	125.3	123.6	120.6	117.0	113.2	109.6	107.7
67.5°	107.2	110.3	112.1	113.1	112.1	110.3	107.2	102.8	99.2	95.2	93.1
70°	97.5	100.6	103.0	103.9	103.0	100.6	97.5	92.3	89.3	85.5	83.6
72.5°	87.9	90.7	92.6	93.6	92.6	90.7	87.9	83.1	79.5	75.8	73.3
75°	71.2	75.0	76.9	77.8	76.9	75.0	71.2	68.6	64.5	60.5	58.5
77.5°	54.9	58.3	59.5	60.0	59.5	58.3	54.9	51.8	48.7	45.8	43.9
80°	44.1	46.2	47.6	47.8	47.6	46.2	44.1	41.6	39.1	36.5	34.6
82.5°	33.9	35.6	36.0	36.6	36.0	35.6	33.9	31.7	29.6	27.6	26.0
85°	18.5	19.4	19.6	19.4	19.6	19.4	18.5	17.1	16.1	15.1	14.4
87.5°	9.2	9.1	9.2	9.6	9.2	9.1	9.2	8.7	8.8	8.3	7.8
90°	15.3	15.8	16.2	16.8	16.2	15.8	15.3	14.9	14.3	13.5	12.8
92.5°	15.0	15.2	15.4	15.6	15.4	15.2	15.0	14.7	14.3	13.5	12.8
95°	14.6	14.6	14.6	14.6	14.6	14.6	14.6	14.6	14.3	13.5	12.8
97.5°	14.6	14.6	14.6	14.6	14.6	14.6	14.6	14.6	16.9	21.2	25.6
100°	16.5	15.9	15.2	14.6	15.2	15.9	16.5	17.1	29.0	52.1	75.2
102.5°	119.3	108.8	98.3	87.7	98.3	108.8	119.3	129.9	137.3	141.7	146.1
105°	207.6	207.4	207.2	207.1	207.2	207.4	207.6	207.8	207.8	207.8	207.8
107.5°	262.5	262.0	261.5	261.1	261.5	262.0	262.5	263.0	263.1	263.1	263.1
110°	298.0	298.2	298.3	298.5	298.3	298.2	298.0	297.8	298.0	298.5	298.9



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	332.6	332.3	332.2	332.0	332.2	332.3	332.6	332.8	333.2	333.8	334.4
115°	385.0	384.0	383.1	382.2	383.1	384.0	385.0	385.8	386.6	387.3	387.9
117.5°	436.9	436.5	436.1	435.7	436.1	436.5	436.9	437.3	437.9	438.7	439.5
120°	470.9	470.2	469.4	468.6	469.4	470.2	470.9	471.7	472.3	472.6	472.9
122.5°	502.6	501.7	500.8	499.9	500.8	501.7	502.6	503.5	504.1	504.4	504.7
125°	548.8	548.3	547.9	547.4	547.9	548.3	548.8	549.3	549.8	550.5	551.1
127.5°	590.9	589.8	588.6	587.5	588.6	589.8	590.9	592.0	592.8	593.2	593.4
130°	618.8	618.0	617.2	616.4	617.2	618.0	618.8	619.6	620.2	620.6	621.1
132.5°	645.6	644.8	644.0	643.3	644.0	644.8	645.6	646.3	646.8	646.8	646.9
135°	682.7	681.8	680.8	679.9	680.8	681.8	682.7	683.7	684.3	684.6	684.9
137.5°	719.2	718.4	717.6	716.8	717.6	718.4	719.2	720.0	720.3	720.2	720.2
140°	741.3	740.4	739.4	738.5	739.4	740.4	741.3	742.3	742.5	742.3	741.9
142.5°	762.0	761.0	760.1	759.1	760.1	761.0	762.0	762.9	763.3	763.2	763.2
145°	792.2	791.3	790.3	789.4	790.3	791.3	792.2	793.1	793.5	793.4	793.2
147.5°	817.7	816.6	815.5	814.4	815.5	816.6	817.7	818.9	819.3	819.1	818.9
150°	834.3	833.0	831.8	830.5	831.8	833.0	834.3	835.5	836.0	835.7	835.4
152.5°	849.0	847.8	846.8	845.6	846.8	847.8	849.0	850.1	850.5	850.2	849.9
155°	869.2	867.9	866.7	865.4	866.7	867.9	869.2	870.4	870.8	870.3	869.9
157.5°	885.7	884.5	883.2	882.0	883.2	884.5	885.7	887.0	887.3	886.9	886.4
160°	896.3	895.1	893.9	892.6	893.9	895.1	896.3	897.6	897.9	897.2	896.6
162.5°	906.2	904.8	903.5	902.1	903.5	904.8	906.2	907.6	907.8	907.0	906.1
165°	918.6	917.4	916.1	914.9	916.1	917.4	918.6	919.9	920.1	919.1	918.2
167.5°	928.0	926.7	925.2	923.9	925.2	926.7	928.0	929.4	929.6	928.4	927.4
170°	933.1	931.7	930.2	928.9	930.2	931.7	933.1	934.4	934.5	933.3	932.0
172.5°	936.4	935.0	933.6	932.2	933.6	935.0	936.4	937.8	938.0	936.8	935.7
175°	940.8	939.3	938.0	936.6	938.0	939.3	940.8	942.1	942.2	940.9	939.7
177.5°	942.0	941.0	940.0	939.1	940.0	941.0	942.0	943.1	943.1	942.2	941.4
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	464.2	466.2	468.6	470.5	473.8	475.2	477.1	478.5	481.2	483.7	486.6
5°	432.9	436.4	441.1	446.3	452.3	456.4	462.2	465.7	472.7	479.0	485.3
7.5°	404.6	408.8	415.5	422.1	430.0	437.0	444.3	452.3	461.2	471.8	480.5
10°	385.1	390.8	398.1	406.4	415.8	424.0	433.7	442.4	453.3	465.7	477.2
12.5°	369.6	374.5	382.5	390.5	400.6	410.7	420.7	432.1	444.9	458.6	473.1
15°	348.2	352.3	358.9	369.9	380.1	390.0	405.1	415.8	431.9	447.1	464.7
17.5°	329.9	335.1	340.6	350.0	360.7	373.0	386.5	399.9	415.4	434.7	454.4
20°	318.8	322.9	329.2	336.4	347.8	360.2	372.9	386.6	405.5	425.5	446.7
22.5°	306.6	311.0	318.3	326.1	335.6	347.5	361.6	376.5	396.3	415.9	439.0
25°	292.2	295.2	301.8	308.9	318.3	328.4	343.0	359.5	379.2	401.6	425.1
27.5°	278.7	281.3	287.3	293.5	302.0	314.0	327.1	343.8	362.2	385.0	411.0
30°	268.9	271.8	277.1	283.7	291.9	302.5	315.8	331.5	351.3	373.5	400.7
32.5°	260.5	263.1	267.1	273.7	281.8	291.9	304.3	320.3	340.1	362.7	389.4
35°	247.4	250.3	253.4	258.6	265.6	275.4	289.1	304.2	323.1	344.9	369.4
37.5°	234.5	237.6	240.4	245.0	251.4	260.1	271.9	287.6	304.7	325.7	349.3
40°	226.4	228.9	231.2	236.1	242.5	250.7	261.7	275.7	293.8	313.4	333.0
42.5°	218.4	220.7	222.6	226.9	232.8	240.7	251.1	264.8	281.6	299.9	317.2
45°	205.6	207.1	209.4	213.0	217.8	225.0	235.1	247.3	261.4	278.7	291.8
47.5°	191.9	194.1	196.0	199.2	203.1	210.2	219.9	230.2	243.2	256.0	265.1
50°	181.3	183.6	186.3	189.4	193.1	199.7	208.5	219.0	230.0	239.9	247.6
52.5°	171.4	173.5	176.4	179.3	183.9	189.4	197.0	206.3	217.1	224.2	230.7
55°	156.8	157.8	161.1	164.0	168.4	172.5	180.1	188.3	194.9	200.3	205.6
57.5°	141.9	143.2	145.2	147.8	152.0	156.9	162.2	169.5	173.3	176.1	180.3
60°	132.2	132.7	133.9	137.1	140.4	144.6	150.8	156.0	158.9	161.1	164.6
62.5°	121.7	121.8	123.9	126.2	128.6	133.3	138.3	142.5	144.8	146.0	149.3
65°	106.9	106.6	107.7	109.6	112.5	115.6	119.9	123.6	123.4	124.7	126.7
67.5°	91.8	91.4	91.4	93.2	95.5	98.3	101.2	103.4	103.4	105.0	106.1
70°	81.6	80.3	81.1	82.7	83.6	86.0	89.3	90.1	90.2	91.0	92.1
72.5°	71.1	70.6	71.2	71.9	72.6	74.4	77.2	77.7	77.8	78.2	79.9
75°	56.4	56.1	55.6	56.3	57.1	58.3	59.3	60.2	59.9	60.2	61.4
77.5°	42.4	41.2	40.9	41.3	41.5	42.3	43.3	43.2	43.4	43.4	44.8
80°	33.6	31.9	31.7	31.7	31.9	32.4	32.7	33.2	32.5	33.2	33.6
82.5°	24.7	23.7	23.6	23.5	23.5	23.6	23.9	24.1	24.0	24.3	24.5
85°	13.6	13.2	12.6	13.0	12.8	12.1	12.6	11.9	11.8	11.9	12.1
87.5°	7.0	7.0	6.5	6.2	5.9	5.8	5.3	4.8	4.5	4.4	4.5
90°	11.9	11.1	10.1	9.0	7.9	6.8	5.6	4.5	3.2	2.0	0.7
92.5°	11.9	11.1	10.2	9.3	8.3	7.3	7.3	8.1	9.0	9.9	10.7
95°	11.9	11.1	17.0	22.9	28.8	34.7	37.9	38.3	38.8	39.3	39.8
97.5°	30.0	34.3	45.9	57.6	69.3	81.0	86.3	85.5	84.6	83.8	83.0
100°	98.3	121.4	120.7	120.1	119.5	118.9	118.3	117.9	117.3	116.9	116.5
102.5°	150.4	154.8	154.4	154.1	153.7	153.3	152.8	152.2	151.7	151.1	150.5
105°	207.8	207.8	207.8	207.8	207.8	207.8	207.5	206.9	206.3	205.6	205.0
107.5°	263.1	263.1	262.7	262.4	262.1	261.8	261.6	261.6	261.6	261.6	261.6
110°	299.4	299.9	299.5	299.3	298.9	298.6	298.5	298.5	298.5	298.5	298.5



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	335.0	335.6	335.4	335.2	335.0	334.8	334.6	334.2	333.8	333.4	333.1
115°	388.5	389.1	389.0	388.8	388.7	388.5	388.1	387.3	386.5	385.8	385.0
117.5°	440.3	441.1	440.6	440.0	439.3	438.8	438.5	438.5	438.5	438.6	438.6
120°	473.2	473.5	473.1	472.6	472.1	471.6	471.4	471.6	471.8	472.0	472.1
122.5°	505.0	505.3	505.1	504.9	504.6	504.4	504.0	503.5	502.8	502.3	501.7
125°	551.7	552.3	552.3	552.3	552.3	552.3	551.8	550.7	549.6	548.5	547.4
127.5°	593.8	594.1	594.2	594.3	594.4	594.5	594.1	593.4	592.6	591.8	591.1
130°	621.6	622.1	621.9	621.7	621.6	621.4	621.0	620.2	619.4	618.7	617.9
132.5°	647.0	647.1	647.5	647.8	648.2	648.5	648.3	647.3	646.4	645.5	644.6
135°	685.2	685.5	685.8	686.1	686.4	686.7	686.4	685.5	684.6	683.7	682.7
137.5°	720.1	720.1	720.4	720.7	720.9	721.2	720.9	720.1	719.3	718.5	717.7
140°	741.6	741.3	741.5	741.6	741.7	741.9	741.8	741.5	741.2	740.9	740.6
142.5°	763.1	763.0	762.9	762.6	762.4	762.1	762.0	761.8	761.6	761.4	761.3
145°	793.1	792.9	792.9	792.9	792.9	792.9	792.7	792.5	792.1	791.8	791.5
147.5°	818.8	818.6	818.4	818.1	818.0	817.8	817.8	817.8	817.9	818.0	818.0
150°	835.1	834.7	834.5	834.1	833.8	833.5	833.5	833.8	834.1	834.5	834.7
152.5°	849.5	849.3	848.9	848.6	848.3	848.0	848.2	848.9	849.5	850.2	851.0
155°	869.3	868.9	868.6	868.3	868.0	867.6	868.0	868.9	869.9	870.8	871.7
157.5°	885.8	885.4	885.3	885.3	885.3	885.2	885.5	886.1	886.6	887.2	887.7
160°	896.0	895.4	895.3	895.1	894.9	894.8	895.2	896.1	897.1	898.0	898.9
162.5°	905.2	904.4	904.2	904.0	903.8	903.7	904.1	905.0	906.0	906.9	907.9
165°	917.3	916.3	916.1	916.1	915.9	915.7	916.1	917.0	917.9	918.9	919.8
167.5°	926.2	925.1	925.0	924.8	924.6	924.5	924.9	925.9	926.8	927.8	928.7
170°	930.9	929.6	929.4	929.3	929.1	929.0	929.4	930.5	931.6	932.6	933.8
172.5°	934.6	933.4	933.2	932.9	932.6	932.4	932.7	933.9	935.0	936.0	937.1
175°	938.5	937.3	937.1	936.9	936.7	936.7	937.0	938.0	938.9	939.8	940.8
177.5°	940.5	939.6	939.5	939.3	939.2	939.1	939.4	940.2	940.9	941.6	942.4
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	488.1	490.4	491.9	494.6	497.0	498.3	499.4	500.4	501.6	502.6	505.4
5°	491.2	496.6	501.1	508.1	514.5	519.4	524.8	529.5	533.4	539.0	543.3
7.5°	489.8	499.4	509.3	520.2	531.3	541.5	551.1	559.9	567.9	577.7	586.2
10°	488.6	501.5	514.2	529.0	543.9	556.7	568.6	580.9	589.7	602.1	612.6
12.5°	487.6	502.8	518.3	535.8	552.3	570.4	586.3	595.2	608.7	618.6	631.1
15°	483.4	503.5	524.8	544.6	568.1	584.8	598.8	616.1	628.7	641.2	654.8
17.5°	475.9	498.8	522.5	548.5	571.0	588.9	607.0	623.7	638.6	655.5	672.4
20°	472.4	495.3	522.5	549.1	571.1	589.9	608.4	626.8	643.3	664.9	684.5
22.5°	465.2	492.8	517.9	543.9	566.5	586.9	608.0	628.7	650.7	675.1	699.6
25°	452.3	480.3	506.8	532.4	555.3	580.9	603.3	631.2	659.2	691.5	722.0
27.5°	438.8	465.7	490.0	514.7	541.4	570.3	599.4	631.0	667.7	708.6	751.5
30°	427.9	453.3	477.0	502.3	530.1	562.7	594.7	632.1	674.6	720.5	771.7
32.5°	415.3	438.6	461.6	488.5	518.8	553.1	590.4	631.5	682.5	734.7	787.3
35°	393.5	413.1	436.8	465.5	499.6	539.0	582.1	630.7	689.2	749.2	793.4
37.5°	367.8	386.0	411.0	442.4	478.2	520.5	571.6	629.3	691.4	739.2	753.5
40°	350.4	367.4	393.3	425.9	462.5	507.3	563.3	624.3	684.5	715.0	703.2
42.5°	332.0	349.7	375.1	407.2	446.7	495.4	552.9	613.9	664.4	675.9	635.3
45°	302.9	321.2	346.2	378.7	421.2	473.9	533.9	589.3	618.3	597.5	534.7
47.5°	275.8	293.0	316.1	349.7	393.5	448.1	505.8	550.0	552.3	502.7	435.5
50°	257.3	273.2	296.5	330.1	373.5	428.8	480.9	515.8	500.1	443.8	379.3
52.5°	239.2	254.8	277.7	310.9	353.9	404.6	453.1	477.5	448.0	390.2	335.2
55°	213.0	226.7	249.1	279.8	320.6	367.6	408.8	417.2	378.9	322.1	277.3
57.5°	187.5	200.2	220.6	248.9	286.2	327.8	360.1	358.2	317.7	268.9	233.4
60°	170.2	182.5	200.7	228.3	262.3	298.2	325.7	319.1	279.0	236.9	207.1
62.5°	154.7	165.8	182.9	207.1	238.1	271.3	293.9	284.2	244.9	208.1	184.5
65°	131.9	141.2	155.8	176.4	202.2	229.5	247.1	234.5	200.9	172.3	153.3
67.5°	110.0	117.5	129.7	146.2	168.2	190.2	200.8	188.2	161.3	140.4	126.4
70°	96.2	102.8	112.3	126.9	146.1	164.6	172.6	161.3	138.2	120.3	110.2
72.5°	82.4	87.8	96.1	109.3	124.7	140.7	147.8	137.0	118.0	102.8	93.5
75°	63.7	67.4	73.1	82.2	94.3	107.2	111.0	101.6	89.4	78.1	71.9
77.5°	45.6	48.7	53.1	58.8	67.4	75.5	78.9	73.5	64.1	56.9	51.8
80°	35.0	36.6	40.4	45.1	51.9	57.1	59.3	55.8	49.2	43.9	39.9
82.5°	25.0	26.7	28.8	32.7	37.1	40.6	43.0	40.7	35.9	31.7	29.4
85°	12.1	13.2	14.4	16.1	19.4	21.4	21.2	19.8	17.9	16.3	15.1
87.5°	4.6	5.1	5.8	6.9	7.7	8.5	9.0	8.9	8.5	8.1	7.8
90°	2.0	3.2	4.5	5.6	6.8	7.9	9.0	10.1	11.1	11.9	12.8
92.5°	9.9	9.0	8.1	7.3	7.3	8.3	9.3	10.2	11.1	11.9	12.8
95°	39.3	38.8	38.3	37.9	34.7	28.8	22.9	17.0	11.1	11.9	12.8
97.5°	83.8	84.6	85.5	86.3	81.0	69.3	57.6	45.9	34.3	30.0	25.6
100°	116.9	117.3	117.9	118.3	118.9	119.5	120.1	120.7	121.4	98.3	75.2
102.5°	151.1	151.7	152.2	152.8	153.3	153.7	154.1	154.4	154.8	150.4	146.1
105°	205.6	206.3	206.9	207.5	207.8	207.8	207.8	207.8	207.8	207.8	207.8
107.5°	261.6	261.6	261.6	261.6	261.8	262.1	262.4	262.7	263.1	263.1	263.1
110°	298.5	298.5	298.5	298.5	298.6	298.9	299.3	299.5	299.9	299.4	298.9



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	333.4	333.8	334.2	334.6	334.8	335.0	335.2	335.4	335.6	335.0	334.4
115°	385.8	386.5	387.3	388.1	388.5	388.7	388.8	389.0	389.1	388.5	387.9
117.5°	438.6	438.5	438.5	438.5	438.8	439.3	440.0	440.6	441.1	440.3	439.5
120°	472.0	471.8	471.6	471.4	471.6	472.1	472.6	473.1	473.5	473.2	472.9
122.5°	502.3	502.8	503.5	504.0	504.4	504.6	504.9	505.1	505.3	505.0	504.7
125°	548.5	549.6	550.7	551.8	552.3	552.3	552.3	552.3	552.3	551.7	551.1
127.5°	591.8	592.6	593.4	594.1	594.5	594.4	594.3	594.2	594.1	593.8	593.4
130°	618.7	619.4	620.2	621.0	621.4	621.6	621.7	621.9	622.1	621.6	621.1
132.5°	645.5	646.4	647.3	648.3	648.5	648.2	647.8	647.5	647.1	647.0	646.9
135°	683.7	684.6	685.5	686.4	686.7	686.4	686.1	685.8	685.5	685.2	684.9
137.5°	718.5	719.3	720.1	720.9	721.2	720.9	720.7	720.4	720.1	720.1	720.2
140°	740.9	741.2	741.5	741.8	741.9	741.7	741.6	741.5	741.3	741.6	741.9
142.5°	761.4	761.6	761.8	762.0	762.1	762.4	762.6	762.9	763.0	763.1	763.2
145°	791.8	792.1	792.5	792.7	792.9	792.9	792.9	792.9	792.9	793.1	793.2
147.5°	818.0	817.9	817.8	817.8	817.8	818.0	818.1	818.4	818.6	818.8	818.9
150°	834.5	834.1	833.8	833.5	833.5	833.8	834.1	834.5	834.7	835.1	835.4
152.5°	850.2	849.5	848.9	848.2	848.0	848.3	848.6	848.9	849.3	849.5	849.9
155°	870.8	869.9	868.9	868.0	867.6	868.0	868.3	868.6	868.9	869.3	869.9
157.5°	887.2	886.6	886.1	885.5	885.2	885.3	885.3	885.3	885.4	885.8	886.4
160°	898.0	897.1	896.1	895.2	894.8	894.9	895.1	895.3	895.4	896.0	896.6
162.5°	906.9	906.0	905.0	904.1	903.7	903.8	904.0	904.2	904.4	905.2	906.1
165°	918.9	917.9	917.0	916.1	915.7	915.9	916.1	916.1	916.3	917.3	918.2
167.5°	927.8	926.8	925.9	924.9	924.5	924.6	924.8	925.0	925.1	926.2	927.4
170°	932.6	931.6	930.5	929.4	929.0	929.1	929.3	929.4	929.6	930.9	932.0
172.5°	936.0	935.0	933.9	932.7	932.4	932.6	932.9	933.2	933.4	934.6	935.7
175°	939.8	938.9	938.0	937.0	936.7	936.7	936.9	937.1	937.3	938.5	939.7
177.5°	941.6	940.9	940.2	939.4	939.1	939.2	939.3	939.5	939.6	940.5	941.4
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	507.7	509.0	511.8	510.9	512.1	512.8	513.4
5°	548.7	555.3	558.2	557.8	562.1	561.1	560.0
7.5°	595.0	601.9	605.8	610.6	613.4	613.7	616.1
10°	621.3	630.3	634.0	639.2	642.5	644.4	644.1
12.5°	641.3	648.5	656.7	659.2	663.7	666.1	665.2
15°	665.6	676.9	685.5	689.8	695.4	697.1	699.3
17.5°	687.2	702.3	712.4	725.9	730.9	734.1	732.2
20°	703.5	723.4	733.5	749.6	758.5	763.2	761.5
22.5°	722.7	744.4	763.0	776.9	790.4	796.8	798.2
25°	755.8	785.4	812.9	831.2	847.8	851.8	860.4
27.5°	792.7	827.7	857.0	876.3	887.9	892.2	895.0
30°	815.9	850.8	872.8	885.2	888.9	888.5	888.1
32.5°	827.3	849.1	853.4	849.9	841.4	834.2	826.7
35°	811.2	795.0	770.6	739.3	716.2	692.9	690.6
37.5°	729.6	677.5	637.0	591.8	565.8	549.7	538.5
40°	652.7	593.6	544.6	506.5	479.9	469.4	459.1
42.5°	569.4	512.8	469.4	437.6	417.6	405.9	397.8
45°	462.5	412.7	378.7	355.6	339.7	330.7	325.6
47.5°	379.1	342.1	313.3	296.6	285.7	278.7	278.7
50°	334.2	299.0	279.8	266.6	257.2	251.6	252.6
52.5°	294.4	268.1	251.8	240.8	233.7	230.3	230.2
55°	246.2	227.3	216.6	208.5	203.8	199.8	200.7
57.5°	210.6	194.7	187.4	180.7	177.5	175.9	173.6
60°	188.5	176.2	170.0	164.6	161.3	160.1	157.8
62.5°	168.9	159.2	153.2	148.8	145.9	145.4	143.7
65°	142.0	134.6	129.2	127.2	124.0	123.2	123.2
67.5°	117.0	111.7	107.5	105.7	104.3	104.5	103.5
70°	101.4	97.0	94.3	92.3	91.3	91.5	90.7
72.5°	88.7	83.8	81.5	80.3	78.9	79.5	79.1
75°	67.1	64.7	63.5	62.2	61.4	61.0	60.5
77.5°	49.3	47.2	46.2	45.5	45.7	44.6	45.4
80°	38.1	36.3	35.7	34.6	34.4	34.4	34.2
82.5°	27.9	26.8	26.4	25.6	25.1	25.5	25.0
85°	14.4	13.6	13.4	13.4	13.0	12.6	13.6
87.5°	7.9	7.5	7.6	7.5	7.6	7.6	7.3
90°	13.5	14.3	14.9	15.3	15.8	16.2	16.8
92.5°	13.5	14.3	14.7	15.0	15.2	15.4	15.6
95°	13.5	14.3	14.6	14.6	14.6	14.6	14.6
97.5°	21.2	16.9	14.6	14.6	14.6	14.6	14.6
100°	52.1	29.0	17.1	16.5	15.9	15.2	14.6
102.5°	141.7	137.3	129.9	119.3	108.8	98.3	87.7
105°	207.8	207.8	207.8	207.6	207.4	207.2	207.1
107.5°	263.1	263.1	263.0	262.5	262.0	261.5	261.1
110°	298.5	298.0	297.8	298.0	298.2	298.3	298.5



TEST NUMBER: P333133-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	333.8	333.2	332.8	332.6	332.3	332.2	332.0
115°	387.3	386.6	385.8	385.0	384.0	383.1	382.2
117.5°	438.7	437.9	437.3	436.9	436.5	436.1	435.7
120°	472.6	472.3	471.7	470.9	470.2	469.4	468.6
122.5°	504.4	504.1	503.5	502.6	501.7	500.8	499.9
125°	550.5	549.8	549.3	548.8	548.3	547.9	547.4
127.5°	593.2	592.8	592.0	590.9	589.8	588.6	587.5
130°	620.6	620.2	619.6	618.8	618.0	617.2	616.4
132.5°	646.8	646.8	646.3	645.6	644.8	644.0	643.3
135°	684.6	684.3	683.7	682.7	681.8	680.8	679.9
137.5°	720.2	720.3	720.0	719.2	718.4	717.6	716.8
140°	742.3	742.5	742.3	741.3	740.4	739.4	738.5
142.5°	763.2	763.3	762.9	762.0	761.0	760.1	759.1
145°	793.4	793.5	793.1	792.2	791.3	790.3	789.4
147.5°	819.1	819.3	818.9	817.7	816.6	815.5	814.4
150°	835.7	836.0	835.5	834.3	833.0	831.8	830.5
152.5°	850.2	850.5	850.1	849.0	847.8	846.8	845.6
155°	870.3	870.8	870.4	869.2	867.9	866.7	865.4
157.5°	886.9	887.3	887.0	885.7	884.5	883.2	882.0
160°	897.2	897.9	897.6	896.3	895.1	893.9	892.6
162.5°	907.0	907.8	907.6	906.2	904.8	903.5	902.1
165°	919.1	920.1	919.9	918.6	917.4	916.1	914.9
167.5°	928.4	929.6	929.4	928.0	926.7	925.2	923.9
170°	933.3	934.5	934.4	933.1	931.7	930.2	928.9
172.5°	936.8	938.0	937.8	936.4	935.0	933.6	932.2
175°	940.9	942.2	942.1	940.8	939.3	938.0	936.6
177.5°	942.2	943.1	943.1	942.0	941.0	940.0	939.1
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8

(END OF REPORT)