

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333139-940

Luminaire Tested: **S125DIP-S375D810U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333139-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D810U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4246.3 lumens
Efficiency: N/A
Efficacy: 136.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333139-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333139-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32					32			
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27					27			
2	85	78	72	67	76	70	65	61	56	53	50	43	41	38	31	29	28	22					22			
3	78	69	61	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19					19			
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16					16			
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14					14			
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12					12			
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11					11			
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10					10			
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	9					9			
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8					8			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3364	3364	3364
5°	3371	3339	3361
10°	3351	3316	3335
15°	3315	3276	3290
20°	3263	3221	3226
25°	3207	3154	3151
30°	3138	3082	3067
35°	3064	3005	2964
40°	2989	2922	2880
45°	2906	2846	2789
50°	2816	2753	2671
55°	2728	2649	2575
60°	2623	2545	2454
65°	2500	2419	2337
70°	2381	2274	2194
75°	2168	2099	2024
80°	1930	1901	1852
85°	1675	1712	1615



TEST NUMBER: P333139-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.1	1.2
10°-20°	138.7	3.3
20°-30°	204.9	4.8
30°-40°	239.0	5.6
40°-50°	240.1	5.7
50°-60°	210.7	5.0
60°-70°	157.0	3.7
70°-80°	89.8	2.1
80°-90°	28.1	0.7
90°-100°	34.2	0.8
100°-110°	210.7	5.0
110°-120°	382.1	9.0
120°-130°	490.4	11.5
130°-140°	527.5	12.4
140°-150°	495.1	11.7
150°-160°	400.5	9.4
160°-170°	259.0	6.1
170°-180°	89.3	2.1
0°-30°	392.7	9.2
0°-40°	631.7	14.9
0°-60°	1082.6	25.5
0°-90°	1357.5	32.0
90°-120°	627.0	14.8
90°-150°	2140.0	50.4
90°-180°	2889.0	68.0
0°-180°	4246.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	521	521	521	521	521	
5°	520	519	515	519	518	49
15°	496	494	490	492	492	140
25°	450	448	443	443	442	207
35°	389	387	381	379	376	243
45°	318	316	312	307	305	245
55°	242	241	235	232	229	216
65°	164	163	158	155	153	162
75°	87	86	84	83	81	93
85°	23	23	23	23	22	25
90°	1	6	11	15	17	3
95°	40	36	11	14	15	51
105°	205	208	208	208	207	217
115°	385	388	389	386	382	381
125°	547	552	552	550	547	489
135°	683	687	686	684	680	526
145°	792	793	793	793	789	495
155°	872	868	869	871	865	401
165°	920	916	916	920	915	260
175°	941	937	937	942	937	90
180°	941	941	941	941	941	



TEST NUMBER: P333139-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	522.2	522.0	521.8	521.6	521.4	520.8	520.1	519.4	518.7	517.9	518.7
5°	520.0	519.9	519.7	519.5	519.3	518.8	517.9	517.0	516.0	515.1	515.9
7.5°	515.3	515.1	515.0	514.8	514.6	514.0	513.0	511.9	511.0	510.0	510.8
10°	511.0	510.9	510.7	510.5	510.3	509.7	508.7	507.7	506.7	505.7	506.4
12.5°	505.8	505.4	505.1	504.8	504.4	503.8	502.8	501.9	501.0	500.1	500.6
15°	495.8	495.5	495.3	495.0	494.6	494.0	493.0	492.0	491.0	490.0	490.4
17.5°	484.3	483.9	483.5	483.1	482.7	482.0	480.9	479.9	478.8	477.8	478.4
20°	474.7	474.6	474.4	474.2	474.0	473.3	472.2	470.9	469.8	468.6	469.2
22.5°	465.2	464.8	464.5	464.2	463.9	463.2	462.0	460.9	459.8	458.7	459.1
25°	450.0	449.6	449.1	448.6	448.2	447.4	446.2	445.0	443.8	442.6	442.8
27.5°	432.3	432.0	431.8	431.5	431.2	430.4	429.3	428.0	426.8	425.5	425.6
30°	420.8	420.5	420.2	419.9	419.6	418.8	417.5	416.1	414.7	413.3	413.1
32.5°	408.2	407.8	407.4	407.0	406.5	405.7	404.5	403.2	402.1	400.8	400.5
35°	388.6	388.3	387.9	387.5	387.2	386.3	385.0	383.8	382.5	381.2	380.8
37.5°	368.3	367.8	367.4	366.8	366.4	365.6	364.4	363.2	361.9	360.8	360.1
40°	354.5	353.9	353.5	353.0	352.6	351.7	350.4	349.2	347.9	346.6	345.8
42.5°	339.6	339.2	338.9	338.4	338.0	337.2	335.9	334.7	333.3	332.1	331.4
45°	318.2	317.8	317.4	317.1	316.6	315.9	314.9	313.8	312.6	311.6	310.5
47.5°	295.1	295.1	295.1	295.2	295.2	294.5	293.2	291.9	290.5	289.2	288.1
50°	280.3	280.0	279.7	279.4	279.1	278.5	277.3	276.3	275.2	274.0	272.9
52.5°	265.1	264.8	264.7	264.5	264.3	263.6	262.4	261.3	260.0	258.9	257.9
55°	242.3	242.0	241.7	241.5	241.2	240.4	239.2	237.9	236.6	235.3	234.5
57.5°	218.4	218.2	218.0	217.9	217.8	217.1	216.1	215.0	213.9	212.9	211.8
60°	203.1	202.8	202.4	202.1	201.7	201.0	200.0	199.0	198.0	197.0	196.1
62.5°	187.3	187.1	186.7	186.5	186.2	185.6	184.8	183.9	183.0	182.2	181.2
65°	163.6	163.5	163.3	163.1	162.9	162.3	161.3	160.2	159.3	158.3	157.4
67.5°	140.6	140.3	139.8	139.5	139.1	138.5	137.8	137.0	136.3	135.5	134.8
70°	126.1	125.6	125.2	124.8	124.3	123.6	122.8	122.0	121.2	120.4	119.8
72.5°	110.3	109.9	109.7	109.3	109.1	108.6	108.1	107.5	107.0	106.5	105.8
75°	86.9	86.8	86.6	86.4	86.2	85.9	85.4	85.0	84.5	84.1	83.8
77.5°	65.5	65.4	65.3	65.2	65.2	65.0	64.7	64.5	64.2	63.9	63.8
80°	51.9	51.9	51.9	51.9	51.9	51.8	51.6	51.5	51.3	51.1	51.0
82.5°	40.0	39.9	39.8	39.6	39.5	39.4	39.3	39.3	39.2	39.2	39.1
85°	22.6	22.7	22.8	22.9	23.0	23.1	23.1	23.1	23.1	23.1	23.0
87.5°	9.0	9.3	9.5	9.8	10.1	10.3	10.3	10.5	10.7	10.8	11.0
90°	0.7	2.0	3.2	4.5	5.6	6.8	7.9	9.0	10.1	11.1	11.9
92.5°	10.7	9.9	9.0	8.1	7.3	7.3	8.3	9.3	10.2	11.1	11.9
95°	39.8	39.3	38.8	38.3	37.9	34.7	28.8	22.9	17.0	11.1	11.9
97.5°	83.0	83.8	84.6	85.5	86.3	81.0	69.3	57.6	45.9	34.3	30.0
100°	116.5	116.9	117.3	117.9	118.3	118.9	119.5	120.1	120.7	121.4	98.3
102.5°	150.5	151.1	151.7	152.2	152.8	153.3	153.7	154.1	154.4	154.8	150.4
105°	205.0	205.6	206.3	206.9	207.5	207.8	207.8	207.8	207.8	207.8	207.8
107.5°	261.6	261.6	261.6	261.6	261.6	261.8	262.1	262.4	262.7	263.1	263.1
110°	298.5	298.5	298.5	298.5	298.5	298.6	298.9	299.3	299.5	299.9	299.4



TEST NUMBER: P333139-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	333.1	333.4	333.8	334.2	334.6	334.8	335.0	335.2	335.4	335.6	335.0
115°	385.0	385.8	386.5	387.3	388.1	388.5	388.7	388.8	389.0	389.1	388.5
117.5°	438.6	438.6	438.5	438.5	438.5	438.8	439.3	440.0	440.6	441.1	440.3
120°	472.1	472.0	471.8	471.6	471.4	471.6	472.1	472.6	473.1	473.5	473.2
122.5°	501.7	502.3	502.8	503.5	504.0	504.4	504.6	504.9	505.1	505.3	505.0
125°	547.4	548.5	549.6	550.7	551.8	552.3	552.3	552.3	552.3	552.3	551.7
127.5°	591.1	591.8	592.6	593.4	594.1	594.5	594.4	594.3	594.2	594.1	593.8
130°	617.9	618.7	619.4	620.2	621.0	621.4	621.6	621.7	621.9	622.1	621.6
132.5°	644.6	645.5	646.4	647.3	648.3	648.5	648.2	647.8	647.5	647.1	647.0
135°	682.7	683.7	684.6	685.5	686.4	686.7	686.4	686.1	685.8	685.5	685.2
137.5°	717.7	718.5	719.3	720.1	720.9	721.2	720.9	720.7	720.4	720.1	720.1
140°	740.6	740.9	741.2	741.5	741.8	741.9	741.7	741.6	741.5	741.3	741.6
142.5°	761.3	761.4	761.6	761.8	762.0	762.1	762.4	762.6	762.9	763.0	763.1
145°	791.5	791.8	792.1	792.5	792.7	792.9	792.9	792.9	792.9	792.9	793.1
147.5°	818.0	818.0	817.9	817.8	817.8	817.8	818.0	818.1	818.4	818.6	818.8
150°	834.7	834.5	834.1	833.8	833.5	833.5	833.8	834.1	834.5	834.7	835.1
152.5°	851.0	850.2	849.5	848.9	848.2	848.0	848.3	848.6	848.9	849.3	849.5
155°	871.7	870.8	869.9	868.9	868.0	867.6	868.0	868.3	868.6	868.9	869.3
157.5°	887.7	887.2	886.6	886.1	885.5	885.2	885.3	885.3	885.3	885.4	885.8
160°	898.9	898.0	897.1	896.1	895.2	894.8	894.9	895.1	895.3	895.4	896.0
162.5°	907.9	906.9	906.0	905.0	904.1	903.7	903.8	904.0	904.2	904.4	905.2
165°	919.8	918.9	917.9	917.0	916.1	915.7	915.9	916.1	916.1	916.3	917.3
167.5°	928.7	927.8	926.8	925.9	924.9	924.5	924.6	924.8	925.0	925.1	926.2
170°	933.8	932.6	931.6	930.5	929.4	929.0	929.1	929.3	929.4	929.6	930.9
172.5°	937.1	936.0	935.0	933.9	932.7	932.4	932.6	932.9	933.2	933.4	934.6
175°	940.8	939.8	938.9	938.0	937.0	936.7	936.7	936.9	937.1	937.3	938.5
177.5°	942.4	941.6	940.9	940.2	939.4	939.1	939.2	939.3	939.5	939.6	940.5
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8



TEST NUMBER: P333139-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	519.4	520.1	520.8	521.2	521.1	521.0	521.0	520.9
5°	516.7	517.6	518.4	518.8	518.7	518.6	518.5	518.4
7.5°	511.6	512.4	513.2	513.5	513.4	513.4	513.3	513.2
10°	507.1	507.8	508.6	508.9	508.8	508.7	508.6	508.5
12.5°	501.2	501.9	502.4	502.7	502.7	502.7	502.7	502.6
15°	490.9	491.3	491.9	492.0	492.0	492.0	492.0	492.0
17.5°	478.9	479.5	480.1	480.1	479.7	479.2	478.8	478.3
20°	469.8	470.5	471.1	471.3	470.7	470.3	469.8	469.4
22.5°	459.5	459.9	460.4	460.4	460.1	459.8	459.5	459.1
25°	443.0	443.2	443.4	443.3	443.0	442.7	442.5	442.2
27.5°	425.6	425.6	425.7	425.6	425.3	425.0	424.7	424.5
30°	413.0	412.8	412.6	412.4	412.1	411.9	411.5	411.3
32.5°	400.2	399.8	399.5	399.1	398.6	398.1	397.6	397.1
35°	380.3	379.9	379.3	378.8	378.1	377.3	376.6	375.9
37.5°	359.4	358.7	358.0	357.5	357.0	356.7	356.2	355.8
40°	344.9	344.1	343.3	342.8	342.5	342.1	341.9	341.6
42.5°	330.6	329.8	329.0	328.5	328.1	327.6	327.3	326.8
45°	309.3	308.3	307.2	306.5	306.2	305.9	305.7	305.4
47.5°	287.0	285.9	284.7	283.8	283.2	282.6	282.0	281.3
50°	271.7	270.5	269.3	268.4	267.7	267.1	266.4	265.8
52.5°	256.8	255.7	254.7	253.9	253.2	252.4	251.7	251.0
55°	233.6	232.8	232.0	231.3	230.7	230.0	229.3	228.7
57.5°	210.7	209.6	208.6	207.9	207.5	207.1	206.8	206.4
60°	195.2	194.2	193.3	192.5	191.9	191.3	190.6	190.0
62.5°	180.2	179.1	178.2	177.5	177.0	176.5	175.9	175.5
65°	156.6	155.8	155.0	154.4	154.0	153.6	153.3	152.9
67.5°	134.1	133.4	132.7	132.2	132.1	131.8	131.6	131.3
70°	119.2	118.7	118.2	117.7	117.3	117.0	116.5	116.2
72.5°	105.2	104.6	104.0	103.5	103.2	102.8	102.4	102.0
75°	83.6	83.3	82.9	82.7	82.3	81.9	81.6	81.1
77.5°	63.7	63.5	63.3	63.1	62.9	62.6	62.3	62.1
80°	50.9	50.8	50.7	50.6	50.4	50.2	50.0	49.8
82.5°	38.9	38.7	38.6	38.4	38.4	38.4	38.3	38.3
85°	22.9	22.8	22.7	22.6	22.4	22.2	22.0	21.8
87.5°	11.1	11.2	11.4	11.5	11.4	11.3	11.3	11.2
90°	12.8	13.5	14.3	14.9	15.3	15.8	16.2	16.8
92.5°	12.8	13.5	14.3	14.7	15.0	15.2	15.4	15.6
95°	12.8	13.5	14.3	14.6	14.6	14.6	14.6	14.6
97.5°	25.6	21.2	16.9	14.6	14.6	14.6	14.6	14.6
100°	75.2	52.1	29.0	17.1	16.5	15.9	15.2	14.6
102.5°	146.1	141.7	137.3	129.9	119.3	108.8	98.3	87.7
105°	207.8	207.8	207.8	207.8	207.6	207.4	207.2	207.1
107.5°	263.1	263.1	263.1	263.0	262.5	262.0	261.5	261.1
110°	298.9	298.5	298.0	297.8	298.0	298.2	298.3	298.5



TEST NUMBER: P333139-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	334.4	333.8	333.2	332.8	332.6	332.3	332.2	332.0
115°	387.9	387.3	386.6	385.8	385.0	384.0	383.1	382.2
117.5°	439.5	438.7	437.9	437.3	436.9	436.5	436.1	435.7
120°	472.9	472.6	472.3	471.7	470.9	470.2	469.4	468.6
122.5°	504.7	504.4	504.1	503.5	502.6	501.7	500.8	499.9
125°	551.1	550.5	549.8	549.3	548.8	548.3	547.9	547.4
127.5°	593.4	593.2	592.8	592.0	590.9	589.8	588.6	587.5
130°	621.1	620.6	620.2	619.6	618.8	618.0	617.2	616.4
132.5°	646.9	646.8	646.8	646.3	645.6	644.8	644.0	643.3
135°	684.9	684.6	684.3	683.7	682.7	681.8	680.8	679.9
137.5°	720.2	720.2	720.3	720.0	719.2	718.4	717.6	716.8
140°	741.9	742.3	742.5	742.3	741.3	740.4	739.4	738.5
142.5°	763.2	763.2	763.3	762.9	762.0	761.0	760.1	759.1
145°	793.2	793.4	793.5	793.1	792.2	791.3	790.3	789.4
147.5°	818.9	819.1	819.3	818.9	817.7	816.6	815.5	814.4
150°	835.4	835.7	836.0	835.5	834.3	833.0	831.8	830.5
152.5°	849.9	850.2	850.5	850.1	849.0	847.8	846.8	845.6
155°	869.9	870.3	870.8	870.4	869.2	867.9	866.7	865.4
157.5°	886.4	886.9	887.3	887.0	885.7	884.5	883.2	882.0
160°	896.6	897.2	897.9	897.6	896.3	895.1	893.9	892.6
162.5°	906.1	907.0	907.8	907.6	906.2	904.8	903.5	902.1
165°	918.2	919.1	920.1	919.9	918.6	917.4	916.1	914.9
167.5°	927.4	928.4	929.6	929.4	928.0	926.7	925.2	923.9
170°	932.0	933.3	934.5	934.4	933.1	931.7	930.2	928.9
172.5°	935.7	936.8	938.0	937.8	936.4	935.0	933.6	932.2
175°	939.7	940.9	942.2	942.1	940.8	939.3	938.0	936.6
177.5°	941.4	942.2	943.1	943.1	942.0	941.0	940.0	939.1
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8

(END OF REPORT)