

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333141-940

Luminaire Tested: **S125DIP-S375D810U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333141-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D810U940-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3950.8 lumens
Efficiency: N/A
Efficacy: 126.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333141-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333141-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35	29
2	86	79	73	67	77	71	66	62	57	54	50	44	42	40	32	31	30	24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	34	29	27	25	20
4	71	61	53	47	64	55	49	43	45	40	36	35	31	29	26	23	22	17
5	65	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	48	41	35	54	44	37	32	36	31	27	28	24	22	21	18	16	13
7	56	44	36	30	50	40	33	28	32	27	24	25	22	19	19	17	15	12
8	52	40	32	27	46	36	29	25	29	24	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3364	3364	3364
5°	3371	3339	3361
10°	3351	3316	3335
15°	3315	3276	3290
20°	3263	3221	3226
25°	3207	3154	3151
30°	3138	3082	3067
35°	3064	3005	2964
40°	2989	2922	2880
45°	2906	2846	2789
50°	2816	2753	2671
55°	2728	2649	2575
60°	2623	2545	2454
65°	2500	2419	2337
70°	2381	2274	2194
75°	2168	2099	2024
80°	1930	1901	1852
85°	1675	1712	1615



TEST NUMBER: P333141-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.1	1.2
10°-20°	138.7	3.5
20°-30°	204.9	5.2
30°-40°	239.0	6.1
40°-50°	240.1	6.1
50°-60°	210.7	5.3
60°-70°	157.0	4.0
70°-80°	89.8	2.3
80°-90°	28.0	0.7
90°-100°	250.7	6.3
100°-110°	538.9	13.6
110°-120°	505.7	12.8
120°-130°	409.8	10.4
130°-140°	328.9	8.3
140°-150°	248.2	6.3
150°-160°	174.7	4.4
160°-170°	103.0	2.6
170°-180°	33.5	0.8
0°-30°	392.7	9.9
0°-40°	631.7	16.0
0°-60°	1082.6	27.4
0°-90°	1357.4	34.4
90°-120°	1295.2	32.8
90°-150°	2282.2	57.8
90°-180°	2593.0	65.6
0°-180°	3950.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	521	521	521	521	521	
5°	520	519	515	519	518	49
15°	496	494	490	492	492	140
25°	450	448	443	443	442	207
35°	389	387	381	379	376	243
45°	318	316	312	307	305	245
55°	242	241	235	232	229	216
65°	164	163	158	155	153	162
75°	87	86	84	83	81	93
85°	23	23	23	23	22	25
90°	1	6	11	15	16	3
95°	23	68	618	280	164	24
105°	79	110	506	995	924	83
115°	141	170	406	875	1029	139
125°	195	229	389	696	811	173
135°	229	275	386	583	674	178
145°	266	305	388	483	531	167
155°	304	327	378	427	446	140
165°	332	341	363	385	390	93
175°	345	345	348	352	351	33
180°	346	346	346	346	346	



TEST NUMBER: P333141-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	522.2	522.0	521.8	521.6	521.4	520.8	520.1	519.4	518.7	517.9	518.7
5°	520.0	519.9	519.7	519.5	519.3	518.8	517.9	517.0	516.0	515.1	515.9
7.5°	515.3	515.1	515.0	514.8	514.6	514.0	513.0	511.9	511.0	510.0	510.8
10°	511.0	510.9	510.7	510.5	510.3	509.7	508.7	507.7	506.7	505.7	506.4
12.5°	505.8	505.4	505.1	504.8	504.4	503.8	502.8	501.9	501.0	500.1	500.6
15°	495.8	495.5	495.3	495.0	494.6	494.0	493.0	492.0	491.0	490.0	490.4
17.5°	484.3	483.9	483.5	483.1	482.7	482.0	480.9	479.9	478.8	477.8	478.4
20°	474.7	474.6	474.4	474.2	474.0	473.3	472.2	470.9	469.8	468.6	469.2
22.5°	465.2	464.8	464.5	464.2	463.9	463.2	462.0	460.9	459.8	458.7	459.1
25°	450.0	449.6	449.1	448.6	448.2	447.4	446.2	445.0	443.8	442.6	442.8
27.5°	432.3	432.0	431.8	431.5	431.2	430.4	429.3	428.0	426.8	425.5	425.6
30°	420.8	420.5	420.2	419.9	419.6	418.8	417.5	416.1	414.7	413.3	413.1
32.5°	408.2	407.8	407.4	407.0	406.5	405.7	404.5	403.2	402.1	400.8	400.5
35°	388.6	388.3	387.9	387.5	387.2	386.3	385.0	383.8	382.5	381.2	380.8
37.5°	368.3	367.8	367.4	366.8	366.4	365.6	364.4	363.2	361.9	360.8	360.1
40°	354.5	353.9	353.5	353.0	352.6	351.7	350.4	349.2	347.9	346.6	345.8
42.5°	339.6	339.2	338.9	338.4	338.0	337.2	335.9	334.7	333.3	332.1	331.4
45°	318.2	317.8	317.4	317.1	316.6	315.9	314.9	313.8	312.6	311.6	310.5
47.5°	295.1	295.1	295.1	295.2	295.2	294.5	293.2	291.9	290.5	289.2	288.1
50°	280.3	280.0	279.7	279.4	279.1	278.5	277.3	276.3	275.2	274.0	272.9
52.5°	265.1	264.8	264.7	264.5	264.3	263.6	262.4	261.3	260.0	258.9	257.9
55°	242.3	242.0	241.7	241.5	241.2	240.4	239.2	237.9	236.6	235.3	234.5
57.5°	218.4	218.2	218.0	217.9	217.8	217.1	216.1	215.0	213.9	212.9	211.8
60°	203.1	202.8	202.4	202.1	201.7	201.0	200.0	199.0	198.0	197.0	196.1
62.5°	187.3	187.1	186.7	186.5	186.2	185.6	184.8	183.9	183.0	182.2	181.2
65°	163.6	163.5	163.3	163.1	162.9	162.3	161.3	160.2	159.3	158.3	157.4
67.5°	140.6	140.3	139.8	139.5	139.1	138.5	137.8	137.0	136.3	135.5	134.8
70°	126.1	125.6	125.2	124.8	124.3	123.6	122.8	122.0	121.2	120.4	119.8
72.5°	110.3	109.9	109.7	109.3	109.1	108.6	108.1	107.5	107.0	106.5	105.8
75°	86.9	86.8	86.6	86.4	86.2	85.9	85.4	85.0	84.5	84.1	83.8
77.5°	65.5	65.4	65.3	65.2	65.2	65.0	64.7	64.5	64.2	63.9	63.8
80°	51.9	51.9	51.9	51.9	51.9	51.8	51.6	51.5	51.3	51.1	51.0
82.5°	40.0	39.9	39.8	39.6	39.5	39.4	39.3	39.3	39.2	39.2	39.1
85°	22.6	22.7	22.8	22.9	23.0	23.1	23.1	23.1	23.1	23.1	23.0
87.5°	9.0	9.2	9.5	9.7	10.0	10.3	10.3	10.5	10.6	10.8	11.0
90°	0.7	1.4	2.8	4.2	5.6	7.0	7.7	9.1	9.7	11.1	11.9
92.5°	8.5	10.3	16.1	24.8	36.8	57.2	95.2	159.1	228.4	224.8	182.0
95°	23.0	23.7	29.2	36.9	52.3	83.6	158.3	311.7	504.1	617.8	604.5
97.5°	38.2	39.1	43.0	50.6	64.4	87.0	136.3	248.8	450.1	659.7	764.8
100°	48.8	50.2	53.0	60.6	73.9	94.8	135.3	225.9	401.6	629.6	803.9
102.5°	60.5	61.3	63.6	71.8	83.9	104.3	140.3	216.4	364.8	576.6	780.5
105°	78.8	78.8	82.3	89.3	100.4	119.9	150.6	212.7	329.1	505.5	705.6
107.5°	96.7	98.0	101.4	107.1	118.7	136.3	165.9	219.1	314.1	456.6	629.2
110°	109.5	110.8	113.6	119.9	130.4	148.5	177.1	225.2	309.6	433.6	585.7



TEST NUMBER: P333141-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	122.3	123.7	125.9	132.2	142.7	160.2	187.7	233.0	309.6	420.3	553.3
115°	140.8	142.2	144.4	150.6	161.0	178.5	204.3	244.7	311.7	405.8	518.0
117.5°	157.6	159.7	161.9	168.2	180.0	196.9	221.3	258.2	316.3	398.7	497.0
120°	168.7	170.9	173.6	179.9	191.7	209.2	233.5	267.1	320.7	395.3	485.3
122.5°	180.5	182.0	184.2	190.5	203.5	220.9	245.3	277.1	324.6	392.5	475.2
125°	195.2	196.6	200.1	206.3	219.6	237.7	260.7	290.7	331.2	389.1	461.5
127.5°	206.8	208.9	213.4	221.3	235.4	253.5	275.7	303.3	338.6	387.4	449.0
130°	214.0	216.2	221.7	230.8	245.4	263.6	285.2	311.7	343.0	386.3	440.7
132.5°	219.6	222.3	229.0	239.2	254.3	272.5	294.1	318.9	348.0	386.3	434.0
135°	228.7	231.5	239.9	251.0	265.6	284.5	306.1	329.1	354.9	386.3	426.0
137.5°	240.1	242.2	250.0	261.2	275.5	294.9	314.6	336.6	361.1	387.1	418.9
140°	246.8	248.9	257.3	268.4	281.7	300.5	320.7	341.6	363.9	387.6	415.5
142.5°	254.6	256.2	263.9	275.1	287.8	305.5	324.6	344.5	365.6	388.3	412.8
145°	266.4	267.7	274.7	284.5	297.0	313.1	331.2	348.6	367.5	387.6	408.6
147.5°	278.6	279.5	285.4	294.5	305.4	319.5	335.4	351.2	368.1	385.8	404.2
150°	285.9	287.2	292.1	301.2	310.9	322.8	338.1	352.8	368.1	384.1	400.9
152.5°	293.6	294.5	298.8	306.7	316.0	326.7	340.9	353.9	367.6	381.9	397.0
155°	304.0	304.0	308.2	315.1	322.1	331.9	343.8	354.9	366.0	377.9	390.5
157.5°	313.2	313.1	316.4	322.4	328.5	335.9	346.1	355.6	364.3	373.7	384.3
160°	319.3	318.6	321.5	326.3	331.9	338.1	347.2	355.6	362.6	371.0	379.3
162.5°	324.3	323.7	326.5	330.7	335.2	340.4	348.3	355.0	360.9	367.6	374.8
165°	331.9	330.5	332.6	336.1	338.9	343.0	348.6	354.2	358.4	362.6	368.1
167.5°	336.9	336.2	337.4	339.4	341.3	344.0	348.6	352.5	354.5	357.7	361.6
170°	340.3	339.6	340.3	341.6	343.0	345.1	348.6	351.4	352.8	354.9	357.7
172.5°	342.5	341.3	341.9	343.3	344.1	345.1	348.0	350.3	350.5	351.5	353.7
175°	345.1	343.8	344.5	345.1	345.1	345.1	347.2	348.6	347.9	347.9	348.6
177.5°	346.3	345.3	345.3	345.8	345.3	345.3	346.3	347.0	345.8	345.8	346.3
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333141-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	519.4	520.1	520.8	521.2	521.1	521.0	521.0	520.9
5°	516.7	517.6	518.4	518.8	518.7	518.6	518.5	518.4
7.5°	511.6	512.4	513.2	513.5	513.4	513.4	513.3	513.2
10°	507.1	507.8	508.6	508.9	508.8	508.7	508.6	508.5
12.5°	501.2	501.9	502.4	502.7	502.7	502.7	502.7	502.6
15°	490.9	491.3	491.9	492.0	492.0	492.0	492.0	492.0
17.5°	478.9	479.5	480.1	480.1	479.7	479.2	478.8	478.3
20°	469.8	470.5	471.1	471.3	470.7	470.3	469.8	469.4
22.5°	459.5	459.9	460.4	460.4	460.1	459.8	459.5	459.1
25°	443.0	443.2	443.4	443.3	443.0	442.7	442.5	442.2
27.5°	425.6	425.6	425.7	425.6	425.3	425.0	424.7	424.5
30°	413.0	412.8	412.6	412.4	412.1	411.9	411.5	411.3
32.5°	400.2	399.8	399.5	399.1	398.6	398.1	397.6	397.1
35°	380.3	379.9	379.3	378.8	378.1	377.3	376.6	375.9
37.5°	359.4	358.7	358.0	357.5	357.0	356.7	356.2	355.8
40°	344.9	344.1	343.3	342.8	342.5	342.1	341.9	341.6
42.5°	330.6	329.8	329.0	328.5	328.1	327.6	327.3	326.8
45°	309.3	308.3	307.2	306.5	306.2	305.9	305.7	305.4
47.5°	287.0	285.9	284.7	283.8	283.2	282.6	282.0	281.3
50°	271.7	270.5	269.3	268.4	267.7	267.1	266.4	265.8
52.5°	256.8	255.7	254.7	253.9	253.2	252.4	251.7	251.0
55°	233.6	232.8	232.0	231.3	230.7	230.0	229.3	228.7
57.5°	210.7	209.6	208.6	207.9	207.5	207.1	206.8	206.4
60°	195.2	194.2	193.3	192.5	191.9	191.3	190.6	190.0
62.5°	180.2	179.1	178.2	177.5	177.0	176.5	175.9	175.5
65°	156.6	155.8	155.0	154.4	154.0	153.6	153.3	152.9
67.5°	134.1	133.4	132.7	132.2	132.1	131.8	131.6	131.3
70°	119.2	118.7	118.2	117.7	117.3	117.0	116.5	116.2
72.5°	105.2	104.6	104.0	103.5	103.2	102.8	102.4	102.0
75°	83.6	83.3	82.9	82.7	82.3	81.9	81.6	81.1
77.5°	63.7	63.5	63.3	63.1	62.9	62.6	62.3	62.1
80°	50.9	50.8	50.7	50.6	50.4	50.2	50.0	49.8
82.5°	38.9	38.7	38.6	38.4	38.4	38.4	38.3	38.3
85°	22.9	22.8	22.7	22.6	22.4	22.2	22.0	21.8
87.5°	11.1	11.2	11.3	11.6	11.4	11.2	11.2	11.1
90°	12.6	13.3	13.9	15.3	15.3	15.3	16.1	16.1
92.5°	123.6	89.7	67.5	57.2	48.2	46.5	45.6	44.5
95°	501.3	395.3	309.6	251.0	201.5	180.6	175.0	163.8
97.5°	746.6	672.3	588.7	507.3	464.2	425.2	404.9	396.0
100°	857.6	823.4	751.6	679.1	631.0	580.8	555.0	543.9
102.5°	894.9	916.1	881.5	832.5	781.0	745.3	717.3	708.9
105°	872.9	968.5	999.2	991.5	969.1	946.1	932.2	923.8
107.5°	794.2	921.8	1000.5	1036.9	1048.2	1048.0	1043.5	1037.9
110°	736.3	868.7	967.1	1026.3	1057.7	1070.9	1075.8	1075.8



TEST NUMBER: P333141-940

CATALOG NUMBER: S125DIP-S375D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	690.5	816.3	915.7	985.6	1031.4	1054.2	1066.3	1071.4
115°	633.1	741.2	836.7	912.7	967.1	1000.5	1020.0	1029.1
117.5°	596.0	689.1	771.4	841.2	895.5	930.1	949.5	955.0
120°	575.9	659.6	736.3	797.6	849.2	882.7	901.5	907.0
122.5°	560.9	638.4	706.7	764.2	810.2	840.9	859.7	864.7
125°	539.0	610.1	670.7	720.9	760.0	788.5	803.9	810.8
127.5°	516.7	583.0	639.6	686.6	722.0	747.3	761.8	764.8
130°	502.7	564.1	618.4	663.8	698.7	721.7	735.6	739.8
132.5°	488.7	546.2	595.6	639.2	674.0	697.1	709.9	714.6
135°	470.6	518.7	563.4	603.1	633.7	656.7	669.3	673.5
137.5°	455.3	494.2	531.3	565.0	592.5	613.4	625.0	629.6
140°	446.9	479.7	511.8	541.0	566.9	585.0	595.4	598.9
142.5°	439.7	467.4	495.0	520.4	542.3	557.7	567.6	570.4
145°	430.2	451.8	473.4	492.2	509.0	520.8	528.5	531.3
147.5°	421.2	438.8	455.4	469.7	482.9	492.4	496.9	498.1
150°	416.3	431.6	444.8	457.4	467.9	476.2	479.0	479.7
152.5°	410.6	424.4	436.5	446.2	455.0	461.7	464.5	465.2
155°	402.3	413.5	423.2	430.9	437.8	442.7	444.8	445.5
157.5°	394.0	403.1	410.6	416.7	422.1	426.1	428.1	427.9
160°	388.3	395.3	402.3	407.2	412.1	415.5	417.0	416.3
162.5°	382.2	388.6	394.5	398.8	402.6	405.5	405.8	405.6
165°	373.7	378.6	382.8	386.3	389.1	390.5	390.5	390.5
167.5°	365.6	368.8	372.0	374.5	375.9	377.2	376.7	376.5
170°	361.1	363.3	365.3	366.8	368.1	368.8	368.8	368.1
172.5°	356.1	358.2	359.8	360.6	360.9	362.1	361.1	360.3
175°	350.7	350.7	352.1	352.1	352.1	352.8	351.4	350.7
177.5°	347.0	347.5	347.5	347.5	347.0	347.5	345.8	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8

(END OF REPORT)