

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333184-940

Luminaire Tested: **S125DIP-S610D810U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333184-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D810U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5119.2 lumens
Efficiency: N/A
Efficacy: 133.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333184-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333184-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	96	92	88	85	88	84	81	78	70	67	65	57	55	53	44	43	42	37
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36	31
3	80	71	63	57	73	65	58	53	54	49	45	44	40	38	34	32	30	26
4	73	62	55	49	67	57	50	45	48	43	39	39	35	32	31	28	26	22
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	32	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5531	5531	5531
5°	5544	5490	5525
10°	5509	5452	5483
15°	5449	5386	5409
20°	5364	5294	5304
25°	5273	5185	5181
30°	5158	5068	5043
35°	5037	4941	4872
40°	4912	4804	4736
45°	4778	4678	4585
50°	4629	4527	4391
55°	4486	4355	4234
60°	4314	4184	4035
65°	4109	3976	3842
70°	3914	3737	3609
75°	3566	3449	3331
80°	3172	3124	3046
85°	2764	2808	2660



TEST NUMBER: P333184-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.7	1.6
10°-20°	228.1	4.5
20°-30°	336.8	6.6
30°-40°	393.0	7.7
40°-50°	394.7	7.7
50°-60°	346.5	6.8
60°-70°	258.2	5.0
70°-80°	147.6	2.9
80°-90°	44.9	0.9
90°-100°	34.2	0.7
100°-110°	210.7	4.1
110°-120°	382.1	7.5
120°-130°	490.4	9.6
130°-140°	527.5	10.3
140°-150°	495.1	9.7
150°-160°	400.5	7.8
160°-170°	259.0	5.1
170°-180°	89.3	1.7
0°-30°	645.6	12.6
0°-40°	1038.6	20.3
0°-60°	1779.7	34.8
0°-90°	2230.4	43.6
90°-120°	627.0	12.2
90°-150°	2140.0	41.8
90°-180°	2889.0	56.4
0°-180°	5119.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	856	856	856	856	856	
5°	855	853	847	853	852	81
15°	815	813	806	809	809	230
25°	740	736	728	729	727	340
35°	639	636	627	623	618	399
45°	523	520	512	504	502	403
55°	398	396	387	381	376	356
65°	269	267	260	254	251	267
75°	143	142	138	136	134	152
85°	37	38	38	37	36	42
90°	1	6	11	15	17	4
95°	40	36	11	14	15	51
105°	205	208	208	208	207	217
115°	385	388	389	386	382	381
125°	547	552	552	550	547	489
135°	683	687	686	684	680	526
145°	792	793	793	793	789	495
155°	872	868	869	871	865	401
165°	920	916	916	920	915	260
175°	941	937	937	942	937	90
180°	941	941	941	941	941	



TEST NUMBER: P333184-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	858.5	858.2	857.8	857.5	857.1	856.3	855.2	853.9	852.7	851.5	852.7
5°	855.1	854.7	854.4	854.1	853.8	852.9	851.4	849.9	848.4	846.9	848.3
7.5°	847.1	846.9	846.6	846.2	846.0	845.0	843.3	841.7	840.0	838.4	839.6
10°	840.1	839.8	839.5	839.2	838.9	837.9	836.2	834.6	832.9	831.3	832.5
12.5°	831.4	830.9	830.4	829.8	829.3	828.2	826.7	825.2	823.6	822.1	823.0
15°	815.0	814.6	814.1	813.7	813.2	812.2	810.6	808.9	807.2	805.6	806.3
17.5°	796.2	795.6	794.9	794.2	793.5	792.4	790.7	788.9	787.2	785.5	786.4
20°	780.5	780.2	779.9	779.6	779.3	778.2	776.2	774.3	772.3	770.3	771.4
22.5°	764.7	764.2	763.7	763.1	762.6	761.4	759.6	757.8	755.9	754.0	754.7
25°	739.9	739.0	738.3	737.6	736.8	735.5	733.5	731.6	729.6	727.6	728.0
27.5°	710.7	710.2	709.8	709.4	708.9	707.7	705.6	703.6	701.6	699.6	699.6
30°	691.7	691.3	690.8	690.4	689.9	688.6	686.3	684.0	681.8	679.6	679.2
32.5°	671.1	670.5	669.8	669.1	668.3	667.0	665.0	663.0	660.9	659.0	658.4
35°	638.9	638.3	637.7	637.1	636.5	635.2	633.0	630.9	628.8	626.7	626.0
37.5°	605.4	604.7	604.0	603.2	602.4	601.0	599.1	597.1	595.0	593.1	592.0
40°	582.6	581.9	581.1	580.4	579.6	578.2	576.1	574.0	571.9	569.8	568.5
42.5°	558.3	557.7	557.0	556.3	555.7	554.4	552.2	550.2	548.0	545.9	544.7
45°	523.1	522.5	521.8	521.2	520.7	519.4	517.6	515.9	514.0	512.2	510.4
47.5°	485.1	485.1	485.2	485.2	485.2	484.1	482.0	479.8	477.7	475.5	473.7
50°	460.7	460.2	459.8	459.3	458.9	457.8	455.9	454.1	452.4	450.6	448.6
52.5°	435.8	435.4	435.2	434.8	434.4	433.3	431.4	429.4	427.6	425.6	423.9
55°	398.4	397.9	397.4	397.0	396.5	395.3	393.2	391.1	389.0	386.8	385.5
57.5°	358.9	358.7	358.5	358.2	358.0	357.0	355.2	353.4	351.6	349.9	348.1
60°	334.0	333.4	332.8	332.2	331.6	330.5	328.9	327.2	325.5	323.9	322.4
62.5°	308.0	307.6	307.0	306.6	306.0	305.1	303.7	302.3	300.9	299.4	297.8
65°	268.9	268.7	268.4	268.0	267.8	266.8	265.1	263.5	261.8	260.2	258.8
67.5°	231.1	230.5	229.9	229.3	228.6	227.7	226.5	225.2	224.0	222.7	221.6
70°	207.3	206.6	205.8	205.1	204.3	203.2	201.9	200.5	199.2	197.9	196.9
72.5°	181.3	180.7	180.3	179.8	179.2	178.5	177.7	176.8	175.9	175.0	174.1
75°	142.9	142.7	142.3	142.0	141.8	141.2	140.4	139.7	138.9	138.2	137.8
77.5°	107.6	107.5	107.4	107.2	107.1	106.8	106.4	106.0	105.6	105.1	104.9
80°	85.3	85.3	85.3	85.3	85.3	85.2	84.9	84.6	84.4	84.0	83.8
82.5°	65.9	65.6	65.4	65.1	64.9	64.7	64.6	64.6	64.6	64.5	64.2
85°	37.3	37.5	37.5	37.7	37.9	37.9	37.9	37.9	37.9	37.9	37.8
87.5°	14.8	15.0	15.2	15.5	15.8	16.0	16.1	16.1	16.2	16.3	16.5
90°	0.7	2.0	3.2	4.5	5.6	6.8	7.9	9.0	10.1	11.1	11.9
92.5°	10.7	9.9	9.0	8.1	7.3	7.3	8.3	9.3	10.2	11.1	11.9
95°	39.8	39.3	38.8	38.3	37.9	34.7	28.8	22.9	17.0	11.1	11.9
97.5°	83.0	83.8	84.6	85.5	86.3	81.0	69.3	57.6	45.9	34.3	30.0
100°	116.5	116.9	117.3	117.9	118.3	118.9	119.5	120.1	120.7	121.4	98.3
102.5°	150.5	151.1	151.7	152.2	152.8	153.3	153.7	154.1	154.4	154.8	150.4
105°	205.0	205.6	206.3	206.9	207.5	207.8	207.8	207.8	207.8	207.8	207.8
107.5°	261.6	261.6	261.6	261.6	261.6	261.8	262.1	262.4	262.7	263.1	263.1
110°	298.5	298.5	298.5	298.5	298.5	298.6	298.9	299.3	299.5	299.9	299.4



TEST NUMBER: P333184-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	333.1	333.4	333.8	334.2	334.6	334.8	335.0	335.2	335.4	335.6	335.0
115°	385.0	385.8	386.5	387.3	388.1	388.5	388.7	388.8	389.0	389.1	388.5
117.5°	438.6	438.6	438.5	438.5	438.5	438.8	439.3	440.0	440.6	441.1	440.3
120°	472.1	472.0	471.8	471.6	471.4	471.6	472.1	472.6	473.1	473.5	473.2
122.5°	501.7	502.3	502.8	503.5	504.0	504.4	504.6	504.9	505.1	505.3	505.0
125°	547.4	548.5	549.6	550.7	551.8	552.3	552.3	552.3	552.3	552.3	551.7
127.5°	591.1	591.8	592.6	593.4	594.1	594.5	594.4	594.3	594.2	594.1	593.8
130°	617.9	618.7	619.4	620.2	621.0	621.4	621.6	621.7	621.9	622.1	621.6
132.5°	644.6	645.5	646.4	647.3	648.3	648.5	648.2	647.8	647.5	647.1	647.0
135°	682.7	683.7	684.6	685.5	686.4	686.7	686.4	686.1	685.8	685.5	685.2
137.5°	717.7	718.5	719.3	720.1	720.9	721.2	720.9	720.7	720.4	720.1	720.1
140°	740.6	740.9	741.2	741.5	741.8	741.9	741.7	741.6	741.5	741.3	741.6
142.5°	761.3	761.4	761.6	761.8	762.0	762.1	762.4	762.6	762.9	763.0	763.1
145°	791.5	791.8	792.1	792.5	792.7	792.9	792.9	792.9	792.9	792.9	793.1
147.5°	818.0	818.0	817.9	817.8	817.8	817.8	818.0	818.1	818.4	818.6	818.8
150°	834.7	834.5	834.1	833.8	833.5	833.5	833.8	834.1	834.5	834.7	835.1
152.5°	851.0	850.2	849.5	848.9	848.2	848.0	848.3	848.6	848.9	849.3	849.5
155°	871.7	870.8	869.9	868.9	868.0	867.6	868.0	868.3	868.6	868.9	869.3
157.5°	887.7	887.2	886.6	886.1	885.5	885.2	885.3	885.3	885.3	885.4	885.8
160°	898.9	898.0	897.1	896.1	895.2	894.8	894.9	895.1	895.3	895.4	896.0
162.5°	907.9	906.9	906.0	905.0	904.1	903.7	903.8	904.0	904.2	904.4	905.2
165°	919.8	918.9	917.9	917.0	916.1	915.7	915.9	916.1	916.1	916.3	917.3
167.5°	928.7	927.8	926.8	925.9	924.9	924.5	924.6	924.8	925.0	925.1	926.2
170°	933.8	932.6	931.6	930.5	929.4	929.0	929.1	929.3	929.4	929.6	930.9
172.5°	937.1	936.0	935.0	933.9	932.7	932.4	932.6	932.9	933.2	933.4	934.6
175°	940.8	939.8	938.9	938.0	937.0	936.7	936.7	936.9	937.1	937.3	938.5
177.5°	942.4	941.6	940.9	940.2	939.4	939.1	939.2	939.3	939.5	939.6	940.5
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8



TEST NUMBER: P333184-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	853.9	855.2	856.3	856.8	856.8	856.6	856.5	856.4
5°	849.6	851.0	852.3	852.9	852.7	852.7	852.5	852.3
7.5°	841.0	842.3	843.6	844.3	844.1	843.9	843.8	843.6
10°	833.7	834.9	836.2	836.7	836.5	836.3	836.2	836.1
12.5°	824.0	825.0	825.9	826.4	826.3	826.3	826.3	826.3
15°	807.1	807.8	808.6	809.0	809.0	809.0	809.0	809.0
17.5°	787.4	788.3	789.3	789.3	788.5	787.8	787.1	786.3
20°	772.4	773.5	774.5	774.7	773.9	773.2	772.4	771.7
22.5°	755.5	756.2	756.9	757.0	756.4	755.9	755.4	754.9
25°	728.3	728.5	728.9	728.8	728.3	727.9	727.5	727.0
27.5°	699.7	699.8	699.8	699.6	699.2	698.7	698.3	697.9
30°	678.9	678.7	678.3	678.0	677.5	677.1	676.6	676.2
32.5°	657.9	657.3	656.7	656.1	655.3	654.5	653.6	652.8
35°	625.2	624.5	623.7	622.7	621.5	620.3	619.1	617.9
37.5°	590.8	589.8	588.6	587.7	587.0	586.4	585.7	585.0
40°	567.0	565.7	564.4	563.5	563.0	562.6	562.1	561.7
42.5°	543.5	542.2	541.0	540.0	539.3	538.7	538.0	537.3
45°	508.5	506.8	505.0	503.8	503.4	502.9	502.5	502.0
47.5°	471.8	469.9	468.1	466.7	465.7	464.6	463.5	462.4
50°	446.7	444.7	442.7	441.2	440.1	439.1	438.0	437.0
52.5°	422.1	420.4	418.7	417.3	416.2	414.9	413.8	412.6
55°	384.1	382.8	381.5	380.2	379.2	378.1	377.1	376.0
57.5°	346.3	344.6	342.9	341.7	341.2	340.5	340.0	339.5
60°	320.8	319.3	317.8	316.6	315.5	314.4	313.3	312.4
62.5°	296.2	294.6	292.9	291.8	291.0	290.1	289.3	288.5
65°	257.4	256.1	254.8	253.8	253.2	252.5	252.0	251.4
67.5°	220.5	219.4	218.2	217.4	217.0	216.7	216.3	216.0
70°	196.0	195.1	194.2	193.5	192.9	192.3	191.6	191.1
72.5°	173.0	172.0	170.9	170.1	169.5	169.0	168.4	167.7
75°	137.3	136.9	136.4	135.9	135.3	134.6	134.1	133.5
77.5°	104.6	104.3	104.1	103.7	103.3	102.9	102.5	102.0
80°	83.7	83.6	83.4	83.2	82.8	82.6	82.3	81.9
82.5°	63.9	63.7	63.4	63.2	63.2	63.1	63.0	63.0
85°	37.6	37.5	37.4	37.1	36.8	36.5	36.2	35.9
87.5°	16.7	16.8	16.9	16.9	16.8	16.7	16.5	16.3
90°	12.8	13.5	14.3	14.9	15.3	15.8	16.2	16.8
92.5°	12.8	13.5	14.3	14.7	15.0	15.2	15.4	15.6
95°	12.8	13.5	14.3	14.6	14.6	14.6	14.6	14.6
97.5°	25.6	21.2	16.9	14.6	14.6	14.6	14.6	14.6
100°	75.2	52.1	29.0	17.1	16.5	15.9	15.2	14.6
102.5°	146.1	141.7	137.3	129.9	119.3	108.8	98.3	87.7
105°	207.8	207.8	207.8	207.8	207.6	207.4	207.2	207.1
107.5°	263.1	263.1	263.1	263.0	262.5	262.0	261.5	261.1
110°	298.9	298.5	298.0	297.8	298.0	298.2	298.3	298.5



TEST NUMBER: P333184-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	334.4	333.8	333.2	332.8	332.6	332.3	332.2	332.0
115°	387.9	387.3	386.6	385.8	385.0	384.0	383.1	382.2
117.5°	439.5	438.7	437.9	437.3	436.9	436.5	436.1	435.7
120°	472.9	472.6	472.3	471.7	470.9	470.2	469.4	468.6
122.5°	504.7	504.4	504.1	503.5	502.6	501.7	500.8	499.9
125°	551.1	550.5	549.8	549.3	548.8	548.3	547.9	547.4
127.5°	593.4	593.2	592.8	592.0	590.9	589.8	588.6	587.5
130°	621.1	620.6	620.2	619.6	618.8	618.0	617.2	616.4
132.5°	646.9	646.8	646.8	646.3	645.6	644.8	644.0	643.3
135°	684.9	684.6	684.3	683.7	682.7	681.8	680.8	679.9
137.5°	720.2	720.2	720.3	720.0	719.2	718.4	717.6	716.8
140°	741.9	742.3	742.5	742.3	741.3	740.4	739.4	738.5
142.5°	763.2	763.2	763.3	762.9	762.0	761.0	760.1	759.1
145°	793.2	793.4	793.5	793.1	792.2	791.3	790.3	789.4
147.5°	818.9	819.1	819.3	818.9	817.7	816.6	815.5	814.4
150°	835.4	835.7	836.0	835.5	834.3	833.0	831.8	830.5
152.5°	849.9	850.2	850.5	850.1	849.0	847.8	846.8	845.6
155°	869.9	870.3	870.8	870.4	869.2	867.9	866.7	865.4
157.5°	886.4	886.9	887.3	887.0	885.7	884.5	883.2	882.0
160°	896.6	897.2	897.9	897.6	896.3	895.1	893.9	892.6
162.5°	906.1	907.0	907.8	907.6	906.2	904.8	903.5	902.1
165°	918.2	919.1	920.1	919.9	918.6	917.4	916.1	914.9
167.5°	927.4	928.4	929.6	929.4	928.0	926.7	925.2	923.9
170°	932.0	933.3	934.5	934.4	933.1	931.7	930.2	928.9
172.5°	935.7	936.8	938.0	937.8	936.4	935.0	933.6	932.2
175°	939.7	940.9	942.2	942.1	940.8	939.3	938.0	936.6
177.5°	941.4	942.2	943.1	943.1	942.0	941.0	940.0	939.1
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8

(END OF REPORT)