

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333134

Luminaire Tested: **S125DIP-S375D810U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333134
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D810U835-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4342.2 lumens
Efficiency: N/A
Efficacy: 139.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35																												
1	95	91	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30																												
2	86	79	73	68	78	72	67	63	58	55	51	45	43	41	34	32	31	25																												
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22																												
4	72	62	54	48	65	56	49	44	46	41	37	36	32	30	27	25	23	19																												
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16																												
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	17	14																												
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	17	16	13																												
8	52	40	33	27	47	37	30	25	30	25	22	24	20	18	18	16	14	11																												
9	48	36	29	24	44	33	27	23	28	23	19	22	18	16	17	14	13	10																												
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	16	13	11	9																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3516	3516	3516	3516
5°	4071	3528	3089	3528
10°	4737	3510	2706	3510
15°	5243	3484	2497	3484
20°	5869	3443	2328	3443
25°	6876	3397	2246	3397
30°	7427	3351	2175	3351
35°	6106	3266	2128	3266
40°	4340	3148	2076	3148
45°	3335	2988	2047	2988
50°	2846	2790	2043	2790
55°	2535	2597	2061	2597
60°	2286	2384	2113	2384
65°	2112	2172	2168	2172
70°	1920	1951	2200	1951
75°	1694	1719	2178	1719
80°	1428	1402	1993	1402
85°	1134	1008	1608	1008



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	1.2
10°-20°	156.0	3.6
20°-30°	253.4	5.8
30°-40°	309.1	7.1
40°-50°	281.2	6.5
50°-60°	224.0	5.2
60°-70°	156.0	3.6
70°-80°	83.2	1.9
80°-90°	23.2	0.5
90°-100°	67.3	1.5
100°-110°	198.7	4.6
110°-120°	336.6	7.8
120°-130°	443.0	10.2
130°-140°	496.4	11.4
140°-150°	486.5	11.2
150°-160°	408.6	9.4
160°-170°	271.6	6.3
170°-180°	95.1	2.2
0°-30°	461.8	10.6
0°-40°	770.9	17.8
0°-60°	1276.0	29.4
0°-90°	1538.4	35.4
90°-120°	602.7	13.9
90°-150°	2028.6	46.7
90°-180°	2804.0	64.6
0°-180°	4342.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	544	544	544	544	544	
5°	628	544	476	544	628	63
15°	784	521	373	521	784	224
25°	965	477	315	477	965	441
35°	774	414	270	414	774	474
45°	365	327	224	327	365	292
55°	225	231	183	231	225	203
65°	138	142	142	142	138	137
75°	68	69	87	69	68	73
85°	15	14	22	14	15	18
90°	19	1	19	1	19	11
95°	67	51	67	51	67	68
105°	194	178	194	178	194	205
115°	340	337	340	337	340	336
125°	495	492	495	492	495	442
135°	642	640	642	640	642	495
145°	778	775	778	775	778	486
155°	887	887	887	887	887	408
165°	962	964	962	964	962	271
175°	999	1002	999	1002	999	95
180°	1005	1005	1005	1005	1005	



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	575.8	575.1	574.3	572.9	574.0	570.8	569.4	566.8	563.6	562.5	561.2
5°	628.0	629.2	630.4	625.5	626.0	622.7	615.3	609.3	604.5	598.2	593.8
7.5°	690.9	688.2	687.9	684.8	679.4	675.0	667.3	657.4	647.8	636.9	627.9
10°	722.3	722.6	720.5	716.8	711.0	706.8	696.7	687.0	675.2	661.3	651.4
12.5°	746.0	747.0	744.3	739.3	736.5	727.2	719.2	707.7	693.7	682.6	667.5
15°	784.2	781.7	779.9	773.6	768.8	759.1	746.4	734.3	719.1	705.0	690.9
17.5°	821.1	823.2	819.7	814.0	798.9	787.6	770.6	754.1	735.1	716.2	699.4
20°	854.0	855.9	850.6	840.6	822.6	811.3	788.9	767.6	745.7	721.4	702.9
22.5°	895.1	893.6	886.4	871.3	855.7	834.8	810.5	784.6	757.1	729.7	705.1
25°	964.9	955.2	950.8	932.1	911.6	880.8	847.6	809.7	775.5	739.2	707.8
27.5°	1003.7	1000.6	995.7	982.7	961.1	928.2	889.0	842.8	794.6	748.8	707.6
30°	995.9	996.4	996.8	992.7	978.8	954.1	915.0	865.4	808.0	756.5	708.9
32.5°	927.1	935.5	943.6	953.1	957.0	952.2	927.8	882.9	823.9	765.4	708.2
35°	774.5	777.1	803.2	829.1	864.2	891.5	909.7	889.8	840.2	772.9	707.3
37.5°	603.9	616.4	634.5	663.7	714.4	759.8	818.2	845.0	829.0	775.4	705.7
40°	514.8	526.4	538.2	568.0	610.7	665.7	732.0	788.6	801.8	767.6	700.1
42.5°	446.1	455.2	468.3	490.7	526.4	575.1	638.5	712.5	758.0	745.1	688.5
45°	365.1	370.9	381.0	398.8	424.7	462.8	518.7	599.6	670.1	693.4	660.9
47.5°	312.5	312.5	320.4	332.6	351.3	383.7	425.1	488.4	563.7	619.4	616.8
50°	283.3	282.1	288.4	299.0	313.8	335.3	374.8	425.4	497.7	560.8	578.4
52.5°	258.1	258.3	262.1	270.0	282.4	300.7	330.2	375.9	437.6	502.4	535.5
55°	225.1	224.1	228.5	233.8	242.9	254.9	276.1	311.0	361.2	424.9	467.9
57.5°	194.7	197.3	199.0	202.7	210.2	218.3	236.2	261.8	301.6	356.3	401.7
60°	177.0	179.5	180.9	184.6	190.6	197.6	211.4	232.2	265.7	312.9	357.9
62.5°	161.1	163.1	163.6	166.9	171.8	178.5	189.4	206.9	233.4	274.6	318.7
65°	138.2	138.2	139.1	142.6	144.9	150.9	159.2	171.9	193.2	225.3	263.0
67.5°	116.1	117.2	117.0	118.5	120.6	125.3	131.2	141.7	157.5	180.9	211.1
70°	101.7	102.6	102.4	103.5	105.8	108.8	113.7	123.6	134.9	155.0	180.9
72.5°	88.7	89.1	88.5	90.0	91.4	94.0	99.5	104.8	115.3	132.3	153.6
75°	67.9	68.4	68.9	69.8	71.2	72.6	75.3	80.6	87.6	100.3	113.9
77.5°	50.9	50.0	51.2	51.0	51.8	52.9	55.3	58.1	63.8	71.9	82.4
80°	38.4	38.6	38.6	38.8	40.0	40.7	42.7	44.8	49.2	55.2	62.6
82.5°	28.0	28.6	28.2	28.7	29.6	30.1	31.3	33.0	35.5	40.3	45.6
85°	15.3	14.1	14.6	15.0	15.0	15.3	16.2	16.9	18.3	20.1	22.2
87.5°	8.2	8.5	8.5	8.4	8.5	8.4	8.9	8.8	9.1	9.5	10.0
90°	18.8	18.2	17.7	17.2	16.7	16.0	15.1	14.2	13.4	12.5	11.3
92.5°	36.9	36.5	36.1	35.8	35.4	34.6	33.5	32.3	31.2	30.0	28.5
95°	67.2	66.9	66.6	66.2	65.9	65.1	63.9	62.6	61.4	60.2	58.5
97.5°	102.0	101.8	101.5	101.3	101.1	100.5	99.3	98.2	97.0	95.9	93.5
100°	128.2	127.9	127.5	127.2	126.9	125.9	124.3	122.8	121.2	119.6	117.4
102.5°	154.5	154.0	153.5	153.1	152.6	151.5	149.8	148.1	146.4	144.7	143.5
105°	193.9	193.4	192.9	192.4	191.8	191.1	190.0	189.0	187.9	186.9	185.8
107.5°	234.3	234.3	234.3	234.4	234.4	234.2	233.6	233.1	232.6	232.1	231.3
110°	264.3	264.5	264.6	264.8	265.0	264.8	264.3	263.8	263.3	262.7	262.2



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	293.7	294.0	294.3	294.6	295.0	295.0	294.7	294.5	294.3	294.0	293.4
115°	340.2	340.3	340.5	340.7	340.8	341.0	341.2	341.4	341.5	341.7	341.4
117.5°	385.5	386.2	386.9	387.6	388.3	388.6	388.4	388.3	388.1	388.0	387.7
120°	416.8	417.5	418.2	418.9	419.6	419.9	419.9	419.9	419.9	419.9	419.7
122.5°	448.1	448.6	449.2	449.7	450.3	450.6	450.8	450.9	451.0	451.2	450.7
125°	495.0	495.2	495.3	495.5	495.7	495.9	496.3	496.6	497.0	497.3	497.1
127.5°	540.0	540.4	540.7	541.1	541.4	541.7	541.8	542.0	542.2	542.4	542.2
130°	570.0	570.4	570.7	571.1	571.4	571.7	571.9	572.0	572.2	572.4	572.0
132.5°	598.2	598.7	599.2	599.7	600.1	600.5	600.6	600.8	601.0	601.2	601.2
135°	642.0	642.7	643.4	644.1	644.8	645.1	645.1	645.1	645.1	645.1	644.9
137.5°	684.8	685.7	686.6	687.4	688.3	688.6	688.4	688.2	688.0	687.8	687.4
140°	712.4	713.2	714.1	715.0	715.8	716.1	715.7	715.4	715.1	714.7	714.2
142.5°	738.6	739.5	740.4	741.2	742.1	742.4	742.2	742.0	741.8	741.6	740.9
145°	778.0	778.6	779.1	779.6	780.1	780.4	780.4	780.4	780.4	780.4	779.9
147.5°	811.7	812.9	814.0	815.2	816.4	816.8	816.4	815.9	815.5	815.1	814.7
150°	836.7	837.0	837.4	837.7	838.1	838.3	838.3	838.3	838.3	838.3	837.6
152.5°	857.3	858.0	858.6	859.2	859.8	859.9	859.5	859.1	858.7	858.3	858.0
155°	886.7	887.6	888.5	889.3	890.2	890.3	889.6	888.9	888.2	887.5	887.3
157.5°	911.3	912.4	913.6	914.7	915.9	916.1	915.4	914.7	914.0	913.3	913.1
160°	928.2	929.0	929.9	930.8	931.7	931.7	931.0	930.4	929.7	929.0	928.8
162.5°	942.6	943.6	944.6	945.6	946.6	946.7	945.9	945.0	944.2	943.4	943.3
165°	961.8	962.8	963.9	964.9	966.0	966.1	965.5	964.8	964.1	963.4	963.2
167.5°	977.1	978.2	979.3	980.4	981.4	981.5	980.4	979.4	978.3	977.3	977.3
170°	985.3	986.5	987.7	988.9	990.1	990.2	989.2	988.1	987.1	986.0	986.0
172.5°	992.1	993.2	994.3	995.4	996.5	996.5	995.4	994.4	993.3	992.3	992.3
175°	998.6	999.8	1001.0	1002.2	1003.4	1003.5	1002.5	1001.4	1000.4	999.3	999.3
177.5°	1002.3	1003.3	1004.3	1005.2	1006.2	1006.3	1005.4	1004.6	1003.8	1002.9	1003.1
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	560.1	558.8	557.3	554.7	551.6	549.9	547.4	545.7	542.4	539.6	536.6
5°	588.5	582.5	577.0	569.8	562.0	556.9	550.9	544.2	537.2	530.1	522.2
7.5°	618.0	607.3	595.8	583.4	571.2	560.0	549.3	538.9	529.1	517.2	507.2
10°	637.7	624.3	610.0	593.2	576.7	562.4	547.9	535.2	522.2	508.4	496.1
12.5°	657.5	639.7	619.4	600.9	581.2	563.9	546.8	530.5	514.3	498.9	484.6
15°	671.5	655.8	637.1	610.7	588.5	564.7	542.1	521.1	501.4	484.3	466.3
17.5°	680.7	660.4	640.3	615.1	586.0	559.4	533.7	509.6	487.5	465.8	448.5
20°	682.3	661.5	640.5	615.8	586.0	555.5	529.8	501.0	477.2	454.7	433.5
22.5°	681.8	658.2	635.3	609.9	580.8	552.7	521.7	492.3	466.4	444.4	422.2
25°	676.6	651.4	622.7	597.1	568.4	538.6	507.2	476.7	450.4	425.2	403.2
27.5°	672.2	639.6	607.1	577.2	549.5	522.2	492.1	460.9	431.7	406.2	385.5
30°	666.9	631.0	594.5	563.3	534.9	508.4	479.9	449.4	418.9	394.0	371.8
32.5°	662.1	620.3	581.8	547.8	517.7	491.9	465.7	436.7	406.7	381.4	359.2
35°	652.8	604.5	560.3	522.0	489.9	463.3	441.3	414.3	386.8	362.3	341.1
37.5°	641.0	583.7	536.3	496.1	460.9	432.9	412.5	391.7	365.3	341.7	322.5
40°	631.7	568.9	518.7	477.6	441.1	412.0	393.0	373.4	351.5	329.5	309.2
42.5°	620.1	555.6	501.0	456.7	420.6	392.2	372.3	355.7	336.3	315.8	297.0
45°	598.7	531.5	472.3	424.7	388.2	360.2	339.7	327.2	312.6	293.2	277.3
47.5°	567.2	502.5	441.3	392.2	354.5	328.6	309.3	297.3	287.1	272.7	258.2
50°	539.3	480.9	418.9	370.2	332.5	306.4	288.6	277.7	269.0	257.9	245.6
52.5°	508.1	453.7	396.9	348.7	311.4	285.7	268.3	258.7	251.4	243.5	231.4
55°	458.4	412.2	359.5	313.8	279.4	254.2	238.9	230.6	224.6	218.6	211.2
57.5°	403.8	367.6	321.0	279.1	247.4	224.5	210.3	202.2	197.5	194.4	190.1
60°	365.3	334.4	294.2	256.0	225.1	204.7	190.9	184.6	180.7	178.2	174.9
62.5°	329.6	304.2	267.0	232.2	205.1	185.9	173.5	167.4	163.7	162.4	159.8
65°	277.1	257.4	226.7	197.8	174.7	158.3	147.9	142.1	139.8	138.4	138.6
67.5°	225.2	213.3	188.6	164.0	145.5	131.8	123.4	119.0	117.8	116.0	116.0
70°	193.6	184.6	163.8	142.3	125.9	115.3	107.9	103.3	102.1	101.2	101.0
72.5°	165.7	157.8	139.8	122.6	107.8	98.5	92.4	89.6	87.7	87.2	87.1
75°	124.5	120.2	105.8	92.2	82.0	75.6	71.4	68.9	67.5	67.2	67.5
77.5°	88.5	84.7	75.6	65.9	59.5	54.6	51.1	50.2	48.7	48.7	48.5
80°	66.5	64.0	58.2	50.6	45.3	41.1	39.3	37.7	37.2	36.5	37.2
82.5°	48.2	45.5	41.6	36.7	32.3	29.9	28.0	27.5	27.2	26.9	27.0
85°	23.8	24.0	21.7	18.0	16.2	14.8	13.6	13.6	13.4	13.2	13.4
87.5°	10.1	9.5	8.6	7.7	6.5	5.7	5.2	5.1	4.9	5.0	5.4
90°	10.1	8.9	7.6	6.3	5.0	3.6	2.2	0.8	2.2	3.6	5.0
92.5°	27.0	25.5	24.0	22.8	21.8	20.9	19.9	18.9	19.9	20.9	21.8
95°	56.7	55.0	53.3	52.2	51.9	51.5	51.2	50.8	51.2	51.5	51.9
97.5°	91.1	88.7	86.3	85.0	84.9	84.7	84.6	84.5	84.6	84.7	84.9
100°	115.1	112.9	110.6	109.5	109.5	109.5	109.5	109.5	109.5	109.5	109.5
102.5°	142.4	141.2	140.1	139.2	138.5	137.8	137.1	136.4	137.1	137.8	138.5
105°	184.8	183.8	182.7	181.8	180.9	180.0	179.2	178.3	179.2	180.0	180.9
107.5°	230.5	229.7	228.9	228.1	227.2	226.3	225.4	224.6	225.4	226.3	227.2
110°	261.7	261.2	260.7	260.0	259.1	258.2	257.4	256.5	257.4	258.2	259.1



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	292.7	292.0	291.4	290.8	290.4	289.9	289.5	289.0	289.5	289.9	290.4
115°	341.0	340.7	340.3	339.8	339.1	338.4	337.7	337.0	337.7	338.4	339.1
117.5°	387.4	387.1	386.8	386.4	386.1	385.8	385.5	385.2	385.5	385.8	386.1
120°	419.6	419.4	419.2	418.7	417.8	417.0	416.1	415.2	416.1	417.0	417.8
122.5°	450.3	449.8	449.4	449.0	448.7	448.4	448.1	447.7	448.1	448.4	448.7
125°	497.0	496.8	496.6	496.0	495.0	493.9	492.9	491.8	492.9	493.9	495.0
127.5°	541.9	541.7	541.5	541.1	540.5	539.9	539.4	538.8	539.4	539.9	540.5
130°	571.7	571.3	571.0	570.4	569.5	568.7	567.8	566.9	567.8	568.7	569.5
132.5°	601.3	601.4	601.4	600.8	599.3	597.9	596.5	595.1	596.5	597.9	599.3
135°	644.8	644.6	644.4	643.8	642.8	641.7	640.7	639.6	640.7	641.7	642.8
137.5°	687.0	686.7	686.3	685.6	684.6	683.6	682.6	681.6	682.6	683.6	684.6
140°	713.7	713.1	712.6	711.9	711.1	710.2	709.3	708.5	709.3	710.2	711.1
142.5°	740.3	739.6	739.0	738.3	737.5	736.8	736.1	735.4	736.1	736.8	737.5
145°	779.3	778.8	778.3	777.7	777.0	776.3	775.6	774.9	775.6	776.3	777.0
147.5°	814.3	813.9	813.4	813.0	812.7	812.3	811.9	811.5	811.9	812.3	812.7
150°	836.9	836.2	835.5	835.2	835.4	835.6	835.7	835.9	835.7	835.6	835.4
152.5°	857.7	857.4	857.2	856.9	856.7	856.4	856.2	855.9	856.2	856.4	856.7
155°	887.2	887.0	886.8	886.7	886.7	886.7	886.7	886.7	886.7	886.7	886.7
157.5°	913.0	912.8	912.6	912.7	913.1	913.5	913.9	914.3	913.9	913.5	913.1
160°	928.6	928.4	928.3	928.4	929.0	929.5	930.0	930.5	930.0	929.5	929.0
162.5°	943.3	943.2	943.2	943.4	943.8	944.1	944.5	944.9	944.5	944.1	943.8
165°	963.0	962.8	962.7	962.8	963.1	963.5	963.8	964.2	963.8	963.5	963.1
167.5°	977.3	977.3	977.3	977.6	978.3	979.0	979.7	980.4	979.7	979.0	978.3
170°	986.0	986.0	986.0	986.4	987.1	987.8	988.5	989.2	988.5	987.8	987.1
172.5°	992.3	992.3	992.3	992.6	993.3	994.0	994.7	995.4	994.7	994.0	993.3
175°	999.3	999.3	999.3	999.7	1000.4	1001.1	1001.8	1002.5	1001.8	1001.1	1000.4
177.5°	1003.2	1003.4	1003.5	1003.8	1004.4	1005.0	1005.5	1006.1	1005.5	1005.0	1004.4
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	535.0	532.9	531.3	527.6	525.5	522.8	520.6	523.0	520.4	521.5	519.8
5°	518.3	511.8	507.2	500.5	494.7	489.4	485.5	484.8	482.9	482.0	479.2
7.5°	498.2	490.1	482.2	473.4	466.0	458.5	453.7	449.7	447.1	443.6	441.2
10°	486.4	475.5	466.3	455.7	446.4	438.3	431.9	428.6	425.6	421.2	419.6
12.5°	471.8	460.6	449.3	437.9	429.0	420.0	414.5	409.6	407.5	402.6	402.1
15°	454.3	437.4	426.3	414.8	402.5	395.1	390.5	385.2	382.9	379.4	376.9
17.5°	433.4	418.3	404.5	392.5	382.0	375.8	370.0	366.4	362.4	360.1	356.0
20°	418.2	403.9	390.0	377.3	369.2	362.1	357.5	354.0	349.8	348.7	344.5
22.5°	405.5	389.7	376.4	365.7	356.9	348.8	343.8	341.4	338.6	335.0	334.2
25°	384.7	368.3	357.0	346.4	338.5	331.1	327.7	324.7	321.9	319.3	318.4
27.5°	366.8	352.1	338.7	329.1	322.2	315.5	312.5	308.8	306.8	304.7	302.2
30°	354.2	339.2	327.4	318.2	310.8	304.8	301.5	299.0	297.2	295.3	293.9
32.5°	341.3	327.4	316.0	306.9	299.5	295.0	292.1	290.3	288.3	286.1	284.3
35°	324.2	308.9	297.8	290.0	284.2	280.7	277.5	275.9	273.6	273.6	271.7
37.5°	304.9	291.7	281.9	274.8	269.6	266.5	263.0	261.9	260.4	259.4	258.8
40°	293.5	281.2	272.0	264.8	259.3	256.7	253.9	252.1	251.2	250.0	249.6
42.5°	281.6	269.9	261.1	254.5	249.6	247.5	244.9	243.6	241.7	240.2	239.9
45°	263.6	252.3	244.2	238.9	234.8	232.2	230.6	227.8	226.9	225.1	224.8
47.5°	246.6	235.7	227.8	223.4	219.8	217.7	215.2	212.4	211.3	210.4	210.3
50°	233.8	223.9	216.5	212.4	208.9	205.9	203.3	201.5	200.8	200.8	201.3
52.5°	220.9	212.4	206.2	201.1	197.8	194.6	192.2	191.1	190.1	191.2	192.0
55°	202.0	193.4	188.8	183.9	180.7	177.0	175.8	175.4	174.7	176.5	177.5
57.5°	181.9	175.9	170.5	165.7	162.8	160.6	159.1	158.8	160.1	161.0	164.0
60°	169.1	162.2	157.4	153.7	150.2	148.8	148.3	147.9	148.8	151.3	155.3
62.5°	155.1	149.5	144.2	141.5	138.9	136.6	136.5	136.8	138.6	141.6	145.5
65°	134.5	129.6	126.2	122.9	120.8	119.5	119.9	120.8	122.9	126.9	131.2
67.5°	113.5	110.2	107.1	104.5	102.5	102.5	103.0	104.4	106.8	111.3	115.3
70°	100.1	96.4	93.8	92.7	91.0	90.1	91.5	93.8	95.9	100.1	103.5
72.5°	86.6	83.4	81.4	80.6	79.9	79.2	79.7	82.2	85.0	89.1	93.2
75°	66.5	65.4	64.0	63.1	62.4	62.9	63.3	65.6	67.9	72.3	76.9
77.5°	48.6	47.4	46.5	46.3	45.9	46.2	47.5	49.2	51.4	54.6	58.1
80°	36.7	36.3	35.8	35.6	35.6	35.8	37.7	38.8	40.9	43.9	46.7
82.5°	26.8	26.5	26.4	26.3	26.5	26.6	27.7	29.2	30.9	33.2	35.6
85°	14.1	13.6	14.3	14.6	14.1	14.8	15.3	16.2	16.9	18.0	19.2
87.5°	5.9	6.5	6.6	7.0	7.3	7.9	7.9	8.8	9.3	9.9	9.8
90°	6.3	7.6	8.9	10.1	11.3	12.5	13.4	14.2	15.1	16.0	16.7
92.5°	22.8	24.0	25.5	27.0	28.5	30.0	31.2	32.3	33.5	34.6	35.4
95°	52.2	53.3	55.0	56.7	58.5	60.2	61.4	62.6	63.9	65.1	65.9
97.5°	85.0	86.3	88.7	91.1	93.5	95.9	97.0	98.2	99.3	100.5	101.1
100°	109.5	110.6	112.9	115.1	117.4	119.6	121.2	122.8	124.3	125.9	126.9
102.5°	139.2	140.1	141.2	142.4	143.5	144.7	146.4	148.1	149.8	151.5	152.6
105°	181.8	182.7	183.8	184.8	185.8	186.9	187.9	189.0	190.0	191.1	191.8
107.5°	228.1	228.9	229.7	230.5	231.3	232.1	232.6	233.1	233.6	234.2	234.4
110°	260.0	260.7	261.2	261.7	262.2	262.7	263.3	263.8	264.3	264.8	265.0



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	290.8	291.4	292.0	292.7	293.4	294.0	294.3	294.5	294.7	295.0	295.0
115°	339.8	340.3	340.7	341.0	341.4	341.7	341.5	341.4	341.2	341.0	340.8
117.5°	386.4	386.8	387.1	387.4	387.7	388.0	388.1	388.3	388.4	388.6	388.3
120°	418.7	419.2	419.4	419.6	419.7	419.9	419.9	419.9	419.9	419.9	419.6
122.5°	449.0	449.4	449.8	450.3	450.7	451.2	451.0	450.9	450.8	450.6	450.3
125°	496.0	496.6	496.8	497.0	497.1	497.3	497.0	496.6	496.3	495.9	495.7
127.5°	541.1	541.5	541.7	541.9	542.2	542.4	542.2	542.0	541.8	541.7	541.4
130°	570.4	571.0	571.3	571.7	572.0	572.4	572.2	572.0	571.9	571.7	571.4
132.5°	600.8	601.4	601.4	601.3	601.2	601.2	601.0	600.8	600.6	600.5	600.1
135°	643.8	644.4	644.6	644.8	644.9	645.1	645.1	645.1	645.1	645.1	644.8
137.5°	685.6	686.3	686.7	687.0	687.4	687.8	688.0	688.2	688.4	688.6	688.3
140°	711.9	712.6	713.1	713.7	714.2	714.7	715.1	715.4	715.7	716.1	715.8
142.5°	738.3	739.0	739.6	740.3	740.9	741.6	741.8	742.0	742.2	742.4	742.1
145°	777.7	778.3	778.8	779.3	779.9	780.4	780.4	780.4	780.4	780.4	780.1
147.5°	813.0	813.4	813.9	814.3	814.7	815.1	815.5	815.9	816.4	816.8	816.4
150°	835.2	835.5	836.2	836.9	837.6	838.3	838.3	838.3	838.3	838.3	838.1
152.5°	856.9	857.2	857.4	857.7	858.0	858.3	858.7	859.1	859.5	859.9	859.8
155°	886.7	886.8	887.0	887.2	887.3	887.5	888.2	888.9	889.6	890.3	890.2
157.5°	912.7	912.6	912.8	913.0	913.1	913.3	914.0	914.7	915.4	916.1	915.9
160°	928.4	928.3	928.4	928.6	928.8	929.0	929.7	930.4	931.0	931.7	931.7
162.5°	943.4	943.2	943.2	943.3	943.3	943.4	944.2	945.0	945.9	946.7	946.6
165°	962.8	962.7	962.8	963.0	963.2	963.4	964.1	964.8	965.5	966.1	966.0
167.5°	977.6	977.3	977.3	977.3	977.3	977.3	978.3	979.4	980.4	981.5	981.4
170°	986.4	986.0	986.0	986.0	986.0	986.0	987.1	988.1	989.2	990.2	990.1
172.5°	992.6	992.3	992.3	992.3	992.3	992.3	993.3	994.4	995.4	996.5	996.5
175°	999.7	999.3	999.3	999.3	999.3	999.3	1000.4	1001.4	1002.5	1003.5	1003.4
177.5°	1003.8	1003.5	1003.4	1003.2	1003.1	1002.9	1003.8	1004.6	1005.4	1006.3	1006.2
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	518.7	520.0	518.9	520.4	518.9	520.0	518.7	519.8	521.5	520.4	523.0
5°	478.1	476.0	477.4	476.5	477.4	476.0	478.1	479.2	482.0	482.9	484.8
7.5°	440.6	438.6	436.3	435.2	436.3	438.6	440.6	441.2	443.6	447.1	449.7
10°	417.1	414.5	414.3	412.7	414.3	414.5	417.1	419.6	421.2	425.6	428.6
12.5°	399.9	397.5	394.9	394.2	394.9	397.5	399.9	402.1	402.6	407.5	409.6
15°	375.5	373.6	372.0	373.4	372.0	373.6	375.5	376.9	379.4	382.9	385.2
17.5°	355.2	353.7	353.4	351.7	353.4	353.7	355.2	356.0	360.1	362.4	366.4
20°	342.4	341.3	341.8	338.7	341.8	341.3	342.4	344.5	348.7	349.8	354.0
22.5°	332.3	330.0	329.7	329.1	329.7	330.0	332.3	334.2	335.0	338.6	341.4
25°	316.3	315.2	314.0	315.2	314.0	315.2	316.3	318.4	319.3	321.9	324.7
27.5°	302.4	301.0	300.7	300.9	300.7	301.0	302.4	302.2	304.7	306.8	308.8
30°	293.9	291.6	291.8	291.6	291.8	291.6	293.9	293.9	295.3	297.2	299.0
32.5°	284.7	283.1	282.8	282.4	282.8	283.1	284.7	284.3	286.1	288.3	290.3
35°	271.0	271.0	269.9	269.9	269.9	271.0	271.0	271.7	273.6	273.6	275.9
37.5°	258.2	258.0	257.3	257.4	257.3	258.0	258.2	258.8	259.4	260.4	261.9
40°	248.6	248.4	247.7	246.3	247.7	248.4	248.6	249.6	250.0	251.2	252.1
42.5°	239.4	238.6	238.3	237.8	238.3	238.6	239.4	239.9	240.2	241.7	243.6
45°	224.8	224.8	224.4	224.1	224.4	224.8	224.8	224.8	225.1	226.9	227.8
47.5°	210.7	211.1	212.0	211.8	212.0	211.1	210.7	210.3	210.4	211.3	212.4
50°	202.2	202.4	203.1	203.3	203.1	202.4	202.2	201.3	200.8	200.8	201.5
52.5°	192.8	194.1	195.0	194.8	195.0	194.1	192.8	192.0	191.2	190.1	191.1
55°	179.5	181.2	182.8	183.0	182.8	181.2	179.5	177.5	176.5	174.7	175.4
57.5°	166.5	168.7	170.4	171.0	170.4	168.7	166.5	164.0	161.0	160.1	158.8
60°	157.6	160.6	162.7	163.6	162.7	160.6	157.6	155.3	151.3	148.8	147.9
62.5°	149.1	152.5	154.5	154.7	154.5	152.5	149.1	145.5	141.6	138.6	136.8
65°	135.2	138.6	140.5	141.9	140.5	138.6	135.2	131.2	126.9	122.9	120.8
67.5°	120.2	123.7	125.7	126.8	125.7	123.7	120.2	115.3	111.3	106.8	104.4
70°	109.3	112.8	115.5	116.5	115.5	112.8	109.3	103.5	100.1	95.9	93.8
72.5°	98.6	101.7	103.9	105.0	103.9	101.7	98.6	93.2	89.1	85.0	82.2
75°	79.9	84.1	86.2	87.3	86.2	84.1	79.9	76.9	72.3	67.9	65.6
77.5°	61.6	65.4	66.7	67.3	66.7	65.4	61.6	58.1	54.6	51.4	49.2
80°	49.4	51.8	53.4	53.6	53.4	51.8	49.4	46.7	43.9	40.9	38.8
82.5°	38.0	39.9	40.4	41.0	40.4	39.9	38.0	35.6	33.2	30.9	29.2
85°	20.8	21.7	22.0	21.7	22.0	21.7	20.8	19.2	18.0	16.9	16.2
87.5°	10.3	10.2	10.3	10.8	10.3	10.2	10.3	9.8	9.9	9.3	8.8
90°	17.2	17.7	18.2	18.8	18.2	17.7	17.2	16.7	16.0	15.1	14.2
92.5°	35.8	36.1	36.5	36.9	36.5	36.1	35.8	35.4	34.6	33.5	32.3
95°	66.2	66.6	66.9	67.2	66.9	66.6	66.2	65.9	65.1	63.9	62.6
97.5°	101.3	101.5	101.8	102.0	101.8	101.5	101.3	101.1	100.5	99.3	98.2
100°	127.2	127.5	127.9	128.2	127.9	127.5	127.2	126.9	125.9	124.3	122.8
102.5°	153.1	153.5	154.0	154.5	154.0	153.5	153.1	152.6	151.5	149.8	148.1
105°	192.4	192.9	193.4	193.9	193.4	192.9	192.4	191.8	191.1	190.0	189.0
107.5°	234.4	234.3	234.3	234.3	234.3	234.3	234.4	234.4	234.2	233.6	233.1
110°	264.8	264.6	264.5	264.3	264.5	264.6	264.8	265.0	264.8	264.3	263.8



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	294.6	294.3	294.0	293.7	294.0	294.3	294.6	295.0	295.0	294.7	294.5
115°	340.7	340.5	340.3	340.2	340.3	340.5	340.7	340.8	341.0	341.2	341.4
117.5°	387.6	386.9	386.2	385.5	386.2	386.9	387.6	388.3	388.6	388.4	388.3
120°	418.9	418.2	417.5	416.8	417.5	418.2	418.9	419.6	419.9	419.9	419.9
122.5°	449.7	449.2	448.6	448.1	448.6	449.2	449.7	450.3	450.6	450.8	450.9
125°	495.5	495.3	495.2	495.0	495.2	495.3	495.5	495.7	495.9	496.3	496.6
127.5°	541.1	540.7	540.4	540.0	540.4	540.7	541.1	541.4	541.7	541.8	542.0
130°	571.1	570.7	570.4	570.0	570.4	570.7	571.1	571.4	571.7	571.9	572.0
132.5°	599.7	599.2	598.7	598.2	598.7	599.2	599.7	600.1	600.5	600.6	600.8
135°	644.1	643.4	642.7	642.0	642.7	643.4	644.1	644.8	645.1	645.1	645.1
137.5°	687.4	686.6	685.7	684.8	685.7	686.6	687.4	688.3	688.6	688.4	688.2
140°	715.0	714.1	713.2	712.4	713.2	714.1	715.0	715.8	716.1	715.7	715.4
142.5°	741.2	740.4	739.5	738.6	739.5	740.4	741.2	742.1	742.4	742.2	742.0
145°	779.6	779.1	778.6	778.0	778.6	779.1	779.6	780.1	780.4	780.4	780.4
147.5°	815.2	814.0	812.9	811.7	812.9	814.0	815.2	816.4	816.8	816.4	815.9
150°	837.7	837.4	837.0	836.7	837.0	837.4	837.7	838.1	838.3	838.3	838.3
152.5°	859.2	858.6	858.0	857.3	858.0	858.6	859.2	859.8	859.9	859.5	859.1
155°	889.3	888.5	887.6	886.7	887.6	888.5	889.3	890.2	890.3	889.6	888.9
157.5°	914.7	913.6	912.4	911.3	912.4	913.6	914.7	915.9	916.1	915.4	914.7
160°	930.8	929.9	929.0	928.2	929.0	929.9	930.8	931.7	931.7	931.0	930.4
162.5°	945.6	944.6	943.6	942.6	943.6	944.6	945.6	946.6	946.7	945.9	945.0
165°	964.9	963.9	962.8	961.8	962.8	963.9	964.9	966.0	966.1	965.5	964.8
167.5°	980.4	979.3	978.2	977.1	978.2	979.3	980.4	981.4	981.5	980.4	979.4
170°	988.9	987.7	986.5	985.3	986.5	987.7	988.9	990.1	990.2	989.2	988.1
172.5°	995.4	994.3	993.2	992.1	993.2	994.3	995.4	996.5	996.5	995.4	994.4
175°	1002.2	1001.0	999.8	998.6	999.8	1001.0	1002.2	1003.4	1003.5	1002.5	1001.4
177.5°	1005.2	1004.3	1003.3	1002.3	1003.3	1004.3	1005.2	1006.2	1006.3	1005.4	1004.6
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	520.6	522.8	525.5	527.6	531.3	532.9	535.0	536.6	539.6	542.4	545.7
5°	485.5	489.4	494.7	500.5	507.2	511.8	518.3	522.2	530.1	537.2	544.2
7.5°	453.7	458.5	466.0	473.4	482.2	490.1	498.2	507.2	517.2	529.1	538.9
10°	431.9	438.3	446.4	455.7	466.3	475.5	486.4	496.1	508.4	522.2	535.2
12.5°	414.5	420.0	429.0	437.9	449.3	460.6	471.8	484.6	498.9	514.3	530.5
15°	390.5	395.1	402.5	414.8	426.3	437.4	454.3	466.3	484.3	501.4	521.1
17.5°	370.0	375.8	382.0	392.5	404.5	418.3	433.4	448.5	465.8	487.5	509.6
20°	357.5	362.1	369.2	377.3	390.0	403.9	418.2	433.5	454.7	477.2	501.0
22.5°	343.8	348.8	356.9	365.7	376.4	389.7	405.5	422.2	444.4	466.4	492.3
25°	327.7	331.1	338.5	346.4	357.0	368.3	384.7	403.2	425.2	450.4	476.7
27.5°	312.5	315.5	322.2	329.1	338.7	352.1	366.8	385.5	406.2	431.7	460.9
30°	301.5	304.8	310.8	318.2	327.4	339.2	354.2	371.8	394.0	418.9	449.4
32.5°	292.1	295.0	299.5	306.9	316.0	327.4	341.3	359.2	381.4	406.7	436.7
35°	277.5	280.7	284.2	290.0	297.8	308.9	324.2	341.1	362.3	386.8	414.3
37.5°	263.0	266.5	269.6	274.8	281.9	291.7	304.9	322.5	341.7	365.3	391.7
40°	253.9	256.7	259.3	264.8	272.0	281.2	293.5	309.2	329.5	351.5	373.4
42.5°	244.9	247.5	249.6	254.5	261.1	269.9	281.6	297.0	315.8	336.3	355.7
45°	230.6	232.2	234.8	238.9	244.2	252.3	263.6	277.3	293.2	312.6	327.2
47.5°	215.2	217.7	219.8	223.4	227.8	235.7	246.6	258.2	272.7	287.1	297.3
50°	203.3	205.9	208.9	212.4	216.5	223.9	233.8	245.6	257.9	269.0	277.7
52.5°	192.2	194.6	197.8	201.1	206.2	212.4	220.9	231.4	243.5	251.4	258.7
55°	175.8	177.0	180.7	183.9	188.8	193.4	202.0	211.2	218.6	224.6	230.6
57.5°	159.1	160.6	162.8	165.7	170.5	175.9	181.9	190.1	194.4	197.5	202.2
60°	148.3	148.8	150.2	153.7	157.4	162.2	169.1	174.9	178.2	180.7	184.6
62.5°	136.5	136.6	138.9	141.5	144.2	149.5	155.1	159.8	162.4	163.7	167.4
65°	119.9	119.5	120.8	122.9	126.2	129.6	134.5	138.6	138.4	139.8	142.1
67.5°	103.0	102.5	102.5	104.5	107.1	110.2	113.5	116.0	116.0	117.8	119.0
70°	91.5	90.1	91.0	92.7	93.8	96.4	100.1	101.0	101.2	102.1	103.3
72.5°	79.7	79.2	79.9	80.6	81.4	83.4	86.6	87.1	87.2	87.7	89.6
75°	63.3	62.9	62.4	63.1	64.0	65.4	66.5	67.5	67.2	67.5	68.9
77.5°	47.5	46.2	45.9	46.3	46.5	47.4	48.6	48.5	48.7	48.7	50.2
80°	37.7	35.8	35.6	35.6	35.8	36.3	36.7	37.2	36.5	37.2	37.7
82.5°	27.7	26.6	26.5	26.3	26.4	26.5	26.8	27.0	26.9	27.2	27.5
85°	15.3	14.8	14.1	14.6	14.3	13.6	14.1	13.4	13.2	13.4	13.6
87.5°	7.9	7.9	7.3	7.0	6.6	6.5	5.9	5.4	5.0	4.9	5.1
90°	13.4	12.5	11.3	10.1	8.9	7.6	6.3	5.0	3.6	2.2	0.8
92.5°	31.2	30.0	28.5	27.0	25.5	24.0	22.8	21.8	20.9	19.9	18.9
95°	61.4	60.2	58.5	56.7	55.0	53.3	52.2	51.9	51.5	51.2	50.8
97.5°	97.0	95.9	93.5	91.1	88.7	86.3	85.0	84.9	84.7	84.6	84.5
100°	121.2	119.6	117.4	115.1	112.9	110.6	109.5	109.5	109.5	109.5	109.5
102.5°	146.4	144.7	143.5	142.4	141.2	140.1	139.2	138.5	137.8	137.1	136.4
105°	187.9	186.9	185.8	184.8	183.8	182.7	181.8	180.9	180.0	179.2	178.3
107.5°	232.6	232.1	231.3	230.5	229.7	228.9	228.1	227.2	226.3	225.4	224.6
110°	263.3	262.7	262.2	261.7	261.2	260.7	260.0	259.1	258.2	257.4	256.5



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	294.3	294.0	293.4	292.7	292.0	291.4	290.8	290.4	289.9	289.5	289.0
115°	341.5	341.7	341.4	341.0	340.7	340.3	339.8	339.1	338.4	337.7	337.0
117.5°	388.1	388.0	387.7	387.4	387.1	386.8	386.4	386.1	385.8	385.5	385.2
120°	419.9	419.9	419.7	419.6	419.4	419.2	418.7	417.8	417.0	416.1	415.2
122.5°	451.0	451.2	450.7	450.3	449.8	449.4	449.0	448.7	448.4	448.1	447.7
125°	497.0	497.3	497.1	497.0	496.8	496.6	496.0	495.0	493.9	492.9	491.8
127.5°	542.2	542.4	542.2	541.9	541.7	541.5	541.1	540.5	539.9	539.4	538.8
130°	572.2	572.4	572.0	571.7	571.3	571.0	570.4	569.5	568.7	567.8	566.9
132.5°	601.0	601.2	601.2	601.3	601.4	601.4	600.8	599.3	597.9	596.5	595.1
135°	645.1	645.1	644.9	644.8	644.6	644.4	643.8	642.8	641.7	640.7	639.6
137.5°	688.0	687.8	687.4	687.0	686.7	686.3	685.6	684.6	683.6	682.6	681.6
140°	715.1	714.7	714.2	713.7	713.1	712.6	711.9	711.1	710.2	709.3	708.5
142.5°	741.8	741.6	740.9	740.3	739.6	739.0	738.3	737.5	736.8	736.1	735.4
145°	780.4	780.4	779.9	779.3	778.8	778.3	777.7	777.0	776.3	775.6	774.9
147.5°	815.5	815.1	814.7	814.3	813.9	813.4	813.0	812.7	812.3	811.9	811.5
150°	838.3	838.3	837.6	836.9	836.2	835.5	835.2	835.4	835.6	835.7	835.9
152.5°	858.7	858.3	858.0	857.7	857.4	857.2	856.9	856.7	856.4	856.2	855.9
155°	888.2	887.5	887.3	887.2	887.0	886.8	886.7	886.7	886.7	886.7	886.7
157.5°	914.0	913.3	913.1	913.0	912.8	912.6	912.7	913.1	913.5	913.9	914.3
160°	929.7	929.0	928.8	928.6	928.4	928.3	928.4	929.0	929.5	930.0	930.5
162.5°	944.2	943.4	943.3	943.3	943.2	943.2	943.4	943.8	944.1	944.5	944.9
165°	964.1	963.4	963.2	963.0	962.8	962.7	962.8	963.1	963.5	963.8	964.2
167.5°	978.3	977.3	977.3	977.3	977.3	977.3	977.6	978.3	979.0	979.7	980.4
170°	987.1	986.0	986.0	986.0	986.0	986.0	986.4	987.1	987.8	988.5	989.2
172.5°	993.3	992.3	992.3	992.3	992.3	992.3	992.6	993.3	994.0	994.7	995.4
175°	1000.4	999.3	999.3	999.3	999.3	999.3	999.7	1000.4	1001.1	1001.8	1002.5
177.5°	1003.8	1002.9	1003.1	1003.2	1003.4	1003.5	1003.8	1004.4	1005.0	1005.5	1006.1
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	547.4	549.9	551.6	554.7	557.3	558.8	560.1	561.2	562.5	563.6	566.8
5°	550.9	556.9	562.0	569.8	577.0	582.5	588.5	593.8	598.2	604.5	609.3
7.5°	549.3	560.0	571.2	583.4	595.8	607.3	618.0	627.9	636.9	647.8	657.4
10°	547.9	562.4	576.7	593.2	610.0	624.3	637.7	651.4	661.3	675.2	687.0
12.5°	546.8	563.9	581.2	600.9	619.4	639.7	657.5	667.5	682.6	693.7	707.7
15°	542.1	564.7	588.5	610.7	637.1	655.8	671.5	690.9	705.0	719.1	734.3
17.5°	533.7	559.4	586.0	615.1	640.3	660.4	680.7	699.4	716.2	735.1	754.1
20°	529.8	555.5	586.0	615.8	640.5	661.5	682.3	702.9	721.4	745.7	767.6
22.5°	521.7	552.7	580.8	609.9	635.3	658.2	681.8	705.1	729.7	757.1	784.6
25°	507.2	538.6	568.4	597.1	622.7	651.4	676.6	707.8	739.2	775.5	809.7
27.5°	492.1	522.2	549.5	577.2	607.1	639.6	672.2	707.6	748.8	794.6	842.8
30°	479.9	508.4	534.9	563.3	594.5	631.0	666.9	708.9	756.5	808.0	865.4
32.5°	465.7	491.9	517.7	547.8	581.8	620.3	662.1	708.2	765.4	823.9	882.9
35°	441.3	463.3	489.9	522.0	560.3	604.5	652.8	707.3	772.9	840.2	889.8
37.5°	412.5	432.9	460.9	496.1	536.3	583.7	641.0	705.7	775.4	829.0	845.0
40°	393.0	412.0	441.1	477.6	518.7	568.9	631.7	700.1	767.6	801.8	788.6
42.5°	372.3	392.2	420.6	456.7	501.0	555.6	620.1	688.5	745.1	758.0	712.5
45°	339.7	360.2	388.2	424.7	472.3	531.5	598.7	660.9	693.4	670.1	599.6
47.5°	309.3	328.6	354.5	392.2	441.3	502.5	567.2	616.8	619.4	563.7	488.4
50°	288.6	306.4	332.5	370.2	418.9	480.9	539.3	578.4	560.8	497.7	425.4
52.5°	268.3	285.7	311.4	348.7	396.9	453.7	508.1	535.5	502.4	437.6	375.9
55°	238.9	254.2	279.4	313.8	359.5	412.2	458.4	467.9	424.9	361.2	311.0
57.5°	210.3	224.5	247.4	279.1	321.0	367.6	403.8	401.7	356.3	301.6	261.8
60°	190.9	204.7	225.1	256.0	294.2	334.4	365.3	357.9	312.9	265.7	232.2
62.5°	173.5	185.9	205.1	232.2	267.0	304.2	329.6	318.7	274.6	233.4	206.9
65°	147.9	158.3	174.7	197.8	226.7	257.4	277.1	263.0	225.3	193.2	171.9
67.5°	123.4	131.8	145.5	164.0	188.6	213.3	225.2	211.1	180.9	157.5	141.7
70°	107.9	115.3	125.9	142.3	163.8	184.6	193.6	180.9	155.0	134.9	123.6
72.5°	92.4	98.5	107.8	122.6	139.8	157.8	165.7	153.6	132.3	115.3	104.8
75°	71.4	75.6	82.0	92.2	105.8	120.2	124.5	113.9	100.3	87.6	80.6
77.5°	51.1	54.6	59.5	65.9	75.6	84.7	88.5	82.4	71.9	63.8	58.1
80°	39.3	41.1	45.3	50.6	58.2	64.0	66.5	62.6	55.2	49.2	44.8
82.5°	28.0	29.9	32.3	36.7	41.6	45.5	48.2	45.6	40.3	35.5	33.0
85°	13.6	14.8	16.2	18.0	21.7	24.0	23.8	22.2	20.1	18.3	16.9
87.5°	5.2	5.7	6.5	7.7	8.6	9.5	10.1	10.0	9.5	9.1	8.8
90°	2.2	3.6	5.0	6.3	7.6	8.9	10.1	11.3	12.5	13.4	14.2
92.5°	19.9	20.9	21.8	22.8	24.0	25.5	27.0	28.5	30.0	31.2	32.3
95°	51.2	51.5	51.9	52.2	53.3	55.0	56.7	58.5	60.2	61.4	62.6
97.5°	84.6	84.7	84.9	85.0	86.3	88.7	91.1	93.5	95.9	97.0	98.2
100°	109.5	109.5	109.5	109.5	110.6	112.9	115.1	117.4	119.6	121.2	122.8
102.5°	137.1	137.8	138.5	139.2	140.1	141.2	142.4	143.5	144.7	146.4	148.1
105°	179.2	180.0	180.9	181.8	182.7	183.8	184.8	185.8	186.9	187.9	189.0
107.5°	225.4	226.3	227.2	228.1	228.9	229.7	230.5	231.3	232.1	232.6	233.1
110°	257.4	258.2	259.1	260.0	260.7	261.2	261.7	262.2	262.7	263.3	263.8



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	289.5	289.9	290.4	290.8	291.4	292.0	292.7	293.4	294.0	294.3	294.5
115°	337.7	338.4	339.1	339.8	340.3	340.7	341.0	341.4	341.7	341.5	341.4
117.5°	385.5	385.8	386.1	386.4	386.8	387.1	387.4	387.7	388.0	388.1	388.3
120°	416.1	417.0	417.8	418.7	419.2	419.4	419.6	419.7	419.9	419.9	419.9
122.5°	448.1	448.4	448.7	449.0	449.4	449.8	450.3	450.7	451.2	451.0	450.9
125°	492.9	493.9	495.0	496.0	496.6	496.8	497.0	497.1	497.3	497.0	496.6
127.5°	539.4	539.9	540.5	541.1	541.5	541.7	541.9	542.2	542.4	542.2	542.0
130°	567.8	568.7	569.5	570.4	571.0	571.3	571.7	572.0	572.4	572.2	572.0
132.5°	596.5	597.9	599.3	600.8	601.4	601.4	601.3	601.2	601.2	601.0	600.8
135°	640.7	641.7	642.8	643.8	644.4	644.6	644.8	644.9	645.1	645.1	645.1
137.5°	682.6	683.6	684.6	685.6	686.3	686.7	687.0	687.4	687.8	688.0	688.2
140°	709.3	710.2	711.1	711.9	712.6	713.1	713.7	714.2	714.7	715.1	715.4
142.5°	736.1	736.8	737.5	738.3	739.0	739.6	740.3	740.9	741.6	741.8	742.0
145°	775.6	776.3	777.0	777.7	778.3	778.8	779.3	779.9	780.4	780.4	780.4
147.5°	811.9	812.3	812.7	813.0	813.4	813.9	814.3	814.7	815.1	815.5	815.9
150°	835.7	835.6	835.4	835.2	835.5	836.2	836.9	837.6	838.3	838.3	838.3
152.5°	856.2	856.4	856.7	856.9	857.2	857.4	857.7	858.0	858.3	858.7	859.1
155°	886.7	886.7	886.7	886.7	886.8	887.0	887.2	887.3	887.5	888.2	888.9
157.5°	913.9	913.5	913.1	912.7	912.6	912.8	913.0	913.1	913.3	914.0	914.7
160°	930.0	929.5	929.0	928.4	928.3	928.4	928.6	928.8	929.0	929.7	930.4
162.5°	944.5	944.1	943.8	943.4	943.2	943.2	943.3	943.3	943.4	944.2	945.0
165°	963.8	963.5	963.1	962.8	962.7	962.8	963.0	963.2	963.4	964.1	964.8
167.5°	979.7	979.0	978.3	977.6	977.3	977.3	977.3	977.3	977.3	978.3	979.4
170°	988.5	987.8	987.1	986.4	986.0	986.0	986.0	986.0	986.0	987.1	988.1
172.5°	994.7	994.0	993.3	992.6	992.3	992.3	992.3	992.3	992.3	993.3	994.4
175°	1001.8	1001.1	1000.4	999.7	999.3	999.3	999.3	999.3	999.3	1000.4	1001.4
177.5°	1005.5	1005.0	1004.4	1003.8	1003.5	1003.4	1003.2	1003.1	1002.9	1003.8	1004.6
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	569.4	570.8	574.0	572.9	574.3	575.1	575.8
5°	615.3	622.7	626.0	625.5	630.4	629.2	628.0
7.5°	667.3	675.0	679.4	684.8	687.9	688.2	690.9
10°	696.7	706.8	711.0	716.8	720.5	722.6	722.3
12.5°	719.2	727.2	736.5	739.3	744.3	747.0	746.0
15°	746.4	759.1	768.8	773.6	779.9	781.7	784.2
17.5°	770.6	787.6	798.9	814.0	819.7	823.2	821.1
20°	788.9	811.3	822.6	840.6	850.6	855.9	854.0
22.5°	810.5	834.8	855.7	871.3	886.4	893.6	895.1
25°	847.6	880.8	911.6	932.1	950.8	955.2	964.9
27.5°	889.0	928.2	961.1	982.7	995.7	1000.6	1003.7
30°	915.0	954.1	978.8	992.7	996.8	996.4	995.9
32.5°	927.8	952.2	957.0	953.1	943.6	935.5	927.1
35°	909.7	891.5	864.2	829.1	803.2	777.1	774.5
37.5°	818.2	759.8	714.4	663.7	634.5	616.4	603.9
40°	732.0	665.7	610.7	568.0	538.2	526.4	514.8
42.5°	638.5	575.1	526.4	490.7	468.3	455.2	446.1
45°	518.7	462.8	424.7	398.8	381.0	370.9	365.1
47.5°	425.1	383.7	351.3	332.6	320.4	312.5	312.5
50°	374.8	335.3	313.8	299.0	288.4	282.1	283.3
52.5°	330.2	300.7	282.4	270.0	262.1	258.3	258.1
55°	276.1	254.9	242.9	233.8	228.5	224.1	225.1
57.5°	236.2	218.3	210.2	202.7	199.0	197.3	194.7
60°	211.4	197.6	190.6	184.6	180.9	179.5	177.0
62.5°	189.4	178.5	171.8	166.9	163.6	163.1	161.1
65°	159.2	150.9	144.9	142.6	139.1	138.2	138.2
67.5°	131.2	125.3	120.6	118.5	117.0	117.2	116.1
70°	113.7	108.8	105.8	103.5	102.4	102.6	101.7
72.5°	99.5	94.0	91.4	90.0	88.5	89.1	88.7
75°	75.3	72.6	71.2	69.8	68.9	68.4	67.9
77.5°	55.3	52.9	51.8	51.0	51.2	50.0	50.9
80°	42.7	40.7	40.0	38.8	38.6	38.6	38.4
82.5°	31.3	30.1	29.6	28.7	28.2	28.6	28.0
85°	16.2	15.3	15.0	15.0	14.6	14.1	15.3
87.5°	8.9	8.4	8.5	8.4	8.5	8.5	8.2
90°	15.1	16.0	16.7	17.2	17.7	18.2	18.8
92.5°	33.5	34.6	35.4	35.8	36.1	36.5	36.9
95°	63.9	65.1	65.9	66.2	66.6	66.9	67.2
97.5°	99.3	100.5	101.1	101.3	101.5	101.8	102.0
100°	124.3	125.9	126.9	127.2	127.5	127.9	128.2
102.5°	149.8	151.5	152.6	153.1	153.5	154.0	154.5
105°	190.0	191.1	191.8	192.4	192.9	193.4	193.9
107.5°	233.6	234.2	234.4	234.4	234.3	234.3	234.3
110°	264.3	264.8	265.0	264.8	264.6	264.5	264.3



TEST NUMBER: P333134

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	294.7	295.0	295.0	294.6	294.3	294.0	293.7
115°	341.2	341.0	340.8	340.7	340.5	340.3	340.2
117.5°	388.4	388.6	388.3	387.6	386.9	386.2	385.5
120°	419.9	419.9	419.6	418.9	418.2	417.5	416.8
122.5°	450.8	450.6	450.3	449.7	449.2	448.6	448.1
125°	496.3	495.9	495.7	495.5	495.3	495.2	495.0
127.5°	541.8	541.7	541.4	541.1	540.7	540.4	540.0
130°	571.9	571.7	571.4	571.1	570.7	570.4	570.0
132.5°	600.6	600.5	600.1	599.7	599.2	598.7	598.2
135°	645.1	645.1	644.8	644.1	643.4	642.7	642.0
137.5°	688.4	688.6	688.3	687.4	686.6	685.7	684.8
140°	715.7	716.1	715.8	715.0	714.1	713.2	712.4
142.5°	742.2	742.4	742.1	741.2	740.4	739.5	738.6
145°	780.4	780.4	780.1	779.6	779.1	778.6	778.0
147.5°	816.4	816.8	816.4	815.2	814.0	812.9	811.7
150°	838.3	838.3	838.1	837.7	837.4	837.0	836.7
152.5°	859.5	859.9	859.8	859.2	858.6	858.0	857.3
155°	889.6	890.3	890.2	889.3	888.5	887.6	886.7
157.5°	915.4	916.1	915.9	914.7	913.6	912.4	911.3
160°	931.0	931.7	931.7	930.8	929.9	929.0	928.2
162.5°	945.9	946.7	946.6	945.6	944.6	943.6	942.6
165°	965.5	966.1	966.0	964.9	963.9	962.8	961.8
167.5°	980.4	981.5	981.4	980.4	979.3	978.2	977.1
170°	989.2	990.2	990.1	988.9	987.7	986.5	985.3
172.5°	995.4	996.5	996.5	995.4	994.3	993.2	992.1
175°	1002.5	1003.5	1003.4	1002.2	1001.0	999.8	998.6
177.5°	1005.4	1006.3	1006.2	1005.2	1004.3	1003.3	1002.3
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8

(END OF REPORT)