

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333197

Luminaire Tested: **S125DIP-S610D1205U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333197  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S610D1205U835-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6695.5 lumens  
Efficiency: N/A  
Efficacy: 135.5 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	67	63	59	56	52	47	44	42	35	34	32	27
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	72	62	54	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20
5	66	55	47	42	60	50	44	38	41	36	32	33	29	27	25	23	21	17
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	57	45	37	31	51	41	34	29	34	29	25	27	23	21	21	18	16	14
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	17	15	12
9	49	37	29	25	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5780	5780	5780	5780
5°	6694	5800	5078	5800
10°	7788	5770	4450	5770
15°	8620	5727	4105	5727
20°	9649	5660	3827	5660
25°	11305	5585	3693	5585
30°	12210	5510	3575	5510
35°	10039	5370	3498	5370
40°	7136	5176	3414	5176
45°	5482	4913	3366	4913
50°	4679	4588	3359	4588
55°	4166	4269	3388	4269
60°	3759	3920	3475	3920
65°	3472	3570	3564	3570
70°	3155	3206	3616	3206
75°	2787	2825	3583	2825
80°	2347	2302	3277	2302
85°	1860	1660	2645	1660



TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.2	1.3
10°-20°	256.5	3.8
20°-30°	416.6	6.2
30°-40°	508.1	7.6
40°-50°	462.2	6.9
50°-60°	368.2	5.5
60°-70°	256.4	3.8
70°-80°	136.8	2.0
80°-90°	37.8	0.6
90°-100°	100.0	1.5
100°-110°	295.3	4.4
110°-120°	500.2	7.5
120°-130°	658.3	9.8
130°-140°	737.7	11.0
140°-150°	723.0	10.8
150°-160°	607.3	9.1
160°-170°	403.7	6.0
170°-180°	141.3	2.1
0°-30°	759.2	11.3
0°-40°	1267.4	18.9
0°-60°	2097.8	31.3
0°-90°	2528.8	37.8
90°-120°	895.6	13.4
90°-150°	3014.6	45.0
90°-180°	4167.0	62.2
0°-180°	6695.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	895	895	895	895	895	
5°	1032	895	783	895	1032	104
15°	1289	857	614	857	1289	369
25°	1586	784	518	784	1586	725
35°	1273	681	444	681	1273	779
45°	600	538	368	538	600	480
55°	370	379	301	379	370	333
65°	227	234	233	234	227	225
75°	112	113	144	113	112	120
85°	25	22	36	22	25	30
90°	28	1	28	1	28	17
95°	100	76	100	76	100	102
105°	288	265	288	265	288	305
115°	506	501	506	501	506	500
125°	736	731	736	731	736	657
135°	954	951	954	951	954	736
145°	1156	1152	1156	1152	1156	722
155°	1318	1318	1318	1318	1318	606
165°	1429	1433	1429	1433	1429	403
175°	1484	1490	1484	1490	1484	141
180°	1493	1493	1493	1493	1493	



TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	946.7	945.4	944.2	941.8	943.6	938.4	936.0	931.8	926.6	924.8	922.6
5°	1032.5	1034.4	1036.3	1028.3	1029.1	1023.8	1011.6	1001.7	993.8	983.5	976.3
7.5°	1135.8	1131.3	1131.0	1125.8	1116.9	1109.8	1097.0	1080.7	1065.0	1047.1	1032.3
10°	1187.5	1187.9	1184.5	1178.4	1168.9	1162.0	1145.3	1129.4	1110.0	1087.2	1070.9
12.5°	1226.4	1228.0	1223.7	1215.5	1210.8	1195.5	1182.4	1163.4	1140.4	1122.2	1097.3
15°	1289.3	1285.1	1282.1	1271.8	1263.8	1247.9	1227.0	1207.2	1182.2	1159.0	1135.8
17.5°	1349.9	1353.3	1347.6	1338.2	1313.5	1294.8	1266.8	1239.8	1208.5	1177.5	1149.8
20°	1404.0	1407.1	1398.3	1382.0	1352.4	1333.7	1296.9	1261.9	1225.9	1186.0	1155.6
22.5°	1471.5	1469.1	1457.3	1432.4	1406.8	1372.3	1332.5	1289.9	1244.7	1199.6	1159.2
25°	1586.4	1570.4	1563.2	1532.4	1498.6	1448.1	1393.4	1331.1	1274.9	1215.2	1163.6
27.5°	1650.0	1645.0	1637.0	1615.5	1580.0	1526.0	1461.5	1385.6	1306.2	1231.0	1163.3
30°	1637.3	1638.0	1638.8	1631.9	1609.2	1568.5	1504.3	1422.6	1328.4	1243.7	1165.5
32.5°	1524.2	1538.0	1551.3	1566.9	1573.3	1565.5	1525.3	1451.5	1354.6	1258.3	1164.2
35°	1273.3	1277.5	1320.5	1363.0	1420.7	1465.6	1495.6	1462.9	1381.2	1270.7	1162.8
37.5°	992.8	1013.4	1043.1	1091.2	1174.5	1249.1	1345.1	1389.2	1362.8	1274.7	1160.1
40°	846.4	865.4	884.7	933.7	1004.0	1094.4	1203.4	1296.5	1318.2	1261.9	1151.0
42.5°	733.3	748.4	769.9	806.7	865.4	945.5	1049.7	1171.3	1246.1	1224.9	1131.9
45°	600.2	609.7	626.4	655.7	698.2	760.9	852.8	985.8	1101.6	1140.0	1086.4
47.5°	513.7	513.7	526.7	546.9	577.6	630.8	698.8	803.0	926.7	1018.3	1014.0
50°	465.7	463.8	474.1	491.6	515.9	551.2	616.2	699.4	818.3	922.0	950.8
52.5°	424.4	424.6	430.9	443.8	464.2	494.4	542.9	617.9	719.5	825.9	880.3
55°	370.0	368.5	375.7	384.4	399.3	419.0	454.0	511.3	593.7	698.6	769.2
57.5°	320.2	324.3	327.2	333.3	345.6	358.8	388.3	430.4	495.8	585.8	660.5
60°	291.0	295.2	297.4	303.5	313.4	324.8	347.6	381.8	436.9	514.4	588.4
62.5°	264.8	268.1	268.9	274.3	282.4	293.5	311.4	340.1	383.7	451.4	524.0
65°	227.2	227.2	228.7	234.4	238.2	248.1	261.7	282.6	317.6	370.4	432.3
67.5°	190.8	192.7	192.3	194.8	198.3	206.0	215.8	233.0	258.9	297.4	347.0
70°	167.1	168.7	168.3	170.2	174.0	178.9	186.9	203.2	221.8	254.9	297.4
72.5°	145.9	146.5	145.5	148.0	150.3	154.6	163.5	172.2	189.6	217.5	252.5
75°	111.7	112.4	113.2	114.7	117.0	119.3	123.8	132.6	144.0	164.9	187.3
77.5°	83.7	82.3	84.1	83.9	85.2	86.9	90.9	95.6	104.9	118.1	135.5
80°	63.1	63.4	63.4	63.8	65.7	66.9	70.3	73.7	80.9	90.8	102.9
82.5°	46.0	47.0	46.4	47.1	48.7	49.5	51.4	54.2	58.4	66.2	75.0
85°	25.1	23.2	23.9	24.7	24.7	25.1	26.6	27.7	30.0	33.0	36.5
87.5°	12.9	13.3	13.5	13.3	13.5	13.3	14.2	14.0	14.6	15.3	16.1
90°	27.9	27.1	26.3	25.6	24.8	23.8	22.5	21.2	19.9	18.6	16.8
92.5°	54.8	54.3	53.7	53.1	52.6	51.4	49.7	48.0	46.3	44.6	42.4
95°	99.9	99.4	98.9	98.4	97.9	96.7	94.9	93.1	91.3	89.5	86.9
97.5°	151.5	151.2	150.9	150.6	150.3	149.3	147.6	145.9	144.2	142.5	138.9
100°	190.6	190.1	189.5	189.0	188.5	187.1	184.8	182.4	180.1	177.8	174.4
102.5°	229.6	228.9	228.2	227.5	226.7	225.1	222.6	220.0	217.5	215.0	213.3
105°	288.2	287.4	286.6	285.9	285.1	283.9	282.4	280.8	279.3	277.7	276.2
107.5°	348.1	348.2	348.3	348.3	348.4	348.0	347.2	346.4	345.7	344.9	343.7
110°	392.8	393.0	393.3	393.5	393.8	393.5	392.8	392.0	391.2	390.4	389.7



TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	436.5	436.9	437.4	437.9	438.3	438.4	438.0	437.7	437.3	436.9	435.9
115°	505.5	505.7	506.0	506.3	506.5	506.8	507.0	507.3	507.6	507.8	507.3
117.5°	572.9	573.9	575.0	576.0	577.0	577.4	577.2	577.0	576.8	576.6	576.1
120°	619.4	620.4	621.4	622.5	623.5	624.0	624.0	624.0	624.0	624.0	623.8
122.5°	665.9	666.7	667.5	668.3	669.2	669.7	669.9	670.1	670.3	670.5	669.8
125°	735.6	735.8	736.1	736.4	736.6	737.0	737.5	738.0	738.5	739.1	738.8
127.5°	802.5	803.0	803.5	804.1	804.6	805.0	805.2	805.5	805.7	806.0	805.7
130°	847.1	847.6	848.2	848.7	849.2	849.6	849.8	850.1	850.4	850.6	850.1
132.5°	889.0	889.7	890.4	891.1	891.9	892.3	892.6	892.9	893.1	893.4	893.5
135°	954.0	955.1	956.1	957.1	958.2	958.7	958.7	958.7	958.7	958.7	958.4
137.5°	1017.7	1019.0	1020.3	1021.6	1022.9	1023.4	1023.1	1022.8	1022.4	1022.1	1021.6
140°	1058.6	1059.9	1061.2	1062.5	1063.8	1064.2	1063.7	1063.1	1062.6	1062.1	1061.3
142.5°	1097.7	1099.0	1100.3	1101.5	1102.8	1103.3	1103.0	1102.7	1102.4	1102.1	1101.1
145°	1156.2	1157.0	1157.8	1158.6	1159.3	1159.7	1159.7	1159.7	1159.7	1159.7	1158.9
147.5°	1206.2	1208.0	1209.7	1211.5	1213.2	1213.8	1213.2	1212.6	1211.9	1211.3	1210.7
150°	1243.4	1243.9	1244.4	1244.9	1245.5	1245.7	1245.7	1245.7	1245.7	1245.7	1244.7
152.5°	1274.1	1275.0	1275.9	1276.9	1277.8	1277.9	1277.3	1276.7	1276.1	1275.5	1275.1
155°	1317.8	1319.1	1320.3	1321.6	1322.9	1323.1	1322.0	1321.0	1320.0	1318.9	1318.7
157.5°	1354.3	1356.0	1357.7	1359.4	1361.1	1361.4	1360.4	1359.3	1358.3	1357.3	1357.0
160°	1379.4	1380.6	1381.9	1383.2	1384.5	1384.6	1383.6	1382.6	1381.5	1380.5	1380.3
162.5°	1400.7	1402.2	1403.7	1405.2	1406.7	1406.9	1405.6	1404.4	1403.1	1401.9	1401.8
165°	1429.3	1430.9	1432.4	1434.0	1435.5	1435.8	1434.7	1433.7	1432.7	1431.6	1431.4
167.5°	1452.1	1453.7	1455.3	1456.9	1458.5	1458.5	1457.0	1455.4	1453.9	1452.3	1452.3
170°	1464.2	1466.0	1467.8	1469.6	1471.4	1471.5	1470.0	1468.4	1466.9	1465.3	1465.3
172.5°	1474.4	1476.0	1477.6	1479.2	1480.8	1480.8	1479.3	1477.7	1476.2	1474.6	1474.6
175°	1483.9	1485.7	1487.6	1489.4	1491.2	1491.3	1489.7	1488.2	1486.6	1485.1	1485.1
177.5°	1489.5	1491.0	1492.4	1493.9	1495.3	1495.4	1494.2	1492.9	1491.7	1490.4	1490.6
180°	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2



TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	920.8	918.7	916.3	912.0	906.8	904.1	899.9	897.1	891.6	887.1	882.2
5°	967.5	957.7	948.6	936.8	923.9	915.5	905.6	894.6	883.2	871.4	858.5
7.5°	1015.9	998.5	979.5	959.0	939.1	920.7	903.1	885.9	869.8	850.3	833.8
10°	1048.5	1026.4	1002.9	975.1	948.2	924.6	900.7	879.8	858.5	835.7	815.6
12.5°	1081.0	1051.6	1018.4	987.9	955.5	927.1	898.9	872.2	845.5	820.2	796.8
15°	1103.9	1078.1	1047.3	1004.0	967.5	928.4	891.2	856.6	824.3	796.2	766.6
17.5°	1119.0	1085.8	1052.7	1011.2	963.4	919.6	877.4	837.9	801.5	765.8	737.3
20°	1121.8	1087.6	1053.0	1012.4	963.4	913.2	871.1	823.6	784.4	747.6	712.6
22.5°	1120.9	1082.1	1044.5	1002.6	954.9	908.7	857.7	809.3	766.8	730.6	694.1
25°	1112.3	1070.9	1023.8	981.6	934.5	885.5	833.8	783.7	740.4	699.0	662.9
27.5°	1105.1	1051.4	998.1	948.9	903.4	858.5	809.1	757.7	709.7	667.7	633.7
30°	1096.3	1037.4	977.4	926.1	879.4	835.7	789.0	738.9	688.7	647.7	611.2
32.5°	1088.4	1019.8	956.5	900.6	851.2	808.7	765.6	717.9	668.7	627.0	590.6
35°	1073.2	993.8	921.2	858.1	805.3	761.7	725.6	681.1	635.9	595.6	560.7
37.5°	1053.8	959.6	881.7	815.6	757.7	711.7	678.1	644.0	600.6	561.8	530.2
40°	1038.6	935.3	852.8	785.2	725.2	677.3	646.2	613.9	577.8	541.7	508.3
42.5°	1019.4	913.4	823.6	750.9	691.5	644.8	612.1	584.7	552.9	519.2	488.2
45°	984.3	873.7	776.5	698.2	638.2	592.2	558.4	537.9	514.0	482.1	455.9
47.5°	932.5	826.1	725.5	644.7	582.8	540.2	508.5	488.8	472.0	448.3	424.5
50°	886.6	790.5	688.7	608.6	546.6	503.7	474.5	456.6	442.2	423.9	403.8
52.5°	835.3	745.8	652.6	573.3	512.0	469.7	441.0	425.3	413.3	400.2	380.4
55°	753.7	677.7	591.1	515.9	459.3	417.9	392.8	379.1	369.2	359.4	347.2
57.5°	663.8	604.4	527.6	458.9	406.8	369.1	345.7	332.4	324.7	319.6	312.5
60°	600.6	549.7	483.6	420.9	370.0	336.6	313.8	303.5	297.1	292.9	287.6
62.5°	541.9	500.1	438.9	381.7	337.2	305.6	285.2	275.3	269.1	267.1	262.6
65°	455.5	423.2	372.7	325.2	287.2	260.2	243.1	233.6	229.8	227.5	227.9
67.5°	370.3	350.6	310.1	269.6	239.2	216.6	202.9	195.6	193.7	190.7	190.6
70°	318.3	303.5	269.3	234.0	207.0	189.6	177.4	169.8	167.9	166.4	166.0
72.5°	272.4	259.5	229.8	201.5	177.3	161.9	151.9	147.3	144.2	143.3	143.2
75°	204.8	197.5	174.0	151.6	134.9	124.2	117.4	113.2	110.9	110.5	110.9
77.5°	145.6	139.3	124.3	108.4	97.9	89.8	84.0	82.6	80.0	80.1	79.7
80°	109.4	105.2	95.7	83.2	74.5	67.6	64.6	61.9	61.2	60.0	61.2
82.5°	79.3	74.8	68.4	60.4	53.2	49.1	46.0	45.2	44.7	44.2	44.4
85°	39.1	39.5	35.7	29.6	26.6	24.3	22.4	22.4	22.0	21.7	22.0
87.5°	16.4	15.4	13.8	12.5	10.6	9.3	8.5	8.4	7.9	8.0	8.8
90°	15.0	13.2	11.4	9.4	7.4	5.3	3.2	1.2	3.2	5.3	7.4
92.5°	40.2	38.0	35.7	33.9	32.5	31.0	29.6	28.1	29.6	31.0	32.5
95°	84.3	81.7	79.1	77.6	77.1	76.6	76.0	75.5	76.0	76.6	77.1
97.5°	135.3	131.8	128.2	126.3	126.1	125.9	125.7	125.5	125.7	125.9	126.1
100°	171.1	167.7	164.4	162.7	162.7	162.7	162.7	162.7	162.7	162.7	162.7
102.5°	211.6	209.9	208.2	206.8	205.8	204.7	203.7	202.7	203.7	204.7	205.8
105°	274.6	273.1	271.5	270.1	268.8	267.5	266.2	264.9	266.2	267.5	268.8
107.5°	342.5	341.3	340.1	338.9	337.6	336.3	335.0	333.7	335.0	336.3	337.6
110°	388.9	388.1	387.3	386.3	385.0	383.7	382.4	381.2	382.4	383.7	385.0





TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	435.0	434.0	433.0	432.2	431.5	430.8	430.2	429.5	430.2	430.8	431.5
115°	506.8	506.3	505.7	505.0	503.9	502.9	501.9	500.8	501.9	502.9	503.9
117.5°	575.7	575.2	574.7	574.3	573.8	573.4	572.9	572.4	572.9	573.4	573.8
120°	623.5	623.2	623.0	622.2	620.9	619.6	618.3	617.0	618.3	619.6	620.9
122.5°	669.2	668.5	667.8	667.2	666.8	666.3	665.9	665.4	665.9	666.3	666.8
125°	738.5	738.3	738.0	737.1	735.6	734.0	732.5	730.9	732.5	734.0	735.6
127.5°	805.4	805.1	804.8	804.2	803.3	802.4	801.5	800.7	801.5	802.4	803.3
130°	849.6	849.1	848.6	847.6	846.4	845.1	843.8	842.5	843.8	845.1	846.4
132.5°	893.6	893.7	893.8	892.8	890.7	888.6	886.4	884.3	886.4	888.6	890.7
135°	958.2	957.9	957.7	956.8	955.2	953.7	952.1	950.6	952.1	953.7	955.2
137.5°	1021.0	1020.4	1019.9	1018.8	1017.3	1015.8	1014.3	1012.8	1014.3	1015.8	1017.3
140°	1060.6	1059.8	1059.0	1058.0	1056.7	1055.4	1054.1	1052.8	1054.1	1055.4	1056.7
142.5°	1100.1	1099.1	1098.2	1097.1	1096.0	1095.0	1093.9	1092.8	1093.9	1095.0	1096.0
145°	1158.2	1157.4	1156.6	1155.7	1154.7	1153.7	1152.6	1151.6	1152.6	1153.7	1154.7
147.5°	1210.1	1209.5	1208.8	1208.2	1207.7	1207.1	1206.5	1206.0	1206.5	1207.1	1207.7
150°	1243.6	1242.6	1241.6	1241.2	1241.5	1241.7	1242.0	1242.2	1242.0	1241.7	1241.5
152.5°	1274.6	1274.2	1273.8	1273.4	1273.1	1272.7	1272.3	1272.0	1272.3	1272.7	1273.1
155°	1318.4	1318.2	1317.9	1317.8	1317.8	1317.8	1317.8	1317.8	1317.8	1317.8	1317.8
157.5°	1356.8	1356.5	1356.2	1356.4	1357.0	1357.5	1358.1	1358.7	1358.1	1357.5	1357.0
160°	1380.0	1379.7	1379.5	1379.7	1380.5	1381.3	1382.1	1382.8	1382.1	1381.3	1380.5
162.5°	1401.8	1401.7	1401.7	1401.9	1402.5	1403.1	1403.7	1404.2	1403.7	1403.1	1402.5
165°	1431.1	1430.9	1430.6	1430.7	1431.3	1431.8	1432.3	1432.8	1432.3	1431.8	1431.3
167.5°	1452.3	1452.3	1452.3	1452.8	1453.9	1454.9	1455.9	1457.0	1455.9	1454.9	1453.9
170°	1465.3	1465.3	1465.3	1465.9	1466.9	1467.9	1469.0	1470.0	1469.0	1467.9	1466.9
172.5°	1474.6	1474.6	1474.6	1475.2	1476.2	1477.2	1478.3	1479.3	1478.3	1477.2	1476.2
175°	1485.1	1485.1	1485.1	1485.6	1486.6	1487.7	1488.7	1489.7	1488.7	1487.7	1486.6
177.5°	1490.9	1491.1	1491.3	1491.8	1492.6	1493.4	1494.3	1495.1	1494.3	1493.4	1492.6
180°	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2



TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	879.5	876.1	873.4	867.3	864.0	859.4	855.8	859.7	855.5	857.3	854.6
5°	852.1	841.4	833.8	822.8	813.3	804.6	798.1	797.0	793.9	792.4	787.9
7.5°	819.1	805.8	792.7	778.3	766.1	753.8	745.8	739.3	735.0	729.3	725.4
10°	799.6	781.8	766.6	749.1	733.9	720.6	710.0	704.7	699.7	692.5	689.9
12.5°	775.6	757.2	738.6	719.9	705.4	690.5	681.4	673.4	670.0	661.8	661.0
15°	746.8	719.1	700.9	681.9	661.7	649.6	642.0	633.3	629.5	623.8	619.6
17.5°	712.5	687.7	664.9	645.3	628.0	617.8	608.3	602.3	595.8	592.1	585.2
20°	687.6	664.0	641.2	620.3	607.0	595.3	587.7	582.0	575.1	573.2	566.4
22.5°	666.6	640.6	618.7	601.2	586.7	573.4	565.2	561.3	556.6	550.7	549.4
25°	632.5	605.5	586.9	569.4	556.5	544.4	538.7	533.7	529.2	525.0	523.5
27.5°	603.0	578.9	556.8	541.0	529.8	518.7	513.7	507.7	504.3	501.0	496.9
30°	582.4	557.7	538.3	523.1	510.9	501.1	495.7	491.6	488.5	485.5	483.2
32.5°	561.1	538.2	519.4	504.6	492.4	485.0	480.2	477.3	473.9	470.3	467.4
35°	533.0	507.9	489.7	476.7	467.2	461.5	456.2	453.6	449.8	449.8	446.7
37.5°	501.3	479.6	463.5	451.7	443.2	438.1	432.4	430.6	428.1	426.5	425.5
40°	482.4	462.3	447.1	435.3	426.2	422.0	417.5	414.4	412.9	411.0	410.3
42.5°	463.0	443.8	429.2	418.3	410.4	406.8	402.6	400.5	397.4	394.9	394.5
45°	433.4	414.8	401.5	392.8	386.0	381.8	379.1	374.6	373.0	370.0	369.6
47.5°	405.4	387.5	374.5	367.3	361.3	357.9	353.7	349.2	347.4	345.9	345.8
50°	384.4	368.1	355.9	349.1	343.4	338.5	334.3	331.3	330.1	330.1	330.9
52.5°	363.2	349.3	338.9	330.6	325.2	319.9	316.1	314.2	312.5	314.3	315.7
55°	332.0	318.0	310.4	302.4	297.1	291.0	289.1	288.3	287.2	290.2	291.7
57.5°	299.0	289.2	280.3	272.4	267.6	264.1	261.5	261.1	263.2	264.6	269.6
60°	278.1	266.7	258.7	252.6	246.9	244.6	243.9	243.1	244.6	248.8	255.3
62.5°	255.0	245.7	237.1	232.6	228.4	224.6	224.4	224.9	227.9	232.7	239.2
65°	221.1	213.1	207.4	202.1	198.7	196.4	197.2	198.7	202.1	208.6	215.8
67.5°	186.7	181.2	176.1	171.8	168.5	168.5	169.3	171.6	175.6	183.0	189.6
70°	164.5	158.4	154.2	152.3	149.7	148.2	150.4	154.2	157.6	164.5	170.2
72.5°	142.3	137.1	133.9	132.6	131.4	130.2	131.0	135.1	139.7	146.6	153.2
75°	109.4	107.5	105.2	103.7	102.6	103.3	104.1	107.9	111.7	118.9	126.5
77.5°	79.9	77.9	76.5	76.1	75.5	75.9	78.0	80.8	84.6	89.8	95.6
80°	60.4	59.6	58.9	58.5	58.5	58.9	61.9	63.8	67.2	72.2	76.7
82.5°	44.0	43.5	43.4	43.3	43.6	43.7	45.5	48.0	50.8	54.6	58.5
85°	23.2	22.4	23.6	23.9	23.2	24.3	25.1	26.6	27.7	29.6	31.5
87.5°	9.5	10.5	10.5	11.2	11.6	12.5	12.5	14.0	14.8	15.7	15.6
90°	9.4	11.4	13.2	15.0	16.8	18.6	19.9	21.2	22.5	23.8	24.8
92.5°	33.9	35.7	38.0	40.2	42.4	44.6	46.3	48.0	49.7	51.4	52.6
95°	77.6	79.1	81.7	84.3	86.9	89.5	91.3	93.1	94.9	96.7	97.9
97.5°	126.3	128.2	131.8	135.3	138.9	142.5	144.2	145.9	147.6	149.3	150.3
100°	162.7	164.4	167.7	171.1	174.4	177.8	180.1	182.4	184.8	187.1	188.5
102.5°	206.8	208.2	209.9	211.6	213.3	215.0	217.5	220.0	222.6	225.1	226.7
105°	270.1	271.5	273.1	274.6	276.2	277.7	279.3	280.8	282.4	283.9	285.1
107.5°	338.9	340.1	341.3	342.5	343.7	344.9	345.7	346.4	347.2	348.0	348.4
110°	386.3	387.3	388.1	388.9	389.7	390.4	391.2	392.0	392.8	393.5	393.8



TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	432.2	433.0	434.0	435.0	435.9	436.9	437.3	437.7	438.0	438.4	438.3
115°	505.0	505.7	506.3	506.8	507.3	507.8	507.6	507.3	507.0	506.8	506.5
117.5°	574.3	574.7	575.2	575.7	576.1	576.6	576.8	577.0	577.2	577.4	577.0
120°	622.2	623.0	623.2	623.5	623.8	624.0	624.0	624.0	624.0	624.0	623.5
122.5°	667.2	667.8	668.5	669.2	669.8	670.5	670.3	670.1	669.9	669.7	669.2
125°	737.1	738.0	738.3	738.5	738.8	739.1	738.5	738.0	737.5	737.0	736.6
127.5°	804.2	804.8	805.1	805.4	805.7	806.0	805.7	805.5	805.2	805.0	804.6
130°	847.6	848.6	849.1	849.6	850.1	850.6	850.4	850.1	849.8	849.6	849.2
132.5°	892.8	893.8	893.7	893.6	893.5	893.4	893.1	892.9	892.6	892.3	891.9
135°	956.8	957.7	957.9	958.2	958.4	958.7	958.7	958.7	958.7	958.7	958.2
137.5°	1018.8	1019.9	1020.4	1021.0	1021.6	1022.1	1022.4	1022.8	1023.1	1023.4	1022.9
140°	1058.0	1059.0	1059.8	1060.6	1061.3	1062.1	1062.6	1063.1	1063.7	1064.2	1063.8
142.5°	1097.1	1098.2	1099.1	1100.1	1101.1	1102.1	1102.4	1102.7	1103.0	1103.3	1102.8
145°	1155.7	1156.6	1157.4	1158.2	1158.9	1159.7	1159.7	1159.7	1159.7	1159.7	1159.3
147.5°	1208.2	1208.8	1209.5	1210.1	1210.7	1211.3	1211.9	1212.6	1213.2	1213.8	1213.2
150°	1241.2	1241.6	1242.6	1243.6	1244.7	1245.7	1245.7	1245.7	1245.7	1245.7	1245.5
152.5°	1273.4	1273.8	1274.2	1274.6	1275.1	1275.5	1276.1	1276.7	1277.3	1277.9	1277.8
155°	1317.8	1317.9	1318.2	1318.4	1318.7	1318.9	1320.0	1321.0	1322.0	1323.1	1322.9
157.5°	1356.4	1356.2	1356.5	1356.8	1357.0	1357.3	1358.3	1359.3	1360.4	1361.4	1361.1
160°	1379.7	1379.5	1379.7	1380.0	1380.3	1380.5	1381.5	1382.6	1383.6	1384.6	1384.5
162.5°	1401.9	1401.7	1401.7	1401.8	1401.8	1401.9	1403.1	1404.4	1405.6	1406.9	1406.7
165°	1430.7	1430.6	1430.9	1431.1	1431.4	1431.6	1432.7	1433.7	1434.7	1435.8	1435.5
167.5°	1452.8	1452.3	1452.3	1452.3	1452.3	1452.3	1453.9	1455.4	1457.0	1458.5	1458.5
170°	1465.9	1465.3	1465.3	1465.3	1465.3	1465.3	1466.9	1468.4	1470.0	1471.5	1471.4
172.5°	1475.2	1474.6	1474.6	1474.6	1474.6	1474.6	1476.2	1477.7	1479.3	1480.8	1480.8
175°	1485.6	1485.1	1485.1	1485.1	1485.1	1485.1	1486.6	1488.2	1489.7	1491.3	1491.2
177.5°	1491.8	1491.3	1491.1	1490.9	1490.6	1490.4	1491.7	1492.9	1494.2	1495.4	1495.3
180°	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2



TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	852.7	854.9	853.1	855.5	853.1	854.9	852.7	854.6	857.3	855.5	859.7
5°	786.0	782.5	784.8	783.3	784.8	782.5	786.0	787.9	792.4	793.9	797.0
7.5°	724.3	721.0	717.3	715.5	717.3	721.0	724.3	725.4	729.3	735.0	739.3
10°	685.7	681.5	681.1	678.5	681.1	681.5	685.7	689.9	692.5	699.7	704.7
12.5°	657.4	653.5	649.2	648.1	649.2	653.5	657.4	661.0	661.8	670.0	673.4
15°	617.3	614.3	611.6	613.9	611.6	614.3	617.3	619.6	623.8	629.5	633.3
17.5°	583.9	581.4	581.0	578.2	581.0	581.4	583.9	585.2	592.1	595.8	602.3
20°	563.0	561.1	561.8	556.9	561.8	561.1	563.0	566.4	573.2	575.1	582.0
22.5°	546.3	542.5	542.1	541.1	542.1	542.5	546.3	549.4	550.7	556.6	561.3
25°	520.1	518.2	516.3	518.2	516.3	518.2	520.1	523.5	525.0	529.2	533.7
27.5°	497.2	494.9	494.4	494.6	494.4	494.9	497.2	496.9	501.0	504.3	507.7
30°	483.2	479.4	479.8	479.4	479.8	479.4	483.2	483.2	485.5	488.5	491.6
32.5°	468.0	465.4	464.9	464.2	464.9	465.4	468.0	467.4	470.3	473.9	477.3
35°	445.6	445.6	443.7	443.7	443.7	445.6	445.6	446.7	449.8	449.8	453.6
37.5°	424.5	424.2	423.0	423.2	423.0	424.2	424.5	425.5	426.5	428.1	430.6
40°	408.7	408.4	407.2	404.9	407.2	408.4	408.7	410.3	411.0	412.9	414.4
42.5°	393.6	392.3	391.7	391.0	391.7	392.3	393.6	394.5	394.9	397.4	400.5
45°	369.6	369.6	368.9	368.5	368.9	369.6	369.6	369.6	370.0	373.0	374.6
47.5°	346.4	347.1	348.5	348.3	348.5	347.1	346.4	345.8	345.9	347.4	349.2
50°	332.4	332.8	333.9	334.3	333.9	332.8	332.4	330.9	330.1	330.1	331.3
52.5°	316.9	319.1	320.5	320.3	320.5	319.1	316.9	315.7	314.3	312.5	314.2
55°	295.2	297.8	300.5	300.9	300.5	297.8	295.2	291.7	290.2	287.2	288.3
57.5°	273.7	277.4	280.2	281.1	280.2	277.4	273.7	269.6	264.6	263.2	261.1
60°	259.1	264.0	267.4	269.0	267.4	264.0	259.1	255.3	248.8	244.6	243.1
62.5°	245.1	250.6	254.1	254.4	254.1	250.6	245.1	239.2	232.7	227.9	224.9
65°	222.2	227.9	231.0	233.2	231.0	227.9	222.2	215.8	208.6	202.1	198.7
67.5°	197.6	203.3	206.7	208.5	206.7	203.3	197.6	189.6	183.0	175.6	171.6
70°	179.7	185.4	189.9	191.5	189.9	185.4	179.7	170.2	164.5	157.6	154.2
72.5°	162.1	167.1	170.8	172.6	170.8	167.1	162.1	153.2	146.6	139.7	135.1
75°	131.4	138.3	141.7	143.6	141.7	138.3	131.4	126.5	118.9	111.7	107.9
77.5°	101.4	107.6	109.6	110.6	109.6	107.6	101.4	95.6	89.8	84.6	80.8
80°	81.3	85.1	87.8	88.1	87.8	85.1	81.3	76.7	72.2	67.2	63.8
82.5°	62.5	65.6	66.5	67.5	66.5	65.6	62.5	58.5	54.6	50.8	48.0
85°	34.2	35.7	36.1	35.7	36.1	35.7	34.2	31.5	29.6	27.7	26.6
87.5°	16.4	16.2	16.4	17.1	16.4	16.2	16.4	15.6	15.7	14.8	14.0
90°	25.6	26.3	27.1	27.9	27.1	26.3	25.6	24.8	23.8	22.5	21.2
92.5°	53.1	53.7	54.3	54.8	54.3	53.7	53.1	52.6	51.4	49.7	48.0
95°	98.4	98.9	99.4	99.9	99.4	98.9	98.4	97.9	96.7	94.9	93.1
97.5°	150.6	150.9	151.2	151.5	151.2	150.9	150.6	150.3	149.3	147.6	145.9
100°	189.0	189.5	190.1	190.6	190.1	189.5	189.0	188.5	187.1	184.8	182.4
102.5°	227.5	228.2	228.9	229.6	228.9	228.2	227.5	226.7	225.1	222.6	220.0
105°	285.9	286.6	287.4	288.2	287.4	286.6	285.9	285.1	283.9	282.4	280.8
107.5°	348.3	348.3	348.2	348.1	348.2	348.3	348.3	348.4	348.0	347.2	346.4
110°	393.5	393.3	393.0	392.8	393.0	393.3	393.5	393.8	393.5	392.8	392.0



TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	437.9	437.4	436.9	436.5	436.9	437.4	437.9	438.3	438.4	438.0	437.7
115°	506.3	506.0	505.7	505.5	505.7	506.0	506.3	506.5	506.8	507.0	507.3
117.5°	576.0	575.0	573.9	572.9	573.9	575.0	576.0	577.0	577.4	577.2	577.0
120°	622.5	621.4	620.4	619.4	620.4	621.4	622.5	623.5	624.0	624.0	624.0
122.5°	668.3	667.5	666.7	665.9	666.7	667.5	668.3	669.2	669.7	669.9	670.1
125°	736.4	736.1	735.8	735.6	735.8	736.1	736.4	736.6	737.0	737.5	738.0
127.5°	804.1	803.5	803.0	802.5	803.0	803.5	804.1	804.6	805.0	805.2	805.5
130°	848.7	848.2	847.6	847.1	847.6	848.2	848.7	849.2	849.6	849.8	850.1
132.5°	891.1	890.4	889.7	889.0	889.7	890.4	891.1	891.9	892.3	892.6	892.9
135°	957.1	956.1	955.1	954.0	955.1	956.1	957.1	958.2	958.7	958.7	958.7
137.5°	1021.6	1020.3	1019.0	1017.7	1019.0	1020.3	1021.6	1022.9	1023.4	1023.1	1022.8
140°	1062.5	1061.2	1059.9	1058.6	1059.9	1061.2	1062.5	1063.8	1064.2	1063.7	1063.1
142.5°	1101.5	1100.3	1099.0	1097.7	1099.0	1100.3	1101.5	1102.8	1103.3	1103.0	1102.7
145°	1158.6	1157.8	1157.0	1156.2	1157.0	1157.8	1158.6	1159.3	1159.7	1159.7	1159.7
147.5°	1211.5	1209.7	1208.0	1206.2	1208.0	1209.7	1211.5	1213.2	1213.8	1213.2	1212.6
150°	1244.9	1244.4	1243.9	1243.4	1243.9	1244.4	1244.9	1245.5	1245.7	1245.7	1245.7
152.5°	1276.9	1275.9	1275.0	1274.1	1275.0	1275.9	1276.9	1277.8	1277.9	1277.3	1276.7
155°	1321.6	1320.3	1319.1	1317.8	1319.1	1320.3	1321.6	1322.9	1323.1	1322.0	1321.0
157.5°	1359.4	1357.7	1356.0	1354.3	1356.0	1357.7	1359.4	1361.1	1361.4	1360.4	1359.3
160°	1383.2	1381.9	1380.6	1379.4	1380.6	1381.9	1383.2	1384.5	1384.6	1383.6	1382.6
162.5°	1405.2	1403.7	1402.2	1400.7	1402.2	1403.7	1405.2	1406.7	1406.9	1405.6	1404.4
165°	1434.0	1432.4	1430.9	1429.3	1430.9	1432.4	1434.0	1435.5	1435.8	1434.7	1433.7
167.5°	1456.9	1455.3	1453.7	1452.1	1453.7	1455.3	1456.9	1458.5	1458.5	1457.0	1455.4
170°	1469.6	1467.8	1466.0	1464.2	1466.0	1467.8	1469.6	1471.4	1471.5	1470.0	1468.4
172.5°	1479.2	1477.6	1476.0	1474.4	1476.0	1477.6	1479.2	1480.8	1480.8	1479.3	1477.7
175°	1489.4	1487.6	1485.7	1483.9	1485.7	1487.6	1489.4	1491.2	1491.3	1489.7	1488.2
177.5°	1493.9	1492.4	1491.0	1489.5	1491.0	1492.4	1493.9	1495.3	1495.4	1494.2	1492.9
180°	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2



TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	855.8	859.4	864.0	867.3	873.4	876.1	879.5	882.2	887.1	891.6	897.1
5°	798.1	804.6	813.3	822.8	833.8	841.4	852.1	858.5	871.4	883.2	894.6
7.5°	745.8	753.8	766.1	778.3	792.7	805.8	819.1	833.8	850.3	869.8	885.9
10°	710.0	720.6	733.9	749.1	766.6	781.8	799.6	815.6	835.7	858.5	879.8
12.5°	681.4	690.5	705.4	719.9	738.6	757.2	775.6	796.8	820.2	845.5	872.2
15°	642.0	649.6	661.7	681.9	700.9	719.1	746.8	766.6	796.2	824.3	856.6
17.5°	608.3	617.8	628.0	645.3	664.9	687.7	712.5	737.3	765.8	801.5	837.9
20°	587.7	595.3	607.0	620.3	641.2	664.0	687.6	712.6	747.6	784.4	823.6
22.5°	565.2	573.4	586.7	601.2	618.7	640.6	666.6	694.1	730.6	766.8	809.3
25°	538.7	544.4	556.5	569.4	586.9	605.5	632.5	662.9	699.0	740.4	783.7
27.5°	513.7	518.7	529.8	541.0	556.8	578.9	603.0	633.7	667.7	709.7	757.7
30°	495.7	501.1	510.9	523.1	538.3	557.7	582.4	611.2	647.7	688.7	738.9
32.5°	480.2	485.0	492.4	504.6	519.4	538.2	561.1	590.6	627.0	668.7	717.9
35°	456.2	461.5	467.2	476.7	489.7	507.9	533.0	560.7	595.6	635.9	681.1
37.5°	432.4	438.1	443.2	451.7	463.5	479.6	501.3	530.2	561.8	600.6	644.0
40°	417.5	422.0	426.2	435.3	447.1	462.3	482.4	508.3	541.7	577.8	613.9
42.5°	402.6	406.8	410.4	418.3	429.2	443.8	463.0	488.2	519.2	552.9	584.7
45°	379.1	381.8	386.0	392.8	401.5	414.8	433.4	455.9	482.1	514.0	537.9
47.5°	353.7	357.9	361.3	367.3	374.5	387.5	405.4	424.5	448.3	472.0	488.8
50°	334.3	338.5	343.4	349.1	355.9	368.1	384.4	403.8	423.9	442.2	456.6
52.5°	316.1	319.9	325.2	330.6	338.9	349.3	363.2	380.4	400.2	413.3	425.3
55°	289.1	291.0	297.1	302.4	310.4	318.0	332.0	347.2	359.4	369.2	379.1
57.5°	261.5	264.1	267.6	272.4	280.3	289.2	299.0	312.5	319.6	324.7	332.4
60°	243.9	244.6	246.9	252.6	258.7	266.7	278.1	287.6	292.9	297.1	303.5
62.5°	224.4	224.6	228.4	232.6	237.1	245.7	255.0	262.6	267.1	269.1	275.3
65°	197.2	196.4	198.7	202.1	207.4	213.1	221.1	227.9	227.5	229.8	233.6
67.5°	169.3	168.5	168.5	171.8	176.1	181.2	186.7	190.6	190.7	193.7	195.6
70°	150.4	148.2	149.7	152.3	154.2	158.4	164.5	166.0	166.4	167.9	169.8
72.5°	131.0	130.2	131.4	132.6	133.9	137.1	142.3	143.2	143.3	144.2	147.3
75°	104.1	103.3	102.6	103.7	105.2	107.5	109.4	110.9	110.5	110.9	113.2
77.5°	78.0	75.9	75.5	76.1	76.5	77.9	79.9	79.7	80.1	80.0	82.6
80°	61.9	58.9	58.5	58.5	58.9	59.6	60.4	61.2	60.0	61.2	61.9
82.5°	45.5	43.7	43.6	43.3	43.4	43.5	44.0	44.4	44.2	44.7	45.2
85°	25.1	24.3	23.2	23.9	23.6	22.4	23.2	22.0	21.7	22.0	22.4
87.5°	12.5	12.5	11.6	11.2	10.5	10.5	9.5	8.8	8.0	7.9	8.4
90°	19.9	18.6	16.8	15.0	13.2	11.4	9.4	7.4	5.3	3.2	1.2
92.5°	46.3	44.6	42.4	40.2	38.0	35.7	33.9	32.5	31.0	29.6	28.1
95°	91.3	89.5	86.9	84.3	81.7	79.1	77.6	77.1	76.6	76.0	75.5
97.5°	144.2	142.5	138.9	135.3	131.8	128.2	126.3	126.1	125.9	125.7	125.5
100°	180.1	177.8	174.4	171.1	167.7	164.4	162.7	162.7	162.7	162.7	162.7
102.5°	217.5	215.0	213.3	211.6	209.9	208.2	206.8	205.8	204.7	203.7	202.7
105°	279.3	277.7	276.2	274.6	273.1	271.5	270.1	268.8	267.5	266.2	264.9
107.5°	345.7	344.9	343.7	342.5	341.3	340.1	338.9	337.6	336.3	335.0	333.7
110°	391.2	390.4	389.7	388.9	388.1	387.3	386.3	385.0	383.7	382.4	381.2



TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	437.3	436.9	435.9	435.0	434.0	433.0	432.2	431.5	430.8	430.2	429.5
115°	507.6	507.8	507.3	506.8	506.3	505.7	505.0	503.9	502.9	501.9	500.8
117.5°	576.8	576.6	576.1	575.7	575.2	574.7	574.3	573.8	573.4	572.9	572.4
120°	624.0	624.0	623.8	623.5	623.2	623.0	622.2	620.9	619.6	618.3	617.0
122.5°	670.3	670.5	669.8	669.2	668.5	667.8	667.2	666.8	666.3	665.9	665.4
125°	738.5	739.1	738.8	738.5	738.3	738.0	737.1	735.6	734.0	732.5	730.9
127.5°	805.7	806.0	805.7	805.4	805.1	804.8	804.2	803.3	802.4	801.5	800.7
130°	850.4	850.6	850.1	849.6	849.1	848.6	847.6	846.4	845.1	843.8	842.5
132.5°	893.1	893.4	893.5	893.6	893.7	893.8	892.8	890.7	888.6	886.4	884.3
135°	958.7	958.7	958.4	958.2	957.9	957.7	956.8	955.2	953.7	952.1	950.6
137.5°	1022.4	1022.1	1021.6	1021.0	1020.4	1019.9	1018.8	1017.3	1015.8	1014.3	1012.8
140°	1062.6	1062.1	1061.3	1060.6	1059.8	1059.0	1058.0	1056.7	1055.4	1054.1	1052.8
142.5°	1102.4	1102.1	1101.1	1100.1	1099.1	1098.2	1097.1	1096.0	1095.0	1093.9	1092.8
145°	1159.7	1159.7	1158.9	1158.2	1157.4	1156.6	1155.7	1154.7	1153.7	1152.6	1151.6
147.5°	1211.9	1211.3	1210.7	1210.1	1209.5	1208.8	1208.2	1207.7	1207.1	1206.5	1206.0
150°	1245.7	1245.7	1244.7	1243.6	1242.6	1241.6	1241.2	1241.5	1241.7	1242.0	1242.2
152.5°	1276.1	1275.5	1275.1	1274.6	1274.2	1273.8	1273.4	1273.1	1272.7	1272.3	1272.0
155°	1320.0	1318.9	1318.7	1318.4	1318.2	1317.9	1317.8	1317.8	1317.8	1317.8	1317.8
157.5°	1358.3	1357.3	1357.0	1356.8	1356.5	1356.2	1356.4	1357.0	1357.5	1358.1	1358.7
160°	1381.5	1380.5	1380.3	1380.0	1379.7	1379.5	1379.7	1380.5	1381.3	1382.1	1382.8
162.5°	1403.1	1401.9	1401.8	1401.8	1401.7	1401.7	1401.9	1402.5	1403.1	1403.7	1404.2
165°	1432.7	1431.6	1431.4	1431.1	1430.9	1430.6	1430.7	1431.3	1431.8	1432.3	1432.8
167.5°	1453.9	1452.3	1452.3	1452.3	1452.3	1452.3	1452.8	1453.9	1454.9	1455.9	1457.0
170°	1466.9	1465.3	1465.3	1465.3	1465.3	1465.3	1465.9	1466.9	1467.9	1469.0	1470.0
172.5°	1476.2	1474.6	1474.6	1474.6	1474.6	1474.6	1475.2	1476.2	1477.2	1478.3	1479.3
175°	1486.6	1485.1	1485.1	1485.1	1485.1	1485.1	1485.6	1486.6	1487.7	1488.7	1489.7
177.5°	1491.7	1490.4	1490.6	1490.9	1491.1	1491.3	1491.8	1492.6	1493.4	1494.3	1495.1
180°	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2



TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	899.9	904.1	906.8	912.0	916.3	918.7	920.8	922.6	924.8	926.6	931.8
5°	905.6	915.5	923.9	936.8	948.6	957.7	967.5	976.3	983.5	993.8	1001.7
7.5°	903.1	920.7	939.1	959.0	979.5	998.5	1015.9	1032.3	1047.1	1065.0	1080.7
10°	900.7	924.6	948.2	975.1	1002.9	1026.4	1048.5	1070.9	1087.2	1110.0	1129.4
12.5°	898.9	927.1	955.5	987.9	1018.4	1051.6	1081.0	1097.3	1122.2	1140.4	1163.4
15°	891.2	928.4	967.5	1004.0	1047.3	1078.1	1103.9	1135.8	1159.0	1182.2	1207.2
17.5°	877.4	919.6	963.4	1011.2	1052.7	1085.8	1119.0	1149.8	1177.5	1208.5	1239.8
20°	871.1	913.2	963.4	1012.4	1053.0	1087.6	1121.8	1155.6	1186.0	1225.9	1261.9
22.5°	857.7	908.7	954.9	1002.6	1044.5	1082.1	1120.9	1159.2	1199.6	1244.7	1289.9
25°	833.8	885.5	934.5	981.6	1023.8	1070.9	1112.3	1163.6	1215.2	1274.9	1331.1
27.5°	809.1	858.5	903.4	948.9	998.1	1051.4	1105.1	1163.3	1231.0	1306.2	1385.6
30°	789.0	835.7	879.4	926.1	977.4	1037.4	1096.3	1165.5	1243.7	1328.4	1422.6
32.5°	765.6	808.7	851.2	900.6	956.5	1019.8	1088.4	1164.2	1258.3	1354.6	1451.5
35°	725.6	761.7	805.3	858.1	921.2	993.8	1073.2	1162.8	1270.7	1381.2	1462.9
37.5°	678.1	711.7	757.7	815.6	881.7	959.6	1053.8	1160.1	1274.7	1362.8	1389.2
40°	646.2	677.3	725.2	785.2	852.8	935.3	1038.6	1151.0	1261.9	1318.2	1296.5
42.5°	612.1	644.8	691.5	750.9	823.6	913.4	1019.4	1131.9	1224.9	1246.1	1171.3
45°	558.4	592.2	638.2	698.2	776.5	873.7	984.3	1086.4	1140.0	1101.6	985.8
47.5°	508.5	540.2	582.8	644.7	725.5	826.1	932.5	1014.0	1018.3	926.7	803.0
50°	474.5	503.7	546.6	608.6	688.7	790.5	886.6	950.8	922.0	818.3	699.4
52.5°	441.0	469.7	512.0	573.3	652.6	745.8	835.3	880.3	825.9	719.5	617.9
55°	392.8	417.9	459.3	515.9	591.1	677.7	753.7	769.2	698.6	593.7	511.3
57.5°	345.7	369.1	406.8	458.9	527.6	604.4	663.8	660.5	585.8	495.8	430.4
60°	313.8	336.6	370.0	420.9	483.6	549.7	600.6	588.4	514.4	436.9	381.8
62.5°	285.2	305.6	337.2	381.7	438.9	500.1	541.9	524.0	451.4	383.7	340.1
65°	243.1	260.2	287.2	325.2	372.7	423.2	455.5	432.3	370.4	317.6	282.6
67.5°	202.9	216.6	239.2	269.6	310.1	350.6	370.3	347.0	297.4	258.9	233.0
70°	177.4	189.6	207.0	234.0	269.3	303.5	318.3	297.4	254.9	221.8	203.2
72.5°	151.9	161.9	177.3	201.5	229.8	259.5	272.4	252.5	217.5	189.6	172.2
75°	117.4	124.2	134.9	151.6	174.0	197.5	204.8	187.3	164.9	144.0	132.6
77.5°	84.0	89.8	97.9	108.4	124.3	139.3	145.6	135.5	118.1	104.9	95.6
80°	64.6	67.6	74.5	83.2	95.7	105.2	109.4	102.9	90.8	80.9	73.7
82.5°	46.0	49.1	53.2	60.4	68.4	74.8	79.3	75.0	66.2	58.4	54.2
85°	22.4	24.3	26.6	29.6	35.7	39.5	39.1	36.5	33.0	30.0	27.7
87.5°	8.5	9.3	10.6	12.5	13.8	15.4	16.4	16.1	15.3	14.6	14.0
90°	3.2	5.3	7.4	9.4	11.4	13.2	15.0	16.8	18.6	19.9	21.2
92.5°	29.6	31.0	32.5	33.9	35.7	38.0	40.2	42.4	44.6	46.3	48.0
95°	76.0	76.6	77.1	77.6	79.1	81.7	84.3	86.9	89.5	91.3	93.1
97.5°	125.7	125.9	126.1	126.3	128.2	131.8	135.3	138.9	142.5	144.2	145.9
100°	162.7	162.7	162.7	162.7	164.4	167.7	171.1	174.4	177.8	180.1	182.4
102.5°	203.7	204.7	205.8	206.8	208.2	209.9	211.6	213.3	215.0	217.5	220.0
105°	266.2	267.5	268.8	270.1	271.5	273.1	274.6	276.2	277.7	279.3	280.8
107.5°	335.0	336.3	337.6	338.9	340.1	341.3	342.5	343.7	344.9	345.7	346.4
110°	382.4	383.7	385.0	386.3	387.3	388.1	388.9	389.7	390.4	391.2	392.0





TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	430.2	430.8	431.5	432.2	433.0	434.0	435.0	435.9	436.9	437.3	437.7
115°	501.9	502.9	503.9	505.0	505.7	506.3	506.8	507.3	507.8	507.6	507.3
117.5°	572.9	573.4	573.8	574.3	574.7	575.2	575.7	576.1	576.6	576.8	577.0
120°	618.3	619.6	620.9	622.2	623.0	623.2	623.5	623.8	624.0	624.0	624.0
122.5°	665.9	666.3	666.8	667.2	667.8	668.5	669.2	669.8	670.5	670.3	670.1
125°	732.5	734.0	735.6	737.1	738.0	738.3	738.5	738.8	739.1	738.5	738.0
127.5°	801.5	802.4	803.3	804.2	804.8	805.1	805.4	805.7	806.0	805.7	805.5
130°	843.8	845.1	846.4	847.6	848.6	849.1	849.6	850.1	850.6	850.4	850.1
132.5°	886.4	888.6	890.7	892.8	893.8	893.7	893.6	893.5	893.4	893.1	892.9
135°	952.1	953.7	955.2	956.8	957.7	957.9	958.2	958.4	958.7	958.7	958.7
137.5°	1014.3	1015.8	1017.3	1018.8	1019.9	1020.4	1021.0	1021.6	1022.1	1022.4	1022.8
140°	1054.1	1055.4	1056.7	1058.0	1059.0	1059.8	1060.6	1061.3	1062.1	1062.6	1063.1
142.5°	1093.9	1095.0	1096.0	1097.1	1098.2	1099.1	1100.1	1101.1	1102.1	1102.4	1102.7
145°	1152.6	1153.7	1154.7	1155.7	1156.6	1157.4	1158.2	1158.9	1159.7	1159.7	1159.7
147.5°	1206.5	1207.1	1207.7	1208.2	1208.8	1209.5	1210.1	1210.7	1211.3	1211.9	1212.6
150°	1242.0	1241.7	1241.5	1241.2	1241.6	1242.6	1243.6	1244.7	1245.7	1245.7	1245.7
152.5°	1272.3	1272.7	1273.1	1273.4	1273.8	1274.2	1274.6	1275.1	1275.5	1276.1	1276.7
155°	1317.8	1317.8	1317.8	1317.8	1317.9	1318.2	1318.4	1318.7	1318.9	1320.0	1321.0
157.5°	1358.1	1357.5	1357.0	1356.4	1356.2	1356.5	1356.8	1357.0	1357.3	1358.3	1359.3
160°	1382.1	1381.3	1380.5	1379.7	1379.5	1379.7	1380.0	1380.3	1380.5	1381.5	1382.6
162.5°	1403.7	1403.1	1402.5	1401.9	1401.7	1401.7	1401.8	1401.8	1401.9	1403.1	1404.4
165°	1432.3	1431.8	1431.3	1430.7	1430.6	1430.9	1431.1	1431.4	1431.6	1432.7	1433.7
167.5°	1455.9	1454.9	1453.9	1452.8	1452.3	1452.3	1452.3	1452.3	1452.3	1453.9	1455.4
170°	1469.0	1467.9	1466.9	1465.9	1465.3	1465.3	1465.3	1465.3	1465.3	1466.9	1468.4
172.5°	1478.3	1477.2	1476.2	1475.2	1474.6	1474.6	1474.6	1474.6	1474.6	1476.2	1477.7
175°	1488.7	1487.7	1486.6	1485.6	1485.1	1485.1	1485.1	1485.1	1485.1	1486.6	1488.2
177.5°	1494.3	1493.4	1492.6	1491.8	1491.3	1491.1	1490.9	1490.6	1490.4	1491.7	1492.9
180°	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2



TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	936.0	938.4	943.6	941.8	944.2	945.4	946.7
5°	1011.6	1023.8	1029.1	1028.3	1036.3	1034.4	1032.5
7.5°	1097.0	1109.8	1116.9	1125.8	1131.0	1131.3	1135.8
10°	1145.3	1162.0	1168.9	1178.4	1184.5	1187.9	1187.5
12.5°	1182.4	1195.5	1210.8	1215.5	1223.7	1228.0	1226.4
15°	1227.0	1247.9	1263.8	1271.8	1282.1	1285.1	1289.3
17.5°	1266.8	1294.8	1313.5	1338.2	1347.6	1353.3	1349.9
20°	1296.9	1333.7	1352.4	1382.0	1398.3	1407.1	1404.0
22.5°	1332.5	1372.3	1406.8	1432.4	1457.3	1469.1	1471.5
25°	1393.4	1448.1	1498.6	1532.4	1563.2	1570.4	1586.4
27.5°	1461.5	1526.0	1580.0	1615.5	1637.0	1645.0	1650.0
30°	1504.3	1568.5	1609.2	1631.9	1638.8	1638.0	1637.3
32.5°	1525.3	1565.5	1573.3	1566.9	1551.3	1538.0	1524.2
35°	1495.6	1465.6	1420.7	1363.0	1320.5	1277.5	1273.3
37.5°	1345.1	1249.1	1174.5	1091.2	1043.1	1013.4	992.8
40°	1203.4	1094.4	1004.0	933.7	884.7	865.4	846.4
42.5°	1049.7	945.5	865.4	806.7	769.9	748.4	733.3
45°	852.8	760.9	698.2	655.7	626.4	609.7	600.2
47.5°	698.8	630.8	577.6	546.9	526.7	513.7	513.7
50°	616.2	551.2	515.9	491.6	474.1	463.8	465.7
52.5°	542.9	494.4	464.2	443.8	430.9	424.6	424.4
55°	454.0	419.0	399.3	384.4	375.7	368.5	370.0
57.5°	388.3	358.8	345.6	333.3	327.2	324.3	320.2
60°	347.6	324.8	313.4	303.5	297.4	295.2	291.0
62.5°	311.4	293.5	282.4	274.3	268.9	268.1	264.8
65°	261.7	248.1	238.2	234.4	228.7	227.2	227.2
67.5°	215.8	206.0	198.3	194.8	192.3	192.7	190.8
70°	186.9	178.9	174.0	170.2	168.3	168.7	167.1
72.5°	163.5	154.6	150.3	148.0	145.5	146.5	145.9
75°	123.8	119.3	117.0	114.7	113.2	112.4	111.7
77.5°	90.9	86.9	85.2	83.9	84.1	82.3	83.7
80°	70.3	66.9	65.7	63.8	63.4	63.4	63.1
82.5°	51.4	49.5	48.7	47.1	46.4	47.0	46.0
85°	26.6	25.1	24.7	24.7	23.9	23.2	25.1
87.5°	14.2	13.3	13.5	13.3	13.5	13.3	12.9
90°	22.5	23.8	24.8	25.6	26.3	27.1	27.9
92.5°	49.7	51.4	52.6	53.1	53.7	54.3	54.8
95°	94.9	96.7	97.9	98.4	98.9	99.4	99.9
97.5°	147.6	149.3	150.3	150.6	150.9	151.2	151.5
100°	184.8	187.1	188.5	189.0	189.5	190.1	190.6
102.5°	222.6	225.1	226.7	227.5	228.2	228.9	229.6
105°	282.4	283.9	285.1	285.9	286.6	287.4	288.2
107.5°	347.2	348.0	348.4	348.3	348.3	348.2	348.1
110°	392.8	393.5	393.8	393.5	393.3	393.0	392.8



TEST NUMBER: P333197

CATALOG NUMBER: S125DIP-S610D1205U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	438.0	438.4	438.3	437.9	437.4	436.9	436.5
115°	507.0	506.8	506.5	506.3	506.0	505.7	505.5
117.5°	577.2	577.4	577.0	576.0	575.0	573.9	572.9
120°	624.0	624.0	623.5	622.5	621.4	620.4	619.4
122.5°	669.9	669.7	669.2	668.3	667.5	666.7	665.9
125°	737.5	737.0	736.6	736.4	736.1	735.8	735.6
127.5°	805.2	805.0	804.6	804.1	803.5	803.0	802.5
130°	849.8	849.6	849.2	848.7	848.2	847.6	847.1
132.5°	892.6	892.3	891.9	891.1	890.4	889.7	889.0
135°	958.7	958.7	958.2	957.1	956.1	955.1	954.0
137.5°	1023.1	1023.4	1022.9	1021.6	1020.3	1019.0	1017.7
140°	1063.7	1064.2	1063.8	1062.5	1061.2	1059.9	1058.6
142.5°	1103.0	1103.3	1102.8	1101.5	1100.3	1099.0	1097.7
145°	1159.7	1159.7	1159.3	1158.6	1157.8	1157.0	1156.2
147.5°	1213.2	1213.8	1213.2	1211.5	1209.7	1208.0	1206.2
150°	1245.7	1245.7	1245.5	1244.9	1244.4	1243.9	1243.4
152.5°	1277.3	1277.9	1277.8	1276.9	1275.9	1275.0	1274.1
155°	1322.0	1323.1	1322.9	1321.6	1320.3	1319.1	1317.8
157.5°	1360.4	1361.4	1361.1	1359.4	1357.7	1356.0	1354.3
160°	1383.6	1384.6	1384.5	1383.2	1381.9	1380.6	1379.4
162.5°	1405.6	1406.9	1406.7	1405.2	1403.7	1402.2	1400.7
165°	1434.7	1435.8	1435.5	1434.0	1432.4	1430.9	1429.3
167.5°	1457.0	1458.5	1458.5	1456.9	1455.3	1453.7	1452.1
170°	1470.0	1471.5	1471.4	1469.6	1467.8	1466.0	1464.2
172.5°	1479.3	1480.8	1480.8	1479.2	1477.6	1476.0	1474.4
175°	1489.7	1491.3	1491.2	1489.4	1487.6	1485.7	1483.9
177.5°	1494.2	1495.4	1495.3	1493.9	1492.4	1491.0	1489.5
180°	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2

(END OF REPORT)