

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333213-940

Luminaire Tested: **S125DIP-S850D365U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333213-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D365U940-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4219.1 lumens  
Efficiency: N/A  
Efficacy: 120.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333213-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333213-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	72
1	103	98	94	90	97	93	90	86	84	81	79	75	73	71	68	66	65	61
2	93	86	79	74	88	81	76	71	74	69	65	66	63	60	59	57	54	51
3	85	75	68	62	81	72	65	59	65	59	55	59	54	50	53	49	46	43
4	78	67	59	52	74	64	56	50	58	52	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	42	38	42	38	35	32
6	66	54	45	39	63	51	43	38	47	40	35	42	37	33	38	34	31	28
7	61	49	40	34	58	46	39	33	42	36	31	39	33	29	35	31	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	40	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7559	7559	7559
5°	7577	7505	7553
10°	7531	7452	7494
15°	7449	7362	7393
20°	7332	7236	7249
25°	7207	7088	7081
30°	7052	6927	6893
35°	6885	6754	6659
40°	6715	6566	6473
45°	6530	6395	6268
50°	6327	6187	6002
55°	6132	5954	5788
60°	5898	5717	5515
65°	5619	5434	5251
70°	5351	5108	4932
75°	4876	4716	4551
80°	4340	4273	4169
85°	3772	3846	3631



TEST NUMBER: P333213-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.4	2.6
10°-20°	311.8	7.4
20°-30°	460.3	10.9
30°-40°	537.2	12.7
40°-50°	539.5	12.8
50°-60°	473.6	11.2
60°-70°	352.9	8.4
70°-80°	201.8	4.8
80°-90°	59.6	1.4
90°-100°	113.3	2.7
100°-110°	243.6	5.8
110°-120°	228.6	5.4
120°-130°	185.2	4.4
130°-140°	148.7	3.5
140°-150°	112.2	2.7
150°-160°	79.0	1.9
160°-170°	46.5	1.1
170°-180°	15.1	0.4
0°-30°	882.5	20.9
0°-40°	1419.6	33.6
0°-60°	2432.7	57.7
0°-90°	3047.0	72.2
90°-120°	585.4	13.9
90°-150°	1031.5	24.4
90°-180°	1172.0	27.8
0°-180°	4219.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1170	1170	1170	1170	1170	
5°	1169	1166	1158	1165	1165	111
15°	1114	1111	1101	1106	1106	314
25°	1011	1006	995	996	994	465
35°	873	869	857	852	845	546
45°	715	711	700	690	686	551
55°	545	541	529	521	514	486
65°	368	365	356	348	344	365
75°	195	193	189	186	182	208
85°	51	52	52	51	49	57
90°	0	3	5	7	7	3
95°	10	31	279	127	74	11
105°	36	50	228	450	418	38
115°	64	77	183	395	465	63
125°	88	103	176	314	366	78
135°	103	124	175	264	304	80
145°	120	138	175	218	240	75
155°	137	148	171	193	201	63
165°	150	154	164	174	176	42
175°	156	156	157	159	158	15
180°	156	156	156	156	156	



TEST NUMBER: P333213-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1173.6	1173.0	1172.6	1172.1	1171.5	1170.5	1168.9	1167.2	1165.6	1164.0	1165.6
5°	1168.8	1168.3	1167.9	1167.5	1167.1	1165.8	1163.8	1161.7	1159.7	1157.6	1159.5
7.5°	1158.0	1157.6	1157.2	1156.7	1156.4	1155.0	1152.7	1150.5	1148.3	1145.9	1147.7
10°	1148.3	1148.0	1147.5	1147.1	1146.7	1145.4	1143.1	1140.9	1138.6	1136.3	1138.0
12.5°	1136.5	1135.8	1135.1	1134.3	1133.5	1132.1	1130.1	1127.9	1125.8	1123.7	1125.1
15°	1114.1	1113.5	1112.9	1112.2	1111.6	1110.2	1108.0	1105.6	1103.4	1101.1	1102.2
17.5°	1088.3	1087.4	1086.5	1085.7	1084.8	1083.1	1080.8	1078.4	1076.0	1073.7	1075.0
20°	1066.8	1066.5	1066.0	1065.6	1065.2	1063.6	1061.0	1058.3	1055.6	1052.9	1054.4
22.5°	1045.4	1044.6	1043.9	1043.1	1042.4	1040.8	1038.3	1035.7	1033.2	1030.7	1031.7
25°	1011.3	1010.3	1009.2	1008.2	1007.2	1005.3	1002.6	1000.0	997.3	994.6	995.1
27.5°	971.4	970.9	970.3	969.6	969.0	967.3	964.6	961.8	959.0	956.3	956.4
30°	945.6	944.9	944.3	943.7	943.1	941.2	938.2	935.0	931.9	928.9	928.4
32.5°	917.4	916.4	915.5	914.5	913.6	911.8	909.0	906.2	903.5	900.7	900.0
35°	873.3	872.4	871.6	870.8	870.0	868.2	865.3	862.4	859.5	856.7	855.6
37.5°	827.6	826.5	825.5	824.5	823.4	821.5	818.9	816.1	813.4	810.7	809.1
40°	796.5	795.4	794.4	793.4	792.3	790.4	787.5	784.6	781.8	778.8	777.0
42.5°	763.1	762.2	761.3	760.5	759.6	757.8	754.9	752.0	749.1	746.3	744.6
45°	715.0	714.1	713.3	712.5	711.7	710.0	707.6	705.1	702.6	700.2	697.7
47.5°	663.1	663.2	663.2	663.2	663.3	661.8	658.8	655.9	652.9	650.0	647.4
50°	629.7	629.1	628.5	627.9	627.3	625.7	623.3	620.8	618.3	615.8	613.1
52.5°	595.7	595.2	594.8	594.3	593.9	592.3	589.7	587.0	584.4	581.8	579.4
55°	544.6	543.9	543.3	542.7	542.1	540.3	537.4	534.6	531.6	528.8	526.9
57.5°	490.6	490.4	490.0	489.6	489.4	487.9	485.5	483.1	480.6	478.2	475.8
60°	456.6	455.8	455.0	454.1	453.3	451.7	449.4	447.2	445.0	442.6	440.6
62.5°	421.0	420.4	419.7	419.0	418.4	417.1	415.2	413.2	411.3	409.3	407.2
65°	367.7	367.2	366.8	366.4	366.0	364.7	362.4	360.2	357.8	355.6	353.7
67.5°	316.0	315.1	314.2	313.3	312.5	311.2	309.6	307.9	306.2	304.5	302.9
70°	283.4	282.3	281.3	280.3	279.3	277.9	276.0	274.1	272.2	270.5	269.2
72.5°	247.8	247.1	246.4	245.8	245.0	244.1	242.9	241.7	240.5	239.3	237.9
75°	195.4	195.0	194.6	194.2	193.8	193.1	192.0	191.0	189.9	189.0	188.3
77.5°	147.0	146.9	146.8	146.6	146.4	146.1	145.4	144.9	144.3	143.7	143.4
80°	116.7	116.7	116.7	116.7	116.7	116.5	116.1	115.7	115.2	114.9	114.7
82.5°	90.0	89.7	89.3	89.0	88.7	88.5	88.4	88.4	88.3	88.2	87.8
85°	50.9	51.2	51.4	51.5	51.7	51.9	51.9	51.9	51.9	51.9	51.6
87.5°	20.1	20.2	20.2	20.4	20.5	20.5	20.4	20.4	20.3	20.2	20.3
90°	0.4	0.6	1.2	1.9	2.5	3.1	3.5	4.1	4.4	5.1	5.4
92.5°	3.8	4.6	7.3	11.2	16.7	25.9	43.1	71.9	103.3	101.6	82.2
95°	10.4	10.7	13.2	16.7	23.6	37.8	71.5	140.9	227.8	279.2	273.2
97.5°	17.3	17.7	19.4	22.9	29.2	39.3	61.6	112.4	203.5	298.2	345.7
100°	22.0	22.6	24.0	27.4	33.4	42.9	61.2	102.1	181.6	284.5	363.4
102.5°	27.4	27.7	28.7	32.5	38.0	47.2	63.4	97.8	164.9	260.6	352.8
105°	35.6	35.6	37.2	40.3	45.4	54.2	68.0	96.1	148.7	228.5	319.0
107.5°	43.7	44.3	45.8	48.4	53.7	61.6	75.0	99.0	142.0	206.3	284.4
110°	49.5	50.1	51.4	54.2	58.9	67.1	80.1	101.8	139.9	196.0	264.7



TEST NUMBER: P333213-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	55.3	55.9	56.9	59.7	64.5	72.4	84.8	105.3	139.9	189.9	250.1
115°	63.7	64.3	65.3	68.0	72.8	80.7	92.4	110.6	140.9	183.4	234.2
117.5°	71.2	72.1	73.2	76.0	81.4	89.0	100.0	116.6	142.9	180.2	224.6
120°	76.2	77.2	78.5	81.3	86.7	94.5	105.6	120.7	145.0	178.7	219.4
122.5°	81.6	82.2	83.3	86.1	91.9	99.9	110.8	125.2	146.7	177.5	214.8
125°	88.3	88.9	90.4	93.3	99.2	107.5	117.9	131.4	149.7	175.8	208.7
127.5°	93.5	94.4	96.4	100.0	106.4	114.6	124.6	137.1	153.0	175.1	203.0
130°	96.8	97.7	100.2	104.3	110.9	119.1	128.9	140.9	155.1	174.6	199.2
132.5°	99.2	100.5	103.5	108.1	114.9	123.1	133.0	144.2	157.3	174.6	196.2
135°	103.3	104.6	108.4	113.4	120.1	128.6	138.3	148.7	160.4	174.6	192.5
137.5°	108.5	109.5	113.0	118.1	124.6	133.3	142.2	152.1	163.3	175.0	189.3
140°	111.6	112.5	116.3	121.4	127.3	135.8	145.0	154.4	164.5	175.2	187.8
142.5°	115.1	115.7	119.3	124.4	130.1	138.1	146.7	155.7	165.2	175.5	186.5
145°	120.4	121.0	124.1	128.6	134.3	141.5	149.7	157.6	166.0	175.2	184.7
147.5°	125.9	126.3	129.0	133.1	138.0	144.4	151.6	158.7	166.4	174.4	182.7
150°	129.2	129.8	132.1	136.2	140.5	145.9	152.8	159.4	166.4	173.6	181.2
152.5°	132.8	133.1	135.1	138.7	142.9	147.7	154.1	160.0	166.1	172.6	179.4
155°	137.4	137.4	139.3	142.4	145.6	150.0	155.3	160.4	165.4	170.9	176.5
157.5°	141.6	141.5	143.0	145.7	148.5	151.9	156.4	160.7	164.6	168.9	173.7
160°	144.4	144.0	145.3	147.5	150.0	152.8	156.9	160.7	163.9	167.6	171.5
162.5°	146.6	146.3	147.6	149.5	151.5	153.8	157.5	160.5	163.1	166.1	169.4
165°	150.0	149.4	150.3	151.9	153.2	155.1	157.6	160.1	162.0	163.9	166.4
167.5°	152.3	151.9	152.6	153.4	154.3	155.5	157.6	159.3	160.2	161.7	163.5
170°	153.8	153.5	153.8	154.4	155.1	156.0	157.6	158.8	159.4	160.4	161.7
172.5°	154.8	154.3	154.5	155.2	155.5	156.0	157.3	158.4	158.5	158.9	159.9
175°	156.0	155.3	155.7	156.0	156.0	156.0	156.9	157.6	157.3	157.3	157.6
177.5°	156.6	156.0	156.0	156.3	156.0	156.0	156.6	156.9	156.3	156.3	156.6
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333213-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1167.2	1168.9	1170.5	1171.3	1171.1	1170.9	1170.7	1170.5
5°	1161.4	1163.1	1165.0	1165.8	1165.6	1165.5	1165.2	1165.0
7.5°	1149.6	1151.4	1153.2	1154.0	1153.8	1153.6	1153.3	1153.2
10°	1139.6	1141.3	1142.9	1143.6	1143.4	1143.2	1143.0	1142.8
12.5°	1126.3	1127.7	1129.0	1129.6	1129.6	1129.5	1129.5	1129.4
15°	1103.2	1104.2	1105.3	1105.7	1105.7	1105.7	1105.7	1105.7
17.5°	1076.3	1077.5	1078.8	1079.0	1077.9	1076.9	1075.8	1074.9
20°	1055.9	1057.3	1058.7	1058.9	1057.9	1056.9	1055.9	1054.8
22.5°	1032.6	1033.6	1034.6	1034.7	1033.9	1033.2	1032.5	1031.9
25°	995.4	995.9	996.3	996.1	995.6	995.0	994.3	993.7
27.5°	956.4	956.5	956.6	956.4	955.7	955.1	954.5	953.9
30°	928.1	927.6	927.2	926.8	926.1	925.5	924.9	924.3
32.5°	899.2	898.5	897.8	896.8	895.7	894.6	893.5	892.4
35°	854.6	853.5	852.6	851.2	849.5	847.9	846.2	844.6
37.5°	807.6	806.1	804.6	803.3	802.5	801.5	800.6	799.6
40°	775.2	773.3	771.4	770.2	769.5	769.0	768.4	767.8
42.5°	742.9	741.2	739.5	738.2	737.3	736.3	735.3	734.4
45°	695.2	692.7	690.3	688.7	688.1	687.5	686.9	686.3
47.5°	644.9	642.4	639.9	637.9	636.5	635.1	633.6	632.1
50°	610.5	607.8	605.1	603.1	601.6	600.2	598.8	597.4
52.5°	577.1	574.7	572.4	570.4	568.8	567.2	565.6	564.0
55°	525.1	523.3	521.4	519.8	518.3	516.8	515.4	514.0
57.5°	473.5	471.1	468.7	467.1	466.3	465.6	464.8	464.0
60°	438.5	436.5	434.4	432.7	431.2	429.8	428.4	427.0
62.5°	404.9	402.7	400.5	398.8	397.7	396.5	395.5	394.3
65°	352.0	350.1	348.2	346.9	346.1	345.3	344.4	343.6
67.5°	301.4	299.8	298.3	297.2	296.8	296.2	295.7	295.2
70°	268.0	266.7	265.5	264.5	263.6	262.8	262.0	261.2
72.5°	236.5	235.1	233.7	232.6	231.8	231.0	230.2	229.3
75°	187.7	187.1	186.5	185.7	184.9	184.0	183.2	182.4
77.5°	143.0	142.6	142.2	141.8	141.2	140.6	140.1	139.5
80°	114.4	114.2	114.0	113.7	113.3	112.9	112.4	112.1
82.5°	87.4	87.0	86.7	86.5	86.4	86.3	86.2	86.1
85°	51.5	51.3	51.0	50.7	50.3	49.9	49.5	49.0
87.5°	20.4	20.4	20.5	20.5	20.2	19.8	19.5	19.3
90°	5.7	6.0	6.3	7.0	7.0	7.0	7.2	7.2
92.5°	55.8	40.5	30.5	25.9	21.8	21.0	20.6	20.1
95°	226.6	178.7	139.9	113.4	91.0	81.6	79.1	74.1
97.5°	337.4	303.9	266.1	229.3	209.8	192.2	183.1	179.0
100°	387.6	372.2	339.7	306.9	285.2	262.5	250.8	245.8
102.5°	404.5	414.0	398.5	376.3	353.0	336.9	324.2	320.5
105°	394.6	437.7	451.6	448.2	438.0	427.7	421.3	417.6
107.5°	359.0	416.6	452.2	468.7	473.8	473.8	471.6	469.1
110°	332.8	392.7	437.1	463.9	478.0	484.0	486.2	486.2





TEST NUMBER: P333213-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	312.1	369.0	413.9	445.5	466.2	476.5	482.0	484.3
115°	286.1	335.0	378.2	412.5	437.1	452.2	461.0	465.1
117.5°	269.4	311.5	348.7	380.2	404.7	420.4	429.2	431.7
120°	260.3	298.1	332.8	360.5	383.9	399.0	407.5	410.0
122.5°	253.5	288.6	319.4	345.4	366.2	380.0	388.6	390.8
125°	243.6	275.7	303.2	325.8	343.5	356.4	363.4	366.5
127.5°	233.5	263.5	289.1	310.3	326.4	337.8	344.3	345.7
130°	227.2	254.9	279.6	300.1	315.8	326.2	332.5	334.4
132.5°	220.9	246.9	269.2	288.9	304.7	315.0	320.8	323.0
135°	212.8	234.4	254.7	272.6	286.5	296.9	302.6	304.4
137.5°	205.8	223.4	240.1	255.4	267.8	277.2	282.5	284.5
140°	202.0	216.8	231.3	244.5	256.2	264.4	269.1	270.7
142.5°	198.8	211.2	223.7	235.2	245.1	252.1	256.5	257.9
145°	194.5	204.2	214.0	222.5	230.1	235.4	238.9	240.1
147.5°	190.4	198.3	205.9	212.3	218.3	222.6	224.5	225.2
150°	188.2	195.1	201.1	206.7	211.4	215.3	216.5	216.8
152.5°	185.7	191.8	197.2	201.7	205.6	208.7	209.9	210.3
155°	181.8	186.9	191.3	194.7	197.9	200.1	201.1	201.3
157.5°	178.1	182.2	185.7	188.3	190.8	192.6	193.5	193.4
160°	175.6	178.7	181.8	184.0	186.3	187.8	188.4	188.2
162.5°	172.7	175.7	178.3	180.3	182.0	183.2	183.4	183.3
165°	168.9	171.1	173.0	174.6	175.8	176.5	176.5	176.5
167.5°	165.2	166.7	168.2	169.3	170.0	170.5	170.2	170.1
170°	163.3	164.2	165.1	165.8	166.4	166.7	166.7	166.4
172.5°	161.0	161.9	162.6	163.0	163.1	163.7	163.2	162.8
175°	158.5	158.5	159.2	159.2	159.2	159.4	158.8	158.5
177.5°	156.9	157.0	157.0	157.0	156.9	157.0	156.3	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3

(END OF REPORT)