

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333220-940

Luminaire Tested: **S125DIP-S850D590U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333220-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D590U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5155.1 lumens
Efficiency: N/A
Efficacy: 127.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333220-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333220-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59																			
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50																			
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42																			
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39	35																			
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	40	36	33	30																			
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	36	32	29	26																			
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26	23																			
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20																			
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	20	18																			
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16																			
10	48	36	28	24	45	34	27	23	30	24	21	27	22	19	23	20	17	15																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7559	7559	7559
5°	7577	7505	7553
10°	7531	7452	7494
15°	7449	7362	7393
20°	7332	7236	7249
25°	7207	7088	7081
30°	7052	6927	6893
35°	6885	6754	6659
40°	6715	6566	6473
45°	6530	6395	6268
50°	6327	6187	6002
55°	6132	5954	5788
60°	5898	5717	5515
65°	5619	5434	5251
70°	5351	5108	4932
75°	4876	4716	4551
80°	4340	4273	4169
85°	3772	3846	3631



TEST NUMBER: P333220-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.4	2.1
10°-20°	311.8	6.0
20°-30°	460.3	8.9
30°-40°	537.2	10.4
40°-50°	539.5	10.5
50°-60°	473.6	9.2
60°-70°	352.9	6.8
70°-80°	201.8	3.9
80°-90°	60.1	1.2
90°-100°	24.9	0.5
100°-110°	153.7	3.0
110°-120°	278.8	5.4
120°-130°	357.8	6.9
130°-140°	384.8	7.5
140°-150°	361.2	7.0
150°-160°	292.2	5.7
160°-170°	189.0	3.7
170°-180°	65.2	1.3
0°-30°	882.5	17.1
0°-40°	1419.6	27.5
0°-60°	2432.7	47.2
0°-90°	3047.5	59.1
90°-120°	457.4	8.9
90°-150°	1561.2	30.3
90°-180°	2108.0	40.9
0°-180°	5155.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1170	1170	1170	1170	1170	
5°	1169	1166	1158	1165	1165	111
15°	1114	1111	1101	1106	1106	314
25°	1011	1006	995	996	994	465
35°	873	869	857	852	845	546
45°	715	711	700	690	686	551
55°	545	541	529	521	514	486
65°	368	365	356	348	344	365
75°	195	193	189	186	182	208
85°	51	52	52	51	49	57
90°	0	5	8	11	12	4
95°	29	26	8	11	11	37
105°	150	152	152	152	151	159
115°	281	283	284	282	279	278
125°	399	403	403	401	399	357
135°	498	501	500	499	496	384
145°	578	578	578	579	576	361
155°	636	633	634	635	631	293
165°	671	668	668	671	667	189
175°	686	683	684	687	683	65
180°	686	686	686	686	686	



TEST NUMBER: P333220-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1173.6	1173.0	1172.6	1172.1	1171.5	1170.5	1168.9	1167.2	1165.6	1164.0	1165.6
5°	1168.8	1168.3	1167.9	1167.5	1167.1	1165.8	1163.8	1161.7	1159.7	1157.6	1159.5
7.5°	1158.0	1157.6	1157.2	1156.7	1156.4	1155.0	1152.7	1150.5	1148.3	1145.9	1147.7
10°	1148.3	1148.0	1147.5	1147.1	1146.7	1145.4	1143.1	1140.9	1138.6	1136.3	1138.0
12.5°	1136.5	1135.8	1135.1	1134.3	1133.5	1132.1	1130.1	1127.9	1125.8	1123.7	1125.1
15°	1114.1	1113.5	1112.9	1112.2	1111.6	1110.2	1108.0	1105.6	1103.4	1101.1	1102.2
17.5°	1088.3	1087.4	1086.5	1085.7	1084.8	1083.1	1080.8	1078.4	1076.0	1073.7	1075.0
20°	1066.8	1066.5	1066.0	1065.6	1065.2	1063.6	1061.0	1058.3	1055.6	1052.9	1054.4
22.5°	1045.4	1044.6	1043.9	1043.1	1042.4	1040.8	1038.3	1035.7	1033.2	1030.7	1031.7
25°	1011.3	1010.3	1009.2	1008.2	1007.2	1005.3	1002.6	1000.0	997.3	994.6	995.1
27.5°	971.4	970.9	970.3	969.6	969.0	967.3	964.6	961.8	959.0	956.3	956.4
30°	945.6	944.9	944.3	943.7	943.1	941.2	938.2	935.0	931.9	928.9	928.4
32.5°	917.4	916.4	915.5	914.5	913.6	911.8	909.0	906.2	903.5	900.7	900.0
35°	873.3	872.4	871.6	870.8	870.0	868.2	865.3	862.4	859.5	856.7	855.6
37.5°	827.6	826.5	825.5	824.5	823.4	821.5	818.9	816.1	813.4	810.7	809.1
40°	796.5	795.4	794.4	793.4	792.3	790.4	787.5	784.6	781.8	778.8	777.0
42.5°	763.1	762.2	761.3	760.5	759.6	757.8	754.9	752.0	749.1	746.3	744.6
45°	715.0	714.1	713.3	712.5	711.7	710.0	707.6	705.1	702.6	700.2	697.7
47.5°	663.1	663.2	663.2	663.2	663.3	661.8	658.8	655.9	652.9	650.0	647.4
50°	629.7	629.1	628.5	627.9	627.3	625.7	623.3	620.8	618.3	615.8	613.1
52.5°	595.7	595.2	594.8	594.3	593.9	592.3	589.7	587.0	584.4	581.8	579.4
55°	544.6	543.9	543.3	542.7	542.1	540.3	537.4	534.6	531.6	528.8	526.9
57.5°	490.6	490.4	490.0	489.6	489.4	487.9	485.5	483.1	480.6	478.2	475.8
60°	456.6	455.8	455.0	454.1	453.3	451.7	449.4	447.2	445.0	442.6	440.6
62.5°	421.0	420.4	419.7	419.0	418.4	417.1	415.2	413.2	411.3	409.3	407.2
65°	367.7	367.2	366.8	366.4	366.0	364.7	362.4	360.2	357.8	355.6	353.7
67.5°	316.0	315.1	314.2	313.3	312.5	311.2	309.6	307.9	306.2	304.5	302.9
70°	283.4	282.3	281.3	280.3	279.3	277.9	276.0	274.1	272.2	270.5	269.2
72.5°	247.8	247.1	246.4	245.8	245.0	244.1	242.9	241.7	240.5	239.3	237.9
75°	195.4	195.0	194.6	194.2	193.8	193.1	192.0	191.0	189.9	189.0	188.3
77.5°	147.0	146.9	146.8	146.6	146.4	146.1	145.4	144.9	144.3	143.7	143.4
80°	116.7	116.7	116.7	116.7	116.7	116.5	116.1	115.7	115.2	114.9	114.7
82.5°	90.0	89.7	89.3	89.0	88.7	88.5	88.4	88.4	88.3	88.2	87.8
85°	50.9	51.2	51.4	51.5	51.7	51.9	51.9	51.9	51.9	51.9	51.6
87.5°	20.1	20.2	20.5	20.7	20.9	21.0	20.9	20.9	20.9	20.9	21.0
90°	0.5	1.4	2.3	3.2	4.1	5.0	5.8	6.6	7.3	8.1	8.7
92.5°	7.8	7.2	6.6	6.0	5.3	5.4	6.1	6.8	7.4	8.1	8.7
95°	29.0	28.6	28.4	28.0	27.6	25.3	21.0	16.8	12.4	8.1	8.7
97.5°	60.5	61.2	61.8	62.3	63.0	59.0	50.6	42.0	33.5	25.1	21.8
100°	85.0	85.3	85.6	86.0	86.3	86.7	87.2	87.7	88.1	88.5	71.7
102.5°	109.8	110.2	110.7	111.1	111.5	111.8	112.1	112.4	112.7	113.0	109.8
105°	149.5	150.0	150.5	151.0	151.4	151.6	151.6	151.6	151.6	151.6	151.6
107.5°	190.9	190.9	190.9	190.9	190.9	191.0	191.2	191.5	191.7	191.9	191.9
110°	217.8	217.8	217.8	217.8	217.8	217.8	218.1	218.3	218.6	218.7	218.5



TEST NUMBER: P333220-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	243.0	243.3	243.5	243.8	244.1	244.2	244.4	244.5	244.7	244.8	244.4
115°	280.8	281.4	282.0	282.5	283.1	283.5	283.6	283.7	283.7	283.9	283.5
117.5°	320.0	319.9	319.9	319.9	319.9	320.1	320.6	321.0	321.4	321.8	321.3
120°	344.5	344.3	344.2	344.1	343.9	344.1	344.5	344.7	345.1	345.4	345.2
122.5°	366.0	366.4	366.8	367.3	367.7	368.0	368.2	368.4	368.5	368.6	368.5
125°	399.4	400.2	400.9	401.7	402.5	403.0	403.0	403.0	403.0	403.0	402.5
127.5°	431.2	431.8	432.4	432.9	433.5	433.7	433.6	433.6	433.5	433.5	433.2
130°	450.8	451.3	451.9	452.5	453.0	453.3	453.4	453.6	453.7	453.8	453.4
132.5°	470.3	470.9	471.6	472.3	472.9	473.1	472.9	472.6	472.3	472.2	472.1
135°	498.1	498.7	499.4	500.1	500.8	501.1	500.8	500.5	500.3	500.1	499.9
137.5°	523.6	524.2	524.8	525.4	525.9	526.2	525.9	525.8	525.6	525.3	525.4
140°	540.3	540.6	540.7	541.0	541.2	541.3	541.2	541.0	540.9	540.8	541.0
142.5°	555.4	555.5	555.6	555.8	555.9	556.1	556.2	556.3	556.5	556.7	556.7
145°	577.5	577.7	577.9	578.1	578.4	578.5	578.5	578.5	578.5	578.5	578.5
147.5°	596.7	596.7	596.6	596.6	596.6	596.6	596.7	596.9	597.0	597.2	597.4
150°	608.9	608.8	608.5	608.3	608.1	608.1	608.3	608.5	608.8	608.9	609.2
152.5°	620.8	620.3	619.8	619.3	618.8	618.7	618.8	619.1	619.3	619.6	619.8
155°	636.0	635.3	634.6	633.9	633.2	633.0	633.2	633.5	633.6	633.9	634.3
157.5°	647.6	647.2	646.8	646.4	646.0	645.9	645.9	645.9	645.9	646.0	646.3
160°	655.8	655.1	654.4	653.7	653.1	652.8	652.9	653.0	653.1	653.3	653.7
162.5°	662.3	661.6	660.9	660.2	659.6	659.3	659.4	659.5	659.6	659.8	660.4
165°	671.0	670.4	669.7	669.1	668.3	668.1	668.2	668.2	668.4	668.5	669.1
167.5°	677.5	676.9	676.2	675.5	674.8	674.5	674.6	674.7	674.8	674.9	675.7
170°	681.3	680.5	679.7	678.9	678.1	677.7	677.8	678.0	678.1	678.1	679.0
172.5°	683.7	682.9	682.1	681.3	680.5	680.2	680.4	680.6	680.8	681.0	681.8
175°	686.3	685.6	684.9	684.3	683.6	683.3	683.4	683.6	683.7	683.8	684.7
177.5°	687.5	687.0	686.4	685.9	685.4	685.1	685.2	685.3	685.4	685.5	686.2
180°	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3



TEST NUMBER: P333220-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1167.2	1168.9	1170.5	1171.3	1171.1	1170.9	1170.7	1170.5
5°	1161.4	1163.1	1165.0	1165.8	1165.6	1165.5	1165.2	1165.0
7.5°	1149.6	1151.4	1153.2	1154.0	1153.8	1153.6	1153.3	1153.2
10°	1139.6	1141.3	1142.9	1143.6	1143.4	1143.2	1143.0	1142.8
12.5°	1126.3	1127.7	1129.0	1129.6	1129.6	1129.5	1129.5	1129.4
15°	1103.2	1104.2	1105.3	1105.7	1105.7	1105.7	1105.7	1105.7
17.5°	1076.3	1077.5	1078.8	1079.0	1077.9	1076.9	1075.8	1074.9
20°	1055.9	1057.3	1058.7	1058.9	1057.9	1056.9	1055.9	1054.8
22.5°	1032.6	1033.6	1034.6	1034.7	1033.9	1033.2	1032.5	1031.9
25°	995.4	995.9	996.3	996.1	995.6	995.0	994.3	993.7
27.5°	956.4	956.5	956.6	956.4	955.7	955.1	954.5	953.9
30°	928.1	927.6	927.2	926.8	926.1	925.5	924.9	924.3
32.5°	899.2	898.5	897.8	896.8	895.7	894.6	893.5	892.4
35°	854.6	853.5	852.6	851.2	849.5	847.9	846.2	844.6
37.5°	807.6	806.1	804.6	803.3	802.5	801.5	800.6	799.6
40°	775.2	773.3	771.4	770.2	769.5	769.0	768.4	767.8
42.5°	742.9	741.2	739.5	738.2	737.3	736.3	735.3	734.4
45°	695.2	692.7	690.3	688.7	688.1	687.5	686.9	686.3
47.5°	644.9	642.4	639.9	637.9	636.5	635.1	633.6	632.1
50°	610.5	607.8	605.1	603.1	601.6	600.2	598.8	597.4
52.5°	577.1	574.7	572.4	570.4	568.8	567.2	565.6	564.0
55°	525.1	523.3	521.4	519.8	518.3	516.8	515.4	514.0
57.5°	473.5	471.1	468.7	467.1	466.3	465.6	464.8	464.0
60°	438.5	436.5	434.4	432.7	431.2	429.8	428.4	427.0
62.5°	404.9	402.7	400.5	398.8	397.7	396.5	395.5	394.3
65°	352.0	350.1	348.2	346.9	346.1	345.3	344.4	343.6
67.5°	301.4	299.8	298.3	297.2	296.8	296.2	295.7	295.2
70°	268.0	266.7	265.5	264.5	263.6	262.8	262.0	261.2
72.5°	236.5	235.1	233.7	232.6	231.8	231.0	230.2	229.3
75°	187.7	187.1	186.5	185.7	184.9	184.0	183.2	182.4
77.5°	143.0	142.6	142.2	141.8	141.2	140.6	140.1	139.5
80°	114.4	114.2	114.0	113.7	113.3	112.9	112.4	112.1
82.5°	87.4	87.0	86.7	86.5	86.4	86.3	86.2	86.1
85°	51.5	51.3	51.0	50.7	50.3	49.9	49.5	49.0
87.5°	21.1	21.2	21.3	21.3	21.0	20.8	20.5	20.2
90°	9.3	9.8	10.4	10.9	11.2	11.5	11.9	12.2
92.5°	9.3	9.8	10.4	10.8	10.9	11.1	11.2	11.4
95°	9.3	9.8	10.4	10.7	10.7	10.7	10.7	10.7
97.5°	18.6	15.4	12.3	10.7	10.7	10.7	10.7	10.7
100°	54.8	38.0	21.1	12.5	12.0	11.6	11.1	10.7
102.5°	106.6	103.3	100.2	94.8	87.0	79.4	71.7	64.0
105°	151.6	151.6	151.6	151.6	151.4	151.3	151.2	151.1
107.5°	192.0	192.0	192.0	191.8	191.5	191.2	190.8	190.5
110°	218.1	217.8	217.4	217.3	217.4	217.5	217.7	217.8



TEST NUMBER: P333220-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	244.0	243.5	243.1	242.8	242.6	242.5	242.4	242.2
115°	282.9	282.5	282.0	281.5	280.8	280.2	279.5	278.8
117.5°	320.7	320.0	319.5	319.1	318.8	318.4	318.2	317.9
120°	345.0	344.7	344.6	344.1	343.6	343.0	342.4	341.9
122.5°	368.2	368.0	367.7	367.3	366.7	366.0	365.3	364.7
125°	402.1	401.5	401.1	400.7	400.4	400.0	399.8	399.4
127.5°	432.9	432.7	432.5	431.9	431.1	430.3	429.4	428.6
130°	453.2	452.8	452.5	452.0	451.5	450.8	450.3	449.8
132.5°	472.0	471.9	471.9	471.5	471.0	470.4	469.8	469.3
135°	499.6	499.4	499.2	498.7	498.1	497.4	496.7	496.1
137.5°	525.4	525.5	525.5	525.2	524.7	524.1	523.5	522.9
140°	541.3	541.4	541.7	541.4	540.8	540.1	539.5	538.8
142.5°	556.8	556.8	556.9	556.5	555.9	555.2	554.5	553.8
145°	578.7	578.8	578.9	578.6	577.9	577.3	576.6	575.9
147.5°	597.4	597.6	597.7	597.4	596.6	595.8	594.9	594.1
150°	609.4	609.7	609.8	609.6	608.7	607.7	606.8	605.9
152.5°	620.0	620.3	620.5	620.2	619.4	618.6	617.7	616.9
155°	634.6	634.9	635.3	635.0	634.1	633.2	632.3	631.3
157.5°	646.7	647.0	647.4	647.1	646.2	645.2	644.4	643.5
160°	654.2	654.6	655.1	654.8	653.9	653.0	652.1	651.2
162.5°	661.0	661.6	662.3	662.1	661.1	660.1	659.2	658.1
165°	669.9	670.6	671.2	671.1	670.2	669.3	668.4	667.4
167.5°	676.5	677.3	678.1	678.1	677.1	676.0	675.0	674.0
170°	680.0	680.9	681.8	681.7	680.7	679.7	678.7	677.7
172.5°	682.6	683.5	684.3	684.2	683.1	682.2	681.1	680.1
175°	685.5	686.4	687.4	687.3	686.3	685.3	684.3	683.2
177.5°	686.8	687.4	688.0	688.0	687.2	686.5	685.8	685.1
180°	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3

(END OF REPORT)