

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333229-940

Luminaire Tested: **S125DIP-S850D810U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333229-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D810U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5936.9 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333229-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333229-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	51	51	51														
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43	43	43	43	43	43	43														
2	89	82	76	70	82	76	70	66	64	60	57	54	51	49	44	42	41	36	36	36	36	36	36	36														
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	35	30	30	30	30	30	30	30														
4	74	64	56	50	68	59	52	47	50	45	41	43	38	35	35	32	30	26	26	26	26	26	26	26														
5	68	57	48	42	63	53	45	40	45	40	35	38	34	30	32	28	26	23	23	23	23	23	23	23														
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20	20	20	20	20	20	20														
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20	18	18	18	18	18	18	18														
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16	16	16	16	16	16	16														
9	50	38	30	25	46	36	29	24	31	25	21	26	22	19	22	19	16	14	14	14	14	14	14	14														
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13	13	13	13	13	13	13														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7559	7559	7559
5°	7577	7505	7553
10°	7531	7452	7494
15°	7449	7362	7393
20°	7332	7236	7249
25°	7207	7088	7081
30°	7052	6927	6893
35°	6885	6754	6659
40°	6715	6566	6473
45°	6530	6395	6268
50°	6327	6187	6002
55°	6132	5954	5788
60°	5898	5717	5515
65°	5619	5434	5251
70°	5351	5108	4932
75°	4876	4716	4551
80°	4340	4273	4169
85°	3772	3846	3631



TEST NUMBER: P333229-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.4	1.9
10°-20°	311.8	5.3
20°-30°	460.3	7.8
30°-40°	537.2	9.0
40°-50°	539.5	9.1
50°-60°	473.6	8.0
60°-70°	352.9	5.9
70°-80°	201.8	3.4
80°-90°	60.7	1.0
90°-100°	34.2	0.6
100°-110°	210.7	3.5
110°-120°	382.1	6.4
120°-130°	490.4	8.3
130°-140°	527.5	8.9
140°-150°	495.1	8.3
150°-160°	400.5	6.7
160°-170°	259.0	4.4
170°-180°	89.3	1.5
0°-30°	882.5	14.9
0°-40°	1419.6	23.9
0°-60°	2432.7	41.0
0°-90°	3048.0	51.3
90°-120°	627.0	10.6
90°-150°	2140.0	36.0
90°-180°	2889.0	48.7
0°-180°	5936.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1170	1170	1170	1170	1170	
5°	1169	1166	1158	1165	1165	111
15°	1114	1111	1101	1106	1106	314
25°	1011	1006	995	996	994	465
35°	873	869	857	852	845	546
45°	715	711	700	690	686	551
55°	545	541	529	521	514	486
65°	368	365	356	348	344	365
75°	195	193	189	186	182	208
85°	51	52	52	51	49	57
90°	1	6	11	15	17	4
95°	40	36	11	14	15	51
105°	205	208	208	208	207	217
115°	385	388	389	386	382	381
125°	547	552	552	550	547	489
135°	683	687	686	684	680	526
145°	792	793	793	793	789	495
155°	872	868	869	871	865	401
165°	920	916	916	920	915	260
175°	941	937	937	942	937	90
180°	941	941	941	941	941	



TEST NUMBER: P333229-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1173.6	1173.0	1172.6	1172.1	1171.5	1170.5	1168.9	1167.2	1165.6	1164.0	1165.6
5°	1168.8	1168.3	1167.9	1167.5	1167.1	1165.8	1163.8	1161.7	1159.7	1157.6	1159.5
7.5°	1158.0	1157.6	1157.2	1156.7	1156.4	1155.0	1152.7	1150.5	1148.3	1145.9	1147.7
10°	1148.3	1148.0	1147.5	1147.1	1146.7	1145.4	1143.1	1140.9	1138.6	1136.3	1138.0
12.5°	1136.5	1135.8	1135.1	1134.3	1133.5	1132.1	1130.1	1127.9	1125.8	1123.7	1125.1
15°	1114.1	1113.5	1112.9	1112.2	1111.6	1110.2	1108.0	1105.6	1103.4	1101.1	1102.2
17.5°	1088.3	1087.4	1086.5	1085.7	1084.8	1083.1	1080.8	1078.4	1076.0	1073.7	1075.0
20°	1066.8	1066.5	1066.0	1065.6	1065.2	1063.6	1061.0	1058.3	1055.6	1052.9	1054.4
22.5°	1045.4	1044.6	1043.9	1043.1	1042.4	1040.8	1038.3	1035.7	1033.2	1030.7	1031.7
25°	1011.3	1010.3	1009.2	1008.2	1007.2	1005.3	1002.6	1000.0	997.3	994.6	995.1
27.5°	971.4	970.9	970.3	969.6	969.0	967.3	964.6	961.8	959.0	956.3	956.4
30°	945.6	944.9	944.3	943.7	943.1	941.2	938.2	935.0	931.9	928.9	928.4
32.5°	917.4	916.4	915.5	914.5	913.6	911.8	909.0	906.2	903.5	900.7	900.0
35°	873.3	872.4	871.6	870.8	870.0	868.2	865.3	862.4	859.5	856.7	855.6
37.5°	827.6	826.5	825.5	824.5	823.4	821.5	818.9	816.1	813.4	810.7	809.1
40°	796.5	795.4	794.4	793.4	792.3	790.4	787.5	784.6	781.8	778.8	777.0
42.5°	763.1	762.2	761.3	760.5	759.6	757.8	754.9	752.0	749.1	746.3	744.6
45°	715.0	714.1	713.3	712.5	711.7	710.0	707.6	705.1	702.6	700.2	697.7
47.5°	663.1	663.2	663.2	663.2	663.3	661.8	658.8	655.9	652.9	650.0	647.4
50°	629.7	629.1	628.5	627.9	627.3	625.7	623.3	620.8	618.3	615.8	613.1
52.5°	595.7	595.2	594.8	594.3	593.9	592.3	589.7	587.0	584.4	581.8	579.4
55°	544.6	543.9	543.3	542.7	542.1	540.3	537.4	534.6	531.6	528.8	526.9
57.5°	490.6	490.4	490.0	489.6	489.4	487.9	485.5	483.1	480.6	478.2	475.8
60°	456.6	455.8	455.0	454.1	453.3	451.7	449.4	447.2	445.0	442.6	440.6
62.5°	421.0	420.4	419.7	419.0	418.4	417.1	415.2	413.2	411.3	409.3	407.2
65°	367.7	367.2	366.8	366.4	366.0	364.7	362.4	360.2	357.8	355.6	353.7
67.5°	316.0	315.1	314.2	313.3	312.5	311.2	309.6	307.9	306.2	304.5	302.9
70°	283.4	282.3	281.3	280.3	279.3	277.9	276.0	274.1	272.2	270.5	269.2
72.5°	247.8	247.1	246.4	245.8	245.0	244.1	242.9	241.7	240.5	239.3	237.9
75°	195.4	195.0	194.6	194.2	193.8	193.1	192.0	191.0	189.9	189.0	188.3
77.5°	147.0	146.9	146.8	146.6	146.4	146.1	145.4	144.9	144.3	143.7	143.4
80°	116.7	116.7	116.7	116.7	116.7	116.5	116.1	115.7	115.2	114.9	114.7
82.5°	90.0	89.7	89.3	89.0	88.7	88.5	88.4	88.4	88.3	88.2	87.8
85°	50.9	51.2	51.4	51.5	51.7	51.9	51.9	51.9	51.9	51.9	51.6
87.5°	20.2	20.4	20.6	20.9	21.1	21.3	21.3	21.4	21.4	21.5	21.7
90°	0.7	2.0	3.2	4.5	5.6	6.8	7.9	9.0	10.1	11.1	11.9
92.5°	10.7	9.9	9.0	8.1	7.3	7.3	8.3	9.3	10.2	11.1	11.9
95°	39.8	39.3	38.8	38.3	37.9	34.7	28.8	22.9	17.0	11.1	11.9
97.5°	83.0	83.8	84.6	85.5	86.3	81.0	69.3	57.6	45.9	34.3	30.0
100°	116.5	116.9	117.3	117.9	118.3	118.9	119.5	120.1	120.7	121.4	98.3
102.5°	150.5	151.1	151.7	152.2	152.8	153.3	153.7	154.1	154.4	154.8	150.4
105°	205.0	205.6	206.3	206.9	207.5	207.8	207.8	207.8	207.8	207.8	207.8
107.5°	261.6	261.6	261.6	261.6	261.6	261.8	262.1	262.4	262.7	263.1	263.1
110°	298.5	298.5	298.5	298.5	298.5	298.6	298.9	299.3	299.5	299.9	299.4



TEST NUMBER: P333229-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	333.1	333.4	333.8	334.2	334.6	334.8	335.0	335.2	335.4	335.6	335.0
115°	385.0	385.8	386.5	387.3	388.1	388.5	388.7	388.8	389.0	389.1	388.5
117.5°	438.6	438.6	438.5	438.5	438.5	438.8	439.3	440.0	440.6	441.1	440.3
120°	472.1	472.0	471.8	471.6	471.4	471.6	472.1	472.6	473.1	473.5	473.2
122.5°	501.7	502.3	502.8	503.5	504.0	504.4	504.6	504.9	505.1	505.3	505.0
125°	547.4	548.5	549.6	550.7	551.8	552.3	552.3	552.3	552.3	552.3	551.7
127.5°	591.1	591.8	592.6	593.4	594.1	594.5	594.4	594.3	594.2	594.1	593.8
130°	617.9	618.7	619.4	620.2	621.0	621.4	621.6	621.7	621.9	622.1	621.6
132.5°	644.6	645.5	646.4	647.3	648.3	648.5	648.2	647.8	647.5	647.1	647.0
135°	682.7	683.7	684.6	685.5	686.4	686.7	686.4	686.1	685.8	685.5	685.2
137.5°	717.7	718.5	719.3	720.1	720.9	721.2	720.9	720.7	720.4	720.1	720.1
140°	740.6	740.9	741.2	741.5	741.8	741.9	741.7	741.6	741.5	741.3	741.6
142.5°	761.3	761.4	761.6	761.8	762.0	762.1	762.4	762.6	762.9	763.0	763.1
145°	791.5	791.8	792.1	792.5	792.7	792.9	792.9	792.9	792.9	792.9	793.1
147.5°	818.0	818.0	817.9	817.8	817.8	817.8	818.0	818.1	818.4	818.6	818.8
150°	834.7	834.5	834.1	833.8	833.5	833.5	833.8	834.1	834.5	834.7	835.1
152.5°	851.0	850.2	849.5	848.9	848.2	848.0	848.3	848.6	848.9	849.3	849.5
155°	871.7	870.8	869.9	868.9	868.0	867.6	868.0	868.3	868.6	868.9	869.3
157.5°	887.7	887.2	886.6	886.1	885.5	885.2	885.3	885.3	885.3	885.4	885.8
160°	898.9	898.0	897.1	896.1	895.2	894.8	894.9	895.1	895.3	895.4	896.0
162.5°	907.9	906.9	906.0	905.0	904.1	903.7	903.8	904.0	904.2	904.4	905.2
165°	919.8	918.9	917.9	917.0	916.1	915.7	915.9	916.1	916.1	916.3	917.3
167.5°	928.7	927.8	926.8	925.9	924.9	924.5	924.6	924.8	925.0	925.1	926.2
170°	933.8	932.6	931.6	930.5	929.4	929.0	929.1	929.3	929.4	929.6	930.9
172.5°	937.1	936.0	935.0	933.9	932.7	932.4	932.6	932.9	933.2	933.4	934.6
175°	940.8	939.8	938.9	938.0	937.0	936.7	936.7	936.9	937.1	937.3	938.5
177.5°	942.4	941.6	940.9	940.2	939.4	939.1	939.2	939.3	939.5	939.6	940.5
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8



TEST NUMBER: P333229-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1167.2	1168.9	1170.5	1171.3	1171.1	1170.9	1170.7	1170.5
5°	1161.4	1163.1	1165.0	1165.8	1165.6	1165.5	1165.2	1165.0
7.5°	1149.6	1151.4	1153.2	1154.0	1153.8	1153.6	1153.3	1153.2
10°	1139.6	1141.3	1142.9	1143.6	1143.4	1143.2	1143.0	1142.8
12.5°	1126.3	1127.7	1129.0	1129.6	1129.6	1129.5	1129.5	1129.4
15°	1103.2	1104.2	1105.3	1105.7	1105.7	1105.7	1105.7	1105.7
17.5°	1076.3	1077.5	1078.8	1079.0	1077.9	1076.9	1075.8	1074.9
20°	1055.9	1057.3	1058.7	1058.9	1057.9	1056.9	1055.9	1054.8
22.5°	1032.6	1033.6	1034.6	1034.7	1033.9	1033.2	1032.5	1031.9
25°	995.4	995.9	996.3	996.1	995.6	995.0	994.3	993.7
27.5°	956.4	956.5	956.6	956.4	955.7	955.1	954.5	953.9
30°	928.1	927.6	927.2	926.8	926.1	925.5	924.9	924.3
32.5°	899.2	898.5	897.8	896.8	895.7	894.6	893.5	892.4
35°	854.6	853.5	852.6	851.2	849.5	847.9	846.2	844.6
37.5°	807.6	806.1	804.6	803.3	802.5	801.5	800.6	799.6
40°	775.2	773.3	771.4	770.2	769.5	769.0	768.4	767.8
42.5°	742.9	741.2	739.5	738.2	737.3	736.3	735.3	734.4
45°	695.2	692.7	690.3	688.7	688.1	687.5	686.9	686.3
47.5°	644.9	642.4	639.9	637.9	636.5	635.1	633.6	632.1
50°	610.5	607.8	605.1	603.1	601.6	600.2	598.8	597.4
52.5°	577.1	574.7	572.4	570.4	568.8	567.2	565.6	564.0
55°	525.1	523.3	521.4	519.8	518.3	516.8	515.4	514.0
57.5°	473.5	471.1	468.7	467.1	466.3	465.6	464.8	464.0
60°	438.5	436.5	434.4	432.7	431.2	429.8	428.4	427.0
62.5°	404.9	402.7	400.5	398.8	397.7	396.5	395.5	394.3
65°	352.0	350.1	348.2	346.9	346.1	345.3	344.4	343.6
67.5°	301.4	299.8	298.3	297.2	296.8	296.2	295.7	295.2
70°	268.0	266.7	265.5	264.5	263.6	262.8	262.0	261.2
72.5°	236.5	235.1	233.7	232.6	231.8	231.0	230.2	229.3
75°	187.7	187.1	186.5	185.7	184.9	184.0	183.2	182.4
77.5°	143.0	142.6	142.2	141.8	141.2	140.6	140.1	139.5
80°	114.4	114.2	114.0	113.7	113.3	112.9	112.4	112.1
82.5°	87.4	87.0	86.7	86.5	86.4	86.3	86.2	86.1
85°	51.5	51.3	51.0	50.7	50.3	49.9	49.5	49.0
87.5°	21.8	21.9	22.1	22.1	21.8	21.6	21.4	21.1
90°	12.8	13.5	14.3	14.9	15.3	15.8	16.2	16.8
92.5°	12.8	13.5	14.3	14.7	15.0	15.2	15.4	15.6
95°	12.8	13.5	14.3	14.6	14.6	14.6	14.6	14.6
97.5°	25.6	21.2	16.9	14.6	14.6	14.6	14.6	14.6
100°	75.2	52.1	29.0	17.1	16.5	15.9	15.2	14.6
102.5°	146.1	141.7	137.3	129.9	119.3	108.8	98.3	87.7
105°	207.8	207.8	207.8	207.8	207.6	207.4	207.2	207.1
107.5°	263.1	263.1	263.1	263.0	262.5	262.0	261.5	261.1
110°	298.9	298.5	298.0	297.8	298.0	298.2	298.3	298.5



TEST NUMBER: P333229-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	334.4	333.8	333.2	332.8	332.6	332.3	332.2	332.0
115°	387.9	387.3	386.6	385.8	385.0	384.0	383.1	382.2
117.5°	439.5	438.7	437.9	437.3	436.9	436.5	436.1	435.7
120°	472.9	472.6	472.3	471.7	470.9	470.2	469.4	468.6
122.5°	504.7	504.4	504.1	503.5	502.6	501.7	500.8	499.9
125°	551.1	550.5	549.8	549.3	548.8	548.3	547.9	547.4
127.5°	593.4	593.2	592.8	592.0	590.9	589.8	588.6	587.5
130°	621.1	620.6	620.2	619.6	618.8	618.0	617.2	616.4
132.5°	646.9	646.8	646.8	646.3	645.6	644.8	644.0	643.3
135°	684.9	684.6	684.3	683.7	682.7	681.8	680.8	679.9
137.5°	720.2	720.2	720.3	720.0	719.2	718.4	717.6	716.8
140°	741.9	742.3	742.5	742.3	741.3	740.4	739.4	738.5
142.5°	763.2	763.2	763.3	762.9	762.0	761.0	760.1	759.1
145°	793.2	793.4	793.5	793.1	792.2	791.3	790.3	789.4
147.5°	818.9	819.1	819.3	818.9	817.7	816.6	815.5	814.4
150°	835.4	835.7	836.0	835.5	834.3	833.0	831.8	830.5
152.5°	849.9	850.2	850.5	850.1	849.0	847.8	846.8	845.6
155°	869.9	870.3	870.8	870.4	869.2	867.9	866.7	865.4
157.5°	886.4	886.9	887.3	887.0	885.7	884.5	883.2	882.0
160°	896.6	897.2	897.9	897.6	896.3	895.1	893.9	892.6
162.5°	906.1	907.0	907.8	907.6	906.2	904.8	903.5	902.1
165°	918.2	919.1	920.1	919.9	918.6	917.4	916.1	914.9
167.5°	927.4	928.4	929.6	929.4	928.0	926.7	925.2	923.9
170°	932.0	933.3	934.5	934.4	933.1	931.7	930.2	928.9
172.5°	935.7	936.8	938.0	937.8	936.4	935.0	933.6	932.2
175°	939.7	940.9	942.2	942.1	940.8	939.3	938.0	936.6
177.5°	941.4	942.2	943.1	943.1	942.0	941.0	940.0	939.1
180°	940.8	940.8	940.8	940.8	940.8	940.8	940.8	940.8

(END OF REPORT)