

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333243

Luminaire Tested: **S125DIP-S850D1205U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333243
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D1205U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7777.3 lumens
Efficiency: N/A
Efficacy: 136.7 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	93	89	85	88	85	82	79	71	68	66	57	56	55	45	44	43	38				
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37	32				
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	36	33	32	27				
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	24				
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20				
6	62	50	42	37	57	47	40	34	39	34	30	33	28	25	26	23	21	18				
7	58	46	38	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16				
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17	14				
9	50	38	30	25	46	35	28	24	30	24	21	25	21	18	20	17	15	13				
10	46	34	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7901	7901	7901	7901
5°	9149	7927	6941	7927
10°	10645	7887	6082	7887
15°	11784	7829	5610	7829
20°	13190	7737	5232	7737
25°	15452	7633	5047	7633
30°	16690	7532	4887	7532
35°	13722	7340	4782	7340
40°	9754	7074	4666	7074
45°	7493	6716	4601	6716
50°	6396	6271	4591	6271
55°	5695	5835	4631	5835
60°	5137	5359	4748	5359
65°	4745	4879	4872	4879
70°	4315	4383	4942	4383
75°	3810	3860	4898	3860
80°	3206	3146	4482	3146
85°	2542	2267	3616	2267



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	1.5
10°-20°	350.7	4.5
20°-30°	569.4	7.3
30°-40°	694.5	8.9
40°-50°	631.8	8.1
50°-60°	503.3	6.5
60°-70°	350.5	4.5
70°-80°	186.9	2.4
80°-90°	50.4	0.6
90°-100°	417.8	5.4
100°-110°	898.0	11.5
110°-120°	842.8	10.8
120°-130°	683.0	8.8
130°-140°	548.1	7.0
140°-150°	413.6	5.3
150°-160°	291.2	3.7
160°-170°	171.6	2.2
170°-180°	55.8	0.7
0°-30°	1037.8	13.3
0°-40°	1732.4	22.3
0°-60°	2867.5	36.9
0°-90°	3455.3	44.4
90°-120°	2158.6	27.8
90°-150°	3803.4	48.9
90°-180°	4322.0	55.6
0°-180°	7777.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1223	1223	1223	1223	1223	
5°	1411	1223	1071	1223	1411	142
15°	1762	1171	839	1171	1762	504
25°	2168	1071	708	1071	2168	990
35°	1740	931	606	931	1740	1065
45°	820	735	504	735	820	657
55°	506	518	411	518	506	455
65°	310	319	319	319	310	308
75°	153	155	196	155	153	164
85°	34	31	49	31	34	40
90°	27	1	27	1	27	20
95°	273	38	273	38	273	387
105°	1540	131	1540	131	1540	1530
115°	1715	235	1715	235	1715	1676
125°	1351	325	1351	325	1351	1223
135°	1122	381	1122	381	1122	870
145°	885	444	885	444	885	563
155°	742	507	742	507	742	346
165°	651	553	651	553	651	186
175°	584	575	584	575	584	57
180°	576	576	576	576	576	



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1294.0	1292.3	1290.7	1287.3	1289.8	1282.8	1279.4	1273.6	1266.6	1264.1	1261.2
5°	1411.3	1413.9	1416.5	1405.6	1406.7	1399.4	1382.8	1369.3	1358.4	1344.4	1334.5
7.5°	1552.6	1546.4	1545.9	1538.9	1526.7	1517.0	1499.5	1477.3	1455.8	1431.3	1411.0
10°	1623.2	1623.7	1619.0	1610.7	1597.8	1588.4	1565.6	1543.7	1517.3	1486.1	1463.8
12.5°	1676.4	1678.5	1672.6	1661.4	1655.1	1634.1	1616.2	1590.3	1558.8	1533.9	1499.9
15°	1762.4	1756.6	1752.5	1738.5	1727.6	1705.8	1677.2	1650.2	1615.9	1584.2	1552.6
17.5°	1845.2	1849.8	1842.0	1829.2	1795.4	1769.9	1731.6	1694.6	1652.0	1609.5	1571.7
20°	1919.2	1923.3	1911.4	1889.1	1848.6	1823.1	1772.7	1725.0	1675.6	1621.1	1579.6
22.5°	2011.4	2008.1	1992.0	1958.0	1922.9	1875.9	1821.3	1763.2	1701.4	1639.8	1584.6
25°	2168.4	2146.6	2136.7	2094.7	2048.5	1979.4	1904.6	1819.5	1742.6	1661.1	1590.5
27.5°	2255.4	2248.6	2237.6	2208.3	2159.7	2085.9	1997.7	1893.9	1785.5	1682.6	1590.2
30°	2238.0	2239.0	2240.1	2230.7	2199.6	2144.0	2056.3	1944.6	1815.8	1700.0	1593.1
32.5°	2083.5	2102.4	2120.4	2141.8	2150.5	2139.9	2084.9	1984.1	1851.6	1720.0	1591.4
35°	1740.5	1746.3	1804.9	1863.1	1942.0	2003.3	2044.3	1999.7	1888.0	1736.9	1589.4
37.5°	1357.1	1385.2	1425.8	1491.5	1605.4	1707.4	1838.6	1898.9	1862.9	1742.4	1585.8
40°	1156.9	1182.9	1209.3	1276.3	1372.4	1496.0	1645.0	1772.2	1801.8	1725.0	1573.3
42.5°	1002.4	1022.9	1052.3	1102.7	1183.0	1292.4	1434.8	1601.1	1703.4	1674.3	1547.2
45°	820.4	833.4	856.3	896.2	954.4	1040.1	1165.7	1347.5	1505.8	1558.3	1485.1
47.5°	702.2	702.1	719.9	747.5	789.5	862.3	955.2	1097.6	1266.8	1391.9	1386.1
50°	636.6	634.0	648.0	671.9	705.1	753.4	842.2	955.9	1118.5	1260.2	1299.7
52.5°	580.1	580.4	589.0	606.7	634.5	675.8	742.1	844.6	983.5	1129.0	1203.3
55°	505.8	503.7	513.5	525.5	545.7	572.7	620.5	698.9	811.6	954.9	1051.5
57.5°	437.6	443.3	447.3	455.6	472.4	490.5	530.8	588.3	677.7	800.7	902.8
60°	397.7	403.5	406.6	414.9	428.4	444.0	475.1	521.9	597.1	703.1	804.3
62.5°	362.0	366.5	367.5	375.0	386.0	401.2	425.7	464.9	524.4	617.1	716.3
65°	310.5	310.5	312.6	320.4	325.6	339.1	357.8	386.3	434.1	506.3	590.9
67.5°	260.9	263.4	262.8	266.3	271.1	281.5	294.9	318.5	353.9	406.6	474.3
70°	228.5	230.5	230.0	232.6	237.8	244.6	255.5	277.8	303.2	348.4	406.6
72.5°	199.4	200.2	198.9	202.3	205.4	211.3	223.5	235.4	259.2	297.3	345.1
75°	152.7	153.7	154.7	156.8	159.9	163.0	169.3	181.2	196.8	225.4	256.0
77.5°	114.4	112.5	115.0	114.7	116.4	118.8	124.3	130.6	143.4	161.5	185.2
80°	86.2	86.7	86.7	87.2	89.8	91.4	96.1	100.7	110.6	124.1	140.7
82.5°	62.9	64.3	63.5	64.4	66.6	67.7	70.3	74.1	79.9	90.5	102.5
85°	34.3	31.7	32.7	33.8	33.8	34.3	36.3	37.9	41.0	45.2	49.8
87.5°	15.3	16.1	16.3	16.3	16.7	16.3	17.7	17.5	18.5	19.5	20.7
90°	26.7	26.7	25.6	25.6	25.6	23.2	22.1	20.9	19.8	18.6	16.3
92.5°	74.1	76.0	77.6	80.4	95.3	112.5	149.4	205.9	303.3	374.6	380.7
95°	273.1	291.7	300.9	335.8	418.3	515.9	658.8	835.4	1007.4	1029.5	840.1
97.5°	660.0	674.9	708.6	773.6	845.4	981.2	1120.4	1244.2	1274.7	1099.4	750.2
100°	906.3	924.9	967.9	1051.6	1131.7	1252.6	1372.3	1429.2	1339.7	1049.2	669.3
102.5°	1181.5	1195.4	1242.1	1301.6	1387.4	1469.2	1526.6	1491.5	1300.7	960.9	607.9
105°	1539.6	1553.5	1576.8	1615.1	1652.3	1665.1	1614.0	1454.8	1175.9	842.4	548.4
107.5°	1729.7	1739.0	1746.7	1746.9	1728.1	1667.4	1536.1	1323.7	1048.6	760.8	523.3
110°	1792.9	1792.9	1784.8	1762.7	1710.4	1611.6	1447.8	1227.0	976.0	722.7	515.9



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1785.5	1777.1	1756.9	1719.0	1642.5	1526.1	1360.4	1150.8	922.1	700.4	515.9
115°	1715.0	1699.9	1667.4	1611.6	1521.0	1394.3	1235.2	1055.1	863.3	676.3	519.4
117.5°	1591.6	1582.4	1550.1	1492.4	1401.8	1285.6	1148.5	993.2	828.2	664.4	527.1
120°	1511.7	1502.4	1471.0	1415.3	1329.3	1227.0	1099.2	959.8	808.7	658.8	534.5
122.5°	1441.1	1432.7	1401.3	1350.2	1273.5	1177.8	1063.9	934.7	792.0	654.2	541.0
125°	1351.4	1339.7	1314.2	1266.5	1201.5	1117.8	1016.7	898.2	769.2	648.4	551.9
127.5°	1274.7	1269.6	1245.4	1203.3	1144.3	1066.0	971.6	861.0	748.3	645.6	564.2
130°	1232.8	1225.9	1202.6	1164.3	1106.2	1030.7	940.0	837.8	734.4	643.7	571.7
132.5°	1191.0	1183.1	1161.7	1123.4	1065.3	992.5	910.3	814.5	723.2	643.7	580.0
135°	1122.5	1115.5	1094.6	1056.2	1005.1	938.9	864.5	784.3	710.0	643.7	591.4
137.5°	1049.2	1041.6	1022.3	987.4	941.7	885.4	823.6	758.8	698.1	645.1	601.9
140°	998.1	992.3	974.9	944.7	901.7	852.9	799.4	744.8	692.5	646.0	606.5
142.5°	950.7	945.8	929.3	903.8	867.3	825.0	779.0	732.7	687.9	647.0	609.3
145°	885.4	880.8	868.0	848.2	820.3	789.0	752.9	716.9	680.9	646.0	612.4
147.5°	830.1	828.0	820.6	804.8	782.7	759.0	731.3	702.1	673.7	643.0	613.5
150°	799.4	798.3	793.6	779.7	762.2	741.3	719.3	693.7	668.1	640.2	613.5
152.5°	775.3	774.1	769.4	758.3	743.7	727.4	707.2	684.4	661.6	636.5	612.6
155°	742.5	741.3	737.8	729.7	718.1	705.3	689.0	670.4	650.7	629.8	610.0
157.5°	713.2	713.4	710.2	703.4	694.4	684.4	671.8	656.5	640.5	622.8	607.0
160°	693.7	694.9	692.5	686.7	678.6	670.4	658.8	647.2	632.1	618.2	604.2
162.5°	676.0	676.3	675.8	670.9	664.6	657.4	647.7	637.0	624.7	612.6	601.4
165°	650.7	650.7	650.7	648.4	643.7	637.9	630.9	622.8	613.5	604.2	597.2
167.5°	627.5	627.7	628.6	626.5	624.2	620.0	614.7	609.3	602.6	596.1	590.7
170°	613.5	614.7	614.7	613.5	611.2	608.9	605.4	601.9	596.1	591.4	588.0
172.5°	600.5	601.7	603.5	601.4	601.0	599.6	597.0	593.5	589.6	585.9	584.2
175°	584.5	585.6	588.0	586.8	586.8	586.8	584.5	584.5	581.0	579.8	579.8
177.5°	576.3	576.3	579.1	578.2	579.1	579.1	579.1	578.2	577.3	576.3	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1258.7	1255.8	1252.4	1246.6	1239.6	1235.8	1230.0	1226.3	1218.8	1212.6	1205.9
5°	1322.5	1309.0	1296.6	1280.5	1262.8	1251.4	1237.9	1222.8	1207.3	1191.2	1173.5
7.5°	1388.7	1364.8	1338.8	1310.9	1283.6	1258.5	1234.5	1210.9	1188.9	1162.3	1139.8
10°	1433.1	1403.0	1370.8	1332.9	1296.1	1263.9	1231.2	1202.6	1173.5	1142.4	1114.8
12.5°	1477.6	1437.5	1392.0	1350.4	1306.0	1267.2	1228.7	1192.2	1155.7	1121.2	1089.1
15°	1509.0	1473.6	1431.6	1372.4	1322.5	1269.1	1218.2	1170.9	1126.8	1088.4	1047.9
17.5°	1529.6	1484.1	1439.0	1382.2	1316.8	1257.0	1199.4	1145.3	1095.5	1046.8	1007.8
20°	1533.4	1486.6	1439.4	1383.8	1316.8	1248.3	1190.7	1125.7	1072.3	1021.9	974.1
22.5°	1532.1	1479.2	1427.7	1370.5	1305.2	1242.1	1172.4	1106.2	1048.2	998.6	948.8
25°	1520.4	1463.8	1399.4	1341.8	1277.4	1210.4	1139.8	1071.2	1012.0	955.4	906.1
27.5°	1510.6	1437.2	1364.3	1297.1	1234.9	1173.5	1105.9	1035.7	970.1	912.7	866.2
30°	1498.6	1418.1	1336.0	1265.9	1202.1	1142.4	1078.5	1010.0	941.4	885.3	835.5
32.5°	1487.8	1394.0	1307.4	1231.1	1163.4	1105.4	1046.5	981.3	914.0	857.1	807.2
35°	1466.9	1358.4	1259.2	1173.0	1100.8	1041.1	991.8	931.0	869.2	814.2	766.4
37.5°	1440.4	1311.6	1205.2	1114.8	1035.7	972.8	926.9	880.2	820.9	767.9	724.7
40°	1419.6	1278.4	1165.7	1073.3	991.3	925.8	883.3	839.1	789.8	740.5	694.8
42.5°	1393.5	1248.5	1125.9	1026.4	945.1	881.4	836.7	799.2	755.7	709.7	667.3
45°	1345.4	1194.3	1061.4	954.4	872.3	809.5	763.3	735.3	702.6	658.9	623.1
47.5°	1274.7	1129.2	991.7	881.3	796.6	738.4	695.1	668.2	645.1	612.7	580.2
50°	1211.9	1080.6	941.4	831.8	747.2	688.5	648.6	624.1	604.4	579.5	552.0
52.5°	1141.7	1019.5	892.0	783.7	699.9	642.0	602.9	581.4	565.0	547.1	520.0
55°	1030.2	926.4	808.0	705.1	627.8	571.2	536.9	518.2	504.7	491.2	474.6
57.5°	907.3	826.1	721.2	627.3	556.0	504.5	472.5	454.3	443.9	436.9	427.1
60°	820.9	751.4	661.0	575.3	505.8	460.1	428.9	414.9	406.1	400.3	393.1
62.5°	740.8	683.7	599.9	521.7	460.9	417.7	389.9	376.3	367.8	365.0	359.0
65°	622.6	578.5	509.4	444.5	392.6	355.7	332.3	319.3	314.1	311.0	311.6
67.5°	506.2	479.3	423.8	368.5	327.0	296.1	277.4	267.4	264.8	260.7	260.6
70°	435.1	414.9	368.2	319.9	283.0	259.1	242.5	232.1	229.5	227.4	226.9
72.5°	372.4	354.7	314.1	275.4	242.3	221.3	207.6	201.4	197.1	195.9	195.8
75°	279.9	270.0	237.8	207.2	184.3	169.8	160.5	154.7	151.6	151.1	151.6
77.5°	199.0	190.4	169.9	148.2	133.8	122.8	114.9	112.9	109.4	109.5	108.9
80°	149.5	143.8	130.9	113.7	101.8	92.4	88.3	84.6	83.6	82.0	83.6
82.5°	108.4	102.3	93.5	82.6	72.7	67.1	62.9	61.8	61.2	60.4	60.8
85°	53.5	54.0	48.8	40.5	36.3	33.2	30.6	30.6	30.1	29.6	30.1
87.5°	21.3	20.0	18.1	16.4	13.9	12.1	11.3	11.4	10.4	10.5	11.4
90°	15.1	12.8	11.6	9.3	7.0	4.6	2.3	1.2	2.3	4.6	7.0
92.5°	265.2	158.7	95.3	61.4	41.4	27.0	17.2	14.2	17.2	27.0	41.4
95°	519.4	263.8	139.4	87.1	61.6	48.8	39.5	38.3	39.5	48.8	61.6
97.5°	414.6	227.3	145.0	107.4	84.4	71.6	65.1	63.7	65.1	71.6	84.4
100°	376.5	225.4	158.0	123.2	101.1	88.3	83.7	81.3	83.7	88.3	101.1
102.5°	360.7	233.8	173.8	139.9	119.7	106.0	102.3	100.9	102.3	106.0	119.7
105°	354.4	251.0	199.9	167.3	148.7	137.1	131.3	131.3	131.3	137.1	148.7
107.5°	365.1	276.5	227.0	197.8	178.5	168.9	163.4	161.0	163.4	168.9	178.5
110°	375.3	295.1	247.5	217.3	199.9	189.4	184.8	182.4	184.8	189.4	199.9



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	388.3	312.8	267.0	237.7	220.3	209.8	206.1	203.8	206.1	209.8	220.3
115°	407.8	340.5	297.5	268.4	251.0	240.5	237.0	234.7	237.0	240.5	251.0
117.5°	430.2	368.8	328.1	300.0	280.3	269.8	266.1	262.6	266.1	269.8	280.3
120°	445.0	389.3	348.6	319.5	299.8	289.3	284.7	281.2	284.7	289.3	299.8
122.5°	461.8	408.8	368.1	339.1	317.4	307.0	303.3	300.7	303.3	307.0	317.4
125°	484.5	434.6	396.2	366.0	343.9	333.5	327.7	325.3	327.7	333.5	343.9
127.5°	505.5	459.4	422.5	392.3	368.8	355.6	348.1	344.6	348.1	355.6	368.8
130°	519.4	475.2	439.2	409.0	384.6	369.5	360.2	356.7	360.2	369.5	384.6
132.5°	531.5	490.1	454.1	423.9	398.6	381.6	370.4	366.0	370.4	381.6	398.6
135°	548.4	510.1	474.1	442.7	418.3	399.7	385.8	381.1	385.8	399.7	418.3
137.5°	561.0	524.3	491.5	459.2	435.3	416.7	403.7	400.2	403.7	416.7	435.3
140°	569.4	534.5	500.8	469.4	447.4	428.8	414.8	411.3	414.8	428.8	447.4
142.5°	574.0	541.0	509.2	479.7	458.5	439.9	426.9	424.3	426.9	439.9	458.5
145°	581.0	551.9	521.7	495.0	474.1	457.8	446.2	443.9	446.2	457.8	474.1
147.5°	585.2	558.9	532.4	508.9	490.8	475.7	465.7	464.3	465.7	475.7	490.8
150°	588.0	563.5	538.0	518.2	502.0	486.9	478.7	476.4	478.7	486.9	502.0
152.5°	589.8	568.2	544.5	526.6	511.3	498.0	490.8	489.4	490.8	498.0	511.3
155°	591.4	572.8	553.1	536.8	525.2	513.6	506.6	506.6	506.6	513.6	525.2
157.5°	592.6	576.8	559.8	547.5	537.3	527.3	521.7	522.0	521.7	527.3	537.3
160°	592.6	578.7	563.5	553.1	543.8	535.7	531.0	532.2	531.0	535.7	543.8
162.5°	591.7	580.5	567.3	558.7	551.2	544.0	539.4	540.5	539.4	544.0	551.2
165°	590.3	581.0	571.7	564.7	560.1	554.3	550.8	553.1	550.8	554.3	560.1
167.5°	587.5	581.0	573.3	568.9	565.6	562.4	560.3	561.5	560.3	562.4	565.6
170°	585.6	581.0	575.2	571.7	569.4	567.0	565.9	567.0	565.9	567.0	569.4
172.5°	583.8	580.0	575.2	573.5	572.1	569.8	568.7	570.8	568.7	569.8	572.1
175°	581.0	578.7	575.2	575.2	575.2	574.0	572.8	575.2	572.8	574.0	575.2
177.5°	578.2	577.3	575.4	575.4	576.3	575.4	575.4	577.3	575.4	575.4	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1202.2	1197.6	1193.9	1185.6	1181.0	1174.8	1169.8	1175.2	1169.4	1171.9	1168.1
5°	1164.7	1150.2	1139.8	1124.7	1111.7	1099.8	1091.0	1089.4	1085.2	1083.2	1076.9
7.5°	1119.6	1101.4	1083.6	1063.9	1047.2	1030.3	1019.5	1010.6	1004.7	996.9	991.6
10°	1093.0	1068.6	1047.9	1024.0	1003.2	985.0	970.5	963.2	956.5	946.6	943.0
12.5°	1060.2	1035.0	1009.6	984.1	964.2	943.9	931.4	920.4	915.8	904.6	903.5
15°	1020.9	983.0	958.0	932.1	904.5	887.9	877.5	865.6	860.4	852.6	846.9
17.5°	973.9	940.1	908.9	882.0	858.4	844.4	831.5	823.3	814.4	809.3	800.0
20°	939.9	907.7	876.5	847.9	829.8	813.7	803.3	795.5	786.2	783.6	774.2
22.5°	911.2	875.7	845.8	821.8	801.9	783.8	772.5	767.3	760.8	752.8	750.9
25°	864.6	827.7	802.3	778.4	760.7	744.1	736.3	729.6	723.3	717.6	715.5
27.5°	824.3	791.3	761.1	739.5	724.2	709.0	702.1	693.9	689.4	684.8	679.2
30°	796.0	762.3	735.8	715.0	698.4	684.9	677.6	671.9	667.8	663.6	660.5
32.5°	766.9	735.7	710.0	689.7	673.1	662.9	656.4	652.4	647.8	642.8	638.9
35°	728.5	694.2	669.3	651.7	638.7	630.9	623.6	620.0	614.8	614.8	610.6
37.5°	685.2	655.6	633.6	617.5	605.9	598.9	591.0	588.5	585.2	583.0	581.6
40°	659.5	631.9	611.2	595.1	582.6	576.9	570.7	566.5	564.4	561.8	560.8
42.5°	632.9	606.6	586.7	571.8	561.0	556.1	550.3	547.4	543.2	539.8	539.2
45°	592.5	567.0	548.9	536.9	527.6	521.9	518.2	512.0	509.9	505.8	505.2
47.5°	554.1	529.7	511.9	502.1	493.9	489.2	483.5	477.3	474.9	472.8	472.6
50°	525.5	503.2	486.5	477.2	469.4	462.7	456.9	452.8	451.2	451.2	452.3
52.5°	496.4	477.4	463.3	451.9	444.5	437.3	432.0	429.5	427.1	429.6	431.5
55°	453.8	434.6	424.2	413.3	406.1	397.7	395.2	394.1	392.6	396.7	398.8
57.5°	408.8	395.3	383.1	372.3	365.8	361.0	357.5	356.8	359.7	361.7	368.5
60°	380.1	364.5	353.6	345.3	337.5	334.4	333.4	332.3	334.4	340.1	348.9
62.5°	348.5	335.9	324.1	317.9	312.2	307.0	306.8	307.4	311.6	318.1	326.9
65°	302.2	291.3	283.5	276.2	271.6	268.5	269.5	271.6	276.2	285.1	294.9
67.5°	255.2	247.7	240.7	234.8	230.3	230.3	231.4	234.5	240.0	250.2	259.2
70°	224.8	216.5	210.8	208.2	204.6	202.5	205.6	210.8	215.5	224.8	232.6
72.5°	194.5	187.5	183.0	181.2	179.7	178.0	179.0	184.6	191.0	200.3	209.4
75°	149.5	146.9	143.8	141.8	140.2	141.2	142.3	147.5	152.7	162.5	172.9
77.5°	109.1	106.4	104.6	104.1	103.2	103.7	106.7	110.5	115.6	122.8	130.6
80°	82.6	81.5	80.5	80.0	80.0	80.5	84.6	87.2	91.9	98.7	104.9
82.5°	60.1	59.5	59.3	59.2	59.6	59.7	62.2	65.6	69.5	74.6	80.0
85°	31.7	30.6	32.2	32.7	31.7	33.2	34.3	36.3	37.9	40.5	43.1
87.5°	12.2	13.5	13.4	14.2	14.5	15.8	15.6	17.5	18.5	19.6	19.7
90°	9.3	11.6	12.8	15.1	16.3	18.6	19.8	20.9	22.1	23.2	25.6
92.5°	61.4	95.3	158.7	265.2	380.7	374.6	303.3	205.9	149.4	112.5	95.3
95°	87.1	139.4	263.8	519.4	840.1	1029.5	1007.4	835.4	658.8	515.9	418.3
97.5°	107.4	145.0	227.3	414.6	750.2	1099.4	1274.7	1244.2	1120.4	981.2	845.4
100°	123.2	158.0	225.4	376.5	669.3	1049.2	1339.7	1429.2	1372.3	1252.6	1131.7
102.5°	139.9	173.8	233.8	360.7	607.9	960.9	1300.7	1491.5	1526.6	1469.2	1387.4
105°	167.3	199.9	251.0	354.4	548.4	842.4	1175.9	1454.8	1614.0	1665.1	1652.3
107.5°	197.8	227.0	276.5	365.1	523.3	760.8	1048.6	1323.7	1536.1	1667.4	1728.1
110°	217.3	247.5	295.1	375.3	515.9	722.7	976.0	1227.0	1447.8	1611.6	1710.4



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	237.7	267.0	312.8	388.3	515.9	700.4	922.1	1150.8	1360.4	1526.1	1642.5
115°	268.4	297.5	340.5	407.8	519.4	676.3	863.3	1055.1	1235.2	1394.3	1521.0
117.5°	300.0	328.1	368.8	430.2	527.1	664.4	828.2	993.2	1148.5	1285.6	1401.8
120°	319.5	348.6	389.3	445.0	534.5	658.8	808.7	959.8	1099.2	1227.0	1329.3
122.5°	339.1	368.1	408.8	461.8	541.0	654.2	792.0	934.7	1063.9	1177.8	1273.5
125°	366.0	396.2	434.6	484.5	551.9	648.4	769.2	898.2	1016.7	1117.8	1201.5
127.5°	392.3	422.5	459.4	505.5	564.2	645.6	748.3	861.0	971.6	1066.0	1144.3
130°	409.0	439.2	475.2	519.4	571.7	643.7	734.4	837.8	940.0	1030.7	1106.2
132.5°	423.9	454.1	490.1	531.5	580.0	643.7	723.2	814.5	910.3	992.5	1065.3
135°	442.7	474.1	510.1	548.4	591.4	643.7	710.0	784.3	864.5	938.9	1005.1
137.5°	459.2	491.5	524.3	561.0	601.9	645.1	698.1	758.8	823.6	885.4	941.7
140°	469.4	500.8	534.5	569.4	606.5	646.0	692.5	744.8	799.4	852.9	901.7
142.5°	479.7	509.2	541.0	574.0	609.3	647.0	687.9	732.7	779.0	825.0	867.3
145°	495.0	521.7	551.9	581.0	612.4	646.0	680.9	716.9	752.9	789.0	820.3
147.5°	508.9	532.4	558.9	585.2	613.5	643.0	673.7	702.1	731.3	759.0	782.7
150°	518.2	538.0	563.5	588.0	613.5	640.2	668.1	693.7	719.3	741.3	762.2
152.5°	526.6	544.5	568.2	589.8	612.6	636.5	661.6	684.4	707.2	727.4	743.7
155°	536.8	553.1	572.8	591.4	610.0	629.8	650.7	670.4	689.0	705.3	718.1
157.5°	547.5	559.8	576.8	592.6	607.0	622.8	640.5	656.5	671.8	684.4	694.4
160°	553.1	563.5	578.7	592.6	604.2	618.2	632.1	647.2	658.8	670.4	678.6
162.5°	558.7	567.3	580.5	591.7	601.4	612.6	624.7	637.0	647.7	657.4	664.6
165°	564.7	571.7	581.0	590.3	597.2	604.2	613.5	622.8	630.9	637.9	643.7
167.5°	568.9	573.3	581.0	587.5	590.7	596.1	602.6	609.3	614.7	620.0	624.2
170°	571.7	575.2	581.0	585.6	588.0	591.4	596.1	601.9	605.4	608.9	611.2
172.5°	573.5	575.2	580.0	583.8	584.2	585.9	589.6	593.5	597.0	599.6	601.0
175°	575.2	575.2	578.7	581.0	579.8	579.8	581.0	584.5	584.5	586.8	586.8
177.5°	575.4	575.4	577.3	578.2	576.3	576.3	577.3	578.2	579.1	579.1	579.1
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1165.6	1168.5	1166.0	1169.4	1166.0	1168.5	1165.6	1168.1	1171.9	1169.4	1175.2
5°	1074.3	1069.7	1072.8	1070.7	1072.8	1069.7	1074.3	1076.9	1083.2	1085.2	1089.4
7.5°	990.0	985.5	980.5	978.1	980.5	985.5	990.0	991.6	996.9	1004.7	1010.6
10°	937.3	931.5	931.0	927.4	931.0	931.5	937.3	943.0	946.6	956.5	963.2
12.5°	898.6	893.3	887.4	885.9	887.4	893.3	898.6	903.5	904.6	915.8	920.4
15°	843.8	839.6	836.0	839.1	836.0	839.6	843.8	846.9	852.6	860.4	865.6
17.5°	798.2	794.8	794.1	790.3	794.1	794.8	798.2	800.0	809.3	814.4	823.3
20°	769.5	766.9	768.0	761.2	768.0	766.9	769.5	774.2	783.6	786.2	795.5
22.5°	746.7	741.6	741.0	739.6	741.0	741.6	746.7	750.9	752.8	760.8	767.3
25°	710.9	708.3	705.7	708.3	705.7	708.3	710.9	715.5	717.6	723.3	729.6
27.5°	679.6	676.5	675.8	676.1	675.8	676.5	679.6	679.2	684.8	689.4	693.9
30°	660.5	655.3	655.8	655.3	655.8	655.3	660.5	660.5	663.6	667.8	671.9
32.5°	639.7	636.2	635.5	634.5	635.5	636.2	639.7	638.9	642.8	647.8	652.4
35°	609.1	609.1	606.5	606.5	606.5	609.1	609.1	610.6	614.8	614.8	620.0
37.5°	580.3	579.8	578.2	578.5	578.2	579.8	580.3	581.6	583.0	585.2	588.5
40°	558.7	558.2	556.6	553.5	556.6	558.2	558.7	560.8	561.8	564.4	566.5
42.5°	537.9	536.2	535.5	534.4	535.5	536.2	537.9	539.2	539.8	543.2	547.4
45°	505.2	505.2	504.2	503.7	504.2	505.2	505.2	505.2	505.8	509.9	512.0
47.5°	473.5	474.4	476.4	476.1	476.4	474.4	473.5	472.6	472.8	474.9	477.3
50°	454.3	454.9	456.4	456.9	456.4	454.9	454.3	452.3	451.2	451.2	452.8
52.5°	433.2	436.2	438.1	437.8	438.1	436.2	433.2	431.5	429.6	427.1	429.5
55°	403.5	407.1	410.7	411.3	410.7	407.1	403.5	398.8	396.7	392.6	394.1
57.5°	374.1	379.2	383.0	384.2	383.0	379.2	374.1	368.5	361.7	359.7	356.8
60°	354.1	360.9	365.6	367.6	365.6	360.9	354.1	348.9	340.1	334.4	332.3
62.5°	335.0	342.6	347.3	347.7	347.3	342.6	335.0	326.9	318.1	311.6	307.4
65°	303.8	311.6	315.7	318.8	315.7	311.6	303.8	294.9	285.1	276.2	271.6
67.5°	270.1	277.9	282.5	285.0	282.5	277.9	270.1	259.2	250.2	240.0	234.5
70°	245.6	253.4	259.6	261.7	259.6	253.4	245.6	232.6	224.8	215.5	210.8
72.5°	221.5	228.5	233.5	235.9	233.5	228.5	221.5	209.4	200.3	191.0	184.6
75°	179.7	189.0	193.7	196.3	193.7	189.0	179.7	172.9	162.5	152.7	147.5
77.5°	138.5	147.1	149.9	151.2	149.9	147.1	138.5	130.6	122.8	115.6	110.5
80°	111.1	116.3	119.9	120.5	119.9	116.3	111.1	104.9	98.7	91.9	87.2
82.5°	85.4	89.7	90.9	92.2	90.9	89.7	85.4	80.0	74.6	69.5	65.6
85°	46.7	48.8	49.3	48.8	49.3	48.8	46.7	43.1	40.5	37.9	36.3
87.5°	20.5	20.1	20.3	21.1	20.3	20.1	20.5	19.7	19.6	18.5	17.5
90°	25.6	25.6	26.7	26.7	26.7	25.6	25.6	25.6	23.2	22.1	20.9
92.5°	80.4	77.6	76.0	74.1	76.0	77.6	80.4	95.3	112.5	149.4	205.9
95°	335.8	300.9	291.7	273.1	291.7	300.9	335.8	418.3	515.9	658.8	835.4
97.5°	773.6	708.6	674.9	660.0	674.9	708.6	773.6	845.4	981.2	1120.4	1244.2
100°	1051.6	967.9	924.9	906.3	924.9	967.9	1051.6	1131.7	1252.6	1372.3	1429.2
102.5°	1301.6	1242.1	1195.4	1181.5	1195.4	1242.1	1301.6	1387.4	1469.2	1526.6	1491.5
105°	1615.1	1576.8	1553.5	1539.6	1553.5	1576.8	1615.1	1652.3	1665.1	1614.0	1454.8
107.5°	1746.9	1746.7	1739.0	1729.7	1739.0	1746.7	1746.9	1728.1	1667.4	1536.1	1323.7
110°	1762.7	1784.8	1792.9	1792.9	1792.9	1784.8	1762.7	1710.4	1611.6	1447.8	1227.0



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1719.0	1756.9	1777.1	1785.5	1777.1	1756.9	1719.0	1642.5	1526.1	1360.4	1150.8
115°	1611.6	1667.4	1699.9	1715.0	1699.9	1667.4	1611.6	1521.0	1394.3	1235.2	1055.1
117.5°	1492.4	1550.1	1582.4	1591.6	1582.4	1550.1	1492.4	1401.8	1285.6	1148.5	993.2
120°	1415.3	1471.0	1502.4	1511.7	1502.4	1471.0	1415.3	1329.3	1227.0	1099.2	959.8
122.5°	1350.2	1401.3	1432.7	1441.1	1432.7	1401.3	1350.2	1273.5	1177.8	1063.9	934.7
125°	1266.5	1314.2	1339.7	1351.4	1339.7	1314.2	1266.5	1201.5	1117.8	1016.7	898.2
127.5°	1203.3	1245.4	1269.6	1274.7	1269.6	1245.4	1203.3	1144.3	1066.0	971.6	861.0
130°	1164.3	1202.6	1225.9	1232.8	1225.9	1202.6	1164.3	1106.2	1030.7	940.0	837.8
132.5°	1123.4	1161.7	1183.1	1191.0	1183.1	1161.7	1123.4	1065.3	992.5	910.3	814.5
135°	1056.2	1094.6	1115.5	1122.5	1115.5	1094.6	1056.2	1005.1	938.9	864.5	784.3
137.5°	987.4	1022.3	1041.6	1049.2	1041.6	1022.3	987.4	941.7	885.4	823.6	758.8
140°	944.7	974.9	992.3	998.1	992.3	974.9	944.7	901.7	852.9	799.4	744.8
142.5°	903.8	929.3	945.8	950.7	945.8	929.3	903.8	867.3	825.0	779.0	732.7
145°	848.2	868.0	880.8	885.4	880.8	868.0	848.2	820.3	789.0	752.9	716.9
147.5°	804.8	820.6	828.0	830.1	828.0	820.6	804.8	782.7	759.0	731.3	702.1
150°	779.7	793.6	798.3	799.4	798.3	793.6	779.7	762.2	741.3	719.3	693.7
152.5°	758.3	769.4	774.1	775.3	774.1	769.4	758.3	743.7	727.4	707.2	684.4
155°	729.7	737.8	741.3	742.5	741.3	737.8	729.7	718.1	705.3	689.0	670.4
157.5°	703.4	710.2	713.4	713.2	713.4	710.2	703.4	694.4	684.4	671.8	656.5
160°	686.7	692.5	694.9	693.7	694.9	692.5	686.7	678.6	670.4	658.8	647.2
162.5°	670.9	675.8	676.3	676.0	676.3	675.8	670.9	664.6	657.4	647.7	637.0
165°	648.4	650.7	650.7	650.7	650.7	650.7	648.4	643.7	637.9	630.9	622.8
167.5°	626.5	628.6	627.7	627.5	627.7	628.6	626.5	624.2	620.0	614.7	609.3
170°	613.5	614.7	614.7	613.5	614.7	614.7	613.5	611.2	608.9	605.4	601.9
172.5°	601.4	603.5	601.7	600.5	601.7	603.5	601.4	601.0	599.6	597.0	593.5
175°	586.8	588.0	585.6	584.5	585.6	588.0	586.8	586.8	586.8	584.5	584.5
177.5°	578.2	579.1	576.3	576.3	576.3	579.1	578.2	579.1	579.1	579.1	578.2
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1169.8	1174.8	1181.0	1185.6	1193.9	1197.6	1202.2	1205.9	1212.6	1218.8	1226.3
5°	1091.0	1099.8	1111.7	1124.7	1139.8	1150.2	1164.7	1173.5	1191.2	1207.3	1222.8
7.5°	1019.5	1030.3	1047.2	1063.9	1083.6	1101.4	1119.6	1139.8	1162.3	1188.9	1210.9
10°	970.5	985.0	1003.2	1024.0	1047.9	1068.6	1093.0	1114.8	1142.4	1173.5	1202.6
12.5°	931.4	943.9	964.2	984.1	1009.6	1035.0	1060.2	1089.1	1121.2	1155.7	1192.2
15°	877.5	887.9	904.5	932.1	958.0	983.0	1020.9	1047.9	1088.4	1126.8	1170.9
17.5°	831.5	844.4	858.4	882.0	908.9	940.1	973.9	1007.8	1046.8	1095.5	1145.3
20°	803.3	813.7	829.8	847.9	876.5	907.7	939.9	974.1	1021.9	1072.3	1125.7
22.5°	772.5	783.8	801.9	821.8	845.8	875.7	911.2	948.8	998.6	1048.2	1106.2
25°	736.3	744.1	760.7	778.4	802.3	827.7	864.6	906.1	955.4	1012.0	1071.2
27.5°	702.1	709.0	724.2	739.5	761.1	791.3	824.3	866.2	912.7	970.1	1035.7
30°	677.6	684.9	698.4	715.0	735.8	762.3	796.0	835.5	885.3	941.4	1010.0
32.5°	656.4	662.9	673.1	689.7	710.0	735.7	766.9	807.2	857.1	914.0	981.3
35°	623.6	630.9	638.7	651.7	669.3	694.2	728.5	766.4	814.2	869.2	931.0
37.5°	591.0	598.9	605.9	617.5	633.6	655.6	685.2	724.7	767.9	820.9	880.2
40°	570.7	576.9	582.6	595.1	611.2	631.9	659.5	694.8	740.5	789.8	839.1
42.5°	550.3	556.1	561.0	571.8	586.7	606.6	632.9	667.3	709.7	755.7	799.2
45°	518.2	521.9	527.6	536.9	548.9	567.0	592.5	623.1	658.9	702.6	735.3
47.5°	483.5	489.2	493.9	502.1	511.9	529.7	554.1	580.2	612.7	645.1	668.2
50°	456.9	462.7	469.4	477.2	486.5	503.2	525.5	552.0	579.5	604.4	624.1
52.5°	432.0	437.3	444.5	451.9	463.3	477.4	496.4	520.0	547.1	565.0	581.4
55°	395.2	397.7	406.1	413.3	424.2	434.6	453.8	474.6	491.2	504.7	518.2
57.5°	357.5	361.0	365.8	372.3	383.1	395.3	408.8	427.1	436.9	443.9	454.3
60°	333.4	334.4	337.5	345.3	353.6	364.5	380.1	393.1	400.3	406.1	414.9
62.5°	306.8	307.0	312.2	317.9	324.1	335.9	348.5	359.0	365.0	367.8	376.3
65°	269.5	268.5	271.6	276.2	283.5	291.3	302.2	311.6	311.0	314.1	319.3
67.5°	231.4	230.3	230.3	234.8	240.7	247.7	255.2	260.6	260.7	264.8	267.4
70°	205.6	202.5	204.6	208.2	210.8	216.5	224.8	226.9	227.4	229.5	232.1
72.5°	179.0	178.0	179.7	181.2	183.0	187.5	194.5	195.8	195.9	197.1	201.4
75°	142.3	141.2	140.2	141.8	143.8	146.9	149.5	151.6	151.1	151.6	154.7
77.5°	106.7	103.7	103.2	104.1	104.6	106.4	109.1	108.9	109.5	109.4	112.9
80°	84.6	80.5	80.0	80.0	80.5	81.5	82.6	83.6	82.0	83.6	84.6
82.5°	62.2	59.7	59.6	59.2	59.3	59.5	60.1	60.8	60.4	61.2	61.8
85°	34.3	33.2	31.7	32.7	32.2	30.6	31.7	30.1	29.6	30.1	30.6
87.5°	15.6	15.8	14.5	14.2	13.4	13.5	12.2	11.4	10.5	10.4	11.4
90°	19.8	18.6	16.3	15.1	12.8	11.6	9.3	7.0	4.6	2.3	1.2
92.5°	303.3	374.6	380.7	265.2	158.7	95.3	61.4	41.4	27.0	17.2	14.2
95°	1007.4	1029.5	840.1	519.4	263.8	139.4	87.1	61.6	48.8	39.5	38.3
97.5°	1274.7	1099.4	750.2	414.6	227.3	145.0	107.4	84.4	71.6	65.1	63.7
100°	1339.7	1049.2	669.3	376.5	225.4	158.0	123.2	101.1	88.3	83.7	81.3
102.5°	1300.7	960.9	607.9	360.7	233.8	173.8	139.9	119.7	106.0	102.3	100.9
105°	1175.9	842.4	548.4	354.4	251.0	199.9	167.3	148.7	137.1	131.3	131.3
107.5°	1048.6	760.8	523.3	365.1	276.5	227.0	197.8	178.5	168.9	163.4	161.0
110°	976.0	722.7	515.9	375.3	295.1	247.5	217.3	199.9	189.4	184.8	182.4



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	922.1	700.4	515.9	388.3	312.8	267.0	237.7	220.3	209.8	206.1	203.8
115°	863.3	676.3	519.4	407.8	340.5	297.5	268.4	251.0	240.5	237.0	234.7
117.5°	828.2	664.4	527.1	430.2	368.8	328.1	300.0	280.3	269.8	266.1	262.6
120°	808.7	658.8	534.5	445.0	389.3	348.6	319.5	299.8	289.3	284.7	281.2
122.5°	792.0	654.2	541.0	461.8	408.8	368.1	339.1	317.4	307.0	303.3	300.7
125°	769.2	648.4	551.9	484.5	434.6	396.2	366.0	343.9	333.5	327.7	325.3
127.5°	748.3	645.6	564.2	505.5	459.4	422.5	392.3	368.8	355.6	348.1	344.6
130°	734.4	643.7	571.7	519.4	475.2	439.2	409.0	384.6	369.5	360.2	356.7
132.5°	723.2	643.7	580.0	531.5	490.1	454.1	423.9	398.6	381.6	370.4	366.0
135°	710.0	643.7	591.4	548.4	510.1	474.1	442.7	418.3	399.7	385.8	381.1
137.5°	698.1	645.1	601.9	561.0	524.3	491.5	459.2	435.3	416.7	403.7	400.2
140°	692.5	646.0	606.5	569.4	534.5	500.8	469.4	447.4	428.8	414.8	411.3
142.5°	687.9	647.0	609.3	574.0	541.0	509.2	479.7	458.5	439.9	426.9	424.3
145°	680.9	646.0	612.4	581.0	551.9	521.7	495.0	474.1	457.8	446.2	443.9
147.5°	673.7	643.0	613.5	585.2	558.9	532.4	508.9	490.8	475.7	465.7	464.3
150°	668.1	640.2	613.5	588.0	563.5	538.0	518.2	502.0	486.9	478.7	476.4
152.5°	661.6	636.5	612.6	589.8	568.2	544.5	526.6	511.3	498.0	490.8	489.4
155°	650.7	629.8	610.0	591.4	572.8	553.1	536.8	525.2	513.6	506.6	506.6
157.5°	640.5	622.8	607.0	592.6	576.8	559.8	547.5	537.3	527.3	521.7	522.0
160°	632.1	618.2	604.2	592.6	578.7	563.5	553.1	543.8	535.7	531.0	532.2
162.5°	624.7	612.6	601.4	591.7	580.5	567.3	558.7	551.2	544.0	539.4	540.5
165°	613.5	604.2	597.2	590.3	581.0	571.7	564.7	560.1	554.3	550.8	553.1
167.5°	602.6	596.1	590.7	587.5	581.0	573.3	568.9	565.6	562.4	560.3	561.5
170°	596.1	591.4	588.0	585.6	581.0	575.2	571.7	569.4	567.0	565.9	567.0
172.5°	589.6	585.9	584.2	583.8	580.0	575.2	573.5	572.1	569.8	568.7	570.8
175°	581.0	579.8	579.8	581.0	578.7	575.2	575.2	575.2	574.0	572.8	575.2
177.5°	577.3	576.3	576.3	578.2	577.3	575.4	575.4	576.3	575.4	575.4	577.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1230.0	1235.8	1239.6	1246.6	1252.4	1255.8	1258.7	1261.2	1264.1	1266.6	1273.6
5°	1237.9	1251.4	1262.8	1280.5	1296.6	1309.0	1322.5	1334.5	1344.4	1358.4	1369.3
7.5°	1234.5	1258.5	1283.6	1310.9	1338.8	1364.8	1388.7	1411.0	1431.3	1455.8	1477.3
10°	1231.2	1263.9	1296.1	1332.9	1370.8	1403.0	1433.1	1463.8	1486.1	1517.3	1543.7
12.5°	1228.7	1267.2	1306.0	1350.4	1392.0	1437.5	1477.6	1499.9	1533.9	1558.8	1590.3
15°	1218.2	1269.1	1322.5	1372.4	1431.6	1473.6	1509.0	1552.6	1584.2	1615.9	1650.2
17.5°	1199.4	1257.0	1316.8	1382.2	1439.0	1484.1	1529.6	1571.7	1609.5	1652.0	1694.6
20°	1190.7	1248.3	1316.8	1383.8	1439.4	1486.6	1533.4	1579.6	1621.1	1675.6	1725.0
22.5°	1172.4	1242.1	1305.2	1370.5	1427.7	1479.2	1532.1	1584.6	1639.8	1701.4	1763.2
25°	1139.8	1210.4	1277.4	1341.8	1399.4	1463.8	1520.4	1590.5	1661.1	1742.6	1819.5
27.5°	1105.9	1173.5	1234.9	1297.1	1364.3	1437.2	1510.6	1590.2	1682.6	1785.5	1893.9
30°	1078.5	1142.4	1202.1	1265.9	1336.0	1418.1	1498.6	1593.1	1700.0	1815.8	1944.6
32.5°	1046.5	1105.4	1163.4	1231.1	1307.4	1394.0	1487.8	1591.4	1720.0	1851.6	1984.1
35°	991.8	1041.1	1100.8	1173.0	1259.2	1358.4	1466.9	1589.4	1736.9	1888.0	1999.7
37.5°	926.9	972.8	1035.7	1114.8	1205.2	1311.6	1440.4	1585.8	1742.4	1862.9	1898.9
40°	883.3	925.8	991.3	1073.3	1165.7	1278.4	1419.6	1573.3	1725.0	1801.8	1772.2
42.5°	836.7	881.4	945.1	1026.4	1125.9	1248.5	1393.5	1547.2	1674.3	1703.4	1601.1
45°	763.3	809.5	872.3	954.4	1061.4	1194.3	1345.4	1485.1	1558.3	1505.8	1347.5
47.5°	695.1	738.4	796.6	881.3	991.7	1129.2	1274.7	1386.1	1391.9	1266.8	1097.6
50°	648.6	688.5	747.2	831.8	941.4	1080.6	1211.9	1299.7	1260.2	1118.5	955.9
52.5°	602.9	642.0	699.9	783.7	892.0	1019.5	1141.7	1203.3	1129.0	983.5	844.6
55°	536.9	571.2	627.8	705.1	808.0	926.4	1030.2	1051.5	954.9	811.6	698.9
57.5°	472.5	504.5	556.0	627.3	721.2	826.1	907.3	902.8	800.7	677.7	588.3
60°	428.9	460.1	505.8	575.3	661.0	751.4	820.9	804.3	703.1	597.1	521.9
62.5°	389.9	417.7	460.9	521.7	599.9	683.7	740.8	716.3	617.1	524.4	464.9
65°	332.3	355.7	392.6	444.5	509.4	578.5	622.6	590.9	506.3	434.1	386.3
67.5°	277.4	296.1	327.0	368.5	423.8	479.3	506.2	474.3	406.6	353.9	318.5
70°	242.5	259.1	283.0	319.9	368.2	414.9	435.1	406.6	348.4	303.2	277.8
72.5°	207.6	221.3	242.3	275.4	314.1	354.7	372.4	345.1	297.3	259.2	235.4
75°	160.5	169.8	184.3	207.2	237.8	270.0	279.9	256.0	225.4	196.8	181.2
77.5°	114.9	122.8	133.8	148.2	169.9	190.4	199.0	185.2	161.5	143.4	130.6
80°	88.3	92.4	101.8	113.7	130.9	143.8	149.5	140.7	124.1	110.6	100.7
82.5°	62.9	67.1	72.7	82.6	93.5	102.3	108.4	102.5	90.5	79.9	74.1
85°	30.6	33.2	36.3	40.5	48.8	54.0	53.5	49.8	45.2	41.0	37.9
87.5°	11.3	12.1	13.9	16.4	18.1	20.0	21.3	20.7	19.5	18.5	17.5
90°	2.3	4.6	7.0	9.3	11.6	12.8	15.1	16.3	18.6	19.8	20.9
92.5°	17.2	27.0	41.4	61.4	95.3	158.7	265.2	380.7	374.6	303.3	205.9
95°	39.5	48.8	61.6	87.1	139.4	263.8	519.4	840.1	1029.5	1007.4	835.4
97.5°	65.1	71.6	84.4	107.4	145.0	227.3	414.6	750.2	1099.4	1274.7	1244.2
100°	83.7	88.3	101.1	123.2	158.0	225.4	376.5	669.3	1049.2	1339.7	1429.2
102.5°	102.3	106.0	119.7	139.9	173.8	233.8	360.7	607.9	960.9	1300.7	1491.5
105°	131.3	137.1	148.7	167.3	199.9	251.0	354.4	548.4	842.4	1175.9	1454.8
107.5°	163.4	168.9	178.5	197.8	227.0	276.5	365.1	523.3	760.8	1048.6	1323.7
110°	184.8	189.4	199.9	217.3	247.5	295.1	375.3	515.9	722.7	976.0	1227.0



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	206.1	209.8	220.3	237.7	267.0	312.8	388.3	515.9	700.4	922.1	1150.8
115°	237.0	240.5	251.0	268.4	297.5	340.5	407.8	519.4	676.3	863.3	1055.1
117.5°	266.1	269.8	280.3	300.0	328.1	368.8	430.2	527.1	664.4	828.2	993.2
120°	284.7	289.3	299.8	319.5	348.6	389.3	445.0	534.5	658.8	808.7	959.8
122.5°	303.3	307.0	317.4	339.1	368.1	408.8	461.8	541.0	654.2	792.0	934.7
125°	327.7	333.5	343.9	366.0	396.2	434.6	484.5	551.9	648.4	769.2	898.2
127.5°	348.1	355.6	368.8	392.3	422.5	459.4	505.5	564.2	645.6	748.3	861.0
130°	360.2	369.5	384.6	409.0	439.2	475.2	519.4	571.7	643.7	734.4	837.8
132.5°	370.4	381.6	398.6	423.9	454.1	490.1	531.5	580.0	643.7	723.2	814.5
135°	385.8	399.7	418.3	442.7	474.1	510.1	548.4	591.4	643.7	710.0	784.3
137.5°	403.7	416.7	435.3	459.2	491.5	524.3	561.0	601.9	645.1	698.1	758.8
140°	414.8	428.8	447.4	469.4	500.8	534.5	569.4	606.5	646.0	692.5	744.8
142.5°	426.9	439.9	458.5	479.7	509.2	541.0	574.0	609.3	647.0	687.9	732.7
145°	446.2	457.8	474.1	495.0	521.7	551.9	581.0	612.4	646.0	680.9	716.9
147.5°	465.7	475.7	490.8	508.9	532.4	558.9	585.2	613.5	643.0	673.7	702.1
150°	478.7	486.9	502.0	518.2	538.0	563.5	588.0	613.5	640.2	668.1	693.7
152.5°	490.8	498.0	511.3	526.6	544.5	568.2	589.8	612.6	636.5	661.6	684.4
155°	506.6	513.6	525.2	536.8	553.1	572.8	591.4	610.0	629.8	650.7	670.4
157.5°	521.7	527.3	537.3	547.5	559.8	576.8	592.6	607.0	622.8	640.5	656.5
160°	531.0	535.7	543.8	553.1	563.5	578.7	592.6	604.2	618.2	632.1	647.2
162.5°	539.4	544.0	551.2	558.7	567.3	580.5	591.7	601.4	612.6	624.7	637.0
165°	550.8	554.3	560.1	564.7	571.7	581.0	590.3	597.2	604.2	613.5	622.8
167.5°	560.3	562.4	565.6	568.9	573.3	581.0	587.5	590.7	596.1	602.6	609.3
170°	565.9	567.0	569.4	571.7	575.2	581.0	585.6	588.0	591.4	596.1	601.9
172.5°	568.7	569.8	572.1	573.5	575.2	580.0	583.8	584.2	585.9	589.6	593.5
175°	572.8	574.0	575.2	575.2	575.2	578.7	581.0	579.8	579.8	581.0	584.5
177.5°	575.4	575.4	576.3	575.4	575.4	577.3	578.2	576.3	576.3	577.3	578.2
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1279.4	1282.8	1289.8	1287.3	1290.7	1292.3	1294.0
5°	1382.8	1399.4	1406.7	1405.6	1416.5	1413.9	1411.3
7.5°	1499.5	1517.0	1526.7	1538.9	1545.9	1546.4	1552.6
10°	1565.6	1588.4	1597.8	1610.7	1619.0	1623.7	1623.2
12.5°	1616.2	1634.1	1655.1	1661.4	1672.6	1678.5	1676.4
15°	1677.2	1705.8	1727.6	1738.5	1752.5	1756.6	1762.4
17.5°	1731.6	1769.9	1795.4	1829.2	1842.0	1849.8	1845.2
20°	1772.7	1823.1	1848.6	1889.1	1911.4	1923.3	1919.2
22.5°	1821.3	1875.9	1922.9	1958.0	1992.0	2008.1	2011.4
25°	1904.6	1979.4	2048.5	2094.7	2136.7	2146.6	2168.4
27.5°	1997.7	2085.9	2159.7	2208.3	2237.6	2248.6	2255.4
30°	2056.3	2144.0	2199.6	2230.7	2240.1	2239.0	2238.0
32.5°	2084.9	2139.9	2150.5	2141.8	2120.4	2102.4	2083.5
35°	2044.3	2003.3	1942.0	1863.1	1804.9	1746.3	1740.5
37.5°	1838.6	1707.4	1605.4	1491.5	1425.8	1385.2	1357.1
40°	1645.0	1496.0	1372.4	1276.3	1209.3	1182.9	1156.9
42.5°	1434.8	1292.4	1183.0	1102.7	1052.3	1022.9	1002.4
45°	1165.7	1040.1	954.4	896.2	856.3	833.4	820.4
47.5°	955.2	862.3	789.5	747.5	719.9	702.1	702.2
50°	842.2	753.4	705.1	671.9	648.0	634.0	636.6
52.5°	742.1	675.8	634.5	606.7	589.0	580.4	580.1
55°	620.5	572.7	545.7	525.5	513.5	503.7	505.8
57.5°	530.8	490.5	472.4	455.6	447.3	443.3	437.6
60°	475.1	444.0	428.4	414.9	406.6	403.5	397.7
62.5°	425.7	401.2	386.0	375.0	367.5	366.5	362.0
65°	357.8	339.1	325.6	320.4	312.6	310.5	310.5
67.5°	294.9	281.5	271.1	266.3	262.8	263.4	260.9
70°	255.5	244.6	237.8	232.6	230.0	230.5	228.5
72.5°	223.5	211.3	205.4	202.3	198.9	200.2	199.4
75°	169.3	163.0	159.9	156.8	154.7	153.7	152.7
77.5°	124.3	118.8	116.4	114.7	115.0	112.5	114.4
80°	96.1	91.4	89.8	87.2	86.7	86.7	86.2
82.5°	70.3	67.7	66.6	64.4	63.5	64.3	62.9
85°	36.3	34.3	33.8	33.8	32.7	31.7	34.3
87.5°	17.7	16.3	16.7	16.3	16.3	16.1	15.3
90°	22.1	23.2	25.6	25.6	25.6	26.7	26.7
92.5°	149.4	112.5	95.3	80.4	77.6	76.0	74.1
95°	658.8	515.9	418.3	335.8	300.9	291.7	273.1
97.5°	1120.4	981.2	845.4	773.6	708.6	674.9	660.0
100°	1372.3	1252.6	1131.7	1051.6	967.9	924.9	906.3
102.5°	1526.6	1469.2	1387.4	1301.6	1242.1	1195.4	1181.5
105°	1614.0	1665.1	1652.3	1615.1	1576.8	1553.5	1539.6
107.5°	1536.1	1667.4	1728.1	1746.9	1746.7	1739.0	1729.7
110°	1447.8	1611.6	1710.4	1762.7	1784.8	1792.9	1792.9



TEST NUMBER: P333243

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1360.4	1526.1	1642.5	1719.0	1756.9	1777.1	1785.5
115°	1235.2	1394.3	1521.0	1611.6	1667.4	1699.9	1715.0
117.5°	1148.5	1285.6	1401.8	1492.4	1550.1	1582.4	1591.6
120°	1099.2	1227.0	1329.3	1415.3	1471.0	1502.4	1511.7
122.5°	1063.9	1177.8	1273.5	1350.2	1401.3	1432.7	1441.1
125°	1016.7	1117.8	1201.5	1266.5	1314.2	1339.7	1351.4
127.5°	971.6	1066.0	1144.3	1203.3	1245.4	1269.6	1274.7
130°	940.0	1030.7	1106.2	1164.3	1202.6	1225.9	1232.8
132.5°	910.3	992.5	1065.3	1123.4	1161.7	1183.1	1191.0
135°	864.5	938.9	1005.1	1056.2	1094.6	1115.5	1122.5
137.5°	823.6	885.4	941.7	987.4	1022.3	1041.6	1049.2
140°	799.4	852.9	901.7	944.7	974.9	992.3	998.1
142.5°	779.0	825.0	867.3	903.8	929.3	945.8	950.7
145°	752.9	789.0	820.3	848.2	868.0	880.8	885.4
147.5°	731.3	759.0	782.7	804.8	820.6	828.0	830.1
150°	719.3	741.3	762.2	779.7	793.6	798.3	799.4
152.5°	707.2	727.4	743.7	758.3	769.4	774.1	775.3
155°	689.0	705.3	718.1	729.7	737.8	741.3	742.5
157.5°	671.8	684.4	694.4	703.4	710.2	713.4	713.2
160°	658.8	670.4	678.6	686.7	692.5	694.9	693.7
162.5°	647.7	657.4	664.6	670.9	675.8	676.3	676.0
165°	630.9	637.9	643.7	648.4	650.7	650.7	650.7
167.5°	614.7	620.0	624.2	626.5	628.6	627.7	627.5
170°	605.4	608.9	611.2	613.5	614.7	614.7	613.5
172.5°	597.0	599.6	601.0	601.4	603.5	601.7	600.5
175°	584.5	586.8	586.8	586.8	588.0	585.6	584.5
177.5°	579.1	579.1	579.1	578.2	579.1	576.3	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3

(END OF REPORT)