

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333499-940

Luminaire Tested: **S125RDIP-S375D590U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333499-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D590U940-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3398.0 lumens  
Efficiency: N/A  
Efficacy: 132.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333499-940

CATALOG NUMBER: S125RDIP-S375D590U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333499-940

CATALOG NUMBER: S125RDIP-S375D590U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	68	63	59	56	53	47	44	42	35	34	33	27
3	79	70	63	57	72	64	58	53	52	48	44	42	38	36	32	30	28	23
4	73	62	54	49	66	57	50	45	47	42	38	37	34	31	28	26	24	20
5	67	55	47	42	60	51	44	39	42	37	33	33	30	27	25	23	21	18
6	61	50	42	36	55	45	38	33	37	32	28	30	26	23	23	21	19	15
7	57	45	37	32	51	41	34	29	34	29	25	27	24	21	21	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3524	3524	3524
5°	3532	3492	3513
10°	3505	3459	3459
15°	3463	3389	3361
20°	3410	3291	3252
25°	3348	3195	3125
30°	3270	3082	2984
35°	3191	2967	2827
40°	3117	2845	2672
45°	3027	2711	2503
50°	2936	2563	2327
55°	2831	2422	2139
60°	2725	2251	1938
65°	2601	2054	1705
70°	2459	1805	1469
75°	2263	1522	1223
80°	1993	1194	1027
85°	1675	978	919



TEST NUMBER: P333499-940

CATALOG NUMBER: S125RDIP-S375D590U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.3	1.5
10°-20°	143.4	4.2
20°-30°	207.9	6.1
30°-40°	237.0	7.0
40°-50°	231.0	6.8
50°-60°	194.4	5.7
60°-70°	136.3	4.0
70°-80°	70.1	2.1
80°-90°	19.1	0.6
90°-100°	24.9	0.7
100°-110°	153.7	4.5
110°-120°	278.8	8.2
120°-130°	357.8	10.5
130°-140°	384.8	11.3
140°-150°	361.2	10.6
150°-160°	292.2	8.6
160°-170°	189.0	5.6
170°-180°	65.2	1.9
0°-30°	402.6	11.8
0°-40°	639.6	18.8
0°-60°	1065.0	31.3
0°-90°	1290.5	38.0
90°-120°	457.4	13.5
90°-150°	1561.2	45.9
90°-180°	2108.0	62.0
0°-180°	3398.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	546	546	546	546	546	
5°	545	543	539	542	542	52
15°	518	515	507	506	503	146
25°	470	463	448	443	438	216
35°	405	394	376	365	359	253
45°	331	319	297	281	274	256
55°	251	238	215	197	190	225
65°	170	156	134	118	112	169
75°	91	78	61	52	49	96
85°	23	16	13	13	12	25
90°	0	5	8	11	12	2
95°	29	26	8	11	11	37
105°	150	152	152	152	151	159
115°	281	283	284	282	279	278
125°	399	403	403	401	399	357
135°	498	501	500	499	496	384
145°	578	578	578	579	576	361
155°	636	633	634	635	631	293
165°	671	668	668	671	667	189
175°	686	683	684	687	683	65
180°	686	686	686	686	686	



TEST NUMBER: P333499-940

CATALOG NUMBER: S125RDIP-S375D590U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6
2.5°	546.6	546.4	546.2	546.0	545.7	545.3	544.6	543.8	543.1	542.3	543.1
5°	544.8	544.5	544.1	543.7	543.3	542.7	541.6	540.6	539.7	538.6	539.6
7.5°	539.5	539.1	538.8	538.4	538.1	537.3	536.1	534.8	533.7	532.4	533.1
10°	534.5	534.2	534.0	533.7	533.4	532.6	531.4	530.0	528.8	527.5	527.8
12.5°	528.9	528.5	528.2	527.9	527.5	526.5	524.8	523.1	521.3	519.6	519.8
15°	518.0	517.5	516.9	516.4	515.9	514.6	512.6	510.8	508.8	506.9	506.8
17.5°	505.8	504.9	504.1	503.2	502.4	500.8	498.3	495.9	493.5	491.1	490.6
20°	496.1	495.3	494.4	493.5	492.5	490.6	487.7	484.7	481.8	478.8	478.4
22.5°	485.6	484.7	483.8	482.9	482.0	480.0	476.9	473.9	470.7	467.7	466.8
25°	469.8	468.4	467.1	465.7	464.3	461.9	458.5	455.1	451.7	448.4	447.2
27.5°	451.7	450.0	448.4	446.7	445.0	442.4	438.7	435.1	431.5	427.8	426.1
30°	438.5	436.8	435.0	433.3	431.5	428.7	424.9	421.1	417.2	413.3	411.3
32.5°	425.6	423.6	421.6	419.5	417.5	414.6	410.6	406.7	402.8	398.9	396.5
35°	404.7	402.5	400.3	398.1	395.9	392.7	388.6	384.5	380.4	376.3	373.6
37.5°	384.1	381.5	378.8	376.1	373.4	370.0	365.8	361.5	357.3	353.0	349.8
40°	369.7	366.9	364.2	361.4	358.6	355.1	350.7	346.3	341.9	337.5	334.0
42.5°	354.5	351.7	348.8	346.1	343.2	339.6	335.0	330.5	325.9	321.4	318.1
45°	331.4	328.7	326.0	323.3	320.7	316.8	311.8	306.8	301.8	296.8	293.0
47.5°	307.4	304.5	301.8	298.9	296.1	292.2	287.1	282.0	277.0	271.9	268.1
50°	292.2	289.2	286.1	283.1	280.1	276.0	270.7	265.6	260.3	255.1	251.3
52.5°	275.7	272.6	269.5	266.4	263.3	259.3	254.4	249.4	244.5	239.6	235.5
55°	251.4	248.4	245.5	242.6	239.7	235.7	230.5	225.3	220.3	215.1	211.0
57.5°	226.9	223.7	220.5	217.4	214.3	210.3	205.3	200.4	195.5	190.5	186.5
60°	211.0	207.8	204.6	201.3	198.1	194.1	189.1	184.2	179.2	174.3	170.3
62.5°	194.2	191.1	188.1	185.0	181.9	177.9	172.9	167.9	162.8	157.8	154.1
65°	170.2	167.1	164.0	160.9	157.7	153.7	148.9	144.1	139.2	134.4	130.7
67.5°	146.4	143.3	140.2	137.1	133.9	130.0	125.4	120.7	116.1	111.5	108.1
70°	130.2	127.2	124.0	120.9	117.8	114.0	109.3	104.8	100.2	95.6	92.7
72.5°	114.4	111.4	108.3	105.3	102.3	98.5	94.3	90.0	85.7	81.4	78.8
75°	90.7	87.9	85.2	82.4	79.7	76.4	72.5	68.7	64.8	61.0	58.9
77.5°	67.1	64.9	62.7	60.5	58.3	55.6	52.6	49.5	46.5	43.3	41.9
80°	53.6	51.4	49.2	47.0	44.8	42.4	39.9	37.3	34.7	32.1	31.3
82.5°	40.4	38.4	36.5	34.4	32.5	30.6	28.9	27.1	25.3	23.5	23.2
85°	22.6	21.0	19.4	17.7	16.1	15.0	14.5	14.1	13.6	13.2	13.1
87.5°	7.7	7.3	7.0	6.7	6.3	6.2	6.3	6.4	6.5	6.6	6.7
90°	0.5	1.4	2.3	3.2	4.1	5.0	5.8	6.6	7.3	8.1	8.7
92.5°	7.8	7.2	6.6	6.0	5.3	5.4	6.1	6.8	7.4	8.1	8.7
95°	29.0	28.6	28.4	28.0	27.6	25.3	21.0	16.8	12.4	8.1	8.7
97.5°	60.5	61.2	61.8	62.3	63.0	59.0	50.6	42.0	33.5	25.1	21.8
100°	85.0	85.3	85.6	86.0	86.3	86.7	87.2	87.7	88.1	88.5	71.7
102.5°	109.8	110.2	110.7	111.1	111.5	111.8	112.1	112.4	112.7	113.0	109.8
105°	149.5	150.0	150.5	151.0	151.4	151.6	151.6	151.6	151.6	151.6	151.6
107.5°	190.9	190.9	190.9	190.9	190.9	191.0	191.2	191.5	191.7	191.9	191.9
110°	217.8	217.8	217.8	217.8	217.8	217.8	218.1	218.3	218.6	218.7	218.5



TEST NUMBER: P333499-940

CATALOG NUMBER: S125RDIP-S375D590U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	243.0	243.3	243.5	243.8	244.1	244.2	244.4	244.5	244.7	244.8	244.4
115°	280.8	281.4	282.0	282.5	283.1	283.5	283.6	283.7	283.7	283.9	283.5
117.5°	320.0	319.9	319.9	319.9	319.9	320.1	320.6	321.0	321.4	321.8	321.3
120°	344.5	344.3	344.2	344.1	343.9	344.1	344.5	344.7	345.1	345.4	345.2
122.5°	366.0	366.4	366.8	367.3	367.7	368.0	368.2	368.4	368.5	368.6	368.5
125°	399.4	400.2	400.9	401.7	402.5	403.0	403.0	403.0	403.0	403.0	402.5
127.5°	431.2	431.8	432.4	432.9	433.5	433.7	433.6	433.6	433.5	433.5	433.2
130°	450.8	451.3	451.9	452.5	453.0	453.3	453.4	453.6	453.7	453.8	453.4
132.5°	470.3	470.9	471.6	472.3	472.9	473.1	472.9	472.6	472.3	472.2	472.1
135°	498.1	498.7	499.4	500.1	500.8	501.1	500.8	500.5	500.3	500.1	499.9
137.5°	523.6	524.2	524.8	525.4	525.9	526.2	525.9	525.8	525.6	525.3	525.4
140°	540.3	540.6	540.7	541.0	541.2	541.3	541.2	541.0	540.9	540.8	541.0
142.5°	555.4	555.5	555.6	555.8	555.9	556.1	556.2	556.3	556.5	556.7	556.7
145°	577.5	577.7	577.9	578.1	578.4	578.5	578.5	578.5	578.5	578.5	578.5
147.5°	596.7	596.7	596.6	596.6	596.6	596.6	596.7	596.9	597.0	597.2	597.4
150°	608.9	608.8	608.5	608.3	608.1	608.1	608.3	608.5	608.8	608.9	609.2
152.5°	620.8	620.3	619.8	619.3	618.8	618.7	618.8	619.1	619.3	619.6	619.8
155°	636.0	635.3	634.6	633.9	633.2	633.0	633.2	633.5	633.6	633.9	634.3
157.5°	647.6	647.2	646.8	646.4	646.0	645.9	645.9	645.9	645.9	646.0	646.3
160°	655.8	655.1	654.4	653.7	653.1	652.8	652.9	653.0	653.1	653.3	653.7
162.5°	662.3	661.6	660.9	660.2	659.6	659.3	659.4	659.5	659.6	659.8	660.4
165°	671.0	670.4	669.7	669.1	668.3	668.1	668.2	668.2	668.4	668.5	669.1
167.5°	677.5	676.9	676.2	675.5	674.8	674.5	674.6	674.7	674.8	674.9	675.7
170°	681.3	680.5	679.7	678.9	678.1	677.7	677.8	678.0	678.1	678.1	679.0
172.5°	683.7	682.9	682.1	681.3	680.5	680.2	680.4	680.6	680.8	681.0	681.8
175°	686.3	685.6	684.9	684.3	683.6	683.3	683.4	683.6	683.7	683.8	684.7
177.5°	687.5	687.0	686.4	685.9	685.4	685.1	685.2	685.3	685.4	685.5	686.2
180°	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3



TEST NUMBER: P333499-940

CATALOG NUMBER: S125RDIP-S375D590U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6
2.5°	543.8	544.6	545.3	545.6	545.5	545.5	545.4	545.3
5°	540.5	541.4	542.2	542.7	542.5	542.2	542.1	541.9
7.5°	533.7	534.4	535.0	535.2	535.0	534.8	534.7	534.4
10°	528.1	528.3	528.6	528.6	528.3	528.1	527.8	527.5
12.5°	520.0	520.2	520.4	520.3	519.9	519.4	519.1	518.6
15°	506.7	506.6	506.5	506.0	505.2	504.4	503.6	502.7
17.5°	490.2	489.7	489.3	488.7	488.0	487.3	486.6	486.0
20°	478.0	477.5	477.1	476.4	475.5	474.7	473.9	473.1
22.5°	465.8	464.9	464.0	463.2	462.6	461.9	461.3	460.6
25°	446.0	444.8	443.6	442.6	441.5	440.5	439.5	438.5
27.5°	424.5	422.8	421.2	419.9	418.9	417.9	417.0	416.0
30°	409.1	407.1	404.9	403.5	402.6	401.8	401.0	400.2
32.5°	394.2	391.9	389.5	387.9	386.8	385.8	384.7	383.7
35°	371.0	368.3	365.6	363.6	362.4	361.1	359.8	358.6
37.5°	346.6	343.5	340.3	338.0	336.8	335.6	334.3	333.1
40°	330.6	327.1	323.6	321.3	320.2	319.1	318.0	316.9
42.5°	314.7	311.4	308.0	305.6	304.0	302.3	300.7	299.1
45°	289.4	285.7	282.0	279.6	278.2	276.8	275.4	274.0
47.5°	264.4	260.6	256.8	254.1	252.6	251.1	249.6	248.1
50°	247.4	243.5	239.7	237.1	235.8	234.3	233.0	231.6
52.5°	231.3	227.2	223.0	220.3	218.9	217.6	216.2	214.8
55°	206.9	202.8	198.7	195.8	194.4	192.9	191.5	190.0
57.5°	182.4	178.4	174.3	171.7	170.4	169.1	167.8	166.5
60°	166.3	162.2	158.2	155.5	154.1	152.8	151.4	150.0
62.5°	150.3	146.6	142.9	140.4	138.9	137.6	136.3	134.8
65°	127.0	123.3	119.7	117.2	115.8	114.4	113.1	111.6
67.5°	104.7	101.4	98.0	95.8	94.7	93.6	92.5	91.4
70°	90.0	87.1	84.3	82.3	81.1	80.1	79.0	77.8
72.5°	76.2	73.6	71.0	69.3	68.6	67.9	67.1	66.3
75°	57.0	54.9	53.0	51.6	51.0	50.3	49.7	49.0
77.5°	40.6	39.1	37.7	36.7	36.3	35.8	35.3	34.9
80°	30.5	29.7	28.9	28.4	28.2	28.0	27.8	27.6
82.5°	22.8	22.4	22.0	21.8	21.7	21.6	21.5	21.3
85°	13.0	12.9	12.8	12.8	12.7	12.6	12.5	12.4
87.5°	6.8	7.0	7.0	7.0	7.0	7.0	7.0	7.0
90°	9.3	9.8	10.4	10.9	11.2	11.5	11.9	12.2
92.5°	9.3	9.8	10.4	10.8	10.9	11.1	11.2	11.4
95°	9.3	9.8	10.4	10.7	10.7	10.7	10.7	10.7
97.5°	18.6	15.4	12.3	10.7	10.7	10.7	10.7	10.7
100°	54.8	38.0	21.1	12.5	12.0	11.6	11.1	10.7
102.5°	106.6	103.3	100.2	94.8	87.0	79.4	71.7	64.0
105°	151.6	151.6	151.6	151.6	151.4	151.3	151.2	151.1
107.5°	192.0	192.0	192.0	191.8	191.5	191.2	190.8	190.5
110°	218.1	217.8	217.4	217.3	217.4	217.5	217.7	217.8





TEST NUMBER: P333499-940

CATALOG NUMBER: S125RDIP-S375D590U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	244.0	243.5	243.1	242.8	242.6	242.5	242.4	242.2
115°	282.9	282.5	282.0	281.5	280.8	280.2	279.5	278.8
117.5°	320.7	320.0	319.5	319.1	318.8	318.4	318.2	317.9
120°	345.0	344.7	344.6	344.1	343.6	343.0	342.4	341.9
122.5°	368.2	368.0	367.7	367.3	366.7	366.0	365.3	364.7
125°	402.1	401.5	401.1	400.7	400.4	400.0	399.8	399.4
127.5°	432.9	432.7	432.5	431.9	431.1	430.3	429.4	428.6
130°	453.2	452.8	452.5	452.0	451.5	450.8	450.3	449.8
132.5°	472.0	471.9	471.9	471.5	471.0	470.4	469.8	469.3
135°	499.6	499.4	499.2	498.7	498.1	497.4	496.7	496.1
137.5°	525.4	525.5	525.5	525.2	524.7	524.1	523.5	522.9
140°	541.3	541.4	541.7	541.4	540.8	540.1	539.5	538.8
142.5°	556.8	556.8	556.9	556.5	555.9	555.2	554.5	553.8
145°	578.7	578.8	578.9	578.6	577.9	577.3	576.6	575.9
147.5°	597.4	597.6	597.7	597.4	596.6	595.8	594.9	594.1
150°	609.4	609.7	609.8	609.6	608.7	607.7	606.8	605.9
152.5°	620.0	620.3	620.5	620.2	619.4	618.6	617.7	616.9
155°	634.6	634.9	635.3	635.0	634.1	633.2	632.3	631.3
157.5°	646.7	647.0	647.4	647.1	646.2	645.2	644.4	643.5
160°	654.2	654.6	655.1	654.8	653.9	653.0	652.1	651.2
162.5°	661.0	661.6	662.3	662.1	661.1	660.1	659.2	658.1
165°	669.9	670.6	671.2	671.1	670.2	669.3	668.4	667.4
167.5°	676.5	677.3	678.1	678.1	677.1	676.0	675.0	674.0
170°	680.0	680.9	681.8	681.7	680.7	679.7	678.7	677.7
172.5°	682.6	683.5	684.3	684.2	683.1	682.2	681.1	680.1
175°	685.5	686.4	687.4	687.3	686.3	685.3	684.3	683.2
177.5°	686.8	687.4	688.0	688.0	687.2	686.5	685.8	685.1
180°	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3

(END OF REPORT)