

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333249

Luminaire Tested: **S125DIP-S850D1205U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333249
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D1205U835-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7741.2 lumens
Efficiency: N/A
Efficacy: 136.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333249

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333249

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44																			
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43	37																			
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	38	36	31																			
3	80	71	63	58	73	65	59	53	54	49	46	44	41	38	35	33	31	26																			
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22																			
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23	20																			
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20	17																			
7	57	45	37	31	52	41	34	29	35	30	26	29	25	22	23	20	18	15																			
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	14																			
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14	12																			
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8478	8478	8478
5°	8497	8416	8470
10°	8445	8357	8405
15°	8354	8256	8291
20°	8223	8115	8130
25°	8082	7948	7941
30°	7908	7768	7730
35°	7722	7574	7468
40°	7530	7363	7259
45°	7323	7172	7029
50°	7095	6939	6731
55°	6876	6677	6490
60°	6613	6412	6185
65°	6301	6094	5888
70°	6001	5727	5531
75°	5467	5288	5105
80°	4868	4790	4675
85°	4231	4313	4076



TEST NUMBER: P333249

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	1.6
10°-20°	349.6	4.5
20°-30°	516.2	6.7
30°-40°	602.4	7.8
40°-50°	605.0	7.8
50°-60°	531.1	6.9
60°-70°	395.7	5.1
70°-80°	226.3	2.9
80°-90°	69.0	0.9
90°-100°	417.8	5.4
100°-110°	898.0	11.6
110°-120°	842.8	10.9
120°-130°	683.0	8.8
130°-140°	548.1	7.1
140°-150°	413.6	5.3
150°-160°	291.2	3.8
160°-170°	171.6	2.2
170°-180°	55.8	0.7
0°-30°	989.7	12.8
0°-40°	1592.1	20.6
0°-60°	2728.2	35.2
0°-90°	3419.2	44.2
90°-120°	2158.6	27.9
90°-150°	3803.4	49.1
90°-180°	4322.0	55.8
0°-180°	7741.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1313	1313	1313	1313	1313	
5°	1311	1308	1298	1307	1306	124
15°	1249	1246	1235	1240	1240	352
25°	1134	1128	1115	1117	1114	522
35°	979	975	961	955	947	612
45°	802	797	785	773	770	618
55°	611	607	593	584	576	545
65°	412	410	399	390	385	409
75°	219	217	212	209	205	234
85°	57	58	58	57	55	64
90°	1	10	19	24	27	5
95°	38	113	1030	467	273	41
105°	131	184	842	1659	1540	138
115°	235	283	676	1458	1715	231
125°	325	381	648	1160	1351	289
135°	381	458	644	972	1122	296
145°	444	508	646	805	885	278
155°	507	545	630	712	742	233
165°	553	568	604	641	651	156
175°	575	575	580	587	584	55
180°	576	576	576	576	576	



TEST NUMBER: P333249

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1316.1	1315.5	1315.0	1314.4	1313.8	1312.6	1310.8	1309.0	1307.1	1305.3	1307.1
5°	1310.7	1310.2	1309.7	1309.3	1308.8	1307.4	1305.1	1302.8	1300.5	1298.2	1300.3
7.5°	1298.6	1298.2	1297.7	1297.2	1296.8	1295.3	1292.7	1290.2	1287.7	1285.1	1287.1
10°	1287.8	1287.4	1286.9	1286.4	1286.0	1284.5	1281.9	1279.4	1276.9	1274.3	1276.2
12.5°	1274.5	1273.7	1272.9	1272.0	1271.2	1269.6	1267.3	1264.9	1262.5	1260.2	1261.7
15°	1249.4	1248.7	1248.0	1247.3	1246.6	1245.0	1242.5	1239.9	1237.4	1234.8	1236.0
17.5°	1220.5	1219.5	1218.5	1217.5	1216.5	1214.6	1212.0	1209.4	1206.7	1204.1	1205.5
20°	1196.4	1196.0	1195.5	1195.0	1194.6	1192.8	1189.8	1186.8	1183.8	1180.8	1182.5
22.5°	1172.3	1171.5	1170.7	1169.8	1169.0	1167.2	1164.4	1161.5	1158.7	1155.9	1157.0
25°	1134.1	1133.0	1131.8	1130.6	1129.5	1127.4	1124.4	1121.4	1118.4	1115.4	1115.9
27.5°	1089.4	1088.8	1088.1	1087.4	1086.7	1084.8	1081.7	1078.6	1075.5	1072.4	1072.5
30°	1060.4	1059.7	1059.0	1058.3	1057.6	1055.5	1052.1	1048.6	1045.1	1041.7	1041.2
32.5°	1028.8	1027.7	1026.7	1025.6	1024.6	1022.5	1019.4	1016.3	1013.2	1010.1	1009.3
35°	979.4	978.4	977.5	976.6	975.7	973.6	970.4	967.1	963.9	960.7	959.5
37.5°	928.1	926.9	925.7	924.6	923.4	921.3	918.3	915.2	912.2	909.2	907.4
40°	893.2	892.0	890.9	889.7	888.5	886.4	883.1	879.9	876.7	873.4	871.4
42.5°	855.8	854.8	853.8	852.9	851.9	849.8	846.6	843.3	840.1	836.9	835.0
45°	801.8	800.8	799.9	799.0	798.1	796.2	793.5	790.7	787.9	785.2	782.4
47.5°	743.6	743.7	743.7	743.7	743.8	742.2	738.8	735.5	732.2	728.9	726.0
50°	706.2	705.5	704.8	704.1	703.5	701.7	699.0	696.2	693.4	690.6	687.6
52.5°	668.0	667.5	667.0	666.5	666.0	664.2	661.3	658.3	655.4	652.4	649.8
55°	610.7	610.0	609.3	608.6	607.9	605.9	602.7	599.5	596.2	593.0	590.9
57.5°	550.2	549.9	549.5	549.1	548.8	547.2	544.5	541.8	539.0	536.3	533.6
60°	512.0	511.1	510.2	509.2	508.3	506.6	504.0	501.5	499.0	496.4	494.1
62.5°	472.1	471.4	470.7	469.9	469.2	467.7	465.6	463.4	461.2	459.0	456.6
65°	412.3	411.8	411.4	410.9	410.5	409.0	406.4	403.9	401.3	398.8	396.7
67.5°	354.4	353.4	352.4	351.4	350.5	349.0	347.2	345.3	343.4	341.5	339.7
70°	317.8	316.6	315.5	314.3	313.2	311.6	309.5	307.4	305.3	303.3	301.9
72.5°	277.9	277.1	276.3	275.6	274.8	273.7	272.4	271.0	269.7	268.4	266.8
75°	219.1	218.7	218.2	217.8	217.3	216.5	215.3	214.2	213.0	211.9	211.2
77.5°	164.9	164.7	164.6	164.4	164.2	163.8	163.1	162.5	161.8	161.2	160.8
80°	130.9	130.9	130.9	130.9	130.9	130.6	130.2	129.7	129.2	128.8	128.6
82.5°	100.9	100.6	100.2	99.8	99.5	99.2	99.1	99.1	99.0	98.9	98.5
85°	57.1	57.4	57.6	57.8	58.0	58.2	58.2	58.2	58.2	58.2	57.9
87.5°	22.7	22.9	23.4	23.8	24.3	24.7	24.7	25.0	25.0	25.3	25.6
90°	1.2	2.3	4.6	7.0	9.3	11.6	12.8	15.1	16.3	18.6	19.8
92.5°	14.2	17.2	27.0	41.4	61.4	95.3	158.7	265.2	380.7	374.6	303.3
95°	38.3	39.5	48.8	61.6	87.1	139.4	263.8	519.4	840.1	1029.5	1007.4
97.5°	63.7	65.1	71.6	84.4	107.4	145.0	227.3	414.6	750.2	1099.4	1274.7
100°	81.3	83.7	88.3	101.1	123.2	158.0	225.4	376.5	669.3	1049.2	1339.7
102.5°	100.9	102.3	106.0	119.7	139.9	173.8	233.8	360.7	607.9	960.9	1300.7
105°	131.3	131.3	137.1	148.7	167.3	199.9	251.0	354.4	548.4	842.4	1175.9
107.5°	161.0	163.4	168.9	178.5	197.8	227.0	276.5	365.1	523.3	760.8	1048.6
110°	182.4	184.8	189.4	199.9	217.3	247.5	295.1	375.3	515.9	722.7	976.0



TEST NUMBER: P333249

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	203.8	206.1	209.8	220.3	237.7	267.0	312.8	388.3	515.9	700.4	922.1
115°	234.7	237.0	240.5	251.0	268.4	297.5	340.5	407.8	519.4	676.3	863.3
117.5°	262.6	266.1	269.8	280.3	300.0	328.1	368.8	430.2	527.1	664.4	828.2
120°	281.2	284.7	289.3	299.8	319.5	348.6	389.3	445.0	534.5	658.8	808.7
122.5°	300.7	303.3	307.0	317.4	339.1	368.1	408.8	461.8	541.0	654.2	792.0
125°	325.3	327.7	333.5	343.9	366.0	396.2	434.6	484.5	551.9	648.4	769.2
127.5°	344.6	348.1	355.6	368.8	392.3	422.5	459.4	505.5	564.2	645.6	748.3
130°	356.7	360.2	369.5	384.6	409.0	439.2	475.2	519.4	571.7	643.7	734.4
132.5°	366.0	370.4	381.6	398.6	423.9	454.1	490.1	531.5	580.0	643.7	723.2
135°	381.1	385.8	399.7	418.3	442.7	474.1	510.1	548.4	591.4	643.7	710.0
137.5°	400.2	403.7	416.7	435.3	459.2	491.5	524.3	561.0	601.9	645.1	698.1
140°	411.3	414.8	428.8	447.4	469.4	500.8	534.5	569.4	606.5	646.0	692.5
142.5°	424.3	426.9	439.9	458.5	479.7	509.2	541.0	574.0	609.3	647.0	687.9
145°	443.9	446.2	457.8	474.1	495.0	521.7	551.9	581.0	612.4	646.0	680.9
147.5°	464.3	465.7	475.7	490.8	508.9	532.4	558.9	585.2	613.5	643.0	673.7
150°	476.4	478.7	486.9	502.0	518.2	538.0	563.5	588.0	613.5	640.2	668.1
152.5°	489.4	490.8	498.0	511.3	526.6	544.5	568.2	589.8	612.6	636.5	661.6
155°	506.6	506.6	513.6	525.2	536.8	553.1	572.8	591.4	610.0	629.8	650.7
157.5°	522.0	521.7	527.3	537.3	547.5	559.8	576.8	592.6	607.0	622.8	640.5
160°	532.2	531.0	535.7	543.8	553.1	563.5	578.7	592.6	604.2	618.2	632.1
162.5°	540.5	539.4	544.0	551.2	558.7	567.3	580.5	591.7	601.4	612.6	624.7
165°	553.1	550.8	554.3	560.1	564.7	571.7	581.0	590.3	597.2	604.2	613.5
167.5°	561.5	560.3	562.4	565.6	568.9	573.3	581.0	587.5	590.7	596.1	602.6
170°	567.0	565.9	567.0	569.4	571.7	575.2	581.0	585.6	588.0	591.4	596.1
172.5°	570.8	568.7	569.8	572.1	573.5	575.2	580.0	583.8	584.2	585.9	589.6
175°	575.2	572.8	574.0	575.2	575.2	575.2	578.7	581.0	579.8	579.8	581.0
177.5°	577.3	575.4	575.4	576.3	575.4	575.4	577.3	578.2	576.3	576.3	577.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333249

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1309.0	1310.8	1312.6	1313.5	1313.3	1313.1	1312.9	1312.7
5°	1302.4	1304.4	1306.5	1307.4	1307.2	1307.0	1306.7	1306.5
7.5°	1289.2	1291.2	1293.2	1294.1	1293.9	1293.7	1293.4	1293.2
10°	1278.0	1279.9	1281.7	1282.5	1282.3	1282.0	1281.8	1281.6
12.5°	1263.1	1264.6	1266.1	1266.8	1266.8	1266.7	1266.7	1266.6
15°	1237.2	1238.3	1239.5	1240.0	1240.0	1240.0	1240.0	1240.0
17.5°	1207.0	1208.4	1209.8	1210.0	1208.8	1207.7	1206.5	1205.4
20°	1184.1	1185.7	1187.3	1187.5	1186.4	1185.2	1184.1	1182.9
22.5°	1158.0	1159.1	1160.2	1160.3	1159.5	1158.7	1157.9	1157.2
25°	1116.3	1116.8	1117.3	1117.1	1116.5	1115.8	1115.1	1114.4
27.5°	1072.6	1072.7	1072.8	1072.5	1071.8	1071.1	1070.4	1069.7
30°	1040.8	1040.3	1039.8	1039.3	1038.6	1037.9	1037.2	1036.5
32.5°	1008.4	1007.6	1006.8	1005.7	1004.5	1003.2	1002.0	1000.8
35°	958.4	957.2	956.1	954.6	952.7	950.9	949.0	947.2
37.5°	905.7	904.0	902.3	900.9	899.9	898.8	897.8	896.7
40°	869.3	867.2	865.1	863.7	863.0	862.4	861.7	861.0
42.5°	833.1	831.2	829.3	827.8	826.8	825.7	824.6	823.6
45°	779.6	776.8	774.1	772.3	771.7	771.0	770.3	769.6
47.5°	723.2	720.4	717.6	715.4	713.8	712.2	710.5	708.9
50°	684.6	681.6	678.6	676.3	674.7	673.1	671.5	669.9
52.5°	647.2	644.5	641.9	639.7	637.9	636.1	634.3	632.5
55°	588.9	586.8	584.7	582.9	581.2	579.6	578.0	576.4
57.5°	531.0	528.3	525.6	523.8	522.9	522.1	521.2	520.3
60°	491.8	489.5	487.2	485.2	483.6	482.0	480.4	478.8
62.5°	454.1	451.6	449.1	447.2	446.0	444.7	443.5	442.2
65°	394.7	392.6	390.5	389.0	388.1	387.2	386.2	385.3
67.5°	338.0	336.2	334.5	333.3	332.8	332.2	331.6	331.1
70°	300.5	299.1	297.7	296.6	295.6	294.7	293.8	292.9
72.5°	265.2	263.7	262.1	260.8	259.9	259.0	258.1	257.1
75°	210.5	209.8	209.1	208.3	207.4	206.4	205.5	204.6
77.5°	160.4	159.9	159.5	159.0	158.3	157.7	157.1	156.4
80°	128.3	128.1	127.9	127.5	127.1	126.6	126.1	125.7
82.5°	98.0	97.6	97.2	97.0	96.9	96.8	96.7	96.6
85°	57.7	57.5	57.2	56.9	56.4	56.0	55.5	55.0
87.5°	25.8	26.0	26.2	26.5	26.2	25.8	25.7	25.3
90°	20.9	22.1	23.2	25.6	25.6	25.6	26.7	26.7
92.5°	205.9	149.4	112.5	95.3	80.4	77.6	76.0	74.1
95°	835.4	658.8	515.9	418.3	335.8	300.9	291.7	273.1
97.5°	1244.2	1120.4	981.2	845.4	773.6	708.6	674.9	660.0
100°	1429.2	1372.3	1252.6	1131.7	1051.6	967.9	924.9	906.3
102.5°	1491.5	1526.6	1469.2	1387.4	1301.6	1242.1	1195.4	1181.5
105°	1454.8	1614.0	1665.1	1652.3	1615.1	1576.8	1553.5	1539.6
107.5°	1323.7	1536.1	1667.4	1728.1	1746.9	1746.7	1739.0	1729.7
110°	1227.0	1447.8	1611.6	1710.4	1762.7	1784.8	1792.9	1792.9



TEST NUMBER: P333249

CATALOG NUMBER: S125DIP-S850D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1150.8	1360.4	1526.1	1642.5	1719.0	1756.9	1777.1	1785.5
115°	1055.1	1235.2	1394.3	1521.0	1611.6	1667.4	1699.9	1715.0
117.5°	993.2	1148.5	1285.6	1401.8	1492.4	1550.1	1582.4	1591.6
120°	959.8	1099.2	1227.0	1329.3	1415.3	1471.0	1502.4	1511.7
122.5°	934.7	1063.9	1177.8	1273.5	1350.2	1401.3	1432.7	1441.1
125°	898.2	1016.7	1117.8	1201.5	1266.5	1314.2	1339.7	1351.4
127.5°	861.0	971.6	1066.0	1144.3	1203.3	1245.4	1269.6	1274.7
130°	837.8	940.0	1030.7	1106.2	1164.3	1202.6	1225.9	1232.8
132.5°	814.5	910.3	992.5	1065.3	1123.4	1161.7	1183.1	1191.0
135°	784.3	864.5	938.9	1005.1	1056.2	1094.6	1115.5	1122.5
137.5°	758.8	823.6	885.4	941.7	987.4	1022.3	1041.6	1049.2
140°	744.8	799.4	852.9	901.7	944.7	974.9	992.3	998.1
142.5°	732.7	779.0	825.0	867.3	903.8	929.3	945.8	950.7
145°	716.9	752.9	789.0	820.3	848.2	868.0	880.8	885.4
147.5°	702.1	731.3	759.0	782.7	804.8	820.6	828.0	830.1
150°	693.7	719.3	741.3	762.2	779.7	793.6	798.3	799.4
152.5°	684.4	707.2	727.4	743.7	758.3	769.4	774.1	775.3
155°	670.4	689.0	705.3	718.1	729.7	737.8	741.3	742.5
157.5°	656.5	671.8	684.4	694.4	703.4	710.2	713.4	713.2
160°	647.2	658.8	670.4	678.6	686.7	692.5	694.9	693.7
162.5°	637.0	647.7	657.4	664.6	670.9	675.8	676.3	676.0
165°	622.8	630.9	637.9	643.7	648.4	650.7	650.7	650.7
167.5°	609.3	614.7	620.0	624.2	626.5	628.6	627.7	627.5
170°	601.9	605.4	608.9	611.2	613.5	614.7	614.7	613.5
172.5°	593.5	597.0	599.6	601.0	601.4	603.5	601.7	600.5
175°	584.5	584.5	586.8	586.8	586.8	588.0	585.6	584.5
177.5°	578.2	579.1	579.1	579.1	578.2	579.1	576.3	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3

(END OF REPORT)