

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333548-940

Luminaire Tested: **S125RDIP-S610D1205U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333548-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D1205U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5837.6 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333548-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333548-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	86	79	73	68	78	72	67	63	58	55	52	46	44	41	34	33	31	26
3	79	70	63	57	71	64	57	53	52	47	44	41	38	35	30	29	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	25	22	24	21	18	19	16	14	12
9	49	37	29	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5794	5794	5794
5°	5806	5741	5776
10°	5762	5687	5687
15°	5695	5572	5526
20°	5606	5411	5346
25°	5504	5253	5137
30°	5376	5068	4906
35°	5245	4877	4647
40°	5123	4678	4392
45°	4975	4455	4116
50°	4827	4214	3826
55°	4654	3983	3518
60°	4481	3702	3185
65°	4276	3376	2806
70°	4043	2968	2417
75°	3721	2500	2011
80°	3277	1967	1689
85°	2764	1608	1504



TEST NUMBER: P333548-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.3	1.4
10°-20°	235.7	4.0
20°-30°	341.8	5.9
30°-40°	389.6	6.7
40°-50°	379.7	6.5
50°-60°	319.6	5.5
60°-70°	224.1	3.8
70°-80°	115.2	2.0
80°-90°	32.0	0.5
90°-100°	89.2	1.5
100°-110°	263.4	4.5
110°-120°	446.1	7.6
120°-130°	587.0	10.1
130°-140°	657.8	11.3
140°-150°	644.7	11.0
150°-160°	541.5	9.3
160°-170°	359.9	6.2
170°-180°	126.0	2.2
0°-30°	661.9	11.3
0°-40°	1051.5	18.0
0°-60°	1750.9	30.0
0°-90°	2122.1	36.4
90°-120°	798.6	13.7
90°-150°	2688.1	46.0
90°-180°	3716.0	63.7
0°-180°	5837.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	897	897	897	897	897	
5°	896	893	886	892	891	85
15°	852	847	833	832	826	240
25°	772	761	737	728	721	355
35°	665	648	619	600	589	416
45°	545	524	488	462	451	420
55°	413	391	354	324	312	370
65°	280	256	221	195	184	277
75°	149	128	100	86	81	158
85°	37	26	22	21	20	42
90°	1	9	17	22	25	5
95°	67	70	80	87	89	72
105°	236	242	248	254	257	252
115°	447	451	453	452	451	442
125°	652	658	659	657	656	584
135°	848	854	855	855	851	653
145°	1027	1031	1034	1034	1031	642
155°	1175	1175	1176	1180	1175	541
165°	1278	1276	1277	1280	1274	360
175°	1328	1324	1324	1330	1323	126
180°	1332	1332	1332	1332	1332	



TEST NUMBER: P333548-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	898.7	898.3	898.0	897.6	897.2	896.4	895.2	894.0	892.8	891.6	892.8
5°	895.6	895.1	894.5	893.9	893.2	892.2	890.5	888.9	887.2	885.5	887.0
7.5°	886.9	886.3	885.7	885.1	884.6	883.3	881.3	879.3	877.4	875.3	876.4
10°	878.7	878.2	877.8	877.4	876.9	875.7	873.5	871.5	869.3	867.2	867.6
12.5°	869.5	869.0	868.3	867.8	867.2	865.5	862.7	859.9	857.0	854.2	854.5
15°	851.7	850.7	849.8	848.9	848.0	846.0	842.8	839.6	836.5	833.3	833.2
17.5°	831.4	830.1	828.7	827.3	825.9	823.2	819.2	815.3	811.3	807.4	806.6
20°	815.7	814.2	812.7	811.2	809.7	806.6	801.7	796.9	792.1	787.3	786.5
22.5°	798.3	796.8	795.4	793.9	792.4	789.1	784.0	779.0	773.9	768.8	767.4
25°	772.4	770.1	767.9	765.6	763.3	759.4	753.9	748.2	742.7	737.1	735.2
27.5°	742.5	739.9	737.1	734.3	731.6	727.3	721.3	715.3	709.4	703.4	700.6
30°	720.9	718.0	715.2	712.3	709.4	704.8	698.5	692.2	685.9	679.6	676.1
32.5°	699.7	696.4	693.0	689.7	686.3	681.4	675.0	668.6	662.1	655.7	651.8
35°	665.3	661.7	658.1	654.5	650.9	645.7	638.9	632.1	625.4	618.6	614.2
37.5°	631.6	627.1	622.8	618.4	614.0	608.3	601.3	594.3	587.4	580.3	575.2
40°	607.7	603.2	598.7	594.1	589.7	583.8	576.6	569.4	562.1	554.9	549.2
42.5°	582.8	578.2	573.5	568.9	564.3	558.2	550.7	543.2	535.8	528.3	522.8
45°	544.7	540.4	536.0	531.6	527.3	520.9	512.6	504.4	496.1	487.8	481.8
47.5°	505.3	500.7	496.1	491.5	486.9	480.4	472.1	463.7	455.4	447.0	440.9
50°	480.4	475.4	470.4	465.5	460.5	453.7	445.1	436.6	427.9	419.4	413.0
52.5°	453.3	448.2	443.1	438.0	432.9	426.3	418.2	410.1	402.0	393.9	387.1
55°	413.3	408.5	403.7	398.9	394.0	387.4	379.0	370.5	362.1	353.7	346.9
57.5°	372.9	367.7	362.6	357.5	352.3	345.6	337.5	329.4	321.3	313.2	306.5
60°	346.9	341.6	336.4	331.1	325.8	319.1	310.9	302.8	294.7	286.6	280.0
62.5°	319.2	314.2	309.2	304.2	299.2	292.5	284.3	276.0	267.8	259.5	253.3
65°	279.8	274.7	269.6	264.5	259.3	252.8	244.8	236.8	228.8	220.9	214.8
67.5°	240.7	235.5	230.4	225.3	220.2	213.8	206.2	198.5	190.8	183.2	177.7
70°	214.1	209.0	203.8	198.8	193.6	187.3	179.8	172.3	164.7	157.2	152.5
72.5°	188.1	183.1	178.1	173.1	168.1	162.0	155.0	147.9	140.9	133.8	129.6
75°	149.1	144.5	140.0	135.5	131.0	125.6	119.2	112.9	106.6	100.2	96.9
77.5°	110.3	106.6	103.1	99.4	95.9	91.5	86.4	81.4	76.3	71.2	68.9
80°	88.1	84.4	80.9	77.2	73.7	69.7	65.5	61.3	57.1	52.9	51.5
82.5°	66.4	63.1	59.9	56.6	53.4	50.3	47.4	44.5	41.6	38.8	38.2
85°	37.3	34.5	31.8	29.2	26.4	24.7	23.9	23.2	22.5	21.7	21.5
87.5°	12.7	12.2	11.7	11.2	10.8	10.6	10.9	11.1	11.2	11.4	11.7
90°	1.1	2.9	4.7	6.6	8.4	10.2	11.8	13.4	15.0	16.6	17.7
92.5°	25.1	26.4	27.6	29.0	30.2	31.8	33.9	35.8	37.8	39.8	41.3
95°	67.3	67.8	68.3	68.8	69.2	70.5	72.9	75.2	77.5	79.8	81.4
97.5°	111.9	112.1	112.3	112.4	112.6	114.3	117.5	120.6	123.9	127.1	128.6
100°	145.1	145.1	145.1	145.1	145.1	146.6	149.5	152.6	155.5	158.5	160.6
102.5°	180.7	181.6	182.5	183.5	184.4	185.7	187.2	188.7	190.2	191.7	193.9
105°	236.2	237.4	238.5	239.7	240.9	242.1	243.5	244.9	246.3	247.6	249.1
107.5°	297.6	298.7	299.9	301.0	302.2	303.3	304.3	305.4	306.5	307.6	308.3
110°	339.9	341.0	342.1	343.3	344.5	345.4	346.1	346.8	347.5	348.1	348.8



TEST NUMBER: P333548-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	383.0	383.6	384.1	384.8	385.4	386.1	387.0	387.9	388.7	389.6	389.9
115°	446.6	447.5	448.4	449.3	450.3	450.9	451.5	451.9	452.4	452.8	452.6
117.5°	510.4	510.9	511.3	511.7	512.1	512.5	512.9	513.4	513.7	514.2	514.3
120°	550.2	551.3	552.5	553.7	554.8	555.5	555.7	556.0	556.2	556.4	556.4
122.5°	593.3	593.8	594.1	594.6	594.9	595.5	596.1	596.7	597.3	597.9	597.7
125°	651.8	653.2	654.5	655.9	657.3	658.1	658.4	658.5	658.8	659.1	658.5
127.5°	714.0	714.7	715.5	716.3	717.1	717.6	717.9	718.2	718.5	718.7	718.5
130°	751.3	752.4	753.6	754.7	755.8	756.7	757.2	757.6	758.0	758.5	758.3
132.5°	788.5	790.4	792.4	794.2	796.1	797.0	796.9	796.8	796.7	796.7	796.4
135°	847.7	849.0	850.4	851.8	853.2	854.0	854.2	854.4	854.6	854.9	854.9
137.5°	903.1	904.5	905.8	907.1	908.5	909.5	909.9	910.4	911.0	911.4	911.7
140°	938.8	940.0	941.1	942.3	943.4	944.3	945.0	945.7	946.4	947.1	947.5
142.5°	974.5	975.4	976.4	977.3	978.3	979.3	980.1	981.0	981.9	982.8	983.0
145°	1026.9	1027.8	1028.8	1029.7	1030.6	1031.4	1032.1	1032.8	1033.4	1034.1	1034.1
147.5°	1075.4	1075.8	1076.4	1076.9	1077.4	1077.9	1078.5	1079.1	1079.6	1080.1	1080.7
150°	1107.7	1107.5	1107.2	1107.1	1106.8	1107.1	1108.0	1108.9	1109.9	1110.8	1110.8
152.5°	1134.3	1134.5	1134.9	1135.2	1135.5	1135.9	1136.2	1136.6	1137.0	1137.4	1137.9
155°	1175.1	1175.1	1175.1	1175.1	1175.1	1175.2	1175.5	1175.6	1175.9	1176.1	1177.1
157.5°	1211.6	1211.0	1210.5	1210.1	1209.5	1209.3	1209.6	1209.9	1210.1	1210.3	1211.2
160°	1233.1	1232.4	1231.7	1231.0	1230.3	1230.1	1230.3	1230.6	1230.8	1231.0	1231.9
162.5°	1252.1	1251.7	1251.2	1250.6	1250.1	1249.9	1249.9	1250.0	1250.0	1250.1	1251.2
165°	1277.6	1277.2	1276.8	1276.3	1275.8	1275.7	1275.9	1276.1	1276.4	1276.6	1277.6
167.5°	1299.2	1298.2	1297.4	1296.5	1295.5	1295.0	1295.0	1295.0	1295.0	1295.0	1296.5
170°	1310.8	1309.9	1308.9	1308.1	1307.2	1306.6	1306.6	1306.6	1306.6	1306.6	1308.1
172.5°	1319.1	1318.2	1317.2	1316.3	1315.5	1314.9	1314.9	1314.9	1314.9	1314.9	1316.3
175°	1328.4	1327.5	1326.6	1325.6	1324.7	1324.3	1324.3	1324.3	1324.3	1324.3	1325.6
177.5°	1333.2	1332.5	1331.7	1331.0	1330.3	1329.8	1329.6	1329.5	1329.2	1329.0	1330.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333548-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	894.0	895.2	896.4	897.0	896.9	896.7	896.6	896.5
5°	888.5	890.0	891.5	892.2	891.8	891.5	891.3	890.9
7.5°	877.4	878.5	879.6	879.9	879.6	879.2	879.0	878.6
10°	868.1	868.5	869.1	869.1	868.5	868.1	867.6	867.2
12.5°	854.9	855.2	855.5	855.3	854.6	854.0	853.3	852.6
15°	833.0	832.9	832.8	832.0	830.6	829.3	828.0	826.5
17.5°	805.8	805.0	804.3	803.3	802.3	801.1	800.0	798.9
20°	785.8	785.0	784.3	783.2	781.9	780.5	779.2	777.8
22.5°	765.9	764.4	762.9	761.6	760.5	759.4	758.3	757.2
25°	733.3	731.3	729.3	727.5	725.9	724.2	722.6	720.9
27.5°	697.9	695.2	692.4	690.3	688.7	687.1	685.5	683.9
30°	672.6	669.1	665.7	663.3	661.9	660.6	659.2	657.9
32.5°	648.0	644.3	640.4	637.7	635.9	634.2	632.5	630.8
35°	609.8	605.5	601.1	597.9	595.8	593.6	591.6	589.4
37.5°	569.9	564.6	559.4	555.7	553.7	551.7	549.7	547.6
40°	543.4	537.7	532.0	528.2	526.5	524.6	522.8	521.0
42.5°	517.4	511.8	506.4	502.3	499.7	497.0	494.4	491.8
45°	475.7	469.8	463.7	459.6	457.4	455.0	452.8	450.6
47.5°	434.6	428.4	422.2	417.9	415.4	412.9	410.4	407.9
50°	406.7	400.4	394.0	389.8	387.5	385.3	383.0	380.8
52.5°	380.3	373.4	366.7	362.1	359.9	357.7	355.3	353.1
55°	340.1	333.3	326.5	322.0	319.6	317.2	314.8	312.4
57.5°	299.9	293.3	286.7	282.2	280.1	277.9	275.9	273.8
60°	273.3	266.7	260.1	255.7	253.4	251.1	248.9	246.6
62.5°	247.2	241.0	234.9	230.7	228.5	226.2	223.9	221.7
65°	208.8	202.8	196.8	192.6	190.4	188.2	185.8	183.6
67.5°	172.2	166.7	161.1	157.5	155.7	153.9	152.0	150.3
70°	147.8	143.2	138.5	135.3	133.5	131.7	129.8	128.0
72.5°	125.3	120.9	116.6	113.9	112.7	111.5	110.3	109.1
75°	93.6	90.3	87.0	84.8	83.8	82.8	81.7	80.6
77.5°	66.6	64.3	62.0	60.5	59.7	58.9	58.1	57.3
80°	50.1	48.8	47.4	46.6	46.3	46.0	45.7	45.4
82.5°	37.5	36.8	36.2	35.8	35.7	35.5	35.3	35.1
85°	21.4	21.2	21.0	21.0	20.8	20.6	20.5	20.3
87.5°	11.9	12.1	12.4	12.5	12.5	12.5	12.6	12.6
90°	18.9	20.1	21.2	22.1	22.8	23.5	24.2	24.9
92.5°	42.8	44.3	45.8	46.9	47.3	47.9	48.4	48.9
95°	83.0	84.6	86.2	87.3	87.7	88.2	88.6	89.1
97.5°	130.1	131.6	133.1	134.0	134.3	134.6	134.8	135.1
100°	162.6	164.8	166.8	168.1	168.5	169.0	169.5	170.0
102.5°	196.2	198.5	200.7	202.2	202.9	203.5	204.1	204.7
105°	250.4	251.8	253.2	254.2	254.9	255.6	256.3	257.0
107.5°	308.9	309.6	310.3	310.7	310.6	310.6	310.5	310.4
110°	349.6	350.3	350.9	351.2	350.9	350.7	350.4	350.3



TEST NUMBER: P333548-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	390.3	390.6	390.9	390.8	390.5	390.0	389.6	389.2
115°	452.4	452.1	451.9	451.7	451.5	451.2	450.9	450.8
117.5°	514.5	514.7	514.9	514.5	513.6	512.7	511.8	510.9
120°	556.4	556.4	556.4	556.0	555.1	554.1	553.2	552.3
122.5°	597.5	597.4	597.2	596.7	595.9	595.2	594.5	593.8
125°	658.1	657.6	657.2	656.8	656.7	656.4	656.1	655.9
127.5°	718.3	718.0	717.8	717.5	717.0	716.5	716.0	715.6
130°	758.0	757.8	757.6	757.2	756.8	756.3	755.8	755.4
132.5°	796.2	795.9	795.7	795.3	794.6	794.0	793.4	792.7
135°	854.9	854.9	854.9	854.4	853.5	852.6	851.7	850.7
137.5°	912.0	912.3	912.6	912.1	911.0	909.8	908.7	907.5
140°	948.0	948.5	949.0	948.6	947.4	946.3	945.1	944.0
142.5°	983.3	983.6	983.8	983.4	982.2	981.1	980.0	978.8
145°	1034.1	1034.1	1034.1	1033.8	1033.1	1032.4	1031.7	1031.0
147.5°	1081.3	1081.8	1082.4	1081.8	1080.3	1078.7	1077.2	1075.6
150°	1110.8	1110.8	1110.8	1110.6	1110.1	1109.6	1109.2	1108.8
152.5°	1138.4	1139.0	1139.5	1139.4	1138.6	1137.7	1136.9	1136.1
155°	1177.9	1178.8	1179.8	1179.6	1178.5	1177.3	1176.3	1175.1
157.5°	1212.1	1213.1	1214.0	1213.7	1212.2	1210.7	1209.2	1207.6
160°	1232.9	1233.8	1234.7	1234.6	1233.4	1232.3	1231.1	1230.0
162.5°	1252.3	1253.4	1254.5	1254.4	1253.0	1251.7	1250.4	1249.0
165°	1278.4	1279.3	1280.3	1280.1	1278.7	1277.3	1275.9	1274.5
167.5°	1297.8	1299.2	1300.6	1300.6	1299.1	1297.7	1296.3	1294.9
170°	1309.4	1310.8	1312.2	1312.1	1310.5	1308.9	1307.2	1305.6
172.5°	1317.7	1319.1	1320.4	1320.4	1319.0	1317.6	1316.2	1314.7
175°	1327.0	1328.4	1329.8	1329.7	1328.1	1326.5	1324.8	1323.2
177.5°	1331.2	1332.4	1333.5	1333.4	1332.1	1330.8	1329.5	1328.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5

(END OF REPORT)