

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333523-940

Luminaire Tested: **S125RDIP-S610D365U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333523-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D365U940-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3425.8 lumens  
Efficiency: N/A  
Efficacy: 124.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333523-940

CATALOG NUMBER: S125RDIP-S610D365U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333523-940

CATALOG NUMBER: S125RDIP-S610D365U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	96	93	89	94	90	87	84	79	77	75	69	67	66	60	58	57
2	92	85	78	73	86	79	74	69	70	66	62	61	58	55	53	51	49
3	84	75	67	61	78	70	64	58	62	57	53	54	50	47	47	44	42
4	77	66	58	52	72	62	55	50	55	50	45	48	44	40	42	39	36
5	71	59	51	45	66	56	48	43	50	44	39	44	39	35	38	35	32
6	65	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	32	28	25
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22
9	53	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5794	5794	5794
5°	5806	5741	5776
10°	5762	5687	5687
15°	5695	5572	5526
20°	5606	5411	5346
25°	5504	5253	5137
30°	5376	5068	4906
35°	5245	4877	4647
40°	5123	4678	4392
45°	4975	4455	4116
50°	4827	4214	3826
55°	4654	3983	3518
60°	4481	3702	3185
65°	4276	3376	2806
70°	4043	2968	2417
75°	3721	2500	2011
80°	3277	1967	1689
85°	2764	1608	1504



TEST NUMBER: P333523-940

CATALOG NUMBER: S125RDIP-S610D365U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.3	2.5
10°-20°	235.7	6.9
20°-30°	341.8	10.0
30°-40°	389.6	11.4
40°-50°	379.7	11.1
50°-60°	319.6	9.3
60°-70°	224.1	6.5
70°-80°	115.2	3.4
80°-90°	30.0	0.9
90°-100°	15.5	0.5
100°-110°	95.2	2.8
110°-120°	172.7	5.0
120°-130°	221.7	6.5
130°-140°	238.4	7.0
140°-150°	223.8	6.5
150°-160°	181.0	5.3
160°-170°	117.1	3.4
170°-180°	40.4	1.2
0°-30°	661.9	19.3
0°-40°	1051.5	30.7
0°-60°	1750.9	51.1
0°-90°	2120.1	61.9
90°-120°	283.4	8.3
90°-150°	967.3	28.2
90°-180°	1306.0	38.1
0°-180°	3425.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	897	897	897	897	897	
5°	896	893	886	892	891	85
15°	852	847	833	832	826	240
25°	772	761	737	728	721	355
35°	665	648	619	600	589	416
45°	545	524	488	462	451	420
55°	413	391	354	324	312	370
65°	280	256	221	195	184	277
75°	149	128	100	86	81	158
85°	37	26	22	21	20	42
90°	0	3	5	7	8	2
95°	18	16	5	6	7	23
105°	93	94	94	94	94	98
115°	174	176	176	175	173	172
125°	247	250	250	248	247	221
135°	309	310	310	309	307	238
145°	358	358	358	359	357	224
155°	394	392	393	394	391	181
165°	416	414	414	416	414	117
175°	425	424	424	426	423	40
180°	425	425	425	425	425	



TEST NUMBER: P333523-940

CATALOG NUMBER: S125RDIP-S610D365U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	898.7	898.3	898.0	897.6	897.2	896.4	895.2	894.0	892.8	891.6	892.8
5°	895.6	895.1	894.5	893.9	893.2	892.2	890.5	888.9	887.2	885.5	887.0
7.5°	886.9	886.3	885.7	885.1	884.6	883.3	881.3	879.3	877.4	875.3	876.4
10°	878.7	878.2	877.8	877.4	876.9	875.7	873.5	871.5	869.3	867.2	867.6
12.5°	869.5	869.0	868.3	867.8	867.2	865.5	862.7	859.9	857.0	854.2	854.5
15°	851.7	850.7	849.8	848.9	848.0	846.0	842.8	839.6	836.5	833.3	833.2
17.5°	831.4	830.1	828.7	827.3	825.9	823.2	819.2	815.3	811.3	807.4	806.6
20°	815.7	814.2	812.7	811.2	809.7	806.6	801.7	796.9	792.1	787.3	786.5
22.5°	798.3	796.8	795.4	793.9	792.4	789.1	784.0	779.0	773.9	768.8	767.4
25°	772.4	770.1	767.9	765.6	763.3	759.4	753.9	748.2	742.7	737.1	735.2
27.5°	742.5	739.9	737.1	734.3	731.6	727.3	721.3	715.3	709.4	703.4	700.6
30°	720.9	718.0	715.2	712.3	709.4	704.8	698.5	692.2	685.9	679.6	676.1
32.5°	699.7	696.4	693.0	689.7	686.3	681.4	675.0	668.6	662.1	655.7	651.8
35°	665.3	661.7	658.1	654.5	650.9	645.7	638.9	632.1	625.4	618.6	614.2
37.5°	631.6	627.1	622.8	618.4	614.0	608.3	601.3	594.3	587.4	580.3	575.2
40°	607.7	603.2	598.7	594.1	589.7	583.8	576.6	569.4	562.1	554.9	549.2
42.5°	582.8	578.2	573.5	568.9	564.3	558.2	550.7	543.2	535.8	528.3	522.8
45°	544.7	540.4	536.0	531.6	527.3	520.9	512.6	504.4	496.1	487.8	481.8
47.5°	505.3	500.7	496.1	491.5	486.9	480.4	472.1	463.7	455.4	447.0	440.9
50°	480.4	475.4	470.4	465.5	460.5	453.7	445.1	436.6	427.9	419.4	413.0
52.5°	453.3	448.2	443.1	438.0	432.9	426.3	418.2	410.1	402.0	393.9	387.1
55°	413.3	408.5	403.7	398.9	394.0	387.4	379.0	370.5	362.1	353.7	346.9
57.5°	372.9	367.7	362.6	357.5	352.3	345.6	337.5	329.4	321.3	313.2	306.5
60°	346.9	341.6	336.4	331.1	325.8	319.1	310.9	302.8	294.7	286.6	280.0
62.5°	319.2	314.2	309.2	304.2	299.2	292.5	284.3	276.0	267.8	259.5	253.3
65°	279.8	274.7	269.6	264.5	259.3	252.8	244.8	236.8	228.8	220.9	214.8
67.5°	240.7	235.5	230.4	225.3	220.2	213.8	206.2	198.5	190.8	183.2	177.7
70°	214.1	209.0	203.8	198.8	193.6	187.3	179.8	172.3	164.7	157.2	152.5
72.5°	188.1	183.1	178.1	173.1	168.1	162.0	155.0	147.9	140.9	133.8	129.6
75°	149.1	144.5	140.0	135.5	131.0	125.6	119.2	112.9	106.6	100.2	96.9
77.5°	110.3	106.6	103.1	99.4	95.9	91.5	86.4	81.4	76.3	71.2	68.9
80°	88.1	84.4	80.9	77.2	73.7	69.7	65.5	61.3	57.1	52.9	51.5
82.5°	66.4	63.1	59.9	56.6	53.4	50.3	47.4	44.5	41.6	38.8	38.2
85°	37.3	34.5	31.8	29.2	26.4	24.7	23.9	23.2	22.5	21.7	21.5
87.5°	12.6	11.8	11.1	10.3	9.6	9.2	9.2	9.2	9.2	9.1	9.2
90°	0.4	0.9	1.4	2.0	2.6	3.1	3.6	4.1	4.5	5.1	5.4
92.5°	4.8	4.5	4.1	3.7	3.3	3.3	3.7	4.2	4.6	5.1	5.4
95°	17.9	17.7	17.6	17.3	17.1	15.7	13.0	10.3	7.7	5.1	5.4
97.5°	37.5	37.9	38.3	38.6	39.1	36.6	31.3	26.0	20.8	15.5	13.6
100°	52.6	52.9	53.1	53.2	53.5	53.7	54.0	54.3	54.6	54.8	44.4
102.5°	68.0	68.3	68.6	68.8	69.1	69.3	69.5	69.6	69.8	70.0	68.0
105°	92.6	92.9	93.3	93.5	93.8	93.9	93.9	93.9	93.9	93.9	93.9
107.5°	118.2	118.2	118.2	118.2	118.2	118.3	118.5	118.6	118.8	118.9	118.9
110°	134.9	134.9	134.9	134.9	134.9	135.0	135.1	135.3	135.4	135.5	135.4



TEST NUMBER: P333523-940

CATALOG NUMBER: S125RDIP-S610D365U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	150.5	150.7	150.9	151.1	151.2	151.3	151.4	151.5	151.6	151.7	151.4
115°	174.0	174.3	174.7	175.0	175.4	175.6	175.7	175.8	175.8	175.8	175.6
117.5°	198.2	198.2	198.2	198.2	198.2	198.3	198.6	198.9	199.1	199.4	199.0
120°	213.4	213.3	213.3	213.2	213.1	213.2	213.4	213.6	213.8	214.0	213.9
122.5°	226.8	227.0	227.3	227.6	227.8	228.0	228.1	228.2	228.3	228.4	228.3
125°	247.4	247.9	248.4	248.9	249.4	249.7	249.7	249.7	249.7	249.7	249.3
127.5°	267.2	267.5	267.9	268.2	268.6	268.8	268.7	268.7	268.6	268.6	268.4
130°	279.3	279.6	280.0	280.4	280.7	280.9	281.0	281.0	281.1	281.2	281.0
132.5°	291.4	291.8	292.2	292.6	293.0	293.1	293.0	292.8	292.7	292.5	292.5
135°	308.6	309.0	309.4	309.9	310.2	310.4	310.2	310.1	310.0	309.9	309.7
137.5°	324.4	324.8	325.1	325.5	325.8	326.0	325.8	325.7	325.6	325.5	325.5
140°	334.7	334.9	335.0	335.2	335.3	335.4	335.3	335.2	335.1	335.1	335.2
142.5°	344.1	344.2	344.3	344.3	344.4	344.5	344.6	344.7	344.8	344.9	344.9
145°	357.8	357.9	358.0	358.2	358.3	358.4	358.4	358.4	358.4	358.4	358.5
147.5°	369.7	369.7	369.7	369.6	369.6	369.6	369.7	369.8	369.9	370.0	370.1
150°	377.3	377.2	377.0	376.8	376.7	376.7	376.8	377.0	377.2	377.3	377.5
152.5°	384.6	384.3	384.0	383.7	383.3	383.3	383.4	383.6	383.7	383.9	384.0
155°	394.0	393.6	393.2	392.7	392.4	392.2	392.4	392.4	392.6	392.7	393.0
157.5°	401.3	401.0	400.7	400.5	400.3	400.1	400.1	400.2	400.2	400.2	400.4
160°	406.3	405.9	405.5	405.0	404.7	404.5	404.5	404.6	404.7	404.7	405.0
162.5°	410.4	409.9	409.5	409.0	408.7	408.5	408.6	408.6	408.7	408.8	409.1
165°	415.7	415.4	414.9	414.5	414.1	413.9	413.9	414.0	414.1	414.2	414.6
167.5°	419.8	419.4	418.9	418.5	418.0	417.9	417.9	418.0	418.1	418.1	418.7
170°	422.0	421.6	421.1	420.6	420.1	419.9	420.0	420.0	420.1	420.2	420.7
172.5°	423.6	423.1	422.6	422.1	421.6	421.4	421.5	421.7	421.8	422.0	422.4
175°	425.2	424.8	424.4	423.9	423.6	423.4	423.4	423.5	423.6	423.7	424.2
177.5°	426.0	425.6	425.3	425.0	424.6	424.5	424.5	424.6	424.6	424.7	425.1
180°	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2



TEST NUMBER: P333523-940

CATALOG NUMBER: S125RDIP-S610D365U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	894.0	895.2	896.4	897.0	896.9	896.7	896.6	896.5
5°	888.5	890.0	891.5	892.2	891.8	891.5	891.3	890.9
7.5°	877.4	878.5	879.6	879.9	879.6	879.2	879.0	878.6
10°	868.1	868.5	869.1	869.1	868.5	868.1	867.6	867.2
12.5°	854.9	855.2	855.5	855.3	854.6	854.0	853.3	852.6
15°	833.0	832.9	832.8	832.0	830.6	829.3	828.0	826.5
17.5°	805.8	805.0	804.3	803.3	802.3	801.1	800.0	798.9
20°	785.8	785.0	784.3	783.2	781.9	780.5	779.2	777.8
22.5°	765.9	764.4	762.9	761.6	760.5	759.4	758.3	757.2
25°	733.3	731.3	729.3	727.5	725.9	724.2	722.6	720.9
27.5°	697.9	695.2	692.4	690.3	688.7	687.1	685.5	683.9
30°	672.6	669.1	665.7	663.3	661.9	660.6	659.2	657.9
32.5°	648.0	644.3	640.4	637.7	635.9	634.2	632.5	630.8
35°	609.8	605.5	601.1	597.9	595.8	593.6	591.6	589.4
37.5°	569.9	564.6	559.4	555.7	553.7	551.7	549.7	547.6
40°	543.4	537.7	532.0	528.2	526.5	524.6	522.8	521.0
42.5°	517.4	511.8	506.4	502.3	499.7	497.0	494.4	491.8
45°	475.7	469.8	463.7	459.6	457.4	455.0	452.8	450.6
47.5°	434.6	428.4	422.2	417.9	415.4	412.9	410.4	407.9
50°	406.7	400.4	394.0	389.8	387.5	385.3	383.0	380.8
52.5°	380.3	373.4	366.7	362.1	359.9	357.7	355.3	353.1
55°	340.1	333.3	326.5	322.0	319.6	317.2	314.8	312.4
57.5°	299.9	293.3	286.7	282.2	280.1	277.9	275.9	273.8
60°	273.3	266.7	260.1	255.7	253.4	251.1	248.9	246.6
62.5°	247.2	241.0	234.9	230.7	228.5	226.2	223.9	221.7
65°	208.8	202.8	196.8	192.6	190.4	188.2	185.8	183.6
67.5°	172.2	166.7	161.1	157.5	155.7	153.9	152.0	150.3
70°	147.8	143.2	138.5	135.3	133.5	131.7	129.8	128.0
72.5°	125.3	120.9	116.6	113.9	112.7	111.5	110.3	109.1
75°	93.6	90.3	87.0	84.8	83.8	82.8	81.7	80.6
77.5°	66.6	64.3	62.0	60.5	59.7	58.9	58.1	57.3
80°	50.1	48.8	47.4	46.6	46.3	46.0	45.7	45.4
82.5°	37.5	36.8	36.2	35.8	35.7	35.5	35.3	35.1
85°	21.4	21.2	21.0	21.0	20.8	20.6	20.5	20.3
87.5°	9.3	9.4	9.5	9.5	9.4	9.3	9.2	9.1
90°	5.7	6.1	6.4	6.7	7.0	7.1	7.3	7.6
92.5°	5.7	6.1	6.4	6.7	6.8	6.9	7.0	7.0
95°	5.7	6.1	6.4	6.6	6.6	6.6	6.6	6.6
97.5°	11.6	9.5	7.6	6.6	6.6	6.6	6.6	6.6
100°	34.0	23.5	13.1	7.8	7.5	7.2	6.9	6.6
102.5°	66.0	64.0	62.1	58.7	53.9	49.2	44.4	39.7
105°	93.9	93.9	93.9	93.9	93.8	93.7	93.7	93.6
107.5°	119.0	119.0	119.0	118.9	118.7	118.4	118.2	118.0
110°	135.1	134.9	134.7	134.6	134.7	134.7	134.8	134.9





TEST NUMBER: P333523-940

CATALOG NUMBER: S125RDIP-S610D365U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	151.1	150.9	150.6	150.4	150.3	150.3	150.2	150.1
115°	175.3	175.0	174.8	174.4	174.0	173.6	173.2	172.7
117.5°	198.7	198.3	198.0	197.7	197.5	197.3	197.2	197.0
120°	213.7	213.6	213.5	213.2	212.9	212.5	212.1	211.8
122.5°	228.1	228.0	227.8	227.6	227.1	226.8	226.3	226.0
125°	249.1	248.8	248.5	248.3	248.1	247.9	247.6	247.4
127.5°	268.2	268.0	268.0	267.6	267.1	266.5	266.1	265.6
130°	280.7	280.5	280.4	280.0	279.7	279.4	279.0	278.7
132.5°	292.4	292.4	292.3	292.1	291.8	291.4	291.1	290.8
135°	309.6	309.4	309.2	309.0	308.6	308.2	307.7	307.3
137.5°	325.6	325.6	325.6	325.4	325.0	324.7	324.3	324.0
140°	335.4	335.5	335.6	335.5	335.1	334.7	334.2	333.8
142.5°	344.9	345.0	345.0	344.8	344.4	343.9	343.6	343.1
145°	358.6	358.6	358.6	358.5	358.1	357.7	357.2	356.8
147.5°	370.1	370.2	370.3	370.1	369.6	369.1	368.6	368.1
150°	377.6	377.7	377.8	377.6	377.1	376.6	375.9	375.4
152.5°	384.1	384.2	384.4	384.2	383.7	383.3	382.7	382.2
155°	393.2	393.3	393.6	393.4	392.9	392.3	391.7	391.2
157.5°	400.6	400.8	401.1	400.9	400.4	399.8	399.2	398.7
160°	405.3	405.6	405.8	405.7	405.1	404.6	404.0	403.5
162.5°	409.6	409.9	410.4	410.2	409.6	408.9	408.4	407.8
165°	415.0	415.4	415.9	415.8	415.3	414.6	414.1	413.6
167.5°	419.2	419.6	420.2	420.1	419.5	418.8	418.2	417.6
170°	421.2	421.9	422.4	422.4	421.8	421.2	420.4	419.8
172.5°	422.9	423.5	423.9	423.9	423.3	422.6	422.0	421.3
175°	424.7	425.3	425.9	425.9	425.2	424.5	423.9	423.3
177.5°	425.5	425.9	426.2	426.2	425.8	425.3	424.9	424.5
180°	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2

(END OF REPORT)