

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333524-940

Luminaire Tested: **S125RDIP-S610D365U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333524-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D365U940-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3250.2 lumens  
Efficiency: N/A  
Efficacy: 118.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333524-940

CATALOG NUMBER: S125RDIP-S610D365U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333524-940

CATALOG NUMBER: S125RDIP-S610D365U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	102	97	93	90	95	92	88	85	81	78	76	71	69	68	62	61	60	56
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	79	71	64	59	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	63	56	50	56	51	46	50	46	42	44	41	38	35
5	71	60	51	45	67	57	49	44	51	45	40	45	40	36	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	36	31	53	42	35	30	38	32	28	34	29	26	31	27	23	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5794	5794	5794
5°	5806	5741	5776
10°	5762	5687	5687
15°	5695	5572	5526
20°	5606	5411	5346
25°	5504	5253	5137
30°	5376	5068	4906
35°	5245	4877	4647
40°	5123	4678	4392
45°	4975	4455	4116
50°	4827	4214	3826
55°	4654	3983	3518
60°	4481	3702	3185
65°	4276	3376	2806
70°	4043	2968	2417
75°	3721	2500	2011
80°	3277	1967	1689
85°	2764	1608	1504



TEST NUMBER: P333524-940

CATALOG NUMBER: S125RDIP-S610D365U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.3	2.6
10°-20°	235.7	7.3
20°-30°	341.8	10.5
30°-40°	389.6	12.0
40°-50°	379.7	11.7
50°-60°	319.6	9.8
60°-70°	224.1	6.9
70°-80°	115.2	3.5
80°-90°	30.0	0.9
90°-100°	27.1	0.8
100°-110°	80.1	2.5
110°-120°	135.7	4.2
120°-130°	178.6	5.5
130°-140°	200.1	6.2
140°-150°	196.1	6.0
150°-160°	164.7	5.1
160°-170°	109.5	3.4
170°-180°	38.3	1.2
0°-30°	661.9	20.4
0°-40°	1051.5	32.4
0°-60°	1750.9	53.9
0°-90°	2120.1	65.2
90°-120°	242.9	7.5
90°-150°	817.6	25.2
90°-180°	1130.0	34.8
0°-180°	3250.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	897	897	897	897	897	
5°	896	893	886	892	891	85
15°	852	847	833	832	826	240
25°	772	761	737	728	721	355
35°	665	648	619	600	589	416
45°	545	524	488	462	451	420
55°	413	391	354	324	312	370
65°	280	256	221	195	184	277
75°	149	128	100	86	81	158
85°	37	26	22	21	20	42
90°	0	3	5	7	8	3
95°	20	21	24	26	27	22
105°	72	74	75	77	78	77
115°	136	137	138	137	137	134
125°	198	200	200	200	200	177
135°	258	260	260	260	259	199
145°	312	314	314	314	314	195
155°	357	357	358	359	357	165
165°	389	388	388	389	388	110
175°	404	403	403	404	402	38
180°	405	405	405	405	405	



TEST NUMBER: P333524-940

CATALOG NUMBER: S125RDIP-S610D365U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	898.7	898.3	898.0	897.6	897.2	896.4	895.2	894.0	892.8	891.6	892.8
5°	895.6	895.1	894.5	893.9	893.2	892.2	890.5	888.9	887.2	885.5	887.0
7.5°	886.9	886.3	885.7	885.1	884.6	883.3	881.3	879.3	877.4	875.3	876.4
10°	878.7	878.2	877.8	877.4	876.9	875.7	873.5	871.5	869.3	867.2	867.6
12.5°	869.5	869.0	868.3	867.8	867.2	865.5	862.7	859.9	857.0	854.2	854.5
15°	851.7	850.7	849.8	848.9	848.0	846.0	842.8	839.6	836.5	833.3	833.2
17.5°	831.4	830.1	828.7	827.3	825.9	823.2	819.2	815.3	811.3	807.4	806.6
20°	815.7	814.2	812.7	811.2	809.7	806.6	801.7	796.9	792.1	787.3	786.5
22.5°	798.3	796.8	795.4	793.9	792.4	789.1	784.0	779.0	773.9	768.8	767.4
25°	772.4	770.1	767.9	765.6	763.3	759.4	753.9	748.2	742.7	737.1	735.2
27.5°	742.5	739.9	737.1	734.3	731.6	727.3	721.3	715.3	709.4	703.4	700.6
30°	720.9	718.0	715.2	712.3	709.4	704.8	698.5	692.2	685.9	679.6	676.1
32.5°	699.7	696.4	693.0	689.7	686.3	681.4	675.0	668.6	662.1	655.7	651.8
35°	665.3	661.7	658.1	654.5	650.9	645.7	638.9	632.1	625.4	618.6	614.2
37.5°	631.6	627.1	622.8	618.4	614.0	608.3	601.3	594.3	587.4	580.3	575.2
40°	607.7	603.2	598.7	594.1	589.7	583.8	576.6	569.4	562.1	554.9	549.2
42.5°	582.8	578.2	573.5	568.9	564.3	558.2	550.7	543.2	535.8	528.3	522.8
45°	544.7	540.4	536.0	531.6	527.3	520.9	512.6	504.4	496.1	487.8	481.8
47.5°	505.3	500.7	496.1	491.5	486.9	480.4	472.1	463.7	455.4	447.0	440.9
50°	480.4	475.4	470.4	465.5	460.5	453.7	445.1	436.6	427.9	419.4	413.0
52.5°	453.3	448.2	443.1	438.0	432.9	426.3	418.2	410.1	402.0	393.9	387.1
55°	413.3	408.5	403.7	398.9	394.0	387.4	379.0	370.5	362.1	353.7	346.9
57.5°	372.9	367.7	362.6	357.5	352.3	345.6	337.5	329.4	321.3	313.2	306.5
60°	346.9	341.6	336.4	331.1	325.8	319.1	310.9	302.8	294.7	286.6	280.0
62.5°	319.2	314.2	309.2	304.2	299.2	292.5	284.3	276.0	267.8	259.5	253.3
65°	279.8	274.7	269.6	264.5	259.3	252.8	244.8	236.8	228.8	220.9	214.8
67.5°	240.7	235.5	230.4	225.3	220.2	213.8	206.2	198.5	190.8	183.2	177.7
70°	214.1	209.0	203.8	198.8	193.6	187.3	179.8	172.3	164.7	157.2	152.5
72.5°	188.1	183.1	178.1	173.1	168.1	162.0	155.0	147.9	140.9	133.8	129.6
75°	149.1	144.5	140.0	135.5	131.0	125.6	119.2	112.9	106.6	100.2	96.9
77.5°	110.3	106.6	103.1	99.4	95.9	91.5	86.4	81.4	76.3	71.2	68.9
80°	88.1	84.4	80.9	77.2	73.7	69.7	65.5	61.3	57.1	52.9	51.5
82.5°	66.4	63.1	59.9	56.6	53.4	50.3	47.4	44.5	41.6	38.8	38.2
85°	37.3	34.5	31.8	29.2	26.4	24.7	23.9	23.2	22.5	21.7	21.5
87.5°	12.6	11.8	11.1	10.3	9.6	9.2	9.2	9.2	9.2	9.1	9.2
90°	0.4	0.9	1.4	2.0	2.6	3.1	3.6	4.1	4.5	5.1	5.4
92.5°	7.7	8.0	8.4	8.8	9.2	9.7	10.3	10.9	11.5	12.1	12.6
95°	20.5	20.6	20.8	20.9	21.0	21.5	22.2	22.8	23.5	24.3	24.8
97.5°	34.1	34.1	34.2	34.2	34.2	34.8	35.8	36.7	37.6	38.6	39.1
100°	44.1	44.1	44.1	44.1	44.1	44.6	45.5	46.4	47.3	48.2	48.9
102.5°	54.9	55.3	55.6	55.8	56.1	56.4	56.9	57.3	57.9	58.3	59.0
105°	71.9	72.2	72.6	72.9	73.3	73.7	74.1	74.5	74.9	75.3	75.7
107.5°	90.5	90.9	91.2	91.6	91.9	92.3	92.6	92.9	93.2	93.5	93.7
110°	103.3	103.7	104.1	104.4	104.8	105.0	105.2	105.5	105.7	105.9	106.1



TEST NUMBER: P333524-940

CATALOG NUMBER: S125RDIP-S610D365U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	116.5	116.6	116.8	117.0	117.2	117.4	117.7	118.0	118.2	118.5	118.6
115°	135.8	136.1	136.4	136.7	137.0	137.1	137.3	137.4	137.6	137.8	137.7
117.5°	155.2	155.3	155.5	155.6	155.8	155.9	156.0	156.1	156.2	156.4	156.4
120°	167.4	167.7	168.1	168.4	168.7	169.0	169.1	169.1	169.2	169.2	169.2
122.5°	180.5	180.6	180.7	180.8	180.9	181.1	181.3	181.5	181.6	181.8	181.8
125°	198.2	198.7	199.1	199.5	199.9	200.2	200.3	200.3	200.4	200.5	200.3
127.5°	217.1	217.4	217.7	217.8	218.1	218.3	218.4	218.5	218.6	218.6	218.6
130°	228.5	228.8	229.2	229.5	229.9	230.2	230.2	230.4	230.6	230.7	230.6
132.5°	239.9	240.4	241.0	241.6	242.1	242.5	242.4	242.4	242.4	242.3	242.2
135°	257.8	258.2	258.7	259.0	259.5	259.8	259.8	259.8	259.9	260.0	260.0
137.5°	274.7	275.1	275.5	275.9	276.3	276.6	276.8	276.9	277.1	277.2	277.3
140°	285.5	285.9	286.2	286.6	287.0	287.2	287.4	287.7	287.8	288.0	288.2
142.5°	296.4	296.7	296.9	297.3	297.6	297.8	298.1	298.4	298.6	298.9	299.0
145°	312.4	312.6	312.9	313.2	313.4	313.7	313.9	314.1	314.3	314.5	314.5
147.5°	327.1	327.3	327.3	327.5	327.7	327.9	328.1	328.2	328.3	328.5	328.7
150°	336.9	336.9	336.8	336.7	336.6	336.7	337.0	337.3	337.6	337.9	337.9
152.5°	345.0	345.1	345.2	345.3	345.4	345.4	345.6	345.7	345.8	345.9	346.1
155°	357.4	357.4	357.4	357.4	357.4	357.4	357.5	357.6	357.7	357.8	358.0
157.5°	368.5	368.4	368.2	368.0	367.9	367.8	367.9	368.0	368.0	368.1	368.4
160°	375.1	374.9	374.6	374.4	374.3	374.2	374.3	374.3	374.3	374.4	374.7
162.5°	380.8	380.7	380.6	380.4	380.2	380.1	380.1	380.2	380.2	380.2	380.6
165°	388.6	388.4	388.3	388.2	388.1	388.0	388.1	388.2	388.3	388.3	388.6
167.5°	395.1	394.8	394.6	394.3	394.0	393.9	393.9	393.9	393.9	393.9	394.3
170°	398.7	398.4	398.1	397.9	397.5	397.4	397.4	397.4	397.4	397.4	397.9
172.5°	401.2	400.9	400.6	400.4	400.1	399.9	399.9	399.9	399.9	399.9	400.4
175°	404.0	403.8	403.5	403.2	403.0	402.8	402.8	402.8	402.8	402.8	403.2
177.5°	405.5	405.3	405.0	404.8	404.6	404.5	404.4	404.4	404.3	404.2	404.6
180°	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0



TEST NUMBER: P333524-940

CATALOG NUMBER: S125RDIP-S610D365U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	894.0	895.2	896.4	897.0	896.9	896.7	896.6	896.5
5°	888.5	890.0	891.5	892.2	891.8	891.5	891.3	890.9
7.5°	877.4	878.5	879.6	879.9	879.6	879.2	879.0	878.6
10°	868.1	868.5	869.1	869.1	868.5	868.1	867.6	867.2
12.5°	854.9	855.2	855.5	855.3	854.6	854.0	853.3	852.6
15°	833.0	832.9	832.8	832.0	830.6	829.3	828.0	826.5
17.5°	805.8	805.0	804.3	803.3	802.3	801.1	800.0	798.9
20°	785.8	785.0	784.3	783.2	781.9	780.5	779.2	777.8
22.5°	765.9	764.4	762.9	761.6	760.5	759.4	758.3	757.2
25°	733.3	731.3	729.3	727.5	725.9	724.2	722.6	720.9
27.5°	697.9	695.2	692.4	690.3	688.7	687.1	685.5	683.9
30°	672.6	669.1	665.7	663.3	661.9	660.6	659.2	657.9
32.5°	648.0	644.3	640.4	637.7	635.9	634.2	632.5	630.8
35°	609.8	605.5	601.1	597.9	595.8	593.6	591.6	589.4
37.5°	569.9	564.6	559.4	555.7	553.7	551.7	549.7	547.6
40°	543.4	537.7	532.0	528.2	526.5	524.6	522.8	521.0
42.5°	517.4	511.8	506.4	502.3	499.7	497.0	494.4	491.8
45°	475.7	469.8	463.7	459.6	457.4	455.0	452.8	450.6
47.5°	434.6	428.4	422.2	417.9	415.4	412.9	410.4	407.9
50°	406.7	400.4	394.0	389.8	387.5	385.3	383.0	380.8
52.5°	380.3	373.4	366.7	362.1	359.9	357.7	355.3	353.1
55°	340.1	333.3	326.5	322.0	319.6	317.2	314.8	312.4
57.5°	299.9	293.3	286.7	282.2	280.1	277.9	275.9	273.8
60°	273.3	266.7	260.1	255.7	253.4	251.1	248.9	246.6
62.5°	247.2	241.0	234.9	230.7	228.5	226.2	223.9	221.7
65°	208.8	202.8	196.8	192.6	190.4	188.2	185.8	183.6
67.5°	172.2	166.7	161.1	157.5	155.7	153.9	152.0	150.3
70°	147.8	143.2	138.5	135.3	133.5	131.7	129.8	128.0
72.5°	125.3	120.9	116.6	113.9	112.7	111.5	110.3	109.1
75°	93.6	90.3	87.0	84.8	83.8	82.8	81.7	80.6
77.5°	66.6	64.3	62.0	60.5	59.7	58.9	58.1	57.3
80°	50.1	48.8	47.4	46.6	46.3	46.0	45.7	45.4
82.5°	37.5	36.8	36.2	35.8	35.7	35.5	35.3	35.1
85°	21.4	21.2	21.0	21.0	20.8	20.6	20.5	20.3
87.5°	9.3	9.4	9.5	9.5	9.4	9.3	9.2	9.1
90°	5.7	6.1	6.4	6.7	7.0	7.1	7.3	7.6
92.5°	13.0	13.5	13.9	14.3	14.4	14.5	14.7	14.9
95°	25.2	25.8	26.2	26.6	26.7	26.8	26.9	27.1
97.5°	39.6	40.0	40.5	40.8	40.8	40.9	41.0	41.1
100°	49.5	50.1	50.7	51.1	51.3	51.5	51.5	51.7
102.5°	59.7	60.4	61.1	61.5	61.7	61.9	62.1	62.2
105°	76.2	76.6	77.0	77.3	77.5	77.8	77.9	78.2
107.5°	94.0	94.2	94.3	94.5	94.4	94.4	94.4	94.4
110°	106.3	106.6	106.7	106.8	106.7	106.6	106.6	106.6





TEST NUMBER: P333524-940

CATALOG NUMBER: S125RDIP-S610D365U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	118.7	118.8	118.9	118.9	118.8	118.6	118.5	118.4
115°	137.6	137.5	137.4	137.4	137.3	137.2	137.1	137.1
117.5°	156.5	156.6	156.6	156.5	156.2	156.0	155.7	155.3
120°	169.2	169.2	169.2	169.1	168.8	168.5	168.3	168.0
122.5°	181.7	181.6	181.6	181.5	181.3	181.0	180.8	180.6
125°	200.2	200.0	199.9	199.7	199.7	199.7	199.6	199.5
127.5°	218.5	218.4	218.3	218.2	218.1	217.9	217.8	217.7
130°	230.6	230.5	230.4	230.3	230.2	230.1	229.9	229.8
132.5°	242.2	242.1	242.0	241.9	241.7	241.5	241.3	241.1
135°	260.0	260.0	260.0	259.8	259.6	259.3	259.0	258.8
137.5°	277.4	277.5	277.6	277.4	277.1	276.7	276.3	276.0
140°	288.4	288.5	288.6	288.6	288.2	287.8	287.5	287.1
142.5°	299.1	299.2	299.3	299.1	298.7	298.4	298.1	297.7
145°	314.5	314.5	314.5	314.4	314.2	314.0	313.8	313.6
147.5°	328.9	329.0	329.2	329.0	328.6	328.1	327.6	327.2
150°	337.9	337.9	337.9	337.8	337.7	337.5	337.3	337.2
152.5°	346.3	346.4	346.6	346.5	346.3	346.1	345.8	345.5
155°	358.3	358.6	358.8	358.8	358.5	358.1	357.8	357.4
157.5°	368.6	369.0	369.3	369.2	368.7	368.2	367.7	367.3
160°	375.0	375.2	375.5	375.5	375.1	374.8	374.4	374.1
162.5°	380.8	381.2	381.6	381.6	381.1	380.7	380.3	379.9
165°	388.9	389.1	389.4	389.3	388.9	388.5	388.1	387.6
167.5°	394.8	395.1	395.6	395.6	395.1	394.7	394.2	393.9
170°	398.2	398.7	399.1	399.0	398.6	398.1	397.6	397.1
172.5°	400.8	401.2	401.6	401.6	401.2	400.7	400.3	399.8
175°	403.6	404.0	404.5	404.4	403.9	403.4	403.0	402.4
177.5°	404.9	405.3	405.6	405.6	405.2	404.7	404.4	403.9
180°	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0

(END OF REPORT)