

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333229

Luminaire Tested: **S125DIP-S850D810U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333229
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D810U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6657.9 lumens
Efficiency: N/A
Efficacy: 145.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333229

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333229

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43
2	89	82	76	70	82	76	70	66	64	60	57	54	51	49	44	42	41	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	35	30
4	74	64	56	50	68	59	52	47	50	45	41	43	38	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	40	35	38	34	30	32	28	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	30	25	46	36	29	24	31	25	21	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8478	8478	8478
5°	8497	8416	8470
10°	8445	8357	8405
15°	8354	8256	8291
20°	8223	8115	8130
25°	8082	7948	7941
30°	7908	7768	7730
35°	7722	7574	7468
40°	7530	7363	7259
45°	7323	7172	7029
50°	7095	6939	6731
55°	6876	6677	6490
60°	6613	6412	6185
65°	6301	6094	5888
70°	6001	5727	5531
75°	5467	5288	5105
80°	4868	4790	4675
85°	4231	4313	4076



TEST NUMBER: P333229

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	1.9
10°-20°	349.6	5.3
20°-30°	516.2	7.8
30°-40°	602.4	9.0
40°-50°	605.0	9.1
50°-60°	531.1	8.0
60°-70°	395.7	5.9
70°-80°	226.3	3.4
80°-90°	68.0	1.0
90°-100°	38.3	0.6
100°-110°	236.3	3.5
110°-120°	428.5	6.4
120°-130°	550.0	8.3
130°-140°	591.5	8.9
140°-150°	555.2	8.3
150°-160°	449.1	6.7
160°-170°	290.5	4.4
170°-180°	100.2	1.5
0°-30°	989.7	14.9
0°-40°	1592.1	23.9
0°-60°	2728.2	41.0
0°-90°	3418.2	51.3
90°-120°	703.1	10.6
90°-150°	2399.9	36.0
90°-180°	3240.0	48.7
0°-180°	6657.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1313	1313	1313	1313	1313	
5°	1311	1308	1298	1307	1306	124
15°	1249	1246	1235	1240	1240	352
25°	1134	1128	1115	1117	1114	522
35°	979	975	961	955	947	612
45°	802	797	785	773	770	618
55°	611	607	593	584	576	545
65°	412	410	399	390	385	409
75°	219	217	212	209	205	234
85°	57	58	58	57	55	64
90°	1	7	12	16	19	5
95°	45	41	12	16	16	57
105°	230	233	233	233	232	244
115°	432	435	436	433	429	428
125°	614	619	619	616	614	548
135°	766	770	769	767	762	590
145°	888	889	889	890	885	555
155°	978	973	974	976	970	450
165°	1032	1027	1028	1032	1026	291
175°	1055	1051	1051	1057	1050	100
180°	1055	1055	1055	1055	1055	



TEST NUMBER: P333229

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1316.1	1315.5	1315.0	1314.4	1313.8	1312.6	1310.8	1309.0	1307.1	1305.3	1307.1
5°	1310.7	1310.2	1309.7	1309.3	1308.8	1307.4	1305.1	1302.8	1300.5	1298.2	1300.3
7.5°	1298.6	1298.2	1297.7	1297.2	1296.8	1295.3	1292.7	1290.2	1287.7	1285.1	1287.1
10°	1287.8	1287.4	1286.9	1286.4	1286.0	1284.5	1281.9	1279.4	1276.9	1274.3	1276.2
12.5°	1274.5	1273.7	1272.9	1272.0	1271.2	1269.6	1267.3	1264.9	1262.5	1260.2	1261.7
15°	1249.4	1248.7	1248.0	1247.3	1246.6	1245.0	1242.5	1239.9	1237.4	1234.8	1236.0
17.5°	1220.5	1219.5	1218.5	1217.5	1216.5	1214.6	1212.0	1209.4	1206.7	1204.1	1205.5
20°	1196.4	1196.0	1195.5	1195.0	1194.6	1192.8	1189.8	1186.8	1183.8	1180.8	1182.5
22.5°	1172.3	1171.5	1170.7	1169.8	1169.0	1167.2	1164.4	1161.5	1158.7	1155.9	1157.0
25°	1134.1	1133.0	1131.8	1130.6	1129.5	1127.4	1124.4	1121.4	1118.4	1115.4	1115.9
27.5°	1089.4	1088.8	1088.1	1087.4	1086.7	1084.8	1081.7	1078.6	1075.5	1072.4	1072.5
30°	1060.4	1059.7	1059.0	1058.3	1057.6	1055.5	1052.1	1048.6	1045.1	1041.7	1041.2
32.5°	1028.8	1027.7	1026.7	1025.6	1024.6	1022.5	1019.4	1016.3	1013.2	1010.1	1009.3
35°	979.4	978.4	977.5	976.6	975.7	973.6	970.4	967.1	963.9	960.7	959.5
37.5°	928.1	926.9	925.7	924.6	923.4	921.3	918.3	915.2	912.2	909.2	907.4
40°	893.2	892.0	890.9	889.7	888.5	886.4	883.1	879.9	876.7	873.4	871.4
42.5°	855.8	854.8	853.8	852.9	851.9	849.8	846.6	843.3	840.1	836.9	835.0
45°	801.8	800.8	799.9	799.0	798.1	796.2	793.5	790.7	787.9	785.2	782.4
47.5°	743.6	743.7	743.7	743.7	743.8	742.2	738.8	735.5	732.2	728.9	726.0
50°	706.2	705.5	704.8	704.1	703.5	701.7	699.0	696.2	693.4	690.6	687.6
52.5°	668.0	667.5	667.0	666.5	666.0	664.2	661.3	658.3	655.4	652.4	649.8
55°	610.7	610.0	609.3	608.6	607.9	605.9	602.7	599.5	596.2	593.0	590.9
57.5°	550.2	549.9	549.5	549.1	548.8	547.2	544.5	541.8	539.0	536.3	533.6
60°	512.0	511.1	510.2	509.2	508.3	506.6	504.0	501.5	499.0	496.4	494.1
62.5°	472.1	471.4	470.7	469.9	469.2	467.7	465.6	463.4	461.2	459.0	456.6
65°	412.3	411.8	411.4	410.9	410.5	409.0	406.4	403.9	401.3	398.8	396.7
67.5°	354.4	353.4	352.4	351.4	350.5	349.0	347.2	345.3	343.4	341.5	339.7
70°	317.8	316.6	315.5	314.3	313.2	311.6	309.5	307.4	305.3	303.3	301.9
72.5°	277.9	277.1	276.3	275.6	274.8	273.7	272.4	271.0	269.7	268.4	266.8
75°	219.1	218.7	218.2	217.8	217.3	216.5	215.3	214.2	213.0	211.9	211.2
77.5°	164.9	164.7	164.6	164.4	164.2	163.8	163.1	162.5	161.8	161.2	160.8
80°	130.9	130.9	130.9	130.9	130.9	130.6	130.2	129.7	129.2	128.8	128.6
82.5°	100.9	100.6	100.2	99.8	99.5	99.2	99.1	99.1	99.0	98.9	98.5
85°	57.1	57.4	57.6	57.8	58.0	58.2	58.2	58.2	58.2	58.2	57.9
87.5°	22.6	22.9	23.1	23.4	23.7	23.9	23.9	24.0	24.0	24.1	24.3
90°	0.8	2.2	3.6	5.0	6.3	7.6	8.9	10.1	11.3	12.5	13.4
92.5°	12.0	11.1	10.1	9.1	8.2	8.2	9.3	10.4	11.4	12.5	13.4
95°	44.6	44.1	43.5	43.0	42.5	38.9	32.3	25.7	19.1	12.5	13.4
97.5°	93.1	94.0	94.9	95.9	96.8	90.8	77.7	64.6	51.5	38.5	33.6
100°	130.6	131.1	131.6	132.2	132.7	133.3	134.0	134.7	135.4	136.1	110.2
102.5°	168.8	169.4	170.1	170.7	171.4	171.9	172.4	172.8	173.2	173.6	168.7
105°	229.9	230.6	231.3	232.0	232.7	233.0	233.0	233.0	233.0	233.0	233.0
107.5°	293.4	293.4	293.4	293.4	293.4	293.6	293.9	294.3	294.6	295.0	295.0
110°	334.7	334.7	334.7	334.7	334.7	334.9	335.2	335.6	335.9	336.3	335.8



TEST NUMBER: P333229

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	373.5	373.9	374.3	374.8	375.2	375.5	375.7	375.9	376.1	376.3	375.7
115°	431.7	432.6	433.4	434.3	435.2	435.7	435.9	436.0	436.2	436.4	435.7
117.5°	491.9	491.9	491.8	491.8	491.8	492.1	492.7	493.4	494.1	494.7	493.8
120°	529.4	529.3	529.1	528.9	528.7	528.9	529.4	530.0	530.5	531.0	530.7
122.5°	562.6	563.3	563.9	564.6	565.2	565.7	565.9	566.2	566.4	566.7	566.3
125°	613.9	615.1	616.3	617.6	618.8	619.4	619.4	619.4	619.4	619.4	618.7
127.5°	662.9	663.7	664.6	665.5	666.3	666.7	666.6	666.5	666.4	666.3	665.9
130°	692.9	693.8	694.6	695.5	696.4	696.9	697.1	697.2	697.4	697.6	697.1
132.5°	722.9	723.9	724.9	725.9	727.0	727.3	726.9	726.5	726.1	725.7	725.6
135°	765.6	766.7	767.7	768.8	769.8	770.1	769.8	769.4	769.1	768.8	768.4
137.5°	804.9	805.8	806.7	807.6	808.5	808.8	808.5	808.2	807.9	807.5	807.6
140°	830.5	830.9	831.2	831.6	831.9	832.0	831.8	831.7	831.5	831.3	831.7
142.5°	853.7	853.9	854.1	854.3	854.5	854.7	855.0	855.2	855.5	855.7	855.8
145°	887.6	888.0	888.3	888.7	889.0	889.2	889.2	889.2	889.2	889.2	889.4
147.5°	917.3	917.3	917.2	917.1	917.1	917.1	917.3	917.5	917.8	918.0	918.2
150°	936.1	935.8	935.4	935.1	934.7	934.7	935.1	935.4	935.8	936.1	936.5
152.5°	954.3	953.5	952.7	952.0	951.2	951.0	951.3	951.7	952.0	952.4	952.7
155°	977.6	976.5	975.5	974.4	973.4	973.0	973.4	973.7	974.1	974.4	974.9
157.5°	995.5	994.9	994.3	993.7	993.0	992.7	992.8	992.8	992.8	992.9	993.4
160°	1008.1	1007.0	1006.0	1004.9	1003.9	1003.5	1003.6	1003.8	1004.0	1004.1	1004.8
162.5°	1018.1	1017.0	1016.0	1014.9	1013.9	1013.5	1013.6	1013.8	1014.0	1014.2	1015.1
165°	1031.5	1030.5	1029.4	1028.4	1027.3	1026.9	1027.1	1027.3	1027.4	1027.6	1028.7
167.5°	1041.5	1040.5	1039.4	1038.3	1037.2	1036.8	1036.9	1037.1	1037.3	1037.5	1038.7
170°	1047.2	1045.9	1044.7	1043.5	1042.3	1041.8	1041.9	1042.1	1042.3	1042.5	1043.9
172.5°	1050.9	1049.7	1048.5	1047.3	1046.0	1045.6	1045.9	1046.2	1046.5	1046.8	1048.1
175°	1055.0	1053.9	1052.9	1051.9	1050.8	1050.4	1050.5	1050.7	1050.9	1051.1	1052.5
177.5°	1056.9	1056.0	1055.2	1054.4	1053.5	1053.2	1053.3	1053.4	1053.6	1053.7	1054.7
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333229

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1309.0	1310.8	1312.6	1313.5	1313.3	1313.1	1312.9	1312.7
5°	1302.4	1304.4	1306.5	1307.4	1307.2	1307.0	1306.7	1306.5
7.5°	1289.2	1291.2	1293.2	1294.1	1293.9	1293.7	1293.4	1293.2
10°	1278.0	1279.9	1281.7	1282.5	1282.3	1282.0	1281.8	1281.6
12.5°	1263.1	1264.6	1266.1	1266.8	1266.8	1266.7	1266.7	1266.6
15°	1237.2	1238.3	1239.5	1240.0	1240.0	1240.0	1240.0	1240.0
17.5°	1207.0	1208.4	1209.8	1210.0	1208.8	1207.7	1206.5	1205.4
20°	1184.1	1185.7	1187.3	1187.5	1186.4	1185.2	1184.1	1182.9
22.5°	1158.0	1159.1	1160.2	1160.3	1159.5	1158.7	1157.9	1157.2
25°	1116.3	1116.8	1117.3	1117.1	1116.5	1115.8	1115.1	1114.4
27.5°	1072.6	1072.7	1072.8	1072.5	1071.8	1071.1	1070.4	1069.7
30°	1040.8	1040.3	1039.8	1039.3	1038.6	1037.9	1037.2	1036.5
32.5°	1008.4	1007.6	1006.8	1005.7	1004.5	1003.2	1002.0	1000.8
35°	958.4	957.2	956.1	954.6	952.7	950.9	949.0	947.2
37.5°	905.7	904.0	902.3	900.9	899.9	898.8	897.8	896.7
40°	869.3	867.2	865.1	863.7	863.0	862.4	861.7	861.0
42.5°	833.1	831.2	829.3	827.8	826.8	825.7	824.6	823.6
45°	779.6	776.8	774.1	772.3	771.7	771.0	770.3	769.6
47.5°	723.2	720.4	717.6	715.4	713.8	712.2	710.5	708.9
50°	684.6	681.6	678.6	676.3	674.7	673.1	671.5	669.9
52.5°	647.2	644.5	641.9	639.7	637.9	636.1	634.3	632.5
55°	588.9	586.8	584.7	582.9	581.2	579.6	578.0	576.4
57.5°	531.0	528.3	525.6	523.8	522.9	522.1	521.2	520.3
60°	491.8	489.5	487.2	485.2	483.6	482.0	480.4	478.8
62.5°	454.1	451.6	449.1	447.2	446.0	444.7	443.5	442.2
65°	394.7	392.6	390.5	389.0	388.1	387.2	386.2	385.3
67.5°	338.0	336.2	334.5	333.3	332.8	332.2	331.6	331.1
70°	300.5	299.1	297.7	296.6	295.6	294.7	293.8	292.9
72.5°	265.2	263.7	262.1	260.8	259.9	259.0	258.1	257.1
75°	210.5	209.8	209.1	208.3	207.4	206.4	205.5	204.6
77.5°	160.4	159.9	159.5	159.0	158.3	157.7	157.1	156.4
80°	128.3	128.1	127.9	127.5	127.1	126.6	126.1	125.7
82.5°	98.0	97.6	97.2	97.0	96.9	96.8	96.7	96.6
85°	57.7	57.5	57.2	56.9	56.4	56.0	55.5	55.0
87.5°	24.5	24.6	24.8	24.8	24.5	24.2	24.0	23.7
90°	14.3	15.1	16.0	16.7	17.2	17.7	18.2	18.8
92.5°	14.3	15.1	16.0	16.5	16.8	17.0	17.3	17.5
95°	14.3	15.1	16.0	16.4	16.4	16.4	16.4	16.4
97.5°	28.7	23.8	18.9	16.4	16.4	16.4	16.4	16.4
100°	84.3	58.4	32.5	19.2	18.5	17.8	17.1	16.4
102.5°	163.8	158.9	154.0	145.7	133.8	122.0	110.2	98.4
105°	233.0	233.0	233.0	233.0	232.8	232.6	232.4	232.3
107.5°	295.1	295.1	295.1	294.9	294.4	293.8	293.3	292.8
110°	335.2	334.7	334.2	334.0	334.2	334.4	334.5	334.7



TEST NUMBER: P333229

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	375.0	374.3	373.7	373.2	373.0	372.7	372.5	372.3
115°	435.0	434.3	433.6	432.7	431.7	430.6	429.6	428.6
117.5°	492.9	492.0	491.1	490.4	490.0	489.5	489.1	488.6
120°	530.3	530.0	529.6	529.0	528.1	527.3	526.4	525.5
122.5°	566.0	565.6	565.3	564.6	563.6	562.6	561.6	560.6
125°	618.0	617.3	616.6	616.0	615.5	614.9	614.4	613.9
127.5°	665.5	665.2	664.8	663.9	662.7	661.4	660.1	658.8
130°	696.5	696.0	695.5	694.8	693.9	693.1	692.2	691.3
132.5°	725.5	725.4	725.3	724.8	724.0	723.1	722.2	721.4
135°	768.1	767.7	767.4	766.7	765.6	764.6	763.5	762.5
137.5°	807.7	807.7	807.8	807.4	806.5	805.6	804.7	803.8
140°	832.0	832.4	832.7	832.4	831.3	830.3	829.2	828.2
142.5°	855.9	855.9	856.0	855.5	854.5	853.4	852.4	851.3
145°	889.5	889.7	889.9	889.4	888.4	887.4	886.3	885.3
147.5°	918.4	918.6	918.8	918.3	917.0	915.8	914.5	913.3
150°	936.8	937.2	937.5	937.0	935.6	934.2	932.8	931.4
152.5°	953.1	953.4	953.8	953.3	952.1	950.8	949.6	948.3
155°	975.5	976.0	976.5	976.1	974.7	973.3	971.9	970.5
157.5°	994.0	994.6	995.1	994.7	993.3	991.9	990.5	989.1
160°	1005.5	1006.2	1006.9	1006.6	1005.2	1003.8	1002.4	1001.0
162.5°	1016.1	1017.1	1018.0	1017.8	1016.2	1014.7	1013.2	1011.7
165°	1029.7	1030.7	1031.8	1031.6	1030.2	1028.8	1027.4	1026.0
167.5°	1040.0	1041.2	1042.5	1042.3	1040.7	1039.2	1037.6	1036.1
170°	1045.2	1046.6	1048.0	1047.9	1046.4	1044.8	1043.2	1041.7
172.5°	1049.3	1050.6	1051.9	1051.7	1050.1	1048.6	1047.0	1045.4
175°	1053.8	1055.2	1056.6	1056.5	1055.0	1053.4	1051.9	1050.3
177.5°	1055.7	1056.6	1057.6	1057.6	1056.4	1055.3	1054.2	1053.1
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0

(END OF REPORT)