

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333555-940

Luminaire Tested: **S125RDIP-S850D365U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333555-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D365U940-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4069.8 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333555-940

CATALOG NUMBER: S125RDIP-S850D365U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333555-940

CATALOG NUMBER: S125RDIP-S850D365U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	99	95	91	97	93	90	87	84	81	79	75	73	72	67	66	65	61
2	94	86	80	75	89	82	77	72	74	70	66	67	63	60	60	57	55	51
3	86	76	69	63	81	73	66	60	66	60	56	59	55	51	53	50	47	44
4	79	68	60	54	74	65	57	52	59	53	48	53	48	44	48	44	41	38
5	73	61	52	46	68	58	50	45	53	46	42	48	43	39	43	39	36	33
6	67	55	46	40	63	52	45	39	48	41	37	43	38	34	39	35	32	29
7	62	50	41	36	59	47	40	35	43	37	32	39	34	30	36	32	28	26
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25	23
9	54	41	34	29	51	40	33	28	36	30	26	33	28	25	31	26	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7919	7919	7919
5°	7937	7847	7895
10°	7877	7774	7774
15°	7783	7616	7554
20°	7663	7396	7307
25°	7524	7180	7021
30°	7348	6927	6706
35°	7171	6666	6352
40°	7003	6395	6004
45°	6801	6090	5624
50°	6597	5760	5230
55°	6361	5443	4808
60°	6124	5059	4354
65°	5845	4614	3834
70°	5527	4056	3305
75°	5085	3421	2750
80°	4478	2685	2310
85°	3772	2193	2060



TEST NUMBER: P333555-940

CATALOG NUMBER: S125RDIP-S850D365U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.3	2.8
10°-20°	322.2	7.9
20°-30°	467.2	11.5
30°-40°	532.5	13.1
40°-50°	519.1	12.8
50°-60°	436.9	10.7
60°-70°	306.3	7.5
70°-80°	157.4	3.9
80°-90°	40.6	1.0
90°-100°	113.3	2.8
100°-110°	243.6	6.0
110°-120°	228.6	5.6
120°-130°	185.2	4.6
130°-140°	148.7	3.7
140°-150°	112.2	2.8
150°-160°	79.0	1.9
160°-170°	46.5	1.1
170°-180°	15.1	0.4
0°-30°	904.7	22.2
0°-40°	1437.3	35.3
0°-60°	2393.2	58.8
0°-90°	2897.6	71.2
90°-120°	585.4	14.4
90°-150°	1031.5	25.3
90°-180°	1172.0	28.8
0°-180°	4069.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1226	1226	1226	1226	1226	
5°	1224	1220	1210	1219	1218	116
15°	1164	1158	1139	1138	1130	328
25°	1056	1041	1008	996	985	486
35°	910	886	846	819	806	569
45°	745	716	667	631	616	574
55°	565	534	483	443	427	505
65°	382	350	302	266	251	379
75°	204	175	137	118	110	216
85°	51	35	30	29	28	57
90°	0	3	5	7	7	3
95°	10	31	279	127	74	11
105°	36	50	228	450	418	38
115°	64	77	183	395	465	63
125°	88	103	176	314	366	78
135°	103	124	175	264	304	80
145°	120	138	175	218	240	75
155°	137	148	171	193	201	63
165°	150	154	164	174	176	42
175°	156	156	157	159	158	15
180°	156	156	156	156	156	



TEST NUMBER: P333555-940

CATALOG NUMBER: S125RDIP-S850D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2
2.5°	1228.3	1227.9	1227.4	1226.9	1226.4	1225.3	1223.7	1222.0	1220.4	1218.7	1220.4
5°	1224.3	1223.5	1222.6	1221.8	1221.0	1219.5	1217.2	1215.0	1212.6	1210.4	1212.5
7.5°	1212.3	1211.5	1210.7	1209.9	1209.2	1207.4	1204.7	1201.9	1199.3	1196.5	1197.9
10°	1201.1	1200.5	1199.9	1199.3	1198.6	1196.9	1194.1	1191.1	1188.3	1185.4	1186.0
12.5°	1188.6	1187.8	1187.0	1186.2	1185.4	1183.1	1179.2	1175.4	1171.5	1167.6	1168.1
15°	1164.1	1162.9	1161.6	1160.4	1159.1	1156.4	1152.1	1147.7	1143.4	1139.1	1138.9
17.5°	1136.5	1134.6	1132.7	1130.9	1128.9	1125.2	1119.8	1114.4	1108.9	1103.5	1102.5
20°	1115.0	1112.9	1110.9	1108.8	1106.8	1102.4	1095.9	1089.3	1082.7	1076.1	1075.1
22.5°	1091.3	1089.2	1087.2	1085.1	1083.1	1078.6	1071.7	1064.8	1057.8	1051.0	1048.9
25°	1055.8	1052.7	1049.5	1046.5	1043.4	1038.0	1030.5	1022.8	1015.2	1007.6	1005.0
27.5°	1015.0	1011.3	1007.5	1003.8	1000.1	994.1	986.0	977.8	969.6	961.4	957.7
30°	985.3	981.4	977.6	973.7	969.7	963.4	954.8	946.2	937.5	928.9	924.2
32.5°	956.4	951.9	947.4	942.8	938.2	931.5	922.7	913.9	905.1	896.3	891.1
35°	909.5	904.5	899.6	894.6	889.7	882.5	873.3	864.1	854.8	845.5	839.5
37.5°	863.3	857.3	851.3	845.3	839.3	831.5	822.0	812.3	802.8	793.3	786.1
40°	830.7	824.6	818.3	812.2	806.0	798.0	788.1	778.2	768.4	758.5	750.6
42.5°	796.7	790.3	784.0	777.6	771.2	763.0	752.8	742.6	732.4	722.2	714.7
45°	744.6	738.6	732.6	726.7	720.7	712.0	700.7	689.5	678.1	666.8	658.5
47.5°	690.7	684.4	678.1	671.8	665.5	656.7	645.2	633.8	622.4	611.0	602.5
50°	656.6	649.8	643.0	636.2	629.5	620.2	608.4	596.7	585.0	573.3	564.6
52.5°	619.6	612.6	605.6	598.7	591.7	582.7	571.7	560.6	549.5	538.4	529.1
55°	564.9	558.3	551.8	545.2	538.6	529.5	518.0	506.5	495.0	483.4	474.1
57.5°	509.7	502.7	495.6	488.6	481.6	472.5	461.4	450.2	439.2	428.0	419.0
60°	474.1	467.0	459.8	452.5	445.3	436.2	425.1	413.9	402.9	391.7	382.7
62.5°	436.4	429.5	422.7	415.7	408.8	399.8	388.5	377.3	366.0	354.7	346.3
65°	382.5	375.5	368.5	361.5	354.5	345.5	334.7	323.7	312.8	301.9	293.6
67.5°	329.0	321.9	315.0	308.0	301.0	292.2	281.8	271.3	260.9	250.4	242.9
70°	292.7	285.6	278.7	271.6	264.7	256.0	245.8	235.4	225.2	214.8	208.5
72.5°	257.1	250.2	243.4	236.6	229.8	221.5	211.9	202.2	192.6	183.0	177.1
75°	203.8	197.6	191.4	185.2	179.1	171.7	163.0	154.4	145.7	137.1	132.5
77.5°	150.8	145.8	140.9	136.0	131.0	125.1	118.2	111.3	104.3	97.5	94.3
80°	120.4	115.5	110.5	105.6	100.7	95.3	89.5	83.7	78.0	72.2	70.4
82.5°	90.8	86.3	81.9	77.4	72.9	68.8	64.8	60.9	56.9	53.0	52.1
85°	50.9	47.3	43.5	39.9	36.1	33.7	32.7	31.7	30.7	29.6	29.4
87.5°	17.1	16.1	15.0	14.0	12.9	12.4	12.3	12.3	12.1	12.1	12.2
90°	0.4	0.6	1.2	1.9	2.5	3.1	3.5	4.1	4.4	5.1	5.4
92.5°	3.8	4.6	7.3	11.2	16.7	25.9	43.1	71.9	103.3	101.6	82.2
95°	10.4	10.7	13.2	16.7	23.6	37.8	71.5	140.9	227.8	279.2	273.2
97.5°	17.3	17.7	19.4	22.9	29.2	39.3	61.6	112.4	203.5	298.2	345.7
100°	22.0	22.6	24.0	27.4	33.4	42.9	61.2	102.1	181.6	284.5	363.4
102.5°	27.4	27.7	28.7	32.5	38.0	47.2	63.4	97.8	164.9	260.6	352.8
105°	35.6	35.6	37.2	40.3	45.4	54.2	68.0	96.1	148.7	228.5	319.0
107.5°	43.7	44.3	45.8	48.4	53.7	61.6	75.0	99.0	142.0	206.3	284.4
110°	49.5	50.1	51.4	54.2	58.9	67.1	80.1	101.8	139.9	196.0	264.7



TEST NUMBER: P333555-940

CATALOG NUMBER: S125RDIP-S850D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	55.3	55.9	56.9	59.7	64.5	72.4	84.8	105.3	139.9	189.9	250.1
115°	63.7	64.3	65.3	68.0	72.8	80.7	92.4	110.6	140.9	183.4	234.2
117.5°	71.2	72.1	73.2	76.0	81.4	89.0	100.0	116.6	142.9	180.2	224.6
120°	76.2	77.2	78.5	81.3	86.7	94.5	105.6	120.7	145.0	178.7	219.4
122.5°	81.6	82.2	83.3	86.1	91.9	99.9	110.8	125.2	146.7	177.5	214.8
125°	88.3	88.9	90.4	93.3	99.2	107.5	117.9	131.4	149.7	175.8	208.7
127.5°	93.5	94.4	96.4	100.0	106.4	114.6	124.6	137.1	153.0	175.1	203.0
130°	96.8	97.7	100.2	104.3	110.9	119.1	128.9	140.9	155.1	174.6	199.2
132.5°	99.2	100.5	103.5	108.1	114.9	123.1	133.0	144.2	157.3	174.6	196.2
135°	103.3	104.6	108.4	113.4	120.1	128.6	138.3	148.7	160.4	174.6	192.5
137.5°	108.5	109.5	113.0	118.1	124.6	133.3	142.2	152.1	163.3	175.0	189.3
140°	111.6	112.5	116.3	121.4	127.3	135.8	145.0	154.4	164.5	175.2	187.8
142.5°	115.1	115.7	119.3	124.4	130.1	138.1	146.7	155.7	165.2	175.5	186.5
145°	120.4	121.0	124.1	128.6	134.3	141.5	149.7	157.6	166.0	175.2	184.7
147.5°	125.9	126.3	129.0	133.1	138.0	144.4	151.6	158.7	166.4	174.4	182.7
150°	129.2	129.8	132.1	136.2	140.5	145.9	152.8	159.4	166.4	173.6	181.2
152.5°	132.8	133.1	135.1	138.7	142.9	147.7	154.1	160.0	166.1	172.6	179.4
155°	137.4	137.4	139.3	142.4	145.6	150.0	155.3	160.4	165.4	170.9	176.5
157.5°	141.6	141.5	143.0	145.7	148.5	151.9	156.4	160.7	164.6	168.9	173.7
160°	144.4	144.0	145.3	147.5	150.0	152.8	156.9	160.7	163.9	167.6	171.5
162.5°	146.6	146.3	147.6	149.5	151.5	153.8	157.5	160.5	163.1	166.1	169.4
165°	150.0	149.4	150.3	151.9	153.2	155.1	157.6	160.1	162.0	163.9	166.4
167.5°	152.3	151.9	152.6	153.4	154.3	155.5	157.6	159.3	160.2	161.7	163.5
170°	153.8	153.5	153.8	154.4	155.1	156.0	157.6	158.8	159.4	160.4	161.7
172.5°	154.8	154.3	154.5	155.2	155.5	156.0	157.3	158.4	158.5	158.9	159.9
175°	156.0	155.3	155.7	156.0	156.0	156.0	156.9	157.6	157.3	157.3	157.6
177.5°	156.6	156.0	156.0	156.3	156.0	156.0	156.6	156.9	156.3	156.3	156.6
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333555-940

CATALOG NUMBER: S125RDIP-S850D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2
2.5°	1222.0	1223.7	1225.3	1226.1	1225.9	1225.7	1225.6	1225.4
5°	1214.5	1216.6	1218.6	1219.5	1219.1	1218.6	1218.3	1217.8
7.5°	1199.4	1200.9	1202.3	1202.7	1202.3	1201.8	1201.4	1201.0
10°	1186.6	1187.2	1187.8	1187.8	1187.2	1186.6	1186.0	1185.4
12.5°	1168.5	1168.9	1169.4	1169.2	1168.2	1167.2	1166.4	1165.4
15°	1138.7	1138.4	1138.3	1137.3	1135.4	1133.5	1131.7	1129.8
17.5°	1101.4	1100.5	1099.4	1098.1	1096.6	1095.1	1093.6	1092.1
20°	1074.1	1073.0	1072.0	1070.6	1068.7	1066.8	1065.0	1063.2
22.5°	1046.9	1044.9	1042.9	1041.1	1039.6	1038.0	1036.5	1035.0
25°	1002.3	999.6	996.9	994.4	992.1	989.9	987.7	985.3
27.5°	954.0	950.2	946.5	943.5	941.4	939.1	937.0	934.8
30°	919.4	914.7	909.9	906.7	904.8	902.9	901.1	899.2
32.5°	885.8	880.6	875.4	871.6	869.2	866.9	864.5	862.2
35°	833.6	827.6	821.6	817.3	814.3	811.5	808.6	805.7
37.5°	779.0	771.8	764.6	759.6	756.9	754.0	751.3	748.5
40°	742.8	735.0	727.2	722.0	719.6	717.1	714.6	712.2
42.5°	707.2	699.7	692.2	686.6	683.1	679.4	675.7	672.2
45°	650.3	642.1	633.8	628.2	625.1	622.1	618.9	615.8
47.5°	594.1	585.6	577.1	571.1	567.8	564.4	560.9	557.5
50°	556.0	547.3	538.7	532.8	529.8	526.6	523.5	520.5
52.5°	519.9	510.5	501.2	495.0	492.0	488.8	485.8	482.7
55°	464.9	455.7	446.4	440.1	436.8	433.5	430.3	427.0
57.5°	409.9	400.9	391.8	385.8	382.9	380.0	377.1	374.2
60°	373.6	364.5	355.5	349.5	346.3	343.3	340.2	337.1
62.5°	337.9	329.5	321.1	315.4	312.3	309.2	306.1	303.0
65°	285.4	277.2	268.9	263.3	260.2	257.2	254.0	250.9
67.5°	235.3	227.8	220.3	215.3	212.9	210.4	207.9	205.5
70°	202.1	195.7	189.3	184.9	182.4	179.9	177.5	175.0
72.5°	171.2	165.3	159.4	155.7	154.0	152.4	150.8	149.1
75°	128.0	123.5	119.0	116.0	114.5	113.1	111.6	110.2
77.5°	91.0	87.9	84.7	82.7	81.6	80.5	79.5	78.4
80°	68.6	66.7	64.8	63.7	63.3	62.9	62.4	62.1
82.5°	51.3	50.4	49.5	49.0	48.7	48.5	48.2	48.0
85°	29.2	29.0	28.8	28.6	28.4	28.2	28.0	27.8
87.5°	12.2	12.3	12.4	12.4	12.2	12.1	11.9	11.9
90°	5.7	6.0	6.3	7.0	7.0	7.0	7.2	7.2
92.5°	55.8	40.5	30.5	25.9	21.8	21.0	20.6	20.1
95°	226.6	178.7	139.9	113.4	91.0	81.6	79.1	74.1
97.5°	337.4	303.9	266.1	229.3	209.8	192.2	183.1	179.0
100°	387.6	372.2	339.7	306.9	285.2	262.5	250.8	245.8
102.5°	404.5	414.0	398.5	376.3	353.0	336.9	324.2	320.5
105°	394.6	437.7	451.6	448.2	438.0	427.7	421.3	417.6
107.5°	359.0	416.6	452.2	468.7	473.8	473.8	471.6	469.1
110°	332.8	392.7	437.1	463.9	478.0	484.0	486.2	486.2



TEST NUMBER: P333555-940

CATALOG NUMBER: S125RDIP-S850D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	312.1	369.0	413.9	445.5	466.2	476.5	482.0	484.3
115°	286.1	335.0	378.2	412.5	437.1	452.2	461.0	465.1
117.5°	269.4	311.5	348.7	380.2	404.7	420.4	429.2	431.7
120°	260.3	298.1	332.8	360.5	383.9	399.0	407.5	410.0
122.5°	253.5	288.6	319.4	345.4	366.2	380.0	388.6	390.8
125°	243.6	275.7	303.2	325.8	343.5	356.4	363.4	366.5
127.5°	233.5	263.5	289.1	310.3	326.4	337.8	344.3	345.7
130°	227.2	254.9	279.6	300.1	315.8	326.2	332.5	334.4
132.5°	220.9	246.9	269.2	288.9	304.7	315.0	320.8	323.0
135°	212.8	234.4	254.7	272.6	286.5	296.9	302.6	304.4
137.5°	205.8	223.4	240.1	255.4	267.8	277.2	282.5	284.5
140°	202.0	216.8	231.3	244.5	256.2	264.4	269.1	270.7
142.5°	198.8	211.2	223.7	235.2	245.1	252.1	256.5	257.9
145°	194.5	204.2	214.0	222.5	230.1	235.4	238.9	240.1
147.5°	190.4	198.3	205.9	212.3	218.3	222.6	224.5	225.2
150°	188.2	195.1	201.1	206.7	211.4	215.3	216.5	216.8
152.5°	185.7	191.8	197.2	201.7	205.6	208.7	209.9	210.3
155°	181.8	186.9	191.3	194.7	197.9	200.1	201.1	201.3
157.5°	178.1	182.2	185.7	188.3	190.8	192.6	193.5	193.4
160°	175.6	178.7	181.8	184.0	186.3	187.8	188.4	188.2
162.5°	172.7	175.7	178.3	180.3	182.0	183.2	183.4	183.3
165°	168.9	171.1	173.0	174.6	175.8	176.5	176.5	176.5
167.5°	165.2	166.7	168.2	169.3	170.0	170.5	170.2	170.1
170°	163.3	164.2	165.1	165.8	166.4	166.7	166.7	166.4
172.5°	161.0	161.9	162.6	163.0	163.1	163.7	163.2	162.8
175°	158.5	158.5	159.2	159.2	159.2	159.4	158.8	158.5
177.5°	156.9	157.0	157.0	157.0	156.9	157.0	156.3	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3

(END OF REPORT)