

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333561-940

Luminaire Tested: **S125RDIP-S850D590U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333561-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D590U940-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4790.1 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333561-940

CATALOG NUMBER: S125RDIP-S850D590U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333561-940

CATALOG NUMBER: S125RDIP-S850D590U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	59	57	56
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	52	50	48
3	84	74	67	61	78	70	63	58	61	56	52	53	50	46	46	43	41
4	77	66	58	52	72	62	55	49	55	49	45	48	43	40	41	38	35
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	27	24
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	23	20
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7919	7919	7919
5°	7937	7847	7895
10°	7877	7774	7774
15°	7783	7616	7554
20°	7663	7396	7307
25°	7524	7180	7021
30°	7348	6927	6706
35°	7171	6666	6352
40°	7003	6395	6004
45°	6801	6090	5624
50°	6597	5760	5230
55°	6361	5443	4808
60°	6124	5059	4354
65°	5845	4614	3834
70°	5527	4056	3305
75°	5085	3421	2750
80°	4478	2685	2310
85°	3772	2193	2060



TEST NUMBER: P333561-940

CATALOG NUMBER: S125RDIP-S850D590U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.3	2.4
10°-20°	322.2	6.7
20°-30°	467.2	9.8
30°-40°	532.5	11.1
40°-50°	519.1	10.8
50°-60°	436.9	9.1
60°-70°	306.3	6.4
70°-80°	157.4	3.3
80°-90°	41.2	0.9
90°-100°	182.9	3.8
100°-110°	393.1	8.2
110°-120°	369.0	7.7
120°-130°	299.0	6.2
130°-140°	240.0	5.0
140°-150°	181.1	3.8
150°-160°	127.5	2.7
160°-170°	75.1	1.6
170°-180°	24.4	0.5
0°-30°	904.7	18.9
0°-40°	1437.3	30.0
0°-60°	2393.2	50.0
0°-90°	2898.1	60.5
90°-120°	945.0	19.7
90°-150°	1665.0	34.8
90°-180°	1892.0	39.5
0°-180°	4790.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1226	1226	1226	1226	1226	
5°	1224	1220	1210	1219	1218	116
15°	1164	1158	1139	1138	1130	328
25°	1056	1041	1008	996	985	486
35°	910	886	846	819	806	569
45°	745	716	667	631	616	574
55°	565	534	483	443	427	505
65°	382	350	302	266	251	379
75°	204	175	137	118	110	216
85°	51	35	30	29	28	57
90°	0	5	8	11	12	3
95°	17	50	451	205	120	18
105°	58	80	369	726	674	61
115°	103	124	296	638	751	101
125°	142	167	284	508	592	126
135°	167	201	282	426	491	129
145°	194	223	283	352	388	122
155°	222	239	276	312	325	102
165°	242	249	264	281	285	68
175°	252	252	254	257	256	24
180°	252	252	252	252	252	



TEST NUMBER: P333561-940

CATALOG NUMBER: S125RDIP-S850D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2
2.5°	1228.3	1227.9	1227.4	1226.9	1226.4	1225.3	1223.7	1222.0	1220.4	1218.7	1220.4
5°	1224.3	1223.5	1222.6	1221.8	1221.0	1219.5	1217.2	1215.0	1212.6	1210.4	1212.5
7.5°	1212.3	1211.5	1210.7	1209.9	1209.2	1207.4	1204.7	1201.9	1199.3	1196.5	1197.9
10°	1201.1	1200.5	1199.9	1199.3	1198.6	1196.9	1194.1	1191.1	1188.3	1185.4	1186.0
12.5°	1188.6	1187.8	1187.0	1186.2	1185.4	1183.1	1179.2	1175.4	1171.5	1167.6	1168.1
15°	1164.1	1162.9	1161.6	1160.4	1159.1	1156.4	1152.1	1147.7	1143.4	1139.1	1138.9
17.5°	1136.5	1134.6	1132.7	1130.9	1128.9	1125.2	1119.8	1114.4	1108.9	1103.5	1102.5
20°	1115.0	1112.9	1110.9	1108.8	1106.8	1102.4	1095.9	1089.3	1082.7	1076.1	1075.1
22.5°	1091.3	1089.2	1087.2	1085.1	1083.1	1078.6	1071.7	1064.8	1057.8	1051.0	1048.9
25°	1055.8	1052.7	1049.5	1046.5	1043.4	1038.0	1030.5	1022.8	1015.2	1007.6	1005.0
27.5°	1015.0	1011.3	1007.5	1003.8	1000.1	994.1	986.0	977.8	969.6	961.4	957.7
30°	985.3	981.4	977.6	973.7	969.7	963.4	954.8	946.2	937.5	928.9	924.2
32.5°	956.4	951.9	947.4	942.8	938.2	931.5	922.7	913.9	905.1	896.3	891.1
35°	909.5	904.5	899.6	894.6	889.7	882.5	873.3	864.1	854.8	845.5	839.5
37.5°	863.3	857.3	851.3	845.3	839.3	831.5	822.0	812.3	802.8	793.3	786.1
40°	830.7	824.6	818.3	812.2	806.0	798.0	788.1	778.2	768.4	758.5	750.6
42.5°	796.7	790.3	784.0	777.6	771.2	763.0	752.8	742.6	732.4	722.2	714.7
45°	744.6	738.6	732.6	726.7	720.7	712.0	700.7	689.5	678.1	666.8	658.5
47.5°	690.7	684.4	678.1	671.8	665.5	656.7	645.2	633.8	622.4	611.0	602.5
50°	656.6	649.8	643.0	636.2	629.5	620.2	608.4	596.7	585.0	573.3	564.6
52.5°	619.6	612.6	605.6	598.7	591.7	582.7	571.7	560.6	549.5	538.4	529.1
55°	564.9	558.3	551.8	545.2	538.6	529.5	518.0	506.5	495.0	483.4	474.1
57.5°	509.7	502.7	495.6	488.6	481.6	472.5	461.4	450.2	439.2	428.0	419.0
60°	474.1	467.0	459.8	452.5	445.3	436.2	425.1	413.9	402.9	391.7	382.7
62.5°	436.4	429.5	422.7	415.7	408.8	399.8	388.5	377.3	366.0	354.7	346.3
65°	382.5	375.5	368.5	361.5	354.5	345.5	334.7	323.7	312.8	301.9	293.6
67.5°	329.0	321.9	315.0	308.0	301.0	292.2	281.8	271.3	260.9	250.4	242.9
70°	292.7	285.6	278.7	271.6	264.7	256.0	245.8	235.4	225.2	214.8	208.5
72.5°	257.1	250.2	243.4	236.6	229.8	221.5	211.9	202.2	192.6	183.0	177.1
75°	203.8	197.6	191.4	185.2	179.1	171.7	163.0	154.4	145.7	137.1	132.5
77.5°	150.8	145.8	140.9	136.0	131.0	125.1	118.2	111.3	104.3	97.5	94.3
80°	120.4	115.5	110.5	105.6	100.7	95.3	89.5	83.7	78.0	72.2	70.4
82.5°	90.8	86.3	81.9	77.4	72.9	68.8	64.8	60.9	56.9	53.0	52.1
85°	50.9	47.3	43.5	39.9	36.1	33.7	32.7	31.7	30.7	29.6	29.4
87.5°	17.1	16.1	15.2	14.2	13.3	12.8	12.8	12.8	12.7	12.8	12.8
90°	0.5	1.0	2.1	3.0	4.1	5.1	5.6	6.6	7.1	8.1	8.6
92.5°	6.2	7.5	11.8	18.1	26.8	41.7	69.5	116.1	166.7	164.0	132.8
95°	16.8	17.3	21.4	26.9	38.2	61.1	115.5	227.4	367.7	450.7	441.0
97.5°	27.9	28.4	31.3	36.9	47.0	63.5	99.5	181.5	328.4	481.3	558.0
100°	35.6	36.6	38.7	44.2	53.9	69.2	98.7	164.8	293.0	459.3	586.5
102.5°	44.1	44.8	46.4	52.4	61.3	76.1	102.4	157.9	266.1	420.6	569.4
105°	57.5	57.5	60.0	65.1	73.2	87.5	109.9	155.2	240.0	368.8	514.8
107.5°	70.5	71.5	73.9	78.1	86.6	99.4	121.1	159.8	229.1	333.1	459.1
110°	79.9	80.9	82.9	87.5	95.1	108.3	129.2	164.3	225.9	316.4	427.3



TEST NUMBER: P333561-940

CATALOG NUMBER: S125RDIP-S850D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	89.3	90.2	91.8	96.5	104.1	116.9	137.0	170.0	225.9	306.7	403.7
115°	102.7	103.8	105.3	109.9	117.5	130.2	149.0	178.5	227.4	296.0	377.9
117.5°	114.9	116.5	118.2	122.7	131.3	143.7	161.5	188.3	230.7	290.9	362.6
120°	123.1	124.7	126.6	131.3	139.9	152.6	170.4	194.8	234.0	288.4	354.0
122.5°	131.6	132.8	134.4	138.9	148.5	161.1	179.0	202.2	236.8	286.4	346.7
125°	142.4	143.5	146.0	150.5	160.2	173.4	190.2	212.1	241.7	283.8	336.7
127.5°	150.9	152.4	155.7	161.5	171.7	184.9	201.1	221.2	247.0	282.6	327.6
130°	156.1	157.7	161.8	168.4	179.1	192.3	208.0	227.4	250.3	281.8	321.5
132.5°	160.2	162.2	167.0	174.5	185.6	198.8	214.5	232.6	254.0	281.8	316.6
135°	166.8	168.9	175.0	183.2	193.8	207.5	223.3	240.0	258.9	281.8	310.8
137.5°	175.2	176.7	182.4	190.6	201.0	215.2	229.5	245.6	263.5	282.4	305.6
140°	180.0	181.6	187.7	195.8	205.5	219.3	234.0	249.2	265.6	282.9	303.2
142.5°	185.7	186.9	192.6	200.7	210.0	222.9	236.8	251.3	266.7	283.2	301.1
145°	194.3	195.3	200.4	207.5	216.7	228.4	241.7	254.3	268.0	282.9	298.1
147.5°	203.2	203.8	208.2	214.8	222.7	233.1	244.7	256.2	268.6	281.5	294.9
150°	208.6	209.6	213.1	219.7	226.9	235.5	246.7	257.3	268.6	280.3	292.5
152.5°	214.3	214.8	218.0	223.8	230.5	238.4	248.7	258.2	268.1	278.7	289.6
155°	221.8	221.8	224.8	229.9	235.0	242.1	250.7	258.9	267.1	275.7	284.8
157.5°	228.5	228.4	230.9	235.2	239.7	245.0	252.5	259.4	265.7	272.6	280.4
160°	233.0	232.5	234.5	238.1	242.1	246.7	253.3	259.4	264.5	270.6	276.7
162.5°	236.7	236.1	238.2	241.3	244.6	248.3	254.1	259.0	263.3	268.1	273.5
165°	242.1	241.1	242.6	245.1	247.2	250.3	254.3	258.4	261.4	264.5	268.6
167.5°	245.8	245.3	246.2	247.6	249.1	250.9	254.3	257.2	258.6	260.9	263.8
170°	248.3	247.7	248.3	249.2	250.3	251.8	254.3	256.4	257.3	258.9	260.9
172.5°	249.9	249.0	249.4	250.5	251.1	251.8	254.0	255.6	255.7	256.5	258.1
175°	251.8	250.7	251.3	251.8	251.8	251.8	253.3	254.3	253.8	253.8	254.3
177.5°	252.7	251.9	251.9	252.3	251.9	251.9	252.7	253.1	252.3	252.3	252.7
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333561-940

CATALOG NUMBER: S125RDIP-S850D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2
2.5°	1222.0	1223.7	1225.3	1226.1	1225.9	1225.7	1225.6	1225.4
5°	1214.5	1216.6	1218.6	1219.5	1219.1	1218.6	1218.3	1217.8
7.5°	1199.4	1200.9	1202.3	1202.7	1202.3	1201.8	1201.4	1201.0
10°	1186.6	1187.2	1187.8	1187.8	1187.2	1186.6	1186.0	1185.4
12.5°	1168.5	1168.9	1169.4	1169.2	1168.2	1167.2	1166.4	1165.4
15°	1138.7	1138.4	1138.3	1137.3	1135.4	1133.5	1131.7	1129.8
17.5°	1101.4	1100.5	1099.4	1098.1	1096.6	1095.1	1093.6	1092.1
20°	1074.1	1073.0	1072.0	1070.6	1068.7	1066.8	1065.0	1063.2
22.5°	1046.9	1044.9	1042.9	1041.1	1039.6	1038.0	1036.5	1035.0
25°	1002.3	999.6	996.9	994.4	992.1	989.9	987.7	985.3
27.5°	954.0	950.2	946.5	943.5	941.4	939.1	937.0	934.8
30°	919.4	914.7	909.9	906.7	904.8	902.9	901.1	899.2
32.5°	885.8	880.6	875.4	871.6	869.2	866.9	864.5	862.2
35°	833.6	827.6	821.6	817.3	814.3	811.5	808.6	805.7
37.5°	779.0	771.8	764.6	759.6	756.9	754.0	751.3	748.5
40°	742.8	735.0	727.2	722.0	719.6	717.1	714.6	712.2
42.5°	707.2	699.7	692.2	686.6	683.1	679.4	675.7	672.2
45°	650.3	642.1	633.8	628.2	625.1	622.1	618.9	615.8
47.5°	594.1	585.6	577.1	571.1	567.8	564.4	560.9	557.5
50°	556.0	547.3	538.7	532.8	529.8	526.6	523.5	520.5
52.5°	519.9	510.5	501.2	495.0	492.0	488.8	485.8	482.7
55°	464.9	455.7	446.4	440.1	436.8	433.5	430.3	427.0
57.5°	409.9	400.9	391.8	385.8	382.9	380.0	377.1	374.2
60°	373.6	364.5	355.5	349.5	346.3	343.3	340.2	337.1
62.5°	337.9	329.5	321.1	315.4	312.3	309.2	306.1	303.0
65°	285.4	277.2	268.9	263.3	260.2	257.2	254.0	250.9
67.5°	235.3	227.8	220.3	215.3	212.9	210.4	207.9	205.5
70°	202.1	195.7	189.3	184.9	182.4	179.9	177.5	175.0
72.5°	171.2	165.3	159.4	155.7	154.0	152.4	150.8	149.1
75°	128.0	123.5	119.0	116.0	114.5	113.1	111.6	110.2
77.5°	91.0	87.9	84.7	82.7	81.6	80.5	79.5	78.4
80°	68.6	66.7	64.8	63.7	63.3	62.9	62.4	62.1
82.5°	51.3	50.4	49.5	49.0	48.7	48.5	48.2	48.0
85°	29.2	29.0	28.8	28.6	28.4	28.2	28.0	27.8
87.5°	12.9	13.0	13.1	13.3	13.1	12.9	12.8	12.8
90°	9.2	9.6	10.2	11.1	11.1	11.1	11.7	11.7
92.5°	90.2	65.5	49.2	41.7	35.2	34.0	33.3	32.5
95°	365.7	288.4	225.9	183.2	147.0	131.7	127.7	119.6
97.5°	544.7	490.4	429.5	370.1	338.7	310.1	295.4	288.9
100°	625.6	600.7	548.3	495.4	460.3	423.7	404.9	396.7
102.5°	652.9	668.2	643.1	607.3	569.8	543.8	523.3	517.2
105°	636.9	706.5	728.9	723.3	707.0	690.3	680.1	674.0
107.5°	579.4	672.4	730.0	756.4	764.7	764.6	761.3	757.2
110°	537.2	633.8	705.5	748.8	771.6	781.3	784.9	784.9



TEST NUMBER: P333561-940

CATALOG NUMBER: S125RDIP-S850D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	503.8	595.6	668.1	719.1	752.5	769.1	777.9	781.6
115°	461.8	540.7	610.4	665.8	705.5	730.0	744.1	750.8
117.5°	434.8	502.7	562.8	613.7	653.4	678.6	692.7	696.8
120°	420.2	481.2	537.2	581.9	619.6	644.0	657.7	661.7
122.5°	409.2	465.7	515.6	557.5	591.0	613.4	627.1	630.8
125°	393.2	445.1	489.4	525.9	554.5	575.3	586.5	591.6
127.5°	376.9	425.3	466.6	501.0	526.7	545.2	555.7	558.0
130°	366.8	411.5	451.2	484.2	509.7	526.5	536.6	539.7
132.5°	356.6	398.5	434.5	466.4	491.8	508.5	517.9	521.4
135°	343.3	378.4	411.0	440.0	462.4	479.1	488.3	491.3
137.5°	332.2	360.5	387.6	412.2	432.2	447.5	455.9	459.3
140°	326.0	350.0	373.4	394.8	413.6	426.8	434.4	436.9
142.5°	320.7	341.0	361.1	379.7	395.7	406.8	414.0	416.2
145°	313.9	329.6	345.4	359.1	371.3	380.0	385.6	387.6
147.5°	307.4	320.1	332.3	342.6	352.3	359.2	362.5	363.4
150°	303.6	314.9	324.5	333.7	341.3	347.4	349.5	350.0
152.5°	299.6	309.6	318.4	325.6	332.0	336.8	338.9	339.4
155°	293.5	301.7	308.7	314.3	319.4	323.0	324.5	325.0
157.5°	287.4	294.1	299.6	304.0	307.9	310.9	312.3	312.2
160°	283.3	288.4	293.5	297.0	300.6	303.2	304.2	303.6
162.5°	278.8	283.6	287.8	291.0	293.7	295.9	296.0	296.0
165°	272.6	276.2	279.3	281.8	283.8	284.8	284.8	284.8
167.5°	266.7	269.1	271.4	273.2	274.3	275.2	274.7	274.6
170°	263.5	265.0	266.5	267.5	268.6	269.1	269.1	268.6
172.5°	259.8	261.4	262.4	263.1	263.3	264.2	263.4	262.9
175°	255.8	255.8	256.9	256.9	256.9	257.3	256.4	255.8
177.5°	253.1	253.5	253.5	253.5	253.1	253.5	252.3	252.3
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3

(END OF REPORT)