

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333633

Luminaire Tested: **S125RDIP-S1270D1035U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333633
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1035U835-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8592.6 lumens
Efficiency: N/A
Efficacy: 128.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333633

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333633

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	95	91	88	93	89	86	83	77	74	72	66	64	62	56	54	53	48
2	91	83	77	72	84	78	73	68	68	64	60	58	55	52	49	47	45	41
3	83	74	66	60	77	69	62	57	60	55	51	51	48	45	44	41	39	35
4	76	65	57	51	71	61	54	49	53	48	44	46	42	38	39	36	34	30
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29	26
6	65	52	44	39	60	49	42	37	43	37	33	38	33	29	32	29	26	23
7	60	47	39	34	56	45	37	32	39	33	29	34	30	26	29	26	23	21
8	55	43	35	30	52	41	34	29	36	30	26	31	27	23	27	24	21	19
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13332	13332	13332
5°	13363	13211	13291
10°	13262	13088	13088
15°	13104	12822	12718
20°	12902	12451	12302
25°	12666	12088	11821
30°	12371	11662	11290
35°	12071	11223	10694
40°	11790	10765	10108
45°	11449	10253	9470
50°	11106	9697	8804
55°	10709	9164	8094
60°	10311	8519	7330
65°	9840	7768	6457
70°	9304	6830	5565
75°	8559	5757	4629
80°	7539	4523	3887
85°	6358	3698	3468



TEST NUMBER: P333633

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.1	2.3
10°-20°	542.5	6.3
20°-30°	786.6	9.2
30°-40°	896.5	10.4
40°-50°	873.9	10.2
50°-60°	735.6	8.6
60°-70°	515.6	6.0
70°-80°	265.0	3.1
80°-90°	69.7	0.8
90°-100°	358.9	4.2
100°-110°	771.5	9.0
110°-120°	724.1	8.4
120°-130°	586.8	6.8
130°-140°	470.9	5.5
140°-150°	355.4	4.1
150°-160°	250.1	2.9
160°-170°	147.4	1.7
170°-180°	48.0	0.6
0°-30°	1523.2	17.7
0°-40°	2419.7	28.2
0°-60°	4029.1	46.9
0°-90°	4879.5	56.8
90°-120°	1854.5	21.6
90°-150°	3267.6	38.0
90°-180°	3713.0	43.2
0°-180°	8592.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2064	2064	2064	2064	2064	
5°	2061	2054	2038	2052	2050	195
15°	1960	1949	1918	1915	1902	552
25°	1777	1752	1696	1676	1659	817
35°	1531	1492	1424	1380	1356	958
45°	1254	1206	1123	1062	1037	967
55°	951	899	814	746	719	850
65°	644	589	508	448	422	638
75°	343	295	231	198	186	363
85°	86	59	50	48	47	96
90°	1	9	16	21	23	6
95°	33	97	884	401	235	35
105°	113	158	724	1425	1323	119
115°	202	243	581	1252	1474	198
125°	280	327	557	996	1161	248
135°	327	394	553	835	964	254
145°	381	437	555	691	761	239
155°	435	468	541	611	638	200
165°	475	488	519	551	559	134
175°	494	494	498	504	502	47
180°	495	495	495	495	495	



TEST NUMBER: P333633

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3
2.5°	2068.0	2067.2	2066.3	2065.5	2064.7	2062.9	2060.1	2057.3	2054.6	2051.8	2054.6
5°	2061.2	2059.8	2058.4	2057.0	2055.6	2053.0	2049.2	2045.4	2041.6	2037.8	2041.2
7.5°	2040.9	2039.6	2038.3	2036.9	2035.6	2032.7	2028.1	2023.5	2019.0	2014.4	2016.8
10°	2022.2	2021.1	2020.1	2019.1	2018.0	2015.1	2010.2	2005.4	2000.5	1995.7	1996.7
12.5°	2001.0	1999.7	1998.3	1997.0	1995.7	1991.8	1985.3	1978.8	1972.2	1965.7	1966.5
15°	1959.8	1957.7	1955.7	1953.6	1951.5	1946.8	1939.5	1932.3	1925.0	1917.7	1917.4
17.5°	1913.3	1910.2	1907.0	1903.8	1900.6	1894.4	1885.3	1876.1	1867.0	1857.8	1856.1
20°	1877.2	1873.7	1870.2	1866.8	1863.3	1856.0	1845.0	1833.9	1822.8	1811.7	1810.0
22.5°	1837.3	1833.8	1830.3	1826.9	1823.4	1815.9	1804.2	1792.6	1780.9	1769.3	1765.9
25°	1777.4	1772.2	1767.0	1761.8	1756.6	1747.6	1734.8	1722.0	1709.1	1696.3	1691.8
27.5°	1708.8	1702.5	1696.2	1689.9	1683.6	1673.6	1659.8	1646.1	1632.4	1618.7	1612.4
30°	1658.9	1652.3	1645.7	1639.2	1632.6	1622.0	1607.4	1592.9	1578.3	1563.8	1555.8
32.5°	1610.3	1602.6	1594.9	1587.2	1579.5	1568.2	1553.4	1538.6	1523.7	1508.9	1500.1
35°	1531.1	1522.7	1514.4	1506.1	1497.8	1485.8	1470.2	1454.7	1439.1	1423.5	1413.4
37.5°	1453.4	1443.3	1433.2	1423.1	1412.9	1399.8	1383.8	1367.7	1351.6	1335.5	1323.5
40°	1398.5	1388.1	1377.7	1367.3	1357.0	1343.4	1326.8	1310.2	1293.5	1276.9	1263.8
42.5°	1341.2	1330.5	1319.8	1309.1	1298.5	1284.5	1267.4	1250.2	1233.0	1215.8	1203.2
45°	1253.5	1243.5	1233.4	1223.4	1213.3	1198.8	1179.7	1160.7	1141.6	1122.6	1108.7
47.5°	1162.8	1152.2	1141.6	1131.0	1120.4	1105.5	1086.3	1067.1	1047.9	1028.7	1014.4
50°	1105.4	1094.0	1082.5	1071.1	1059.7	1044.1	1024.3	1004.6	984.8	965.1	950.5
52.5°	1043.0	1031.3	1019.6	1007.9	996.2	981.0	962.4	943.8	925.1	906.5	890.8
55°	951.1	940.0	928.9	917.8	906.7	891.5	872.1	852.7	833.3	813.9	798.3
57.5°	858.1	846.3	834.4	822.6	810.7	795.5	776.8	758.0	739.3	720.6	705.4
60°	798.3	786.1	774.0	761.9	749.8	734.3	715.6	696.9	678.2	659.5	644.3
62.5°	734.7	723.1	711.5	699.9	688.4	673.1	654.1	635.1	616.1	597.1	583.0
65°	643.9	632.1	620.4	608.6	596.8	581.7	563.4	545.0	526.6	508.3	494.4
67.5°	553.8	542.0	530.2	518.5	506.7	492.0	474.4	456.8	439.2	421.6	408.9
70°	492.7	480.9	469.1	457.3	445.6	431.0	413.7	396.4	379.0	361.7	351.0
72.5°	432.8	421.3	409.8	398.3	386.8	372.9	356.7	340.5	324.3	308.1	298.2
75°	343.0	332.6	322.2	311.8	301.4	289.0	274.4	259.9	245.3	230.7	223.1
77.5°	253.8	245.5	237.2	228.9	220.6	210.6	198.9	187.3	175.7	164.0	158.7
80°	202.7	194.4	186.1	177.7	169.4	160.4	150.7	141.0	131.3	121.6	118.5
82.5°	152.8	145.3	137.8	130.3	122.9	115.8	109.1	102.5	95.8	89.2	87.7
85°	85.8	79.5	73.3	67.0	60.8	56.8	55.1	53.4	51.6	49.9	49.5
87.5°	28.9	27.1	25.6	24.1	22.5	21.8	21.7	21.9	21.8	21.9	22.1
90°	1.0	2.0	4.0	6.0	8.0	10.0	11.0	13.0	14.0	16.0	17.0
92.5°	12.2	14.8	23.2	35.5	52.7	81.9	136.4	227.8	327.0	321.8	260.5
95°	32.9	33.9	41.9	52.9	74.9	119.8	226.6	446.2	721.8	884.5	865.5
97.5°	54.7	55.9	61.5	72.5	92.2	124.6	195.3	356.2	644.5	944.6	1095.1
100°	69.9	71.9	75.9	86.8	105.8	135.8	193.7	323.4	575.0	901.4	1151.0
102.5°	86.7	87.8	91.0	102.8	120.2	149.3	200.9	309.9	522.3	825.6	1117.5
105°	112.8	112.8	117.8	127.8	143.8	171.7	215.6	304.5	471.2	723.7	1010.3
107.5°	138.4	140.4	145.1	153.3	169.9	195.1	237.6	313.7	449.6	653.7	900.8
110°	156.7	158.7	162.7	171.7	186.7	212.6	253.6	322.4	443.2	620.9	838.5



TEST NUMBER: P333633

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	175.1	177.1	180.3	189.3	204.2	229.4	268.7	333.6	443.2	601.8	792.2
115°	201.7	203.6	206.6	215.6	230.6	255.6	292.5	350.4	446.2	581.0	741.7
117.5°	225.6	228.6	231.8	240.8	257.8	281.9	316.9	369.6	452.8	570.8	711.6
120°	241.6	244.6	248.6	257.6	274.5	299.5	334.4	382.3	459.2	566.0	694.8
122.5°	258.4	260.5	263.7	272.7	291.3	316.3	351.2	396.7	464.8	562.0	680.4
125°	279.5	281.5	286.5	295.5	314.5	340.4	373.4	416.3	474.2	557.0	660.9
127.5°	296.1	299.1	305.5	316.9	337.0	363.0	394.7	434.2	484.8	554.6	642.9
130°	306.5	309.5	317.5	330.4	351.4	377.3	408.3	446.2	491.2	553.0	630.9
132.5°	314.5	318.2	327.8	342.4	364.2	390.1	421.1	456.6	498.3	553.0	621.3
135°	327.4	331.4	343.4	359.4	380.3	407.3	438.2	471.2	508.1	553.0	609.9
137.5°	343.8	346.8	358.0	374.0	394.5	422.3	450.4	482.0	517.1	554.2	599.8
140°	353.4	356.4	368.4	384.3	403.3	430.3	459.2	489.2	521.1	555.0	595.0
142.5°	364.6	366.8	377.9	393.9	412.1	437.4	464.8	493.1	523.5	555.8	591.0
145°	381.3	383.3	393.3	407.3	425.3	448.2	474.2	499.1	526.1	555.0	585.0
147.5°	398.9	400.1	408.7	421.7	437.2	457.4	480.2	502.7	527.1	552.4	578.8
150°	409.3	411.3	418.3	431.3	445.2	462.2	484.2	505.1	527.1	550.0	574.0
152.5°	420.5	421.7	427.9	439.2	452.4	467.8	488.2	506.7	526.3	546.9	568.4
155°	435.2	435.2	441.2	451.2	461.2	475.2	492.1	508.1	524.1	541.1	559.0
157.5°	448.4	448.2	453.0	461.6	470.4	481.0	495.5	509.1	521.5	535.1	550.2
160°	457.2	456.2	460.2	467.2	475.2	484.2	497.1	509.1	519.1	531.1	543.1
162.5°	464.4	463.4	467.4	473.6	480.0	487.4	498.7	508.3	516.7	526.3	536.7
165°	475.2	473.2	476.2	481.2	485.2	491.2	499.1	507.1	513.1	519.1	527.1
167.5°	482.4	481.4	483.2	486.0	488.8	492.5	499.1	504.7	507.5	512.1	517.7
170°	487.2	486.2	487.2	489.2	491.2	494.1	499.1	503.1	505.1	508.1	512.1
172.5°	490.4	488.6	489.6	491.5	492.7	494.1	498.3	501.5	501.9	503.3	506.5
175°	494.1	492.1	493.1	494.1	494.1	494.1	497.1	499.1	498.1	498.1	499.1
177.5°	495.9	494.3	494.3	495.1	494.3	494.3	495.9	496.7	495.1	495.1	495.9
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333633

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3
2.5°	2057.3	2060.1	2062.9	2064.1	2063.9	2063.6	2063.3	2063.0
5°	2044.7	2048.2	2051.6	2053.0	2052.3	2051.6	2050.9	2050.2
7.5°	2019.2	2021.7	2024.1	2024.9	2024.1	2023.4	2022.6	2021.9
10°	1997.7	1998.8	1999.8	1999.8	1998.8	1997.7	1996.7	1995.7
12.5°	1967.3	1968.0	1968.8	1968.4	1966.8	1965.2	1963.6	1962.0
15°	1917.0	1916.7	1916.3	1914.6	1911.5	1908.4	1905.2	1902.1
17.5°	1854.4	1852.6	1850.9	1848.8	1846.2	1843.6	1841.1	1838.5
20°	1808.2	1806.5	1804.8	1802.3	1799.2	1796.1	1793.0	1789.9
22.5°	1762.5	1759.1	1755.7	1752.7	1750.2	1747.6	1745.0	1742.5
25°	1687.3	1682.8	1678.3	1674.1	1670.3	1666.5	1662.7	1658.9
27.5°	1606.1	1599.8	1593.5	1588.5	1584.8	1581.1	1577.4	1573.8
30°	1547.9	1539.9	1531.9	1526.4	1523.3	1520.1	1517.0	1513.9
32.5°	1491.3	1482.5	1473.7	1467.3	1463.4	1459.4	1455.5	1451.5
35°	1403.4	1393.3	1383.3	1375.8	1371.0	1366.1	1361.3	1356.4
37.5°	1311.4	1299.4	1287.3	1278.9	1274.2	1269.5	1264.8	1260.1
40°	1250.6	1237.4	1224.3	1215.6	1211.4	1207.3	1203.1	1199.0
42.5°	1190.6	1178.0	1165.4	1156.0	1149.9	1143.8	1137.7	1131.6
45°	1094.8	1081.0	1067.1	1057.6	1052.4	1047.2	1042.0	1036.8
47.5°	1000.2	985.9	971.6	961.6	955.8	950.1	944.3	938.6
50°	936.0	921.4	906.9	897.0	891.8	886.6	881.4	876.2
52.5°	875.1	859.5	843.8	833.4	828.2	823.0	817.8	812.6
55°	782.7	767.1	751.5	740.9	735.4	729.8	724.3	718.8
57.5°	690.1	674.9	659.6	649.6	644.6	639.7	634.8	629.9
60°	629.0	613.8	598.5	588.3	583.1	577.9	572.7	567.5
62.5°	568.9	554.7	540.6	530.9	525.7	520.5	515.3	510.1
65°	480.6	466.7	452.8	443.3	438.1	432.9	427.7	422.5
67.5°	396.2	383.5	370.9	362.4	358.3	354.1	350.0	345.8
70°	340.2	329.5	318.8	311.3	307.1	303.0	298.8	294.7
72.5°	288.3	278.4	268.4	262.1	259.3	256.6	253.8	251.0
75°	215.5	207.9	200.3	195.2	192.8	190.4	188.0	185.5
77.5°	153.3	148.0	142.7	139.1	137.3	135.5	133.7	131.9
80°	115.4	112.3	109.1	107.2	106.5	105.8	105.2	104.5
82.5°	86.3	84.8	83.4	82.4	82.0	81.6	81.2	80.8
85°	49.2	48.9	48.5	48.2	47.8	47.5	47.1	46.8
87.5°	22.3	22.5	22.7	23.0	22.7	22.4	22.3	22.1
90°	18.0	19.0	20.0	22.0	22.0	22.0	23.0	23.0
92.5°	176.9	128.4	96.6	81.9	69.1	66.7	65.3	63.7
95°	717.8	566.0	443.2	359.4	288.5	258.6	250.6	234.6
97.5°	1069.0	962.5	842.9	726.3	664.7	608.7	579.8	567.0
100°	1227.9	1179.0	1076.1	972.3	903.4	831.6	794.6	778.7
102.5°	1281.4	1311.5	1262.2	1191.9	1118.3	1067.2	1027.0	1015.0
105°	1249.8	1386.6	1430.5	1419.5	1387.6	1354.7	1334.7	1322.7
107.5°	1137.2	1319.7	1432.5	1484.6	1500.8	1500.6	1494.0	1486.0
110°	1054.2	1243.8	1384.6	1469.5	1514.4	1533.3	1540.3	1540.3



TEST NUMBER: P333633

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	988.7	1168.8	1311.1	1411.2	1476.8	1509.4	1526.8	1533.9
115°	906.4	1061.2	1197.9	1306.7	1384.6	1432.5	1460.5	1473.5
117.5°	853.3	986.7	1104.5	1204.3	1282.2	1331.7	1359.4	1367.4
120°	824.6	944.4	1054.2	1142.0	1215.9	1263.8	1290.8	1298.8
122.5°	803.0	914.0	1011.8	1094.1	1160.0	1203.9	1230.9	1238.1
125°	771.7	873.5	960.3	1032.2	1088.1	1129.0	1151.0	1161.0
127.5°	739.7	834.8	915.8	983.1	1033.8	1069.9	1090.7	1095.1
130°	719.8	807.6	885.5	950.4	1000.3	1033.2	1053.2	1059.2
132.5°	699.8	782.0	852.7	915.2	965.1	998.1	1016.4	1023.2
135°	673.8	742.7	806.6	863.5	907.4	940.4	958.3	964.3
137.5°	651.9	707.6	760.7	809.0	848.3	878.3	894.9	901.4
140°	639.9	686.8	732.7	774.7	811.6	837.6	852.5	857.5
142.5°	629.5	669.2	708.8	745.1	776.5	798.4	812.6	816.8
145°	615.9	646.9	677.8	704.8	728.7	745.7	756.7	760.7
147.5°	603.2	628.3	652.1	672.4	691.4	705.0	711.4	713.2
150°	596.0	617.9	636.9	654.9	669.8	681.8	685.8	686.8
152.5°	588.0	607.5	624.9	638.9	651.5	661.1	665.0	666.0
155°	576.0	592.0	606.0	616.9	626.9	633.9	636.9	637.9
157.5°	564.0	577.2	588.0	596.6	604.4	610.1	612.9	612.7
160°	556.0	566.0	576.0	583.0	590.0	595.0	597.0	596.0
162.5°	547.3	556.4	564.8	571.0	576.4	580.6	581.0	580.8
165°	535.1	542.1	548.1	553.0	557.0	559.0	559.0	559.0
167.5°	523.5	528.1	532.7	536.3	538.3	540.1	539.3	539.1
170°	517.1	520.1	523.1	525.1	527.1	528.1	528.1	527.1
172.5°	509.9	512.9	515.1	516.3	516.7	518.5	516.9	515.9
175°	502.1	502.1	504.1	504.1	504.1	505.1	503.1	502.1
177.5°	496.7	497.5	497.5	497.5	496.7	497.5	495.1	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1

(END OF REPORT)