

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333614

Luminaire Tested: **S125RDIP-S1270D365U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333614
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D365U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6145.1 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333614

CATALOG NUMBER: S125RDIP-S1270D365U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333614

CATALOG NUMBER: S125RDIP-S1270D365U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	79																				
1	105	100	96	93	100	96	93	89	88	85	83	81	79	77	74	72	71	68																				
2	96	88	82	77	91	84	79	74	78	73	69	71	68	65	66	63	60	57																				
3	88	78	70	64	83	75	68	62	69	63	59	63	59	55	58	55	52	49																				
4	80	69	61	55	77	67	59	53	61	55	50	57	52	48	52	48	45	42																				
5	74	62	54	47	70	60	52	46	55	49	44	51	46	42	47	43	39	37																				
6	68	56	47	41	65	54	46	40	50	43	39	46	41	37	43	38	35	32																				
7	63	51	42	37	61	49	41	36	46	39	34	42	37	33	39	35	31	29																				
8	59	46	38	33	56	45	37	32	42	35	31	39	33	29	36	32	28	26																				
9	55	42	35	29	53	41	34	29	38	32	28	36	30	26	34	29	25	23																				
10	52	39	32	27	49	38	31	26	36	29	25	33	28	24	31	27	23	21																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13332	13332	13332
5°	13363	13211	13291
10°	13262	13088	13088
15°	13104	12822	12718
20°	12902	12451	12302
25°	12666	12088	11821
30°	12371	11662	11290
35°	12071	11223	10694
40°	11790	10765	10108
45°	11449	10253	9470
50°	11106	9697	8804
55°	10709	9164	8094
60°	10311	8519	7330
65°	9840	7768	6457
70°	9304	6830	5565
75°	8559	5757	4629
80°	7539	4523	3887
85°	6358	3698	3468



TEST NUMBER: P333614

CATALOG NUMBER: S125RDIP-S1270D365U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.1	3.2
10°-20°	542.5	8.8
20°-30°	786.6	12.8
30°-40°	896.5	14.6
40°-50°	873.9	14.2
50°-60°	735.6	12.0
60°-70°	515.6	8.4
70°-80°	265.0	4.3
80°-90°	67.9	1.1
90°-100°	30.4	0.5
100°-110°	89.8	1.5
110°-120°	152.1	2.5
120°-130°	200.2	3.3
130°-140°	224.4	3.7
140°-150°	219.9	3.6
150°-160°	184.7	3.0
160°-170°	122.8	2.0
170°-180°	43.0	0.7
0°-30°	1523.2	24.8
0°-40°	2419.7	39.4
0°-60°	4029.1	65.6
0°-90°	4877.7	79.4
90°-120°	272.4	4.4
90°-150°	916.9	14.9
90°-180°	1267.0	20.6
0°-180°	6145.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2064	2064	2064	2064	2064	
5°	2061	2054	2038	2052	2050	195
15°	1960	1949	1918	1915	1902	552
25°	1777	1752	1696	1676	1659	817
35°	1531	1492	1424	1380	1356	958
45°	1254	1206	1123	1062	1037	967
55°	951	899	814	746	719	850
65°	644	589	508	448	422	638
75°	343	295	231	198	186	363
85°	86	59	50	48	47	96
90°	0	3	6	7	8	5
95°	23	24	27	30	30	25
105°	81	82	84	87	88	86
115°	152	154	154	154	154	151
125°	222	224	225	224	224	199
135°	289	291	292	292	290	223
145°	350	352	353	353	352	219
155°	401	401	401	402	401	185
165°	436	435	435	437	435	123
175°	453	452	452	454	451	43
180°	454	454	454	454	454	



TEST NUMBER: P333614

CATALOG NUMBER: S125RDIP-S1270D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3
2.5°	2068.0	2067.2	2066.3	2065.5	2064.7	2062.9	2060.1	2057.3	2054.6	2051.8	2054.6
5°	2061.2	2059.8	2058.4	2057.0	2055.6	2053.0	2049.2	2045.4	2041.6	2037.8	2041.2
7.5°	2040.9	2039.6	2038.3	2036.9	2035.6	2032.7	2028.1	2023.5	2019.0	2014.4	2016.8
10°	2022.2	2021.1	2020.1	2019.1	2018.0	2015.1	2010.2	2005.4	2000.5	1995.7	1996.7
12.5°	2001.0	1999.7	1998.3	1997.0	1995.7	1991.8	1985.3	1978.8	1972.2	1965.7	1966.5
15°	1959.8	1957.7	1955.7	1953.6	1951.5	1946.8	1939.5	1932.3	1925.0	1917.7	1917.4
17.5°	1913.3	1910.2	1907.0	1903.8	1900.6	1894.4	1885.3	1876.1	1867.0	1857.8	1856.1
20°	1877.2	1873.7	1870.2	1866.8	1863.3	1856.0	1845.0	1833.9	1822.8	1811.7	1810.0
22.5°	1837.3	1833.8	1830.3	1826.9	1823.4	1815.9	1804.2	1792.6	1780.9	1769.3	1765.9
25°	1777.4	1772.2	1767.0	1761.8	1756.6	1747.6	1734.8	1722.0	1709.1	1696.3	1691.8
27.5°	1708.8	1702.5	1696.2	1689.9	1683.6	1673.6	1659.8	1646.1	1632.4	1618.7	1612.4
30°	1658.9	1652.3	1645.7	1639.2	1632.6	1622.0	1607.4	1592.9	1578.3	1563.8	1555.8
32.5°	1610.3	1602.6	1594.9	1587.2	1579.5	1568.2	1553.4	1538.6	1523.7	1508.9	1500.1
35°	1531.1	1522.7	1514.4	1506.1	1497.8	1485.8	1470.2	1454.7	1439.1	1423.5	1413.4
37.5°	1453.4	1443.3	1433.2	1423.1	1412.9	1399.8	1383.8	1367.7	1351.6	1335.5	1323.5
40°	1398.5	1388.1	1377.7	1367.3	1357.0	1343.4	1326.8	1310.2	1293.5	1276.9	1263.8
42.5°	1341.2	1330.5	1319.8	1309.1	1298.5	1284.5	1267.4	1250.2	1233.0	1215.8	1203.2
45°	1253.5	1243.5	1233.4	1223.4	1213.3	1198.8	1179.7	1160.7	1141.6	1122.6	1108.7
47.5°	1162.8	1152.2	1141.6	1131.0	1120.4	1105.5	1086.3	1067.1	1047.9	1028.7	1014.4
50°	1105.4	1094.0	1082.5	1071.1	1059.7	1044.1	1024.3	1004.6	984.8	965.1	950.5
52.5°	1043.0	1031.3	1019.6	1007.9	996.2	981.0	962.4	943.8	925.1	906.5	890.8
55°	951.1	940.0	928.9	917.8	906.7	891.5	872.1	852.7	833.3	813.9	798.3
57.5°	858.1	846.3	834.4	822.6	810.7	795.5	776.8	758.0	739.3	720.6	705.4
60°	798.3	786.1	774.0	761.9	749.8	734.3	715.6	696.9	678.2	659.5	644.3
62.5°	734.7	723.1	711.5	699.9	688.4	673.1	654.1	635.1	616.1	597.1	583.0
65°	643.9	632.1	620.4	608.6	596.8	581.7	563.4	545.0	526.6	508.3	494.4
67.5°	553.8	542.0	530.2	518.5	506.7	492.0	474.4	456.8	439.2	421.6	408.9
70°	492.7	480.9	469.1	457.3	445.6	431.0	413.7	396.4	379.0	361.7	351.0
72.5°	432.8	421.3	409.8	398.3	386.8	372.9	356.7	340.5	324.3	308.1	298.2
75°	343.0	332.6	322.2	311.8	301.4	289.0	274.4	259.9	245.3	230.7	223.1
77.5°	253.8	245.5	237.2	228.9	220.6	210.6	198.9	187.3	175.7	164.0	158.7
80°	202.7	194.4	186.1	177.7	169.4	160.4	150.7	141.0	131.3	121.6	118.5
82.5°	152.8	145.3	137.8	130.3	122.9	115.8	109.1	102.5	95.8	89.2	87.7
85°	85.8	79.5	73.3	67.0	60.8	56.8	55.1	53.4	51.6	49.9	49.5
87.5°	28.8	26.9	25.1	23.3	21.5	20.5	20.3	20.2	20.0	19.8	19.9
90°	0.4	1.0	1.6	2.2	2.9	3.5	4.0	4.6	5.1	5.7	6.0
92.5°	8.6	9.0	9.4	9.9	10.3	10.9	11.5	12.2	12.9	13.6	14.1
95°	23.0	23.1	23.3	23.4	23.6	24.1	24.9	25.6	26.4	27.2	27.8
97.5°	38.2	38.2	38.3	38.4	38.4	39.0	40.1	41.2	42.2	43.3	43.9
100°	49.5	49.5	49.5	49.5	49.5	50.0	51.0	52.0	53.1	54.1	54.8
102.5°	61.6	62.0	62.3	62.6	62.9	63.3	63.8	64.3	64.9	65.4	66.2
105°	80.6	81.0	81.4	81.8	82.2	82.6	83.1	83.5	84.0	84.5	84.9
107.5°	101.5	101.9	102.3	102.7	103.1	103.5	103.8	104.2	104.5	104.9	105.1
110°	115.9	116.3	116.7	117.1	117.5	117.8	118.0	118.3	118.5	118.8	119.0



TEST NUMBER: P333614

CATALOG NUMBER: S125RDIP-S1270D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	130.6	130.8	131.0	131.2	131.4	131.7	132.0	132.3	132.6	132.9	133.0
115°	152.3	152.6	153.0	153.3	153.6	153.8	154.0	154.1	154.3	154.5	154.4
117.5°	174.1	174.2	174.4	174.5	174.7	174.8	175.0	175.1	175.2	175.4	175.4
120°	187.7	188.1	188.5	188.9	189.2	189.5	189.6	189.6	189.7	189.8	189.8
122.5°	202.4	202.5	202.7	202.8	202.9	203.1	203.3	203.5	203.7	203.9	203.9
125°	222.3	222.8	223.3	223.7	224.2	224.5	224.6	224.6	224.7	224.8	224.6
127.5°	243.5	243.8	244.1	244.3	244.6	244.8	244.9	245.0	245.1	245.1	245.1
130°	256.2	256.6	257.0	257.4	257.8	258.1	258.2	258.4	258.6	258.7	258.6
132.5°	269.0	269.6	270.3	270.9	271.5	271.9	271.8	271.8	271.8	271.7	271.6
135°	289.1	289.6	290.1	290.5	291.0	291.3	291.4	291.4	291.5	291.6	291.6
137.5°	308.1	308.5	309.0	309.4	309.9	310.2	310.4	310.5	310.7	310.9	311.0
140°	320.2	320.6	321.0	321.4	321.8	322.1	322.3	322.6	322.8	323.0	323.2
142.5°	332.4	332.7	333.0	333.4	333.7	334.0	334.3	334.6	334.9	335.2	335.3
145°	350.3	350.6	350.9	351.2	351.5	351.8	352.0	352.3	352.5	352.7	352.7
147.5°	366.8	367.0	367.1	367.3	367.5	367.7	367.9	368.1	368.2	368.4	368.6
150°	377.8	377.8	377.7	377.6	377.5	377.6	377.9	378.3	378.6	378.9	378.9
152.5°	386.9	387.0	387.1	387.2	387.3	387.4	387.6	387.7	387.8	387.9	388.1
155°	400.8	400.8	400.8	400.8	400.8	400.8	400.9	401.0	401.1	401.2	401.5
157.5°	413.2	413.1	412.9	412.7	412.6	412.5	412.6	412.7	412.7	412.8	413.1
160°	420.6	420.4	420.1	419.9	419.7	419.6	419.7	419.7	419.8	419.9	420.2
162.5°	427.1	426.9	426.8	426.6	426.4	426.3	426.3	426.4	426.4	426.4	426.8
165°	435.8	435.6	435.5	435.3	435.2	435.1	435.2	435.3	435.4	435.4	435.8
167.5°	443.1	442.8	442.5	442.2	441.9	441.7	441.7	441.7	441.7	441.7	442.2
170°	447.1	446.8	446.5	446.2	445.8	445.7	445.7	445.7	445.7	445.7	446.2
172.5°	449.9	449.6	449.3	449.0	448.7	448.5	448.5	448.5	448.5	448.5	449.0
175°	453.1	452.8	452.5	452.2	451.9	451.7	451.7	451.7	451.7	451.7	452.2
177.5°	454.7	454.5	454.2	454.0	453.7	453.6	453.5	453.5	453.4	453.3	453.7
180°	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2



TEST NUMBER: P333614

CATALOG NUMBER: S125RDIP-S1270D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3
2.5°	2057.3	2060.1	2062.9	2064.1	2063.9	2063.6	2063.3	2063.0
5°	2044.7	2048.2	2051.6	2053.0	2052.3	2051.6	2050.9	2050.2
7.5°	2019.2	2021.7	2024.1	2024.9	2024.1	2023.4	2022.6	2021.9
10°	1997.7	1998.8	1999.8	1999.8	1998.8	1997.7	1996.7	1995.7
12.5°	1967.3	1968.0	1968.8	1968.4	1966.8	1965.2	1963.6	1962.0
15°	1917.0	1916.7	1916.3	1914.6	1911.5	1908.4	1905.2	1902.1
17.5°	1854.4	1852.6	1850.9	1848.8	1846.2	1843.6	1841.1	1838.5
20°	1808.2	1806.5	1804.8	1802.3	1799.2	1796.1	1793.0	1789.9
22.5°	1762.5	1759.1	1755.7	1752.7	1750.2	1747.6	1745.0	1742.5
25°	1687.3	1682.8	1678.3	1674.1	1670.3	1666.5	1662.7	1658.9
27.5°	1606.1	1599.8	1593.5	1588.5	1584.8	1581.1	1577.4	1573.8
30°	1547.9	1539.9	1531.9	1526.4	1523.3	1520.1	1517.0	1513.9
32.5°	1491.3	1482.5	1473.7	1467.3	1463.4	1459.4	1455.5	1451.5
35°	1403.4	1393.3	1383.3	1375.8	1371.0	1366.1	1361.3	1356.4
37.5°	1311.4	1299.4	1287.3	1278.9	1274.2	1269.5	1264.8	1260.1
40°	1250.6	1237.4	1224.3	1215.6	1211.4	1207.3	1203.1	1199.0
42.5°	1190.6	1178.0	1165.4	1156.0	1149.9	1143.8	1137.7	1131.6
45°	1094.8	1081.0	1067.1	1057.6	1052.4	1047.2	1042.0	1036.8
47.5°	1000.2	985.9	971.6	961.6	955.8	950.1	944.3	938.6
50°	936.0	921.4	906.9	897.0	891.8	886.6	881.4	876.2
52.5°	875.1	859.5	843.8	833.4	828.2	823.0	817.8	812.6
55°	782.7	767.1	751.5	740.9	735.4	729.8	724.3	718.8
57.5°	690.1	674.9	659.6	649.6	644.6	639.7	634.8	629.9
60°	629.0	613.8	598.5	588.3	583.1	577.9	572.7	567.5
62.5°	568.9	554.7	540.6	530.9	525.7	520.5	515.3	510.1
65°	480.6	466.7	452.8	443.3	438.1	432.9	427.7	422.5
67.5°	396.2	383.5	370.9	362.4	358.3	354.1	350.0	345.8
70°	340.2	329.5	318.8	311.3	307.1	303.0	298.8	294.7
72.5°	288.3	278.4	268.4	262.1	259.3	256.6	253.8	251.0
75°	215.5	207.9	200.3	195.2	192.8	190.4	188.0	185.5
77.5°	153.3	148.0	142.7	139.1	137.3	135.5	133.7	131.9
80°	115.4	112.3	109.1	107.2	106.5	105.8	105.2	104.5
82.5°	86.3	84.8	83.4	82.4	82.0	81.6	81.2	80.8
85°	49.2	48.9	48.5	48.2	47.8	47.5	47.1	46.8
87.5°	20.0	20.1	20.2	20.1	19.8	19.6	19.4	19.2
90°	6.4	6.8	7.2	7.5	7.8	8.0	8.2	8.5
92.5°	14.6	15.1	15.6	16.0	16.2	16.3	16.5	16.7
95°	28.3	28.9	29.4	29.8	29.9	30.1	30.2	30.4
97.5°	44.4	44.9	45.4	45.7	45.8	45.9	46.0	46.1
100°	55.5	56.2	56.9	57.3	57.5	57.7	57.8	58.0
102.5°	66.9	67.7	68.5	69.0	69.2	69.4	69.6	69.8
105°	85.4	85.9	86.4	86.7	86.9	87.2	87.4	87.7
107.5°	105.4	105.6	105.8	106.0	105.9	105.9	105.9	105.9
110°	119.2	119.5	119.7	119.8	119.7	119.6	119.5	119.5



TEST NUMBER: P333614

CATALOG NUMBER: S125RDIP-S1270D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	133.1	133.2	133.3	133.3	133.2	133.0	132.9	132.8
115°	154.3	154.2	154.1	154.1	154.0	153.9	153.8	153.7
117.5°	175.5	175.6	175.6	175.5	175.2	174.9	174.6	174.2
120°	189.8	189.8	189.8	189.6	189.3	189.0	188.7	188.4
122.5°	203.8	203.7	203.7	203.5	203.3	203.0	202.8	202.5
125°	224.5	224.3	224.2	224.0	224.0	223.9	223.8	223.7
127.5°	245.0	244.9	244.8	244.7	244.6	244.4	244.2	244.1
130°	258.6	258.5	258.4	258.3	258.1	258.0	257.8	257.7
132.5°	271.6	271.5	271.4	271.3	271.0	270.8	270.6	270.4
135°	291.6	291.6	291.6	291.4	291.1	290.8	290.5	290.2
137.5°	311.1	311.2	311.3	311.1	310.7	310.3	309.9	309.5
140°	323.4	323.5	323.7	323.6	323.2	322.8	322.4	322.0
142.5°	335.4	335.5	335.6	335.4	335.0	334.6	334.3	333.9
145°	352.7	352.7	352.7	352.6	352.4	352.1	351.9	351.7
147.5°	368.8	369.0	369.2	369.0	368.5	367.9	367.4	366.9
150°	378.9	378.9	378.9	378.8	378.7	378.5	378.3	378.2
152.5°	388.3	388.5	388.7	388.6	388.4	388.1	387.8	387.5
155°	401.8	402.1	402.4	402.4	402.0	401.6	401.2	400.8
157.5°	413.4	413.8	414.1	414.0	413.5	412.9	412.4	411.9
160°	420.5	420.8	421.1	421.1	420.7	420.3	419.9	419.5
162.5°	427.1	427.5	427.9	427.9	427.4	426.9	426.5	426.0
165°	436.1	436.4	436.7	436.6	436.1	435.7	435.2	434.7
167.5°	442.7	443.1	443.6	443.6	443.1	442.6	442.1	441.7
170°	446.6	447.1	447.6	447.5	447.0	446.4	445.9	445.3
172.5°	449.5	449.9	450.4	450.4	449.9	449.4	448.9	448.4
175°	452.6	453.1	453.6	453.5	453.0	452.4	451.9	451.3
177.5°	454.1	454.5	454.8	454.8	454.4	453.9	453.5	453.0
180°	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2

(END OF REPORT)