

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333615

Luminaire Tested: **S125RDIP-S1270D365U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333615
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D365U835-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6192.3 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333615

CATALOG NUMBER: S125RDIP-S1270D365U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333615

CATALOG NUMBER: S125RDIP-S1270D365U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83	79
1	105	100	96	93	100	96	92	89	88	85	83	80	78	76	74	72	71	67
2	96	88	82	76	91	84	79	74	77	73	69	71	67	64	65	62	60	57
3	87	78	70	64	83	75	68	62	69	63	58	63	59	55	58	54	51	48
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	52	48	45	42
5	74	62	53	47	70	60	52	46	55	49	44	51	46	41	47	43	39	36
6	68	56	47	41	65	54	46	40	50	43	38	46	41	36	43	38	35	32
7	63	51	42	37	60	49	41	36	45	39	34	42	37	32	39	34	31	29
8	59	46	38	33	56	45	37	32	42	35	31	39	33	29	36	31	28	26
9	55	42	35	29	53	41	34	29	38	32	28	36	30	26	33	29	25	23
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13332	13332	13332
5°	13363	13211	13291
10°	13262	13088	13088
15°	13104	12822	12718
20°	12902	12451	12302
25°	12666	12088	11821
30°	12371	11662	11290
35°	12071	11223	10694
40°	11790	10765	10108
45°	11449	10253	9470
50°	11106	9697	8804
55°	10709	9164	8094
60°	10311	8519	7330
65°	9840	7768	6457
70°	9304	6830	5565
75°	8559	5757	4629
80°	7539	4523	3887
85°	6358	3698	3468



TEST NUMBER: P333615

CATALOG NUMBER: S125RDIP-S1270D365U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.1	3.1
10°-20°	542.5	8.8
20°-30°	786.6	12.7
30°-40°	896.5	14.5
40°-50°	873.9	14.1
50°-60°	735.6	11.9
60°-70°	515.6	8.3
70°-80°	265.0	4.3
80°-90°	67.9	1.1
90°-100°	127.1	2.1
100°-110°	273.1	4.4
110°-120°	256.3	4.1
120°-130°	207.7	3.4
130°-140°	166.7	2.7
140°-150°	125.8	2.0
150°-160°	88.6	1.4
160°-170°	52.2	0.8
170°-180°	17.0	0.3
0°-30°	1523.2	24.6
0°-40°	2419.7	39.1
0°-60°	4029.1	65.1
0°-90°	4877.7	78.8
90°-120°	656.5	10.6
90°-150°	1156.8	18.7
90°-180°	1315.0	21.2
0°-180°	6192.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2064	2064	2064	2064	2064	
5°	2061	2054	2038	2052	2050	195
15°	1960	1949	1918	1915	1902	552
25°	1777	1752	1696	1676	1659	817
35°	1531	1492	1424	1380	1356	958
45°	1254	1206	1123	1062	1037	967
55°	951	899	814	746	719	850
65°	644	589	508	448	422	638
75°	343	295	231	198	186	363
85°	86	59	50	48	47	96
90°	0	3	6	7	8	5
95°	12	34	313	142	83	12
105°	40	56	256	504	468	42
115°	71	86	206	443	522	70
125°	99	116	197	353	411	88
135°	116	139	196	296	341	90
145°	135	155	196	245	269	85
155°	154	166	192	216	226	71
165°	168	173	184	195	198	47
175°	175	175	176	178	178	17
180°	175	175	175	175	175	



TEST NUMBER: P333615

CATALOG NUMBER: S125RDIP-S1270D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3
2.5°	2068.0	2067.2	2066.3	2065.5	2064.7	2062.9	2060.1	2057.3	2054.6	2051.8	2054.6
5°	2061.2	2059.8	2058.4	2057.0	2055.6	2053.0	2049.2	2045.4	2041.6	2037.8	2041.2
7.5°	2040.9	2039.6	2038.3	2036.9	2035.6	2032.7	2028.1	2023.5	2019.0	2014.4	2016.8
10°	2022.2	2021.1	2020.1	2019.1	2018.0	2015.1	2010.2	2005.4	2000.5	1995.7	1996.7
12.5°	2001.0	1999.7	1998.3	1997.0	1995.7	1991.8	1985.3	1978.8	1972.2	1965.7	1966.5
15°	1959.8	1957.7	1955.7	1953.6	1951.5	1946.8	1939.5	1932.3	1925.0	1917.7	1917.4
17.5°	1913.3	1910.2	1907.0	1903.8	1900.6	1894.4	1885.3	1876.1	1867.0	1857.8	1856.1
20°	1877.2	1873.7	1870.2	1866.8	1863.3	1856.0	1845.0	1833.9	1822.8	1811.7	1810.0
22.5°	1837.3	1833.8	1830.3	1826.9	1823.4	1815.9	1804.2	1792.6	1780.9	1769.3	1765.9
25°	1777.4	1772.2	1767.0	1761.8	1756.6	1747.6	1734.8	1722.0	1709.1	1696.3	1691.8
27.5°	1708.8	1702.5	1696.2	1689.9	1683.6	1673.6	1659.8	1646.1	1632.4	1618.7	1612.4
30°	1658.9	1652.3	1645.7	1639.2	1632.6	1622.0	1607.4	1592.9	1578.3	1563.8	1555.8
32.5°	1610.3	1602.6	1594.9	1587.2	1579.5	1568.2	1553.4	1538.6	1523.7	1508.9	1500.1
35°	1531.1	1522.7	1514.4	1506.1	1497.8	1485.8	1470.2	1454.7	1439.1	1423.5	1413.4
37.5°	1453.4	1443.3	1433.2	1423.1	1412.9	1399.8	1383.8	1367.7	1351.6	1335.5	1323.5
40°	1398.5	1388.1	1377.7	1367.3	1357.0	1343.4	1326.8	1310.2	1293.5	1276.9	1263.8
42.5°	1341.2	1330.5	1319.8	1309.1	1298.5	1284.5	1267.4	1250.2	1233.0	1215.8	1203.2
45°	1253.5	1243.5	1233.4	1223.4	1213.3	1198.8	1179.7	1160.7	1141.6	1122.6	1108.7
47.5°	1162.8	1152.2	1141.6	1131.0	1120.4	1105.5	1086.3	1067.1	1047.9	1028.7	1014.4
50°	1105.4	1094.0	1082.5	1071.1	1059.7	1044.1	1024.3	1004.6	984.8	965.1	950.5
52.5°	1043.0	1031.3	1019.6	1007.9	996.2	981.0	962.4	943.8	925.1	906.5	890.8
55°	951.1	940.0	928.9	917.8	906.7	891.5	872.1	852.7	833.3	813.9	798.3
57.5°	858.1	846.3	834.4	822.6	810.7	795.5	776.8	758.0	739.3	720.6	705.4
60°	798.3	786.1	774.0	761.9	749.8	734.3	715.6	696.9	678.2	659.5	644.3
62.5°	734.7	723.1	711.5	699.9	688.4	673.1	654.1	635.1	616.1	597.1	583.0
65°	643.9	632.1	620.4	608.6	596.8	581.7	563.4	545.0	526.6	508.3	494.4
67.5°	553.8	542.0	530.2	518.5	506.7	492.0	474.4	456.8	439.2	421.6	408.9
70°	492.7	480.9	469.1	457.3	445.6	431.0	413.7	396.4	379.0	361.7	351.0
72.5°	432.8	421.3	409.8	398.3	386.8	372.9	356.7	340.5	324.3	308.1	298.2
75°	343.0	332.6	322.2	311.8	301.4	289.0	274.4	259.9	245.3	230.7	223.1
77.5°	253.8	245.5	237.2	228.9	220.6	210.6	198.9	187.3	175.7	164.0	158.7
80°	202.7	194.4	186.1	177.7	169.4	160.4	150.7	141.0	131.3	121.6	118.5
82.5°	152.8	145.3	137.8	130.3	122.9	115.8	109.1	102.5	95.8	89.2	87.7
85°	85.8	79.5	73.3	67.0	60.8	56.8	55.1	53.4	51.6	49.9	49.5
87.5°	28.8	26.9	25.1	23.3	21.5	20.5	20.3	20.2	20.0	19.8	19.9
90°	0.4	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.7	6.0
92.5°	4.3	5.2	8.2	12.6	18.7	29.0	48.3	80.6	115.8	113.9	92.2
95°	11.7	12.0	14.8	18.7	26.5	42.4	80.2	158.0	255.5	313.1	306.4
97.5°	19.4	19.8	21.8	25.7	32.7	44.1	69.1	126.1	228.2	334.4	387.7
100°	24.7	25.4	26.9	30.7	37.5	48.1	68.6	114.5	203.6	319.1	407.5
102.5°	30.7	31.1	32.2	36.4	42.6	52.9	71.1	109.7	184.9	292.3	395.6
105°	39.9	39.9	41.7	45.2	50.9	60.8	76.3	107.8	166.8	256.2	357.7
107.5°	49.0	49.7	51.4	54.3	60.2	69.1	84.1	111.0	159.2	231.4	318.9
110°	55.5	56.2	57.6	60.8	66.1	75.3	89.8	114.2	156.9	219.8	296.9



TEST NUMBER: P333615

CATALOG NUMBER: S125RDIP-S1270D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.0	62.7	63.8	67.0	72.3	81.2	95.1	118.1	156.9	213.0	280.5
115°	71.4	72.1	73.2	76.3	81.6	90.5	103.6	124.0	158.0	205.7	262.6
117.5°	79.9	80.9	82.1	85.2	91.3	99.8	112.2	130.8	160.3	202.1	251.9
120°	85.5	86.6	88.0	91.2	97.2	106.0	118.4	135.4	162.6	200.4	246.0
122.5°	91.5	92.2	93.4	96.6	103.1	112.0	124.3	140.4	164.5	199.0	240.9
125°	99.0	99.7	101.4	104.6	111.3	120.5	132.2	147.4	167.9	197.2	234.0
127.5°	104.8	105.9	108.1	112.2	119.3	128.5	139.7	153.7	171.6	196.4	227.6
130°	108.5	109.6	112.4	117.0	124.4	133.6	144.5	158.0	173.9	195.8	223.4
132.5°	111.3	112.7	116.1	121.2	128.9	138.1	149.1	161.7	176.4	195.8	220.0
135°	115.9	117.3	121.6	127.2	134.7	144.2	155.1	166.8	179.9	195.8	215.9
137.5°	121.7	122.8	126.7	132.4	139.7	149.5	159.5	170.6	183.1	196.2	212.3
140°	125.1	126.2	130.4	136.1	142.8	152.3	162.6	173.2	184.5	196.5	210.6
142.5°	129.1	129.8	133.8	139.5	145.9	154.9	164.5	174.6	185.3	196.8	209.2
145°	135.0	135.7	139.2	144.2	150.6	158.7	167.9	176.7	186.2	196.5	207.1
147.5°	141.2	141.6	144.7	149.3	154.8	161.9	170.0	178.0	186.6	195.6	204.9
150°	144.9	145.6	148.1	152.7	157.6	163.6	171.4	178.8	186.6	194.7	203.2
152.5°	148.9	149.3	151.5	155.5	160.2	165.6	172.8	179.4	186.3	193.6	201.2
155°	154.1	154.1	156.2	159.7	163.3	168.2	174.2	179.9	185.5	191.6	197.9
157.5°	158.8	158.7	160.4	163.4	166.5	170.3	175.4	180.2	184.6	189.4	194.8
160°	161.9	161.5	162.9	165.4	168.2	171.4	176.0	180.2	183.8	188.0	192.3
162.5°	164.4	164.1	165.5	167.7	169.9	172.5	176.6	180.0	182.9	186.3	190.0
165°	168.2	167.5	168.6	170.3	171.8	173.9	176.7	179.5	181.7	183.8	186.6
167.5°	170.8	170.4	171.1	172.0	173.0	174.4	176.7	178.7	179.7	181.3	183.3
170°	172.5	172.1	172.5	173.2	173.9	174.9	176.7	178.1	178.8	179.9	181.3
172.5°	173.6	173.0	173.3	174.0	174.4	174.9	176.4	177.6	177.7	178.2	179.3
175°	174.9	174.2	174.6	174.9	174.9	174.9	176.0	176.7	176.4	176.4	176.7
177.5°	175.6	175.0	175.0	175.3	175.0	175.0	175.6	175.9	175.3	175.3	175.6
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333615

CATALOG NUMBER: S125RDIP-S1270D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3
2.5°	2057.3	2060.1	2062.9	2064.1	2063.9	2063.6	2063.3	2063.0
5°	2044.7	2048.2	2051.6	2053.0	2052.3	2051.6	2050.9	2050.2
7.5°	2019.2	2021.7	2024.1	2024.9	2024.1	2023.4	2022.6	2021.9
10°	1997.7	1998.8	1999.8	1999.8	1998.8	1997.7	1996.7	1995.7
12.5°	1967.3	1968.0	1968.8	1968.4	1966.8	1965.2	1963.6	1962.0
15°	1917.0	1916.7	1916.3	1914.6	1911.5	1908.4	1905.2	1902.1
17.5°	1854.4	1852.6	1850.9	1848.8	1846.2	1843.6	1841.1	1838.5
20°	1808.2	1806.5	1804.8	1802.3	1799.2	1796.1	1793.0	1789.9
22.5°	1762.5	1759.1	1755.7	1752.7	1750.2	1747.6	1745.0	1742.5
25°	1687.3	1682.8	1678.3	1674.1	1670.3	1666.5	1662.7	1658.9
27.5°	1606.1	1599.8	1593.5	1588.5	1584.8	1581.1	1577.4	1573.8
30°	1547.9	1539.9	1531.9	1526.4	1523.3	1520.1	1517.0	1513.9
32.5°	1491.3	1482.5	1473.7	1467.3	1463.4	1459.4	1455.5	1451.5
35°	1403.4	1393.3	1383.3	1375.8	1371.0	1366.1	1361.3	1356.4
37.5°	1311.4	1299.4	1287.3	1278.9	1274.2	1269.5	1264.8	1260.1
40°	1250.6	1237.4	1224.3	1215.6	1211.4	1207.3	1203.1	1199.0
42.5°	1190.6	1178.0	1165.4	1156.0	1149.9	1143.8	1137.7	1131.6
45°	1094.8	1081.0	1067.1	1057.6	1052.4	1047.2	1042.0	1036.8
47.5°	1000.2	985.9	971.6	961.6	955.8	950.1	944.3	938.6
50°	936.0	921.4	906.9	897.0	891.8	886.6	881.4	876.2
52.5°	875.1	859.5	843.8	833.4	828.2	823.0	817.8	812.6
55°	782.7	767.1	751.5	740.9	735.4	729.8	724.3	718.8
57.5°	690.1	674.9	659.6	649.6	644.6	639.7	634.8	629.9
60°	629.0	613.8	598.5	588.3	583.1	577.9	572.7	567.5
62.5°	568.9	554.7	540.6	530.9	525.7	520.5	515.3	510.1
65°	480.6	466.7	452.8	443.3	438.1	432.9	427.7	422.5
67.5°	396.2	383.5	370.9	362.4	358.3	354.1	350.0	345.8
70°	340.2	329.5	318.8	311.3	307.1	303.0	298.8	294.7
72.5°	288.3	278.4	268.4	262.1	259.3	256.6	253.8	251.0
75°	215.5	207.9	200.3	195.2	192.8	190.4	188.0	185.5
77.5°	153.3	148.0	142.7	139.1	137.3	135.5	133.7	131.9
80°	115.4	112.3	109.1	107.2	106.5	105.8	105.2	104.5
82.5°	86.3	84.8	83.4	82.4	82.0	81.6	81.2	80.8
85°	49.2	48.9	48.5	48.2	47.8	47.5	47.1	46.8
87.5°	20.0	20.1	20.1	20.1	19.8	19.6	19.4	19.1
90°	6.4	6.7	7.1	7.8	7.8	7.8	8.1	8.1
92.5°	62.6	45.4	34.2	29.0	24.5	23.6	23.1	22.5
95°	254.1	200.4	156.9	127.2	102.1	91.5	88.7	83.1
97.5°	378.4	340.8	298.4	257.1	235.3	215.5	205.3	200.7
100°	434.7	417.4	381.0	344.2	319.8	294.4	281.3	275.7
102.5°	453.6	464.3	446.9	422.0	395.9	377.8	363.6	359.4
105°	442.5	490.9	506.4	502.6	491.2	479.6	472.5	468.3
107.5°	402.6	467.2	507.1	525.6	531.3	531.3	528.9	526.1
110°	373.2	440.4	490.2	520.2	536.1	542.8	545.3	545.3



TEST NUMBER: P333615

CATALOG NUMBER: S125RDIP-S1270D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	350.0	413.8	464.2	499.6	522.8	534.4	540.5	543.1
115°	320.9	375.7	424.1	462.6	490.2	507.1	517.0	521.6
117.5°	302.1	349.3	391.0	426.4	453.9	471.5	481.3	484.1
120°	291.9	334.3	373.2	404.3	430.5	447.4	457.0	459.8
122.5°	284.3	323.6	358.2	387.3	410.7	426.2	435.8	438.3
125°	273.2	309.2	340.0	365.4	385.2	399.7	407.5	411.0
127.5°	261.9	295.5	324.2	348.0	366.0	378.8	386.1	387.7
130°	254.8	285.9	313.5	336.5	354.1	365.8	372.9	375.0
132.5°	247.7	276.9	301.9	324.0	341.7	353.3	359.8	362.2
135°	238.6	262.9	285.6	305.7	321.3	332.9	339.3	341.4
137.5°	230.8	250.5	269.3	286.4	300.3	310.9	316.8	319.1
140°	226.5	243.1	259.4	274.2	287.3	296.5	301.8	303.6
142.5°	222.9	236.9	250.9	263.8	274.9	282.7	287.7	289.2
145°	218.1	229.0	240.0	249.5	258.0	264.0	267.9	269.3
147.5°	213.5	222.4	230.9	238.1	244.8	249.6	251.8	252.5
150°	211.0	218.8	225.5	231.8	237.1	241.4	242.8	243.1
152.5°	208.2	215.1	221.2	226.2	230.6	234.0	235.4	235.8
155°	203.9	209.6	214.5	218.4	221.9	224.4	225.5	225.8
157.5°	199.7	204.3	208.2	211.2	214.0	216.0	217.0	216.9
160°	196.9	200.4	203.9	206.4	208.9	210.6	211.3	211.0
162.5°	193.7	197.0	200.0	202.2	204.1	205.5	205.7	205.6
165°	189.4	191.9	194.0	195.8	197.2	197.9	197.9	197.9
167.5°	185.3	187.0	188.6	189.9	190.6	191.2	190.9	190.8
170°	183.1	184.1	185.2	185.9	186.6	187.0	187.0	186.6
172.5°	180.5	181.6	182.4	182.8	182.9	183.6	183.0	182.6
175°	177.8	177.8	178.5	178.5	178.5	178.8	178.1	177.8
177.5°	175.9	176.1	176.1	176.1	175.9	176.1	175.3	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3

(END OF REPORT)