

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333622

Luminaire Tested: **S125RDIP-S1270D810U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333622  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D810U835-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8161.6 lumens  
Efficiency: N/A  
Efficacy: 134.5 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	101	96	93	89	94	90	87	84	79	77	74	68	67	65	59	58	56	52
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	52	50	48	44
3	84	75	68	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38
4	77	67	59	53	72	63	56	50	55	50	45	48	44	41	42	39	36	33
5	71	60	51	46	66	56	49	44	50	44	39	44	39	36	38	35	32	29
6	66	54	46	40	61	51	43	38	45	39	35	40	35	31	35	31	28	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20
9	53	40	33	28	49	38	31	27	34	29	25	30	26	22	27	23	20	18
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	18	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12264	12264	12264	12264
5°	14110	12280	10845	12280
10°	16184	12218	9569	12218
15°	17481	12092	8506	12092
20°	19276	11947	7854	11947
25°	22308	11754	7288	11754
30°	24276	11551	6918	11551
35°	20478	11315	6576	11315
40°	14300	10890	6283	10890
45°	10609	10316	5994	10316
50°	8459	9720	5749	9720
55°	7179	8979	5530	8979
60°	6203	8317	5176	8317
65°	5527	7600	4455	7600
70°	4857	6962	4062	6962
75°	4202	6029	3813	6029
80°	3187	5073	3187	5073
85°	2660	3987	3001	3987



TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.1	2.2
10°-20°	533.6	6.5
20°-30°	846.1	10.4
30°-40°	1020.3	12.5
40°-50°	911.2	11.2
50°-60°	698.8	8.6
60°-70°	454.1	5.6
70°-80°	220.8	2.7
80°-90°	54.9	0.7
90°-100°	38.3	0.5
100°-110°	236.3	2.9
110°-120°	428.5	5.3
120°-130°	550.0	6.7
130°-140°	591.5	7.2
140°-150°	555.2	6.8
150°-160°	449.1	5.5
160°-170°	290.5	3.6
170°-180°	100.2	1.2
0°-30°	1561.8	19.1
0°-40°	2582.2	31.6
0°-60°	4192.1	51.4
0°-90°	4921.9	60.3
90°-120°	703.1	8.6
90°-150°	2399.9	29.4
90°-180°	3240.0	39.7
0°-180°	8161.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2176	1894	1673	1894	2176	217
15°	2614	1808	1272	1808	2614	749
25°	3130	1649	1023	1649	3130	1437
35°	2597	1435	834	1435	2597	1569
45°	1162	1130	656	1130	1162	927
55°	638	797	491	797	638	579
65°	362	497	292	497	362	360
75°	168	242	153	242	168	179
85°	36	54	40	54	36	42
90°	19	1	19	1	19	10
95°	16	45	16	45	16	14
105°	232	230	232	230	232	210
115°	429	432	429	432	429	425
125°	614	614	614	614	614	546
135°	762	766	762	766	762	588
145°	885	888	885	888	885	553
155°	970	978	970	978	970	447
165°	1026	1032	1026	1032	1026	290
175°	1050	1055	1050	1055	1050	100
180°	1055	1055	1055	1055	1055	



TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1997.4	1996.2	1998.7	1991.8	1992.4	1981.8	1981.8	1973.7	1963.1	1955.0	1951.3
5°	2176.4	2178.0	2174.8	2163.1	2155.4	2143.7	2130.4	2107.0	2087.5	2068.8	2054.0
7.5°	2360.7	2361.8	2351.5	2347.9	2328.2	2313.9	2284.4	2252.6	2224.4	2188.6	2161.1
10°	2467.9	2467.2	2456.2	2447.7	2430.5	2408.7	2379.9	2342.4	2307.4	2268.4	2231.0
12.5°	2530.3	2528.3	2524.8	2514.4	2498.5	2479.2	2454.7	2417.9	2374.7	2332.0	2288.3
15°	2614.5	2609.0	2598.9	2585.6	2563.0	2540.4	2513.1	2480.4	2439.1	2390.8	2350.2
17.5°	2718.6	2718.8	2703.2	2684.8	2654.1	2614.2	2572.1	2519.2	2463.1	2409.9	2366.8
20°	2804.7	2802.3	2786.8	2750.9	2715.8	2665.9	2617.6	2552.9	2484.3	2414.9	2361.1
22.5°	2928.2	2922.1	2905.9	2858.8	2804.4	2740.1	2666.2	2587.2	2504.3	2425.5	2354.9
25°	3130.5	3125.8	3093.9	3039.3	2962.9	2863.9	2767.3	2658.9	2539.7	2436.0	2350.2
27.5°	3269.0	3263.8	3240.1	3194.8	3124.3	3020.1	2889.3	2744.5	2595.6	2453.0	2329.3
30°	3255.2	3266.9	3263.8	3242.8	3189.8	3096.2	2975.4	2812.5	2635.5	2467.9	2320.6
32.5°	3059.4	3069.9	3097.3	3138.6	3141.7	3104.3	3014.1	2863.6	2680.4	2489.8	2313.7
35°	2597.3	2611.4	2664.4	2747.8	2856.9	2948.1	2966.8	2885.8	2721.3	2516.3	2303.5
37.5°	1996.8	2073.5	2118.1	2205.9	2370.8	2538.6	2699.9	2759.3	2689.3	2505.4	2286.8
40°	1696.2	1714.9	1794.4	1893.4	2032.2	2206.8	2436.8	2602.8	2608.2	2480.4	2260.6
42.5°	1451.8	1475.5	1530.0	1609.1	1727.9	1902.5	2139.9	2359.0	2460.5	2411.8	2226.3
45°	1161.5	1179.4	1219.2	1280.0	1371.2	1515.4	1719.6	1972.9	2174.1	2252.8	2134.3
47.5°	954.1	963.8	998.4	1044.7	1112.2	1217.3	1375.4	1595.3	1836.5	2005.7	1989.0
50°	841.9	852.8	879.3	914.4	971.3	1060.1	1186.4	1369.6	1618.3	1824.8	1866.2
52.5°	754.6	763.6	780.1	813.3	860.3	928.6	1030.5	1196.2	1420.0	1639.6	1735.2
55°	637.6	643.9	657.1	675.8	713.3	762.4	850.4	965.0	1145.9	1367.3	1507.6
57.5°	541.3	544.4	552.8	570.1	596.0	631.9	695.5	792.6	922.3	1121.7	1276.5
60°	480.2	483.3	494.2	505.9	526.2	558.9	608.8	676.6	801.3	965.8	1122.5
62.5°	431.5	433.4	438.1	449.8	467.6	492.8	532.1	587.4	686.6	831.1	979.1
65°	361.7	362.5	364.0	373.4	384.3	403.0	428.7	467.7	542.5	651.7	782.6
67.5°	294.7	295.7	301.2	304.5	315.9	325.7	340.8	370.6	423.3	496.9	598.7
70°	257.2	256.5	261.9	265.8	269.7	281.4	291.5	315.7	348.4	404.6	489.5
72.5°	222.3	220.3	222.6	224.0	229.2	237.1	247.3	262.1	287.3	326.0	391.0
75°	168.4	169.2	169.2	170.7	174.6	177.7	180.8	188.6	202.7	228.4	263.5
77.5°	118.2	116.9	120.2	120.7	123.0	126.4	129.1	132.2	138.0	148.6	166.7
80°	85.7	85.7	86.5	88.9	88.1	89.6	93.5	96.7	103.7	109.9	116.1
82.5°	65.8	65.2	65.9	66.4	66.3	67.8	69.2	69.8	72.5	75.6	80.0
85°	35.9	35.9	36.6	36.6	37.4	37.4	38.2	38.2	38.2	39.0	39.8
87.5°	17.5	16.7	16.0	15.9	16.4	17.5	16.7	15.9	15.8	15.6	16.0
90°	18.8	18.2	17.7	17.2	16.7	16.0	15.1	14.3	13.4	12.5	11.3
92.5°	17.5	17.3	17.0	16.8	16.5	16.0	15.1	14.3	13.4	12.5	11.4
95°	16.4	16.4	16.4	16.4	16.4	16.0	15.1	14.3	13.4	12.5	19.1
97.5°	16.4	16.4	16.4	16.4	16.4	18.9	23.8	28.7	33.6	38.5	51.5
100°	16.4	17.1	17.8	18.5	19.2	32.5	58.4	84.3	110.2	136.1	135.4
102.5°	98.4	110.2	122.0	133.8	145.7	154.0	158.9	163.8	168.7	173.6	173.2
105°	232.3	232.4	232.6	232.8	233.0	233.0	233.0	233.0	233.0	233.0	233.0
107.5°	292.8	293.3	293.8	294.4	294.9	295.1	295.1	295.1	295.0	295.0	294.6
110°	334.7	334.5	334.4	334.2	334.0	334.2	334.7	335.2	335.8	336.3	335.9



TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	372.3	372.5	372.7	373.0	373.2	373.7	374.3	375.0	375.7	376.3	376.1
115°	428.6	429.6	430.6	431.7	432.7	433.6	434.3	435.0	435.7	436.4	436.2
117.5°	488.6	489.1	489.5	490.0	490.4	491.1	492.0	492.9	493.8	494.7	494.1
120°	525.5	526.4	527.3	528.1	529.0	529.6	530.0	530.3	530.7	531.0	530.5
122.5°	560.6	561.6	562.6	563.6	564.6	565.3	565.6	566.0	566.3	566.7	566.4
125°	613.9	614.4	614.9	615.5	616.0	616.6	617.3	618.0	618.7	619.4	619.4
127.5°	658.8	660.1	661.4	662.7	663.9	664.8	665.2	665.5	665.9	666.3	666.4
130°	691.3	692.2	693.1	693.9	694.8	695.5	696.0	696.5	697.1	697.6	697.4
132.5°	721.4	722.2	723.1	724.0	724.8	725.3	725.4	725.5	725.6	725.7	726.1
135°	762.5	763.5	764.6	765.6	766.7	767.4	767.7	768.1	768.4	768.8	769.1
137.5°	803.8	804.7	805.6	806.5	807.4	807.8	807.7	807.7	807.6	807.5	807.9
140°	828.2	829.2	830.3	831.3	832.4	832.7	832.4	832.0	831.7	831.3	831.5
142.5°	851.3	852.4	853.4	854.5	855.5	856.0	855.9	855.9	855.8	855.7	855.5
145°	885.3	886.3	887.4	888.4	889.4	889.9	889.7	889.5	889.4	889.2	889.2
147.5°	913.3	914.5	915.8	917.0	918.3	918.8	918.6	918.4	918.2	918.0	917.8
150°	931.4	932.8	934.2	935.6	937.0	937.5	937.2	936.8	936.5	936.1	935.8
152.5°	948.3	949.6	950.8	952.1	953.3	953.8	953.4	953.1	952.7	952.4	952.0
155°	970.5	971.9	973.3	974.7	976.1	976.5	976.0	975.5	974.9	974.4	974.1
157.5°	989.1	990.5	991.9	993.3	994.7	995.1	994.6	994.0	993.4	992.9	992.8
160°	1001.0	1002.4	1003.8	1005.2	1006.6	1006.9	1006.2	1005.5	1004.8	1004.1	1004.0
162.5°	1011.7	1013.2	1014.7	1016.2	1017.8	1018.0	1017.1	1016.1	1015.1	1014.2	1014.0
165°	1026.0	1027.4	1028.8	1030.2	1031.6	1031.8	1030.7	1029.7	1028.7	1027.6	1027.4
167.5°	1036.1	1037.6	1039.2	1040.7	1042.3	1042.5	1041.2	1040.0	1038.7	1037.5	1037.3
170°	1041.7	1043.2	1044.8	1046.4	1047.9	1048.0	1046.6	1045.2	1043.9	1042.5	1042.3
172.5°	1045.4	1047.0	1048.6	1050.1	1051.7	1051.9	1050.6	1049.3	1048.1	1046.8	1046.5
175°	1050.3	1051.9	1053.4	1055.0	1056.5	1056.6	1055.2	1053.8	1052.5	1051.1	1050.9
177.5°	1053.1	1054.2	1055.3	1056.4	1057.6	1057.6	1056.6	1055.7	1054.7	1053.7	1053.6
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1951.3	1946.9	1938.8	1931.3	1922.0	1913.9	1908.2	1901.4	1892.7	1882.1	1873.3
5°	2037.6	2020.5	1997.9	1978.4	1953.5	1934.0	1913.7	1894.2	1874.7	1849.8	1828.0
7.5°	2133.4	2098.0	2063.5	2020.2	1980.9	1945.8	1912.1	1878.0	1844.6	1809.2	1775.1
10°	2192.0	2149.1	2101.6	2047.0	1997.1	1949.6	1905.9	1863.0	1817.8	1778.1	1735.2
12.5°	2246.9	2191.5	2137.1	2068.2	2008.3	1950.2	1894.7	1841.2	1792.9	1741.3	1695.3
15°	2296.4	2241.9	2181.1	2096.9	2013.5	1943.3	1877.8	1808.5	1748.4	1690.8	1639.3
17.5°	2315.6	2258.4	2187.8	2106.9	2015.7	1927.4	1843.1	1767.0	1696.4	1629.2	1571.3
20°	2308.1	2252.8	2180.3	2103.1	2005.7	1913.7	1822.5	1738.3	1659.6	1588.6	1527.1
22.5°	2290.1	2232.8	2162.8	2081.3	1988.8	1891.3	1793.8	1704.0	1621.5	1548.1	1480.9
25°	2262.9	2185.0	2113.3	2033.7	1945.7	1849.0	1748.4	1649.4	1561.4	1486.5	1413.3
27.5°	2234.7	2137.4	2046.2	1967.2	1874.1	1787.9	1690.9	1589.4	1496.8	1420.6	1345.4
30°	2209.1	2100.0	1999.4	1909.8	1821.7	1739.9	1647.9	1548.9	1453.8	1375.1	1298.7
32.5°	2177.3	2061.3	1950.8	1847.4	1762.5	1681.3	1598.0	1503.4	1410.8	1329.5	1251.9
35°	2137.4	1989.3	1869.3	1759.4	1665.0	1586.3	1511.5	1435.1	1342.3	1258.1	1182.5
37.5°	2085.0	1917.0	1778.1	1658.3	1558.9	1479.8	1420.7	1350.9	1266.2	1185.6	1115.5
40°	2053.2	1864.6	1712.6	1594.1	1489.6	1406.2	1350.9	1291.7	1214.5	1138.9	1068.7
42.5°	2010.8	1816.6	1646.5	1523.0	1417.9	1337.6	1281.7	1229.9	1165.2	1094.0	1018.8
45°	1927.7	1723.5	1545.0	1412.5	1306.5	1227.7	1175.5	1129.5	1080.4	1014.9	949.4
47.5°	1819.5	1626.4	1439.6	1294.9	1191.1	1118.0	1067.3	1031.0	995.9	940.2	876.6
50°	1732.9	1546.6	1364.1	1223.8	1113.1	1043.8	996.2	967.4	935.4	884.7	831.7
52.5°	1630.6	1464.2	1285.6	1142.1	1037.7	972.7	927.0	898.2	871.8	830.5	780.0
55°	1469.4	1323.6	1159.9	1029.7	933.9	868.4	824.7	797.4	781.9	746.8	707.0
57.5°	1283.4	1178.9	1034.6	909.1	824.3	759.6	727.6	704.4	686.8	662.0	633.9
60°	1153.7	1080.4	951.0	831.7	753.8	692.2	663.4	643.9	627.5	606.5	584.6
62.5°	1022.1	968.8	856.2	753.8	682.1	630.5	603.5	585.9	567.0	552.8	531.6
65°	845.8	798.2	720.3	640.0	573.7	532.4	512.9	497.3	485.6	470.0	455.2
67.5°	657.9	638.6	584.8	529.4	481.9	445.1	428.3	417.4	403.3	394.0	383.8
70°	542.5	533.2	495.0	458.4	413.9	389.0	373.4	368.7	351.6	342.2	335.2
72.5°	440.3	435.9	413.9	388.5	357.2	335.3	321.0	315.7	304.8	297.3	292.8
75°	301.7	303.2	299.3	283.0	271.3	257.2	244.8	241.6	233.9	227.6	223.7
77.5°	190.8	198.8	199.1	198.3	193.6	185.1	179.9	177.6	169.9	167.6	166.7
80°	131.0	139.5	147.3	146.5	145.0	142.7	138.8	136.4	132.5	130.2	128.6
82.5°	87.3	95.3	101.8	106.0	105.7	103.4	100.7	99.6	98.8	97.1	96.8
85°	41.3	42.9	45.2	50.7	54.6	55.3	54.6	53.8	51.4	52.2	53.0
87.5°	16.4	16.1	16.5	16.2	15.3	18.2	19.8	20.1	19.1	18.2	17.2
90°	10.1	8.9	7.6	6.3	5.0	3.6	2.2	0.8	2.2	3.6	5.0
92.5°	10.4	9.3	8.2	8.2	9.1	10.1	11.1	12.0	11.1	10.1	9.1
95°	25.7	32.3	38.9	42.5	43.0	43.5	44.1	44.6	44.1	43.5	43.0
97.5°	64.6	77.7	90.8	96.8	95.9	94.9	94.0	93.1	94.0	94.9	95.9
100°	134.7	134.0	133.3	132.7	132.2	131.6	131.1	130.6	131.1	131.6	132.2
102.5°	172.8	172.4	171.9	171.4	170.7	170.1	169.4	168.8	169.4	170.1	170.7
105°	233.0	233.0	233.0	232.7	232.0	231.3	230.6	229.9	230.6	231.3	232.0
107.5°	294.3	293.9	293.6	293.4	293.4	293.4	293.4	293.4	293.4	293.4	293.4
110°	335.6	335.2	334.9	334.7	334.7	334.7	334.7	334.7	334.7	334.7	334.7





TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	375.9	375.7	375.5	375.2	374.8	374.3	373.9	373.5	373.9	374.3	374.8
115°	436.0	435.9	435.7	435.2	434.3	433.4	432.6	431.7	432.6	433.4	434.3
117.5°	493.4	492.7	492.1	491.8	491.8	491.8	491.9	491.9	491.9	491.8	491.8
120°	530.0	529.4	528.9	528.7	528.9	529.1	529.3	529.4	529.3	529.1	528.9
122.5°	566.2	565.9	565.7	565.2	564.6	563.9	563.3	562.6	563.3	563.9	564.6
125°	619.4	619.4	619.4	618.8	617.6	616.3	615.1	613.9	615.1	616.3	617.6
127.5°	666.5	666.6	666.7	666.3	665.5	664.6	663.7	662.9	663.7	664.6	665.5
130°	697.2	697.1	696.9	696.4	695.5	694.6	693.8	692.9	693.8	694.6	695.5
132.5°	726.5	726.9	727.3	727.0	725.9	724.9	723.9	722.9	723.9	724.9	725.9
135°	769.4	769.8	770.1	769.8	768.8	767.7	766.7	765.6	766.7	767.7	768.8
137.5°	808.2	808.5	808.8	808.5	807.6	806.7	805.8	804.9	805.8	806.7	807.6
140°	831.7	831.8	832.0	831.9	831.6	831.2	830.9	830.5	830.9	831.2	831.6
142.5°	855.2	855.0	854.7	854.5	854.3	854.1	853.9	853.7	853.9	854.1	854.3
145°	889.2	889.2	889.2	889.0	888.7	888.3	888.0	887.6	888.0	888.3	888.7
147.5°	917.5	917.3	917.1	917.1	917.1	917.2	917.3	917.3	917.3	917.2	917.1
150°	935.4	935.1	934.7	934.7	935.1	935.4	935.8	936.1	935.8	935.4	935.1
152.5°	951.7	951.3	951.0	951.2	952.0	952.7	953.5	954.3	953.5	952.7	952.0
155°	973.7	973.4	973.0	973.4	974.4	975.5	976.5	977.6	976.5	975.5	974.4
157.5°	992.8	992.8	992.7	993.0	993.7	994.3	994.9	995.5	994.9	994.3	993.7
160°	1003.8	1003.6	1003.5	1003.9	1004.9	1006.0	1007.0	1008.1	1007.0	1006.0	1004.9
162.5°	1013.8	1013.6	1013.5	1013.9	1014.9	1016.0	1017.0	1018.1	1017.0	1016.0	1014.9
165°	1027.3	1027.1	1026.9	1027.3	1028.4	1029.4	1030.5	1031.5	1030.5	1029.4	1028.4
167.5°	1037.1	1036.9	1036.8	1037.2	1038.3	1039.4	1040.5	1041.5	1040.5	1039.4	1038.3
170°	1042.1	1041.9	1041.8	1042.3	1043.5	1044.7	1045.9	1047.2	1045.9	1044.7	1043.5
172.5°	1046.2	1045.9	1045.6	1046.0	1047.3	1048.5	1049.7	1050.9	1049.7	1048.5	1047.3
175°	1050.7	1050.5	1050.4	1050.8	1051.9	1052.9	1053.9	1055.0	1053.9	1052.9	1051.9
177.5°	1053.4	1053.3	1053.2	1053.5	1054.4	1055.2	1056.0	1056.9	1056.0	1055.2	1054.4
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1867.1	1858.4	1852.1	1839.6	1830.9	1827.2	1820.3	1818.4	1825.3	1820.3	1819.7
5°	1811.6	1789.0	1771.1	1753.1	1733.6	1721.2	1702.5	1699.3	1694.7	1687.6	1686.1
7.5°	1745.0	1715.6	1692.5	1662.9	1637.1	1616.4	1593.0	1581.9	1575.9	1566.8	1554.7
10°	1700.1	1665.0	1633.9	1604.2	1572.3	1546.6	1523.2	1505.2	1493.5	1482.6	1478.0
12.5°	1655.8	1620.1	1580.2	1544.4	1508.7	1479.8	1453.9	1442.3	1429.3	1416.5	1405.6
15°	1587.1	1539.5	1495.9	1454.6	1424.2	1393.0	1368.0	1350.9	1331.4	1326.0	1304.9
17.5°	1514.1	1467.5	1416.4	1372.9	1337.6	1303.3	1275.9	1256.4	1241.8	1221.7	1212.0
20°	1468.6	1413.3	1363.4	1323.6	1284.6	1244.1	1216.0	1199.7	1185.6	1169.3	1161.5
22.5°	1420.0	1365.9	1314.7	1268.1	1228.5	1188.6	1168.6	1151.7	1135.7	1120.6	1110.3
25°	1348.6	1294.0	1240.2	1191.9	1150.6	1121.7	1098.3	1078.8	1070.3	1055.5	1044.5
27.5°	1277.9	1219.9	1164.1	1115.9	1083.5	1055.0	1035.8	1020.4	1004.9	992.0	982.5
30°	1232.4	1173.2	1112.4	1074.2	1039.9	1012.6	991.5	976.7	965.0	953.3	946.3
32.5°	1186.9	1125.8	1071.8	1030.5	998.1	974.5	952.9	938.7	926.4	913.4	905.2
35°	1113.9	1051.6	1007.9	967.4	935.4	913.6	898.8	878.5	868.4	859.0	850.4
37.5°	1046.1	988.1	940.9	905.3	877.6	855.9	836.7	825.8	813.3	804.9	797.8
40°	996.2	943.2	900.3	862.9	842.7	818.5	800.6	786.5	777.2	766.3	758.5
42.5°	951.3	902.1	860.4	826.8	801.5	781.1	763.8	749.7	737.9	730.1	723.5
45°	887.9	838.8	798.2	767.0	743.7	724.2	706.2	699.2	683.6	674.3	671.2
47.5°	822.2	778.3	739.1	710.4	686.4	668.0	651.2	636.9	628.3	619.1	614.1
50°	778.0	735.9	699.2	671.2	647.8	627.5	611.9	602.6	590.9	582.3	576.1
52.5°	733.7	694.7	658.1	631.2	611.0	590.7	573.3	563.9	552.8	547.4	543.0
55°	670.4	629.1	597.9	571.4	550.3	531.6	515.3	505.9	498.9	493.4	491.9
57.5°	598.7	565.9	536.9	513.1	491.2	473.6	459.3	450.4	444.2	443.4	438.7
60°	551.9	522.3	495.8	470.0	451.3	435.0	422.5	412.4	406.1	405.3	403.8
62.5°	505.1	476.7	452.1	429.5	412.7	396.9	385.1	373.7	370.0	366.1	362.6
65°	435.7	410.0	389.8	371.8	353.9	340.6	329.0	321.9	313.4	308.7	300.1
67.5°	367.6	347.7	328.2	313.1	299.0	286.4	276.7	266.3	260.5	256.8	250.5
70°	322.7	307.1	287.6	271.3	260.4	250.2	242.4	230.7	226.8	223.7	220.6
72.5°	280.3	266.6	250.2	237.0	226.1	216.5	207.5	202.0	198.2	195.0	193.2
75°	220.6	207.4	193.3	184.0	176.2	168.4	163.7	159.8	158.2	157.5	154.3
77.5°	162.0	155.0	143.7	136.3	131.1	128.0	123.8	121.8	121.6	118.2	117.1
80°	123.9	120.0	110.7	107.6	103.7	100.6	98.2	94.3	90.4	88.9	86.5
82.5°	92.1	88.2	84.5	79.5	76.2	74.4	72.0	70.6	71.1	68.9	67.8
85°	49.1	45.2	43.7	42.9	41.3	42.9	42.1	41.3	40.5	39.8	40.5
87.5°	16.9	17.1	16.7	18.2	16.6	17.5	17.6	17.2	17.4	17.5	17.1
90°	6.3	7.6	8.9	10.1	11.3	12.5	13.4	14.3	15.1	16.0	16.7
92.5°	8.2	8.2	9.3	10.4	11.4	12.5	13.4	14.3	15.1	16.0	16.5
95°	42.5	38.9	32.3	25.7	19.1	12.5	13.4	14.3	15.1	16.0	16.4
97.5°	96.8	90.8	77.7	64.6	51.5	38.5	33.6	28.7	23.8	18.9	16.4
100°	132.7	133.3	134.0	134.7	135.4	136.1	110.2	84.3	58.4	32.5	19.2
102.5°	171.4	171.9	172.4	172.8	173.2	173.6	168.7	163.8	158.9	154.0	145.7
105°	232.7	233.0	233.0	233.0	233.0	233.0	233.0	233.0	233.0	233.0	233.0
107.5°	293.4	293.6	293.9	294.3	294.6	295.0	295.0	295.1	295.1	295.1	294.9
110°	334.7	334.9	335.2	335.6	335.9	336.3	335.8	335.2	334.7	334.2	334.0



TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	375.2	375.5	375.7	375.9	376.1	376.3	375.7	375.0	374.3	373.7	373.2
115°	435.2	435.7	435.9	436.0	436.2	436.4	435.7	435.0	434.3	433.6	432.7
117.5°	491.8	492.1	492.7	493.4	494.1	494.7	493.8	492.9	492.0	491.1	490.4
120°	528.7	528.9	529.4	530.0	530.5	531.0	530.7	530.3	530.0	529.6	529.0
122.5°	565.2	565.7	565.9	566.2	566.4	566.7	566.3	566.0	565.6	565.3	564.6
125°	618.8	619.4	619.4	619.4	619.4	619.4	618.7	618.0	617.3	616.6	616.0
127.5°	666.3	666.7	666.6	666.5	666.4	666.3	665.9	665.5	665.2	664.8	663.9
130°	696.4	696.9	697.1	697.2	697.4	697.6	697.1	696.5	696.0	695.5	694.8
132.5°	727.0	727.3	726.9	726.5	726.1	725.7	725.6	725.5	725.4	725.3	724.8
135°	769.8	770.1	769.8	769.4	769.1	768.8	768.4	768.1	767.7	767.4	766.7
137.5°	808.5	808.8	808.5	808.2	807.9	807.5	807.6	807.7	807.7	807.8	807.4
140°	831.9	832.0	831.8	831.7	831.5	831.3	831.7	832.0	832.4	832.7	832.4
142.5°	854.5	854.7	855.0	855.2	855.5	855.7	855.8	855.9	855.9	856.0	855.5
145°	889.0	889.2	889.2	889.2	889.2	889.2	889.4	889.5	889.7	889.9	889.4
147.5°	917.1	917.1	917.3	917.5	917.8	918.0	918.2	918.4	918.6	918.8	918.3
150°	934.7	934.7	935.1	935.4	935.8	936.1	936.5	936.8	937.2	937.5	937.0
152.5°	951.2	951.0	951.3	951.7	952.0	952.4	952.7	953.1	953.4	953.8	953.3
155°	973.4	973.0	973.4	973.7	974.1	974.4	974.9	975.5	976.0	976.5	976.1
157.5°	993.0	992.7	992.8	992.8	992.8	992.9	993.4	994.0	994.6	995.1	994.7
160°	1003.9	1003.5	1003.6	1003.8	1004.0	1004.1	1004.8	1005.5	1006.2	1006.9	1006.6
162.5°	1013.9	1013.5	1013.6	1013.8	1014.0	1014.2	1015.1	1016.1	1017.1	1018.0	1017.8
165°	1027.3	1026.9	1027.1	1027.3	1027.4	1027.6	1028.7	1029.7	1030.7	1031.8	1031.6
167.5°	1037.2	1036.8	1036.9	1037.1	1037.3	1037.5	1038.7	1040.0	1041.2	1042.5	1042.3
170°	1042.3	1041.8	1041.9	1042.1	1042.3	1042.5	1043.9	1045.2	1046.6	1048.0	1047.9
172.5°	1046.0	1045.6	1045.9	1046.2	1046.5	1046.8	1048.1	1049.3	1050.6	1051.9	1051.7
175°	1050.8	1050.4	1050.5	1050.7	1050.9	1051.1	1052.5	1053.8	1055.2	1056.6	1056.5
177.5°	1053.5	1053.2	1053.3	1053.4	1053.6	1053.7	1054.7	1055.7	1056.6	1057.6	1057.6
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1819.1	1812.2	1810.3	1812.8	1810.3	1812.2	1819.1	1819.7	1820.3	1825.3	1818.4
5°	1678.3	1670.5	1674.4	1672.8	1674.4	1670.5	1678.3	1686.1	1687.6	1694.7	1699.3
7.5°	1554.5	1544.8	1534.5	1537.8	1534.5	1544.8	1554.5	1554.7	1566.8	1575.9	1581.9
10°	1467.8	1460.0	1455.3	1459.2	1455.3	1460.0	1467.8	1478.0	1482.6	1493.5	1505.2
12.5°	1394.9	1390.2	1386.1	1384.4	1386.1	1390.2	1394.9	1405.6	1416.5	1429.3	1442.3
15°	1295.5	1286.2	1282.3	1272.2	1282.3	1286.2	1295.5	1304.9	1326.0	1331.4	1350.9
17.5°	1204.0	1200.9	1190.8	1186.4	1190.8	1200.9	1204.0	1212.0	1221.7	1241.8	1256.4
20°	1149.8	1146.7	1136.5	1142.8	1136.5	1146.7	1149.8	1161.5	1169.3	1185.6	1199.7
22.5°	1104.9	1098.0	1094.7	1092.9	1094.7	1098.0	1104.9	1110.3	1120.6	1135.7	1151.7
25°	1041.4	1031.3	1027.4	1022.7	1027.4	1031.3	1041.4	1044.5	1055.5	1070.3	1078.8
27.5°	978.1	972.7	967.5	966.3	967.5	972.7	978.1	982.5	992.0	1004.9	1020.4
30°	937.0	931.5	927.6	927.6	927.6	931.5	937.0	946.3	953.3	965.0	976.7
32.5°	900.2	896.0	892.1	891.5	892.1	896.0	900.2	905.2	913.4	926.4	938.7
35°	846.6	840.3	838.8	834.1	838.8	840.3	846.6	850.4	859.0	868.4	878.5
37.5°	790.9	785.7	785.6	785.1	785.6	785.7	790.9	797.8	804.9	813.3	825.8
40°	755.3	751.4	750.7	745.2	750.7	751.4	755.3	758.5	766.3	777.2	786.5
42.5°	717.3	715.3	712.6	710.3	712.6	715.3	717.3	723.5	730.1	737.9	749.7
45°	665.7	660.2	660.2	656.3	660.2	660.2	665.7	671.2	674.3	683.6	699.2
47.5°	612.4	608.2	608.6	604.6	608.6	608.2	612.4	614.1	619.1	628.3	636.9
50°	576.8	574.5	573.7	572.2	573.7	574.5	576.8	576.1	582.3	590.9	602.6
52.5°	541.3	540.2	543.2	539.7	543.2	540.2	541.3	543.0	547.4	552.8	563.9
55°	493.4	491.1	495.8	491.1	495.8	491.1	493.4	491.9	493.4	498.9	505.9
57.5°	438.4	436.2	440.4	438.1	440.4	436.2	438.4	438.7	443.4	444.2	450.4
60°	402.2	397.6	399.9	400.7	399.9	397.6	402.2	403.8	405.3	406.1	412.4
62.5°	359.2	356.4	358.1	354.5	358.1	356.4	359.2	362.6	366.1	370.0	373.7
65°	298.6	296.2	293.1	291.5	293.1	296.2	298.6	300.1	308.7	313.4	321.9
67.5°	250.8	245.2	245.1	246.3	245.1	245.2	250.8	250.5	256.8	260.5	266.3
70°	215.9	215.9	215.1	215.1	215.1	215.9	215.9	220.6	223.7	226.8	230.7
72.5°	191.6	191.0	189.6	189.0	189.6	191.0	191.6	193.2	195.0	198.2	202.0
75°	154.3	155.1	153.6	152.8	153.6	155.1	154.3	154.3	157.5	158.2	159.8
77.5°	114.0	110.7	112.4	110.7	112.4	110.7	114.0	117.1	118.2	121.6	121.8
80°	86.5	85.7	88.1	85.7	88.1	85.7	86.5	86.5	88.9	90.4	94.3
82.5°	68.4	67.7	68.8	67.0	68.8	67.7	68.4	67.8	68.9	71.1	70.6
85°	41.3	40.5	39.8	40.5	39.8	40.5	41.3	40.5	39.8	40.5	41.3
87.5°	17.8	17.3	17.4	17.5	17.4	17.3	17.8	17.1	17.5	17.4	17.2
90°	17.2	17.7	18.2	18.8	18.2	17.7	17.2	16.7	16.0	15.1	14.3
92.5°	16.8	17.0	17.3	17.5	17.3	17.0	16.8	16.5	16.0	15.1	14.3
95°	16.4	16.4	16.4	16.4	16.4	16.4	16.4	16.4	16.0	15.1	14.3
97.5°	16.4	16.4	16.4	16.4	16.4	16.4	16.4	16.4	18.9	23.8	28.7
100°	18.5	17.8	17.1	16.4	17.1	17.8	18.5	19.2	32.5	58.4	84.3
102.5°	133.8	122.0	110.2	98.4	110.2	122.0	133.8	145.7	154.0	158.9	163.8
105°	232.8	232.6	232.4	232.3	232.4	232.6	232.8	233.0	233.0	233.0	233.0
107.5°	294.4	293.8	293.3	292.8	293.3	293.8	294.4	294.9	295.1	295.1	295.1
110°	334.2	334.4	334.5	334.7	334.5	334.4	334.2	334.0	334.2	334.7	335.2



TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	373.0	372.7	372.5	372.3	372.5	372.7	373.0	373.2	373.7	374.3	375.0
115°	431.7	430.6	429.6	428.6	429.6	430.6	431.7	432.7	433.6	434.3	435.0
117.5°	490.0	489.5	489.1	488.6	489.1	489.5	490.0	490.4	491.1	492.0	492.9
120°	528.1	527.3	526.4	525.5	526.4	527.3	528.1	529.0	529.6	530.0	530.3
122.5°	563.6	562.6	561.6	560.6	561.6	562.6	563.6	564.6	565.3	565.6	566.0
125°	615.5	614.9	614.4	613.9	614.4	614.9	615.5	616.0	616.6	617.3	618.0
127.5°	662.7	661.4	660.1	658.8	660.1	661.4	662.7	663.9	664.8	665.2	665.5
130°	693.9	693.1	692.2	691.3	692.2	693.1	693.9	694.8	695.5	696.0	696.5
132.5°	724.0	723.1	722.2	721.4	722.2	723.1	724.0	724.8	725.3	725.4	725.5
135°	765.6	764.6	763.5	762.5	763.5	764.6	765.6	766.7	767.4	767.7	768.1
137.5°	806.5	805.6	804.7	803.8	804.7	805.6	806.5	807.4	807.8	807.7	807.7
140°	831.3	830.3	829.2	828.2	829.2	830.3	831.3	832.4	832.7	832.4	832.0
142.5°	854.5	853.4	852.4	851.3	852.4	853.4	854.5	855.5	856.0	855.9	855.9
145°	888.4	887.4	886.3	885.3	886.3	887.4	888.4	889.4	889.9	889.7	889.5
147.5°	917.0	915.8	914.5	913.3	914.5	915.8	917.0	918.3	918.8	918.6	918.4
150°	935.6	934.2	932.8	931.4	932.8	934.2	935.6	937.0	937.5	937.2	936.8
152.5°	952.1	950.8	949.6	948.3	949.6	950.8	952.1	953.3	953.8	953.4	953.1
155°	974.7	973.3	971.9	970.5	971.9	973.3	974.7	976.1	976.5	976.0	975.5
157.5°	993.3	991.9	990.5	989.1	990.5	991.9	993.3	994.7	995.1	994.6	994.0
160°	1005.2	1003.8	1002.4	1001.0	1002.4	1003.8	1005.2	1006.6	1006.9	1006.2	1005.5
162.5°	1016.2	1014.7	1013.2	1011.7	1013.2	1014.7	1016.2	1017.8	1018.0	1017.1	1016.1
165°	1030.2	1028.8	1027.4	1026.0	1027.4	1028.8	1030.2	1031.6	1031.8	1030.7	1029.7
167.5°	1040.7	1039.2	1037.6	1036.1	1037.6	1039.2	1040.7	1042.3	1042.5	1041.2	1040.0
170°	1046.4	1044.8	1043.2	1041.7	1043.2	1044.8	1046.4	1047.9	1048.0	1046.6	1045.2
172.5°	1050.1	1048.6	1047.0	1045.4	1047.0	1048.6	1050.1	1051.7	1051.9	1050.6	1049.3
175°	1055.0	1053.4	1051.9	1050.3	1051.9	1053.4	1055.0	1056.5	1056.6	1055.2	1053.8
177.5°	1056.4	1055.3	1054.2	1053.1	1054.2	1055.3	1056.4	1057.6	1057.6	1056.6	1055.7
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1820.3	1827.2	1830.9	1839.6	1852.1	1858.4	1867.1	1873.3	1882.1	1892.7	1901.4
5°	1702.5	1721.2	1733.6	1753.1	1771.1	1789.0	1811.6	1828.0	1849.8	1874.7	1894.2
7.5°	1593.0	1616.4	1637.1	1662.9	1692.5	1715.6	1745.0	1775.1	1809.2	1844.6	1878.0
10°	1523.2	1546.6	1572.3	1604.2	1633.9	1665.0	1700.1	1735.2	1778.1	1817.8	1863.0
12.5°	1453.9	1479.8	1508.7	1544.4	1580.2	1620.1	1655.8	1695.3	1741.3	1792.9	1841.2
15°	1368.0	1393.0	1424.2	1454.6	1495.9	1539.5	1587.1	1639.3	1690.8	1748.4	1808.5
17.5°	1275.9	1303.3	1337.6	1372.9	1416.4	1467.5	1514.1	1571.3	1629.2	1696.4	1767.0
20°	1216.0	1244.1	1284.6	1323.6	1363.4	1413.3	1468.6	1527.1	1588.6	1659.6	1738.3
22.5°	1168.6	1188.6	1228.5	1268.1	1314.7	1365.9	1420.0	1480.9	1548.1	1621.5	1704.0
25°	1098.3	1121.7	1150.6	1191.9	1240.2	1294.0	1348.6	1413.3	1486.5	1561.4	1649.4
27.5°	1035.8	1055.0	1083.5	1115.9	1164.1	1219.9	1277.9	1345.4	1420.6	1496.8	1589.4
30°	991.5	1012.6	1039.9	1074.2	1112.4	1173.2	1232.4	1298.7	1375.1	1453.8	1548.9
32.5°	952.9	974.5	998.1	1030.5	1071.8	1125.8	1186.9	1251.9	1329.5	1410.8	1503.4
35°	898.8	913.6	935.4	967.4	1007.9	1051.6	1113.9	1182.5	1258.1	1342.3	1435.1
37.5°	836.7	855.9	877.6	905.3	940.9	988.1	1046.1	1115.5	1185.6	1266.2	1350.9
40°	800.6	818.5	842.7	862.9	900.3	943.2	996.2	1068.7	1138.9	1214.5	1291.7
42.5°	763.8	781.1	801.5	826.8	860.4	902.1	951.3	1018.8	1094.0	1165.2	1229.9
45°	706.2	724.2	743.7	767.0	798.2	838.8	887.9	949.4	1014.9	1080.4	1129.5
47.5°	651.2	668.0	686.4	710.4	739.1	778.3	822.2	876.6	940.2	995.9	1031.0
50°	611.9	627.5	647.8	671.2	699.2	735.9	778.0	831.7	884.7	935.4	967.4
52.5°	573.3	590.7	611.0	631.2	658.1	694.7	733.7	780.0	830.5	871.8	898.2
55°	515.3	531.6	550.3	571.4	597.9	629.1	670.4	707.0	746.8	781.9	797.4
57.5°	459.3	473.6	491.2	513.1	536.9	565.9	598.7	633.9	662.0	686.8	704.4
60°	422.5	435.0	451.3	470.0	495.8	522.3	551.9	584.6	606.5	627.5	643.9
62.5°	385.1	396.9	412.7	429.5	452.1	476.7	505.1	531.6	552.8	567.0	585.9
65°	329.0	340.6	353.9	371.8	389.8	410.0	435.7	455.2	470.0	485.6	497.3
67.5°	276.7	286.4	299.0	313.1	328.2	347.7	367.6	383.8	394.0	403.3	417.4
70°	242.4	250.2	260.4	271.3	287.6	307.1	322.7	335.2	342.2	351.6	368.7
72.5°	207.5	216.5	226.1	237.0	250.2	266.6	280.3	292.8	297.3	304.8	315.7
75°	163.7	168.4	176.2	184.0	193.3	207.4	220.6	223.7	227.6	233.9	241.6
77.5°	123.8	128.0	131.1	136.3	143.7	155.0	162.0	166.7	167.6	169.9	177.6
80°	98.2	100.6	103.7	107.6	110.7	120.0	123.9	128.6	130.2	132.5	136.4
82.5°	72.0	74.4	76.2	79.5	84.5	88.2	92.1	96.8	97.1	98.8	99.6
85°	42.1	42.9	41.3	42.9	43.7	45.2	49.1	53.0	52.2	51.4	53.8
87.5°	17.6	17.5	16.6	18.2	16.7	17.1	16.9	17.2	18.2	19.1	20.1
90°	13.4	12.5	11.3	10.1	8.9	7.6	6.3	5.0	3.6	2.2	0.8
92.5°	13.4	12.5	11.4	10.4	9.3	8.2	8.2	9.1	10.1	11.1	12.0
95°	13.4	12.5	19.1	25.7	32.3	38.9	42.5	43.0	43.5	44.1	44.6
97.5°	33.6	38.5	51.5	64.6	77.7	90.8	96.8	95.9	94.9	94.0	93.1
100°	110.2	136.1	135.4	134.7	134.0	133.3	132.7	132.2	131.6	131.1	130.6
102.5°	168.7	173.6	173.2	172.8	172.4	171.9	171.4	170.7	170.1	169.4	168.8
105°	233.0	233.0	233.0	233.0	233.0	233.0	232.7	232.0	231.3	230.6	229.9
107.5°	295.0	295.0	294.6	294.3	293.9	293.6	293.4	293.4	293.4	293.4	293.4
110°	335.8	336.3	335.9	335.6	335.2	334.9	334.7	334.7	334.7	334.7	334.7



TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	375.7	376.3	376.1	375.9	375.7	375.5	375.2	374.8	374.3	373.9	373.5
115°	435.7	436.4	436.2	436.0	435.9	435.7	435.2	434.3	433.4	432.6	431.7
117.5°	493.8	494.7	494.1	493.4	492.7	492.1	491.8	491.8	491.8	491.9	491.9
120°	530.7	531.0	530.5	530.0	529.4	528.9	528.7	528.9	529.1	529.3	529.4
122.5°	566.3	566.7	566.4	566.2	565.9	565.7	565.2	564.6	563.9	563.3	562.6
125°	618.7	619.4	619.4	619.4	619.4	619.4	618.8	617.6	616.3	615.1	613.9
127.5°	665.9	666.3	666.4	666.5	666.6	666.7	666.3	665.5	664.6	663.7	662.9
130°	697.1	697.6	697.4	697.2	697.1	696.9	696.4	695.5	694.6	693.8	692.9
132.5°	725.6	725.7	726.1	726.5	726.9	727.3	727.0	725.9	724.9	723.9	722.9
135°	768.4	768.8	769.1	769.4	769.8	770.1	769.8	768.8	767.7	766.7	765.6
137.5°	807.6	807.5	807.9	808.2	808.5	808.8	808.5	807.6	806.7	805.8	804.9
140°	831.7	831.3	831.5	831.7	831.8	832.0	831.9	831.6	831.2	830.9	830.5
142.5°	855.8	855.7	855.5	855.2	855.0	854.7	854.5	854.3	854.1	853.9	853.7
145°	889.4	889.2	889.2	889.2	889.2	889.2	889.0	888.7	888.3	888.0	887.6
147.5°	918.2	918.0	917.8	917.5	917.3	917.1	917.1	917.1	917.2	917.3	917.3
150°	936.5	936.1	935.8	935.4	935.1	934.7	934.7	935.1	935.4	935.8	936.1
152.5°	952.7	952.4	952.0	951.7	951.3	951.0	951.2	952.0	952.7	953.5	954.3
155°	974.9	974.4	974.1	973.7	973.4	973.0	973.4	974.4	975.5	976.5	977.6
157.5°	993.4	992.9	992.8	992.8	992.8	992.7	993.0	993.7	994.3	994.9	995.5
160°	1004.8	1004.1	1004.0	1003.8	1003.6	1003.5	1003.9	1004.9	1006.0	1007.0	1008.1
162.5°	1015.1	1014.2	1014.0	1013.8	1013.6	1013.5	1013.9	1014.9	1016.0	1017.0	1018.1
165°	1028.7	1027.6	1027.4	1027.3	1027.1	1026.9	1027.3	1028.4	1029.4	1030.5	1031.5
167.5°	1038.7	1037.5	1037.3	1037.1	1036.9	1036.8	1037.2	1038.3	1039.4	1040.5	1041.5
170°	1043.9	1042.5	1042.3	1042.1	1041.9	1041.8	1042.3	1043.5	1044.7	1045.9	1047.2
172.5°	1048.1	1046.8	1046.5	1046.2	1045.9	1045.6	1046.0	1047.3	1048.5	1049.7	1050.9
175°	1052.5	1051.1	1050.9	1050.7	1050.5	1050.4	1050.8	1051.9	1052.9	1053.9	1055.0
177.5°	1054.7	1053.7	1053.6	1053.4	1053.3	1053.2	1053.5	1054.4	1055.2	1056.0	1056.9
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1908.2	1913.9	1922.0	1931.3	1938.8	1946.9	1951.3	1951.3	1955.0	1963.1	1973.7
5°	1913.7	1934.0	1953.5	1978.4	1997.9	2020.5	2037.6	2054.0	2068.8	2087.5	2107.0
7.5°	1912.1	1945.8	1980.9	2020.2	2063.5	2098.0	2133.4	2161.1	2188.6	2224.4	2252.6
10°	1905.9	1949.6	1997.1	2047.0	2101.6	2149.1	2192.0	2231.0	2268.4	2307.4	2342.4
12.5°	1894.7	1950.2	2008.3	2068.2	2137.1	2191.5	2246.9	2288.3	2332.0	2374.7	2417.9
15°	1877.8	1943.3	2013.5	2096.9	2181.1	2241.9	2296.4	2350.2	2390.8	2439.1	2480.4
17.5°	1843.1	1927.4	2015.7	2106.9	2187.8	2258.4	2315.6	2366.8	2409.9	2463.1	2519.2
20°	1822.5	1913.7	2005.7	2103.1	2180.3	2252.8	2308.1	2361.1	2414.9	2484.3	2552.9
22.5°	1793.8	1891.3	1988.8	2081.3	2162.8	2232.8	2290.1	2354.9	2425.5	2504.3	2587.2
25°	1748.4	1849.0	1945.7	2033.7	2113.3	2185.0	2262.9	2350.2	2436.0	2539.7	2658.9
27.5°	1690.9	1787.9	1874.1	1967.2	2046.2	2137.4	2234.7	2329.3	2453.0	2595.6	2744.5
30°	1647.9	1739.9	1821.7	1909.8	1999.4	2100.0	2209.1	2320.6	2467.9	2635.5	2812.5
32.5°	1598.0	1681.3	1762.5	1847.4	1950.8	2061.3	2177.3	2313.7	2489.8	2680.4	2863.6
35°	1511.5	1586.3	1665.0	1759.4	1869.3	1989.3	2137.4	2303.5	2516.3	2721.3	2885.8
37.5°	1420.7	1479.8	1558.9	1658.3	1778.1	1917.0	2085.0	2286.8	2505.4	2689.3	2759.3
40°	1350.9	1406.2	1489.6	1594.1	1712.6	1864.6	2053.2	2260.6	2480.4	2608.2	2602.8
42.5°	1281.7	1337.6	1417.9	1523.0	1646.5	1816.6	2010.8	2226.3	2411.8	2460.5	2359.0
45°	1175.5	1227.7	1306.5	1412.5	1545.0	1723.5	1927.7	2134.3	2252.8	2174.1	1972.9
47.5°	1067.3	1118.0	1191.1	1294.9	1439.6	1626.4	1819.5	1989.0	2005.7	1836.5	1595.3
50°	996.2	1043.8	1113.1	1223.8	1364.1	1546.6	1732.9	1866.2	1824.8	1618.3	1369.6
52.5°	927.0	972.7	1037.7	1142.1	1285.6	1464.2	1630.6	1735.2	1639.6	1420.0	1196.2
55°	824.7	868.4	933.9	1029.7	1159.9	1323.6	1469.4	1507.6	1367.3	1145.9	965.0
57.5°	727.6	759.6	824.3	909.1	1034.6	1178.9	1283.4	1276.5	1121.7	922.3	792.6
60°	663.4	692.2	753.8	831.7	951.0	1080.4	1153.7	1122.5	965.8	801.3	676.6
62.5°	603.5	630.5	682.1	753.8	856.2	968.8	1022.1	979.1	831.1	686.6	587.4
65°	512.9	532.4	573.7	640.0	720.3	798.2	845.8	782.6	651.7	542.5	467.7
67.5°	428.3	445.1	481.9	529.4	584.8	638.6	657.9	598.7	496.9	423.3	370.6
70°	373.4	389.0	413.9	458.4	495.0	533.2	542.5	489.5	404.6	348.4	315.7
72.5°	321.0	335.3	357.2	388.5	413.9	435.9	440.3	391.0	326.0	287.3	262.1
75°	244.8	257.2	271.3	283.0	299.3	303.2	301.7	263.5	228.4	202.7	188.6
77.5°	179.9	185.1	193.6	198.3	199.1	198.8	190.8	166.7	148.6	138.0	132.2
80°	138.8	142.7	145.0	146.5	147.3	139.5	131.0	116.1	109.9	103.7	96.7
82.5°	100.7	103.4	105.7	106.0	101.8	95.3	87.3	80.0	75.6	72.5	69.8
85°	54.6	55.3	54.6	50.7	45.2	42.9	41.3	39.8	39.0	38.2	38.2
87.5°	19.8	18.2	15.3	16.2	16.5	16.1	16.4	16.0	15.6	15.8	15.9
90°	2.2	3.6	5.0	6.3	7.6	8.9	10.1	11.3	12.5	13.4	14.3
92.5°	11.1	10.1	9.1	8.2	8.2	9.3	10.4	11.4	12.5	13.4	14.3
95°	44.1	43.5	43.0	42.5	38.9	32.3	25.7	19.1	12.5	13.4	14.3
97.5°	94.0	94.9	95.9	96.8	90.8	77.7	64.6	51.5	38.5	33.6	28.7
100°	131.1	131.6	132.2	132.7	133.3	134.0	134.7	135.4	136.1	110.2	84.3
102.5°	169.4	170.1	170.7	171.4	171.9	172.4	172.8	173.2	173.6	168.7	163.8
105°	230.6	231.3	232.0	232.7	233.0	233.0	233.0	233.0	233.0	233.0	233.0
107.5°	293.4	293.4	293.4	293.4	293.6	293.9	294.3	294.6	295.0	295.0	295.1
110°	334.7	334.7	334.7	334.7	334.9	335.2	335.6	335.9	336.3	335.8	335.2





TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	373.9	374.3	374.8	375.2	375.5	375.7	375.9	376.1	376.3	375.7	375.0
115°	432.6	433.4	434.3	435.2	435.7	435.9	436.0	436.2	436.4	435.7	435.0
117.5°	491.9	491.8	491.8	491.8	492.1	492.7	493.4	494.1	494.7	493.8	492.9
120°	529.3	529.1	528.9	528.7	528.9	529.4	530.0	530.5	531.0	530.7	530.3
122.5°	563.3	563.9	564.6	565.2	565.7	565.9	566.2	566.4	566.7	566.3	566.0
125°	615.1	616.3	617.6	618.8	619.4	619.4	619.4	619.4	619.4	618.7	618.0
127.5°	663.7	664.6	665.5	666.3	666.7	666.6	666.5	666.4	666.3	665.9	665.5
130°	693.8	694.6	695.5	696.4	696.9	697.1	697.2	697.4	697.6	697.1	696.5
132.5°	723.9	724.9	725.9	727.0	727.3	726.9	726.5	726.1	725.7	725.6	725.5
135°	766.7	767.7	768.8	769.8	770.1	769.8	769.4	769.1	768.8	768.4	768.1
137.5°	805.8	806.7	807.6	808.5	808.8	808.5	808.2	807.9	807.5	807.6	807.7
140°	830.9	831.2	831.6	831.9	832.0	831.8	831.7	831.5	831.3	831.7	832.0
142.5°	853.9	854.1	854.3	854.5	854.7	855.0	855.2	855.5	855.7	855.8	855.9
145°	888.0	888.3	888.7	889.0	889.2	889.2	889.2	889.2	889.2	889.4	889.5
147.5°	917.3	917.2	917.1	917.1	917.1	917.3	917.5	917.8	918.0	918.2	918.4
150°	935.8	935.4	935.1	934.7	934.7	935.1	935.4	935.8	936.1	936.5	936.8
152.5°	953.5	952.7	952.0	951.2	951.0	951.3	951.7	952.0	952.4	952.7	953.1
155°	976.5	975.5	974.4	973.4	973.0	973.4	973.7	974.1	974.4	974.9	975.5
157.5°	994.9	994.3	993.7	993.0	992.7	992.8	992.8	992.8	992.9	993.4	994.0
160°	1007.0	1006.0	1004.9	1003.9	1003.5	1003.6	1003.8	1004.0	1004.1	1004.8	1005.5
162.5°	1017.0	1016.0	1014.9	1013.9	1013.5	1013.6	1013.8	1014.0	1014.2	1015.1	1016.1
165°	1030.5	1029.4	1028.4	1027.3	1026.9	1027.1	1027.3	1027.4	1027.6	1028.7	1029.7
167.5°	1040.5	1039.4	1038.3	1037.2	1036.8	1036.9	1037.1	1037.3	1037.5	1038.7	1040.0
170°	1045.9	1044.7	1043.5	1042.3	1041.8	1041.9	1042.1	1042.3	1042.5	1043.9	1045.2
172.5°	1049.7	1048.5	1047.3	1046.0	1045.6	1045.9	1046.2	1046.5	1046.8	1048.1	1049.3
175°	1053.9	1052.9	1051.9	1050.8	1050.4	1050.5	1050.7	1050.9	1051.1	1052.5	1053.8
177.5°	1056.0	1055.2	1054.4	1053.5	1053.2	1053.3	1053.4	1053.6	1053.7	1054.7	1055.7
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1981.8	1981.8	1992.4	1991.8	1998.7	1996.2	1997.4
5°	2130.4	2143.7	2155.4	2163.1	2174.8	2178.0	2176.4
7.5°	2284.4	2313.9	2328.2	2347.9	2351.5	2361.8	2360.7
10°	2379.9	2408.7	2430.5	2447.7	2456.2	2467.2	2467.9
12.5°	2454.7	2479.2	2498.5	2514.4	2524.8	2528.3	2530.3
15°	2513.1	2540.4	2563.0	2585.6	2598.9	2609.0	2614.5
17.5°	2572.1	2614.2	2654.1	2684.8	2703.2	2718.8	2718.6
20°	2617.6	2665.9	2715.8	2750.9	2786.8	2802.3	2804.7
22.5°	2666.2	2740.1	2804.4	2858.8	2905.9	2922.1	2928.2
25°	2767.3	2863.9	2962.9	3039.3	3093.9	3125.8	3130.5
27.5°	2889.3	3020.1	3124.3	3194.8	3240.1	3263.8	3269.0
30°	2975.4	3096.2	3189.8	3242.8	3263.8	3266.9	3255.2
32.5°	3014.1	3104.3	3141.7	3138.6	3097.3	3069.9	3059.4
35°	2966.8	2948.1	2856.9	2747.8	2664.4	2611.4	2597.3
37.5°	2699.9	2538.6	2370.8	2205.9	2118.1	2073.5	1996.8
40°	2436.8	2206.8	2032.2	1893.4	1794.4	1714.9	1696.2
42.5°	2139.9	1902.5	1727.9	1609.1	1530.0	1475.5	1451.8
45°	1719.6	1515.4	1371.2	1280.0	1219.2	1179.4	1161.5
47.5°	1375.4	1217.3	1112.2	1044.7	998.4	963.8	954.1
50°	1186.4	1060.1	971.3	914.4	879.3	852.8	841.9
52.5°	1030.5	928.6	860.3	813.3	780.1	763.6	754.6
55°	850.4	762.4	713.3	675.8	657.1	643.9	637.6
57.5°	695.5	631.9	596.0	570.1	552.8	544.4	541.3
60°	608.8	558.9	526.2	505.9	494.2	483.3	480.2
62.5°	532.1	492.8	467.6	449.8	438.1	433.4	431.5
65°	428.7	403.0	384.3	373.4	364.0	362.5	361.7
67.5°	340.8	325.7	315.9	304.5	301.2	295.7	294.7
70°	291.5	281.4	269.7	265.8	261.9	256.5	257.2
72.5°	247.3	237.1	229.2	224.0	222.6	220.3	222.3
75°	180.8	177.7	174.6	170.7	169.2	169.2	168.4
77.5°	129.1	126.4	123.0	120.7	120.2	116.9	118.2
80°	93.5	89.6	88.1	88.9	86.5	85.7	85.7
82.5°	69.2	67.8	66.3	66.4	65.9	65.2	65.8
85°	38.2	37.4	37.4	36.6	36.6	35.9	35.9
87.5°	16.7	17.5	16.4	15.9	16.0	16.7	17.5
90°	15.1	16.0	16.7	17.2	17.7	18.2	18.8
92.5°	15.1	16.0	16.5	16.8	17.0	17.3	17.5
95°	15.1	16.0	16.4	16.4	16.4	16.4	16.4
97.5°	23.8	18.9	16.4	16.4	16.4	16.4	16.4
100°	58.4	32.5	19.2	18.5	17.8	17.1	16.4
102.5°	158.9	154.0	145.7	133.8	122.0	110.2	98.4
105°	233.0	233.0	233.0	232.8	232.6	232.4	232.3
107.5°	295.1	295.1	294.9	294.4	293.8	293.3	292.8
110°	334.7	334.2	334.0	334.2	334.4	334.5	334.7



TEST NUMBER: P333622

CATALOG NUMBER: S125RDIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	374.3	373.7	373.2	373.0	372.7	372.5	372.3
115°	434.3	433.6	432.7	431.7	430.6	429.6	428.6
117.5°	492.0	491.1	490.4	490.0	489.5	489.1	488.6
120°	530.0	529.6	529.0	528.1	527.3	526.4	525.5
122.5°	565.6	565.3	564.6	563.6	562.6	561.6	560.6
125°	617.3	616.6	616.0	615.5	614.9	614.4	613.9
127.5°	665.2	664.8	663.9	662.7	661.4	660.1	658.8
130°	696.0	695.5	694.8	693.9	693.1	692.2	691.3
132.5°	725.4	725.3	724.8	724.0	723.1	722.2	721.4
135°	767.7	767.4	766.7	765.6	764.6	763.5	762.5
137.5°	807.7	807.8	807.4	806.5	805.6	804.7	803.8
140°	832.4	832.7	832.4	831.3	830.3	829.2	828.2
142.5°	855.9	856.0	855.5	854.5	853.4	852.4	851.3
145°	889.7	889.9	889.4	888.4	887.4	886.3	885.3
147.5°	918.6	918.8	918.3	917.0	915.8	914.5	913.3
150°	937.2	937.5	937.0	935.6	934.2	932.8	931.4
152.5°	953.4	953.8	953.3	952.1	950.8	949.6	948.3
155°	976.0	976.5	976.1	974.7	973.3	971.9	970.5
157.5°	994.6	995.1	994.7	993.3	991.9	990.5	989.1
160°	1006.2	1006.9	1006.6	1005.2	1003.8	1002.4	1001.0
162.5°	1017.1	1018.0	1017.8	1016.2	1014.7	1013.2	1011.7
165°	1030.7	1031.8	1031.6	1030.2	1028.8	1027.4	1026.0
167.5°	1041.2	1042.5	1042.3	1040.7	1039.2	1037.6	1036.1
170°	1046.6	1048.0	1047.9	1046.4	1044.8	1043.2	1041.7
172.5°	1050.6	1051.9	1051.7	1050.1	1048.6	1047.0	1045.4
175°	1055.2	1056.6	1056.5	1055.0	1053.4	1051.9	1050.3
177.5°	1056.6	1057.6	1057.6	1056.4	1055.3	1054.2	1053.1
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0

(END OF REPORT)