

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331277-927

Luminaire Tested: **SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331277-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4086.4 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	25	24	19
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	21	20	18	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	18	16	12
6	60	48	41	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	11	9
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7561	7561	7561	7561
5°	8475	7609	6744	7609
10°	9712	7547	5835	7547
15°	10745	7408	5157	7408
20°	10581	7261	4699	7261
25°	9540	7062	4411	7062
30°	7884	6747	4200	6747
35°	5746	6416	4050	6416
40°	4591	6028	3967	6028
45°	4010	5576	3854	5576
50°	3770	5139	3778	5139
55°	3474	4695	3676	4695
60°	3184	4224	3523	4224
65°	2904	3801	3370	3801
70°	2634	3389	3144	3389
75°	2339	2932	2782	2932
80°	2008	2427	2241	2427
85°	1797	1797	1334	1797



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.6	1.1
10°-20°	129.6	3.2
20°-30°	188.1	4.6
30°-40°	198.5	4.9
40°-50°	175.8	4.3
50°-60°	140.3	3.4
60°-70°	95.4	2.3
70°-80°	48.9	1.2
80°-90°	16.1	0.4
90°-100°	69.1	1.7
100°-110°	214.6	5.3
110°-120°	366.8	9.0
120°-130°	482.4	11.8
130°-140°	541.4	13.2
140°-150°	530.9	13.0
150°-160°	445.3	10.9
160°-170°	295.3	7.2
170°-180°	103.2	2.5
0°-30°	362.4	8.9
0°-40°	560.9	13.7
0°-60°	877.0	21.5
0°-90°	1037.4	25.4
90°-120°	650.5	15.9
90°-150°	2205.2	54.0
90°-180°	3049.0	74.6
0°-180°	4086.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	468	468	468	468	468	
5°	523	470	416	470	523	52
15°	643	443	308	443	643	177
25°	536	396	248	396	536	242
35°	292	326	206	326	292	190
45°	176	244	169	244	176	138
55°	123	167	131	167	123	111
65°	76	100	88	100	76	76
75°	38	47	45	47	38	40
85°	10	10	7	10	10	11
90°	31	1	31	1	31	14
95°	57	48	57	48	57	64
105°	204	198	204	198	204	215
115°	368	368	368	368	368	363
125°	537	536	537	536	537	479
135°	701	693	701	693	701	540
145°	850	841	850	841	850	531
155°	969	962	969	962	969	446
165°	1047	1046	1047	1046	1047	295
175°	1085	1089	1085	1089	1085	103
180°	1090	1090	1090	1090	1090	



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	489.8	490.0	490.3	488.0	487.7	487.7	485.7	483.9	481.9	479.2	479.5
5°	522.9	524.9	525.6	523.5	520.2	519.9	516.8	511.8	507.1	503.4	500.7
7.5°	562.4	563.2	561.5	558.6	556.3	551.9	546.2	540.7	532.8	525.7	520.4
10°	592.4	593.5	590.4	586.3	582.9	577.8	569.6	561.1	550.9	541.0	533.1
12.5°	615.1	617.8	613.9	613.4	607.5	600.6	590.7	586.5	572.0	558.3	549.7
15°	642.8	642.6	643.0	639.5	635.3	634.1	623.8	612.4	592.1	583.9	569.9
17.5°	634.8	637.5	638.8	638.7	638.7	637.9	634.6	627.5	617.3	604.1	588.0
20°	615.8	619.4	620.0	624.1	626.5	629.5	630.7	628.8	622.5	611.5	597.5
22.5°	586.5	587.5	589.1	595.6	600.6	608.3	612.3	619.0	616.6	611.2	599.4
25°	535.5	533.8	540.0	543.3	555.0	567.2	576.1	585.7	594.4	599.6	596.2
27.5°	474.4	471.7	481.2	489.8	499.2	512.5	526.2	542.5	556.0	572.9	578.7
30°	422.9	424.5	433.5	442.7	457.1	475.8	491.3	509.1	528.4	547.2	560.4
32.5°	367.3	373.5	379.2	393.3	406.0	426.8	449.6	471.8	495.8	517.3	537.7
35°	291.5	298.7	306.7	316.9	334.7	355.4	377.6	407.6	440.4	469.7	493.8
37.5°	245.4	244.2	248.7	256.2	270.6	287.3	312.8	342.5	381.0	415.5	449.6
40°	217.8	217.1	220.2	227.1	238.1	250.3	272.7	298.7	334.5	376.7	417.2
42.5°	198.8	199.2	201.0	205.8	213.3	223.4	240.1	262.3	295.1	334.8	378.3
45°	175.6	176.9	178.9	181.3	185.5	193.8	203.2	219.0	244.9	278.1	320.8
47.5°	159.0	159.1	161.1	163.1	165.6	170.3	178.0	187.9	206.2	233.1	270.0
50°	150.1	148.9	150.3	151.9	154.6	157.8	162.9	172.2	184.4	206.2	237.0
52.5°	139.1	139.2	140.5	141.1	143.5	146.7	151.3	157.8	168.9	185.9	211.2
55°	123.4	124.4	125.1	126.1	128.3	130.6	134.3	138.6	147.2	159.9	178.7
57.5°	108.7	109.0	109.7	111.8	113.1	115.3	118.7	122.6	128.3	137.7	151.8
60°	98.6	98.6	100.1	100.9	102.7	104.9	107.6	111.4	116.5	124.1	135.5
62.5°	89.4	89.3	89.8	91.3	92.7	94.7	97.4	100.6	105.4	112.3	121.5
65°	76.0	75.6	76.7	77.0	78.4	80.4	82.6	86.0	89.8	94.8	103.1
67.5°	63.0	63.5	64.0	64.6	65.4	67.6	69.0	71.4	74.6	78.8	84.4
70°	55.8	55.8	55.8	56.3	57.4	58.5	59.9	61.9	65.0	68.5	73.6
72.5°	47.7	48.3	48.9	48.6	49.9	50.5	52.3	53.4	56.3	58.6	63.1
75°	37.5	37.5	37.5	38.3	38.9	39.4	40.5	41.6	43.0	45.9	48.2
77.5°	28.0	27.9	28.0	28.3	28.8	29.5	29.8	30.7	32.1	33.4	35.4
80°	21.6	21.9	22.1	22.5	22.5	22.8	23.1	24.3	25.2	26.1	27.3
82.5°	16.7	16.8	16.8	16.9	17.0	17.3	17.7	18.1	18.5	19.2	20.1
85°	9.7	9.5	9.5	9.9	9.7	9.7	10.1	10.5	10.5	10.6	11.2
87.5°	10.0	10.0	10.1	9.9	9.8	10.0	10.1	10.0	10.2	10.5	9.7
90°	31.3	31.1	30.9	30.7	30.5	30.6	31.0	31.4	31.8	32.2	27.7
92.5°	29.8	29.8	29.7	29.7	29.6	29.6	29.5	29.4	29.3	29.2	28.2
95°	57.0	57.4	57.9	58.3	58.7	58.9	58.9	58.9	58.9	58.9	58.5
97.5°	98.9	98.9	98.9	98.9	99.0	99.0	99.0	99.0	99.0	99.0	98.2
100°	126.0	126.3	126.5	126.7	126.9	127.0	127.0	127.0	127.0	127.0	126.4
102.5°	157.0	157.2	157.4	157.6	157.8	157.8	157.6	157.5	157.3	157.2	156.4
105°	204.3	204.3	204.3	204.3	204.3	204.1	203.7	203.3	202.9	202.4	202.0
107.5°	248.8	249.8	250.7	251.7	252.5	252.9	252.8	252.6	252.5	252.3	252.3
110°	283.4	284.0	284.6	285.3	285.9	286.2	286.2	286.2	286.2	286.2	286.2



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	316.6	317.0	317.4	317.9	318.4	318.9	319.3	319.8	320.3	320.8	320.9
115°	368.0	368.7	369.3	369.9	370.5	370.9	371.1	371.4	371.5	371.8	372.2
117.5°	417.2	417.8	418.4	419.1	419.7	420.3	420.7	421.2	421.7	422.2	423.3
120°	451.8	452.4	453.0	453.7	454.2	454.6	454.6	454.6	454.6	454.6	456.2
122.5°	485.7	486.2	486.6	487.0	487.5	487.9	488.5	488.9	489.4	489.9	491.1
125°	537.4	537.6	537.8	538.0	538.2	538.6	539.2	539.9	540.4	541.1	541.7
127.5°	584.5	585.2	585.8	586.5	587.1	587.8	588.5	589.3	590.0	590.7	591.5
130°	618.4	619.2	620.0	620.8	621.6	622.3	622.7	623.1	623.4	623.9	624.3
132.5°	650.8	651.4	652.0	652.8	653.4	654.2	655.1	655.9	656.9	657.7	657.7
135°	701.2	701.8	702.4	703.0	703.6	704.0	704.3	704.5	704.6	704.9	704.5
137.5°	746.8	747.7	748.5	749.2	750.1	750.6	750.8	750.9	751.1	751.2	750.7
140°	778.5	779.3	780.1	780.9	781.7	782.1	782.1	782.1	782.1	782.1	781.2
142.5°	807.2	808.0	808.8	809.6	810.5	810.8	810.6	810.5	810.3	810.2	809.5
145°	850.2	851.0	851.9	852.7	853.5	853.8	853.7	853.4	853.2	853.0	851.8
147.5°	888.7	889.5	890.3	891.0	891.8	892.0	891.5	891.1	890.7	890.2	889.4
150°	913.8	914.3	915.0	915.6	916.2	916.2	915.6	915.0	914.3	913.8	912.9
152.5°	937.3	938.1	938.9	939.6	940.4	940.4	939.6	938.9	938.1	937.3	936.4
155°	968.9	969.6	970.2	970.8	971.4	971.2	970.2	969.2	968.1	967.1	966.5
157.5°	996.2	997.2	998.1	999.1	1000.1	999.9	998.5	997.1	995.8	994.3	994.0
160°	1013.1	1013.9	1014.8	1015.6	1016.4	1016.2	1014.9	1013.8	1012.5	1011.3	1011.1
162.5°	1027.9	1028.8	1029.8	1030.8	1031.7	1031.6	1030.2	1028.8	1027.4	1026.0	1025.8
165°	1047.2	1048.2	1049.2	1050.3	1051.2	1051.1	1049.6	1048.2	1046.8	1045.4	1045.4
167.5°	1063.0	1064.1	1065.1	1066.2	1067.2	1067.1	1065.6	1064.2	1062.8	1061.4	1061.4
170°	1071.1	1072.3	1073.6	1074.8	1076.0	1075.9	1074.4	1073.0	1071.6	1070.2	1070.4
172.5°	1077.7	1079.0	1080.1	1081.4	1082.6	1082.5	1081.1	1079.7	1078.2	1076.8	1077.0
175°	1084.9	1086.2	1087.3	1088.6	1089.8	1089.7	1088.3	1086.9	1085.4	1083.9	1084.4
177.5°	1088.2	1089.2	1090.2	1091.2	1092.1	1092.1	1091.2	1090.2	1089.2	1088.2	1088.5
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	480.5	479.3	478.6	476.0	473.7	471.4	470.7	471.0	467.8	464.8	463.5
5°	499.2	495.6	492.2	487.4	481.6	475.2	472.1	469.5	463.2	456.4	452.4
7.5°	515.9	510.8	504.2	495.1	486.7	476.8	470.5	464.9	455.7	446.1	440.1
10°	526.2	519.2	510.7	499.6	489.3	477.2	468.8	460.3	449.6	438.0	430.8
12.5°	535.0	525.5	517.2	502.9	490.8	475.6	465.6	453.7	442.4	428.6	421.6
15°	555.9	538.4	522.6	506.4	491.5	470.4	459.2	443.2	428.3	411.4	403.3
17.5°	572.0	552.4	527.5	506.9	489.5	466.1	449.8	430.6	413.0	393.6	382.6
20°	581.2	558.7	532.0	507.5	486.6	459.9	442.1	422.6	401.9	380.1	368.2
22.5°	586.7	563.1	536.5	505.3	480.9	455.0	432.5	411.0	390.1	366.5	354.1
25°	588.4	566.9	538.8	503.5	473.6	444.3	417.3	396.4	371.1	349.1	331.0
27.5°	579.9	564.4	537.4	500.1	465.3	431.0	400.9	377.3	350.5	326.7	308.4
30°	569.3	560.4	534.1	496.7	458.7	421.8	388.7	361.9	335.3	311.2	292.4
32.5°	553.1	551.2	528.1	491.8	451.6	410.2	375.9	348.8	319.2	295.6	277.7
35°	521.2	529.8	515.2	480.9	438.4	393.6	356.5	325.5	294.9	272.3	255.6
37.5°	478.3	499.8	496.0	464.9	420.4	375.5	334.5	302.2	273.1	250.2	233.8
40°	448.8	476.2	480.1	452.6	407.8	361.6	318.1	286.0	257.5	236.6	220.1
42.5°	417.2	449.1	459.9	437.9	394.0	346.8	303.5	270.1	241.9	221.7	207.0
45°	364.1	406.3	426.0	413.4	370.9	322.7	278.1	244.2	218.6	199.6	188.2
47.5°	314.4	360.6	387.0	382.5	345.2	297.5	253.3	220.9	196.0	180.8	170.6
50°	279.3	326.8	358.6	360.1	326.8	279.5	235.2	204.6	181.7	167.5	159.2
52.5°	248.7	294.1	328.8	336.5	306.2	260.8	219.0	188.5	168.3	155.3	147.9
55°	208.9	247.2	285.7	299.8	275.5	232.3	193.6	166.8	147.9	138.9	132.5
57.5°	173.7	205.7	241.2	256.7	241.8	204.8	168.5	145.2	129.9	122.0	117.0
60°	155.1	180.3	212.0	230.5	217.5	184.7	153.0	130.8	118.2	111.2	106.5
62.5°	137.8	160.2	187.0	203.9	196.9	165.8	137.4	117.9	107.0	100.4	97.0
65°	113.8	131.3	152.1	167.7	163.0	139.5	116.2	99.5	90.9	85.6	82.9
67.5°	93.6	106.4	120.7	134.4	130.7	114.0	95.4	82.3	75.9	71.4	69.7
70°	81.0	90.7	103.5	114.5	111.4	97.8	82.9	71.8	66.2	62.4	60.8
72.5°	68.9	76.8	86.7	95.6	93.6	82.1	69.9	61.5	57.1	53.6	52.4
75°	52.0	58.1	64.1	70.0	69.5	60.7	53.5	47.0	43.6	40.9	40.3
77.5°	38.4	41.8	45.9	49.4	48.4	43.3	37.7	34.0	31.5	29.7	29.4
80°	29.3	31.3	34.2	36.7	35.5	33.3	28.8	26.1	24.3	22.5	21.8
82.5°	21.3	23.2	25.0	26.4	25.3	23.4	20.6	18.8	17.7	16.5	16.2
85°	11.2	12.2	13.0	13.3	13.0	11.7	10.5	9.7	8.8	8.2	8.1
87.5°	9.0	8.1	7.1	6.7	5.9	5.3	4.3	3.3	3.7	4.0	4.3
90°	23.2	18.7	14.2	10.8	8.3	5.9	3.4	1.0	3.4	5.9	8.3
92.5°	27.2	26.1	25.0	23.6	21.8	20.0	18.1	16.4	18.1	20.0	21.8
95°	58.1	57.7	57.3	56.0	53.9	52.0	49.9	47.8	49.9	52.0	53.9
97.5°	97.4	96.6	95.9	94.6	92.8	91.0	89.2	87.5	89.2	91.0	92.8
100°	125.7	125.2	124.5	123.4	121.8	120.2	118.5	116.8	118.5	120.2	121.8
102.5°	155.6	154.9	154.1	153.0	151.7	150.4	149.1	147.8	149.1	150.4	151.7
105°	201.6	201.2	200.8	200.3	199.7	199.1	198.4	197.8	198.4	199.1	199.7
107.5°	252.3	252.3	252.3	251.8	251.0	250.1	249.1	248.3	249.1	250.1	251.0
110°	286.2	286.2	286.2	285.6	284.3	283.1	281.9	280.7	281.9	283.1	284.3



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	321.1	321.2	321.5	320.9	319.6	318.5	317.2	316.0	317.2	318.5	319.6
115°	372.6	373.0	373.4	373.0	371.8	370.5	369.3	368.0	369.3	370.5	371.8
117.5°	424.5	425.6	426.7	426.5	424.8	423.3	421.6	419.9	421.6	423.3	424.8
120°	457.9	459.5	461.1	461.1	459.5	457.9	456.2	454.6	456.2	457.9	459.5
122.5°	492.2	493.4	494.5	494.1	492.1	490.1	488.2	486.2	488.2	490.1	492.1
125°	542.3	542.9	543.5	542.9	541.1	539.2	537.4	535.5	537.4	539.2	541.1
127.5°	592.2	592.9	593.7	592.9	590.6	588.3	585.9	583.6	585.9	588.3	590.6
130°	624.7	625.1	625.5	624.4	621.7	619.1	616.4	613.8	616.4	619.1	621.7
132.5°	657.6	657.5	657.4	656.3	654.1	652.0	649.8	647.6	649.8	652.0	654.1
135°	704.0	703.6	703.2	701.9	699.7	697.4	695.1	692.9	695.1	697.4	699.7
137.5°	750.2	749.6	749.1	747.9	746.1	744.3	742.4	740.5	742.4	744.3	746.1
140°	780.1	779.1	778.1	776.7	774.8	772.9	771.1	769.3	771.1	772.9	774.8
142.5°	808.7	808.0	807.3	806.0	804.2	802.4	800.6	798.8	800.6	802.4	804.2
145°	850.6	849.3	848.1	846.8	845.3	843.9	842.5	841.1	842.5	843.9	845.3
147.5°	888.6	887.7	886.9	885.7	883.9	882.2	880.5	878.8	880.5	882.2	883.9
150°	912.1	911.3	910.5	909.4	908.2	907.0	905.8	904.5	905.8	907.0	908.2
152.5°	935.3	934.4	933.3	932.2	931.1	929.8	928.6	927.3	928.6	929.8	931.1
155°	965.9	965.3	964.6	964.1	963.5	962.8	962.2	961.6	962.2	962.8	963.5
157.5°	993.6	993.2	992.8	992.5	992.0	991.7	991.3	990.9	991.3	991.7	992.0
160°	1010.9	1010.7	1010.4	1010.2	1009.7	1009.3	1008.9	1008.5	1008.9	1009.3	1009.7
162.5°	1025.6	1025.4	1025.2	1025.1	1024.9	1024.8	1024.8	1024.7	1024.8	1024.8	1024.9
165°	1045.4	1045.4	1045.4	1045.4	1045.6	1045.8	1046.1	1046.2	1046.1	1045.8	1045.6
167.5°	1061.4	1061.4	1061.5	1061.8	1062.5	1063.0	1063.7	1064.3	1063.7	1063.0	1062.5
170°	1070.6	1070.8	1071.0	1071.4	1072.0	1072.6	1073.2	1073.9	1073.2	1072.6	1072.0
172.5°	1077.2	1077.4	1077.6	1078.0	1078.6	1079.3	1079.9	1080.5	1079.9	1079.3	1078.6
175°	1084.8	1085.2	1085.6	1086.2	1086.7	1087.3	1088.0	1088.6	1088.0	1087.3	1086.7
177.5°	1088.9	1089.2	1089.5	1090.0	1090.4	1090.9	1091.4	1091.9	1091.4	1090.9	1090.4
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	462.1	461.2	458.2	456.6	454.0	451.5	450.0	450.7	451.2	451.0	450.5
5°	448.8	445.4	440.1	435.7	432.5	426.5	424.0	422.7	421.6	420.4	419.1
7.5°	433.0	427.6	420.2	413.8	407.7	400.3	396.1	393.6	391.0	388.2	385.6
10°	421.8	414.2	406.3	397.4	390.1	383.5	377.6	373.6	369.9	366.5	364.1
12.5°	410.0	401.3	391.5	379.2	371.3	361.7	360.8	353.9	348.2	346.1	343.2
15°	391.3	379.0	366.5	352.0	345.7	337.1	331.7	326.2	321.4	318.0	317.1
17.5°	369.9	354.0	341.7	331.2	320.9	312.0	307.0	302.8	298.7	294.2	293.6
20°	353.6	339.9	326.5	317.3	306.7	297.6	291.5	287.2	283.8	281.1	278.8
22.5°	338.2	323.2	310.9	300.9	290.4	283.1	278.3	274.1	271.2	268.3	266.1
25°	313.5	301.8	288.3	276.9	268.3	263.6	259.7	256.1	254.3	252.3	249.8
27.5°	291.8	278.8	266.3	257.5	249.9	245.7	242.9	240.4	238.8	237.6	236.1
30°	276.6	263.5	253.6	244.9	238.6	234.5	232.7	231.2	229.3	228.5	227.8
32.5°	261.9	250.1	241.6	234.1	228.1	225.4	223.8	222.4	220.9	220.2	218.7
35°	241.1	231.2	223.0	218.8	214.0	211.6	210.4	208.6	207.2	206.4	206.2
37.5°	221.6	213.0	207.6	202.2	200.2	198.8	197.0	195.8	195.4	195.3	195.0
40°	208.9	201.9	197.0	192.7	191.9	189.6	188.2	187.2	187.2	187.4	187.2
42.5°	197.4	191.1	186.8	183.1	182.0	180.8	179.3	179.3	179.5	180.1	179.5
45°	180.0	175.5	172.4	170.6	168.7	167.4	167.2	167.7	167.9	168.1	168.7
47.5°	163.9	160.9	158.1	156.1	155.3	155.1	154.9	155.8	156.7	157.0	157.8
50°	154.4	151.0	148.6	147.3	146.6	146.3	146.6	147.7	148.5	149.3	149.9
52.5°	143.8	141.3	139.7	138.7	138.5	138.7	138.7	140.0	141.1	141.5	141.7
55°	129.0	127.2	126.9	125.2	126.0	125.8	126.7	127.4	128.5	129.6	129.8
57.5°	114.3	112.9	111.9	112.1	112.3	113.1	113.8	115.1	116.2	117.4	117.5
60°	104.6	103.9	103.3	103.3	103.6	104.7	105.6	106.9	107.6	108.4	108.8
62.5°	95.6	94.9	94.3	94.7	95.6	96.3	97.3	98.0	98.7	99.4	99.7
65°	81.5	81.2	81.7	82.1	82.2	83.1	84.4	84.9	85.6	86.0	87.3
67.5°	68.5	68.6	68.5	69.0	70.1	70.3	71.5	72.7	72.9	73.6	74.4
70°	59.7	60.1	60.4	60.8	61.7	62.1	63.0	63.5	64.2	64.8	65.4
72.5°	51.7	51.7	52.1	52.0	52.8	53.6	54.3	54.9	55.6	56.3	56.8
75°	39.8	39.8	40.2	40.3	41.2	42.1	41.9	42.3	43.0	43.7	44.1
77.5°	29.1	28.7	29.1	29.2	29.5	30.3	30.4	30.9	31.8	31.5	31.9
80°	22.1	21.6	22.1	22.3	22.3	23.2	23.2	23.6	24.1	23.6	24.1
82.5°	15.8	15.5	15.9	16.0	16.2	16.3	16.6	16.6	17.2	17.0	17.2
85°	7.9	7.8	7.9	7.8	7.9	8.1	8.1	7.9	7.9	8.2	7.8
87.5°	4.6	5.1	5.9	6.8	7.5	8.3	8.1	8.0	7.9	7.5	7.5
90°	10.8	14.2	18.7	23.2	27.7	32.2	31.8	31.4	31.0	30.6	30.5
92.5°	23.6	25.0	26.1	27.2	28.2	29.2	29.3	29.4	29.5	29.6	29.6
95°	56.0	57.3	57.7	58.1	58.5	58.9	58.9	58.9	58.9	58.9	58.7
97.5°	94.6	95.9	96.6	97.4	98.2	99.0	99.0	99.0	99.0	99.0	99.0
100°	123.4	124.5	125.2	125.7	126.4	127.0	127.0	127.0	127.0	127.0	126.9
102.5°	153.0	154.1	154.9	155.6	156.4	157.2	157.3	157.5	157.6	157.8	157.8
105°	200.3	200.8	201.2	201.6	202.0	202.4	202.9	203.3	203.7	204.1	204.3
107.5°	251.8	252.3	252.3	252.3	252.3	252.3	252.5	252.6	252.8	252.9	252.5
110°	285.6	286.2	286.2	286.2	286.2	286.2	286.2	286.2	286.2	286.2	285.9



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	320.9	321.5	321.2	321.1	320.9	320.8	320.3	319.8	319.3	318.9	318.4
115°	373.0	373.4	373.0	372.6	372.2	371.8	371.5	371.4	371.1	370.9	370.5
117.5°	426.5	426.7	425.6	424.5	423.3	422.2	421.7	421.2	420.7	420.3	419.7
120°	461.1	461.1	459.5	457.9	456.2	454.6	454.6	454.6	454.6	454.6	454.2
122.5°	494.1	494.5	493.4	492.2	491.1	489.9	489.4	488.9	488.5	487.9	487.5
125°	542.9	543.5	542.9	542.3	541.7	541.1	540.4	539.9	539.2	538.6	538.2
127.5°	592.9	593.7	592.9	592.2	591.5	590.7	590.0	589.3	588.5	587.8	587.1
130°	624.4	625.5	625.1	624.7	624.3	623.9	623.4	623.1	622.7	622.3	621.6
132.5°	656.3	657.4	657.5	657.6	657.7	657.7	656.9	655.9	655.1	654.2	653.4
135°	701.9	703.2	703.6	704.0	704.5	704.9	704.6	704.5	704.3	704.0	703.6
137.5°	747.9	749.1	749.6	750.2	750.7	751.2	751.1	750.9	750.8	750.6	750.1
140°	776.7	778.1	779.1	780.1	781.2	782.1	782.1	782.1	782.1	782.1	781.7
142.5°	806.0	807.3	808.0	808.7	809.5	810.2	810.3	810.5	810.6	810.8	810.5
145°	846.8	848.1	849.3	850.6	851.8	853.0	853.2	853.4	853.7	853.8	853.5
147.5°	885.7	886.9	887.7	888.6	889.4	890.2	890.7	891.1	891.5	892.0	891.8
150°	909.4	910.5	911.3	912.1	912.9	913.8	914.3	915.0	915.6	916.2	916.2
152.5°	932.2	933.3	934.4	935.3	936.4	937.3	938.1	938.9	939.6	940.4	940.4
155°	964.1	964.6	965.3	965.9	966.5	967.1	968.1	969.2	970.2	971.2	971.4
157.5°	992.5	992.8	993.2	993.6	994.0	994.3	995.8	997.1	998.5	999.9	1000.1
160°	1010.2	1010.4	1010.7	1010.9	1011.1	1011.3	1012.5	1013.8	1014.9	1016.2	1016.4
162.5°	1025.1	1025.2	1025.4	1025.6	1025.8	1026.0	1027.4	1028.8	1030.2	1031.6	1031.7
165°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1046.8	1048.2	1049.6	1051.1	1051.2
167.5°	1061.8	1061.5	1061.4	1061.4	1061.4	1061.4	1062.8	1064.2	1065.6	1067.1	1067.2
170°	1071.4	1071.0	1070.8	1070.6	1070.4	1070.2	1071.6	1073.0	1074.4	1075.9	1076.0
172.5°	1078.0	1077.6	1077.4	1077.2	1077.0	1076.8	1078.2	1079.7	1081.1	1082.5	1082.6
175°	1086.2	1085.6	1085.2	1084.8	1084.4	1083.9	1085.4	1086.9	1088.3	1089.7	1089.8
177.5°	1090.0	1089.5	1089.2	1088.9	1088.5	1088.2	1089.2	1090.2	1091.2	1092.1	1092.1
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	449.1	448.8	448.8	447.5	448.8	448.8	449.1	450.5	451.0	451.2	450.7
5°	416.6	416.1	415.2	416.1	415.2	416.1	416.6	419.1	420.4	421.6	422.7
7.5°	384.4	382.3	382.0	379.9	382.0	382.3	384.4	385.6	388.2	391.0	393.6
10°	361.0	359.6	359.3	355.9	359.3	359.6	361.0	364.1	366.5	369.9	373.6
12.5°	343.2	339.7	340.4	338.4	340.4	339.7	343.2	343.2	346.1	348.2	353.9
15°	312.2	312.2	311.5	308.5	311.5	312.2	312.2	317.1	318.0	321.4	326.2
17.5°	290.0	289.6	288.0	288.8	288.0	289.6	290.0	293.6	294.2	298.7	302.8
20°	276.8	275.7	273.5	273.5	273.5	275.7	276.8	278.8	281.1	283.8	287.2
22.5°	264.3	264.2	261.9	262.6	261.9	264.2	264.3	266.1	268.3	271.2	274.1
25°	249.6	248.2	247.1	247.6	247.1	248.2	249.6	249.8	252.3	254.3	256.1
27.5°	235.7	234.9	234.8	233.4	234.8	234.9	235.7	236.1	237.6	238.8	240.4
30°	227.7	225.9	226.2	225.3	226.2	225.9	227.7	227.8	228.5	229.3	231.2
32.5°	218.4	217.8	217.5	216.7	217.5	217.8	218.4	218.7	220.2	220.9	222.4
35°	205.9	206.0	205.2	205.5	205.2	206.0	205.9	206.2	206.4	207.2	208.6
37.5°	194.9	195.4	195.0	195.1	195.0	195.4	194.9	195.0	195.3	195.4	195.8
40°	187.7	187.7	187.7	188.2	187.7	187.7	187.7	187.2	187.4	187.2	187.2
42.5°	180.8	180.5	180.2	180.1	180.2	180.5	180.8	179.5	180.1	179.5	179.3
45°	169.0	169.5	169.7	168.8	169.7	169.5	169.0	168.7	168.1	167.9	167.7
47.5°	158.3	158.4	158.3	159.1	158.3	158.4	158.3	157.8	157.0	156.7	155.8
50°	150.8	150.4	150.8	150.4	150.8	150.4	150.8	149.9	149.3	148.5	147.7
52.5°	142.9	143.0	142.8	142.7	142.8	143.0	142.9	141.7	141.5	141.1	140.0
55°	130.5	130.8	130.6	130.6	130.6	130.8	130.5	129.8	129.6	128.5	127.4
57.5°	117.6	118.0	118.2	117.4	118.2	118.0	117.6	117.5	117.4	116.2	115.1
60°	108.7	109.6	109.4	109.1	109.4	109.6	108.7	108.8	108.4	107.6	106.9
62.5°	100.4	100.8	100.8	100.7	100.8	100.8	100.4	99.7	99.4	98.7	98.0
65°	87.9	88.2	87.6	88.2	87.6	88.2	87.9	87.3	86.0	85.6	84.9
67.5°	74.1	74.3	74.7	74.9	74.7	74.3	74.1	74.4	73.6	72.9	72.7
70°	65.7	65.5	66.1	66.6	66.1	65.5	65.7	65.4	64.8	64.2	63.5
72.5°	56.7	57.1	57.0	57.4	57.0	57.1	56.7	56.8	56.3	55.6	54.9
75°	43.7	44.3	44.1	44.6	44.1	44.3	43.7	44.1	43.7	43.0	42.3
77.5°	31.6	31.7	31.6	31.9	31.6	31.7	31.6	31.9	31.5	31.8	30.9
80°	24.1	23.8	23.4	24.1	23.4	23.8	24.1	24.1	23.6	24.1	23.6
82.5°	16.8	17.0	16.6	16.6	16.6	17.0	16.8	17.2	17.0	17.2	16.6
85°	7.8	7.5	7.2	7.2	7.2	7.5	7.8	7.8	8.2	7.9	7.9
87.5°	7.6	7.4	7.5	7.4	7.5	7.4	7.6	7.5	7.5	7.9	8.0
90°	30.7	30.9	31.1	31.3	31.1	30.9	30.7	30.5	30.6	31.0	31.4
92.5°	29.7	29.7	29.8	29.8	29.8	29.7	29.7	29.6	29.6	29.5	29.4
95°	58.3	57.9	57.4	57.0	57.4	57.9	58.3	58.7	58.9	58.9	58.9
97.5°	98.9	98.9	98.9	98.9	98.9	98.9	98.9	99.0	99.0	99.0	99.0
100°	126.7	126.5	126.3	126.0	126.3	126.5	126.7	126.9	127.0	127.0	127.0
102.5°	157.6	157.4	157.2	157.0	157.2	157.4	157.6	157.8	157.8	157.6	157.5
105°	204.3	204.3	204.3	204.3	204.3	204.3	204.3	204.3	204.1	203.7	203.3
107.5°	251.7	250.7	249.8	248.8	249.8	250.7	251.7	252.5	252.9	252.8	252.6
110°	285.3	284.6	284.0	283.4	284.0	284.6	285.3	285.9	286.2	286.2	286.2



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	317.9	317.4	317.0	316.6	317.0	317.4	317.9	318.4	318.9	319.3	319.8
115°	369.9	369.3	368.7	368.0	368.7	369.3	369.9	370.5	370.9	371.1	371.4
117.5°	419.1	418.4	417.8	417.2	417.8	418.4	419.1	419.7	420.3	420.7	421.2
120°	453.7	453.0	452.4	451.8	452.4	453.0	453.7	454.2	454.6	454.6	454.6
122.5°	487.0	486.6	486.2	485.7	486.2	486.6	487.0	487.5	487.9	488.5	488.9
125°	538.0	537.8	537.6	537.4	537.6	537.8	538.0	538.2	538.6	539.2	539.9
127.5°	586.5	585.8	585.2	584.5	585.2	585.8	586.5	587.1	587.8	588.5	589.3
130°	620.8	620.0	619.2	618.4	619.2	620.0	620.8	621.6	622.3	622.7	623.1
132.5°	652.8	652.0	651.4	650.8	651.4	652.0	652.8	653.4	654.2	655.1	655.9
135°	703.0	702.4	701.8	701.2	701.8	702.4	703.0	703.6	704.0	704.3	704.5
137.5°	749.2	748.5	747.7	746.8	747.7	748.5	749.2	750.1	750.6	750.8	750.9
140°	780.9	780.1	779.3	778.5	779.3	780.1	780.9	781.7	782.1	782.1	782.1
142.5°	809.6	808.8	808.0	807.2	808.0	808.8	809.6	810.5	810.8	810.6	810.5
145°	852.7	851.9	851.0	850.2	851.0	851.9	852.7	853.5	853.8	853.7	853.4
147.5°	891.0	890.3	889.5	888.7	889.5	890.3	891.0	891.8	892.0	891.5	891.1
150°	915.6	915.0	914.3	913.8	914.3	915.0	915.6	916.2	916.2	915.6	915.0
152.5°	939.6	938.9	938.1	937.3	938.1	938.9	939.6	940.4	940.4	939.6	938.9
155°	970.8	970.2	969.6	968.9	969.6	970.2	970.8	971.4	971.2	970.2	969.2
157.5°	999.1	998.1	997.2	996.2	997.2	998.1	999.1	1000.1	999.9	998.5	997.1
160°	1015.6	1014.8	1013.9	1013.1	1013.9	1014.8	1015.6	1016.4	1016.2	1014.9	1013.8
162.5°	1030.8	1029.8	1028.8	1027.9	1028.8	1029.8	1030.8	1031.7	1031.6	1030.2	1028.8
165°	1050.3	1049.2	1048.2	1047.2	1048.2	1049.2	1050.3	1051.2	1051.1	1049.6	1048.2
167.5°	1066.2	1065.1	1064.1	1063.0	1064.1	1065.1	1066.2	1067.2	1067.1	1065.6	1064.2
170°	1074.8	1073.6	1072.3	1071.1	1072.3	1073.6	1074.8	1076.0	1075.9	1074.4	1073.0
172.5°	1081.4	1080.1	1079.0	1077.7	1079.0	1080.1	1081.4	1082.6	1082.5	1081.1	1079.7
175°	1088.6	1087.3	1086.2	1084.9	1086.2	1087.3	1088.6	1089.8	1089.7	1088.3	1086.9
177.5°	1091.2	1090.2	1089.2	1088.2	1089.2	1090.2	1091.2	1092.1	1092.1	1091.2	1090.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	450.0	451.5	454.0	456.6	458.2	461.2	462.1	463.5	464.8	467.8	471.0
5°	424.0	426.5	432.5	435.7	440.1	445.4	448.8	452.4	456.4	463.2	469.5
7.5°	396.1	400.3	407.7	413.8	420.2	427.6	433.0	440.1	446.1	455.7	464.9
10°	377.6	383.5	390.1	397.4	406.3	414.2	421.8	430.8	438.0	449.6	460.3
12.5°	360.8	361.7	371.3	379.2	391.5	401.3	410.0	421.6	428.6	442.4	453.7
15°	331.7	337.1	345.7	352.0	366.5	379.0	391.3	403.3	411.4	428.3	443.2
17.5°	307.0	312.0	320.9	331.2	341.7	354.0	369.9	382.6	393.6	413.0	430.6
20°	291.5	297.6	306.7	317.3	326.5	339.9	353.6	368.2	380.1	401.9	422.6
22.5°	278.3	283.1	290.4	300.9	310.9	323.2	338.2	354.1	366.5	390.1	411.0
25°	259.7	263.6	268.3	276.9	288.3	301.8	313.5	331.0	349.1	371.1	396.4
27.5°	242.9	245.7	249.9	257.5	266.3	278.8	291.8	308.4	326.7	350.5	377.3
30°	232.7	234.5	238.6	244.9	253.6	263.5	276.6	292.4	311.2	335.3	361.9
32.5°	223.8	225.4	228.1	234.1	241.6	250.1	261.9	277.7	295.6	319.2	348.8
35°	210.4	211.6	214.0	218.8	223.0	231.2	241.1	255.6	272.3	294.9	325.5
37.5°	197.0	198.8	200.2	202.2	207.6	213.0	221.6	233.8	250.2	273.1	302.2
40°	188.2	189.6	191.9	192.7	197.0	201.9	208.9	220.1	236.6	257.5	286.0
42.5°	179.3	180.8	182.0	183.1	186.8	191.1	197.4	207.0	221.7	241.9	270.1
45°	167.2	167.4	168.7	170.6	172.4	175.5	180.0	188.2	199.6	218.6	244.2
47.5°	154.9	155.1	155.3	156.1	158.1	160.9	163.9	170.6	180.8	196.0	220.9
50°	146.6	146.3	146.6	147.3	148.6	151.0	154.4	159.2	167.5	181.7	204.6
52.5°	138.7	138.7	138.5	138.7	139.7	141.3	143.8	147.9	155.3	168.3	188.5
55°	126.7	125.8	126.0	125.2	126.9	127.2	129.0	132.5	138.9	147.9	166.8
57.5°	113.8	113.1	112.3	112.1	111.9	112.9	114.3	117.0	122.0	129.9	145.2
60°	105.6	104.7	103.6	103.3	103.3	103.9	104.6	106.5	111.2	118.2	130.8
62.5°	97.3	96.3	95.6	94.7	94.3	94.9	95.6	97.0	100.4	107.0	117.9
65°	84.4	83.1	82.2	82.1	81.7	81.2	81.5	82.9	85.6	90.9	99.5
67.5°	71.5	70.3	70.1	69.0	68.5	68.6	68.5	69.7	71.4	75.9	82.3
70°	63.0	62.1	61.7	60.8	60.4	60.1	59.7	60.8	62.4	66.2	71.8
72.5°	54.3	53.6	52.8	52.0	52.1	51.7	51.7	52.4	53.6	57.1	61.5
75°	41.9	42.1	41.2	40.3	40.2	39.8	39.8	40.3	40.9	43.6	47.0
77.5°	30.4	30.3	29.5	29.2	29.1	28.7	29.1	29.4	29.7	31.5	34.0
80°	23.2	23.2	22.3	22.3	22.1	21.6	22.1	21.8	22.5	24.3	26.1
82.5°	16.6	16.3	16.2	16.0	15.9	15.5	15.8	16.2	16.5	17.7	18.8
85°	8.1	8.1	7.9	7.8	7.9	7.8	7.9	8.1	8.2	8.8	9.7
87.5°	8.1	8.3	7.5	6.8	5.9	5.1	4.6	4.3	4.0	3.7	3.3
90°	31.8	32.2	27.7	23.2	18.7	14.2	10.8	8.3	5.9	3.4	1.0
92.5°	29.3	29.2	28.2	27.2	26.1	25.0	23.6	21.8	20.0	18.1	16.4
95°	58.9	58.9	58.5	58.1	57.7	57.3	56.0	53.9	52.0	49.9	47.8
97.5°	99.0	99.0	98.2	97.4	96.6	95.9	94.6	92.8	91.0	89.2	87.5
100°	127.0	127.0	126.4	125.7	125.2	124.5	123.4	121.8	120.2	118.5	116.8
102.5°	157.3	157.2	156.4	155.6	154.9	154.1	153.0	151.7	150.4	149.1	147.8
105°	202.9	202.4	202.0	201.6	201.2	200.8	200.3	199.7	199.1	198.4	197.8
107.5°	252.5	252.3	252.3	252.3	252.3	252.3	251.8	251.0	250.1	249.1	248.3
110°	286.2	286.2	286.2	286.2	286.2	286.2	285.6	284.3	283.1	281.9	280.7



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	320.3	320.8	320.9	321.1	321.2	321.5	320.9	319.6	318.5	317.2	316.0
115°	371.5	371.8	372.2	372.6	373.0	373.4	373.0	371.8	370.5	369.3	368.0
117.5°	421.7	422.2	423.3	424.5	425.6	426.7	426.5	424.8	423.3	421.6	419.9
120°	454.6	454.6	456.2	457.9	459.5	461.1	461.1	459.5	457.9	456.2	454.6
122.5°	489.4	489.9	491.1	492.2	493.4	494.5	494.1	492.1	490.1	488.2	486.2
125°	540.4	541.1	541.7	542.3	542.9	543.5	542.9	541.1	539.2	537.4	535.5
127.5°	590.0	590.7	591.5	592.2	592.9	593.7	592.9	590.6	588.3	585.9	583.6
130°	623.4	623.9	624.3	624.7	625.1	625.5	624.4	621.7	619.1	616.4	613.8
132.5°	656.9	657.7	657.7	657.6	657.5	657.4	656.3	654.1	652.0	649.8	647.6
135°	704.6	704.9	704.5	704.0	703.6	703.2	701.9	699.7	697.4	695.1	692.9
137.5°	751.1	751.2	750.7	750.2	749.6	749.1	747.9	746.1	744.3	742.4	740.5
140°	782.1	782.1	781.2	780.1	779.1	778.1	776.7	774.8	772.9	771.1	769.3
142.5°	810.3	810.2	809.5	808.7	808.0	807.3	806.0	804.2	802.4	800.6	798.8
145°	853.2	853.0	851.8	850.6	849.3	848.1	846.8	845.3	843.9	842.5	841.1
147.5°	890.7	890.2	889.4	888.6	887.7	886.9	885.7	883.9	882.2	880.5	878.8
150°	914.3	913.8	912.9	912.1	911.3	910.5	909.4	908.2	907.0	905.8	904.5
152.5°	938.1	937.3	936.4	935.3	934.4	933.3	932.2	931.1	929.8	928.6	927.3
155°	968.1	967.1	966.5	965.9	965.3	964.6	964.1	963.5	962.8	962.2	961.6
157.5°	995.8	994.3	994.0	993.6	993.2	992.8	992.5	992.0	991.7	991.3	990.9
160°	1012.5	1011.3	1011.1	1010.9	1010.7	1010.4	1010.2	1009.7	1009.3	1008.9	1008.5
162.5°	1027.4	1026.0	1025.8	1025.6	1025.4	1025.2	1025.1	1024.9	1024.8	1024.8	1024.7
165°	1046.8	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.6	1045.8	1046.1	1046.2
167.5°	1062.8	1061.4	1061.4	1061.4	1061.4	1061.5	1061.8	1062.5	1063.0	1063.7	1064.3
170°	1071.6	1070.2	1070.4	1070.6	1070.8	1071.0	1071.4	1072.0	1072.6	1073.2	1073.9
172.5°	1078.2	1076.8	1077.0	1077.2	1077.4	1077.6	1078.0	1078.6	1079.3	1079.9	1080.5
175°	1085.4	1083.9	1084.4	1084.8	1085.2	1085.6	1086.2	1086.7	1087.3	1088.0	1088.6
177.5°	1089.2	1088.2	1088.5	1088.9	1089.2	1089.5	1090.0	1090.4	1090.9	1091.4	1091.9
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	470.7	471.4	473.7	476.0	478.6	479.3	480.5	479.5	479.2	481.9	483.9
5°	472.1	475.2	481.6	487.4	492.2	495.6	499.2	500.7	503.4	507.1	511.8
7.5°	470.5	476.8	486.7	495.1	504.2	510.8	515.9	520.4	525.7	532.8	540.7
10°	468.8	477.2	489.3	499.6	510.7	519.2	526.2	533.1	541.0	550.9	561.1
12.5°	465.6	475.6	490.8	502.9	517.2	525.5	535.0	549.7	558.3	572.0	586.5
15°	459.2	470.4	491.5	506.4	522.6	538.4	555.9	569.9	583.9	592.1	612.4
17.5°	449.8	466.1	489.5	506.9	527.5	552.4	572.0	588.0	604.1	617.3	627.5
20°	442.1	459.9	486.6	507.5	532.0	558.7	581.2	597.5	611.5	622.5	628.8
22.5°	432.5	455.0	480.9	505.3	536.5	563.1	586.7	599.4	611.2	616.6	619.0
25°	417.3	444.3	473.6	503.5	538.8	566.9	588.4	596.2	599.6	594.4	585.7
27.5°	400.9	431.0	465.3	500.1	537.4	564.4	579.9	578.7	572.9	556.0	542.5
30°	388.7	421.8	458.7	496.7	534.1	560.4	569.3	560.4	547.2	528.4	509.1
32.5°	375.9	410.2	451.6	491.8	528.1	551.2	553.1	537.7	517.3	495.8	471.8
35°	356.5	393.6	438.4	480.9	515.2	529.8	521.2	493.8	469.7	440.4	407.6
37.5°	334.5	375.5	420.4	464.9	496.0	499.8	478.3	449.6	415.5	381.0	342.5
40°	318.1	361.6	407.8	452.6	480.1	476.2	448.8	417.2	376.7	334.5	298.7
42.5°	303.5	346.8	394.0	437.9	459.9	449.1	417.2	378.3	334.8	295.1	262.3
45°	278.1	322.7	370.9	413.4	426.0	406.3	364.1	320.8	278.1	244.9	219.0
47.5°	253.3	297.5	345.2	382.5	387.0	360.6	314.4	270.0	233.1	206.2	187.9
50°	235.2	279.5	326.8	360.1	358.6	326.8	279.3	237.0	206.2	184.4	172.2
52.5°	219.0	260.8	306.2	336.5	328.8	294.1	248.7	211.2	185.9	168.9	157.8
55°	193.6	232.3	275.5	299.8	285.7	247.2	208.9	178.7	159.9	147.2	138.6
57.5°	168.5	204.8	241.8	256.7	241.2	205.7	173.7	151.8	137.7	128.3	122.6
60°	153.0	184.7	217.5	230.5	212.0	180.3	155.1	135.5	124.1	116.5	111.4
62.5°	137.4	165.8	196.9	203.9	187.0	160.2	137.8	121.5	112.3	105.4	100.6
65°	116.2	139.5	163.0	167.7	152.1	131.3	113.8	103.1	94.8	89.8	86.0
67.5°	95.4	114.0	130.7	134.4	120.7	106.4	93.6	84.4	78.8	74.6	71.4
70°	82.9	97.8	111.4	114.5	103.5	90.7	81.0	73.6	68.5	65.0	61.9
72.5°	69.9	82.1	93.6	95.6	86.7	76.8	68.9	63.1	58.6	56.3	53.4
75°	53.5	60.7	69.5	70.0	64.1	58.1	52.0	48.2	45.9	43.0	41.6
77.5°	37.7	43.3	48.4	49.4	45.9	41.8	38.4	35.4	33.4	32.1	30.7
80°	28.8	33.3	35.5	36.7	34.2	31.3	29.3	27.3	26.1	25.2	24.3
82.5°	20.6	23.4	25.3	26.4	25.0	23.2	21.3	20.1	19.2	18.5	18.1
85°	10.5	11.7	13.0	13.3	13.0	12.2	11.2	11.2	10.6	10.5	10.5
87.5°	4.3	5.3	5.9	6.7	7.1	8.1	9.0	9.7	10.5	10.2	10.0
90°	3.4	5.9	8.3	10.8	14.2	18.7	23.2	27.7	32.2	31.8	31.4
92.5°	18.1	20.0	21.8	23.6	25.0	26.1	27.2	28.2	29.2	29.3	29.4
95°	49.9	52.0	53.9	56.0	57.3	57.7	58.1	58.5	58.9	58.9	58.9
97.5°	89.2	91.0	92.8	94.6	95.9	96.6	97.4	98.2	99.0	99.0	99.0
100°	118.5	120.2	121.8	123.4	124.5	125.2	125.7	126.4	127.0	127.0	127.0
102.5°	149.1	150.4	151.7	153.0	154.1	154.9	155.6	156.4	157.2	157.3	157.5
105°	198.4	199.1	199.7	200.3	200.8	201.2	201.6	202.0	202.4	202.9	203.3
107.5°	249.1	250.1	251.0	251.8	252.3	252.3	252.3	252.3	252.3	252.5	252.6
110°	281.9	283.1	284.3	285.6	286.2	286.2	286.2	286.2	286.2	286.2	286.2



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	317.2	318.5	319.6	320.9	321.5	321.2	321.1	320.9	320.8	320.3	319.8
115°	369.3	370.5	371.8	373.0	373.4	373.0	372.6	372.2	371.8	371.5	371.4
117.5°	421.6	423.3	424.8	426.5	426.7	425.6	424.5	423.3	422.2	421.7	421.2
120°	456.2	457.9	459.5	461.1	461.1	459.5	457.9	456.2	454.6	454.6	454.6
122.5°	488.2	490.1	492.1	494.1	494.5	493.4	492.2	491.1	489.9	489.4	488.9
125°	537.4	539.2	541.1	542.9	543.5	542.9	542.3	541.7	541.1	540.4	539.9
127.5°	585.9	588.3	590.6	592.9	593.7	592.9	592.2	591.5	590.7	590.0	589.3
130°	616.4	619.1	621.7	624.4	625.5	625.1	624.7	624.3	623.9	623.4	623.1
132.5°	649.8	652.0	654.1	656.3	657.4	657.5	657.6	657.7	657.7	656.9	655.9
135°	695.1	697.4	699.7	701.9	703.2	703.6	704.0	704.5	704.9	704.6	704.5
137.5°	742.4	744.3	746.1	747.9	749.1	749.6	750.2	750.7	751.2	751.1	750.9
140°	771.1	772.9	774.8	776.7	778.1	779.1	780.1	781.2	782.1	782.1	782.1
142.5°	800.6	802.4	804.2	806.0	807.3	808.0	808.7	809.5	810.2	810.3	810.5
145°	842.5	843.9	845.3	846.8	848.1	849.3	850.6	851.8	853.0	853.2	853.4
147.5°	880.5	882.2	883.9	885.7	886.9	887.7	888.6	889.4	890.2	890.7	891.1
150°	905.8	907.0	908.2	909.4	910.5	911.3	912.1	912.9	913.8	914.3	915.0
152.5°	928.6	929.8	931.1	932.2	933.3	934.4	935.3	936.4	937.3	938.1	938.9
155°	962.2	962.8	963.5	964.1	964.6	965.3	965.9	966.5	967.1	968.1	969.2
157.5°	991.3	991.7	992.0	992.5	992.8	993.2	993.6	994.0	994.3	995.8	997.1
160°	1008.9	1009.3	1009.7	1010.2	1010.4	1010.7	1010.9	1011.1	1011.3	1012.5	1013.8
162.5°	1024.8	1024.8	1024.9	1025.1	1025.2	1025.4	1025.6	1025.8	1026.0	1027.4	1028.8
165°	1046.1	1045.8	1045.6	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1046.8	1048.2
167.5°	1063.7	1063.0	1062.5	1061.8	1061.5	1061.4	1061.4	1061.4	1061.4	1062.8	1064.2
170°	1073.2	1072.6	1072.0	1071.4	1071.0	1070.8	1070.6	1070.4	1070.2	1071.6	1073.0
172.5°	1079.9	1079.3	1078.6	1078.0	1077.6	1077.4	1077.2	1077.0	1076.8	1078.2	1079.7
175°	1088.0	1087.3	1086.7	1086.2	1085.6	1085.2	1084.8	1084.4	1083.9	1085.4	1086.9
177.5°	1091.4	1090.9	1090.4	1090.0	1089.5	1089.2	1088.9	1088.5	1088.2	1089.2	1090.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	485.7	487.7	487.7	488.0	490.3	490.0	489.8
5°	516.8	519.9	520.2	523.5	525.6	524.9	522.9
7.5°	546.2	551.9	556.3	558.6	561.5	563.2	562.4
10°	569.6	577.8	582.9	586.3	590.4	593.5	592.4
12.5°	590.7	600.6	607.5	613.4	613.9	617.8	615.1
15°	623.8	634.1	635.3	639.5	643.0	642.6	642.8
17.5°	634.6	637.9	638.7	638.7	638.8	637.5	634.8
20°	630.7	629.5	626.5	624.1	620.0	619.4	615.8
22.5°	612.3	608.3	600.6	595.6	589.1	587.5	586.5
25°	576.1	567.2	555.0	543.3	540.0	533.8	535.5
27.5°	526.2	512.5	499.2	489.8	481.2	471.7	474.4
30°	491.3	475.8	457.1	442.7	433.5	424.5	422.9
32.5°	449.6	426.8	406.0	393.3	379.2	373.5	367.3
35°	377.6	355.4	334.7	316.9	306.7	298.7	291.5
37.5°	312.8	287.3	270.6	256.2	248.7	244.2	245.4
40°	272.7	250.3	238.1	227.1	220.2	217.1	217.8
42.5°	240.1	223.4	213.3	205.8	201.0	199.2	198.8
45°	203.2	193.8	185.5	181.3	178.9	176.9	175.6
47.5°	178.0	170.3	165.6	163.1	161.1	159.1	159.0
50°	162.9	157.8	154.6	151.9	150.3	148.9	150.1
52.5°	151.3	146.7	143.5	141.1	140.5	139.2	139.1
55°	134.3	130.6	128.3	126.1	125.1	124.4	123.4
57.5°	118.7	115.3	113.1	111.8	109.7	109.0	108.7
60°	107.6	104.9	102.7	100.9	100.1	98.6	98.6
62.5°	97.4	94.7	92.7	91.3	89.8	89.3	89.4
65°	82.6	80.4	78.4	77.0	76.7	75.6	76.0
67.5°	69.0	67.6	65.4	64.6	64.0	63.5	63.0
70°	59.9	58.5	57.4	56.3	55.8	55.8	55.8
72.5°	52.3	50.5	49.9	48.6	48.9	48.3	47.7
75°	40.5	39.4	38.9	38.3	37.5	37.5	37.5
77.5°	29.8	29.5	28.8	28.3	28.0	27.9	28.0
80°	23.1	22.8	22.5	22.5	22.1	21.9	21.6
82.5°	17.7	17.3	17.0	16.9	16.8	16.8	16.7
85°	10.1	9.7	9.7	9.9	9.5	9.5	9.7
87.5°	10.1	10.0	9.8	9.9	10.1	10.0	10.0
90°	31.0	30.6	30.5	30.7	30.9	31.1	31.3
92.5°	29.5	29.6	29.6	29.7	29.7	29.8	29.8
95°	58.9	58.9	58.7	58.3	57.9	57.4	57.0
97.5°	99.0	99.0	99.0	98.9	98.9	98.9	98.9
100°	127.0	127.0	126.9	126.7	126.5	126.3	126.0
102.5°	157.6	157.8	157.8	157.6	157.4	157.2	157.0
105°	203.7	204.1	204.3	204.3	204.3	204.3	204.3
107.5°	252.8	252.9	252.5	251.7	250.7	249.8	248.8
110°	286.2	286.2	285.9	285.3	284.6	284.0	283.4



TEST NUMBER: P331277-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	319.3	318.9	318.4	317.9	317.4	317.0	316.6
115°	371.1	370.9	370.5	369.9	369.3	368.7	368.0
117.5°	420.7	420.3	419.7	419.1	418.4	417.8	417.2
120°	454.6	454.6	454.2	453.7	453.0	452.4	451.8
122.5°	488.5	487.9	487.5	487.0	486.6	486.2	485.7
125°	539.2	538.6	538.2	538.0	537.8	537.6	537.4
127.5°	588.5	587.8	587.1	586.5	585.8	585.2	584.5
130°	622.7	622.3	621.6	620.8	620.0	619.2	618.4
132.5°	655.1	654.2	653.4	652.8	652.0	651.4	650.8
135°	704.3	704.0	703.6	703.0	702.4	701.8	701.2
137.5°	750.8	750.6	750.1	749.2	748.5	747.7	746.8
140°	782.1	782.1	781.7	780.9	780.1	779.3	778.5
142.5°	810.6	810.8	810.5	809.6	808.8	808.0	807.2
145°	853.7	853.8	853.5	852.7	851.9	851.0	850.2
147.5°	891.5	892.0	891.8	891.0	890.3	889.5	888.7
150°	915.6	916.2	916.2	915.6	915.0	914.3	913.8
152.5°	939.6	940.4	940.4	939.6	938.9	938.1	937.3
155°	970.2	971.2	971.4	970.8	970.2	969.6	968.9
157.5°	998.5	999.9	1000.1	999.1	998.1	997.2	996.2
160°	1014.9	1016.2	1016.4	1015.6	1014.8	1013.9	1013.1
162.5°	1030.2	1031.6	1031.7	1030.8	1029.8	1028.8	1027.9
165°	1049.6	1051.1	1051.2	1050.3	1049.2	1048.2	1047.2
167.5°	1065.6	1067.1	1067.2	1066.2	1065.1	1064.1	1063.0
170°	1074.4	1075.9	1076.0	1074.8	1073.6	1072.3	1071.1
172.5°	1081.1	1082.5	1082.6	1081.4	1080.1	1079.0	1077.7
175°	1088.3	1089.7	1089.8	1088.6	1087.3	1086.2	1084.9
177.5°	1091.2	1092.1	1092.1	1091.2	1090.2	1089.2	1088.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4

(END OF REPORT)