

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331283-927

Luminaire Tested: **SA2XXDIP-C290D1080U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331283-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4005.5 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331283-927
CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331283-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24				24
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27				20	
2	84	77	71	66	74	68	63	59	53	49	46	38	36	34	25	24	23				17	
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	21	19				14	
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17				12	
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	18	16	14				11	
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13				9	
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	15	13	11				8	
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10				7	
9	46	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9				7	
10	43	32	25	20	38	29	23	18	23	18	15	17	14	12	11	10	8				6	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6042	6042	6042
5°	6065	5977	6015
10°	6030	5917	5946
15°	5954	5840	5835
20°	5849	5727	5720
25°	5744	5585	5585
30°	5610	5455	5407
35°	5483	5298	5219
40°	5324	5143	5044
45°	5167	4987	4864
50°	4999	4828	4657
55°	4822	4642	4467
60°	4624	4414	4253
65°	4413	4195	4000
70°	4145	3923	3734
75°	3768	3612	3525
80°	3347	3245	3078
85°	2723	2594	2334



TEST NUMBER: P331283-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.2	0.9
10°-20°	99.0	2.5
20°-30°	145.6	3.6
30°-40°	169.1	4.2
40°-50°	168.9	4.2
50°-60°	147.3	3.7
60°-70°	108.9	2.7
70°-80°	61.7	1.5
80°-90°	20.9	0.5
90°-100°	69.1	1.7
100°-110°	214.6	5.4
110°-120°	366.8	9.2
120°-130°	482.4	12.0
130°-140°	541.4	13.5
140°-150°	530.9	13.3
150°-160°	445.3	11.1
160°-170°	295.3	7.4
170°-180°	103.2	2.6
0°-30°	279.8	7.0
0°-40°	448.8	11.2
0°-60°	765.0	19.1
0°-90°	956.5	23.9
90°-120°	650.5	16.2
90°-150°	2205.2	55.1
90°-180°	3049.0	76.1
0°-180°	4005.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	374	374	374	374	374	
5°	374	373	369	372	371	35
15°	356	354	349	351	349	100
25°	322	319	314	314	314	148
35°	278	274	269	267	265	174
45°	226	224	218	215	213	175
55°	171	169	165	161	159	153
65°	116	113	110	107	105	114
75°	60	60	58	56	56	65
85°	15	14	14	13	13	17
90°	1	12	32	31	31	3
95°	48	57	59	59	57	55
105°	198	201	202	204	204	209
115°	368	373	372	371	368	364
125°	536	543	541	538	537	478
135°	693	703	705	704	701	535
145°	841	847	853	854	850	525
155°	962	964	967	971	969	442
165°	1046	1045	1045	1051	1047	295
175°	1089	1086	1084	1090	1085	103
180°	1090	1090	1090	1090	1090	



TEST NUMBER: P331283-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
2.5°	376.0	375.7	375.3	375.0	374.7	374.2	373.5	372.8	372.1	371.4	372.0
5°	374.2	373.9	373.6	373.3	373.0	372.4	371.5	370.7	369.7	368.8	369.5
7.5°	371.0	370.4	369.9	369.5	369.0	368.3	367.4	366.5	365.6	364.7	365.4
10°	367.8	367.3	366.7	366.1	365.5	364.8	363.8	362.9	361.9	360.9	361.6
12.5°	363.5	363.0	362.5	361.9	361.5	360.8	359.8	358.9	357.9	357.0	357.4
15°	356.2	355.8	355.3	354.8	354.3	353.6	352.5	351.5	350.5	349.4	349.7
17.5°	347.1	346.6	346.1	345.6	345.2	344.4	343.3	342.2	341.2	340.2	340.5
20°	340.4	339.9	339.5	339.0	338.5	337.7	336.6	335.5	334.4	333.3	333.5
22.5°	333.8	333.1	332.5	331.8	331.1	330.3	329.2	328.1	327.1	326.1	326.1
25°	322.4	321.8	321.2	320.5	319.9	318.9	317.5	316.2	314.8	313.5	313.6
27.5°	309.5	309.0	308.3	307.8	307.2	306.3	305.3	304.2	303.2	302.1	301.8
30°	300.9	300.2	299.6	299.0	298.3	297.4	296.2	295.0	293.7	292.6	292.3
32.5°	291.6	291.1	290.7	290.1	289.6	288.7	287.4	286.2	284.9	283.7	283.2
35°	278.2	277.3	276.6	275.8	275.0	273.9	272.7	271.4	270.1	268.8	268.3
37.5°	263.0	262.3	261.6	260.9	260.2	259.2	257.9	256.7	255.3	254.1	253.5
40°	252.6	252.0	251.4	250.7	250.1	249.1	247.8	246.5	245.3	244.0	243.3
42.5°	242.6	241.9	241.3	240.7	240.0	239.0	237.7	236.5	235.2	233.9	233.1
45°	226.3	225.8	225.2	224.7	224.1	223.2	222.0	220.9	219.7	218.4	217.5
47.5°	210.2	209.7	209.2	208.7	208.1	207.2	206.0	204.8	203.5	202.2	201.3
50°	199.0	198.6	198.2	197.8	197.4	196.6	195.5	194.4	193.3	192.2	191.1
52.5°	188.1	187.5	187.0	186.5	185.9	185.1	184.1	183.1	182.0	180.9	180.0
55°	171.3	170.8	170.3	169.8	169.4	168.7	167.7	166.8	165.8	164.9	163.8
57.5°	154.5	154.1	153.7	153.3	152.9	152.2	151.1	150.1	149.0	148.0	147.0
60°	143.2	142.9	142.6	142.3	142.0	141.2	140.1	139.0	137.8	136.7	135.9
62.5°	132.3	131.7	131.3	130.8	130.2	129.5	128.7	127.9	127.0	126.1	125.2
65°	115.5	115.0	114.5	114.1	113.6	113.0	112.2	111.4	110.6	109.8	109.0
67.5°	98.5	98.1	97.7	97.3	97.0	96.4	95.6	94.9	94.2	93.5	92.9
70°	87.8	87.5	87.1	86.8	86.5	86.0	85.3	84.6	83.8	83.1	82.5
72.5°	76.8	76.5	76.2	75.9	75.6	75.2	74.7	74.3	73.8	73.4	72.8
75°	60.4	60.3	60.1	60.0	59.8	59.6	59.2	58.7	58.3	57.9	57.4
77.5°	45.8	45.5	45.2	45.0	44.7	44.4	44.3	44.1	44.0	43.8	43.6
80°	36.0	35.9	35.8	35.7	35.6	35.6	35.4	35.3	35.1	34.9	34.7
82.5°	26.8	26.8	26.8	26.7	26.7	26.6	26.5	26.5	26.4	26.3	26.0
85°	14.7	14.7	14.6	14.5	14.4	14.3	14.3	14.2	14.1	14.0	13.8
87.5°	5.4	5.7	6.1	6.4	6.8	7.4	8.2	9.0	9.7	10.5	10.2
90°	1.0	3.4	5.9	8.3	10.8	14.2	18.7	23.2	27.7	32.2	31.8
92.5°	16.4	18.1	20.0	21.8	23.6	25.0	26.1	27.2	28.2	29.2	29.3
95°	47.8	49.9	52.0	53.9	56.0	57.3	57.7	58.1	58.5	58.9	58.9
97.5°	87.5	89.2	91.0	92.8	94.6	95.9	96.6	97.4	98.2	99.0	99.0
100°	116.8	118.5	120.2	121.8	123.4	124.5	125.2	125.7	126.4	127.0	127.0
102.5°	147.8	149.1	150.4	151.7	153.0	154.1	154.9	155.6	156.4	157.2	157.3
105°	197.8	198.4	199.1	199.7	200.3	200.8	201.2	201.6	202.0	202.4	202.9
107.5°	248.3	249.1	250.1	251.0	251.8	252.3	252.3	252.3	252.3	252.3	252.5
110°	280.7	281.9	283.1	284.3	285.6	286.2	286.2	286.2	286.2	286.2	286.2



TEST NUMBER: P331283-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	316.0	317.2	318.5	319.6	320.9	321.5	321.2	321.1	320.9	320.8	320.3
115°	368.0	369.3	370.5	371.8	373.0	373.4	373.0	372.6	372.2	371.8	371.5
117.5°	419.9	421.6	423.3	424.8	426.5	426.7	425.6	424.5	423.3	422.2	421.7
120°	454.6	456.2	457.9	459.5	461.1	461.1	459.5	457.9	456.2	454.6	454.6
122.5°	486.2	488.2	490.1	492.1	494.1	494.5	493.4	492.2	491.1	489.9	489.4
125°	535.5	537.4	539.2	541.1	542.9	543.5	542.9	542.3	541.7	541.1	540.4
127.5°	583.6	585.9	588.3	590.6	592.9	593.7	592.9	592.2	591.5	590.7	590.0
130°	613.8	616.4	619.1	621.7	624.4	625.5	625.1	624.7	624.3	623.9	623.4
132.5°	647.6	649.8	652.0	654.1	656.3	657.4	657.5	657.6	657.7	657.7	656.9
135°	692.9	695.1	697.4	699.7	701.9	703.2	703.6	704.0	704.5	704.9	704.6
137.5°	740.5	742.4	744.3	746.1	747.9	749.1	749.6	750.2	750.7	751.2	751.1
140°	769.3	771.1	772.9	774.8	776.7	778.1	779.1	780.1	781.2	782.1	782.1
142.5°	798.8	800.6	802.4	804.2	806.0	807.3	808.0	808.7	809.5	810.2	810.3
145°	841.1	842.5	843.9	845.3	846.8	848.1	849.3	850.6	851.8	853.0	853.2
147.5°	878.8	880.5	882.2	883.9	885.7	886.9	887.7	888.6	889.4	890.2	890.7
150°	904.5	905.8	907.0	908.2	909.4	910.5	911.3	912.1	912.9	913.8	914.3
152.5°	927.3	928.6	929.8	931.1	932.2	933.3	934.4	935.3	936.4	937.3	938.1
155°	961.6	962.2	962.8	963.5	964.1	964.6	965.3	965.9	966.5	967.1	968.1
157.5°	990.9	991.3	991.7	992.0	992.5	992.8	993.2	993.6	994.0	994.3	995.8
160°	1008.5	1008.9	1009.3	1009.7	1010.2	1010.4	1010.7	1010.9	1011.1	1011.3	1012.5
162.5°	1024.7	1024.8	1024.8	1024.9	1025.1	1025.2	1025.4	1025.6	1025.8	1026.0	1027.4
165°	1046.2	1046.1	1045.8	1045.6	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1046.8
167.5°	1064.3	1063.7	1063.0	1062.5	1061.8	1061.5	1061.4	1061.4	1061.4	1061.4	1062.8
170°	1073.9	1073.2	1072.6	1072.0	1071.4	1071.0	1070.8	1070.6	1070.4	1070.2	1071.6
172.5°	1080.5	1079.9	1079.3	1078.6	1078.0	1077.6	1077.4	1077.2	1077.0	1076.8	1078.2
175°	1088.6	1088.0	1087.3	1086.7	1086.2	1085.6	1085.2	1084.8	1084.4	1083.9	1085.4
177.5°	1091.9	1091.4	1090.9	1090.4	1090.0	1089.5	1089.2	1088.9	1088.5	1088.2	1089.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331283-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
2.5°	372.6	373.3	373.9	374.2	374.1	373.9	373.8	373.7
5°	370.2	370.8	371.5	371.7	371.5	371.4	371.2	371.1
7.5°	366.0	366.6	367.3	367.5	367.3	367.1	366.9	366.8
10°	362.3	362.9	363.5	363.7	363.5	363.2	363.0	362.7
12.5°	357.8	358.2	358.7	358.9	358.7	358.5	358.3	358.1
15°	350.1	350.4	350.7	350.7	350.3	349.9	349.5	349.1
17.5°	340.9	341.3	341.6	341.6	341.2	340.9	340.5	340.1
20°	333.7	334.0	334.2	334.1	333.8	333.5	333.2	332.9
22.5°	326.1	326.2	326.2	326.1	326.0	325.7	325.6	325.4
25°	313.8	313.9	314.1	314.1	313.9	313.8	313.6	313.5
27.5°	301.6	301.3	301.1	300.8	300.4	300.0	299.7	299.3
30°	292.1	291.8	291.6	291.4	291.0	290.7	290.4	290.0
32.5°	282.8	282.3	281.9	281.5	281.2	280.9	280.6	280.3
35°	267.8	267.4	266.9	266.5	266.1	265.7	265.3	264.8
37.5°	252.9	252.3	251.7	251.2	250.8	250.4	250.1	249.7
40°	242.6	241.9	241.1	240.6	240.3	240.0	239.6	239.3
42.5°	232.3	231.6	230.8	230.1	229.7	229.3	228.9	228.4
45°	216.7	215.8	214.9	214.3	214.0	213.7	213.3	213.0
47.5°	200.4	199.5	198.5	197.8	197.4	196.9	196.5	196.0
50°	190.0	188.8	187.7	187.0	186.6	186.2	185.8	185.4
52.5°	179.1	178.2	177.2	176.5	175.9	175.5	174.9	174.4
55°	162.9	161.9	161.0	160.3	159.9	159.5	159.1	158.7
57.5°	146.1	145.1	144.2	143.5	143.3	143.0	142.7	142.4
60°	135.0	134.1	133.2	132.7	132.5	132.2	132.0	131.7
62.5°	124.5	123.7	122.9	122.3	122.0	121.7	121.4	121.0
65°	108.3	107.6	106.9	106.3	105.9	105.5	105.1	104.7
67.5°	92.4	91.8	91.3	90.8	90.5	90.2	89.8	89.5
70°	82.0	81.4	80.9	80.5	80.2	79.8	79.5	79.1
72.5°	72.2	71.7	71.1	70.7	70.4	70.2	69.9	69.6
75°	57.0	56.5	56.0	55.8	56.0	56.2	56.3	56.5
77.5°	43.3	43.1	42.9	42.6	42.4	42.2	42.0	41.7
80°	34.5	34.2	34.0	33.7	33.6	33.4	33.3	33.1
82.5°	25.7	25.3	25.0	24.9	24.9	24.8	24.8	24.8
85°	13.5	13.3	13.1	12.9	12.8	12.8	12.7	12.6
87.5°	9.9	9.7	9.3	9.2	9.2	9.2	9.2	9.1
90°	31.4	31.0	30.6	30.5	30.7	30.9	31.1	31.3
92.5°	29.4	29.5	29.6	29.6	29.7	29.7	29.8	29.8
95°	58.9	58.9	58.9	58.7	58.3	57.9	57.4	57.0
97.5°	99.0	99.0	99.0	99.0	98.9	98.9	98.9	98.9
100°	127.0	127.0	127.0	126.9	126.7	126.5	126.3	126.0
102.5°	157.5	157.6	157.8	157.8	157.6	157.4	157.2	157.0
105°	203.3	203.7	204.1	204.3	204.3	204.3	204.3	204.3
107.5°	252.6	252.8	252.9	252.5	251.7	250.7	249.8	248.8
110°	286.2	286.2	286.2	285.9	285.3	284.6	284.0	283.4



TEST NUMBER: P331283-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	319.8	319.3	318.9	318.4	317.9	317.4	317.0	316.6
115°	371.4	371.1	370.9	370.5	369.9	369.3	368.7	368.0
117.5°	421.2	420.7	420.3	419.7	419.1	418.4	417.8	417.2
120°	454.6	454.6	454.6	454.2	453.7	453.0	452.4	451.8
122.5°	488.9	488.5	487.9	487.5	487.0	486.6	486.2	485.7
125°	539.9	539.2	538.6	538.2	538.0	537.8	537.6	537.4
127.5°	589.3	588.5	587.8	587.1	586.5	585.8	585.2	584.5
130°	623.1	622.7	622.3	621.6	620.8	620.0	619.2	618.4
132.5°	655.9	655.1	654.2	653.4	652.8	652.0	651.4	650.8
135°	704.5	704.3	704.0	703.6	703.0	702.4	701.8	701.2
137.5°	750.9	750.8	750.6	750.1	749.2	748.5	747.7	746.8
140°	782.1	782.1	782.1	781.7	780.9	780.1	779.3	778.5
142.5°	810.5	810.6	810.8	810.5	809.6	808.8	808.0	807.2
145°	853.4	853.7	853.8	853.5	852.7	851.9	851.0	850.2
147.5°	891.1	891.5	892.0	891.8	891.0	890.3	889.5	888.7
150°	915.0	915.6	916.2	916.2	915.6	915.0	914.3	913.8
152.5°	938.9	939.6	940.4	940.4	939.6	938.9	938.1	937.3
155°	969.2	970.2	971.2	971.4	970.8	970.2	969.6	968.9
157.5°	997.1	998.5	999.9	1000.1	999.1	998.1	997.2	996.2
160°	1013.8	1014.9	1016.2	1016.4	1015.6	1014.8	1013.9	1013.1
162.5°	1028.8	1030.2	1031.6	1031.7	1030.8	1029.8	1028.8	1027.9
165°	1048.2	1049.6	1051.1	1051.2	1050.3	1049.2	1048.2	1047.2
167.5°	1064.2	1065.6	1067.1	1067.2	1066.2	1065.1	1064.1	1063.0
170°	1073.0	1074.4	1075.9	1076.0	1074.8	1073.6	1072.3	1071.1
172.5°	1079.7	1081.1	1082.5	1082.6	1081.4	1080.1	1079.0	1077.7
175°	1086.9	1088.3	1089.7	1089.8	1088.6	1087.3	1086.2	1084.9
177.5°	1090.2	1091.2	1092.1	1092.1	1091.2	1090.2	1089.2	1088.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4

(END OF REPORT)