

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331249-927

Luminaire Tested: **SA2XXDIP-C290D530U927-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331249-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D530U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2708.8 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331249-927
CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	35	33	28
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24
4	73	63	55	50	66	57	51	46	47	43	39	38	35	32	29	27	25	21
5	67	56	48	43	61	51	45	40	42	37	34	34	31	28	26	24	22	19
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	22	20	17
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14	12
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7561	7561	7561	7561
5°	8475	7609	6744	7609
10°	9712	7547	5835	7547
15°	10745	7408	5157	7408
20°	10581	7261	4699	7261
25°	9540	7062	4411	7062
30°	7884	6747	4200	6747
35°	5746	6416	4050	6416
40°	4591	6028	3967	6028
45°	4010	5576	3854	5576
50°	3770	5139	3778	5139
55°	3474	4695	3676	4695
60°	3184	4224	3523	4224
65°	2904	3801	3370	3801
70°	2634	3389	3144	3389
75°	2339	2932	2782	2932
80°	2008	2427	2241	2427
85°	1797	1797	1334	1797



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.6	1.6
10°-20°	129.6	4.8
20°-30°	188.1	6.9
30°-40°	198.5	7.3
40°-50°	175.8	6.5
50°-60°	140.3	5.2
60°-70°	95.4	3.5
70°-80°	48.9	1.8
80°-90°	13.2	0.5
90°-100°	19.1	0.7
100°-110°	69.9	2.6
110°-120°	186.8	6.9
120°-130°	308.4	11.4
130°-140°	328.0	12.1
140°-150°	304.8	11.3
150°-160°	245.1	9.0
160°-170°	157.9	5.8
170°-180°	54.4	2.0
0°-30°	362.4	13.4
0°-40°	560.9	20.7
0°-60°	877.0	32.4
0°-90°	1034.4	38.2
90°-120°	275.8	10.2
90°-150°	1217.0	44.9
90°-180°	1674.0	61.8
0°-180°	2708.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	468	468	468	468	468	
5°	523	470	416	470	523	52
15°	643	443	308	443	643	177
25°	536	396	248	396	536	242
35°	292	326	206	326	292	190
45°	176	244	169	244	176	138
55°	123	167	131	167	123	111
65°	76	100	88	100	76	76
75°	38	47	45	47	38	40
85°	10	10	7	10	10	11
90°	11	0	11	0	11	5
95°	18	27	18	27	18	17
105°	31	126	31	126	31	33
115°	34	238	34	238	34	85
125°	354	336	354	336	354	306
135°	430	416	430	416	430	331
145°	490	482	490	482	490	306
155°	532	531	532	531	532	245
165°	558	560	558	560	558	158
175°	569	573	569	573	569	54
180°	571	571	571	571	571	



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	489.8	490.0	490.3	488.0	487.7	487.7	485.7	483.9	481.9	479.2	479.5
5°	522.9	524.9	525.6	523.5	520.2	519.9	516.8	511.8	507.1	503.4	500.7
7.5°	562.4	563.2	561.5	558.6	556.3	551.9	546.2	540.7	532.8	525.7	520.4
10°	592.4	593.5	590.4	586.3	582.9	577.8	569.6	561.1	550.9	541.0	533.1
12.5°	615.1	617.8	613.9	613.4	607.5	600.6	590.7	586.5	572.0	558.3	549.7
15°	642.8	642.6	643.0	639.5	635.3	634.1	623.8	612.4	592.1	583.9	569.9
17.5°	634.8	637.5	638.8	638.7	638.7	637.9	634.6	627.5	617.3	604.1	588.0
20°	615.8	619.4	620.0	624.1	626.5	629.5	630.7	628.8	622.5	611.5	597.5
22.5°	586.5	587.5	589.1	595.6	600.6	608.3	612.3	619.0	616.6	611.2	599.4
25°	535.5	533.8	540.0	543.3	555.0	567.2	576.1	585.7	594.4	599.6	596.2
27.5°	474.4	471.7	481.2	489.8	499.2	512.5	526.2	542.5	556.0	572.9	578.7
30°	422.9	424.5	433.5	442.7	457.1	475.8	491.3	509.1	528.4	547.2	560.4
32.5°	367.3	373.5	379.2	393.3	406.0	426.8	449.6	471.8	495.8	517.3	537.7
35°	291.5	298.7	306.7	316.9	334.7	355.4	377.6	407.6	440.4	469.7	493.8
37.5°	245.4	244.2	248.7	256.2	270.6	287.3	312.8	342.5	381.0	415.5	449.6
40°	217.8	217.1	220.2	227.1	238.1	250.3	272.7	298.7	334.5	376.7	417.2
42.5°	198.8	199.2	201.0	205.8	213.3	223.4	240.1	262.3	295.1	334.8	378.3
45°	175.6	176.9	178.9	181.3	185.5	193.8	203.2	219.0	244.9	278.1	320.8
47.5°	159.0	159.1	161.1	163.1	165.6	170.3	178.0	187.9	206.2	233.1	270.0
50°	150.1	148.9	150.3	151.9	154.6	157.8	162.9	172.2	184.4	206.2	237.0
52.5°	139.1	139.2	140.5	141.1	143.5	146.7	151.3	157.8	168.9	185.9	211.2
55°	123.4	124.4	125.1	126.1	128.3	130.6	134.3	138.6	147.2	159.9	178.7
57.5°	108.7	109.0	109.7	111.8	113.1	115.3	118.7	122.6	128.3	137.7	151.8
60°	98.6	98.6	100.1	100.9	102.7	104.9	107.6	111.4	116.5	124.1	135.5
62.5°	89.4	89.3	89.8	91.3	92.7	94.7	97.4	100.6	105.4	112.3	121.5
65°	76.0	75.6	76.7	77.0	78.4	80.4	82.6	86.0	89.8	94.8	103.1
67.5°	63.0	63.5	64.0	64.6	65.4	67.6	69.0	71.4	74.6	78.8	84.4
70°	55.8	55.8	55.8	56.3	57.4	58.5	59.9	61.9	65.0	68.5	73.6
72.5°	47.7	48.3	48.9	48.6	49.9	50.5	52.3	53.4	56.3	58.6	63.1
75°	37.5	37.5	37.5	38.3	38.9	39.4	40.5	41.6	43.0	45.9	48.2
77.5°	28.0	27.9	28.0	28.3	28.8	29.5	29.8	30.7	32.1	33.4	35.4
80°	21.6	21.9	22.1	22.5	22.5	22.8	23.1	24.3	25.2	26.1	27.3
82.5°	16.7	16.8	16.8	16.9	17.0	17.3	17.7	18.1	18.5	19.2	20.1
85°	9.7	9.5	9.5	9.9	9.7	9.7	10.1	10.5	10.5	10.6	11.2
87.5°	5.9	5.9	6.0	5.9	5.9	5.9	5.8	5.5	5.6	5.7	5.7
90°	11.2	11.0	10.8	10.6	10.5	10.1	9.7	9.2	8.7	8.2	7.5
92.5°	11.2	11.1	10.9	10.9	10.7	10.5	10.3	10.1	9.8	9.6	9.2
95°	17.7	17.9	18.0	18.1	18.1	18.0	17.5	17.0	16.6	16.2	15.4
97.5°	23.8	23.6	23.5	23.4	23.3	23.1	22.7	22.3	21.9	21.5	20.1
100°	27.7	27.5	27.3	27.2	26.9	26.5	25.7	25.0	24.3	23.5	22.0
102.5°	29.7	29.4	29.2	28.9	28.7	28.0	27.1	26.1	25.2	24.2	37.3
105°	31.4	31.1	30.7	30.3	29.9	29.2	28.3	27.3	26.2	25.2	50.3
107.5°	32.3	31.9	31.6	31.2	30.9	31.2	32.2	33.3	34.3	35.3	65.4
110°	32.6	32.3	31.9	31.5	31.2	35.6	44.8	53.9	63.1	72.3	98.9



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	33.0	32.7	32.4	32.1	31.8	48.4	81.9	115.4	148.9	182.5	189.0
115°	33.9	40.5	47.1	53.7	60.4	84.9	127.5	170.0	212.5	255.1	252.8
117.5°	138.4	160.2	181.9	203.6	225.4	241.4	251.7	262.0	272.3	282.5	281.0
120°	252.2	264.6	277.0	289.4	301.8	307.4	306.3	305.2	304.1	303.0	301.3
122.5°	314.7	317.1	319.5	321.9	324.3	325.2	324.6	323.8	323.2	322.6	320.8
125°	353.5	353.2	352.9	352.7	352.4	351.9	351.3	350.6	350.0	349.4	347.6
127.5°	378.0	377.9	377.9	377.8	377.7	377.2	376.3	375.3	374.4	373.5	372.2
130°	393.2	393.2	393.3	393.4	393.6	393.1	392.1	391.0	390.1	389.0	388.0
132.5°	408.1	408.1	408.2	408.3	408.4	408.1	407.2	406.3	405.4	404.6	403.5
135°	429.5	429.8	429.9	430.1	430.3	429.9	429.0	428.1	427.1	426.2	425.4
137.5°	449.2	449.5	449.7	450.0	450.4	450.1	449.2	448.3	447.4	446.5	445.5
140°	461.4	461.8	462.3	462.7	463.2	463.0	462.2	461.4	460.6	459.7	458.7
142.5°	473.2	473.7	474.2	474.7	475.2	475.0	474.2	473.5	472.7	472.0	470.8
145°	489.9	490.4	490.8	491.3	491.7	491.6	491.0	490.4	489.7	489.1	487.5
147.5°	504.5	504.9	505.3	505.7	506.0	506.0	505.6	505.1	504.6	504.1	502.6
150°	513.5	513.9	514.4	514.8	515.3	515.2	514.7	514.1	513.6	513.0	511.6
152.5°	521.1	521.7	522.3	522.9	523.5	523.6	523.0	522.4	521.9	521.3	519.9
155°	531.6	532.4	533.1	533.9	534.6	534.7	534.2	533.6	533.1	532.5	531.4
157.5°	541.3	542.0	542.7	543.4	544.2	544.2	543.6	543.0	542.3	541.8	541.0
160°	546.9	547.6	548.3	548.9	549.5	549.5	549.0	548.4	548.0	547.4	546.8
162.5°	551.6	552.4	553.2	554.0	554.8	554.8	554.2	553.6	552.9	552.3	551.8
165°	558.5	559.2	559.8	560.5	561.1	561.1	560.5	559.8	559.2	558.5	558.3
167.5°	562.9	563.7	564.6	565.4	566.3	566.3	565.7	565.0	564.4	563.7	563.5
170°	565.5	566.4	567.2	568.0	568.9	568.9	568.3	567.7	567.0	566.4	566.2
172.5°	567.5	568.4	569.2	570.1	570.8	570.9	570.3	569.7	569.0	568.4	568.2
175°	569.3	570.2	571.1	572.0	573.0	573.1	572.4	571.8	571.2	570.5	570.3
177.5°	570.4	571.0	571.6	572.4	573.0	573.1	572.6	572.0	571.6	571.0	570.9
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	480.5	479.3	478.6	476.0	473.7	471.4	470.7	471.0	467.8	464.8	463.5
5°	499.2	495.6	492.2	487.4	481.6	475.2	472.1	469.5	463.2	456.4	452.4
7.5°	515.9	510.8	504.2	495.1	486.7	476.8	470.5	464.9	455.7	446.1	440.1
10°	526.2	519.2	510.7	499.6	489.3	477.2	468.8	460.3	449.6	438.0	430.8
12.5°	535.0	525.5	517.2	502.9	490.8	475.6	465.6	453.7	442.4	428.6	421.6
15°	555.9	538.4	522.6	506.4	491.5	470.4	459.2	443.2	428.3	411.4	403.3
17.5°	572.0	552.4	527.5	506.9	489.5	466.1	449.8	430.6	413.0	393.6	382.6
20°	581.2	558.7	532.0	507.5	486.6	459.9	442.1	422.6	401.9	380.1	368.2
22.5°	586.7	563.1	536.5	505.3	480.9	455.0	432.5	411.0	390.1	366.5	354.1
25°	588.4	566.9	538.8	503.5	473.6	444.3	417.3	396.4	371.1	349.1	331.0
27.5°	579.9	564.4	537.4	500.1	465.3	431.0	400.9	377.3	350.5	326.7	308.4
30°	569.3	560.4	534.1	496.7	458.7	421.8	388.7	361.9	335.3	311.2	292.4
32.5°	553.1	551.2	528.1	491.8	451.6	410.2	375.9	348.8	319.2	295.6	277.7
35°	521.2	529.8	515.2	480.9	438.4	393.6	356.5	325.5	294.9	272.3	255.6
37.5°	478.3	499.8	496.0	464.9	420.4	375.5	334.5	302.2	273.1	250.2	233.8
40°	448.8	476.2	480.1	452.6	407.8	361.6	318.1	286.0	257.5	236.6	220.1
42.5°	417.2	449.1	459.9	437.9	394.0	346.8	303.5	270.1	241.9	221.7	207.0
45°	364.1	406.3	426.0	413.4	370.9	322.7	278.1	244.2	218.6	199.6	188.2
47.5°	314.4	360.6	387.0	382.5	345.2	297.5	253.3	220.9	196.0	180.8	170.6
50°	279.3	326.8	358.6	360.1	326.8	279.5	235.2	204.6	181.7	167.5	159.2
52.5°	248.7	294.1	328.8	336.5	306.2	260.8	219.0	188.5	168.3	155.3	147.9
55°	208.9	247.2	285.7	299.8	275.5	232.3	193.6	166.8	147.9	138.9	132.5
57.5°	173.7	205.7	241.2	256.7	241.8	204.8	168.5	145.2	129.9	122.0	117.0
60°	155.1	180.3	212.0	230.5	217.5	184.7	153.0	130.8	118.2	111.2	106.5
62.5°	137.8	160.2	187.0	203.9	196.9	165.8	137.4	117.9	107.0	100.4	97.0
65°	113.8	131.3	152.1	167.7	163.0	139.5	116.2	99.5	90.9	85.6	82.9
67.5°	93.6	106.4	120.7	134.4	130.7	114.0	95.4	82.3	75.9	71.4	69.7
70°	81.0	90.7	103.5	114.5	111.4	97.8	82.9	71.8	66.2	62.4	60.8
72.5°	68.9	76.8	86.7	95.6	93.6	82.1	69.9	61.5	57.1	53.6	52.4
75°	52.0	58.1	64.1	70.0	69.5	60.7	53.5	47.0	43.6	40.9	40.3
77.5°	38.4	41.8	45.9	49.4	48.4	43.3	37.7	34.0	31.5	29.7	29.4
80°	29.3	31.3	34.2	36.7	35.5	33.3	28.8	26.1	24.3	22.5	21.8
82.5°	21.3	23.2	25.0	26.4	25.3	23.4	20.6	18.8	17.7	16.5	16.2
85°	11.2	12.2	13.0	13.3	13.0	11.7	10.5	9.7	8.8	8.2	8.1
87.5°	5.7	5.5	5.4	5.5	4.8	4.7	3.9	3.2	3.3	3.3	3.2
90°	6.8	6.1	5.3	4.4	3.4	2.5	1.4	0.4	1.4	2.5	3.4
92.5°	8.9	8.5	8.2	8.0	8.1	8.2	8.2	8.3	8.2	8.2	8.1
95°	14.8	14.2	13.5	14.7	17.7	20.8	23.8	26.9	23.8	20.8	17.7
97.5°	18.6	17.1	15.6	19.2	27.7	36.3	44.8	53.3	44.8	36.3	27.7
100°	20.4	18.9	17.3	22.8	35.4	48.0	60.6	73.2	60.6	48.0	35.4
102.5°	50.4	63.5	76.4	84.4	87.0	89.7	92.4	95.0	92.4	89.7	87.0
105°	75.4	100.4	125.6	136.7	134.0	131.2	128.4	125.6	128.4	131.2	134.0
107.5°	95.5	125.6	155.6	169.5	167.3	165.1	162.9	160.7	162.9	165.1	167.3
110°	125.5	152.0	178.6	190.8	188.9	187.0	185.1	183.2	185.1	187.0	188.9



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	195.6	202.2	208.7	211.1	209.5	207.7	206.0	204.3	206.0	207.7	209.5
115°	250.5	248.2	245.9	244.0	242.4	240.8	239.2	237.7	239.2	240.8	242.4
117.5°	279.4	277.8	276.2	274.6	272.8	271.1	269.3	267.6	269.3	271.1	272.8
120°	299.8	298.1	296.4	294.9	293.5	292.2	290.7	289.4	290.7	292.2	293.5
122.5°	318.9	317.1	315.4	313.7	312.3	310.9	309.3	307.9	309.3	310.9	312.3
125°	345.9	344.1	342.4	340.9	339.7	338.5	337.3	336.1	337.3	338.5	339.7
127.5°	370.9	369.6	368.3	366.9	365.6	364.3	363.0	361.6	363.0	364.3	365.6
130°	387.0	386.0	385.0	383.7	382.3	380.8	379.3	377.9	379.3	380.8	382.3
132.5°	402.6	401.6	400.5	399.4	398.2	396.9	395.6	394.4	395.6	396.9	398.2
135°	424.6	423.7	422.9	421.8	420.3	418.8	417.4	415.9	417.4	418.8	420.3
137.5°	444.7	443.7	442.8	441.7	440.7	439.7	438.6	437.7	438.6	439.7	440.7
140°	457.7	456.7	455.7	454.8	454.1	453.4	452.6	451.9	452.6	453.4	454.1
142.5°	469.6	468.5	467.3	466.4	465.7	465.1	464.5	463.7	464.5	465.1	465.7
145°	485.9	484.4	482.8	482.1	482.2	482.3	482.4	482.4	482.4	482.3	482.2
147.5°	501.1	499.5	498.0	497.3	497.7	498.0	498.4	498.8	498.4	498.0	497.7
150°	510.1	508.7	507.2	506.8	507.4	508.0	508.7	509.3	508.7	508.0	507.4
152.5°	518.6	517.1	515.7	515.4	516.1	516.8	517.5	518.2	517.5	516.8	516.1
155°	530.3	529.2	528.1	527.9	528.8	529.6	530.4	531.2	530.4	529.6	528.8
157.5°	540.2	539.4	538.7	538.6	539.3	540.0	540.7	541.4	540.7	540.0	539.3
160°	546.3	545.7	545.2	545.2	545.7	546.3	546.8	547.4	546.8	546.3	545.7
162.5°	551.4	550.9	550.4	550.5	551.0	551.5	552.1	552.6	552.1	551.5	551.0
165°	557.9	557.7	557.5	557.5	558.1	558.6	559.2	559.8	559.2	558.6	558.1
167.5°	563.2	562.9	562.7	562.8	563.4	564.0	564.5	565.1	564.5	564.0	563.4
170°	566.0	565.9	565.6	565.9	566.4	567.0	567.5	568.0	567.5	567.0	566.4
172.5°	568.0	567.8	567.6	567.8	568.4	568.9	569.5	570.1	569.5	568.9	568.4
175°	570.1	570.0	569.8	570.0	570.7	571.3	572.0	572.6	572.0	571.3	570.7
177.5°	570.8	570.8	570.7	570.9	571.5	572.0	572.5	573.0	572.5	572.0	571.5
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	462.1	461.2	458.2	456.6	454.0	451.5	450.0	450.7	451.2	451.0	450.5
5°	448.8	445.4	440.1	435.7	432.5	426.5	424.0	422.7	421.6	420.4	419.1
7.5°	433.0	427.6	420.2	413.8	407.7	400.3	396.1	393.6	391.0	388.2	385.6
10°	421.8	414.2	406.3	397.4	390.1	383.5	377.6	373.6	369.9	366.5	364.1
12.5°	410.0	401.3	391.5	379.2	371.3	361.7	360.8	353.9	348.2	346.1	343.2
15°	391.3	379.0	366.5	352.0	345.7	337.1	331.7	326.2	321.4	318.0	317.1
17.5°	369.9	354.0	341.7	331.2	320.9	312.0	307.0	302.8	298.7	294.2	293.6
20°	353.6	339.9	326.5	317.3	306.7	297.6	291.5	287.2	283.8	281.1	278.8
22.5°	338.2	323.2	310.9	300.9	290.4	283.1	278.3	274.1	271.2	268.3	266.1
25°	313.5	301.8	288.3	276.9	268.3	263.6	259.7	256.1	254.3	252.3	249.8
27.5°	291.8	278.8	266.3	257.5	249.9	245.7	242.9	240.4	238.8	237.6	236.1
30°	276.6	263.5	253.6	244.9	238.6	234.5	232.7	231.2	229.3	228.5	227.8
32.5°	261.9	250.1	241.6	234.1	228.1	225.4	223.8	222.4	220.9	220.2	218.7
35°	241.1	231.2	223.0	218.8	214.0	211.6	210.4	208.6	207.2	206.4	206.2
37.5°	221.6	213.0	207.6	202.2	200.2	198.8	197.0	195.8	195.4	195.3	195.0
40°	208.9	201.9	197.0	192.7	191.9	189.6	188.2	187.2	187.2	187.4	187.2
42.5°	197.4	191.1	186.8	183.1	182.0	180.8	179.3	179.3	179.5	180.1	179.5
45°	180.0	175.5	172.4	170.6	168.7	167.4	167.2	167.7	167.9	168.1	168.7
47.5°	163.9	160.9	158.1	156.1	155.3	155.1	154.9	155.8	156.7	157.0	157.8
50°	154.4	151.0	148.6	147.3	146.6	146.3	146.6	147.7	148.5	149.3	149.9
52.5°	143.8	141.3	139.7	138.7	138.5	138.7	138.7	140.0	141.1	141.5	141.7
55°	129.0	127.2	126.9	125.2	126.0	125.8	126.7	127.4	128.5	129.6	129.8
57.5°	114.3	112.9	111.9	112.1	112.3	113.1	113.8	115.1	116.2	117.4	117.5
60°	104.6	103.9	103.3	103.3	103.6	104.7	105.6	106.9	107.6	108.4	108.8
62.5°	95.6	94.9	94.3	94.7	95.6	96.3	97.3	98.0	98.7	99.4	99.7
65°	81.5	81.2	81.7	82.1	82.2	83.1	84.4	84.9	85.6	86.0	87.3
67.5°	68.5	68.6	68.5	69.0	70.1	70.3	71.5	72.7	72.9	73.6	74.4
70°	59.7	60.1	60.4	60.8	61.7	62.1	63.0	63.5	64.2	64.8	65.4
72.5°	51.7	51.7	52.1	52.0	52.8	53.6	54.3	54.9	55.6	56.3	56.8
75°	39.8	39.8	40.2	40.3	41.2	42.1	41.9	42.3	43.0	43.7	44.1
77.5°	29.1	28.7	29.1	29.2	29.5	30.3	30.4	30.9	31.8	31.5	31.9
80°	22.1	21.6	22.1	22.3	22.3	23.2	23.2	23.6	24.1	23.6	24.1
82.5°	15.8	15.5	15.9	16.0	16.2	16.3	16.6	16.6	17.2	17.0	17.2
85°	7.9	7.8	7.9	7.8	7.9	8.1	8.1	7.9	7.9	8.2	7.8
87.5°	3.3	3.4	3.4	3.5	3.5	3.5	3.5	3.6	3.6	3.5	3.5
90°	4.4	5.3	6.1	6.8	7.5	8.2	8.7	9.2	9.7	10.1	10.5
92.5°	8.0	8.2	8.5	8.9	9.2	9.6	9.8	10.1	10.3	10.5	10.7
95°	14.7	13.5	14.2	14.8	15.4	16.2	16.6	17.0	17.5	18.0	18.1
97.5°	19.2	15.6	17.1	18.6	20.1	21.5	21.9	22.3	22.7	23.1	23.3
100°	22.8	17.3	18.9	20.4	22.0	23.5	24.3	25.0	25.7	26.5	26.9
102.5°	84.4	76.4	63.5	50.4	37.3	24.2	25.2	26.1	27.1	28.0	28.7
105°	136.7	125.6	100.4	75.4	50.3	25.2	26.2	27.3	28.3	29.2	29.9
107.5°	169.5	155.6	125.6	95.5	65.4	35.3	34.3	33.3	32.2	31.2	30.9
110°	190.8	178.6	152.0	125.5	98.9	72.3	63.1	53.9	44.8	35.6	31.2



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	211.1	208.7	202.2	195.6	189.0	182.5	148.9	115.4	81.9	48.4	31.8
115°	244.0	245.9	248.2	250.5	252.8	255.1	212.5	170.0	127.5	84.9	60.4
117.5°	274.6	276.2	277.8	279.4	281.0	282.5	272.3	262.0	251.7	241.4	225.4
120°	294.9	296.4	298.1	299.8	301.3	303.0	304.1	305.2	306.3	307.4	301.8
122.5°	313.7	315.4	317.1	318.9	320.8	322.6	323.2	323.8	324.6	325.2	324.3
125°	340.9	342.4	344.1	345.9	347.6	349.4	350.0	350.6	351.3	351.9	352.4
127.5°	366.9	368.3	369.6	370.9	372.2	373.5	374.4	375.3	376.3	377.2	377.7
130°	383.7	385.0	386.0	387.0	388.0	389.0	390.1	391.0	392.1	393.1	393.6
132.5°	399.4	400.5	401.6	402.6	403.5	404.6	405.4	406.3	407.2	408.1	408.4
135°	421.8	422.9	423.7	424.6	425.4	426.2	427.1	428.1	429.0	429.9	430.3
137.5°	441.7	442.8	443.7	444.7	445.5	446.5	447.4	448.3	449.2	450.1	450.4
140°	454.8	455.7	456.7	457.7	458.7	459.7	460.6	461.4	462.2	463.0	463.2
142.5°	466.4	467.3	468.5	469.6	470.8	472.0	472.7	473.5	474.2	475.0	475.2
145°	482.1	482.8	484.4	485.9	487.5	489.1	489.7	490.4	491.0	491.6	491.7
147.5°	497.3	498.0	499.5	501.1	502.6	504.1	504.6	505.1	505.6	506.0	506.0
150°	506.8	507.2	508.7	510.1	511.6	513.0	513.6	514.1	514.7	515.2	515.3
152.5°	515.4	515.7	517.1	518.6	519.9	521.3	521.9	522.4	523.0	523.6	523.5
155°	527.9	528.1	529.2	530.3	531.4	532.5	533.1	533.6	534.2	534.7	534.6
157.5°	538.6	538.7	539.4	540.2	541.0	541.8	542.3	543.0	543.6	544.2	544.2
160°	545.2	545.2	545.7	546.3	546.8	547.4	548.0	548.4	549.0	549.5	549.5
162.5°	550.5	550.4	550.9	551.4	551.8	552.3	552.9	553.6	554.2	554.8	554.8
165°	557.5	557.5	557.7	557.9	558.3	558.5	559.2	559.8	560.5	561.1	561.1
167.5°	562.8	562.7	562.9	563.2	563.5	563.7	564.4	565.0	565.7	566.3	566.3
170°	565.9	565.6	565.9	566.0	566.2	566.4	567.0	567.7	568.3	568.9	568.9
172.5°	567.8	567.6	567.8	568.0	568.2	568.4	569.0	569.7	570.3	570.9	570.8
175°	570.0	569.8	570.0	570.1	570.3	570.5	571.2	571.8	572.4	573.1	573.0
177.5°	570.9	570.7	570.8	570.8	570.9	571.0	571.6	572.0	572.6	573.1	573.0
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	449.1	448.8	448.8	447.5	448.8	448.8	449.1	450.5	451.0	451.2	450.7
5°	416.6	416.1	415.2	416.1	415.2	416.1	416.6	419.1	420.4	421.6	422.7
7.5°	384.4	382.3	382.0	379.9	382.0	382.3	384.4	385.6	388.2	391.0	393.6
10°	361.0	359.6	359.3	355.9	359.3	359.6	361.0	364.1	366.5	369.9	373.6
12.5°	343.2	339.7	340.4	338.4	340.4	339.7	343.2	343.2	346.1	348.2	353.9
15°	312.2	312.2	311.5	308.5	311.5	312.2	312.2	317.1	318.0	321.4	326.2
17.5°	290.0	289.6	288.0	288.8	288.0	289.6	290.0	293.6	294.2	298.7	302.8
20°	276.8	275.7	273.5	273.5	273.5	275.7	276.8	278.8	281.1	283.8	287.2
22.5°	264.3	264.2	261.9	262.6	261.9	264.2	264.3	266.1	268.3	271.2	274.1
25°	249.6	248.2	247.1	247.6	247.1	248.2	249.6	249.8	252.3	254.3	256.1
27.5°	235.7	234.9	234.8	233.4	234.8	234.9	235.7	236.1	237.6	238.8	240.4
30°	227.7	225.9	226.2	225.3	226.2	225.9	227.7	227.8	228.5	229.3	231.2
32.5°	218.4	217.8	217.5	216.7	217.5	217.8	218.4	218.7	220.2	220.9	222.4
35°	205.9	206.0	205.2	205.5	205.2	206.0	205.9	206.2	206.4	207.2	208.6
37.5°	194.9	195.4	195.0	195.1	195.0	195.4	194.9	195.0	195.3	195.4	195.8
40°	187.7	187.7	187.7	188.2	187.7	187.7	187.7	187.2	187.4	187.2	187.2
42.5°	180.8	180.5	180.2	180.1	180.2	180.5	180.8	179.5	180.1	179.5	179.3
45°	169.0	169.5	169.7	168.8	169.7	169.5	169.0	168.7	168.1	167.9	167.7
47.5°	158.3	158.4	158.3	159.1	158.3	158.4	158.3	157.8	157.0	156.7	155.8
50°	150.8	150.4	150.8	150.4	150.8	150.4	150.8	149.9	149.3	148.5	147.7
52.5°	142.9	143.0	142.8	142.7	142.8	143.0	142.9	141.7	141.5	141.1	140.0
55°	130.5	130.8	130.6	130.6	130.6	130.8	130.5	129.8	129.6	128.5	127.4
57.5°	117.6	118.0	118.2	117.4	118.2	118.0	117.6	117.5	117.4	116.2	115.1
60°	108.7	109.6	109.4	109.1	109.4	109.6	108.7	108.8	108.4	107.6	106.9
62.5°	100.4	100.8	100.8	100.7	100.8	100.8	100.4	99.7	99.4	98.7	98.0
65°	87.9	88.2	87.6	88.2	87.6	88.2	87.9	87.3	86.0	85.6	84.9
67.5°	74.1	74.3	74.7	74.9	74.7	74.3	74.1	74.4	73.6	72.9	72.7
70°	65.7	65.5	66.1	66.6	66.1	65.5	65.7	65.4	64.8	64.2	63.5
72.5°	56.7	57.1	57.0	57.4	57.0	57.1	56.7	56.8	56.3	55.6	54.9
75°	43.7	44.3	44.1	44.6	44.1	44.3	43.7	44.1	43.7	43.0	42.3
77.5°	31.6	31.7	31.6	31.9	31.6	31.7	31.6	31.9	31.5	31.8	30.9
80°	24.1	23.8	23.4	24.1	23.4	23.8	24.1	24.1	23.6	24.1	23.6
82.5°	16.8	17.0	16.6	16.6	16.6	17.0	16.8	17.2	17.0	17.2	16.6
85°	7.8	7.5	7.2	7.2	7.2	7.5	7.8	7.8	8.2	7.9	7.9
87.5°	3.6	3.5	3.5	3.4	3.5	3.5	3.6	3.5	3.5	3.6	3.6
90°	10.6	10.8	11.0	11.2	11.0	10.8	10.6	10.5	10.1	9.7	9.2
92.5°	10.9	10.9	11.1	11.2	11.1	10.9	10.9	10.7	10.5	10.3	10.1
95°	18.1	18.0	17.9	17.7	17.9	18.0	18.1	18.1	18.0	17.5	17.0
97.5°	23.4	23.5	23.6	23.8	23.6	23.5	23.4	23.3	23.1	22.7	22.3
100°	27.2	27.3	27.5	27.7	27.5	27.3	27.2	26.9	26.5	25.7	25.0
102.5°	28.9	29.2	29.4	29.7	29.4	29.2	28.9	28.7	28.0	27.1	26.1
105°	30.3	30.7	31.1	31.4	31.1	30.7	30.3	29.9	29.2	28.3	27.3
107.5°	31.2	31.6	31.9	32.3	31.9	31.6	31.2	30.9	31.2	32.2	33.3
110°	31.5	31.9	32.3	32.6	32.3	31.9	31.5	31.2	35.6	44.8	53.9



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	32.1	32.4	32.7	33.0	32.7	32.4	32.1	31.8	48.4	81.9	115.4
115°	53.7	47.1	40.5	33.9	40.5	47.1	53.7	60.4	84.9	127.5	170.0
117.5°	203.6	181.9	160.2	138.4	160.2	181.9	203.6	225.4	241.4	251.7	262.0
120°	289.4	277.0	264.6	252.2	264.6	277.0	289.4	301.8	307.4	306.3	305.2
122.5°	321.9	319.5	317.1	314.7	317.1	319.5	321.9	324.3	325.2	324.6	323.8
125°	352.7	352.9	353.2	353.5	353.2	352.9	352.7	352.4	351.9	351.3	350.6
127.5°	377.8	377.9	377.9	378.0	377.9	377.9	377.8	377.7	377.2	376.3	375.3
130°	393.4	393.3	393.2	393.2	393.2	393.3	393.4	393.6	393.1	392.1	391.0
132.5°	408.3	408.2	408.1	408.1	408.1	408.2	408.3	408.4	408.1	407.2	406.3
135°	430.1	429.9	429.8	429.5	429.8	429.9	430.1	430.3	429.9	429.0	428.1
137.5°	450.0	449.7	449.5	449.2	449.5	449.7	450.0	450.4	450.1	449.2	448.3
140°	462.7	462.3	461.8	461.4	461.8	462.3	462.7	463.2	463.0	462.2	461.4
142.5°	474.7	474.2	473.7	473.2	473.7	474.2	474.7	475.2	475.0	474.2	473.5
145°	491.3	490.8	490.4	489.9	490.4	490.8	491.3	491.7	491.6	491.0	490.4
147.5°	505.7	505.3	504.9	504.5	504.9	505.3	505.7	506.0	506.0	505.6	505.1
150°	514.8	514.4	513.9	513.5	513.9	514.4	514.8	515.3	515.2	514.7	514.1
152.5°	522.9	522.3	521.7	521.1	521.7	522.3	522.9	523.5	523.6	523.0	522.4
155°	533.9	533.1	532.4	531.6	532.4	533.1	533.9	534.6	534.7	534.2	533.6
157.5°	543.4	542.7	542.0	541.3	542.0	542.7	543.4	544.2	544.2	543.6	543.0
160°	548.9	548.3	547.6	546.9	547.6	548.3	548.9	549.5	549.5	549.0	548.4
162.5°	554.0	553.2	552.4	551.6	552.4	553.2	554.0	554.8	554.8	554.2	553.6
165°	560.5	559.8	559.2	558.5	559.2	559.8	560.5	561.1	561.1	560.5	559.8
167.5°	565.4	564.6	563.7	562.9	563.7	564.6	565.4	566.3	566.3	565.7	565.0
170°	568.0	567.2	566.4	565.5	566.4	567.2	568.0	568.9	568.9	568.3	567.7
172.5°	570.1	569.2	568.4	567.5	568.4	569.2	570.1	570.8	570.9	570.3	569.7
175°	572.0	571.1	570.2	569.3	570.2	571.1	572.0	573.0	573.1	572.4	571.8
177.5°	572.4	571.6	571.0	570.4	571.0	571.6	572.4	573.0	573.1	572.6	572.0
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	450.0	451.5	454.0	456.6	458.2	461.2	462.1	463.5	464.8	467.8	471.0
5°	424.0	426.5	432.5	435.7	440.1	445.4	448.8	452.4	456.4	463.2	469.5
7.5°	396.1	400.3	407.7	413.8	420.2	427.6	433.0	440.1	446.1	455.7	464.9
10°	377.6	383.5	390.1	397.4	406.3	414.2	421.8	430.8	438.0	449.6	460.3
12.5°	360.8	361.7	371.3	379.2	391.5	401.3	410.0	421.6	428.6	442.4	453.7
15°	331.7	337.1	345.7	352.0	366.5	379.0	391.3	403.3	411.4	428.3	443.2
17.5°	307.0	312.0	320.9	331.2	341.7	354.0	369.9	382.6	393.6	413.0	430.6
20°	291.5	297.6	306.7	317.3	326.5	339.9	353.6	368.2	380.1	401.9	422.6
22.5°	278.3	283.1	290.4	300.9	310.9	323.2	338.2	354.1	366.5	390.1	411.0
25°	259.7	263.6	268.3	276.9	288.3	301.8	313.5	331.0	349.1	371.1	396.4
27.5°	242.9	245.7	249.9	257.5	266.3	278.8	291.8	308.4	326.7	350.5	377.3
30°	232.7	234.5	238.6	244.9	253.6	263.5	276.6	292.4	311.2	335.3	361.9
32.5°	223.8	225.4	228.1	234.1	241.6	250.1	261.9	277.7	295.6	319.2	348.8
35°	210.4	211.6	214.0	218.8	223.0	231.2	241.1	255.6	272.3	294.9	325.5
37.5°	197.0	198.8	200.2	202.2	207.6	213.0	221.6	233.8	250.2	273.1	302.2
40°	188.2	189.6	191.9	192.7	197.0	201.9	208.9	220.1	236.6	257.5	286.0
42.5°	179.3	180.8	182.0	183.1	186.8	191.1	197.4	207.0	221.7	241.9	270.1
45°	167.2	167.4	168.7	170.6	172.4	175.5	180.0	188.2	199.6	218.6	244.2
47.5°	154.9	155.1	155.3	156.1	158.1	160.9	163.9	170.6	180.8	196.0	220.9
50°	146.6	146.3	146.6	147.3	148.6	151.0	154.4	159.2	167.5	181.7	204.6
52.5°	138.7	138.7	138.5	138.7	139.7	141.3	143.8	147.9	155.3	168.3	188.5
55°	126.7	125.8	126.0	125.2	126.9	127.2	129.0	132.5	138.9	147.9	166.8
57.5°	113.8	113.1	112.3	112.1	111.9	112.9	114.3	117.0	122.0	129.9	145.2
60°	105.6	104.7	103.6	103.3	103.3	103.9	104.6	106.5	111.2	118.2	130.8
62.5°	97.3	96.3	95.6	94.7	94.3	94.9	95.6	97.0	100.4	107.0	117.9
65°	84.4	83.1	82.2	82.1	81.7	81.2	81.5	82.9	85.6	90.9	99.5
67.5°	71.5	70.3	70.1	69.0	68.5	68.6	68.5	69.7	71.4	75.9	82.3
70°	63.0	62.1	61.7	60.8	60.4	60.1	59.7	60.8	62.4	66.2	71.8
72.5°	54.3	53.6	52.8	52.0	52.1	51.7	51.7	52.4	53.6	57.1	61.5
75°	41.9	42.1	41.2	40.3	40.2	39.8	39.8	40.3	40.9	43.6	47.0
77.5°	30.4	30.3	29.5	29.2	29.1	28.7	29.1	29.4	29.7	31.5	34.0
80°	23.2	23.2	22.3	22.3	22.1	21.6	22.1	21.8	22.5	24.3	26.1
82.5°	16.6	16.3	16.2	16.0	15.9	15.5	15.8	16.2	16.5	17.7	18.8
85°	8.1	8.1	7.9	7.8	7.9	7.8	7.9	8.1	8.2	8.8	9.7
87.5°	3.5	3.5	3.5	3.5	3.4	3.4	3.3	3.2	3.3	3.3	3.2
90°	8.7	8.2	7.5	6.8	6.1	5.3	4.4	3.4	2.5	1.4	0.4
92.5°	9.8	9.6	9.2	8.9	8.5	8.2	8.0	8.1	8.2	8.2	8.3
95°	16.6	16.2	15.4	14.8	14.2	13.5	14.7	17.7	20.8	23.8	26.9
97.5°	21.9	21.5	20.1	18.6	17.1	15.6	19.2	27.7	36.3	44.8	53.3
100°	24.3	23.5	22.0	20.4	18.9	17.3	22.8	35.4	48.0	60.6	73.2
102.5°	25.2	24.2	37.3	50.4	63.5	76.4	84.4	87.0	89.7	92.4	95.0
105°	26.2	25.2	50.3	75.4	100.4	125.6	136.7	134.0	131.2	128.4	125.6
107.5°	34.3	35.3	65.4	95.5	125.6	155.6	169.5	167.3	165.1	162.9	160.7
110°	63.1	72.3	98.9	125.5	152.0	178.6	190.8	188.9	187.0	185.1	183.2



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	148.9	182.5	189.0	195.6	202.2	208.7	211.1	209.5	207.7	206.0	204.3
115°	212.5	255.1	252.8	250.5	248.2	245.9	244.0	242.4	240.8	239.2	237.7
117.5°	272.3	282.5	281.0	279.4	277.8	276.2	274.6	272.8	271.1	269.3	267.6
120°	304.1	303.0	301.3	299.8	298.1	296.4	294.9	293.5	292.2	290.7	289.4
122.5°	323.2	322.6	320.8	318.9	317.1	315.4	313.7	312.3	310.9	309.3	307.9
125°	350.0	349.4	347.6	345.9	344.1	342.4	340.9	339.7	338.5	337.3	336.1
127.5°	374.4	373.5	372.2	370.9	369.6	368.3	366.9	365.6	364.3	363.0	361.6
130°	390.1	389.0	388.0	387.0	386.0	385.0	383.7	382.3	380.8	379.3	377.9
132.5°	405.4	404.6	403.5	402.6	401.6	400.5	399.4	398.2	396.9	395.6	394.4
135°	427.1	426.2	425.4	424.6	423.7	422.9	421.8	420.3	418.8	417.4	415.9
137.5°	447.4	446.5	445.5	444.7	443.7	442.8	441.7	440.7	439.7	438.6	437.7
140°	460.6	459.7	458.7	457.7	456.7	455.7	454.8	454.1	453.4	452.6	451.9
142.5°	472.7	472.0	470.8	469.6	468.5	467.3	466.4	465.7	465.1	464.5	463.7
145°	489.7	489.1	487.5	485.9	484.4	482.8	482.1	482.2	482.3	482.4	482.4
147.5°	504.6	504.1	502.6	501.1	499.5	498.0	497.3	497.7	498.0	498.4	498.8
150°	513.6	513.0	511.6	510.1	508.7	507.2	506.8	507.4	508.0	508.7	509.3
152.5°	521.9	521.3	519.9	518.6	517.1	515.7	515.4	516.1	516.8	517.5	518.2
155°	533.1	532.5	531.4	530.3	529.2	528.1	527.9	528.8	529.6	530.4	531.2
157.5°	542.3	541.8	541.0	540.2	539.4	538.7	538.6	539.3	540.0	540.7	541.4
160°	548.0	547.4	546.8	546.3	545.7	545.2	545.2	545.7	546.3	546.8	547.4
162.5°	552.9	552.3	551.8	551.4	550.9	550.4	550.5	551.0	551.5	552.1	552.6
165°	559.2	558.5	558.3	557.9	557.7	557.5	557.5	558.1	558.6	559.2	559.8
167.5°	564.4	563.7	563.5	563.2	562.9	562.7	562.8	563.4	564.0	564.5	565.1
170°	567.0	566.4	566.2	566.0	565.9	565.6	565.9	566.4	567.0	567.5	568.0
172.5°	569.0	568.4	568.2	568.0	567.8	567.6	567.8	568.4	568.9	569.5	570.1
175°	571.2	570.5	570.3	570.1	570.0	569.8	570.0	570.7	571.3	572.0	572.6
177.5°	571.6	571.0	570.9	570.8	570.8	570.7	570.9	571.5	572.0	572.5	573.0
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	470.7	471.4	473.7	476.0	478.6	479.3	480.5	479.5	479.2	481.9	483.9
5°	472.1	475.2	481.6	487.4	492.2	495.6	499.2	500.7	503.4	507.1	511.8
7.5°	470.5	476.8	486.7	495.1	504.2	510.8	515.9	520.4	525.7	532.8	540.7
10°	468.8	477.2	489.3	499.6	510.7	519.2	526.2	533.1	541.0	550.9	561.1
12.5°	465.6	475.6	490.8	502.9	517.2	525.5	535.0	549.7	558.3	572.0	586.5
15°	459.2	470.4	491.5	506.4	522.6	538.4	555.9	569.9	583.9	592.1	612.4
17.5°	449.8	466.1	489.5	506.9	527.5	552.4	572.0	588.0	604.1	617.3	627.5
20°	442.1	459.9	486.6	507.5	532.0	558.7	581.2	597.5	611.5	622.5	628.8
22.5°	432.5	455.0	480.9	505.3	536.5	563.1	586.7	599.4	611.2	616.6	619.0
25°	417.3	444.3	473.6	503.5	538.8	566.9	588.4	596.2	599.6	594.4	585.7
27.5°	400.9	431.0	465.3	500.1	537.4	564.4	579.9	578.7	572.9	556.0	542.5
30°	388.7	421.8	458.7	496.7	534.1	560.4	569.3	560.4	547.2	528.4	509.1
32.5°	375.9	410.2	451.6	491.8	528.1	551.2	553.1	537.7	517.3	495.8	471.8
35°	356.5	393.6	438.4	480.9	515.2	529.8	521.2	493.8	469.7	440.4	407.6
37.5°	334.5	375.5	420.4	464.9	496.0	499.8	478.3	449.6	415.5	381.0	342.5
40°	318.1	361.6	407.8	452.6	480.1	476.2	448.8	417.2	376.7	334.5	298.7
42.5°	303.5	346.8	394.0	437.9	459.9	449.1	417.2	378.3	334.8	295.1	262.3
45°	278.1	322.7	370.9	413.4	426.0	406.3	364.1	320.8	278.1	244.9	219.0
47.5°	253.3	297.5	345.2	382.5	387.0	360.6	314.4	270.0	233.1	206.2	187.9
50°	235.2	279.5	326.8	360.1	358.6	326.8	279.3	237.0	206.2	184.4	172.2
52.5°	219.0	260.8	306.2	336.5	328.8	294.1	248.7	211.2	185.9	168.9	157.8
55°	193.6	232.3	275.5	299.8	285.7	247.2	208.9	178.7	159.9	147.2	138.6
57.5°	168.5	204.8	241.8	256.7	241.2	205.7	173.7	151.8	137.7	128.3	122.6
60°	153.0	184.7	217.5	230.5	212.0	180.3	155.1	135.5	124.1	116.5	111.4
62.5°	137.4	165.8	196.9	203.9	187.0	160.2	137.8	121.5	112.3	105.4	100.6
65°	116.2	139.5	163.0	167.7	152.1	131.3	113.8	103.1	94.8	89.8	86.0
67.5°	95.4	114.0	130.7	134.4	120.7	106.4	93.6	84.4	78.8	74.6	71.4
70°	82.9	97.8	111.4	114.5	103.5	90.7	81.0	73.6	68.5	65.0	61.9
72.5°	69.9	82.1	93.6	95.6	86.7	76.8	68.9	63.1	58.6	56.3	53.4
75°	53.5	60.7	69.5	70.0	64.1	58.1	52.0	48.2	45.9	43.0	41.6
77.5°	37.7	43.3	48.4	49.4	45.9	41.8	38.4	35.4	33.4	32.1	30.7
80°	28.8	33.3	35.5	36.7	34.2	31.3	29.3	27.3	26.1	25.2	24.3
82.5°	20.6	23.4	25.3	26.4	25.0	23.2	21.3	20.1	19.2	18.5	18.1
85°	10.5	11.7	13.0	13.3	13.0	12.2	11.2	11.2	10.6	10.5	10.5
87.5°	3.9	4.7	4.8	5.5	5.4	5.5	5.7	5.7	5.7	5.6	5.5
90°	1.4	2.5	3.4	4.4	5.3	6.1	6.8	7.5	8.2	8.7	9.2
92.5°	8.2	8.2	8.1	8.0	8.2	8.5	8.9	9.2	9.6	9.8	10.1
95°	23.8	20.8	17.7	14.7	13.5	14.2	14.8	15.4	16.2	16.6	17.0
97.5°	44.8	36.3	27.7	19.2	15.6	17.1	18.6	20.1	21.5	21.9	22.3
100°	60.6	48.0	35.4	22.8	17.3	18.9	20.4	22.0	23.5	24.3	25.0
102.5°	92.4	89.7	87.0	84.4	76.4	63.5	50.4	37.3	24.2	25.2	26.1
105°	128.4	131.2	134.0	136.7	125.6	100.4	75.4	50.3	25.2	26.2	27.3
107.5°	162.9	165.1	167.3	169.5	155.6	125.6	95.5	65.4	35.3	34.3	33.3
110°	185.1	187.0	188.9	190.8	178.6	152.0	125.5	98.9	72.3	63.1	53.9



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	206.0	207.7	209.5	211.1	208.7	202.2	195.6	189.0	182.5	148.9	115.4
115°	239.2	240.8	242.4	244.0	245.9	248.2	250.5	252.8	255.1	212.5	170.0
117.5°	269.3	271.1	272.8	274.6	276.2	277.8	279.4	281.0	282.5	272.3	262.0
120°	290.7	292.2	293.5	294.9	296.4	298.1	299.8	301.3	303.0	304.1	305.2
122.5°	309.3	310.9	312.3	313.7	315.4	317.1	318.9	320.8	322.6	323.2	323.8
125°	337.3	338.5	339.7	340.9	342.4	344.1	345.9	347.6	349.4	350.0	350.6
127.5°	363.0	364.3	365.6	366.9	368.3	369.6	370.9	372.2	373.5	374.4	375.3
130°	379.3	380.8	382.3	383.7	385.0	386.0	387.0	388.0	389.0	390.1	391.0
132.5°	395.6	396.9	398.2	399.4	400.5	401.6	402.6	403.5	404.6	405.4	406.3
135°	417.4	418.8	420.3	421.8	422.9	423.7	424.6	425.4	426.2	427.1	428.1
137.5°	438.6	439.7	440.7	441.7	442.8	443.7	444.7	445.5	446.5	447.4	448.3
140°	452.6	453.4	454.1	454.8	455.7	456.7	457.7	458.7	459.7	460.6	461.4
142.5°	464.5	465.1	465.7	466.4	467.3	468.5	469.6	470.8	472.0	472.7	473.5
145°	482.4	482.3	482.2	482.1	482.8	484.4	485.9	487.5	489.1	489.7	490.4
147.5°	498.4	498.0	497.7	497.3	498.0	499.5	501.1	502.6	504.1	504.6	505.1
150°	508.7	508.0	507.4	506.8	507.2	508.7	510.1	511.6	513.0	513.6	514.1
152.5°	517.5	516.8	516.1	515.4	515.7	517.1	518.6	519.9	521.3	521.9	522.4
155°	530.4	529.6	528.8	527.9	528.1	529.2	530.3	531.4	532.5	533.1	533.6
157.5°	540.7	540.0	539.3	538.6	538.7	539.4	540.2	541.0	541.8	542.3	543.0
160°	546.8	546.3	545.7	545.2	545.2	545.7	546.3	546.8	547.4	548.0	548.4
162.5°	552.1	551.5	551.0	550.5	550.4	550.9	551.4	551.8	552.3	552.9	553.6
165°	559.2	558.6	558.1	557.5	557.5	557.7	557.9	558.3	558.5	559.2	559.8
167.5°	564.5	564.0	563.4	562.8	562.7	562.9	563.2	563.5	563.7	564.4	565.0
170°	567.5	567.0	566.4	565.9	565.6	565.9	566.0	566.2	566.4	567.0	567.7
172.5°	569.5	568.9	568.4	567.8	567.6	567.8	568.0	568.2	568.4	569.0	569.7
175°	572.0	571.3	570.7	570.0	569.8	570.0	570.1	570.3	570.5	571.2	571.8
177.5°	572.5	572.0	571.5	570.9	570.7	570.8	570.8	570.9	571.0	571.6	572.0
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	485.7	487.7	487.7	488.0	490.3	490.0	489.8
5°	516.8	519.9	520.2	523.5	525.6	524.9	522.9
7.5°	546.2	551.9	556.3	558.6	561.5	563.2	562.4
10°	569.6	577.8	582.9	586.3	590.4	593.5	592.4
12.5°	590.7	600.6	607.5	613.4	613.9	617.8	615.1
15°	623.8	634.1	635.3	639.5	643.0	642.6	642.8
17.5°	634.6	637.9	638.7	638.7	638.8	637.5	634.8
20°	630.7	629.5	626.5	624.1	620.0	619.4	615.8
22.5°	612.3	608.3	600.6	595.6	589.1	587.5	586.5
25°	576.1	567.2	555.0	543.3	540.0	533.8	535.5
27.5°	526.2	512.5	499.2	489.8	481.2	471.7	474.4
30°	491.3	475.8	457.1	442.7	433.5	424.5	422.9
32.5°	449.6	426.8	406.0	393.3	379.2	373.5	367.3
35°	377.6	355.4	334.7	316.9	306.7	298.7	291.5
37.5°	312.8	287.3	270.6	256.2	248.7	244.2	245.4
40°	272.7	250.3	238.1	227.1	220.2	217.1	217.8
42.5°	240.1	223.4	213.3	205.8	201.0	199.2	198.8
45°	203.2	193.8	185.5	181.3	178.9	176.9	175.6
47.5°	178.0	170.3	165.6	163.1	161.1	159.1	159.0
50°	162.9	157.8	154.6	151.9	150.3	148.9	150.1
52.5°	151.3	146.7	143.5	141.1	140.5	139.2	139.1
55°	134.3	130.6	128.3	126.1	125.1	124.4	123.4
57.5°	118.7	115.3	113.1	111.8	109.7	109.0	108.7
60°	107.6	104.9	102.7	100.9	100.1	98.6	98.6
62.5°	97.4	94.7	92.7	91.3	89.8	89.3	89.4
65°	82.6	80.4	78.4	77.0	76.7	75.6	76.0
67.5°	69.0	67.6	65.4	64.6	64.0	63.5	63.0
70°	59.9	58.5	57.4	56.3	55.8	55.8	55.8
72.5°	52.3	50.5	49.9	48.6	48.9	48.3	47.7
75°	40.5	39.4	38.9	38.3	37.5	37.5	37.5
77.5°	29.8	29.5	28.8	28.3	28.0	27.9	28.0
80°	23.1	22.8	22.5	22.5	22.1	21.9	21.6
82.5°	17.7	17.3	17.0	16.9	16.8	16.8	16.7
85°	10.1	9.7	9.7	9.9	9.5	9.5	9.7
87.5°	5.8	5.9	5.9	5.9	6.0	5.9	5.9
90°	9.7	10.1	10.5	10.6	10.8	11.0	11.2
92.5°	10.3	10.5	10.7	10.9	10.9	11.1	11.2
95°	17.5	18.0	18.1	18.1	18.0	17.9	17.7
97.5°	22.7	23.1	23.3	23.4	23.5	23.6	23.8
100°	25.7	26.5	26.9	27.2	27.3	27.5	27.7
102.5°	27.1	28.0	28.7	28.9	29.2	29.4	29.7
105°	28.3	29.2	29.9	30.3	30.7	31.1	31.4
107.5°	32.2	31.2	30.9	31.2	31.6	31.9	32.3
110°	44.8	35.6	31.2	31.5	31.9	32.3	32.6



TEST NUMBER: P331249-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	81.9	48.4	31.8	32.1	32.4	32.7	33.0
115°	127.5	84.9	60.4	53.7	47.1	40.5	33.9
117.5°	251.7	241.4	225.4	203.6	181.9	160.2	138.4
120°	306.3	307.4	301.8	289.4	277.0	264.6	252.2
122.5°	324.6	325.2	324.3	321.9	319.5	317.1	314.7
125°	351.3	351.9	352.4	352.7	352.9	353.2	353.5
127.5°	376.3	377.2	377.7	377.8	377.9	377.9	378.0
130°	392.1	393.1	393.6	393.4	393.3	393.2	393.2
132.5°	407.2	408.1	408.4	408.3	408.2	408.1	408.1
135°	429.0	429.9	430.3	430.1	429.9	429.8	429.5
137.5°	449.2	450.1	450.4	450.0	449.7	449.5	449.2
140°	462.2	463.0	463.2	462.7	462.3	461.8	461.4
142.5°	474.2	475.0	475.2	474.7	474.2	473.7	473.2
145°	491.0	491.6	491.7	491.3	490.8	490.4	489.9
147.5°	505.6	506.0	506.0	505.7	505.3	504.9	504.5
150°	514.7	515.2	515.3	514.8	514.4	513.9	513.5
152.5°	523.0	523.6	523.5	522.9	522.3	521.7	521.1
155°	534.2	534.7	534.6	533.9	533.1	532.4	531.6
157.5°	543.6	544.2	544.2	543.4	542.7	542.0	541.3
160°	549.0	549.5	549.5	548.9	548.3	547.6	546.9
162.5°	554.2	554.8	554.8	554.0	553.2	552.4	551.6
165°	560.5	561.1	561.1	560.5	559.8	559.2	558.5
167.5°	565.7	566.3	566.3	565.4	564.6	563.7	562.9
170°	568.3	568.9	568.9	568.0	567.2	566.4	565.5
172.5°	570.3	570.9	570.8	570.1	569.2	568.4	567.5
175°	572.4	573.1	573.0	572.0	571.1	570.2	569.3
177.5°	572.6	573.1	573.0	572.4	571.6	571.0	570.4
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3

(END OF REPORT)