

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331250-927

Luminaire Tested: **SA2XXDIP-C290D530U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331250-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2532.0 lumens  
Efficiency: N/A  
Efficacy: 98.9 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41				41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41				35	
2	88	81	75	70	80	74	69	65	61	57	54	49	47	45	38	37	35				30	
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30				26	
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26				23	
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23				20	
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21				18	
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19				16	
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	21	19	17				14	
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15				13	
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	18	16	14				12	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7561	7561	7561	7561
5°	8475	7609	6744	7609
10°	9712	7547	5835	7547
15°	10745	7408	5157	7408
20°	10581	7261	4699	7261
25°	9540	7062	4411	7062
30°	7884	6747	4200	6747
35°	5746	6416	4050	6416
40°	4591	6028	3967	6028
45°	4010	5576	3854	5576
50°	3770	5139	3778	5139
55°	3474	4695	3676	4695
60°	3184	4224	3523	4224
65°	2904	3801	3370	3801
70°	2634	3389	3144	3389
75°	2339	2932	2782	2932
80°	2008	2427	2241	2427
85°	1797	1797	1334	1797



TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.6	1.8
10°-20°	129.6	5.1
20°-30°	188.1	7.4
30°-40°	198.5	7.8
40°-50°	175.8	6.9
50°-60°	140.3	5.5
60°-70°	95.4	3.8
70°-80°	48.9	1.9
80°-90°	13.9	0.5
90°-100°	33.9	1.3
100°-110°	105.4	4.2
110°-120°	180.1	7.1
120°-130°	236.8	9.4
130°-140°	265.8	10.5
140°-150°	260.6	10.3
150°-160°	218.6	8.6
160°-170°	145.0	5.7
170°-180°	50.7	2.0
0°-30°	362.4	14.3
0°-40°	560.9	22.2
0°-60°	877.0	34.6
0°-90°	1035.2	40.9
90°-120°	319.4	12.6
90°-150°	1082.6	42.8
90°-180°	1497.0	59.1
0°-180°	2532.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	468	468	468	468	468	
5°	523	470	416	470	523	52
15°	643	443	308	443	643	177
25°	536	396	248	396	536	242
35°	292	326	206	326	292	190
45°	176	244	169	244	176	138
55°	123	167	131	167	123	111
65°	76	100	88	100	76	76
75°	38	47	45	47	38	40
85°	10	10	7	10	10	11
90°	15	0	15	0	15	7
95°	28	24	28	24	28	31
105°	100	97	100	97	100	105
115°	181	181	181	181	181	178
125°	264	263	264	263	264	235
135°	344	340	344	340	344	265
145°	417	413	417	413	417	261
155°	476	472	476	472	476	219
165°	514	514	514	514	514	145
175°	533	534	533	534	533	51
180°	535	535	535	535	535	



TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	489.8	490.0	490.3	488.0	487.7	487.7	485.7	483.9	481.9	479.2	479.5
5°	522.9	524.9	525.6	523.5	520.2	519.9	516.8	511.8	507.1	503.4	500.7
7.5°	562.4	563.2	561.5	558.6	556.3	551.9	546.2	540.7	532.8	525.7	520.4
10°	592.4	593.5	590.4	586.3	582.9	577.8	569.6	561.1	550.9	541.0	533.1
12.5°	615.1	617.8	613.9	613.4	607.5	600.6	590.7	586.5	572.0	558.3	549.7
15°	642.8	642.6	643.0	639.5	635.3	634.1	623.8	612.4	592.1	583.9	569.9
17.5°	634.8	637.5	638.8	638.7	638.7	637.9	634.6	627.5	617.3	604.1	588.0
20°	615.8	619.4	620.0	624.1	626.5	629.5	630.7	628.8	622.5	611.5	597.5
22.5°	586.5	587.5	589.1	595.6	600.6	608.3	612.3	619.0	616.6	611.2	599.4
25°	535.5	533.8	540.0	543.3	555.0	567.2	576.1	585.7	594.4	599.6	596.2
27.5°	474.4	471.7	481.2	489.8	499.2	512.5	526.2	542.5	556.0	572.9	578.7
30°	422.9	424.5	433.5	442.7	457.1	475.8	491.3	509.1	528.4	547.2	560.4
32.5°	367.3	373.5	379.2	393.3	406.0	426.8	449.6	471.8	495.8	517.3	537.7
35°	291.5	298.7	306.7	316.9	334.7	355.4	377.6	407.6	440.4	469.7	493.8
37.5°	245.4	244.2	248.7	256.2	270.6	287.3	312.8	342.5	381.0	415.5	449.6
40°	217.8	217.1	220.2	227.1	238.1	250.3	272.7	298.7	334.5	376.7	417.2
42.5°	198.8	199.2	201.0	205.8	213.3	223.4	240.1	262.3	295.1	334.8	378.3
45°	175.6	176.9	178.9	181.3	185.5	193.8	203.2	219.0	244.9	278.1	320.8
47.5°	159.0	159.1	161.1	163.1	165.6	170.3	178.0	187.9	206.2	233.1	270.0
50°	150.1	148.9	150.3	151.9	154.6	157.8	162.9	172.2	184.4	206.2	237.0
52.5°	139.1	139.2	140.5	141.1	143.5	146.7	151.3	157.8	168.9	185.9	211.2
55°	123.4	124.4	125.1	126.1	128.3	130.6	134.3	138.6	147.2	159.9	178.7
57.5°	108.7	109.0	109.7	111.8	113.1	115.3	118.7	122.6	128.3	137.7	151.8
60°	98.6	98.6	100.1	100.9	102.7	104.9	107.6	111.4	116.5	124.1	135.5
62.5°	89.4	89.3	89.8	91.3	92.7	94.7	97.4	100.6	105.4	112.3	121.5
65°	76.0	75.6	76.7	77.0	78.4	80.4	82.6	86.0	89.8	94.8	103.1
67.5°	63.0	63.5	64.0	64.6	65.4	67.6	69.0	71.4	74.6	78.8	84.4
70°	55.8	55.8	55.8	56.3	57.4	58.5	59.9	61.9	65.0	68.5	73.6
72.5°	47.7	48.3	48.9	48.6	49.9	50.5	52.3	53.4	56.3	58.6	63.1
75°	37.5	37.5	37.5	38.3	38.9	39.4	40.5	41.6	43.0	45.9	48.2
77.5°	28.0	27.9	28.0	28.3	28.8	29.5	29.8	30.7	32.1	33.4	35.4
80°	21.6	21.9	22.1	22.5	22.5	22.8	23.1	24.3	25.2	26.1	27.3
82.5°	16.7	16.8	16.8	16.9	17.0	17.3	17.7	18.1	18.5	19.2	20.1
85°	9.7	9.5	9.5	9.9	9.7	9.7	10.1	10.5	10.5	10.6	11.2
87.5°	6.8	6.8	6.9	6.7	6.7	6.9	6.9	6.8	7.0	7.2	6.9
90°	15.4	15.3	15.1	15.1	15.0	15.0	15.2	15.4	15.6	15.8	13.6
92.5°	14.7	14.7	14.6	14.6	14.6	14.5	14.5	14.4	14.4	14.3	13.9
95°	28.0	28.2	28.4	28.6	28.8	28.9	28.9	28.9	28.9	28.9	28.7
97.5°	48.5	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.2
100°	61.9	62.0	62.1	62.2	62.3	62.3	62.3	62.3	62.3	62.3	62.0
102.5°	77.1	77.2	77.2	77.4	77.5	77.5	77.4	77.3	77.2	77.2	76.8
105°	100.3	100.3	100.3	100.3	100.3	100.2	100.0	99.8	99.6	99.4	99.2
107.5°	122.2	122.6	123.1	123.5	124.0	124.2	124.1	124.1	124.0	123.9	123.9
110°	139.1	139.4	139.7	140.1	140.4	140.5	140.5	140.5	140.5	140.5	140.5



TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.4	155.6	155.8	156.1	156.3	156.5	156.8	157.0	157.2	157.5	157.6
115°	180.7	181.0	181.3	181.6	181.9	182.1	182.2	182.3	182.4	182.5	182.7
117.5°	204.8	205.1	205.4	205.7	206.0	206.3	206.5	206.8	207.0	207.2	207.8
120°	221.8	222.1	222.4	222.7	223.0	223.2	223.2	223.2	223.2	223.2	223.9
122.5°	238.4	238.7	238.8	239.1	239.3	239.6	239.8	240.0	240.3	240.5	241.1
125°	263.8	263.9	264.0	264.1	264.2	264.4	264.7	265.0	265.3	265.6	265.9
127.5°	286.9	287.2	287.6	287.9	288.2	288.6	288.9	289.3	289.6	290.0	290.4
130°	303.6	304.0	304.4	304.8	305.1	305.5	305.7	305.9	306.1	306.3	306.5
132.5°	319.5	319.8	320.1	320.4	320.8	321.2	321.5	322.0	322.5	322.9	322.9
135°	344.2	344.5	344.8	345.2	345.4	345.6	345.7	345.9	345.9	346.0	345.9
137.5°	366.6	367.0	367.4	367.8	368.2	368.4	368.5	368.6	368.7	368.8	368.5
140°	382.1	382.5	382.9	383.3	383.8	384.0	384.0	384.0	384.0	384.0	383.5
142.5°	396.2	396.6	397.0	397.4	397.8	398.0	397.9	397.8	397.8	397.7	397.4
145°	417.4	417.8	418.2	418.6	419.0	419.1	419.1	419.0	418.8	418.7	418.2
147.5°	436.3	436.7	437.0	437.4	437.8	437.9	437.7	437.4	437.2	437.0	436.6
150°	448.6	448.9	449.2	449.5	449.8	449.8	449.5	449.2	448.9	448.6	448.1
152.5°	460.2	460.5	460.9	461.3	461.7	461.7	461.3	460.9	460.5	460.2	459.6
155°	475.7	475.9	476.3	476.6	476.9	476.8	476.3	475.8	475.3	474.8	474.4
157.5°	489.0	489.6	490.0	490.5	491.0	490.9	490.2	489.5	488.9	488.1	488.0
160°	497.3	497.7	498.2	498.6	499.0	498.8	498.3	497.6	497.1	496.5	496.4
162.5°	504.6	505.1	505.6	506.0	506.5	506.4	505.7	505.0	504.4	503.7	503.6
165°	514.0	514.6	515.1	515.6	516.1	515.9	515.3	514.6	513.9	513.2	513.2
167.5°	521.8	522.4	522.9	523.4	523.9	523.9	523.2	522.4	521.7	521.0	521.0
170°	525.9	526.4	527.0	527.6	528.2	528.1	527.5	526.8	526.1	525.4	525.5
172.5°	529.1	529.7	530.3	530.9	531.5	531.4	530.8	530.0	529.3	528.6	528.7
175°	532.6	533.2	533.8	534.4	535.0	535.0	534.2	533.5	532.8	532.1	532.3
177.5°	534.2	534.7	535.2	535.7	536.1	536.1	535.7	535.2	534.7	534.2	534.4
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	480.5	479.3	478.6	476.0	473.7	471.4	470.7	471.0	467.8	464.8	463.5
5°	499.2	495.6	492.2	487.4	481.6	475.2	472.1	469.5	463.2	456.4	452.4
7.5°	515.9	510.8	504.2	495.1	486.7	476.8	470.5	464.9	455.7	446.1	440.1
10°	526.2	519.2	510.7	499.6	489.3	477.2	468.8	460.3	449.6	438.0	430.8
12.5°	535.0	525.5	517.2	502.9	490.8	475.6	465.6	453.7	442.4	428.6	421.6
15°	555.9	538.4	522.6	506.4	491.5	470.4	459.2	443.2	428.3	411.4	403.3
17.5°	572.0	552.4	527.5	506.9	489.5	466.1	449.8	430.6	413.0	393.6	382.6
20°	581.2	558.7	532.0	507.5	486.6	459.9	442.1	422.6	401.9	380.1	368.2
22.5°	586.7	563.1	536.5	505.3	480.9	455.0	432.5	411.0	390.1	366.5	354.1
25°	588.4	566.9	538.8	503.5	473.6	444.3	417.3	396.4	371.1	349.1	331.0
27.5°	579.9	564.4	537.4	500.1	465.3	431.0	400.9	377.3	350.5	326.7	308.4
30°	569.3	560.4	534.1	496.7	458.7	421.8	388.7	361.9	335.3	311.2	292.4
32.5°	553.1	551.2	528.1	491.8	451.6	410.2	375.9	348.8	319.2	295.6	277.7
35°	521.2	529.8	515.2	480.9	438.4	393.6	356.5	325.5	294.9	272.3	255.6
37.5°	478.3	499.8	496.0	464.9	420.4	375.5	334.5	302.2	273.1	250.2	233.8
40°	448.8	476.2	480.1	452.6	407.8	361.6	318.1	286.0	257.5	236.6	220.1
42.5°	417.2	449.1	459.9	437.9	394.0	346.8	303.5	270.1	241.9	221.7	207.0
45°	364.1	406.3	426.0	413.4	370.9	322.7	278.1	244.2	218.6	199.6	188.2
47.5°	314.4	360.6	387.0	382.5	345.2	297.5	253.3	220.9	196.0	180.8	170.6
50°	279.3	326.8	358.6	360.1	326.8	279.5	235.2	204.6	181.7	167.5	159.2
52.5°	248.7	294.1	328.8	336.5	306.2	260.8	219.0	188.5	168.3	155.3	147.9
55°	208.9	247.2	285.7	299.8	275.5	232.3	193.6	166.8	147.9	138.9	132.5
57.5°	173.7	205.7	241.2	256.7	241.8	204.8	168.5	145.2	129.9	122.0	117.0
60°	155.1	180.3	212.0	230.5	217.5	184.7	153.0	130.8	118.2	111.2	106.5
62.5°	137.8	160.2	187.0	203.9	196.9	165.8	137.4	117.9	107.0	100.4	97.0
65°	113.8	131.3	152.1	167.7	163.0	139.5	116.2	99.5	90.9	85.6	82.9
67.5°	93.6	106.4	120.7	134.4	130.7	114.0	95.4	82.3	75.9	71.4	69.7
70°	81.0	90.7	103.5	114.5	111.4	97.8	82.9	71.8	66.2	62.4	60.8
72.5°	68.9	76.8	86.7	95.6	93.6	82.1	69.9	61.5	57.1	53.6	52.4
75°	52.0	58.1	64.1	70.0	69.5	60.7	53.5	47.0	43.6	40.9	40.3
77.5°	38.4	41.8	45.9	49.4	48.4	43.3	37.7	34.0	31.5	29.7	29.4
80°	29.3	31.3	34.2	36.7	35.5	33.3	28.8	26.1	24.3	22.5	21.8
82.5°	21.3	23.2	25.0	26.4	25.3	23.4	20.6	18.8	17.7	16.5	16.2
85°	11.2	12.2	13.0	13.3	13.0	11.7	10.5	9.7	8.8	8.2	8.1
87.5°	6.6	6.2	5.7	5.6	5.0	4.8	4.0	3.2	3.3	3.5	3.4
90°	11.4	9.2	7.0	5.3	4.0	2.9	1.7	0.5	1.7	2.9	4.0
92.5°	13.3	12.8	12.3	11.6	10.7	9.8	9.0	8.1	9.0	9.8	10.7
95°	28.5	28.3	28.1	27.5	26.5	25.5	24.5	23.5	24.5	25.5	26.5
97.5°	47.8	47.5	47.1	46.4	45.6	44.7	43.8	42.9	43.8	44.7	45.6
100°	61.7	61.5	61.2	60.6	59.8	58.9	58.1	57.4	58.1	58.9	59.8
102.5°	76.4	76.0	75.7	75.1	74.5	73.8	73.2	72.6	73.2	73.8	74.5
105°	98.9	98.8	98.5	98.3	98.0	97.8	97.4	97.1	97.4	97.8	98.0
107.5°	123.9	123.9	123.9	123.7	123.2	122.8	122.3	121.9	122.3	122.8	123.2
110°	140.5	140.5	140.5	140.2	139.6	138.9	138.4	137.8	138.4	138.9	139.6





TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	157.6	157.7	157.8	157.6	156.9	156.3	155.7	155.1	155.7	156.3	156.9
115°	182.9	183.1	183.3	183.1	182.5	181.9	181.3	180.7	181.3	181.9	182.5
117.5°	208.3	209.0	209.5	209.4	208.6	207.8	207.0	206.2	207.0	207.8	208.6
120°	224.7	225.5	226.4	226.4	225.5	224.7	223.9	223.2	223.9	224.7	225.5
122.5°	241.6	242.2	242.7	242.6	241.6	240.7	239.6	238.7	239.6	240.7	241.6
125°	266.3	266.5	266.8	266.5	265.6	264.7	263.8	262.9	263.8	264.7	265.6
127.5°	290.7	291.1	291.4	291.0	289.9	288.8	287.6	286.5	287.6	288.8	289.9
130°	306.7	306.9	307.0	306.5	305.2	303.9	302.6	301.3	302.6	303.9	305.2
132.5°	322.8	322.8	322.7	322.2	321.2	320.0	319.0	317.9	319.0	320.0	321.2
135°	345.6	345.4	345.2	344.6	343.5	342.4	341.3	340.2	341.3	342.4	343.5
137.5°	368.3	368.0	367.7	367.2	366.3	365.4	364.5	363.5	364.5	365.4	366.3
140°	382.9	382.5	382.0	381.3	380.3	379.5	378.6	377.6	378.6	379.5	380.3
142.5°	397.0	396.7	396.3	395.7	394.8	394.0	393.0	392.1	393.0	394.0	394.8
145°	417.6	416.9	416.4	415.7	415.0	414.3	413.6	412.9	413.6	414.3	415.0
147.5°	436.2	435.8	435.4	434.7	434.0	433.1	432.2	431.4	432.2	433.1	434.0
150°	447.7	447.3	446.9	446.5	445.8	445.3	444.7	444.1	444.7	445.3	445.8
152.5°	459.1	458.7	458.2	457.6	457.1	456.5	455.9	455.3	455.9	456.5	457.1
155°	474.2	473.9	473.6	473.2	472.9	472.7	472.4	472.1	472.4	472.7	472.9
157.5°	487.8	487.6	487.4	487.3	487.0	486.8	486.6	486.4	486.6	486.8	487.0
160°	496.2	496.1	496.1	495.9	495.7	495.5	495.3	495.1	495.3	495.5	495.7
162.5°	503.5	503.4	503.3	503.2	503.2	503.1	503.1	503.0	503.1	503.1	503.2
165°	513.2	513.2	513.2	513.3	513.3	513.4	513.5	513.7	513.5	513.4	513.3
167.5°	521.1	521.1	521.1	521.3	521.6	521.9	522.2	522.4	522.2	521.9	521.6
170°	525.5	525.7	525.8	526.0	526.2	526.6	526.9	527.2	526.9	526.6	526.2
172.5°	528.9	528.9	529.0	529.3	529.5	529.8	530.1	530.4	530.1	529.8	529.5
175°	532.6	532.7	533.0	533.2	533.5	533.8	534.1	534.4	534.1	533.8	533.5
177.5°	534.6	534.7	534.9	535.0	535.3	535.5	535.8	536.1	535.8	535.5	535.3
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	462.1	461.2	458.2	456.6	454.0	451.5	450.0	450.7	451.2	451.0	450.5
5°	448.8	445.4	440.1	435.7	432.5	426.5	424.0	422.7	421.6	420.4	419.1
7.5°	433.0	427.6	420.2	413.8	407.7	400.3	396.1	393.6	391.0	388.2	385.6
10°	421.8	414.2	406.3	397.4	390.1	383.5	377.6	373.6	369.9	366.5	364.1
12.5°	410.0	401.3	391.5	379.2	371.3	361.7	360.8	353.9	348.2	346.1	343.2
15°	391.3	379.0	366.5	352.0	345.7	337.1	331.7	326.2	321.4	318.0	317.1
17.5°	369.9	354.0	341.7	331.2	320.9	312.0	307.0	302.8	298.7	294.2	293.6
20°	353.6	339.9	326.5	317.3	306.7	297.6	291.5	287.2	283.8	281.1	278.8
22.5°	338.2	323.2	310.9	300.9	290.4	283.1	278.3	274.1	271.2	268.3	266.1
25°	313.5	301.8	288.3	276.9	268.3	263.6	259.7	256.1	254.3	252.3	249.8
27.5°	291.8	278.8	266.3	257.5	249.9	245.7	242.9	240.4	238.8	237.6	236.1
30°	276.6	263.5	253.6	244.9	238.6	234.5	232.7	231.2	229.3	228.5	227.8
32.5°	261.9	250.1	241.6	234.1	228.1	225.4	223.8	222.4	220.9	220.2	218.7
35°	241.1	231.2	223.0	218.8	214.0	211.6	210.4	208.6	207.2	206.4	206.2
37.5°	221.6	213.0	207.6	202.2	200.2	198.8	197.0	195.8	195.4	195.3	195.0
40°	208.9	201.9	197.0	192.7	191.9	189.6	188.2	187.2	187.2	187.4	187.2
42.5°	197.4	191.1	186.8	183.1	182.0	180.8	179.3	179.3	179.5	180.1	179.5
45°	180.0	175.5	172.4	170.6	168.7	167.4	167.2	167.7	167.9	168.1	168.7
47.5°	163.9	160.9	158.1	156.1	155.3	155.1	154.9	155.8	156.7	157.0	157.8
50°	154.4	151.0	148.6	147.3	146.6	146.3	146.6	147.7	148.5	149.3	149.9
52.5°	143.8	141.3	139.7	138.7	138.5	138.7	138.7	140.0	141.1	141.5	141.7
55°	129.0	127.2	126.9	125.2	126.0	125.8	126.7	127.4	128.5	129.6	129.8
57.5°	114.3	112.9	111.9	112.1	112.3	113.1	113.8	115.1	116.2	117.4	117.5
60°	104.6	103.9	103.3	103.3	103.6	104.7	105.6	106.9	107.6	108.4	108.8
62.5°	95.6	94.9	94.3	94.7	95.6	96.3	97.3	98.0	98.7	99.4	99.7
65°	81.5	81.2	81.7	82.1	82.2	83.1	84.4	84.9	85.6	86.0	87.3
67.5°	68.5	68.6	68.5	69.0	70.1	70.3	71.5	72.7	72.9	73.6	74.4
70°	59.7	60.1	60.4	60.8	61.7	62.1	63.0	63.5	64.2	64.8	65.4
72.5°	51.7	51.7	52.1	52.0	52.8	53.6	54.3	54.9	55.6	56.3	56.8
75°	39.8	39.8	40.2	40.3	41.2	42.1	41.9	42.3	43.0	43.7	44.1
77.5°	29.1	28.7	29.1	29.2	29.5	30.3	30.4	30.9	31.8	31.5	31.9
80°	22.1	21.6	22.1	22.3	22.3	23.2	23.2	23.6	24.1	23.6	24.1
82.5°	15.8	15.5	15.9	16.0	16.2	16.3	16.6	16.6	17.2	17.0	17.2
85°	7.9	7.8	7.9	7.8	7.9	8.1	8.1	7.9	7.9	8.2	7.8
87.5°	3.5	3.7	4.0	4.4	4.8	5.1	4.8	4.8	4.8	4.4	4.4
90°	5.3	7.0	9.2	11.4	13.6	15.8	15.6	15.4	15.2	15.0	15.0
92.5°	11.6	12.3	12.8	13.3	13.9	14.3	14.4	14.4	14.5	14.5	14.6
95°	27.5	28.1	28.3	28.5	28.7	28.9	28.9	28.9	28.9	28.9	28.8
97.5°	46.4	47.1	47.5	47.8	48.2	48.6	48.6	48.6	48.6	48.6	48.6
100°	60.6	61.2	61.5	61.7	62.0	62.3	62.3	62.3	62.3	62.3	62.3
102.5°	75.1	75.7	76.0	76.4	76.8	77.2	77.2	77.3	77.4	77.5	77.5
105°	98.3	98.5	98.8	98.9	99.2	99.4	99.6	99.8	100.0	100.2	100.3
107.5°	123.7	123.9	123.9	123.9	123.9	123.9	124.0	124.1	124.1	124.2	124.0
110°	140.2	140.5	140.5	140.5	140.5	140.5	140.5	140.5	140.5	140.5	140.4



TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	157.6	157.8	157.7	157.6	157.6	157.5	157.2	157.0	156.8	156.5	156.3
115°	183.1	183.3	183.1	182.9	182.7	182.5	182.4	182.3	182.2	182.1	181.9
117.5°	209.4	209.5	209.0	208.3	207.8	207.2	207.0	206.8	206.5	206.3	206.0
120°	226.4	226.4	225.5	224.7	223.9	223.2	223.2	223.2	223.2	223.2	223.0
122.5°	242.6	242.7	242.2	241.6	241.1	240.5	240.3	240.0	239.8	239.6	239.3
125°	266.5	266.8	266.5	266.3	265.9	265.6	265.3	265.0	264.7	264.4	264.2
127.5°	291.0	291.4	291.1	290.7	290.4	290.0	289.6	289.3	288.9	288.6	288.2
130°	306.5	307.0	306.9	306.7	306.5	306.3	306.1	305.9	305.7	305.5	305.1
132.5°	322.2	322.7	322.8	322.8	322.9	322.9	322.5	322.0	321.5	321.2	320.8
135°	344.6	345.2	345.4	345.6	345.9	346.0	345.9	345.9	345.7	345.6	345.4
137.5°	367.2	367.7	368.0	368.3	368.5	368.8	368.7	368.6	368.5	368.4	368.2
140°	381.3	382.0	382.5	382.9	383.5	384.0	384.0	384.0	384.0	384.0	383.8
142.5°	395.7	396.3	396.7	397.0	397.4	397.7	397.8	397.8	397.9	398.0	397.8
145°	415.7	416.4	416.9	417.6	418.2	418.7	418.8	419.0	419.1	419.1	419.0
147.5°	434.7	435.4	435.8	436.2	436.6	437.0	437.2	437.4	437.7	437.9	437.8
150°	446.5	446.9	447.3	447.7	448.1	448.6	448.9	449.2	449.5	449.8	449.8
152.5°	457.6	458.2	458.7	459.1	459.6	460.2	460.5	460.9	461.3	461.7	461.7
155°	473.2	473.6	473.9	474.2	474.4	474.8	475.3	475.8	476.3	476.8	476.9
157.5°	487.3	487.4	487.6	487.8	488.0	488.1	488.9	489.5	490.2	490.9	491.0
160°	495.9	496.1	496.1	496.2	496.4	496.5	497.1	497.6	498.3	498.8	499.0
162.5°	503.2	503.3	503.4	503.5	503.6	503.7	504.4	505.0	505.7	506.4	506.5
165°	513.3	513.2	513.2	513.2	513.2	513.2	513.9	514.6	515.3	515.9	516.1
167.5°	521.3	521.1	521.1	521.1	521.0	521.0	521.7	522.4	523.2	523.9	523.9
170°	526.0	525.8	525.7	525.5	525.5	525.4	526.1	526.8	527.5	528.1	528.2
172.5°	529.3	529.0	528.9	528.9	528.7	528.6	529.3	530.0	530.8	531.4	531.5
175°	533.2	533.0	532.7	532.6	532.3	532.1	532.8	533.5	534.2	535.0	535.0
177.5°	535.0	534.9	534.7	534.6	534.4	534.2	534.7	535.2	535.7	536.1	536.1
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	449.1	448.8	448.8	447.5	448.8	448.8	449.1	450.5	451.0	451.2	450.7
5°	416.6	416.1	415.2	416.1	415.2	416.1	416.6	419.1	420.4	421.6	422.7
7.5°	384.4	382.3	382.0	379.9	382.0	382.3	384.4	385.6	388.2	391.0	393.6
10°	361.0	359.6	359.3	355.9	359.3	359.6	361.0	364.1	366.5	369.9	373.6
12.5°	343.2	339.7	340.4	338.4	340.4	339.7	343.2	343.2	346.1	348.2	353.9
15°	312.2	312.2	311.5	308.5	311.5	312.2	312.2	317.1	318.0	321.4	326.2
17.5°	290.0	289.6	288.0	288.8	288.0	289.6	290.0	293.6	294.2	298.7	302.8
20°	276.8	275.7	273.5	273.5	273.5	275.7	276.8	278.8	281.1	283.8	287.2
22.5°	264.3	264.2	261.9	262.6	261.9	264.2	264.3	266.1	268.3	271.2	274.1
25°	249.6	248.2	247.1	247.6	247.1	248.2	249.6	249.8	252.3	254.3	256.1
27.5°	235.7	234.9	234.8	233.4	234.8	234.9	235.7	236.1	237.6	238.8	240.4
30°	227.7	225.9	226.2	225.3	226.2	225.9	227.7	227.8	228.5	229.3	231.2
32.5°	218.4	217.8	217.5	216.7	217.5	217.8	218.4	218.7	220.2	220.9	222.4
35°	205.9	206.0	205.2	205.5	205.2	206.0	205.9	206.2	206.4	207.2	208.6
37.5°	194.9	195.4	195.0	195.1	195.0	195.4	194.9	195.0	195.3	195.4	195.8
40°	187.7	187.7	187.7	188.2	187.7	187.7	187.7	187.2	187.4	187.2	187.2
42.5°	180.8	180.5	180.2	180.1	180.2	180.5	180.8	179.5	180.1	179.5	179.3
45°	169.0	169.5	169.7	168.8	169.7	169.5	169.0	168.7	168.1	167.9	167.7
47.5°	158.3	158.4	158.3	159.1	158.3	158.4	158.3	157.8	157.0	156.7	155.8
50°	150.8	150.4	150.8	150.4	150.8	150.4	150.8	149.9	149.3	148.5	147.7
52.5°	142.9	143.0	142.8	142.7	142.8	143.0	142.9	141.7	141.5	141.1	140.0
55°	130.5	130.8	130.6	130.6	130.6	130.8	130.5	129.8	129.6	128.5	127.4
57.5°	117.6	118.0	118.2	117.4	118.2	118.0	117.6	117.5	117.4	116.2	115.1
60°	108.7	109.6	109.4	109.1	109.4	109.6	108.7	108.8	108.4	107.6	106.9
62.5°	100.4	100.8	100.8	100.7	100.8	100.8	100.4	99.7	99.4	98.7	98.0
65°	87.9	88.2	87.6	88.2	87.6	88.2	87.9	87.3	86.0	85.6	84.9
67.5°	74.1	74.3	74.7	74.9	74.7	74.3	74.1	74.4	73.6	72.9	72.7
70°	65.7	65.5	66.1	66.6	66.1	65.5	65.7	65.4	64.8	64.2	63.5
72.5°	56.7	57.1	57.0	57.4	57.0	57.1	56.7	56.8	56.3	55.6	54.9
75°	43.7	44.3	44.1	44.6	44.1	44.3	43.7	44.1	43.7	43.0	42.3
77.5°	31.6	31.7	31.6	31.9	31.6	31.7	31.6	31.9	31.5	31.8	30.9
80°	24.1	23.8	23.4	24.1	23.4	23.8	24.1	24.1	23.6	24.1	23.6
82.5°	16.8	17.0	16.6	16.6	16.6	17.0	16.8	17.2	17.0	17.2	16.6
85°	7.8	7.5	7.2	7.2	7.2	7.5	7.8	7.8	8.2	7.9	7.9
87.5°	4.4	4.4	4.4	4.2	4.4	4.4	4.4	4.4	4.4	4.8	4.8
90°	15.1	15.1	15.3	15.4	15.3	15.1	15.1	15.0	15.0	15.2	15.4
92.5°	14.6	14.6	14.7	14.7	14.7	14.6	14.6	14.6	14.5	14.5	14.4
95°	28.6	28.4	28.2	28.0	28.2	28.4	28.6	28.8	28.9	28.9	28.9
97.5°	48.6	48.6	48.6	48.5	48.6	48.6	48.6	48.6	48.6	48.6	48.6
100°	62.2	62.1	62.0	61.9	62.0	62.1	62.2	62.3	62.3	62.3	62.3
102.5°	77.4	77.2	77.2	77.1	77.2	77.2	77.4	77.5	77.5	77.4	77.3
105°	100.3	100.3	100.3	100.3	100.3	100.3	100.3	100.3	100.2	100.0	99.8
107.5°	123.5	123.1	122.6	122.2	122.6	123.1	123.5	124.0	124.2	124.1	124.1
110°	140.1	139.7	139.4	139.1	139.4	139.7	140.1	140.4	140.5	140.5	140.5



TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	156.1	155.8	155.6	155.4	155.6	155.8	156.1	156.3	156.5	156.8	157.0
115°	181.6	181.3	181.0	180.7	181.0	181.3	181.6	181.9	182.1	182.2	182.3
117.5°	205.7	205.4	205.1	204.8	205.1	205.4	205.7	206.0	206.3	206.5	206.8
120°	222.7	222.4	222.1	221.8	222.1	222.4	222.7	223.0	223.2	223.2	223.2
122.5°	239.1	238.8	238.7	238.4	238.7	238.8	239.1	239.3	239.6	239.8	240.0
125°	264.1	264.0	263.9	263.8	263.9	264.0	264.1	264.2	264.4	264.7	265.0
127.5°	287.9	287.6	287.2	286.9	287.2	287.6	287.9	288.2	288.6	288.9	289.3
130°	304.8	304.4	304.0	303.6	304.0	304.4	304.8	305.1	305.5	305.7	305.9
132.5°	320.4	320.1	319.8	319.5	319.8	320.1	320.4	320.8	321.2	321.5	322.0
135°	345.2	344.8	344.5	344.2	344.5	344.8	345.2	345.4	345.6	345.7	345.9
137.5°	367.8	367.4	367.0	366.6	367.0	367.4	367.8	368.2	368.4	368.5	368.6
140°	383.3	382.9	382.5	382.1	382.5	382.9	383.3	383.8	384.0	384.0	384.0
142.5°	397.4	397.0	396.6	396.2	396.6	397.0	397.4	397.8	398.0	397.9	397.8
145°	418.6	418.2	417.8	417.4	417.8	418.2	418.6	419.0	419.1	419.1	419.0
147.5°	437.4	437.0	436.7	436.3	436.7	437.0	437.4	437.8	437.9	437.7	437.4
150°	449.5	449.2	448.9	448.6	448.9	449.2	449.5	449.8	449.8	449.5	449.2
152.5°	461.3	460.9	460.5	460.2	460.5	460.9	461.3	461.7	461.7	461.3	460.9
155°	476.6	476.3	475.9	475.7	475.9	476.3	476.6	476.9	476.8	476.3	475.8
157.5°	490.5	490.0	489.6	489.0	489.6	490.0	490.5	491.0	490.9	490.2	489.5
160°	498.6	498.2	497.7	497.3	497.7	498.2	498.6	499.0	498.8	498.3	497.6
162.5°	506.0	505.6	505.1	504.6	505.1	505.6	506.0	506.5	506.4	505.7	505.0
165°	515.6	515.1	514.6	514.0	514.6	515.1	515.6	516.1	515.9	515.3	514.6
167.5°	523.4	522.9	522.4	521.8	522.4	522.9	523.4	523.9	523.9	523.2	522.4
170°	527.6	527.0	526.4	525.9	526.4	527.0	527.6	528.2	528.1	527.5	526.8
172.5°	530.9	530.3	529.7	529.1	529.7	530.3	530.9	531.5	531.4	530.8	530.0
175°	534.4	533.8	533.2	532.6	533.2	533.8	534.4	535.0	535.0	534.2	533.5
177.5°	535.7	535.2	534.7	534.2	534.7	535.2	535.7	536.1	536.1	535.7	535.2
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	450.0	451.5	454.0	456.6	458.2	461.2	462.1	463.5	464.8	467.8	471.0
5°	424.0	426.5	432.5	435.7	440.1	445.4	448.8	452.4	456.4	463.2	469.5
7.5°	396.1	400.3	407.7	413.8	420.2	427.6	433.0	440.1	446.1	455.7	464.9
10°	377.6	383.5	390.1	397.4	406.3	414.2	421.8	430.8	438.0	449.6	460.3
12.5°	360.8	361.7	371.3	379.2	391.5	401.3	410.0	421.6	428.6	442.4	453.7
15°	331.7	337.1	345.7	352.0	366.5	379.0	391.3	403.3	411.4	428.3	443.2
17.5°	307.0	312.0	320.9	331.2	341.7	354.0	369.9	382.6	393.6	413.0	430.6
20°	291.5	297.6	306.7	317.3	326.5	339.9	353.6	368.2	380.1	401.9	422.6
22.5°	278.3	283.1	290.4	300.9	310.9	323.2	338.2	354.1	366.5	390.1	411.0
25°	259.7	263.6	268.3	276.9	288.3	301.8	313.5	331.0	349.1	371.1	396.4
27.5°	242.9	245.7	249.9	257.5	266.3	278.8	291.8	308.4	326.7	350.5	377.3
30°	232.7	234.5	238.6	244.9	253.6	263.5	276.6	292.4	311.2	335.3	361.9
32.5°	223.8	225.4	228.1	234.1	241.6	250.1	261.9	277.7	295.6	319.2	348.8
35°	210.4	211.6	214.0	218.8	223.0	231.2	241.1	255.6	272.3	294.9	325.5
37.5°	197.0	198.8	200.2	202.2	207.6	213.0	221.6	233.8	250.2	273.1	302.2
40°	188.2	189.6	191.9	192.7	197.0	201.9	208.9	220.1	236.6	257.5	286.0
42.5°	179.3	180.8	182.0	183.1	186.8	191.1	197.4	207.0	221.7	241.9	270.1
45°	167.2	167.4	168.7	170.6	172.4	175.5	180.0	188.2	199.6	218.6	244.2
47.5°	154.9	155.1	155.3	156.1	158.1	160.9	163.9	170.6	180.8	196.0	220.9
50°	146.6	146.3	146.6	147.3	148.6	151.0	154.4	159.2	167.5	181.7	204.6
52.5°	138.7	138.7	138.5	138.7	139.7	141.3	143.8	147.9	155.3	168.3	188.5
55°	126.7	125.8	126.0	125.2	126.9	127.2	129.0	132.5	138.9	147.9	166.8
57.5°	113.8	113.1	112.3	112.1	111.9	112.9	114.3	117.0	122.0	129.9	145.2
60°	105.6	104.7	103.6	103.3	103.3	103.9	104.6	106.5	111.2	118.2	130.8
62.5°	97.3	96.3	95.6	94.7	94.3	94.9	95.6	97.0	100.4	107.0	117.9
65°	84.4	83.1	82.2	82.1	81.7	81.2	81.5	82.9	85.6	90.9	99.5
67.5°	71.5	70.3	70.1	69.0	68.5	68.6	68.5	69.7	71.4	75.9	82.3
70°	63.0	62.1	61.7	60.8	60.4	60.1	59.7	60.8	62.4	66.2	71.8
72.5°	54.3	53.6	52.8	52.0	52.1	51.7	51.7	52.4	53.6	57.1	61.5
75°	41.9	42.1	41.2	40.3	40.2	39.8	39.8	40.3	40.9	43.6	47.0
77.5°	30.4	30.3	29.5	29.2	29.1	28.7	29.1	29.4	29.7	31.5	34.0
80°	23.2	23.2	22.3	22.3	22.1	21.6	22.1	21.8	22.5	24.3	26.1
82.5°	16.6	16.3	16.2	16.0	15.9	15.5	15.8	16.2	16.5	17.7	18.8
85°	8.1	8.1	7.9	7.8	7.9	7.8	7.9	8.1	8.2	8.8	9.7
87.5°	4.8	5.1	4.8	4.4	4.0	3.7	3.5	3.4	3.5	3.3	3.2
90°	15.6	15.8	13.6	11.4	9.2	7.0	5.3	4.0	2.9	1.7	0.5
92.5°	14.4	14.3	13.9	13.3	12.8	12.3	11.6	10.7	9.8	9.0	8.1
95°	28.9	28.9	28.7	28.5	28.3	28.1	27.5	26.5	25.5	24.5	23.5
97.5°	48.6	48.6	48.2	47.8	47.5	47.1	46.4	45.6	44.7	43.8	42.9
100°	62.3	62.3	62.0	61.7	61.5	61.2	60.6	59.8	58.9	58.1	57.4
102.5°	77.2	77.2	76.8	76.4	76.0	75.7	75.1	74.5	73.8	73.2	72.6
105°	99.6	99.4	99.2	98.9	98.8	98.5	98.3	98.0	97.8	97.4	97.1
107.5°	124.0	123.9	123.9	123.9	123.9	123.9	123.7	123.2	122.8	122.3	121.9
110°	140.5	140.5	140.5	140.5	140.5	140.5	140.2	139.6	138.9	138.4	137.8



TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	157.2	157.5	157.6	157.6	157.7	157.8	157.6	156.9	156.3	155.7	155.1
115°	182.4	182.5	182.7	182.9	183.1	183.3	183.1	182.5	181.9	181.3	180.7
117.5°	207.0	207.2	207.8	208.3	209.0	209.5	209.4	208.6	207.8	207.0	206.2
120°	223.2	223.2	223.9	224.7	225.5	226.4	226.4	225.5	224.7	223.9	223.2
122.5°	240.3	240.5	241.1	241.6	242.2	242.7	242.6	241.6	240.7	239.6	238.7
125°	265.3	265.6	265.9	266.3	266.5	266.8	266.5	265.6	264.7	263.8	262.9
127.5°	289.6	290.0	290.4	290.7	291.1	291.4	291.0	289.9	288.8	287.6	286.5
130°	306.1	306.3	306.5	306.7	306.9	307.0	306.5	305.2	303.9	302.6	301.3
132.5°	322.5	322.9	322.9	322.8	322.8	322.7	322.2	321.2	320.0	319.0	317.9
135°	345.9	346.0	345.9	345.6	345.4	345.2	344.6	343.5	342.4	341.3	340.2
137.5°	368.7	368.8	368.5	368.3	368.0	367.7	367.2	366.3	365.4	364.5	363.5
140°	384.0	384.0	383.5	382.9	382.5	382.0	381.3	380.3	379.5	378.6	377.6
142.5°	397.8	397.7	397.4	397.0	396.7	396.3	395.7	394.8	394.0	393.0	392.1
145°	418.8	418.7	418.2	417.6	416.9	416.4	415.7	415.0	414.3	413.6	412.9
147.5°	437.2	437.0	436.6	436.2	435.8	435.4	434.7	434.0	433.1	432.2	431.4
150°	448.9	448.6	448.1	447.7	447.3	446.9	446.5	445.8	445.3	444.7	444.1
152.5°	460.5	460.2	459.6	459.1	458.7	458.2	457.6	457.1	456.5	455.9	455.3
155°	475.3	474.8	474.4	474.2	473.9	473.6	473.2	472.9	472.7	472.4	472.1
157.5°	488.9	488.1	488.0	487.8	487.6	487.4	487.3	487.0	486.8	486.6	486.4
160°	497.1	496.5	496.4	496.2	496.1	496.1	495.9	495.7	495.5	495.3	495.1
162.5°	504.4	503.7	503.6	503.5	503.4	503.3	503.2	503.2	503.1	503.1	503.0
165°	513.9	513.2	513.2	513.2	513.2	513.2	513.3	513.3	513.4	513.5	513.7
167.5°	521.7	521.0	521.0	521.1	521.1	521.1	521.3	521.6	521.9	522.2	522.4
170°	526.1	525.4	525.5	525.5	525.7	525.8	526.0	526.2	526.6	526.9	527.2
172.5°	529.3	528.6	528.7	528.9	528.9	529.0	529.3	529.5	529.8	530.1	530.4
175°	532.8	532.1	532.3	532.6	532.7	533.0	533.2	533.5	533.8	534.1	534.4
177.5°	534.7	534.2	534.4	534.6	534.7	534.9	535.0	535.3	535.5	535.8	536.1
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	470.7	471.4	473.7	476.0	478.6	479.3	480.5	479.5	479.2	481.9	483.9
5°	472.1	475.2	481.6	487.4	492.2	495.6	499.2	500.7	503.4	507.1	511.8
7.5°	470.5	476.8	486.7	495.1	504.2	510.8	515.9	520.4	525.7	532.8	540.7
10°	468.8	477.2	489.3	499.6	510.7	519.2	526.2	533.1	541.0	550.9	561.1
12.5°	465.6	475.6	490.8	502.9	517.2	525.5	535.0	549.7	558.3	572.0	586.5
15°	459.2	470.4	491.5	506.4	522.6	538.4	555.9	569.9	583.9	592.1	612.4
17.5°	449.8	466.1	489.5	506.9	527.5	552.4	572.0	588.0	604.1	617.3	627.5
20°	442.1	459.9	486.6	507.5	532.0	558.7	581.2	597.5	611.5	622.5	628.8
22.5°	432.5	455.0	480.9	505.3	536.5	563.1	586.7	599.4	611.2	616.6	619.0
25°	417.3	444.3	473.6	503.5	538.8	566.9	588.4	596.2	599.6	594.4	585.7
27.5°	400.9	431.0	465.3	500.1	537.4	564.4	579.9	578.7	572.9	556.0	542.5
30°	388.7	421.8	458.7	496.7	534.1	560.4	569.3	560.4	547.2	528.4	509.1
32.5°	375.9	410.2	451.6	491.8	528.1	551.2	553.1	537.7	517.3	495.8	471.8
35°	356.5	393.6	438.4	480.9	515.2	529.8	521.2	493.8	469.7	440.4	407.6
37.5°	334.5	375.5	420.4	464.9	496.0	499.8	478.3	449.6	415.5	381.0	342.5
40°	318.1	361.6	407.8	452.6	480.1	476.2	448.8	417.2	376.7	334.5	298.7
42.5°	303.5	346.8	394.0	437.9	459.9	449.1	417.2	378.3	334.8	295.1	262.3
45°	278.1	322.7	370.9	413.4	426.0	406.3	364.1	320.8	278.1	244.9	219.0
47.5°	253.3	297.5	345.2	382.5	387.0	360.6	314.4	270.0	233.1	206.2	187.9
50°	235.2	279.5	326.8	360.1	358.6	326.8	279.3	237.0	206.2	184.4	172.2
52.5°	219.0	260.8	306.2	336.5	328.8	294.1	248.7	211.2	185.9	168.9	157.8
55°	193.6	232.3	275.5	299.8	285.7	247.2	208.9	178.7	159.9	147.2	138.6
57.5°	168.5	204.8	241.8	256.7	241.2	205.7	173.7	151.8	137.7	128.3	122.6
60°	153.0	184.7	217.5	230.5	212.0	180.3	155.1	135.5	124.1	116.5	111.4
62.5°	137.4	165.8	196.9	203.9	187.0	160.2	137.8	121.5	112.3	105.4	100.6
65°	116.2	139.5	163.0	167.7	152.1	131.3	113.8	103.1	94.8	89.8	86.0
67.5°	95.4	114.0	130.7	134.4	120.7	106.4	93.6	84.4	78.8	74.6	71.4
70°	82.9	97.8	111.4	114.5	103.5	90.7	81.0	73.6	68.5	65.0	61.9
72.5°	69.9	82.1	93.6	95.6	86.7	76.8	68.9	63.1	58.6	56.3	53.4
75°	53.5	60.7	69.5	70.0	64.1	58.1	52.0	48.2	45.9	43.0	41.6
77.5°	37.7	43.3	48.4	49.4	45.9	41.8	38.4	35.4	33.4	32.1	30.7
80°	28.8	33.3	35.5	36.7	34.2	31.3	29.3	27.3	26.1	25.2	24.3
82.5°	20.6	23.4	25.3	26.4	25.0	23.2	21.3	20.1	19.2	18.5	18.1
85°	10.5	11.7	13.0	13.3	13.0	12.2	11.2	11.2	10.6	10.5	10.5
87.5°	4.0	4.8	5.0	5.6	5.7	6.2	6.6	6.9	7.2	7.0	6.8
90°	1.7	2.9	4.0	5.3	7.0	9.2	11.4	13.6	15.8	15.6	15.4
92.5°	9.0	9.8	10.7	11.6	12.3	12.8	13.3	13.9	14.3	14.4	14.4
95°	24.5	25.5	26.5	27.5	28.1	28.3	28.5	28.7	28.9	28.9	28.9
97.5°	43.8	44.7	45.6	46.4	47.1	47.5	47.8	48.2	48.6	48.6	48.6
100°	58.1	58.9	59.8	60.6	61.2	61.5	61.7	62.0	62.3	62.3	62.3
102.5°	73.2	73.8	74.5	75.1	75.7	76.0	76.4	76.8	77.2	77.2	77.3
105°	97.4	97.8	98.0	98.3	98.5	98.8	98.9	99.2	99.4	99.6	99.8
107.5°	122.3	122.8	123.2	123.7	123.9	123.9	123.9	123.9	123.9	124.0	124.1
110°	138.4	138.9	139.6	140.2	140.5	140.5	140.5	140.5	140.5	140.5	140.5





TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	155.7	156.3	156.9	157.6	157.8	157.7	157.6	157.6	157.5	157.2	157.0
115°	181.3	181.9	182.5	183.1	183.3	183.1	182.9	182.7	182.5	182.4	182.3
117.5°	207.0	207.8	208.6	209.4	209.5	209.0	208.3	207.8	207.2	207.0	206.8
120°	223.9	224.7	225.5	226.4	226.4	225.5	224.7	223.9	223.2	223.2	223.2
122.5°	239.6	240.7	241.6	242.6	242.7	242.2	241.6	241.1	240.5	240.3	240.0
125°	263.8	264.7	265.6	266.5	266.8	266.5	266.3	265.9	265.6	265.3	265.0
127.5°	287.6	288.8	289.9	291.0	291.4	291.1	290.7	290.4	290.0	289.6	289.3
130°	302.6	303.9	305.2	306.5	307.0	306.9	306.7	306.5	306.3	306.1	305.9
132.5°	319.0	320.0	321.2	322.2	322.7	322.8	322.8	322.9	322.9	322.5	322.0
135°	341.3	342.4	343.5	344.6	345.2	345.4	345.6	345.9	346.0	345.9	345.9
137.5°	364.5	365.4	366.3	367.2	367.7	368.0	368.3	368.5	368.8	368.7	368.6
140°	378.6	379.5	380.3	381.3	382.0	382.5	382.9	383.5	384.0	384.0	384.0
142.5°	393.0	394.0	394.8	395.7	396.3	396.7	397.0	397.4	397.7	397.8	397.8
145°	413.6	414.3	415.0	415.7	416.4	416.9	417.6	418.2	418.7	418.8	419.0
147.5°	432.2	433.1	434.0	434.7	435.4	435.8	436.2	436.6	437.0	437.2	437.4
150°	444.7	445.3	445.8	446.5	446.9	447.3	447.7	448.1	448.6	448.9	449.2
152.5°	455.9	456.5	457.1	457.6	458.2	458.7	459.1	459.6	460.2	460.5	460.9
155°	472.4	472.7	472.9	473.2	473.6	473.9	474.2	474.4	474.8	475.3	475.8
157.5°	486.6	486.8	487.0	487.3	487.4	487.6	487.8	488.0	488.1	488.9	489.5
160°	495.3	495.5	495.7	495.9	496.1	496.1	496.2	496.4	496.5	497.1	497.6
162.5°	503.1	503.1	503.2	503.2	503.3	503.4	503.5	503.6	503.7	504.4	505.0
165°	513.5	513.4	513.3	513.3	513.2	513.2	513.2	513.2	513.2	513.9	514.6
167.5°	522.2	521.9	521.6	521.3	521.1	521.1	521.1	521.0	521.0	521.7	522.4
170°	526.9	526.6	526.2	526.0	525.8	525.7	525.5	525.5	525.4	526.1	526.8
172.5°	530.1	529.8	529.5	529.3	529.0	528.9	528.9	528.7	528.6	529.3	530.0
175°	534.1	533.8	533.5	533.2	533.0	532.7	532.6	532.3	532.1	532.8	533.5
177.5°	535.8	535.5	535.3	535.0	534.9	534.7	534.6	534.4	534.2	534.7	535.2
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	485.7	487.7	487.7	488.0	490.3	490.0	489.8
5°	516.8	519.9	520.2	523.5	525.6	524.9	522.9
7.5°	546.2	551.9	556.3	558.6	561.5	563.2	562.4
10°	569.6	577.8	582.9	586.3	590.4	593.5	592.4
12.5°	590.7	600.6	607.5	613.4	613.9	617.8	615.1
15°	623.8	634.1	635.3	639.5	643.0	642.6	642.8
17.5°	634.6	637.9	638.7	638.7	638.8	637.5	634.8
20°	630.7	629.5	626.5	624.1	620.0	619.4	615.8
22.5°	612.3	608.3	600.6	595.6	589.1	587.5	586.5
25°	576.1	567.2	555.0	543.3	540.0	533.8	535.5
27.5°	526.2	512.5	499.2	489.8	481.2	471.7	474.4
30°	491.3	475.8	457.1	442.7	433.5	424.5	422.9
32.5°	449.6	426.8	406.0	393.3	379.2	373.5	367.3
35°	377.6	355.4	334.7	316.9	306.7	298.7	291.5
37.5°	312.8	287.3	270.6	256.2	248.7	244.2	245.4
40°	272.7	250.3	238.1	227.1	220.2	217.1	217.8
42.5°	240.1	223.4	213.3	205.8	201.0	199.2	198.8
45°	203.2	193.8	185.5	181.3	178.9	176.9	175.6
47.5°	178.0	170.3	165.6	163.1	161.1	159.1	159.0
50°	162.9	157.8	154.6	151.9	150.3	148.9	150.1
52.5°	151.3	146.7	143.5	141.1	140.5	139.2	139.1
55°	134.3	130.6	128.3	126.1	125.1	124.4	123.4
57.5°	118.7	115.3	113.1	111.8	109.7	109.0	108.7
60°	107.6	104.9	102.7	100.9	100.1	98.6	98.6
62.5°	97.4	94.7	92.7	91.3	89.8	89.3	89.4
65°	82.6	80.4	78.4	77.0	76.7	75.6	76.0
67.5°	69.0	67.6	65.4	64.6	64.0	63.5	63.0
70°	59.9	58.5	57.4	56.3	55.8	55.8	55.8
72.5°	52.3	50.5	49.9	48.6	48.9	48.3	47.7
75°	40.5	39.4	38.9	38.3	37.5	37.5	37.5
77.5°	29.8	29.5	28.8	28.3	28.0	27.9	28.0
80°	23.1	22.8	22.5	22.5	22.1	21.9	21.6
82.5°	17.7	17.3	17.0	16.9	16.8	16.8	16.7
85°	10.1	9.7	9.7	9.9	9.5	9.5	9.7
87.5°	6.9	6.9	6.7	6.7	6.9	6.8	6.8
90°	15.2	15.0	15.0	15.1	15.1	15.3	15.4
92.5°	14.5	14.5	14.6	14.6	14.6	14.7	14.7
95°	28.9	28.9	28.8	28.6	28.4	28.2	28.0
97.5°	48.6	48.6	48.6	48.6	48.6	48.6	48.5
100°	62.3	62.3	62.3	62.2	62.1	62.0	61.9
102.5°	77.4	77.5	77.5	77.4	77.2	77.2	77.1
105°	100.0	100.2	100.3	100.3	100.3	100.3	100.3
107.5°	124.1	124.2	124.0	123.5	123.1	122.6	122.2
110°	140.5	140.5	140.4	140.1	139.7	139.4	139.1



TEST NUMBER: P331250-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	156.8	156.5	156.3	156.1	155.8	155.6	155.4
115°	182.2	182.1	181.9	181.6	181.3	181.0	180.7
117.5°	206.5	206.3	206.0	205.7	205.4	205.1	204.8
120°	223.2	223.2	223.0	222.7	222.4	222.1	221.8
122.5°	239.8	239.6	239.3	239.1	238.8	238.7	238.4
125°	264.7	264.4	264.2	264.1	264.0	263.9	263.8
127.5°	288.9	288.6	288.2	287.9	287.6	287.2	286.9
130°	305.7	305.5	305.1	304.8	304.4	304.0	303.6
132.5°	321.5	321.2	320.8	320.4	320.1	319.8	319.5
135°	345.7	345.6	345.4	345.2	344.8	344.5	344.2
137.5°	368.5	368.4	368.2	367.8	367.4	367.0	366.6
140°	384.0	384.0	383.8	383.3	382.9	382.5	382.1
142.5°	397.9	398.0	397.8	397.4	397.0	396.6	396.2
145°	419.1	419.1	419.0	418.6	418.2	417.8	417.4
147.5°	437.7	437.9	437.8	437.4	437.0	436.7	436.3
150°	449.5	449.8	449.8	449.5	449.2	448.9	448.6
152.5°	461.3	461.7	461.7	461.3	460.9	460.5	460.2
155°	476.3	476.8	476.9	476.6	476.3	475.9	475.7
157.5°	490.2	490.9	491.0	490.5	490.0	489.6	489.0
160°	498.3	498.8	499.0	498.6	498.2	497.7	497.3
162.5°	505.7	506.4	506.5	506.0	505.6	505.1	504.6
165°	515.3	515.9	516.1	515.6	515.1	514.6	514.0
167.5°	523.2	523.9	523.9	523.4	522.9	522.4	521.8
170°	527.5	528.1	528.2	527.6	527.0	526.4	525.9
172.5°	530.8	531.4	531.5	530.9	530.3	529.7	529.1
175°	534.2	535.0	535.0	534.4	533.8	533.2	532.6
177.5°	535.7	536.1	536.1	535.7	535.2	534.7	534.2
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3

(END OF REPORT)