

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333519

Luminaire Tested: **S125RDIP-S375D1205U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333519
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D1205U835-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5770.8 lumens
Efficiency: N/A
Efficacy: 136.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333519

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333519

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25
1	92	88	84	81	82	79	76	73	61	59	57	45	43	42	29	29	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	26	21	19	18	13
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	19	17	15	12
6	59	48	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14	10
7	55	43	35	30	48	39	32	27	30	26	22	23	19	17	15	14	12	9
8	50	39	31	26	45	35	28	24	28	23	20	21	17	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3952	3952	3952
5°	3961	3916	3940
10°	3931	3880	3880
15°	3884	3801	3770
20°	3824	3691	3647
25°	3755	3583	3504
30°	3667	3457	3347
35°	3578	3327	3170
40°	3495	3191	2996
45°	3394	3040	2807
50°	3293	2875	2609
55°	3174	2716	2399
60°	3056	2525	2173
65°	2917	2303	1913
70°	2757	2024	1648
75°	2538	1707	1372
80°	2235	1339	1153
85°	1882	1097	1030



TEST NUMBER: P333519

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	1.0
10°-20°	160.8	2.8
20°-30°	233.2	4.0
30°-40°	265.7	4.6
40°-50°	259.0	4.5
50°-60°	218.0	3.8
60°-70°	152.8	2.6
70°-80°	78.6	1.4
80°-90°	23.1	0.4
90°-100°	417.8	7.2
100°-110°	898.0	15.6
110°-120°	842.8	14.6
120°-130°	683.0	11.8
130°-140°	548.1	9.5
140°-150°	413.6	7.2
150°-160°	291.2	5.0
160°-170°	171.6	3.0
170°-180°	55.8	1.0
0°-30°	451.5	7.8
0°-40°	717.3	12.4
0°-60°	1194.3	20.7
0°-90°	1448.8	25.1
90°-120°	2158.6	37.4
90°-150°	3803.4	65.9
90°-180°	4322.0	74.9
0°-180°	5770.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	612	612	612	612	612	
5°	611	609	604	608	608	58
15°	581	578	568	568	564	164
25°	527	519	503	497	492	242
35°	454	442	422	409	402	284
45°	372	358	333	315	307	287
55°	282	267	241	221	213	252
65°	191	175	151	133	125	189
75°	102	88	68	59	55	108
85°	25	17	15	14	14	29
90°	1	10	19	24	27	3
95°	38	113	1030	467	273	41
105°	131	184	842	1659	1540	138
115°	235	283	676	1458	1715	231
125°	325	381	648	1160	1351	289
135°	381	458	644	972	1122	296
145°	444	508	646	805	885	278
155°	507	545	630	712	742	233
165°	553	568	604	641	651	156
175°	575	575	580	587	584	55
180°	576	576	576	576	576	



TEST NUMBER: P333519

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9
2.5°	613.0	612.8	612.5	612.3	612.0	611.5	610.7	609.8	609.0	608.2	609.0
5°	611.0	610.6	610.2	609.7	609.3	608.6	607.4	606.3	605.2	604.0	605.1
7.5°	605.0	604.6	604.2	603.8	603.4	602.5	601.2	599.8	598.5	597.1	597.8
10°	599.4	599.1	598.8	598.5	598.2	597.3	595.9	594.4	593.0	591.6	591.9
12.5°	593.1	592.7	592.4	592.0	591.6	590.4	588.5	586.6	584.6	582.7	582.9
15°	580.9	580.3	579.7	579.1	578.5	577.1	574.9	572.8	570.6	568.5	568.4
17.5°	567.2	566.2	565.3	564.3	563.4	561.6	558.8	556.1	553.4	550.7	550.2
20°	556.4	555.4	554.4	553.4	552.3	550.2	546.9	543.6	540.3	537.0	536.5
22.5°	544.6	543.6	542.6	541.5	540.5	538.3	534.8	531.4	527.9	524.5	523.5
25°	526.9	525.3	523.8	522.2	520.7	518.0	514.2	510.4	506.6	502.8	501.5
27.5°	506.5	504.7	502.8	500.9	499.0	496.1	492.0	487.9	483.9	479.8	477.9
30°	491.7	489.8	487.8	485.9	483.9	480.8	476.5	472.2	467.9	463.5	461.2
32.5°	477.3	475.0	472.8	470.5	468.2	464.9	460.5	456.1	451.7	447.3	444.7
35°	453.8	451.4	448.9	446.4	444.0	440.4	435.8	431.2	426.6	422.0	419.0
37.5°	430.8	427.8	424.8	421.8	418.8	414.9	410.2	405.4	400.7	395.9	392.3
40°	414.6	411.5	408.4	405.3	402.2	398.2	393.3	388.4	383.4	378.5	374.6
42.5°	397.5	394.4	391.2	388.1	384.9	380.8	375.7	370.6	365.5	360.4	356.7
45°	371.6	368.6	365.6	362.6	359.7	355.3	349.7	344.1	338.4	332.8	328.6
47.5°	344.7	341.5	338.4	335.2	332.1	327.7	322.0	316.3	310.6	304.9	300.7
50°	327.7	324.3	320.9	317.5	314.1	309.5	303.6	297.8	291.9	286.1	281.8
52.5°	309.2	305.7	302.2	298.8	295.3	290.8	285.3	279.7	274.2	268.7	264.1
55°	281.9	278.6	275.3	272.1	268.8	264.3	258.5	252.7	247.0	241.2	236.6
57.5°	254.4	250.9	247.3	243.8	240.3	235.8	230.2	224.7	219.2	213.6	209.1
60°	236.6	233.0	229.4	225.8	222.2	217.7	212.1	206.6	201.0	195.5	191.0
62.5°	217.8	214.3	210.9	207.5	204.0	199.5	193.9	188.3	182.6	177.0	172.8
65°	190.9	187.4	183.9	180.4	176.9	172.4	167.0	161.6	156.1	150.7	146.6
67.5°	164.2	160.7	157.2	153.7	150.2	145.8	140.6	135.4	130.2	125.0	121.2
70°	146.0	142.6	139.1	135.6	132.1	127.8	122.6	117.5	112.4	107.2	104.0
72.5°	128.3	124.9	121.5	118.1	114.7	110.5	105.7	100.9	96.1	91.3	88.4
75°	101.7	98.6	95.5	92.4	89.4	85.7	81.3	77.0	72.7	68.4	66.1
77.5°	75.2	72.8	70.3	67.8	65.4	62.4	59.0	55.5	52.1	48.6	47.0
80°	60.1	57.6	55.2	52.7	50.2	47.6	44.7	41.8	38.9	36.0	35.1
82.5°	45.3	43.1	40.9	38.6	36.4	34.3	32.4	30.4	28.4	26.4	26.0
85°	25.4	23.6	21.7	19.9	18.0	16.8	16.3	15.8	15.3	14.8	14.7
87.5°	8.7	8.4	8.3	8.2	8.1	8.2	8.3	8.7	8.9	9.3	9.5
90°	1.2	2.3	4.6	7.0	9.3	11.6	12.8	15.1	16.3	18.6	19.8
92.5°	14.2	17.2	27.0	41.4	61.4	95.3	158.7	265.2	380.7	374.6	303.3
95°	38.3	39.5	48.8	61.6	87.1	139.4	263.8	519.4	840.1	1029.5	1007.4
97.5°	63.7	65.1	71.6	84.4	107.4	145.0	227.3	414.6	750.2	1099.4	1274.7
100°	81.3	83.7	88.3	101.1	123.2	158.0	225.4	376.5	669.3	1049.2	1339.7
102.5°	100.9	102.3	106.0	119.7	139.9	173.8	233.8	360.7	607.9	960.9	1300.7
105°	131.3	131.3	137.1	148.7	167.3	199.9	251.0	354.4	548.4	842.4	1175.9
107.5°	161.0	163.4	168.9	178.5	197.8	227.0	276.5	365.1	523.3	760.8	1048.6
110°	182.4	184.8	189.4	199.9	217.3	247.5	295.1	375.3	515.9	722.7	976.0



TEST NUMBER: P333519

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	203.8	206.1	209.8	220.3	237.7	267.0	312.8	388.3	515.9	700.4	922.1
115°	234.7	237.0	240.5	251.0	268.4	297.5	340.5	407.8	519.4	676.3	863.3
117.5°	262.6	266.1	269.8	280.3	300.0	328.1	368.8	430.2	527.1	664.4	828.2
120°	281.2	284.7	289.3	299.8	319.5	348.6	389.3	445.0	534.5	658.8	808.7
122.5°	300.7	303.3	307.0	317.4	339.1	368.1	408.8	461.8	541.0	654.2	792.0
125°	325.3	327.7	333.5	343.9	366.0	396.2	434.6	484.5	551.9	648.4	769.2
127.5°	344.6	348.1	355.6	368.8	392.3	422.5	459.4	505.5	564.2	645.6	748.3
130°	356.7	360.2	369.5	384.6	409.0	439.2	475.2	519.4	571.7	643.7	734.4
132.5°	366.0	370.4	381.6	398.6	423.9	454.1	490.1	531.5	580.0	643.7	723.2
135°	381.1	385.8	399.7	418.3	442.7	474.1	510.1	548.4	591.4	643.7	710.0
137.5°	400.2	403.7	416.7	435.3	459.2	491.5	524.3	561.0	601.9	645.1	698.1
140°	411.3	414.8	428.8	447.4	469.4	500.8	534.5	569.4	606.5	646.0	692.5
142.5°	424.3	426.9	439.9	458.5	479.7	509.2	541.0	574.0	609.3	647.0	687.9
145°	443.9	446.2	457.8	474.1	495.0	521.7	551.9	581.0	612.4	646.0	680.9
147.5°	464.3	465.7	475.7	490.8	508.9	532.4	558.9	585.2	613.5	643.0	673.7
150°	476.4	478.7	486.9	502.0	518.2	538.0	563.5	588.0	613.5	640.2	668.1
152.5°	489.4	490.8	498.0	511.3	526.6	544.5	568.2	589.8	612.6	636.5	661.6
155°	506.6	506.6	513.6	525.2	536.8	553.1	572.8	591.4	610.0	629.8	650.7
157.5°	522.0	521.7	527.3	537.3	547.5	559.8	576.8	592.6	607.0	622.8	640.5
160°	532.2	531.0	535.7	543.8	553.1	563.5	578.7	592.6	604.2	618.2	632.1
162.5°	540.5	539.4	544.0	551.2	558.7	567.3	580.5	591.7	601.4	612.6	624.7
165°	553.1	550.8	554.3	560.1	564.7	571.7	581.0	590.3	597.2	604.2	613.5
167.5°	561.5	560.3	562.4	565.6	568.9	573.3	581.0	587.5	590.7	596.1	602.6
170°	567.0	565.9	567.0	569.4	571.7	575.2	581.0	585.6	588.0	591.4	596.1
172.5°	570.8	568.7	569.8	572.1	573.5	575.2	580.0	583.8	584.2	585.9	589.6
175°	575.2	572.8	574.0	575.2	575.2	575.2	578.7	581.0	579.8	579.8	581.0
177.5°	577.3	575.4	575.4	576.3	575.4	575.4	577.3	578.2	576.3	576.3	577.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333519

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9
2.5°	609.8	610.7	611.5	611.9	611.8	611.7	611.6	611.5
5°	606.1	607.1	608.1	608.6	608.4	608.1	607.9	607.7
7.5°	598.5	599.3	600.0	600.2	600.0	599.8	599.6	599.3
10°	592.2	592.5	592.8	592.8	592.5	592.2	591.9	591.6
12.5°	583.1	583.4	583.6	583.5	583.0	582.5	582.1	581.6
15°	568.2	568.1	568.0	567.5	566.6	565.7	564.8	563.8
17.5°	549.7	549.2	548.7	548.0	547.3	546.5	545.7	545.0
20°	536.0	535.5	535.0	534.3	533.3	532.4	531.5	530.6
22.5°	522.4	521.4	520.4	519.5	518.8	518.0	517.3	516.5
25°	500.2	498.8	497.5	496.3	495.1	494.0	492.9	491.7
27.5°	476.1	474.2	472.3	470.9	469.8	468.7	467.6	466.5
30°	458.8	456.5	454.1	452.5	451.5	450.6	449.7	448.8
32.5°	442.1	439.5	436.8	435.0	433.8	432.6	431.4	430.3
35°	416.0	413.0	410.0	407.8	406.4	405.0	403.5	402.1
37.5°	388.7	385.2	381.6	379.1	377.7	376.3	374.9	373.5
40°	370.7	366.8	362.9	360.3	359.1	357.9	356.6	355.4
42.5°	352.9	349.2	345.4	342.7	340.9	339.0	337.2	335.4
45°	324.5	320.4	316.3	313.5	312.0	310.4	308.9	307.3
47.5°	296.5	292.2	288.0	285.0	283.3	281.6	279.9	278.2
50°	277.4	273.1	268.8	265.9	264.4	262.8	261.3	259.7
52.5°	259.4	254.8	250.1	247.0	245.5	244.0	242.4	240.9
55°	232.0	227.4	222.8	219.6	218.0	216.3	214.7	213.1
57.5°	204.6	200.1	195.5	192.5	191.1	189.6	188.2	186.7
60°	186.5	181.9	177.4	174.4	172.8	171.3	169.8	168.2
62.5°	168.6	164.4	160.2	157.4	155.8	154.3	152.8	151.2
65°	142.4	138.3	134.2	131.4	129.9	128.3	126.8	125.2
67.5°	117.4	113.7	109.9	107.4	106.2	105.0	103.7	102.5
70°	100.9	97.7	94.5	92.3	91.0	89.8	88.6	87.3
72.5°	85.4	82.5	79.6	77.7	76.9	76.1	75.2	74.4
75°	63.9	61.6	59.4	57.9	57.2	56.4	55.7	55.0
77.5°	45.5	43.9	42.3	41.2	40.7	40.2	39.6	39.1
80°	34.2	33.3	32.4	31.8	31.6	31.4	31.2	31.0
82.5°	25.6	25.1	24.7	24.4	24.3	24.2	24.1	23.9
85°	14.6	14.5	14.4	14.3	14.2	14.1	14.0	13.9
87.5°	9.7	10.0	10.2	10.6	10.5	10.5	10.6	10.5
90°	20.9	22.1	23.2	25.6	25.6	25.6	26.7	26.7
92.5°	205.9	149.4	112.5	95.3	80.4	77.6	76.0	74.1
95°	835.4	658.8	515.9	418.3	335.8	300.9	291.7	273.1
97.5°	1244.2	1120.4	981.2	845.4	773.6	708.6	674.9	660.0
100°	1429.2	1372.3	1252.6	1131.7	1051.6	967.9	924.9	906.3
102.5°	1491.5	1526.6	1469.2	1387.4	1301.6	1242.1	1195.4	1181.5
105°	1454.8	1614.0	1665.1	1652.3	1615.1	1576.8	1553.5	1539.6
107.5°	1323.7	1536.1	1667.4	1728.1	1746.9	1746.7	1739.0	1729.7
110°	1227.0	1447.8	1611.6	1710.4	1762.7	1784.8	1792.9	1792.9



TEST NUMBER: P333519

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1150.8	1360.4	1526.1	1642.5	1719.0	1756.9	1777.1	1785.5
115°	1055.1	1235.2	1394.3	1521.0	1611.6	1667.4	1699.9	1715.0
117.5°	993.2	1148.5	1285.6	1401.8	1492.4	1550.1	1582.4	1591.6
120°	959.8	1099.2	1227.0	1329.3	1415.3	1471.0	1502.4	1511.7
122.5°	934.7	1063.9	1177.8	1273.5	1350.2	1401.3	1432.7	1441.1
125°	898.2	1016.7	1117.8	1201.5	1266.5	1314.2	1339.7	1351.4
127.5°	861.0	971.6	1066.0	1144.3	1203.3	1245.4	1269.6	1274.7
130°	837.8	940.0	1030.7	1106.2	1164.3	1202.6	1225.9	1232.8
132.5°	814.5	910.3	992.5	1065.3	1123.4	1161.7	1183.1	1191.0
135°	784.3	864.5	938.9	1005.1	1056.2	1094.6	1115.5	1122.5
137.5°	758.8	823.6	885.4	941.7	987.4	1022.3	1041.6	1049.2
140°	744.8	799.4	852.9	901.7	944.7	974.9	992.3	998.1
142.5°	732.7	779.0	825.0	867.3	903.8	929.3	945.8	950.7
145°	716.9	752.9	789.0	820.3	848.2	868.0	880.8	885.4
147.5°	702.1	731.3	759.0	782.7	804.8	820.6	828.0	830.1
150°	693.7	719.3	741.3	762.2	779.7	793.6	798.3	799.4
152.5°	684.4	707.2	727.4	743.7	758.3	769.4	774.1	775.3
155°	670.4	689.0	705.3	718.1	729.7	737.8	741.3	742.5
157.5°	656.5	671.8	684.4	694.4	703.4	710.2	713.4	713.2
160°	647.2	658.8	670.4	678.6	686.7	692.5	694.9	693.7
162.5°	637.0	647.7	657.4	664.6	670.9	675.8	676.3	676.0
165°	622.8	630.9	637.9	643.7	648.4	650.7	650.7	650.7
167.5°	609.3	614.7	620.0	624.2	626.5	628.6	627.7	627.5
170°	601.9	605.4	608.9	611.2	613.5	614.7	614.7	613.5
172.5°	593.5	597.0	599.6	601.0	601.4	603.5	601.7	600.5
175°	584.5	584.5	586.8	586.8	586.8	588.0	585.6	584.5
177.5°	578.2	579.1	579.1	579.1	578.2	579.1	576.3	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3

(END OF REPORT)