

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331266-927

Luminaire Tested: **SA2XXDIP-C290D725U927-4F0-1E-UDD-F4**


Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331266-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C290D725U927-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3195.8 lumens  
Efficiency: N/A  
Efficacy: 102.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331266-927  
CATALOG NUMBER: SA2XXDIP-C290D725U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331266-927

CATALOG NUMBER: SA2XXDIP-C290D725U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	93	89	85	82	84	80	77	74	63	61	59	48	46	45	33	32	32	25
2	85	78	72	67	76	70	65	61	55	52	49	42	39	37	29	28	27	21
3	77	68	61	56	69	61	55	51	49	44	41	37	34	32	26	24	23	18
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	40	58	48	42	37	39	34	30	29	26	23	21	19	17	13
6	60	48	40	34	53	43	37	32	35	30	26	26	23	20	19	17	15	12
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13	10
8	51	39	32	26	46	35	29	24	28	24	20	22	18	16	16	14	12	9
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11	8
10	44	32	25	21	40	29	23	19	24	19	16	19	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6042	6042	6042
5°	6065	5977	6015
10°	6030	5917	5946
15°	5954	5840	5835
20°	5849	5727	5720
25°	5744	5585	5585
30°	5610	5455	5407
35°	5483	5298	5219
40°	5324	5143	5044
45°	5167	4987	4864
50°	4999	4828	4657
55°	4822	4642	4467
60°	4624	4414	4253
65°	4413	4195	4000
70°	4145	3923	3734
75°	3768	3612	3525
80°	3347	3245	3078
85°	2723	2594	2334



TEST NUMBER: P331266-927

CATALOG NUMBER: SA2XXDIP-C290D725U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	35.2	1.1
10°-20°	99.0	3.1
20°-30°	145.6	4.6
30°-40°	169.1	5.3
40°-50°	168.9	5.3
50°-60°	147.3	4.6
60°-70°	108.9	3.4
70°-80°	61.7	1.9
80°-90°	19.5	0.6
90°-100°	128.7	4.0
100°-110°	436.9	13.7
110°-120°	464.2	14.5
120°-130°	382.1	12.0
130°-140°	306.8	9.6
140°-150°	231.9	7.3
150°-160°	163.0	5.1
160°-170°	95.9	3.0
170°-180°	31.2	1.0
0°-30°	279.8	8.8
0°-40°	448.8	14.0
0°-60°	765.0	23.9
0°-90°	955.1	29.9
90°-120°	1029.8	32.2
90°-150°	1950.7	61.0
90°-180°	2241.0	70.1
0°-180°	3195.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	374	374	374	374	374	
5°	374	373	369	372	371	35
15°	356	354	349	351	349	100
25°	322	319	314	314	314	148
35°	278	274	269	267	265	174
45°	226	224	218	215	213	175
55°	171	169	165	161	159	153
65°	116	113	110	107	105	114
75°	60	60	58	56	56	65
85°	15	14	14	13	13	17
90°	1	8	21	20	20	2
95°	22	53	243	92	71	23
105°	76	114	459	820	698	80
115°	133	168	384	792	918	132
125°	186	220	369	642	745	165
135°	218	260	365	539	617	168
145°	249	286	363	451	493	156
155°	283	306	352	398	414	130
165°	308	318	338	358	364	87
175°	321	322	324	328	328	31
180°	322	322	322	322	322	



TEST NUMBER: P331266-927

CATALOG NUMBER: SA2XXDIP-C290D725U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
2.5°	376.0	375.7	375.3	375.0	374.7	374.2	373.5	372.8	372.1	371.4	372.0
5°	374.2	373.9	373.6	373.3	373.0	372.4	371.5	370.7	369.7	368.8	369.5
7.5°	371.0	370.4	369.9	369.5	369.0	368.3	367.4	366.5	365.6	364.7	365.4
10°	367.8	367.3	366.7	366.1	365.5	364.8	363.8	362.9	361.9	360.9	361.6
12.5°	363.5	363.0	362.5	361.9	361.5	360.8	359.8	358.9	357.9	357.0	357.4
15°	356.2	355.8	355.3	354.8	354.3	353.6	352.5	351.5	350.5	349.4	349.7
17.5°	347.1	346.6	346.1	345.6	345.2	344.4	343.3	342.2	341.2	340.2	340.5
20°	340.4	339.9	339.5	339.0	338.5	337.7	336.6	335.5	334.4	333.3	333.5
22.5°	333.8	333.1	332.5	331.8	331.1	330.3	329.2	328.1	327.1	326.1	326.1
25°	322.4	321.8	321.2	320.5	319.9	318.9	317.5	316.2	314.8	313.5	313.6
27.5°	309.5	309.0	308.3	307.8	307.2	306.3	305.3	304.2	303.2	302.1	301.8
30°	300.9	300.2	299.6	299.0	298.3	297.4	296.2	295.0	293.7	292.6	292.3
32.5°	291.6	291.1	290.7	290.1	289.6	288.7	287.4	286.2	284.9	283.7	283.2
35°	278.2	277.3	276.6	275.8	275.0	273.9	272.7	271.4	270.1	268.8	268.3
37.5°	263.0	262.3	261.6	260.9	260.2	259.2	257.9	256.7	255.3	254.1	253.5
40°	252.6	252.0	251.4	250.7	250.1	249.1	247.8	246.5	245.3	244.0	243.3
42.5°	242.6	241.9	241.3	240.7	240.0	239.0	237.7	236.5	235.2	233.9	233.1
45°	226.3	225.8	225.2	224.7	224.1	223.2	222.0	220.9	219.7	218.4	217.5
47.5°	210.2	209.7	209.2	208.7	208.1	207.2	206.0	204.8	203.5	202.2	201.3
50°	199.0	198.6	198.2	197.8	197.4	196.6	195.5	194.4	193.3	192.2	191.1
52.5°	188.1	187.5	187.0	186.5	185.9	185.1	184.1	183.1	182.0	180.9	180.0
55°	171.3	170.8	170.3	169.8	169.4	168.7	167.7	166.8	165.8	164.9	163.8
57.5°	154.5	154.1	153.7	153.3	152.9	152.2	151.1	150.1	149.0	148.0	147.0
60°	143.2	142.9	142.6	142.3	142.0	141.2	140.1	139.0	137.8	136.7	135.9
62.5°	132.3	131.7	131.3	130.8	130.2	129.5	128.7	127.9	127.0	126.1	125.2
65°	115.5	115.0	114.5	114.1	113.6	113.0	112.2	111.4	110.6	109.8	109.0
67.5°	98.5	98.1	97.7	97.3	97.0	96.4	95.6	94.9	94.2	93.5	92.9
70°	87.8	87.5	87.1	86.8	86.5	86.0	85.3	84.6	83.8	83.1	82.5
72.5°	76.8	76.5	76.2	75.9	75.6	75.2	74.7	74.3	73.8	73.4	72.8
75°	60.4	60.3	60.1	60.0	59.8	59.6	59.2	58.7	58.3	57.9	57.4
77.5°	45.8	45.5	45.2	45.0	44.7	44.4	44.3	44.1	44.0	43.8	43.6
80°	36.0	35.9	35.8	35.7	35.6	35.6	35.4	35.3	35.1	34.9	34.7
82.5°	26.8	26.8	26.8	26.7	26.7	26.6	26.5	26.5	26.4	26.3	26.0
85°	14.7	14.7	14.6	14.5	14.4	14.3	14.3	14.2	14.1	14.0	13.8
87.5°	5.3	5.5	5.9	6.0	6.2	6.4	6.9	7.6	8.2	8.2	7.9
90°	0.6	2.5	5.0	6.2	7.4	9.3	12.4	16.7	20.4	21.1	20.4
92.5°	7.5	10.9	15.4	18.1	22.3	28.1	42.1	61.8	79.4	80.5	68.0
95°	21.7	24.2	30.3	35.9	45.8	60.7	89.2	143.1	214.9	242.7	212.4
97.5°	35.3	38.7	45.2	53.6	65.0	81.8	117.6	192.7	312.1	414.4	434.7
100°	47.7	49.5	55.1	65.0	77.4	94.7	127.5	203.1	336.8	489.2	578.4
102.5°	59.1	60.4	66.0	75.9	88.8	106.2	136.5	203.6	327.5	491.7	631.8
105°	75.6	78.0	82.4	91.7	105.3	122.6	151.7	206.8	309.0	458.8	623.6
107.5°	93.4	95.4	99.6	108.1	121.6	139.1	167.3	215.4	299.8	423.7	569.2
110°	105.3	107.7	111.5	119.5	132.5	150.5	177.7	222.3	297.9	406.9	535.0



TEST NUMBER: P331266-927

CATALOG NUMBER: SA2XXDIP-C290D725U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	116.1	118.7	122.9	130.4	142.9	161.4	187.7	229.7	298.3	395.9	511.3
115°	133.2	136.3	140.0	147.3	159.8	176.5	203.1	240.9	301.0	384.0	481.8
117.5°	150.8	153.2	156.9	163.5	175.4	192.7	217.4	252.8	305.4	378.1	463.2
120°	161.6	164.1	167.8	173.4	185.8	203.1	227.3	260.7	308.4	374.6	453.3
122.5°	172.1	174.0	177.7	183.8	196.1	214.0	236.7	267.7	311.9	372.6	444.9
125°	185.8	187.7	191.3	198.8	211.2	228.5	250.8	278.7	317.0	369.1	432.8
127.5°	196.7	199.2	204.4	212.5	224.4	242.2	264.0	288.9	322.4	366.9	421.7
130°	203.1	205.6	211.8	220.5	232.8	250.2	271.9	295.4	326.4	366.0	414.3
132.5°	209.1	212.1	218.7	227.9	240.7	258.1	278.8	301.8	330.3	365.5	408.4
135°	218.0	220.5	227.9	237.2	251.4	268.8	288.6	310.2	335.0	364.7	400.1
137.5°	226.4	229.3	236.8	246.7	260.9	276.9	296.5	316.7	339.2	364.6	394.2
140°	232.8	235.3	242.7	252.6	266.3	282.4	301.0	320.1	341.2	364.1	390.8
142.5°	239.2	241.3	248.2	258.1	271.2	286.4	304.4	323.1	342.7	364.1	387.3
145°	248.9	251.4	257.6	266.9	279.2	292.9	309.7	326.9	344.3	362.9	382.7
147.5°	259.4	261.2	267.1	275.7	286.0	298.1	313.9	329.1	344.8	360.7	378.0
150°	266.3	268.2	273.1	281.1	290.4	301.6	315.8	330.0	344.3	359.2	374.0
152.5°	273.2	274.1	279.0	286.1	294.9	305.1	317.8	330.6	343.3	356.7	370.6
155°	283.0	283.6	287.3	294.1	301.0	310.2	320.8	331.3	341.8	352.4	364.1
157.5°	291.2	291.8	294.8	300.7	306.2	313.9	322.9	331.3	339.0	347.9	358.1
160°	296.6	297.2	299.7	304.7	309.7	316.4	323.8	331.3	337.5	344.9	353.6
162.5°	302.1	301.7	304.2	308.2	312.6	317.9	324.4	330.8	336.0	342.5	349.6
165°	308.4	307.8	309.0	312.8	315.8	319.6	325.1	329.5	333.2	337.5	343.1
167.5°	313.6	312.8	313.9	316.3	318.5	320.9	325.0	328.6	330.3	333.2	336.6
170°	317.0	315.8	316.4	318.3	319.6	321.4	324.5	327.6	328.8	330.7	333.2
172.5°	319.0	318.3	317.9	319.8	320.5	321.9	324.0	326.1	326.9	327.7	329.7
175°	321.4	320.8	320.1	321.4	321.4	322.0	323.2	324.5	323.8	324.5	325.1
177.5°	322.5	321.5	321.0	322.0	322.0	322.0	322.5	323.5	322.5	322.0	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331266-927

CATALOG NUMBER: SA2XXDIP-C290D725U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
2.5°	372.6	373.3	373.9	374.2	374.1	373.9	373.8	373.7
5°	370.2	370.8	371.5	371.7	371.5	371.4	371.2	371.1
7.5°	366.0	366.6	367.3	367.5	367.3	367.1	366.9	366.8
10°	362.3	362.9	363.5	363.7	363.5	363.2	363.0	362.7
12.5°	357.8	358.2	358.7	358.9	358.7	358.5	358.3	358.1
15°	350.1	350.4	350.7	350.7	350.3	349.9	349.5	349.1
17.5°	340.9	341.3	341.6	341.6	341.2	340.9	340.5	340.1
20°	333.7	334.0	334.2	334.1	333.8	333.5	333.2	332.9
22.5°	326.1	326.2	326.2	326.1	326.0	325.7	325.6	325.4
25°	313.8	313.9	314.1	314.1	313.9	313.8	313.6	313.5
27.5°	301.6	301.3	301.1	300.8	300.4	300.0	299.7	299.3
30°	292.1	291.8	291.6	291.4	291.0	290.7	290.4	290.0
32.5°	282.8	282.3	281.9	281.5	281.2	280.9	280.6	280.3
35°	267.8	267.4	266.9	266.5	266.1	265.7	265.3	264.8
37.5°	252.9	252.3	251.7	251.2	250.8	250.4	250.1	249.7
40°	242.6	241.9	241.1	240.6	240.3	240.0	239.6	239.3
42.5°	232.3	231.6	230.8	230.1	229.7	229.3	228.9	228.4
45°	216.7	215.8	214.9	214.3	214.0	213.7	213.3	213.0
47.5°	200.4	199.5	198.5	197.8	197.4	196.9	196.5	196.0
50°	190.0	188.8	187.7	187.0	186.6	186.2	185.8	185.4
52.5°	179.1	178.2	177.2	176.5	175.9	175.5	174.9	174.4
55°	162.9	161.9	161.0	160.3	159.9	159.5	159.1	158.7
57.5°	146.1	145.1	144.2	143.5	143.3	143.0	142.7	142.4
60°	135.0	134.1	133.2	132.7	132.5	132.2	132.0	131.7
62.5°	124.5	123.7	122.9	122.3	122.0	121.7	121.4	121.0
65°	108.3	107.6	106.9	106.3	105.9	105.5	105.1	104.7
67.5°	92.4	91.8	91.3	90.8	90.5	90.2	89.8	89.5
70°	82.0	81.4	80.9	80.5	80.2	79.8	79.5	79.1
72.5°	72.2	71.7	71.1	70.7	70.4	70.2	69.9	69.6
75°	57.0	56.5	56.0	55.8	56.0	56.2	56.3	56.5
77.5°	43.3	43.1	42.9	42.6	42.4	42.2	42.0	41.7
80°	34.5	34.2	34.0	33.7	33.6	33.4	33.3	33.1
82.5°	25.7	25.3	25.0	24.9	24.9	24.8	24.8	24.8
85°	13.5	13.3	13.1	12.9	12.8	12.8	12.7	12.6
87.5°	7.6	7.2	7.2	7.2	7.1	7.1	7.1	7.0
90°	19.8	18.6	19.8	20.4	20.4	20.4	20.4	20.4
92.5°	54.0	46.3	41.1	37.3	36.8	34.8	35.3	34.3
95°	162.2	124.5	98.5	84.8	76.8	71.9	69.9	70.6
97.5°	378.6	309.7	242.7	198.0	168.4	153.2	144.2	138.9
100°	565.4	488.6	403.8	328.8	277.4	250.8	232.8	221.7
102.5°	687.8	670.4	608.3	528.9	473.1	427.6	405.2	390.1
105°	752.4	822.4	830.4	810.0	771.6	733.2	706.5	697.9
107.5°	705.8	811.2	875.6	905.6	910.5	908.3	903.0	891.4
110°	665.7	776.6	855.8	906.6	933.2	945.0	950.5	949.9





TEST NUMBER: P331266-927

CATALOG NUMBER: SA2XXDIP-C290D725U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	629.1	735.4	820.1	878.4	915.4	935.1	945.6	949.0
115°	583.9	679.3	760.4	824.2	868.2	896.7	912.8	918.4
117.5°	550.0	633.7	707.3	767.1	812.0	842.1	859.0	863.7
120°	533.1	610.0	675.6	732.0	775.3	804.4	822.4	828.5
122.5°	519.8	590.2	652.3	703.2	742.1	770.7	786.7	791.9
125°	500.3	564.1	618.6	665.0	701.0	724.5	740.0	745.0
127.5°	481.2	538.8	590.3	633.1	664.5	686.5	699.9	703.9
130°	468.7	522.0	570.9	611.8	642.1	663.2	675.6	680.6
132.5°	456.9	506.2	551.1	589.5	619.4	640.4	651.8	656.2
135°	440.3	481.2	522.0	556.7	583.4	603.8	614.9	617.4
137.5°	427.1	461.2	493.7	523.9	548.2	565.8	575.5	579.2
140°	418.6	448.4	476.8	504.1	523.9	540.0	549.3	553.0
142.5°	411.7	437.0	461.4	484.3	503.1	517.7	526.0	526.7
145°	401.9	422.3	441.6	459.5	474.4	484.9	491.1	492.9
147.5°	394.3	410.4	425.4	438.6	450.8	459.2	463.4	464.5
150°	388.9	402.5	415.5	426.7	435.9	443.4	447.1	447.7
152.5°	383.4	396.1	407.1	416.8	424.1	430.5	433.2	433.3
155°	375.9	385.8	395.1	401.9	408.7	413.0	415.5	414.3
157.5°	367.1	375.4	383.2	388.5	393.3	397.0	398.1	398.1
160°	361.6	368.4	375.3	379.6	384.0	387.1	387.6	387.6
162.5°	356.2	362.0	367.8	371.2	375.5	377.6	378.3	377.7
165°	348.0	352.4	356.7	359.2	361.6	364.1	364.1	363.5
167.5°	340.2	343.6	346.5	348.8	349.9	351.3	351.1	350.4
170°	336.3	338.1	340.6	341.8	342.5	344.3	343.6	342.5
172.5°	331.8	333.2	335.2	335.9	336.5	337.4	336.8	336.0
175°	326.9	327.6	328.2	328.8	328.8	329.5	328.8	327.6
177.5°	323.5	323.5	324.0	324.0	324.0	324.0	323.5	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0

(END OF REPORT)