

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333530

Luminaire Tested: **S125RDIP-S610D590U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333530
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D590U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4423.7 lumens
Efficiency: N/A
Efficacy: 134.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333530

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333530

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	60	53	48	52	47	43	45	41	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6497	6497	6497
5°	6512	6438	6477
10°	6462	6378	6378
15°	6386	6248	6197
20°	6287	6068	5994
25°	6173	5890	5761
30°	6029	5683	5502
35°	5882	5469	5211
40°	5746	5246	4926
45°	5580	4996	4615
50°	5413	4725	4290
55°	5219	4466	3944
60°	5025	4151	3573
65°	4795	3785	3147
70°	4534	3329	2712
75°	4172	2805	2256
80°	3675	2205	1893
85°	3097	1801	1690



TEST NUMBER: P333530

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	2.1
10°-20°	264.3	6.0
20°-30°	383.3	8.7
30°-40°	436.9	9.9
40°-50°	425.9	9.6
50°-60°	358.5	8.1
60°-70°	251.3	5.7
70°-80°	129.2	2.9
80°-90°	34.2	0.8
90°-100°	49.1	1.1
100°-110°	145.0	3.3
110°-120°	245.6	5.6
120°-130°	323.2	7.3
130°-140°	362.1	8.2
140°-150°	354.9	8.0
150°-160°	298.1	6.7
160°-170°	198.2	4.5
170°-180°	69.4	1.6
0°-30°	742.3	16.8
0°-40°	1179.2	26.7
0°-60°	1963.5	44.4
0°-90°	2378.1	53.8
90°-120°	439.7	9.9
90°-150°	1479.9	33.5
90°-180°	2046.0	46.3
0°-180°	4423.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1004	1001	993	1000	999	95
15°	955	950	934	933	927	269
25°	866	854	827	817	808	398
35°	746	727	694	672	661	467
45°	611	588	547	518	505	471
55°	464	438	397	364	350	414
65°	314	287	248	218	206	311
75°	167	144	112	96	90	177
85°	42	29	24	24	23	47
90°	1	5	9	12	14	4
95°	37	38	44	48	49	40
105°	130	133	136	140	142	139
115°	246	248	249	249	248	243
125°	359	362	363	362	361	321
135°	467	470	471	470	468	360
145°	565	568	569	569	568	353
155°	647	647	648	650	647	298
165°	703	702	703	705	702	198
175°	731	729	729	732	728	69
180°	733	733	733	733	733	



TEST NUMBER: P333530

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1007.8	1007.4	1007.0	1006.6	1006.2	1005.3	1003.9	1002.6	1001.2	999.9	1001.2
5°	1004.4	1003.8	1003.1	1002.4	1001.7	1000.5	998.6	996.8	994.9	993.0	994.7
7.5°	994.6	993.9	993.3	992.6	992.0	990.6	988.3	986.1	983.9	981.6	982.8
10°	985.4	984.9	984.4	983.9	983.4	982.0	979.6	977.3	974.9	972.5	973.0
12.5°	975.1	974.5	973.8	973.2	972.5	970.6	967.5	964.3	961.1	957.9	958.3
15°	955.1	954.0	953.0	952.0	951.0	948.7	945.2	941.6	938.1	934.5	934.4
17.5°	932.4	930.9	929.3	927.8	926.2	923.2	918.7	914.3	909.8	905.4	904.5
20°	914.8	913.1	911.4	909.7	908.0	904.5	899.1	893.7	888.3	882.9	882.0
22.5°	895.3	893.6	892.0	890.3	888.6	884.9	879.2	873.6	867.9	862.2	860.6
25°	866.2	863.6	861.1	858.6	856.0	851.6	845.4	839.1	832.9	826.6	824.5
27.5°	832.7	829.7	826.6	823.5	820.4	815.6	808.9	802.2	795.5	788.8	785.7
30°	808.4	805.2	802.0	798.8	795.6	790.4	783.3	776.3	769.2	762.1	758.2
32.5°	784.7	781.0	777.2	773.5	769.7	764.2	757.0	749.8	742.5	735.3	731.0
35°	746.1	742.1	738.0	734.0	729.9	724.1	716.5	708.9	701.3	693.7	688.8
37.5°	708.3	703.3	698.4	693.5	688.6	682.2	674.3	666.5	658.7	650.8	645.0
40°	681.5	676.5	671.4	666.3	661.3	654.7	646.6	638.5	630.4	622.3	615.9
42.5°	653.6	648.4	643.2	638.0	632.8	626.0	617.6	609.2	600.9	592.5	586.3
45°	610.9	606.0	601.1	596.2	591.3	584.2	574.9	565.6	556.3	547.0	540.3
47.5°	566.7	561.5	556.3	551.2	546.0	538.7	529.4	520.0	510.7	501.3	494.4
50°	538.7	533.1	527.5	522.0	516.4	508.8	499.2	489.6	479.9	470.3	463.2
52.5°	508.3	502.6	496.9	491.2	485.5	478.1	469.0	459.9	450.8	441.7	434.1
55°	463.5	458.1	452.7	447.3	441.9	434.4	425.0	415.5	406.1	396.6	389.0
57.5°	418.2	412.4	406.6	400.9	395.1	387.6	378.5	369.4	360.3	351.2	343.7
60°	389.0	383.1	377.2	371.3	365.4	357.9	348.7	339.6	330.5	321.4	314.0
62.5°	358.0	352.4	346.7	341.1	335.5	328.0	318.8	309.5	300.3	291.0	284.1
65°	313.8	308.1	302.3	296.6	290.8	283.5	274.5	265.6	256.6	247.7	240.9
67.5°	269.9	264.1	258.4	252.7	246.9	239.8	231.2	222.6	214.0	205.4	199.3
70°	240.1	234.4	228.6	222.9	217.1	210.0	201.6	193.2	184.7	176.3	171.0
72.5°	210.9	205.3	199.7	194.1	188.5	181.7	173.8	165.9	158.0	150.1	145.3
75°	167.2	162.1	157.0	152.0	146.9	140.8	133.7	126.6	119.5	112.4	108.7
77.5°	123.7	119.6	115.6	111.5	107.5	102.6	96.9	91.3	85.6	79.9	77.3
80°	98.8	94.7	90.7	86.6	82.6	78.2	73.4	68.7	64.0	59.3	57.7
82.5°	74.5	70.8	67.2	63.5	59.9	56.4	53.2	49.9	46.7	43.5	42.8
85°	41.8	38.7	35.7	32.7	29.6	27.7	26.8	26.0	25.2	24.3	24.1
87.5°	14.1	13.4	12.6	11.9	11.1	10.8	10.8	10.9	10.9	10.9	11.1
90°	0.6	1.6	2.6	3.6	4.6	5.6	6.5	7.4	8.2	9.1	9.8
92.5°	13.8	14.5	15.2	15.9	16.6	17.5	18.6	19.7	20.8	21.9	22.7
95°	37.1	37.3	37.6	37.8	38.1	38.9	40.1	41.4	42.7	43.9	44.8
97.5°	61.6	61.7	61.8	61.9	62.0	62.9	64.7	66.4	68.2	69.9	70.8
100°	79.9	79.9	79.9	79.9	79.9	80.7	82.3	84.0	85.6	87.3	88.4
102.5°	99.5	100.0	100.5	101.0	101.5	102.2	103.0	103.9	104.7	105.5	106.8
105°	130.1	130.7	131.3	132.0	132.6	133.3	134.1	134.8	135.6	136.3	137.1
107.5°	163.8	164.5	165.1	165.7	166.4	167.0	167.6	168.1	168.7	169.3	169.7
110°	187.1	187.7	188.4	189.0	189.7	190.2	190.5	190.9	191.3	191.7	192.1



TEST NUMBER: P333530

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	210.8	211.2	211.5	211.8	212.2	212.6	213.1	213.5	214.0	214.5	214.7
115°	245.9	246.4	246.9	247.4	247.9	248.3	248.5	248.8	249.0	249.3	249.2
117.5°	281.0	281.2	281.5	281.7	281.9	282.2	282.4	282.6	282.8	283.1	283.2
120°	302.9	303.6	304.2	304.8	305.5	305.8	306.0	306.1	306.2	306.3	306.3
122.5°	326.7	326.9	327.1	327.3	327.6	327.8	328.2	328.5	328.8	329.2	329.1
125°	358.8	359.6	360.3	361.1	361.9	362.3	362.4	362.6	362.7	362.8	362.6
127.5°	393.1	393.5	393.9	394.3	394.8	395.1	395.2	395.4	395.5	395.7	395.6
130°	413.6	414.2	414.9	415.5	416.1	416.6	416.8	417.1	417.3	417.6	417.5
132.5°	434.1	435.2	436.2	437.2	438.3	438.8	438.7	438.7	438.6	438.6	438.5
135°	466.6	467.4	468.2	468.9	469.7	470.1	470.3	470.4	470.5	470.6	470.6
137.5°	497.2	498.0	498.7	499.4	500.2	500.7	501.0	501.2	501.5	501.8	501.9
140°	516.8	517.5	518.1	518.7	519.4	519.9	520.3	520.7	521.0	521.4	521.7
142.5°	536.5	537.0	537.5	538.1	538.6	539.1	539.6	540.1	540.6	541.0	541.2
145°	565.3	565.8	566.4	566.9	567.4	567.8	568.2	568.6	569.0	569.3	569.3
147.5°	592.0	592.3	592.6	592.9	593.2	593.4	593.7	594.1	594.4	594.7	595.0
150°	609.8	609.7	609.6	609.5	609.3	609.5	610.0	610.5	611.0	611.5	611.5
152.5°	624.4	624.6	624.8	625.0	625.1	625.3	625.5	625.7	625.9	626.2	626.5
155°	646.9	646.9	646.9	646.9	646.9	647.0	647.1	647.2	647.4	647.5	648.0
157.5°	667.0	666.7	666.4	666.2	665.9	665.8	665.9	666.1	666.2	666.3	666.8
160°	678.9	678.5	678.1	677.7	677.3	677.2	677.3	677.5	677.6	677.7	678.2
162.5°	689.4	689.1	688.8	688.5	688.2	688.1	688.1	688.2	688.2	688.2	688.8
165°	703.4	703.1	702.9	702.6	702.4	702.3	702.4	702.6	702.7	702.8	703.3
167.5°	715.3	714.8	714.2	713.7	713.2	713.0	713.0	713.0	713.0	713.0	713.7
170°	721.6	721.1	720.6	720.1	719.6	719.4	719.4	719.4	719.4	719.4	720.1
172.5°	726.2	725.7	725.2	724.7	724.2	723.9	723.9	723.9	723.9	723.9	724.7
175°	731.3	730.8	730.3	729.8	729.3	729.1	729.1	729.1	729.1	729.1	729.8
177.5°	734.0	733.6	733.2	732.8	732.3	732.1	732.0	731.9	731.8	731.7	732.3
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333530

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1002.6	1003.9	1005.3	1005.9	1005.8	1005.6	1005.5	1005.4
5°	996.4	998.1	999.8	1000.5	1000.1	999.8	999.5	999.1
7.5°	984.0	985.2	986.4	986.8	986.4	986.0	985.7	985.3
10°	973.5	974.0	974.6	974.6	974.0	973.5	973.0	972.5
12.5°	958.7	959.1	959.4	959.2	958.4	957.7	956.9	956.1
15°	934.2	934.0	933.9	933.0	931.5	930.0	928.5	926.9
17.5°	903.7	902.8	902.0	900.9	899.7	898.4	897.2	895.9
20°	881.2	880.3	879.5	878.3	876.8	875.3	873.8	872.2
22.5°	858.9	857.2	855.6	854.1	852.9	851.6	850.4	849.1
25°	822.3	820.1	817.9	815.8	814.0	812.1	810.3	808.4
27.5°	782.7	779.6	776.5	774.1	772.3	770.5	768.7	766.9
30°	754.3	750.4	746.5	743.8	742.3	740.8	739.3	737.8
32.5°	726.7	722.5	718.2	715.1	713.1	711.2	709.3	707.4
35°	683.9	679.0	674.1	670.5	668.1	665.7	663.4	661.0
37.5°	639.1	633.2	627.3	623.2	620.9	618.7	616.4	614.1
40°	609.4	603.0	596.6	592.4	590.4	588.3	586.3	584.3
42.5°	580.2	574.0	567.9	563.3	560.4	557.4	554.4	551.5
45°	533.5	526.8	520.0	515.4	512.9	510.3	507.8	505.3
47.5°	487.4	480.4	473.5	468.6	465.8	463.0	460.2	457.4
50°	456.1	449.0	441.9	437.1	434.6	432.1	429.5	427.0
52.5°	426.5	418.8	411.2	406.1	403.6	401.1	398.5	396.0
55°	381.4	373.8	366.2	361.1	358.4	355.7	353.0	350.3
57.5°	336.3	328.9	321.5	316.5	314.1	311.7	309.4	307.0
60°	306.5	299.1	291.7	286.7	284.2	281.6	279.1	276.6
62.5°	277.2	270.3	263.4	258.7	256.2	253.7	251.1	248.6
65°	234.2	227.4	220.7	216.0	213.5	211.0	208.4	205.9
67.5°	193.1	186.9	180.7	176.6	174.6	172.6	170.5	168.5
70°	165.8	160.6	155.3	151.7	149.7	147.7	145.6	143.6
72.5°	140.5	135.6	130.8	127.7	126.4	125.0	123.7	122.3
75°	105.0	101.3	97.6	95.1	94.0	92.8	91.6	90.4
77.5°	74.7	72.1	69.5	67.8	66.9	66.0	65.2	64.3
80°	56.2	54.7	53.2	52.3	51.9	51.6	51.2	50.9
82.5°	42.0	41.3	40.6	40.2	40.0	39.8	39.6	39.4
85°	24.0	23.8	23.6	23.5	23.3	23.1	23.0	22.8
87.5°	11.2	11.3	11.5	11.5	11.4	11.4	11.3	11.2
90°	10.4	11.0	11.7	12.2	12.6	12.9	13.3	13.7
92.5°	23.6	24.4	25.3	25.8	26.1	26.4	26.6	26.9
95°	45.7	46.6	47.5	48.0	48.3	48.6	48.8	49.1
97.5°	71.6	72.5	73.3	73.8	73.9	74.1	74.2	74.4
100°	89.6	90.7	91.8	92.5	92.8	93.1	93.3	93.6
102.5°	108.0	109.3	110.5	111.3	111.7	112.0	112.4	112.7
105°	137.9	138.6	139.4	140.0	140.3	140.7	141.1	141.5
107.5°	170.1	170.5	170.8	171.0	171.0	171.0	170.9	170.9
110°	192.4	192.8	193.2	193.3	193.2	193.1	192.9	192.8



TEST NUMBER: P333530

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	214.9	215.0	215.2	215.2	215.0	214.7	214.5	214.3
115°	249.0	248.9	248.8	248.7	248.5	248.4	248.3	248.2
117.5°	283.3	283.4	283.5	283.3	282.8	282.3	281.8	281.2
120°	306.3	306.3	306.3	306.1	305.6	305.1	304.6	304.1
122.5°	329.0	328.9	328.8	328.5	328.1	327.7	327.3	326.9
125°	362.3	362.1	361.8	361.6	361.5	361.4	361.2	361.1
127.5°	395.4	395.3	395.2	395.0	394.7	394.5	394.2	394.0
130°	417.3	417.2	417.1	416.9	416.6	416.4	416.1	415.9
132.5°	438.3	438.2	438.1	437.8	437.5	437.1	436.8	436.4
135°	470.6	470.6	470.6	470.4	469.9	469.4	468.9	468.4
137.5°	502.1	502.2	502.4	502.2	501.5	500.9	500.3	499.6
140°	521.9	522.2	522.4	522.2	521.6	521.0	520.3	519.7
142.5°	541.3	541.5	541.6	541.4	540.8	540.1	539.5	538.9
145°	569.3	569.3	569.3	569.1	568.8	568.4	568.0	567.6
147.5°	595.3	595.6	595.9	595.6	594.7	593.9	593.0	592.2
150°	611.5	611.5	611.5	611.4	611.2	610.9	610.7	610.4
152.5°	626.8	627.1	627.4	627.3	626.8	626.4	625.9	625.5
155°	648.5	649.0	649.5	649.5	648.8	648.2	647.5	646.9
157.5°	667.3	667.8	668.3	668.2	667.3	666.5	665.7	664.8
160°	678.7	679.2	679.7	679.7	679.1	678.4	677.8	677.2
162.5°	689.4	690.0	690.7	690.6	689.9	689.1	688.4	687.6
165°	703.8	704.3	704.9	704.7	704.0	703.2	702.4	701.7
167.5°	714.5	715.3	716.0	716.0	715.2	714.4	713.6	712.9
170°	720.9	721.6	722.4	722.3	721.5	720.6	719.7	718.8
172.5°	725.5	726.2	727.0	727.0	726.2	725.4	724.6	723.8
175°	730.6	731.3	732.1	732.0	731.2	730.3	729.4	728.5
177.5°	732.9	733.5	734.1	734.1	733.4	732.7	731.9	731.2
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1

(END OF REPORT)